

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333435-930

Luminaire Tested: **S125DIW-S1090D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333435-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D470U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4946.2 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 46.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8985	8985	8985
5°	9005	8919	8976
10°	8950	8857	8907
15°	8852	8750	8787
20°	8715	8601	8616
25°	8565	8424	8416
30°	8380	8232	8192
35°	8183	8027	7914
40°	7981	7804	7692
45°	7761	7600	7448
50°	7519	7354	7133
55°	7287	7076	6877
60°	7009	6795	6554
65°	6677	6460	6240
70°	6360	6069	5861
75°	5794	5602	5410
80°	5159	5077	4950
85°	4483	4565	4320



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.2	2.7
10°-20°	370.5	7.5
20°-30°	547.1	11.1
30°-40°	638.4	12.9
40°-50°	641.2	13.0
50°-60°	562.8	11.4
60°-70°	419.4	8.5
70°-80°	239.8	4.8
80°-90°	70.8	1.4
90°-100°	31.8	0.6
100°-110°	93.9	1.9
110°-120°	159.1	3.2
120°-130°	209.4	4.2
130°-140°	234.6	4.7
140°-150°	229.9	4.6
150°-160°	193.1	3.9
160°-170°	128.4	2.6
170°-180°	44.9	0.9
0°-30°	1048.8	21.2
0°-40°	1687.2	34.1
0°-60°	2891.2	58.5
0°-90°	3621.1	73.2
90°-120°	284.8	5.8
90°-150°	958.7	19.4
90°-180°	1325.0	26.8
0°-180°	4946.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1391	1391	1391	1391	1391	
5°	1389	1386	1376	1385	1385	132
15°	1324	1320	1309	1314	1314	373
25°	1202	1196	1182	1184	1181	553
35°	1038	1033	1018	1012	1004	649
45°	850	845	832	819	816	655
55°	647	643	628	619	611	578
65°	437	434	423	413	408	433
75°	232	230	224	221	217	248
85°	60	62	62	60	58	68
90°	0	3	6	8	9	5
95°	24	25	28	31	32	26
105°	84	86	88	90	92	90
115°	159	161	162	161	161	157
125°	232	235	235	234	234	208
135°	302	304	305	305	303	233
145°	366	368	369	369	368	229
155°	419	419	419	421	419	193
165°	456	455	455	457	454	128
175°	474	472	472	474	472	45
180°	475	475	475	475	475	



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1394.7	1394.2	1393.5	1392.9	1392.4	1391.1	1389.1	1387.2	1385.2	1383.2	1385.2
5°	1389.0	1388.5	1388.0	1387.6	1387.1	1385.6	1383.2	1380.7	1378.3	1375.8	1378.0
7.5°	1376.2	1375.7	1375.2	1374.8	1374.3	1372.6	1369.9	1367.3	1364.6	1361.9	1364.1
10°	1364.8	1364.3	1363.8	1363.3	1362.9	1361.2	1358.5	1355.8	1353.2	1350.5	1352.4
12.5°	1350.7	1349.8	1348.9	1348.0	1347.2	1345.5	1343.0	1340.5	1338.0	1335.5	1337.1
15°	1324.0	1323.3	1322.6	1321.8	1321.1	1319.4	1316.7	1314.0	1311.3	1308.6	1309.9
17.5°	1293.5	1292.4	1291.3	1290.2	1289.2	1287.2	1284.4	1281.7	1278.9	1276.0	1277.6
20°	1268.0	1267.5	1267.0	1266.5	1266.0	1264.1	1260.9	1257.8	1254.6	1251.4	1253.1
22.5°	1242.4	1241.5	1240.6	1239.7	1238.8	1236.9	1234.0	1230.9	1228.0	1225.0	1226.1
25°	1201.9	1200.7	1199.5	1198.2	1197.0	1194.8	1191.6	1188.5	1185.3	1182.1	1182.6
27.5°	1154.5	1153.8	1153.1	1152.3	1151.6	1149.7	1146.3	1143.0	1139.8	1136.5	1136.6
30°	1123.7	1123.0	1122.3	1121.5	1120.8	1118.6	1114.9	1111.3	1107.6	1103.9	1103.4
32.5°	1090.3	1089.2	1088.0	1086.9	1085.8	1083.6	1080.3	1077.0	1073.7	1070.5	1069.6
35°	1037.9	1036.9	1035.9	1034.9	1034.0	1031.8	1028.3	1024.9	1021.5	1018.1	1016.8
37.5°	983.5	982.3	981.0	979.8	978.6	976.4	973.1	970.0	966.7	963.5	961.6
40°	946.6	945.3	944.1	942.9	941.7	939.3	935.9	932.5	929.0	925.6	923.4
42.5°	906.9	905.9	904.9	903.8	902.8	900.6	897.2	893.7	890.3	886.9	884.8
45°	849.7	848.7	847.7	846.8	845.8	843.8	840.9	838.0	835.0	832.1	829.2
47.5°	788.1	788.1	788.1	788.2	788.2	786.5	783.0	779.4	775.9	772.4	769.4
50°	748.4	747.7	747.0	746.2	745.5	743.6	740.7	737.8	734.8	731.9	728.7
52.5°	707.9	707.4	706.9	706.3	705.8	703.9	700.8	697.7	694.6	691.4	688.6
55°	647.2	646.5	645.7	645.0	644.2	642.1	638.7	635.3	631.9	628.4	626.2
57.5°	583.1	582.7	582.4	582.0	581.6	579.9	577.0	574.1	571.3	568.3	565.5
60°	542.6	541.6	540.6	539.6	538.7	536.9	534.2	531.5	528.8	526.1	523.7
62.5°	500.3	499.5	498.8	498.0	497.3	495.7	493.3	491.1	488.8	486.5	483.8
65°	436.9	436.4	435.9	435.5	435.0	433.4	430.7	428.0	425.3	422.7	420.4
67.5°	375.5	374.5	373.5	372.4	371.5	369.9	367.9	365.9	363.9	361.9	360.0
70°	336.8	335.6	334.4	333.1	331.9	330.2	328.0	325.8	323.6	321.4	319.9
72.5°	294.6	293.7	292.9	292.0	291.2	290.1	288.7	287.2	285.8	284.4	282.7
75°	232.2	231.7	231.2	230.7	230.2	229.4	228.2	227.0	225.8	224.5	223.8
77.5°	174.8	174.6	174.4	174.2	174.0	173.6	172.8	172.2	171.5	170.8	170.4
80°	138.7	138.7	138.7	138.7	138.7	138.4	137.9	137.5	137.0	136.5	136.2
82.5°	107.0	106.6	106.2	105.8	105.4	105.2	105.1	105.0	104.8	104.8	104.4
85°	60.5	60.7	61.0	61.2	61.5	61.6	61.6	61.6	61.6	61.6	61.4
87.5°	23.8	24.0	24.1	24.2	24.4	24.4	24.3	24.2	24.1	24.1	24.1
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	6.0	6.4
92.5°	9.0	9.4	9.9	10.4	10.8	11.3	12.1	12.8	13.5	14.2	14.8
95°	24.1	24.2	24.4	24.5	24.7	25.2	26.0	26.8	27.6	28.5	29.0
97.5°	39.9	39.9	40.0	40.1	40.2	40.8	41.9	43.0	44.2	45.3	45.8
100°	51.8	51.8	51.8	51.8	51.8	52.3	53.3	54.4	55.4	56.5	57.3
102.5°	64.4	64.7	65.1	65.5	65.8	66.2	66.8	67.3	67.8	68.3	69.1
105°	84.2	84.6	85.0	85.4	85.9	86.3	86.8	87.3	87.8	88.3	88.8
107.5°	106.2	106.6	107.0	107.4	107.8	108.2	108.5	108.9	109.3	109.7	109.9
110°	121.2	121.6	122.1	122.5	122.9	123.2	123.4	123.7	123.9	124.2	124.4



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	136.6	136.8	137.0	137.2	137.5	137.7	138.0	138.4	138.6	138.9	139.1
115°	159.2	159.6	160.0	160.3	160.6	160.9	161.0	161.2	161.3	161.5	161.4
117.5°	182.1	182.1	182.3	182.5	182.6	182.8	183.0	183.0	183.2	183.4	183.4
120°	196.2	196.7	197.1	197.5	197.9	198.1	198.2	198.3	198.4	198.4	198.4
122.5°	211.6	211.7	211.9	212.1	212.1	212.4	212.5	212.8	213.0	213.2	213.1
125°	232.4	232.9	233.4	233.9	234.4	234.7	234.8	234.9	235.0	235.1	234.9
127.5°	254.6	254.9	255.2	255.4	255.8	255.9	256.0	256.1	256.2	256.3	256.2
130°	267.9	268.3	268.7	269.1	269.5	269.9	270.0	270.2	270.4	270.5	270.4
132.5°	281.2	281.8	282.6	283.2	283.9	284.2	284.2	284.1	284.1	284.1	284.0
135°	302.2	302.8	303.3	303.8	304.3	304.5	304.6	304.7	304.8	304.8	304.8
137.5°	322.0	322.5	323.0	323.5	324.0	324.3	324.5	324.7	324.8	325.1	325.1
140°	334.8	335.2	335.6	336.0	336.4	336.8	337.0	337.3	337.5	337.8	337.9
142.5°	347.5	347.8	348.2	348.5	348.9	349.2	349.5	349.8	350.2	350.5	350.6
145°	366.2	366.6	366.9	367.2	367.5	367.8	368.0	368.3	368.5	368.8	368.8
147.5°	383.5	383.7	383.8	384.0	384.3	384.4	384.6	384.8	385.0	385.2	385.4
150°	395.0	394.9	394.8	394.8	394.7	394.8	395.2	395.5	395.8	396.2	396.2
152.5°	404.5	404.6	404.7	404.8	405.0	405.0	405.2	405.4	405.4	405.6	405.8
155°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.2	419.3	419.4	419.7
157.5°	432.0	431.9	431.7	431.5	431.3	431.3	431.4	431.5	431.5	431.6	431.9
160°	439.8	439.5	439.2	439.0	438.7	438.6	438.7	438.8	438.9	439.0	439.4
162.5°	446.5	446.4	446.2	446.0	445.8	445.7	445.7	445.7	445.8	445.8	446.2
165°	455.6	455.4	455.3	455.1	454.9	454.9	455.0	455.1	455.2	455.3	455.6
167.5°	463.3	463.0	462.7	462.4	462.0	461.9	461.9	461.9	461.9	461.9	462.4
170°	467.4	467.1	466.8	466.4	466.1	465.9	465.9	465.9	465.9	465.9	466.4
172.5°	470.4	470.1	469.8	469.4	469.1	469.0	469.0	469.0	469.0	469.0	469.4
175°	473.8	473.4	473.0	472.7	472.4	472.2	472.2	472.2	472.2	472.2	472.7
177.5°	475.4	475.2	474.9	474.7	474.3	474.2	474.2	474.1	474.0	473.9	474.3
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2	1391.2
2.5°	1387.2	1389.1	1391.1	1392.0	1391.8	1391.6	1391.4	1391.2
5°	1380.2	1382.4	1384.6	1385.6	1385.4	1385.1	1384.9	1384.6
7.5°	1366.2	1368.4	1370.5	1371.5	1371.3	1371.0	1370.8	1370.5
10°	1354.4	1356.3	1358.3	1359.2	1358.9	1358.7	1358.5	1358.2
12.5°	1338.6	1340.2	1341.7	1342.6	1342.5	1342.4	1342.4	1342.3
15°	1311.1	1312.3	1313.5	1314.2	1314.2	1314.2	1314.2	1314.2
17.5°	1279.1	1280.6	1282.1	1282.3	1281.1	1279.9	1278.6	1277.4
20°	1254.8	1256.5	1258.3	1258.5	1257.3	1256.1	1254.8	1253.6
22.5°	1227.3	1228.4	1229.5	1229.6	1228.8	1228.0	1227.2	1226.3
25°	1183.1	1183.6	1184.1	1183.9	1183.2	1182.4	1181.7	1181.0
27.5°	1136.7	1136.8	1136.9	1136.6	1135.9	1135.1	1134.4	1133.7
30°	1102.9	1102.4	1102.0	1101.4	1100.7	1099.9	1099.2	1098.5
32.5°	1068.7	1067.8	1067.0	1065.8	1064.5	1063.2	1061.8	1060.5
35°	1015.6	1014.4	1013.2	1011.6	1009.7	1007.7	1005.8	1003.8
37.5°	959.9	958.1	956.3	954.8	953.7	952.5	951.4	950.3
40°	921.2	919.0	916.8	915.3	914.6	913.9	913.1	912.4
42.5°	882.9	880.8	878.9	877.3	876.2	875.1	873.9	872.8
45°	826.2	823.3	820.4	818.5	817.7	817.0	816.3	815.5
47.5°	766.5	763.4	760.5	758.1	756.4	754.7	753.0	751.3
50°	725.5	722.4	719.2	716.7	715.0	713.3	711.6	709.9
52.5°	685.8	683.1	680.3	677.9	676.0	674.1	672.2	670.3
55°	624.0	621.8	619.6	617.7	616.0	614.2	612.5	610.8
57.5°	562.7	559.9	557.0	555.1	554.2	553.3	552.4	551.4
60°	521.2	518.8	516.3	514.2	512.5	510.8	509.1	507.4
62.5°	481.2	478.6	475.9	473.9	472.6	471.3	469.9	468.6
65°	418.2	416.0	413.8	412.2	411.2	410.3	409.3	408.3
67.5°	358.2	356.3	354.4	353.2	352.6	352.0	351.5	350.9
70°	318.5	317.0	315.5	314.3	313.3	312.3	311.4	310.4
72.5°	281.1	279.4	277.8	276.5	275.5	274.5	273.5	272.6
75°	223.1	222.3	221.6	220.7	219.7	218.7	217.8	216.8
77.5°	169.9	169.5	169.1	168.5	167.8	167.1	166.4	165.8
80°	136.0	135.7	135.5	135.1	134.6	134.1	133.6	133.1
82.5°	103.9	103.5	103.1	102.7	102.6	102.6	102.5	102.3
85°	61.1	60.9	60.7	60.3	59.8	59.3	58.8	58.3
87.5°	24.2	24.3	24.4	24.3	24.0	23.6	23.2	22.9
90°	6.8	7.2	7.6	7.9	8.2	8.4	8.6	8.9
92.5°	15.2	15.8	16.4	16.7	16.9	17.0	17.3	17.4
95°	29.6	30.2	30.7	31.1	31.3	31.5	31.6	31.8
97.5°	46.4	47.0	47.5	47.8	47.9	48.0	48.1	48.2
100°	58.0	58.8	59.5	59.9	60.1	60.3	60.4	60.6
102.5°	70.0	70.8	71.6	72.1	72.3	72.6	72.8	73.1
105°	89.3	89.8	90.3	90.7	90.9	91.2	91.4	91.6
107.5°	110.1	110.4	110.6	110.8	110.8	110.7	110.7	110.7
110°	124.7	124.9	125.1	125.2	125.1	125.1	125.0	124.9



TEST NUMBER: P333435-930

CATALOG NUMBER: S125DIW-S1090D470U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	139.2	139.3	139.4	139.4	139.3	139.1	138.9	138.8
115°	161.3	161.3	161.2	161.1	161.0	160.9	160.9	160.8
117.5°	183.5	183.5	183.6	183.5	183.2	182.9	182.5	182.1
120°	198.4	198.4	198.4	198.3	198.0	197.6	197.3	197.0
122.5°	213.1	213.0	213.0	212.8	212.5	212.3	212.0	211.7
125°	234.7	234.6	234.4	234.2	234.2	234.1	234.0	233.9
127.5°	256.2	256.1	256.0	255.8	255.7	255.5	255.4	255.2
130°	270.4	270.3	270.2	270.0	269.9	269.7	269.5	269.4
132.5°	283.9	283.8	283.7	283.6	283.4	283.2	282.9	282.7
135°	304.8	304.8	304.8	304.7	304.4	304.0	303.7	303.4
137.5°	325.2	325.3	325.5	325.3	324.9	324.5	324.0	323.6
140°	338.1	338.3	338.4	338.3	337.9	337.5	337.0	336.6
142.5°	350.7	350.7	350.8	350.7	350.3	349.8	349.4	349.0
145°	368.8	368.8	368.8	368.7	368.4	368.2	367.9	367.7
147.5°	385.6	385.8	386.0	385.8	385.2	384.7	384.1	383.6
150°	396.2	396.2	396.2	396.1	395.9	395.7	395.6	395.4
152.5°	406.0	406.2	406.3	406.3	406.0	405.8	405.4	405.1
155°	420.0	420.4	420.7	420.7	420.3	419.9	419.5	419.1
157.5°	432.3	432.6	432.9	432.8	432.3	431.7	431.2	430.6
160°	439.7	440.0	440.3	440.3	439.9	439.4	439.0	438.6
162.5°	446.6	446.9	447.4	447.4	446.9	446.4	445.9	445.4
165°	455.9	456.2	456.6	456.5	456.0	455.5	455.0	454.5
167.5°	462.8	463.3	463.8	463.8	463.3	462.8	462.3	461.8
170°	466.9	467.4	468.0	467.9	467.3	466.8	466.2	465.6
172.5°	469.9	470.4	470.9	470.9	470.3	469.9	469.4	468.9
175°	473.2	473.8	474.3	474.2	473.6	473.0	472.5	471.9
177.5°	474.7	475.2	475.6	475.5	475.1	474.6	474.1	473.7
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8

(END OF REPORT)