

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333436-930

Luminaire Tested: **S125DIW-S1090D770U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333436-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6162.7 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333436-930
CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	59
1	100	96	92	89	93	90	86	83	78	76	73	67	66	64	58	56	55	51
2	91	84	78	73	85	79	73	69	69	65	61	60	57	54	51	49	47	43
3	84	74	67	61	78	69	63	58	61	56	52	53	49	46	45	43	40	36
4	77	66	58	52	71	62	55	49	54	49	44	47	43	39	41	37	35	31
5	70	59	51	44	65	55	48	42	49	43	38	42	38	34	37	33	30	27
6	65	53	45	39	60	50	42	37	44	38	34	38	34	30	33	30	27	24
7	60	48	40	34	56	45	38	33	40	34	30	35	30	27	30	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	31	26	33	28	24	29	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8373	8373	8373	8373
5°	9697	8401	7356	8401
10°	11281	8358	6445	8358
15°	12488	8297	5945	8297
20°	13978	8199	5544	8199
25°	16376	8089	5349	8089
30°	17687	7982	5179	7982
35°	14542	7779	5067	7779
40°	10336	7497	4945	7497
45°	7941	7117	4875	7117
50°	6779	6646	4866	6646
55°	6035	6184	4908	6184
60°	5444	5679	5032	5679
65°	5029	5171	5164	5171
70°	4572	4645	5238	4645
75°	4037	4092	5190	4092
80°	3396	3336	4749	3336
85°	2690	2401	3831	2401



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.8	2.0
10°-20°	371.6	6.0
20°-30°	603.4	9.8
30°-40°	736.0	11.9
40°-50°	669.6	10.9
50°-60°	533.4	8.7
60°-70°	371.5	6.0
70°-80°	198.1	3.2
80°-90°	51.7	0.8
90°-100°	29.6	0.5
100°-110°	182.5	3.0
110°-120°	331.0	5.4
120°-130°	424.8	6.9
130°-140°	456.9	7.4
140°-150°	428.9	7.0
150°-160°	346.9	5.6
160°-170°	224.4	3.6
170°-180°	77.4	1.3
0°-30°	1099.8	17.8
0°-40°	1835.9	29.8
0°-60°	3038.8	49.3
0°-90°	3660.1	59.4
90°-120°	543.2	8.8
90°-150°	1853.8	30.1
90°-180°	2503.0	40.6
0°-180°	6162.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1296	1296	1296	1296	1296	
5°	1496	1296	1135	1296	1496	151
15°	1868	1241	889	1241	1868	535
25°	2298	1135	751	1135	2298	1050
35°	1844	987	643	987	1844	1129
45°	869	779	534	779	869	696
55°	536	549	436	549	536	483
65°	329	338	338	338	329	327
75°	162	164	208	164	162	174
85°	36	32	52	32	36	42
90°	14	1	14	1	14	8
95°	13	34	13	34	13	10
105°	179	178	179	178	179	162
115°	331	334	331	334	331	329
125°	474	474	474	474	474	422
135°	589	591	589	591	589	455
145°	684	686	684	686	684	427
155°	750	755	750	755	750	346
165°	793	797	793	797	793	224
175°	811	815	811	815	811	77
180°	815	815	815	815	815	



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1371.3	1369.5	1367.8	1364.2	1366.9	1359.4	1355.9	1349.7	1342.2	1339.6	1336.5
5°	1495.7	1498.4	1501.2	1489.6	1490.7	1483.0	1465.4	1451.1	1439.6	1424.7	1414.2
7.5°	1645.4	1638.8	1638.3	1630.8	1618.0	1607.6	1589.1	1565.5	1542.8	1516.8	1495.3
10°	1720.2	1720.8	1715.8	1707.0	1693.2	1683.3	1659.1	1636.0	1607.9	1574.9	1551.3
12.5°	1776.5	1778.8	1772.6	1760.7	1754.0	1731.8	1712.9	1685.3	1652.0	1625.5	1589.6
15°	1867.7	1861.7	1857.3	1842.3	1830.8	1807.7	1777.4	1748.8	1712.5	1678.9	1645.4
17.5°	1955.5	1960.3	1952.1	1938.5	1902.7	1875.7	1835.1	1795.9	1750.7	1705.7	1665.6
20°	2033.8	2038.2	2025.6	2002.0	1959.0	1932.1	1878.7	1828.1	1775.8	1718.0	1674.0
22.5°	2131.6	2128.1	2111.0	2075.0	2037.8	1987.9	1930.2	1868.6	1803.0	1737.8	1679.3
25°	2298.0	2274.8	2264.4	2219.9	2170.9	2097.7	2018.4	1928.2	1846.7	1760.4	1685.5
27.5°	2390.2	2383.0	2371.3	2340.2	2288.8	2210.5	2117.1	2007.1	1892.2	1783.1	1685.2
30°	2371.7	2372.8	2373.9	2364.0	2331.0	2272.2	2179.1	2060.8	1924.4	1801.6	1688.2
32.5°	2208.0	2228.0	2247.1	2269.8	2279.1	2267.8	2209.5	2102.7	1962.2	1822.8	1686.5
35°	1844.5	1850.6	1912.8	1974.4	2058.1	2123.0	2166.5	2119.1	2000.8	1840.7	1684.4
37.5°	1438.3	1467.9	1511.0	1580.6	1701.4	1809.5	1948.5	2012.4	1974.2	1846.6	1680.6
40°	1226.0	1253.5	1281.7	1352.6	1454.4	1585.3	1743.3	1878.1	1909.5	1828.1	1667.4
42.5°	1062.3	1084.1	1115.2	1168.6	1253.7	1369.7	1520.5	1696.7	1805.2	1774.3	1639.6
45°	869.4	883.2	907.4	949.8	1011.5	1102.2	1235.4	1428.0	1595.9	1651.4	1573.9
47.5°	744.2	744.1	763.0	792.2	836.7	913.8	1012.3	1163.2	1342.5	1475.1	1468.9
50°	674.7	671.9	686.7	712.1	747.3	798.5	892.6	1013.1	1185.3	1335.5	1377.4
52.5°	614.8	615.1	624.3	642.9	672.5	716.2	786.4	895.1	1042.3	1196.5	1275.2
55°	536.0	533.8	544.2	556.9	578.4	607.0	657.6	740.7	860.1	1011.9	1114.4
57.5°	463.7	469.9	474.0	482.8	500.7	519.8	562.5	623.5	718.2	848.6	956.8
60°	421.5	427.5	430.9	439.7	454.0	470.5	503.5	553.0	632.8	745.1	852.4
62.5°	383.7	388.4	389.5	397.4	409.1	425.2	451.1	492.8	555.8	654.0	759.0
65°	329.1	329.1	331.3	339.5	345.0	359.3	379.1	409.4	460.1	536.5	626.2
67.5°	276.5	279.1	278.6	282.2	287.2	298.4	312.6	337.5	375.0	430.9	502.6
70°	242.1	244.3	243.8	246.5	252.0	259.2	270.8	294.4	321.4	369.2	430.9
72.5°	211.3	212.2	210.8	214.4	217.7	224.0	236.8	249.5	274.7	315.1	365.7
75°	161.8	162.9	164.0	166.2	169.5	172.8	179.4	192.1	208.6	238.8	271.3
77.5°	121.3	119.2	121.8	121.5	123.4	125.9	131.8	138.4	152.0	171.1	196.2
80°	91.3	91.9	91.9	92.5	95.2	96.9	101.8	106.7	117.2	131.5	149.1
82.5°	66.7	68.2	67.3	68.2	70.5	71.7	74.5	78.6	84.6	95.9	108.6
85°	36.3	33.6	34.7	35.8	35.8	36.3	38.5	40.2	43.5	47.9	52.8
87.5°	13.5	14.3	14.6	14.5	14.9	14.8	16.4	16.3	17.4	18.7	20.2
90°	14.5	14.1	13.7	13.3	12.9	12.3	11.7	11.0	10.4	9.7	8.7
92.5°	13.5	13.4	13.1	13.0	12.8	12.3	11.7	11.0	10.4	9.7	8.8
95°	12.7	12.7	12.7	12.7	12.7	12.3	11.7	11.0	10.4	9.7	14.8
97.5°	12.7	12.7	12.7	12.7	12.7	14.6	18.3	22.2	25.9	29.8	39.8
100°	12.7	13.2	13.8	14.3	14.8	25.1	45.1	65.1	85.1	105.1	104.6
102.5°	76.0	85.1	94.2	103.4	112.5	119.0	122.8	126.5	130.4	134.1	133.8
105°	179.4	179.5	179.7	179.9	179.9	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.2	226.6	227.0	227.4	227.8	228.0	228.0	228.0	227.9	227.9	227.6
110°	258.5	258.4	258.3	258.1	258.0	258.1	258.5	258.9	259.3	259.8	259.5



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	287.6	287.7	288.0	288.1	288.3	288.6	289.2	289.7	290.2	290.7	290.6
115°	331.0	331.8	332.6	333.5	334.3	334.9	335.5	336.0	336.6	337.1	337.0
117.5°	377.5	377.8	378.1	378.5	378.9	379.4	380.1	380.7	381.5	382.1	381.6
120°	405.9	406.7	407.3	408.0	408.6	409.1	409.4	409.7	409.9	410.2	409.8
122.5°	433.0	433.8	434.6	435.4	436.1	436.7	436.9	437.2	437.5	437.7	437.6
125°	474.3	474.7	475.0	475.4	475.8	476.3	476.9	477.4	477.9	478.4	478.4
127.5°	508.9	509.9	510.9	511.8	512.9	513.6	513.8	514.1	514.4	514.7	514.8
130°	534.0	534.7	535.4	536.1	536.7	537.3	537.7	538.1	538.4	538.8	538.7
132.5°	557.3	557.9	558.6	559.2	559.9	560.3	560.4	560.4	560.5	560.6	560.9
135°	589.0	589.8	590.6	591.4	592.2	592.8	593.0	593.3	593.5	593.9	594.1
137.5°	620.9	621.6	622.3	623.0	623.7	624.0	623.9	623.9	623.9	623.8	624.0
140°	639.8	640.6	641.4	642.1	642.9	643.3	642.9	642.7	642.5	642.1	642.3
142.5°	657.6	658.4	659.3	660.1	660.9	661.2	661.2	661.1	661.0	661.0	660.8
145°	683.9	684.7	685.4	686.2	687.1	687.4	687.3	687.1	687.0	686.9	686.9
147.5°	705.5	706.5	707.4	708.4	709.3	709.7	709.6	709.4	709.2	709.1	708.9
150°	719.5	720.6	721.6	722.7	723.8	724.2	723.9	723.7	723.4	723.1	722.8
152.5°	732.5	733.5	734.5	735.4	736.4	736.8	736.5	736.2	736.0	735.6	735.4
155°	749.7	750.8	751.9	752.9	754.0	754.3	753.9	753.5	753.1	752.7	752.4
157.5°	764.1	765.2	766.2	767.3	768.3	768.7	768.3	767.8	767.4	767.0	767.0
160°	773.2	774.4	775.4	776.5	777.6	777.8	777.3	776.7	776.2	775.7	775.5
162.5°	781.5	782.7	783.8	785.1	786.2	786.4	785.6	784.9	784.2	783.4	783.3
165°	792.6	793.7	794.8	795.8	796.9	797.0	796.2	795.4	794.6	793.8	793.7
167.5°	800.3	801.5	802.7	804.0	805.2	805.3	804.3	803.3	802.3	801.4	801.3
170°	804.7	805.8	807.1	808.3	809.5	809.6	808.5	807.4	806.3	805.3	805.1
172.5°	807.6	808.8	810.0	811.2	812.4	812.5	811.5	810.6	809.6	808.7	808.5
175°	811.3	812.5	813.8	815.0	816.1	816.2	815.1	814.1	813.0	812.0	811.8
177.5°	813.5	814.3	815.2	816.0	816.9	817.0	816.2	815.5	814.7	814.0	813.8
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1333.9	1330.8	1327.3	1321.1	1313.6	1309.7	1303.5	1299.6	1291.6	1285.0	1278.0
5°	1401.6	1387.3	1374.1	1357.0	1338.3	1326.2	1311.9	1295.9	1279.4	1262.3	1243.7
7.5°	1471.7	1446.3	1418.9	1389.3	1360.3	1333.7	1308.2	1283.3	1260.0	1231.8	1207.9
10°	1518.8	1486.9	1452.8	1412.6	1373.5	1339.4	1304.7	1274.5	1243.7	1210.6	1181.5
12.5°	1565.9	1523.4	1475.2	1431.1	1384.1	1342.9	1302.1	1263.5	1224.7	1188.2	1154.1
15°	1599.1	1561.7	1517.1	1454.4	1401.6	1344.9	1290.9	1240.9	1194.1	1153.4	1110.5
17.5°	1621.1	1572.8	1524.9	1464.8	1395.5	1332.1	1271.1	1213.7	1161.0	1109.4	1068.0
20°	1625.0	1575.5	1525.4	1466.5	1395.5	1322.9	1261.8	1193.0	1136.4	1083.0	1032.3
22.5°	1623.7	1567.6	1513.0	1452.5	1383.2	1316.3	1242.4	1172.3	1110.8	1058.3	1005.5
25°	1611.3	1551.3	1483.0	1422.0	1353.7	1282.7	1207.9	1135.2	1072.5	1012.5	960.3
27.5°	1600.9	1523.1	1445.9	1374.6	1308.7	1243.7	1172.0	1097.6	1028.0	967.3	918.0
30°	1588.1	1502.8	1415.8	1341.6	1273.9	1210.6	1143.0	1070.3	997.7	938.2	885.4
32.5°	1576.7	1477.3	1385.5	1304.6	1233.0	1171.4	1109.1	1039.9	968.6	908.3	855.5
35°	1554.5	1439.6	1334.5	1243.1	1166.6	1103.3	1051.1	986.7	921.2	862.8	812.2
37.5°	1526.5	1390.0	1277.2	1181.5	1097.6	1030.9	982.3	932.9	870.0	813.8	768.0
40°	1504.5	1354.8	1235.4	1137.4	1050.5	981.1	936.0	889.2	837.0	784.7	736.3
42.5°	1476.8	1323.1	1193.1	1087.7	1001.6	934.1	886.7	847.0	800.9	752.1	707.2
45°	1425.8	1265.7	1124.8	1011.5	924.5	857.9	808.9	779.2	744.5	698.3	660.3
47.5°	1350.9	1196.6	1050.9	933.9	844.2	782.5	736.6	708.1	683.7	649.3	614.9
50°	1284.3	1145.2	997.7	881.6	791.9	729.7	687.3	661.5	640.5	614.1	585.0
52.5°	1210.0	1080.4	945.3	830.5	741.7	680.4	638.9	616.1	598.7	579.8	551.1
55°	1091.8	981.7	856.2	747.3	665.3	605.3	569.0	549.2	534.9	520.6	503.0
57.5°	961.6	875.5	764.3	664.7	589.2	534.7	500.8	481.5	470.3	463.0	452.7
60°	870.0	796.3	700.5	609.7	536.0	487.5	454.5	439.7	430.3	424.3	416.5
62.5°	785.1	724.5	635.8	552.9	488.4	442.6	413.2	398.8	389.8	386.9	380.5
65°	659.8	613.0	539.8	471.1	416.0	376.9	352.2	338.4	332.9	329.6	330.2
67.5°	536.4	507.9	449.1	390.4	346.6	313.8	294.0	283.4	280.6	276.2	276.1
70°	461.1	439.7	390.1	339.0	299.9	274.6	257.0	246.0	243.2	241.0	240.5
72.5°	394.7	375.9	332.9	291.9	256.7	234.6	220.0	213.4	208.9	207.6	207.5
75°	296.6	286.2	252.0	219.6	195.3	179.9	170.1	164.0	160.7	160.1	160.7
77.5°	210.8	201.7	180.0	157.0	141.8	130.1	121.7	119.6	115.9	116.0	115.4
80°	158.5	152.5	138.7	120.5	107.9	97.9	93.5	89.7	88.6	86.9	88.6
82.5°	114.9	108.4	99.1	87.5	77.0	71.1	66.7	65.5	64.8	64.1	64.4
85°	56.7	57.2	51.7	42.9	38.5	35.2	32.4	32.4	31.9	31.4	31.9
87.5°	21.0	19.9	17.9	16.4	13.9	12.5	11.8	12.0	10.9	10.7	11.3
90°	7.8	6.8	5.9	4.9	3.8	2.8	1.7	0.6	1.7	2.8	3.8
92.5°	8.0	7.2	6.4	6.3	7.0	7.8	8.6	9.3	8.6	7.8	7.0
95°	19.9	24.9	30.1	32.9	33.3	33.6	34.0	34.4	34.0	33.6	33.3
97.5°	49.9	60.0	70.1	74.8	74.0	73.4	72.6	71.9	72.6	73.4	74.0
100°	104.0	103.5	103.0	102.5	102.1	101.7	101.3	100.9	101.3	101.7	102.1
102.5°	133.5	133.1	132.8	132.4	131.9	131.4	130.9	130.4	130.9	131.4	131.9
105°	180.0	180.0	180.0	179.8	179.2	178.7	178.1	177.6	178.1	178.7	179.2
107.5°	227.3	227.1	226.8	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7
110°	259.3	258.9	258.7	258.5	258.5	258.5	258.5	258.5	258.5	258.5	258.5



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	290.4	290.2	290.1	289.8	289.5	289.2	288.9	288.5	288.9	289.2	289.5
115°	336.8	336.7	336.6	336.1	335.5	334.8	334.1	333.5	334.1	334.8	335.5
117.5°	381.2	380.7	380.1	379.8	379.9	379.9	379.9	380.0	379.9	379.9	379.9
120°	409.4	409.0	408.5	408.5	408.5	408.7	408.9	409.0	408.9	408.7	408.5
122.5°	437.3	437.2	437.0	436.7	436.1	435.6	435.1	434.6	435.1	435.6	436.1
125°	478.4	478.4	478.4	478.0	477.0	476.1	475.2	474.3	475.2	476.1	477.0
127.5°	514.9	514.9	515.0	514.7	514.0	513.4	512.7	512.0	512.7	513.4	514.0
130°	538.6	538.4	538.3	537.9	537.3	536.5	535.9	535.2	535.9	536.5	537.3
132.5°	561.2	561.5	561.8	561.6	560.8	560.0	559.2	558.4	559.2	560.0	560.8
135°	594.4	594.7	594.9	594.7	593.9	593.0	592.2	591.4	592.2	593.0	593.9
137.5°	624.3	624.5	624.8	624.5	623.9	623.1	622.5	621.7	622.5	623.1	623.9
140°	642.5	642.5	642.7	642.6	642.4	642.1	641.8	641.6	641.8	642.1	642.4
142.5°	660.6	660.5	660.2	660.1	659.9	659.7	659.6	659.4	659.6	659.7	659.9
145°	686.9	686.9	686.9	686.7	686.5	686.2	685.9	685.7	685.9	686.2	686.5
147.5°	708.7	708.7	708.5	708.4	708.5	708.5	708.6	708.7	708.6	708.5	708.5
150°	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	722.8	722.6	722.3
152.5°	735.2	734.9	734.6	734.7	735.4	736.0	736.5	737.1	736.5	736.0	735.4
155°	752.2	752.0	751.6	752.0	752.7	753.5	754.3	755.1	754.3	753.5	752.7
157.5°	767.0	766.9	766.9	767.1	767.6	768.1	768.6	769.0	768.6	768.1	767.6
160°	775.4	775.3	775.1	775.5	776.2	777.1	777.9	778.7	777.9	777.1	776.2
162.5°	783.2	783.0	782.9	783.2	784.0	784.8	785.6	786.4	785.6	784.8	784.0
165°	793.5	793.4	793.3	793.6	794.4	795.2	796.0	796.8	796.0	795.2	794.4
167.5°	801.1	801.0	800.9	801.2	802.1	802.9	803.7	804.5	803.7	802.9	802.1
170°	805.0	804.9	804.7	805.1	806.1	807.0	808.0	808.9	808.0	807.0	806.1
172.5°	808.2	808.0	807.7	808.0	808.9	809.9	810.9	811.8	810.9	809.9	808.9
175°	811.6	811.5	811.4	811.7	812.5	813.3	814.2	815.0	814.2	813.3	812.5
177.5°	813.8	813.7	813.5	813.8	814.5	815.1	815.7	816.4	815.7	815.1	814.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1274.0	1269.2	1265.2	1256.4	1251.6	1245.0	1239.7	1245.4	1239.3	1241.9	1238.0
5°	1234.3	1218.9	1207.9	1191.9	1178.2	1165.5	1156.2	1154.5	1150.1	1147.9	1141.3
7.5°	1186.5	1167.3	1148.3	1127.4	1109.8	1091.8	1080.4	1071.0	1064.7	1056.5	1050.8
10°	1158.4	1132.5	1110.5	1085.2	1063.2	1043.9	1028.5	1020.8	1013.7	1003.1	999.3
12.5°	1123.6	1096.8	1070.0	1042.9	1021.7	1000.3	987.1	975.4	970.5	958.7	957.5
15°	1081.9	1041.7	1015.3	987.7	958.6	941.0	930.0	917.3	911.8	903.6	897.5
17.5°	1032.1	996.2	963.2	934.7	909.7	894.9	881.3	872.5	863.1	857.7	847.7
20°	996.1	961.9	928.9	898.6	879.4	862.3	851.3	843.0	833.2	830.4	820.5
22.5°	965.6	928.0	896.3	870.9	849.9	830.6	818.7	813.1	806.2	797.8	795.8
25°	916.2	877.2	850.2	824.9	806.2	788.6	780.3	773.1	766.5	760.5	758.3
27.5°	873.5	838.6	806.6	783.7	767.4	751.4	744.1	735.4	730.6	725.7	719.7
30°	843.6	807.8	779.8	757.7	740.1	725.9	718.1	712.1	707.7	703.3	699.9
32.5°	812.8	779.7	752.4	730.9	713.3	702.5	695.7	691.4	686.6	681.3	677.1
35°	772.1	735.7	709.3	690.6	676.9	668.6	660.9	657.0	651.5	651.5	647.1
37.5°	726.2	694.8	671.5	654.4	642.0	634.7	626.3	623.7	620.2	617.8	616.3
40°	698.9	669.7	647.7	630.6	617.4	611.4	604.8	600.4	598.2	595.4	594.3
42.5°	670.7	642.9	621.7	606.0	594.5	589.4	583.2	580.1	575.7	572.1	571.4
45°	627.9	600.9	581.6	569.0	559.1	553.0	549.2	542.6	540.4	536.0	535.4
47.5°	587.3	561.4	542.5	532.1	523.4	518.4	512.4	505.8	503.3	501.1	500.8
50°	556.9	533.2	515.6	505.7	497.5	490.3	484.3	479.9	478.2	478.2	479.3
52.5°	526.1	505.9	491.0	478.8	471.1	463.4	457.9	455.2	452.7	455.3	457.3
55°	480.9	460.6	449.6	438.1	430.3	421.5	418.7	417.7	416.0	420.4	422.7
57.5°	433.2	418.9	406.0	394.5	387.6	382.5	378.8	378.1	381.2	383.4	390.4
60°	402.8	386.3	374.7	365.9	357.7	354.4	353.3	352.2	354.4	360.4	369.8
62.5°	369.3	356.0	343.5	336.9	330.8	325.3	325.1	325.8	330.2	337.1	346.4
65°	320.2	308.7	300.4	292.8	287.8	284.5	285.6	287.8	292.8	302.1	312.6
67.5°	270.4	262.5	255.1	248.8	244.1	244.1	245.2	248.5	254.4	265.1	274.7
70°	238.3	229.5	223.4	220.7	216.8	214.6	217.9	223.4	228.4	238.3	246.5
72.5°	206.1	198.7	194.0	192.1	190.4	188.7	189.7	195.7	202.4	212.3	221.8
75°	158.5	155.7	152.5	150.3	148.5	149.7	150.7	156.3	161.8	172.3	183.3
77.5°	115.7	112.8	110.8	110.3	109.4	110.0	113.0	117.1	122.5	130.1	138.4
80°	87.5	86.4	85.3	84.7	84.7	85.3	89.7	92.5	97.4	104.5	111.1
82.5°	63.8	63.0	62.9	62.7	63.2	63.3	66.0	69.5	73.6	79.0	84.7
85°	33.6	32.4	34.1	34.7	33.6	35.2	36.3	38.5	40.2	42.9	45.7
87.5°	12.0	13.0	12.8	13.5	13.6	14.7	14.4	16.3	17.3	18.3	18.0
90°	4.9	5.9	6.8	7.8	8.7	9.7	10.4	11.0	11.7	12.3	12.9
92.5°	6.3	6.4	7.2	8.0	8.8	9.7	10.4	11.0	11.7	12.3	12.8
95°	32.9	30.1	24.9	19.9	14.8	9.7	10.4	11.0	11.7	12.3	12.7
97.5°	74.8	70.1	60.0	49.9	39.8	29.8	25.9	22.2	18.3	14.6	12.7
100°	102.5	103.0	103.5	104.0	104.6	105.1	85.1	65.1	45.1	25.1	14.8
102.5°	132.4	132.8	133.1	133.5	133.8	134.1	130.4	126.5	122.8	119.0	112.5
105°	179.8	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0	179.9
107.5°	226.7	226.8	227.1	227.3	227.6	227.9	227.9	228.0	228.0	228.0	227.8
110°	258.5	258.7	258.9	259.3	259.5	259.8	259.3	258.9	258.5	258.1	258.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.8	290.1	290.2	290.4	290.6	290.7	290.2	289.7	289.2	288.6	288.3
115°	336.1	336.6	336.7	336.8	337.0	337.1	336.6	336.0	335.5	334.9	334.3
117.5°	379.8	380.1	380.7	381.2	381.6	382.1	381.5	380.7	380.1	379.4	378.9
120°	408.5	408.5	409.0	409.4	409.8	410.2	409.9	409.7	409.4	409.1	408.6
122.5°	436.7	437.0	437.2	437.3	437.6	437.7	437.5	437.2	436.9	436.7	436.1
125°	478.0	478.4	478.4	478.4	478.4	478.4	477.9	477.4	476.9	476.3	475.8
127.5°	514.7	515.0	514.9	514.9	514.8	514.7	514.4	514.1	513.8	513.6	512.9
130°	537.9	538.3	538.4	538.6	538.7	538.8	538.4	538.1	537.7	537.3	536.7
132.5°	561.6	561.8	561.5	561.2	560.9	560.6	560.5	560.4	560.4	560.3	559.9
135°	594.7	594.9	594.7	594.4	594.1	593.9	593.5	593.3	593.0	592.8	592.2
137.5°	624.5	624.8	624.5	624.3	624.0	623.8	623.9	623.9	623.9	624.0	623.7
140°	642.6	642.7	642.5	642.5	642.3	642.1	642.5	642.7	642.9	643.3	642.9
142.5°	660.1	660.2	660.5	660.6	660.8	661.0	661.0	661.1	661.2	661.2	660.9
145°	686.7	686.9	686.9	686.9	686.9	686.9	687.0	687.1	687.3	687.4	687.1
147.5°	708.4	708.5	708.7	708.7	708.9	709.1	709.2	709.4	709.6	709.7	709.3
150°	722.0	722.0	722.3	722.6	722.8	723.1	723.4	723.7	723.9	724.2	723.8
152.5°	734.7	734.6	734.9	735.2	735.4	735.6	736.0	736.2	736.5	736.8	736.4
155°	752.0	751.6	752.0	752.2	752.4	752.7	753.1	753.5	753.9	754.3	754.0
157.5°	767.1	766.9	766.9	767.0	767.0	767.0	767.4	767.8	768.3	768.7	768.3
160°	775.5	775.1	775.3	775.4	775.5	775.7	776.2	776.7	777.3	777.8	777.6
162.5°	783.2	782.9	783.0	783.2	783.3	783.4	784.2	784.9	785.6	786.4	786.2
165°	793.6	793.3	793.4	793.5	793.7	793.8	794.6	795.4	796.2	797.0	796.9
167.5°	801.2	800.9	801.0	801.1	801.3	801.4	802.3	803.3	804.3	805.3	805.2
170°	805.1	804.7	804.9	805.0	805.1	805.3	806.3	807.4	808.5	809.6	809.5
172.5°	808.0	807.7	808.0	808.2	808.5	808.7	809.6	810.6	811.5	812.5	812.4
175°	811.7	811.4	811.5	811.6	811.8	812.0	813.0	814.1	815.1	816.2	816.1
177.5°	813.8	813.5	813.7	813.8	813.8	814.0	814.7	815.5	816.2	817.0	816.9
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1235.3	1238.4	1235.7	1239.3	1235.7	1238.4	1235.3	1238.0	1241.9	1239.3	1245.4
5°	1138.6	1133.6	1136.9	1134.7	1136.9	1133.6	1138.6	1141.3	1147.9	1150.1	1154.5
7.5°	1049.2	1044.5	1039.0	1036.5	1039.0	1044.5	1049.2	1050.8	1056.5	1064.7	1071.0
10°	993.3	987.2	986.7	982.8	986.7	987.2	993.3	999.3	1003.1	1013.7	1020.8
12.5°	952.4	946.7	940.4	938.8	940.4	946.7	952.4	957.5	958.7	970.5	975.4
15°	894.2	889.8	886.0	889.2	886.0	889.8	894.2	897.5	903.6	911.8	917.3
17.5°	845.9	842.3	841.6	837.6	841.6	842.3	845.9	847.7	857.7	863.1	872.5
20°	815.5	812.8	813.9	806.7	813.9	812.8	815.5	820.5	830.4	833.2	843.0
22.5°	791.3	785.9	785.3	783.8	785.3	785.9	791.3	795.8	797.8	806.2	813.1
25°	753.3	750.6	747.9	750.6	747.9	750.6	753.3	758.3	760.5	766.5	773.1
27.5°	720.2	716.9	716.2	716.5	716.2	716.9	720.2	719.7	725.7	730.6	735.4
30°	699.9	694.5	695.0	694.5	695.0	694.5	699.9	699.9	703.3	707.7	712.1
32.5°	677.9	674.2	673.4	672.5	673.4	674.2	677.9	677.1	681.3	686.6	691.4
35°	645.5	645.5	642.7	642.7	642.7	645.5	645.5	647.1	651.5	651.5	657.0
37.5°	615.0	614.4	612.8	613.0	612.8	614.4	615.0	616.3	617.8	620.2	623.7
40°	592.1	591.6	589.9	586.6	589.9	591.6	592.1	594.3	595.4	598.2	600.4
42.5°	570.1	568.3	567.4	566.4	567.4	568.3	570.1	571.4	572.1	575.7	580.1
45°	535.4	535.4	534.3	533.8	534.3	535.4	535.4	535.4	536.0	540.4	542.6
47.5°	501.7	502.7	504.8	504.5	504.8	502.7	501.7	500.8	501.1	503.3	505.8
50°	481.5	482.1	483.7	484.3	483.7	482.1	481.5	479.3	478.2	478.2	479.9
52.5°	459.0	462.3	464.3	464.0	464.3	462.3	459.0	457.3	455.3	452.7	455.2
55°	427.5	431.5	435.3	435.9	435.3	431.5	427.5	422.7	420.4	416.0	417.7
57.5°	396.4	401.8	405.9	407.2	405.9	401.8	396.4	390.4	383.4	381.2	378.1
60°	375.3	382.5	387.4	389.6	387.4	382.5	375.3	369.8	360.4	354.4	352.2
62.5°	355.1	363.1	368.0	368.4	368.0	363.1	355.1	346.4	337.1	330.2	325.8
65°	321.9	330.2	334.6	337.9	334.6	330.2	321.9	312.6	302.1	292.8	287.8
67.5°	286.3	294.5	299.4	302.0	299.4	294.5	286.3	274.7	265.1	254.4	248.5
70°	260.3	268.6	275.2	277.4	275.2	268.6	260.3	246.5	238.3	228.4	223.4
72.5°	234.7	242.1	247.4	250.1	247.4	242.1	234.7	221.8	212.3	202.4	195.7
75°	190.4	200.3	205.3	208.0	205.3	200.3	190.4	183.3	172.3	161.8	156.3
77.5°	146.8	155.8	158.8	160.2	158.8	155.8	146.8	138.4	130.1	122.5	117.1
80°	117.7	123.3	127.1	127.7	127.1	123.3	117.7	111.1	104.5	97.4	92.5
82.5°	90.5	95.1	96.3	97.8	96.3	95.1	90.5	84.7	79.0	73.6	69.5
85°	49.5	51.7	52.3	51.7	52.3	51.7	49.5	45.7	42.9	40.2	38.5
87.5°	18.9	18.6	18.7	19.6	18.7	18.6	18.9	18.0	18.3	17.3	16.3
90°	13.3	13.7	14.1	14.5	14.1	13.7	13.3	12.9	12.3	11.7	11.0
92.5°	13.0	13.1	13.4	13.5	13.4	13.1	13.0	12.8	12.3	11.7	11.0
95°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.3	11.7	11.0
97.5°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	14.6	18.3	22.2
100°	14.3	13.8	13.2	12.7	13.2	13.8	14.3	14.8	25.1	45.1	65.1
102.5°	103.4	94.2	85.1	76.0	85.1	94.2	103.4	112.5	119.0	122.8	126.5
105°	179.9	179.7	179.5	179.4	179.5	179.7	179.9	179.9	180.0	180.0	180.0
107.5°	227.4	227.0	226.6	226.2	226.6	227.0	227.4	227.8	228.0	228.0	228.0
110°	258.1	258.3	258.4	258.5	258.4	258.3	258.1	258.0	258.1	258.5	258.9



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	288.1	288.0	287.7	287.6	287.7	288.0	288.1	288.3	288.6	289.2	289.7
115°	333.5	332.6	331.8	331.0	331.8	332.6	333.5	334.3	334.9	335.5	336.0
117.5°	378.5	378.1	377.8	377.5	377.8	378.1	378.5	378.9	379.4	380.1	380.7
120°	408.0	407.3	406.7	405.9	406.7	407.3	408.0	408.6	409.1	409.4	409.7
122.5°	435.4	434.6	433.8	433.0	433.8	434.6	435.4	436.1	436.7	436.9	437.2
125°	475.4	475.0	474.7	474.3	474.7	475.0	475.4	475.8	476.3	476.9	477.4
127.5°	511.8	510.9	509.9	508.9	509.9	510.9	511.8	512.9	513.6	513.8	514.1
130°	536.1	535.4	534.7	534.0	534.7	535.4	536.1	536.7	537.3	537.7	538.1
132.5°	559.2	558.6	557.9	557.3	557.9	558.6	559.2	559.9	560.3	560.4	560.4
135°	591.4	590.6	589.8	589.0	589.8	590.6	591.4	592.2	592.8	593.0	593.3
137.5°	623.0	622.3	621.6	620.9	621.6	622.3	623.0	623.7	624.0	623.9	623.9
140°	642.1	641.4	640.6	639.8	640.6	641.4	642.1	642.9	643.3	642.9	642.7
142.5°	660.1	659.3	658.4	657.6	658.4	659.3	660.1	660.9	661.2	661.2	661.1
145°	686.2	685.4	684.7	683.9	684.7	685.4	686.2	687.1	687.4	687.3	687.1
147.5°	708.4	707.4	706.5	705.5	706.5	707.4	708.4	709.3	709.7	709.6	709.4
150°	722.7	721.6	720.6	719.5	720.6	721.6	722.7	723.8	724.2	723.9	723.7
152.5°	735.4	734.5	733.5	732.5	733.5	734.5	735.4	736.4	736.8	736.5	736.2
155°	752.9	751.9	750.8	749.7	750.8	751.9	752.9	754.0	754.3	753.9	753.5
157.5°	767.3	766.2	765.2	764.1	765.2	766.2	767.3	768.3	768.7	768.3	767.8
160°	776.5	775.4	774.4	773.2	774.4	775.4	776.5	777.6	777.8	777.3	776.7
162.5°	785.1	783.8	782.7	781.5	782.7	783.8	785.1	786.2	786.4	785.6	784.9
165°	795.8	794.8	793.7	792.6	793.7	794.8	795.8	796.9	797.0	796.2	795.4
167.5°	804.0	802.7	801.5	800.3	801.5	802.7	804.0	805.2	805.3	804.3	803.3
170°	808.3	807.1	805.8	804.7	805.8	807.1	808.3	809.5	809.6	808.5	807.4
172.5°	811.2	810.0	808.8	807.6	808.8	810.0	811.2	812.4	812.5	811.5	810.6
175°	815.0	813.8	812.5	811.3	812.5	813.8	815.0	816.1	816.2	815.1	814.1
177.5°	816.0	815.2	814.3	813.5	814.3	815.2	816.0	816.9	817.0	816.2	815.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1239.7	1245.0	1251.6	1256.4	1265.2	1269.2	1274.0	1278.0	1285.0	1291.6	1299.6
5°	1156.2	1165.5	1178.2	1191.9	1207.9	1218.9	1234.3	1243.7	1262.3	1279.4	1295.9
7.5°	1080.4	1091.8	1109.8	1127.4	1148.3	1167.3	1186.5	1207.9	1231.8	1260.0	1283.3
10°	1028.5	1043.9	1063.2	1085.2	1110.5	1132.5	1158.4	1181.5	1210.6	1243.7	1274.5
12.5°	987.1	1000.3	1021.7	1042.9	1070.0	1096.8	1123.6	1154.1	1188.2	1224.7	1263.5
15°	930.0	941.0	958.6	987.7	1015.3	1041.7	1081.9	1110.5	1153.4	1194.1	1240.9
17.5°	881.3	894.9	909.7	934.7	963.2	996.2	1032.1	1068.0	1109.4	1161.0	1213.7
20°	851.3	862.3	879.4	898.6	928.9	961.9	996.1	1032.3	1083.0	1136.4	1193.0
22.5°	818.7	830.6	849.9	870.9	896.3	928.0	965.6	1005.5	1058.3	1110.8	1172.3
25°	780.3	788.6	806.2	824.9	850.2	877.2	916.2	960.3	1012.5	1072.5	1135.2
27.5°	744.1	751.4	767.4	783.7	806.6	838.6	873.5	918.0	967.3	1028.0	1097.6
30°	718.1	725.9	740.1	757.7	779.8	807.8	843.6	885.4	938.2	997.7	1070.3
32.5°	695.7	702.5	713.3	730.9	752.4	779.7	812.8	855.5	908.3	968.6	1039.9
35°	660.9	668.6	676.9	690.6	709.3	735.7	772.1	812.2	862.8	921.2	986.7
37.5°	626.3	634.7	642.0	654.4	671.5	694.8	726.2	768.0	813.8	870.0	932.9
40°	604.8	611.4	617.4	630.6	647.7	669.7	698.9	736.3	784.7	837.0	889.2
42.5°	583.2	589.4	594.5	606.0	621.7	642.9	670.7	707.2	752.1	800.9	847.0
45°	549.2	553.0	559.1	569.0	581.6	600.9	627.9	660.3	698.3	744.5	779.2
47.5°	512.4	518.4	523.4	532.1	542.5	561.4	587.3	614.9	649.3	683.7	708.1
50°	484.3	490.3	497.5	505.7	515.6	533.2	556.9	585.0	614.1	640.5	661.5
52.5°	457.9	463.4	471.1	478.8	491.0	505.9	526.1	551.1	579.8	598.7	616.1
55°	418.7	421.5	430.3	438.1	449.6	460.6	480.9	503.0	520.6	534.9	549.2
57.5°	378.8	382.5	387.6	394.5	406.0	418.9	433.2	452.7	463.0	470.3	481.5
60°	353.3	354.4	357.7	365.9	374.7	386.3	402.8	416.5	424.3	430.3	439.7
62.5°	325.1	325.3	330.8	336.9	343.5	356.0	369.3	380.5	386.9	389.8	398.8
65°	285.6	284.5	287.8	292.8	300.4	308.7	320.2	330.2	329.6	332.9	338.4
67.5°	245.2	244.1	244.1	248.8	255.1	262.5	270.4	276.1	276.2	280.6	283.4
70°	217.9	214.6	216.8	220.7	223.4	229.5	238.3	240.5	241.0	243.2	246.0
72.5°	189.7	188.7	190.4	192.1	194.0	198.7	206.1	207.5	207.6	208.9	213.4
75°	150.7	149.7	148.5	150.3	152.5	155.7	158.5	160.7	160.1	160.7	164.0
77.5°	113.0	110.0	109.4	110.3	110.8	112.8	115.7	115.4	116.0	115.9	119.6
80°	89.7	85.3	84.7	84.7	85.3	86.4	87.5	88.6	86.9	88.6	89.7
82.5°	66.0	63.3	63.2	62.7	62.9	63.0	63.8	64.4	64.1	64.8	65.5
85°	36.3	35.2	33.6	34.7	34.1	32.4	33.6	31.9	31.4	31.9	32.4
87.5°	14.4	14.7	13.6	13.5	12.8	13.0	12.0	11.3	10.7	10.9	12.0
90°	10.4	9.7	8.7	7.8	6.8	5.9	4.9	3.8	2.8	1.7	0.6
92.5°	10.4	9.7	8.8	8.0	7.2	6.4	6.3	7.0	7.8	8.6	9.3
95°	10.4	9.7	14.8	19.9	24.9	30.1	32.9	33.3	33.6	34.0	34.4
97.5°	25.9	29.8	39.8	49.9	60.0	70.1	74.8	74.0	73.4	72.6	71.9
100°	85.1	105.1	104.6	104.0	103.5	103.0	102.5	102.1	101.7	101.3	100.9
102.5°	130.4	134.1	133.8	133.5	133.1	132.8	132.4	131.9	131.4	130.9	130.4
105°	180.0	180.0	180.0	180.0	180.0	180.0	179.8	179.2	178.7	178.1	177.6
107.5°	227.9	227.9	227.6	227.3	227.1	226.8	226.7	226.7	226.7	226.7	226.7
110°	259.3	259.8	259.5	259.3	258.9	258.7	258.5	258.5	258.5	258.5	258.5



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.2	290.7	290.6	290.4	290.2	290.1	289.8	289.5	289.2	288.9	288.5
115°	336.6	337.1	337.0	336.8	336.7	336.6	336.1	335.5	334.8	334.1	333.5
117.5°	381.5	382.1	381.6	381.2	380.7	380.1	379.8	379.9	379.9	379.9	380.0
120°	409.9	410.2	409.8	409.4	409.0	408.5	408.5	408.5	408.7	408.9	409.0
122.5°	437.5	437.7	437.6	437.3	437.2	437.0	436.7	436.1	435.6	435.1	434.6
125°	477.9	478.4	478.4	478.4	478.4	478.4	478.0	477.0	476.1	475.2	474.3
127.5°	514.4	514.7	514.8	514.9	514.9	515.0	514.7	514.0	513.4	512.7	512.0
130°	538.4	538.8	538.7	538.6	538.4	538.3	537.9	537.3	536.5	535.9	535.2
132.5°	560.5	560.6	560.9	561.2	561.5	561.8	561.6	560.8	560.0	559.2	558.4
135°	593.5	593.9	594.1	594.4	594.7	594.9	594.7	593.9	593.0	592.2	591.4
137.5°	623.9	623.8	624.0	624.3	624.5	624.8	624.5	623.9	623.1	622.5	621.7
140°	642.5	642.1	642.3	642.5	642.5	642.7	642.6	642.4	642.1	641.8	641.6
142.5°	661.0	661.0	660.8	660.6	660.5	660.2	660.1	659.9	659.7	659.6	659.4
145°	687.0	686.9	686.9	686.9	686.9	686.9	686.7	686.5	686.2	685.9	685.7
147.5°	709.2	709.1	708.9	708.7	708.7	708.5	708.4	708.5	708.5	708.6	708.7
150°	723.4	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1
152.5°	736.0	735.6	735.4	735.2	734.9	734.6	734.7	735.4	736.0	736.5	737.1
155°	753.1	752.7	752.4	752.2	752.0	751.6	752.0	752.7	753.5	754.3	755.1
157.5°	767.4	767.0	767.0	767.0	766.9	766.9	767.1	767.6	768.1	768.6	769.0
160°	776.2	775.7	775.5	775.4	775.3	775.1	775.5	776.2	777.1	777.9	778.7
162.5°	784.2	783.4	783.3	783.2	783.0	782.9	783.2	784.0	784.8	785.6	786.4
165°	794.6	793.8	793.7	793.5	793.4	793.3	793.6	794.4	795.2	796.0	796.8
167.5°	802.3	801.4	801.3	801.1	801.0	800.9	801.2	802.1	802.9	803.7	804.5
170°	806.3	805.3	805.1	805.0	804.9	804.7	805.1	806.1	807.0	808.0	808.9
172.5°	809.6	808.7	808.5	808.2	808.0	807.7	808.0	808.9	809.9	810.9	811.8
175°	813.0	812.0	811.8	811.6	811.5	811.4	811.7	812.5	813.3	814.2	815.0
177.5°	814.7	814.0	813.8	813.8	813.7	813.5	813.8	814.5	815.1	815.7	816.4
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1303.5	1309.7	1313.6	1321.1	1327.3	1330.8	1333.9	1336.5	1339.6	1342.2	1349.7
5°	1311.9	1326.2	1338.3	1357.0	1374.1	1387.3	1401.6	1414.2	1424.7	1439.6	1451.1
7.5°	1308.2	1333.7	1360.3	1389.3	1418.9	1446.3	1471.7	1495.3	1516.8	1542.8	1565.5
10°	1304.7	1339.4	1373.5	1412.6	1452.8	1486.9	1518.8	1551.3	1574.9	1607.9	1636.0
12.5°	1302.1	1342.9	1384.1	1431.1	1475.2	1523.4	1565.9	1589.6	1625.5	1652.0	1685.3
15°	1290.9	1344.9	1401.6	1454.4	1517.1	1561.7	1599.1	1645.4	1678.9	1712.5	1748.8
17.5°	1271.1	1332.1	1395.5	1464.8	1524.9	1572.8	1621.1	1665.6	1705.7	1750.7	1795.9
20°	1261.8	1322.9	1395.5	1466.5	1525.4	1575.5	1625.0	1674.0	1718.0	1775.8	1828.1
22.5°	1242.4	1316.3	1383.2	1452.5	1513.0	1567.6	1623.7	1679.3	1737.8	1803.0	1868.6
25°	1207.9	1282.7	1353.7	1422.0	1483.0	1551.3	1611.3	1685.5	1760.4	1846.7	1928.2
27.5°	1172.0	1243.7	1308.7	1374.6	1445.9	1523.1	1600.9	1685.2	1783.1	1892.2	2007.1
30°	1143.0	1210.6	1273.9	1341.6	1415.8	1502.8	1588.1	1688.2	1801.6	1924.4	2060.8
32.5°	1109.1	1171.4	1233.0	1304.6	1385.5	1477.3	1576.7	1686.5	1822.8	1962.2	2102.7
35°	1051.1	1103.3	1166.6	1243.1	1334.5	1439.6	1554.5	1684.4	1840.7	2000.8	2119.1
37.5°	982.3	1030.9	1097.6	1181.5	1277.2	1390.0	1526.5	1680.6	1846.6	1974.2	2012.4
40°	936.0	981.1	1050.5	1137.4	1235.4	1354.8	1504.5	1667.4	1828.1	1909.5	1878.1
42.5°	886.7	934.1	1001.6	1087.7	1193.1	1323.1	1476.8	1639.6	1774.3	1805.2	1696.7
45°	808.9	857.9	924.5	1011.5	1124.8	1265.7	1425.8	1573.9	1651.4	1595.9	1428.0
47.5°	736.6	782.5	844.2	933.9	1050.9	1196.6	1350.9	1468.9	1475.1	1342.5	1163.2
50°	687.3	729.7	791.9	881.6	997.7	1145.2	1284.3	1377.4	1335.5	1185.3	1013.1
52.5°	638.9	680.4	741.7	830.5	945.3	1080.4	1210.0	1275.2	1196.5	1042.3	895.1
55°	569.0	605.3	665.3	747.3	856.2	981.7	1091.8	1114.4	1011.9	860.1	740.7
57.5°	500.8	534.7	589.2	664.7	764.3	875.5	961.6	956.8	848.6	718.2	623.5
60°	454.5	487.5	536.0	609.7	700.5	796.3	870.0	852.4	745.1	632.8	553.0
62.5°	413.2	442.6	488.4	552.9	635.8	724.5	785.1	759.0	654.0	555.8	492.8
65°	352.2	376.9	416.0	471.1	539.8	613.0	659.8	626.2	536.5	460.1	409.4
67.5°	294.0	313.8	346.6	390.4	449.1	507.9	536.4	502.6	430.9	375.0	337.5
70°	257.0	274.6	299.9	339.0	390.1	439.7	461.1	430.9	369.2	321.4	294.4
72.5°	220.0	234.6	256.7	291.9	332.9	375.9	394.7	365.7	315.1	274.7	249.5
75°	170.1	179.9	195.3	219.6	252.0	286.2	296.6	271.3	238.8	208.6	192.1
77.5°	121.7	130.1	141.8	157.0	180.0	201.7	210.8	196.2	171.1	152.0	138.4
80°	93.5	97.9	107.9	120.5	138.7	152.5	158.5	149.1	131.5	117.2	106.7
82.5°	66.7	71.1	77.0	87.5	99.1	108.4	114.9	108.6	95.9	84.6	78.6
85°	32.4	35.2	38.5	42.9	51.7	57.2	56.7	52.8	47.9	43.5	40.2
87.5°	11.8	12.5	13.9	16.4	17.9	19.9	21.0	20.2	18.7	17.4	16.3
90°	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4	11.0
92.5°	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4	11.0
95°	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4	11.0
97.5°	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9	22.2
100°	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1	65.1
102.5°	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4	126.5
105°	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9	228.0
110°	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3	258.9



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2	289.7
115°	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6	336.0
117.5°	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5	380.7
120°	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9	409.7
122.5°	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5	437.2
125°	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9	477.4
127.5°	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4	514.1
130°	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4	538.1
132.5°	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5	560.4
135°	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5	593.3
137.5°	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9	623.9
140°	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5	642.7
142.5°	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0	661.1
145°	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0	687.1
147.5°	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2	709.4
150°	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4	723.7
152.5°	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0	736.2
155°	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1	753.5
157.5°	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4	767.8
160°	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2	776.7
162.5°	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2	784.9
165°	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6	795.4
167.5°	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3	803.3
170°	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3	807.4
172.5°	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6	810.6
175°	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0	814.1
177.5°	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7	815.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5	1296.5
2.5°	1355.9	1359.4	1366.9	1364.2	1367.8	1369.5	1371.3
5°	1465.4	1483.0	1490.7	1489.6	1501.2	1498.4	1495.7
7.5°	1589.1	1607.6	1618.0	1630.8	1638.3	1638.8	1645.4
10°	1659.1	1683.3	1693.2	1707.0	1715.8	1720.8	1720.2
12.5°	1712.9	1731.8	1754.0	1760.7	1772.6	1778.8	1776.5
15°	1777.4	1807.7	1830.8	1842.3	1857.3	1861.7	1867.7
17.5°	1835.1	1875.7	1902.7	1938.5	1952.1	1960.3	1955.5
20°	1878.7	1932.1	1959.0	2002.0	2025.6	2038.2	2033.8
22.5°	1930.2	1987.9	2037.8	2075.0	2111.0	2128.1	2131.6
25°	2018.4	2097.7	2170.9	2219.9	2264.4	2274.8	2298.0
27.5°	2117.1	2210.5	2288.8	2340.2	2371.3	2383.0	2390.2
30°	2179.1	2272.2	2331.0	2364.0	2373.9	2372.8	2371.7
32.5°	2209.5	2267.8	2279.1	2269.8	2247.1	2228.0	2208.0
35°	2166.5	2123.0	2058.1	1974.4	1912.8	1850.6	1844.5
37.5°	1948.5	1809.5	1701.4	1580.6	1511.0	1467.9	1438.3
40°	1743.3	1585.3	1454.4	1352.6	1281.7	1253.5	1226.0
42.5°	1520.5	1369.7	1253.7	1168.6	1115.2	1084.1	1062.3
45°	1235.4	1102.2	1011.5	949.8	907.4	883.2	869.4
47.5°	1012.3	913.8	836.7	792.2	763.0	744.1	744.2
50°	892.6	798.5	747.3	712.1	686.7	671.9	674.7
52.5°	786.4	716.2	672.5	642.9	624.3	615.1	614.8
55°	657.6	607.0	578.4	556.9	544.2	533.8	536.0
57.5°	562.5	519.8	500.7	482.8	474.0	469.9	463.7
60°	503.5	470.5	454.0	439.7	430.9	427.5	421.5
62.5°	451.1	425.2	409.1	397.4	389.5	388.4	383.7
65°	379.1	359.3	345.0	339.5	331.3	329.1	329.1
67.5°	312.6	298.4	287.2	282.2	278.6	279.1	276.5
70°	270.8	259.2	252.0	246.5	243.8	244.3	242.1
72.5°	236.8	224.0	217.7	214.4	210.8	212.2	211.3
75°	179.4	172.8	169.5	166.2	164.0	162.9	161.8
77.5°	131.8	125.9	123.4	121.5	121.8	119.2	121.3
80°	101.8	96.9	95.2	92.5	91.9	91.9	91.3
82.5°	74.5	71.7	70.5	68.2	67.3	68.2	66.7
85°	38.5	36.3	35.8	35.8	34.7	33.6	36.3
87.5°	16.4	14.8	14.9	14.5	14.6	14.3	13.5
90°	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333436-930

CATALOG NUMBER: S125DIW-S1090D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)