

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333037-940

Luminaire Tested: **S124RDIW-S575D470U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333037-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S575D470U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 575 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3766.7 lumens
Efficiency: N/A
Efficacy: 124.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	55	53	52	47
2	91	83	77	72	84	78	72	68	67	63	60	57	55	52	48	46	45	40
3	83	74	66	61	77	69	62	57	60	55	51	51	47	44	43	41	38	34
4	76	65	57	51	70	61	54	49	53	48	43	46	42	38	39	36	33	30
5	70	58	50	44	65	55	47	42	48	42	38	41	37	33	35	32	29	26
6	64	52	44	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	47	40	34	55	45	37	32	39	33	29	34	29	26	29	26	23	20
8	55	43	35	30	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	30	26	33	27	23	29	24	21	25	21	19	17
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7316	7316	7316
5°	7332	7243	7288
10°	7287	7156	7156
15°	7203	7005	6954
20°	7088	6808	6682
25°	6942	6576	6409
30°	6797	6332	6068
35°	6640	6080	5724
40°	6450	5792	5352
45°	6275	5505	4975
50°	6075	5176	4575
55°	5859	4835	4141
60°	5624	4459	3697
65°	5408	3989	3261
70°	5094	3472	2769
75°	4697	2879	2249
80°	4096	2194	2064
85°	3473	1991	1871



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.1	2.3
10°-20°	237.4	6.3
20°-30°	342.8	9.1
30°-40°	388.6	10.3
40°-50°	375.2	10.0
50°-60°	312.0	8.3
60°-70°	215.4	5.7
70°-80°	109.2	2.9
80°-90°	29.6	0.8
90°-100°	18.5	0.5
100°-110°	117.8	3.1
110°-120°	225.4	6.0
120°-130°	286.1	7.6
130°-140°	306.1	8.1
140°-150°	286.3	7.6
150°-160°	230.9	6.1
160°-170°	148.9	4.0
170°-180°	51.3	1.4
0°-30°	665.3	17.7
0°-40°	1053.9	28.0
0°-60°	1741.1	46.2
0°-90°	2095.3	55.6
90°-120°	361.7	9.6
90°-150°	1240.3	32.9
90°-180°	1671.0	44.4
0°-180°	3766.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	906	906	906	906	906	
5°	905	902	894	900	899	86
15°	862	855	838	837	832	243
25°	779	766	738	727	720	359
35°	674	651	617	594	581	421
45°	550	523	482	449	436	424
55°	416	388	344	309	294	372
65°	283	252	209	180	171	279
75°	151	125	92	77	72	159
85°	38	24	22	20	20	42
90°	1	6	9	11	12	3
95°	22	9	9	11	12	29
105°	122	124	126	129	115	127
115°	227	228	228	229	229	223
125°	319	321	320	321	322	285
135°	396	396	397	398	399	305
145°	457	458	458	458	459	285
155°	501	501	500	501	500	231
165°	528	526	526	529	526	149
175°	540	538	538	541	537	51
180°	540	540	540	540	540	



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	908.5	907.9	907.5	907.0	906.5	905.5	904.2	902.9	901.4	900.1	901.4
5°	904.8	904.2	903.6	902.9	902.4	901.2	899.3	897.4	895.5	893.8	895.3
7.5°	896.6	896.0	895.4	894.7	894.0	892.5	890.1	887.7	885.3	882.9	883.9
10°	888.9	888.1	887.3	886.5	885.8	884.0	881.3	878.4	875.7	872.9	873.5
12.5°	878.9	878.0	877.1	876.2	875.3	873.3	870.0	866.7	863.4	860.1	860.5
15°	861.8	860.4	859.1	857.6	856.2	853.6	849.8	846.0	842.0	838.2	837.9
17.5°	841.2	839.1	837.1	835.1	833.1	829.8	825.2	820.6	815.9	811.3	810.5
20°	825.0	823.0	821.0	819.0	817.0	813.4	808.2	802.9	797.6	792.5	791.2
22.5°	807.3	805.0	802.8	800.5	798.3	794.3	788.7	783.1	777.5	771.9	770.0
25°	779.3	776.5	773.6	770.9	768.1	763.6	757.2	750.9	744.6	738.3	735.7
27.5°	749.8	746.4	742.9	739.4	735.8	730.8	724.0	717.3	710.5	703.7	700.5
30°	729.2	725.4	721.6	717.7	713.9	708.3	701.1	693.8	686.5	679.3	675.5
32.5°	707.7	703.3	698.9	694.6	690.3	684.3	676.8	669.3	661.8	654.3	649.9
35°	673.8	668.9	663.9	659.0	654.1	647.7	640.0	632.3	624.6	616.9	611.6
37.5°	637.6	632.5	627.4	622.3	617.2	610.4	601.8	593.3	584.8	576.2	570.3
40°	612.0	606.9	601.8	596.7	591.7	584.7	576.0	567.1	558.4	549.6	543.1
42.5°	587.5	582.3	576.9	571.6	566.2	559.0	549.8	540.6	531.5	522.4	515.8
45°	549.6	543.9	538.1	532.4	526.7	519.2	510.0	500.8	491.5	482.2	474.7
47.5°	510.3	504.4	498.5	492.6	486.7	478.9	469.3	459.8	450.1	440.5	432.7
50°	483.7	477.6	471.6	465.6	459.6	451.7	441.8	431.9	422.0	412.1	404.5
52.5°	456.5	450.6	444.7	438.8	432.8	424.9	414.7	404.7	394.5	384.4	376.6
55°	416.3	410.2	404.0	397.8	391.6	383.5	373.5	363.6	353.5	343.5	335.5
57.5°	376.7	370.2	363.8	357.4	351.0	342.9	333.0	323.1	313.3	303.4	295.2
60°	348.3	342.1	336.0	329.8	323.7	315.7	305.8	295.9	286.1	276.2	268.1
62.5°	322.8	316.4	310.0	303.5	297.1	288.9	278.7	268.7	258.5	248.4	241.0
65°	283.1	276.5	269.8	263.2	256.5	248.3	238.4	228.6	218.7	208.8	202.2
67.5°	241.9	235.5	229.2	222.8	216.5	208.7	199.6	190.4	181.3	172.1	166.4
70°	215.8	209.3	202.9	196.4	189.9	182.3	173.4	164.7	155.9	147.1	142.0
72.5°	188.1	182.2	176.3	170.5	164.6	157.6	149.3	141.0	132.6	124.3	120.0
75°	150.6	144.9	139.2	133.5	127.8	121.3	114.0	106.7	99.5	92.3	88.7
77.5°	112.5	107.7	102.9	98.0	93.2	87.8	81.9	76.2	70.3	64.4	62.3
80°	88.1	83.6	79.2	74.7	70.3	65.7	61.1	56.4	51.8	47.2	46.7
82.5°	67.1	63.0	58.9	54.8	50.6	47.3	44.6	41.9	39.3	36.6	36.3
85°	37.5	34.4	31.3	28.2	25.1	23.4	22.9	22.5	21.9	21.5	21.2
87.5°	13.0	12.2	11.4	10.6	9.8	9.5	9.5	9.5	9.5	9.5	9.5
90°	1.2	2.2	3.2	4.2	5.2	6.0	6.8	7.5	8.2	8.9	9.5
92.5°	5.1	5.2	5.2	5.3	5.4	5.7	6.4	7.1	7.8	8.6	9.1
95°	22.2	19.2	16.1	13.1	10.0	8.6	8.6	8.7	8.8	8.9	9.5
97.5°	47.2	49.1	51.0	52.9	54.8	50.7	40.8	30.7	20.7	10.7	10.7
100°	66.3	67.9	69.6	71.2	72.8	67.3	54.9	42.5	30.1	17.7	16.2
102.5°	87.7	88.8	90.0	91.1	92.4	92.1	90.5	88.9	87.3	85.7	69.2
105°	121.6	122.2	122.7	123.2	123.8	124.3	124.8	125.2	125.6	126.1	126.9
107.5°	153.3	153.6	153.8	154.1	154.4	154.8	155.3	156.0	156.6	157.2	157.6
110°	174.6	174.9	175.1	175.4	175.7	176.0	176.6	177.2	177.7	178.3	178.4



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.3	195.7	196.3	196.7	197.2	197.6	197.9	198.0	198.3	198.6	198.6
115°	227.1	227.4	227.7	227.9	228.2	228.3	228.2	228.1	228.0	227.9	228.1
117.5°	255.8	256.2	256.5	256.9	257.3	257.5	257.7	257.9	258.2	258.3	258.2
120°	275.2	275.5	275.9	276.3	276.6	276.8	276.7	276.6	276.5	276.4	276.6
122.5°	293.3	293.6	293.7	294.0	294.2	294.4	294.4	294.6	294.7	294.9	295.0
125°	319.2	319.6	319.9	320.3	320.7	320.7	320.6	320.4	320.2	320.0	320.3
127.5°	343.8	343.9	344.0	344.1	344.2	344.5	344.8	345.3	345.7	346.1	346.1
130°	359.6	359.7	359.9	360.0	360.1	360.3	360.5	360.8	361.1	361.3	361.4
132.5°	374.3	374.3	374.5	374.7	374.9	375.1	375.5	375.8	376.1	376.5	376.6
135°	396.0	395.9	395.8	395.7	395.7	395.8	396.2	396.5	396.9	397.3	397.4
137.5°	415.4	415.4	415.4	415.4	415.5	415.7	416.1	416.5	416.9	417.3	417.5
140°	427.9	428.1	428.3	428.5	428.6	428.8	429.0	429.3	429.4	429.6	429.9
142.5°	439.3	439.6	440.0	440.2	440.6	440.8	440.9	441.0	441.1	441.2	441.4
145°	456.6	456.9	457.2	457.4	457.7	457.9	457.9	457.9	457.9	457.9	458.0
147.5°	470.5	471.0	471.4	472.0	472.5	472.7	472.6	472.5	472.4	472.3	472.4
150°	480.5	480.9	481.3	481.6	482.0	482.1	482.0	481.9	481.8	481.7	481.7
152.5°	488.9	489.2	489.5	489.7	490.1	490.1	490.0	489.8	489.6	489.5	489.6
155°	500.7	500.8	500.9	501.0	501.1	501.0	500.7	500.4	500.2	499.9	500.2
157.5°	510.7	510.6	510.5	510.5	510.4	510.2	510.0	509.6	509.3	509.1	509.5
160°	516.5	516.2	515.9	515.7	515.4	515.2	515.1	515.1	515.0	514.9	515.4
162.5°	521.7	521.3	520.9	520.6	520.3	520.0	520.0	519.9	519.8	519.7	520.2
165°	528.2	527.7	527.3	526.8	526.4	526.2	526.2	526.2	526.2	526.2	526.9
167.5°	533.3	532.9	532.4	532.0	531.5	531.2	531.2	531.1	531.1	531.0	531.8
170°	536.3	535.7	535.2	534.7	534.1	533.9	534.0	534.0	534.1	534.2	534.9
172.5°	538.2	537.7	537.2	536.6	536.1	535.8	535.9	536.0	536.1	536.2	536.9
175°	540.3	539.8	539.2	538.7	538.1	538.0	538.1	538.1	538.2	538.3	539.1
177.5°	541.3	540.8	540.3	539.8	539.3	539.1	539.2	539.4	539.5	539.7	540.2
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	906.2	906.2	906.2	906.2	906.2	906.2	906.2	906.2
2.5°	902.9	904.2	905.5	906.2	906.1	905.9	905.8	905.7
5°	896.8	898.4	899.9	900.5	900.2	899.9	899.6	899.3
7.5°	884.8	885.8	886.9	887.1	886.6	886.1	885.6	885.1
10°	874.1	874.8	875.4	875.4	874.8	874.1	873.5	872.9
12.5°	860.9	861.2	861.7	861.4	860.5	859.7	858.8	857.9
15°	837.6	837.3	837.0	836.3	835.2	834.1	833.0	832.0
17.5°	809.6	808.7	807.8	806.6	804.9	803.3	801.6	800.0
20°	790.0	788.7	787.5	785.9	783.9	781.9	779.9	777.8
22.5°	768.2	766.3	764.5	762.8	761.1	759.5	757.9	756.2
25°	733.1	730.4	727.8	725.8	724.2	722.6	721.1	719.5
27.5°	697.2	694.0	690.8	688.0	685.8	683.6	681.4	679.2
30°	671.6	667.7	663.9	660.8	658.3	655.8	653.4	650.9
32.5°	645.4	641.0	636.4	633.0	630.7	628.4	626.0	623.7
35°	606.4	601.1	595.9	591.9	589.2	586.3	583.5	580.8
37.5°	564.5	558.7	552.8	548.5	545.6	542.9	540.1	537.3
40°	536.6	530.1	523.6	519.1	516.2	513.4	510.7	507.9
42.5°	509.2	502.6	496.0	491.2	488.3	485.4	482.5	479.7
45°	467.2	459.6	452.0	446.8	444.1	441.3	438.5	435.8
47.5°	424.8	417.0	409.1	403.7	400.6	397.6	394.6	391.5
50°	396.7	389.1	381.3	376.0	373.1	370.1	367.2	364.3
52.5°	368.7	360.9	353.1	347.7	344.6	341.5	338.5	335.5
55°	327.4	319.4	311.4	305.9	303.0	300.1	297.1	294.2
57.5°	287.0	278.9	270.8	265.6	263.4	261.2	259.0	256.7
60°	260.1	252.1	244.1	238.9	236.4	233.9	231.5	229.0
62.5°	233.6	226.2	218.8	214.1	212.1	210.2	208.2	206.3
65°	195.6	189.0	182.4	178.1	176.3	174.4	172.5	170.7
67.5°	160.7	155.0	149.3	145.4	143.4	141.3	139.3	137.2
70°	137.0	131.9	126.7	123.4	121.9	120.4	118.8	117.3
72.5°	115.7	111.3	106.9	104.1	102.6	101.2	99.8	98.4
75°	85.2	81.7	78.1	75.9	74.9	74.0	73.1	72.1
77.5°	60.3	58.2	56.1	54.9	54.7	54.4	54.1	53.9
80°	46.3	45.8	45.3	45.0	44.9	44.7	44.6	44.4
82.5°	35.9	35.6	35.3	35.0	34.9	34.7	34.6	34.4
85°	20.9	20.6	20.2	20.2	20.2	20.2	20.2	20.2
87.5°	9.5	9.5	9.5	9.5	9.7	9.9	10.1	10.2
90°	10.0	10.5	11.1	11.4	11.6	11.8	11.9	12.1
92.5°	9.6	10.2	10.7	11.0	11.1	11.1	11.1	11.1
95°	10.0	10.5	11.1	11.3	11.4	11.5	11.6	11.7
97.5°	10.8	10.8	10.9	11.0	11.1	11.1	11.2	11.3
100°	14.7	13.2	11.7	11.0	11.1	11.1	11.2	11.3
102.5°	52.7	36.3	19.8	11.6	11.6	11.6	11.6	11.7
105°	127.7	128.5	129.3	128.1	124.8	121.6	118.4	115.2
107.5°	158.0	158.4	158.8	159.2	159.5	159.8	160.2	160.5
110°	178.6	178.8	179.0	179.1	179.4	179.7	179.9	180.2



TEST NUMBER: P333037-940

CATALOG NUMBER: S124RDIW-S575D470U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.5	198.5	198.4	198.6	198.9	199.3	199.7	199.9
115°	228.3	228.5	228.6	228.7	228.7	228.7	228.7	228.7
117.5°	258.2	258.2	258.2	258.2	258.1	258.1	258.1	258.0
120°	276.8	277.0	277.1	277.1	277.0	276.8	276.6	276.4
122.5°	295.1	295.2	295.2	295.2	295.1	294.9	294.7	294.5
125°	320.6	320.8	321.1	321.3	321.4	321.5	321.6	321.6
127.5°	346.0	345.9	345.9	345.8	345.7	345.6	345.6	345.5
130°	361.5	361.6	361.7	361.7	361.7	361.7	361.7	361.7
132.5°	376.7	376.7	376.8	376.8	376.7	376.7	376.7	376.6
135°	397.6	397.8	398.0	398.1	398.3	398.5	398.7	398.9
137.5°	417.7	417.9	418.1	418.1	418.1	418.0	418.0	417.9
140°	430.2	430.4	430.7	430.9	431.0	431.1	431.1	431.2
142.5°	441.6	441.8	442.0	442.1	442.1	442.2	442.2	442.2
145°	458.1	458.2	458.3	458.3	458.5	458.7	458.9	459.1
147.5°	472.5	472.5	472.6	472.7	472.8	472.9	473.0	473.1
150°	481.7	481.7	481.7	481.8	481.9	482.0	482.1	482.1
152.5°	489.7	489.9	490.1	490.1	490.1	490.0	489.9	489.9
155°	500.6	501.0	501.3	501.4	501.1	500.9	500.6	500.3
157.5°	510.0	510.4	510.9	510.9	510.4	510.0	509.5	509.1
160°	515.9	516.5	517.0	517.0	516.5	515.9	515.4	514.9
162.5°	520.8	521.3	521.8	521.8	521.2	520.6	520.0	519.4
165°	527.6	528.3	529.1	529.0	528.2	527.4	526.6	525.8
167.5°	532.6	533.4	534.2	534.1	533.2	532.4	531.5	530.6
170°	535.7	536.4	537.2	537.1	536.1	535.2	534.3	533.4
172.5°	537.6	538.3	539.0	539.0	538.0	537.0	536.0	535.0
175°	539.9	540.7	541.5	541.4	540.3	539.2	538.1	537.1
177.5°	540.8	541.4	542.0	541.8	541.0	540.1	539.2	538.4
180°	540.3	540.3	540.3	540.3	540.3	540.3	540.3	540.3

(END OF REPORT)