

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333065-940

Luminaire Tested: **S124RDIW-S795D1050U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333065-940
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S124RDIW-S795D1050U940-4F0-1E-UDD-F
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6602.0 lumens
Efficiency: N/A
Efficacy: 125.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	50	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	43	62	52	45	40	44	38	34	36	32	29	29	26	24	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	32	27	33	27	23	27	23	20	22	19	17	14
9	50	38	30	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.4	1.8
10°-20°	324.5	4.9
20°-30°	468.6	7.1
30°-40°	531.1	8.0
40°-50°	512.9	7.8
50°-60°	426.5	6.5
60°-70°	294.5	4.5
70°-80°	149.3	2.3
80°-90°	41.8	0.6
90°-100°	41.3	0.6
100°-110°	263.4	4.0
110°-120°	503.9	7.6
120°-130°	639.7	9.7
130°-140°	684.4	10.4
140°-150°	640.0	9.7
150°-160°	516.1	7.8
160°-170°	332.9	5.0
170°-180°	114.7	1.7
0°-30°	909.4	13.8
0°-40°	1440.5	21.8
0°-60°	2379.9	36.0
0°-90°	2865.4	43.4
90°-120°	808.6	12.2
90°-150°	2772.8	42.0
90°-180°	3737.0	56.6
0°-180°	6602.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	3	12	20	25	27	5
95°	50	21	20	25	26	64
105°	272	277	282	288	258	285
115°	508	510	510	511	511	499
125°	714	717	716	718	719	637
135°	885	885	888	890	892	682
145°	1021	1023	1024	1025	1026	638
155°	1119	1120	1118	1121	1118	516
165°	1181	1177	1176	1183	1175	334
175°	1208	1203	1204	1210	1201	115
180°	1208	1208	1208	1208	1208	



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	18.0	17.1	16.1	15.2	14.4	14.0	14.2	14.3	14.4	14.6	14.7
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	11.4	11.5	11.6	11.8	11.9	12.8	14.4	16.0	17.6	19.2	20.3
95°	49.7	42.9	36.0	29.2	22.4	19.1	19.3	19.4	19.7	19.9	21.0
97.5°	105.5	109.8	114.0	118.3	122.5	113.5	91.0	68.7	46.3	23.8	24.0
100°	148.2	151.8	155.4	159.0	162.6	150.6	122.9	95.1	67.5	39.8	36.4
102.5°	195.9	198.5	201.2	203.8	206.4	206.0	202.4	198.8	195.1	191.5	154.7
105°	272.0	273.1	274.4	275.5	276.8	277.9	278.8	279.9	280.9	281.9	283.7
107.5°	342.6	343.2	343.8	344.4	345.0	346.0	347.3	348.7	350.1	351.4	352.3
110°	390.3	390.9	391.5	392.1	392.7	393.6	394.8	396.0	397.3	398.4	398.9



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	436.6	437.7	438.7	439.8	440.9	441.8	442.3	442.8	443.4	444.0	443.9
115°	507.7	508.4	509.0	509.5	510.1	510.3	510.1	510.0	509.8	509.5	510.0
117.5°	571.9	572.7	573.5	574.3	575.1	575.7	576.1	576.6	577.0	577.5	577.4
120°	615.3	616.1	616.9	617.7	618.5	618.8	618.6	618.4	618.1	618.0	618.4
122.5°	655.8	656.2	656.7	657.2	657.6	658.1	658.4	658.6	658.9	659.2	659.4
125°	713.7	714.5	715.3	716.1	716.9	717.1	716.8	716.3	716.0	715.5	716.1
127.5°	768.7	768.8	769.1	769.3	769.5	770.0	771.0	771.9	772.8	773.7	773.6
130°	804.1	804.3	804.5	804.7	804.9	805.3	805.9	806.5	807.1	807.7	807.9
132.5°	836.6	837.0	837.3	837.7	838.0	838.7	839.4	840.2	840.9	841.7	841.9
135°	885.4	885.2	885.0	884.8	884.6	884.9	885.7	886.5	887.3	888.1	888.5
137.5°	928.5	928.6	928.7	928.8	928.9	929.3	930.2	931.1	932.0	932.9	933.4
140°	956.8	957.2	957.6	958.0	958.4	958.8	959.2	959.6	960.0	960.4	961.0
142.5°	982.0	982.8	983.5	984.3	985.0	985.4	985.7	985.9	986.1	986.4	986.9
145°	1020.9	1021.5	1022.1	1022.7	1023.3	1023.6	1023.6	1023.6	1023.6	1023.6	1023.9
147.5°	1051.8	1052.9	1054.1	1055.2	1056.3	1056.8	1056.6	1056.4	1056.1	1056.0	1056.1
150°	1074.2	1075.0	1075.8	1076.7	1077.5	1077.7	1077.5	1077.4	1077.1	1076.9	1076.9
152.5°	1093.0	1093.7	1094.3	1094.9	1095.6	1095.7	1095.4	1095.0	1094.7	1094.3	1094.6
155°	1119.4	1119.6	1119.8	1120.0	1120.2	1120.0	1119.4	1118.8	1118.2	1117.6	1118.4
157.5°	1141.7	1141.5	1141.4	1141.2	1141.1	1140.8	1140.1	1139.3	1138.7	1138.0	1139.1
160°	1154.6	1154.1	1153.4	1152.8	1152.2	1151.8	1151.6	1151.4	1151.2	1151.0	1152.2
162.5°	1166.2	1165.5	1164.7	1163.9	1163.1	1162.6	1162.4	1162.3	1162.1	1161.8	1163.1
165°	1180.8	1179.8	1178.8	1177.8	1176.8	1176.3	1176.3	1176.3	1176.3	1176.3	1177.9
167.5°	1192.4	1191.3	1190.3	1189.3	1188.2	1187.7	1187.5	1187.4	1187.3	1187.1	1188.9
170°	1198.9	1197.7	1196.5	1195.2	1194.1	1193.6	1193.7	1194.0	1194.2	1194.4	1196.0
172.5°	1203.2	1202.0	1200.8	1199.6	1198.4	1197.9	1198.1	1198.3	1198.5	1198.7	1200.3
175°	1207.9	1206.8	1205.5	1204.3	1203.1	1202.7	1202.8	1203.0	1203.2	1203.5	1205.2
177.5°	1210.1	1209.0	1207.8	1206.8	1205.6	1205.2	1205.5	1205.9	1206.1	1206.5	1207.7
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	14.7	14.8	14.9	15.1	15.3	15.5	15.8	16.1
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	21.6	22.7	24.0	24.6	24.7	24.8	24.9	25.0
95°	22.3	23.5	24.7	25.4	25.6	25.8	26.0	26.2
97.5°	24.1	24.3	24.3	24.5	24.7	24.9	25.1	25.3
100°	32.9	29.5	26.1	24.5	24.7	24.9	25.1	25.3
102.5°	117.9	81.1	44.2	25.9	25.9	25.9	25.9	26.0
105°	285.5	287.3	289.1	286.4	279.2	272.0	264.7	257.5
107.5°	353.2	354.1	355.0	355.8	356.6	357.3	358.1	358.8
110°	399.2	399.7	400.0	400.6	401.2	401.7	402.3	403.0



TEST NUMBER: P333065-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	443.8	443.7	443.6	444.0	444.8	445.5	446.3	447.0
115°	510.3	510.8	511.1	511.4	511.4	511.4	511.4	511.4
117.5°	577.3	577.3	577.2	577.1	577.0	576.9	576.8	576.8
120°	618.8	619.2	619.6	619.6	619.2	618.8	618.4	618.0
122.5°	659.7	659.9	660.1	660.0	659.7	659.2	658.9	658.4
125°	716.8	717.4	717.9	718.4	718.5	718.7	719.0	719.2
127.5°	773.5	773.4	773.2	773.1	772.9	772.8	772.6	772.5
130°	808.1	808.3	808.5	808.6	808.6	808.6	808.6	808.6
132.5°	842.0	842.3	842.5	842.5	842.3	842.1	842.0	841.9
135°	888.9	889.3	889.7	890.1	890.6	890.9	891.4	891.7
137.5°	933.8	934.2	934.7	934.9	934.7	934.6	934.5	934.3
140°	961.6	962.2	962.8	963.2	963.4	963.6	963.8	964.0
142.5°	987.3	987.7	988.2	988.4	988.5	988.5	988.6	988.6
145°	1024.0	1024.2	1024.4	1024.8	1025.1	1025.6	1025.9	1026.4
147.5°	1056.3	1056.4	1056.6	1056.8	1057.0	1057.2	1057.4	1057.6
150°	1076.9	1076.9	1076.9	1077.0	1077.2	1077.5	1077.6	1077.8
152.5°	1094.9	1095.2	1095.6	1095.6	1095.6	1095.4	1095.3	1095.2
155°	1119.2	1120.0	1120.8	1120.9	1120.3	1119.7	1119.1	1118.5
157.5°	1140.1	1141.1	1142.2	1142.2	1141.1	1140.1	1139.1	1138.0
160°	1153.4	1154.6	1155.8	1155.8	1154.6	1153.4	1152.2	1151.0
162.5°	1164.2	1165.5	1166.6	1166.6	1165.2	1163.9	1162.5	1161.1
165°	1179.6	1181.2	1182.8	1182.6	1180.8	1179.0	1177.2	1175.4
167.5°	1190.7	1192.5	1194.2	1194.1	1192.1	1190.1	1188.1	1186.1
170°	1197.6	1199.2	1200.8	1200.6	1198.5	1196.6	1194.5	1192.6
172.5°	1201.9	1203.5	1205.1	1204.9	1202.7	1200.5	1198.4	1196.1
175°	1207.0	1208.8	1210.7	1210.3	1207.9	1205.5	1203.1	1200.7
177.5°	1209.1	1210.3	1211.7	1211.3	1209.3	1207.5	1205.5	1203.6
180°	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9	1207.9

(END OF REPORT)