

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333066-940

Luminaire Tested: **S124RDIW-S795D1050U940-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333066-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-10,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1050U940-4F0-1E-UDD-F1  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6106.0 lumens  
Efficiency: N/A  
Efficacy: 116.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40
2	89	82	76	71	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	48	46	43	40	37	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	28	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	24	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	22	18	16	14
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.4	1.9
10°-20°	324.5	5.3
20°-30°	468.6	7.7
30°-40°	531.1	8.7
40°-50°	512.9	8.4
50°-60°	426.5	7.0
60°-70°	294.5	4.8
70°-80°	149.3	2.4
80°-90°	41.8	0.7
90°-100°	77.0	1.3
100°-110°	228.2	3.7
110°-120°	387.4	6.3
120°-130°	510.8	8.4
130°-140°	573.6	9.4
140°-150°	563.7	9.2
150°-160°	474.1	7.8
160°-170°	315.4	5.2
170°-180°	110.5	1.8
0°-30°	909.4	14.9
0°-40°	1440.5	23.6
0°-60°	2379.9	39.0
0°-90°	2865.4	46.9
90°-120°	692.6	11.3
90°-150°	2340.6	38.3
90°-180°	3241.0	53.1
0°-180°	6106.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	3	12	20	25	27	6
95°	54	62	69	71	71	60
105°	210	212	215	218	220	223
115°	394	394	392	391	390	388
125°	574	574	573	571	569	511
135°	740	745	745	743	741	572
145°	899	902	903	902	900	562
155°	1030	1030	1029	1032	1029	474
165°	1121	1118	1116	1121	1118	316
175°	1166	1162	1161	1166	1161	111
180°	1168	1168	1168	1168	1168	



TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	18.0	17.1	16.1	15.2	14.4	14.0	14.2	14.3	14.4	14.6	14.7
90°	2.7	4.9	7.1	9.4	11.5	13.5	15.1	16.7	18.3	19.9	21.0
92.5°	19.4	21.8	24.4	26.9	29.4	31.3	32.4	33.5	34.7	35.8	36.5
95°	54.2	56.0	57.8	59.7	61.4	63.0	64.5	65.8	67.2	68.7	69.3
97.5°	94.7	96.1	97.6	99.0	100.5	102.0	103.6	105.3	106.9	108.6	109.3
100°	126.4	127.2	128.0	128.9	129.7	131.0	132.8	134.6	136.4	138.2	138.6
102.5°	159.7	160.1	160.3	160.7	161.0	161.9	163.6	165.2	166.9	168.5	169.2
105°	210.4	210.7	210.9	211.1	211.2	211.8	212.6	213.4	214.2	215.0	215.6
107.5°	263.8	264.0	264.2	264.5	264.7	264.9	265.0	265.2	265.3	265.4	266.0
110°	299.9	300.3	300.7	301.1	301.5	301.6	301.4	301.2	301.0	300.8	300.4



TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	337.5	337.6	337.7	337.7	337.8	337.7	337.3	337.0	336.6	336.3	336.2
115°	393.9	393.9	393.9	393.9	393.9	393.7	393.2	392.9	392.4	392.1	391.8
117.5°	447.0	447.1	447.3	447.5	447.6	447.5	447.3	447.0	446.7	446.4	445.8
120°	482.4	483.2	484.0	484.8	485.6	485.7	485.1	484.5	483.9	483.3	482.3
122.5°	519.2	519.6	519.9	520.2	520.5	520.6	520.2	520.0	519.7	519.4	518.7
125°	573.6	573.6	573.6	573.6	573.6	573.5	573.3	573.1	572.9	572.7	572.3
127.5°	622.9	623.6	624.1	624.7	625.4	625.5	625.2	624.8	624.6	624.2	623.8
130°	657.6	658.3	658.8	659.4	660.0	660.3	660.3	660.3	660.3	660.3	660.0
132.5°	693.0	693.5	693.9	694.4	694.8	694.9	694.8	694.6	694.5	694.3	693.9
135°	739.9	741.0	742.3	743.4	744.7	745.3	745.3	745.3	745.3	745.3	744.8
137.5°	790.8	791.3	791.9	792.5	793.0	793.4	793.8	794.2	794.4	794.8	794.2
140°	824.7	825.2	825.5	826.0	826.3	826.5	826.5	826.5	826.5	826.5	826.3
142.5°	855.9	856.2	856.7	857.0	857.5	857.6	857.4	857.2	857.1	856.9	856.8
145°	898.8	899.6	900.4	901.3	902.1	902.5	902.8	902.9	903.1	903.3	903.1
147.5°	941.5	942.4	943.4	944.3	945.3	945.7	945.6	945.4	945.2	945.0	944.9
150°	967.5	968.3	969.1	969.9	970.7	971.1	971.1	971.1	971.1	971.1	971.1
152.5°	992.0	992.6	993.0	993.5	994.0	994.3	994.4	994.6	994.8	995.0	995.4
155°	1029.8	1029.8	1029.8	1029.8	1029.8	1029.7	1029.5	1029.3	1029.1	1028.9	1029.7
157.5°	1061.6	1061.2	1060.9	1060.5	1060.2	1060.0	1059.9	1059.9	1059.8	1059.8	1060.4
160°	1080.4	1080.2	1080.0	1079.8	1079.6	1079.4	1079.1	1079.0	1078.8	1078.6	1079.1
162.5°	1097.7	1097.3	1096.7	1096.2	1095.6	1095.3	1095.1	1094.9	1094.7	1094.5	1095.6
165°	1121.1	1120.4	1119.8	1119.3	1118.7	1118.1	1117.8	1117.3	1117.0	1116.5	1117.8
167.5°	1138.9	1138.1	1137.3	1136.4	1135.6	1135.1	1135.2	1135.2	1135.2	1135.3	1136.5
170°	1149.1	1148.1	1147.0	1146.0	1145.0	1144.6	1144.9	1145.0	1145.2	1145.4	1146.7
172.5°	1156.3	1155.4	1154.6	1153.8	1152.9	1152.5	1152.5	1152.6	1152.6	1152.6	1154.1
175°	1166.2	1165.2	1164.2	1163.2	1162.2	1161.6	1161.4	1161.2	1161.0	1160.8	1162.2
177.5°	1169.5	1168.7	1167.9	1167.1	1166.3	1165.8	1165.8	1165.8	1165.8	1165.8	1167.0
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1



TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	14.7	14.8	14.9	15.1	15.3	15.5	15.8	16.1
90°	22.3	23.5	24.7	25.5	25.9	26.3	26.7	27.1
92.5°	37.2	37.9	38.7	39.1	39.4	39.6	39.9	40.1
95°	69.8	70.4	71.1	71.3	71.3	71.3	71.3	71.3
97.5°	110.0	110.8	111.5	111.8	111.8	111.8	111.8	111.8
100°	139.0	139.4	139.8	140.0	140.0	140.0	140.0	140.0
102.5°	169.7	170.2	170.9	171.2	171.3	171.5	171.7	171.8
105°	216.2	216.8	217.4	218.0	218.6	219.2	219.8	220.4
107.5°	266.5	267.1	267.7	267.9	267.9	267.9	267.8	267.8
110°	300.0	299.6	299.2	299.3	299.9	300.5	301.1	301.8





TEST NUMBER: P333066-940

CATALOG NUMBER: S124RDIW-S795D1050U940-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	336.1	336.0	335.9	335.9	336.1	336.2	336.3	336.4
115°	391.6	391.5	391.3	391.0	390.8	390.7	390.5	390.2
117.5°	445.1	444.3	443.7	443.2	442.7	442.4	441.9	441.6
120°	481.3	480.3	479.3	478.9	479.4	479.7	480.2	480.5
122.5°	518.1	517.4	516.7	515.9	515.2	514.5	513.8	513.1
125°	571.9	571.5	571.1	570.7	570.3	569.9	569.5	569.1
127.5°	623.4	623.0	622.6	622.2	621.9	621.6	621.3	621.0
130°	659.5	659.2	658.7	658.2	657.4	656.6	655.8	655.0
132.5°	693.5	693.1	692.7	692.3	692.1	691.7	691.3	691.1
135°	744.5	744.0	743.7	743.2	742.5	741.9	741.4	740.7
137.5°	793.7	793.2	792.6	792.5	792.6	792.7	792.8	792.9
140°	826.2	826.0	825.7	825.5	825.4	825.2	824.9	824.7
142.5°	856.8	856.8	856.8	856.7	856.7	856.7	856.6	856.6
145°	902.9	902.8	902.5	902.1	901.5	900.9	900.4	899.7
147.5°	944.8	944.6	944.4	944.2	944.1	943.9	943.6	943.4
150°	971.1	971.1	971.1	971.0	970.8	970.6	970.4	970.2
152.5°	995.9	996.4	996.8	996.8	996.3	995.8	995.2	994.8
155°	1030.6	1031.4	1032.2	1032.2	1031.4	1030.6	1029.7	1028.9
157.5°	1061.0	1061.6	1062.2	1062.2	1061.5	1060.8	1060.2	1059.4
160°	1079.8	1080.4	1081.0	1080.8	1079.8	1078.8	1077.8	1076.7
162.5°	1096.6	1097.7	1098.9	1098.9	1097.9	1096.9	1095.8	1094.8
165°	1118.9	1120.2	1121.3	1121.5	1120.7	1119.9	1119.1	1118.3
167.5°	1137.7	1138.9	1140.1	1140.1	1138.9	1137.6	1136.4	1135.1
170°	1147.8	1149.1	1150.2	1150.1	1148.8	1147.4	1145.9	1144.5
172.5°	1155.4	1156.7	1158.2	1158.1	1156.7	1155.3	1153.9	1152.4
175°	1163.6	1165.0	1166.4	1166.4	1165.0	1163.6	1162.2	1160.8
177.5°	1168.1	1169.2	1170.4	1170.3	1168.9	1167.7	1166.4	1165.1
180°	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1	1168.1

(END OF REPORT)