

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333073-940

Luminaire Tested: **S124RDIW-S795D1560U940-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333073-940  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-6,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S124RDIW-S795D1560U940-4F0-1E-UDD-F  
Description: DEFINE 4 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 795 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8428.6 lumens  
Efficiency: N/A  
Efficacy: 123.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24  
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	87	83	85	82	78	76	65	63	61	51	49	48	37	36	35	29
2	86	79	73	68	77	71	67	62	57	54	51	45	42	40	33	31	30	25
3	79	69	62	57	71	63	57	52	51	47	43	40	37	34	29	27	26	21
4	72	62	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	32	32	28	25	24	21	19	16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	21	19	17	14
7	56	44	37	31	51	40	34	29	33	28	24	26	22	20	20	17	15	12
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	11
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12	10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10001	10001	10001
5°	10023	9900	9961
10°	9960	9781	9781
15°	9845	9576	9504
20°	9688	9306	9135
25°	9487	8989	8761
30°	9292	8655	8294
35°	9077	8310	7824
40°	8816	7917	7317
45°	8576	7526	6801
50°	8303	7076	6253
55°	8010	6608	5661
60°	7689	6095	5054
65°	7393	5454	4458
70°	6963	4747	3784
75°	6419	3936	3075
80°	5602	2999	2822
85°	4742	2723	2547



TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	116.4	1.4
10°-20°	324.5	3.8
20°-30°	468.6	5.6
30°-40°	531.1	6.3
40°-50°	512.9	6.1
50°-60°	426.5	5.1
60°-70°	294.5	3.5
70°-80°	149.3	1.8
80°-90°	43.5	0.5
90°-100°	61.5	0.7
100°-110°	392.1	4.7
110°-120°	750.0	8.9
120°-130°	952.1	11.3
130°-140°	1018.7	12.1
140°-150°	952.6	11.3
150°-160°	768.2	9.1
160°-170°	495.5	5.9
170°-180°	170.8	2.0
0°-30°	909.4	10.8
0°-40°	1440.5	17.1
0°-60°	2379.9	28.2
0°-90°	2867.2	34.0
90°-120°	1203.6	14.3
90°-150°	4127.0	49.0
90°-180°	5561.0	66.0
0°-180°	8428.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1239	1239	1239	1239	1239	
5°	1237	1233	1222	1230	1229	117
15°	1178	1169	1146	1144	1137	332
25°	1065	1047	1009	993	984	491
35°	921	890	843	812	794	575
45°	751	715	659	614	596	579
55°	569	530	470	422	402	509
65°	387	345	286	246	233	382
75°	206	170	126	105	99	217
85°	51	33	29	28	28	58
90°	4	19	30	37	40	6
95°	74	31	30	37	39	95
105°	405	413	420	428	383	423
115°	756	759	758	761	761	743
125°	1062	1067	1065	1069	1070	948
135°	1318	1317	1322	1325	1327	1015
145°	1520	1523	1524	1525	1528	949
155°	1666	1667	1663	1668	1665	768
165°	1758	1751	1751	1760	1750	496
175°	1798	1790	1791	1802	1787	171
180°	1798	1798	1798	1798	1798	



TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1241.8	1241.1	1240.4	1239.7	1239.0	1237.8	1235.9	1234.1	1232.3	1230.4	1232.3
5°	1236.8	1236.0	1235.1	1234.3	1233.4	1231.8	1229.2	1226.7	1224.1	1221.6	1223.8
7.5°	1225.7	1224.8	1223.9	1223.0	1222.1	1220.0	1216.7	1213.4	1210.1	1206.8	1208.2
10°	1215.0	1214.0	1212.9	1211.8	1210.8	1208.4	1204.6	1200.8	1197.0	1193.2	1194.0
12.5°	1201.3	1200.2	1198.9	1197.7	1196.5	1193.6	1189.2	1184.6	1180.2	1175.7	1176.3
15°	1178.0	1176.2	1174.2	1172.3	1170.5	1166.9	1161.5	1156.3	1151.0	1145.8	1145.3
17.5°	1149.8	1147.0	1144.2	1141.6	1138.8	1134.3	1127.9	1121.6	1115.3	1108.9	1107.8
20°	1127.7	1125.0	1122.3	1119.5	1116.8	1111.9	1104.7	1097.5	1090.3	1083.2	1081.5
22.5°	1103.5	1100.4	1097.3	1094.2	1091.2	1085.7	1078.1	1070.4	1062.7	1055.1	1052.6
25°	1065.1	1061.3	1057.6	1053.7	1050.0	1043.7	1035.1	1026.4	1017.8	1009.1	1005.6
27.5°	1024.9	1020.2	1015.4	1010.7	1005.8	998.9	989.6	980.4	971.2	962.0	957.5
30°	996.8	991.6	986.3	981.1	975.8	968.2	958.3	948.4	938.4	928.5	923.3
32.5°	967.2	961.4	955.4	949.4	943.5	935.4	925.1	914.9	904.6	894.4	888.3
35°	921.0	914.3	907.5	900.7	894.0	885.4	874.9	864.2	853.7	843.2	836.1
37.5°	871.5	864.5	857.6	850.6	843.6	834.4	822.7	811.0	799.3	787.6	779.6
40°	836.6	829.6	822.7	815.7	808.8	799.2	787.2	775.3	763.2	751.2	742.3
42.5°	803.2	795.9	788.6	781.3	774.0	764.1	751.6	739.0	726.6	714.0	705.0
45°	751.2	743.4	735.6	727.8	720.0	709.8	697.1	684.5	671.8	659.2	648.9
47.5°	697.5	689.5	681.4	673.3	665.3	654.7	641.6	628.4	615.3	602.1	591.4
50°	661.1	652.9	644.6	636.4	628.2	617.3	603.9	590.4	576.8	563.4	552.9
52.5°	623.9	615.9	607.8	599.8	591.7	580.8	566.9	553.1	539.3	525.5	514.8
55°	569.1	560.6	552.2	543.8	535.4	524.3	510.6	496.9	483.2	469.5	458.5
57.5°	514.9	506.0	497.3	488.6	479.7	468.6	455.1	441.7	428.2	414.6	403.6
60°	476.2	467.7	459.3	450.8	442.4	431.5	417.9	404.5	391.0	377.5	366.5
62.5°	441.2	432.5	423.7	414.9	406.2	394.8	381.0	367.2	353.4	339.6	329.4
65°	387.0	377.9	368.8	359.8	350.7	339.5	325.9	312.5	299.0	285.5	276.4
67.5°	330.6	322.0	313.3	304.6	295.9	285.3	272.8	260.3	247.7	235.2	227.4
70°	295.0	286.1	277.2	268.4	259.6	249.1	237.1	225.1	213.1	201.1	194.1
72.5°	257.1	249.1	241.0	233.0	225.0	215.3	204.0	192.6	181.3	170.0	164.0
75°	205.8	198.0	190.2	182.4	174.6	165.8	155.9	146.0	136.1	126.2	121.3
77.5°	153.8	147.2	140.6	134.0	127.3	120.0	112.1	104.1	96.0	88.0	85.2
80°	120.5	114.3	108.3	102.1	96.0	89.8	83.5	77.1	70.8	64.5	63.8
82.5°	91.7	86.1	80.4	74.8	69.2	64.6	61.0	57.3	53.7	50.1	49.6
85°	51.2	47.0	42.8	38.6	34.3	31.9	31.3	30.7	30.1	29.4	29.0
87.5°	18.3	17.6	16.9	16.1	15.5	15.3	15.6	16.0	16.2	16.5	16.8
90°	4.0	7.3	10.6	13.9	17.2	20.1	22.4	24.8	27.2	29.6	31.4
92.5°	16.9	17.1	17.3	17.5	17.7	18.9	21.3	23.7	26.1	28.5	30.3
95°	73.9	63.8	53.7	43.5	33.3	28.4	28.7	29.0	29.2	29.6	31.4
97.5°	157.0	163.4	169.7	176.1	182.4	168.9	135.5	102.2	68.8	35.5	35.7
100°	220.5	226.0	231.3	236.7	242.0	224.1	182.9	141.6	100.4	59.2	54.1
102.5°	291.5	295.5	299.4	303.4	307.3	306.6	301.2	295.9	290.4	285.1	230.2
105°	404.7	406.5	408.3	410.2	412.0	413.6	415.1	416.6	418.0	419.5	422.2
107.5°	509.9	510.9	511.8	512.6	513.5	515.0	517.0	519.1	521.0	523.1	524.4
110°	580.9	581.8	582.7	583.6	584.5	585.9	587.6	589.4	591.2	593.0	593.6



TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	649.8	651.4	653.0	654.6	656.2	657.5	658.3	659.2	660.0	660.8	660.7
115°	755.7	756.6	757.5	758.4	759.3	759.6	759.3	759.0	758.8	758.4	759.0
117.5°	851.2	852.4	853.6	854.8	856.0	856.9	857.6	858.3	858.9	859.5	859.4
120°	915.8	916.9	918.2	919.4	920.5	921.0	920.7	920.4	920.1	919.8	920.4
122.5°	976.0	976.7	977.4	978.1	978.9	979.5	979.9	980.3	980.7	981.1	981.5
125°	1062.4	1063.5	1064.7	1066.0	1067.1	1067.4	1066.8	1066.2	1065.6	1065.1	1066.0
127.5°	1144.1	1144.4	1144.7	1145.0	1145.3	1146.1	1147.5	1148.9	1150.2	1151.6	1151.5
130°	1196.9	1197.1	1197.4	1197.7	1198.0	1198.6	1199.5	1200.4	1201.3	1202.2	1202.5
132.5°	1245.2	1245.7	1246.3	1246.9	1247.4	1248.2	1249.4	1250.4	1251.6	1252.8	1253.0
135°	1317.9	1317.5	1317.2	1317.0	1316.6	1317.1	1318.3	1319.5	1320.7	1321.9	1322.5
137.5°	1382.2	1382.2	1382.3	1382.5	1382.6	1383.3	1384.6	1386.0	1387.2	1388.6	1389.2
140°	1424.1	1424.7	1425.3	1425.8	1426.5	1427.1	1427.6	1428.3	1428.9	1429.4	1430.4
142.5°	1461.7	1462.8	1463.9	1465.0	1466.1	1466.8	1467.1	1467.5	1467.8	1468.2	1468.8
145°	1519.6	1520.5	1521.3	1522.2	1523.1	1523.6	1523.6	1523.6	1523.6	1523.6	1523.8
147.5°	1565.6	1567.2	1568.9	1570.6	1572.3	1572.9	1572.6	1572.4	1572.0	1571.7	1572.0
150°	1598.9	1600.1	1601.2	1602.5	1603.7	1604.1	1603.8	1603.6	1603.2	1602.9	1602.9
152.5°	1626.8	1627.8	1628.8	1629.7	1630.7	1630.9	1630.3	1629.8	1629.2	1628.7	1629.2
155°	1666.2	1666.4	1666.7	1667.1	1667.3	1667.1	1666.2	1665.3	1664.4	1663.4	1664.6
157.5°	1699.2	1699.1	1698.9	1698.7	1698.5	1697.9	1696.8	1695.9	1694.9	1693.8	1695.4
160°	1718.6	1717.7	1716.8	1715.9	1715.0	1714.4	1714.0	1713.8	1713.5	1713.2	1715.0
162.5°	1735.8	1734.6	1733.5	1732.4	1731.3	1730.5	1730.2	1729.9	1729.7	1729.3	1731.1
165°	1757.6	1756.0	1754.6	1753.1	1751.6	1750.9	1750.9	1750.9	1750.9	1750.9	1753.2
167.5°	1774.8	1773.3	1771.7	1770.1	1768.5	1767.7	1767.5	1767.4	1767.2	1767.0	1769.6
170°	1784.5	1782.7	1780.8	1779.1	1777.3	1776.6	1776.8	1777.2	1777.4	1777.7	1780.1
172.5°	1790.9	1789.1	1787.3	1785.6	1783.8	1783.0	1783.3	1783.6	1783.9	1784.2	1786.5
175°	1797.9	1796.1	1794.3	1792.5	1790.7	1790.0	1790.3	1790.6	1790.9	1791.2	1793.9
177.5°	1801.2	1799.5	1797.8	1796.1	1794.5	1793.9	1794.3	1794.8	1795.3	1795.7	1797.7
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9



TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8	1238.8
2.5°	1234.1	1235.9	1237.8	1238.7	1238.5	1238.3	1238.1	1238.0
5°	1225.8	1228.0	1230.1	1230.9	1230.5	1230.1	1229.7	1229.2
7.5°	1209.5	1210.9	1212.3	1212.5	1211.9	1211.2	1210.6	1209.9
10°	1194.9	1195.7	1196.6	1196.6	1195.7	1194.9	1194.0	1193.2
12.5°	1176.8	1177.2	1177.8	1177.4	1176.3	1175.1	1173.8	1172.7
15°	1145.0	1144.5	1144.1	1143.2	1141.7	1140.1	1138.7	1137.2
17.5°	1106.6	1105.5	1104.2	1102.5	1100.3	1098.1	1095.8	1093.6
20°	1079.8	1078.1	1076.4	1074.2	1071.5	1068.7	1066.0	1063.3
22.5°	1050.1	1047.5	1045.0	1042.6	1040.4	1038.1	1035.9	1033.7
25°	1002.0	998.4	994.9	992.0	989.9	987.8	985.7	983.6
27.5°	953.1	948.7	944.2	940.5	937.5	934.4	931.4	928.4
30°	918.0	912.8	907.5	903.1	899.8	896.4	893.0	889.7
32.5°	882.2	876.1	870.0	865.3	862.1	858.9	855.7	852.5
35°	828.8	821.7	814.6	809.0	805.3	801.5	797.6	793.9
37.5°	771.6	763.6	755.5	749.7	745.9	742.1	738.3	734.5
40°	733.5	724.6	715.8	709.4	705.7	701.9	698.1	694.3
42.5°	696.0	687.0	678.0	671.5	667.4	663.5	659.6	655.6
45°	638.6	628.2	617.9	610.8	607.0	603.2	599.4	595.7
47.5°	580.7	570.0	559.3	551.8	547.7	543.5	539.3	535.1
50°	542.3	531.8	521.2	514.0	510.0	506.0	501.9	497.9
52.5°	504.1	493.4	482.6	475.2	471.0	466.8	462.7	458.5
55°	447.5	436.6	425.7	418.2	414.2	410.2	406.2	402.2
57.5°	392.4	381.3	370.1	363.1	360.1	357.0	354.0	351.0
60°	355.6	344.6	333.7	326.5	323.2	319.8	316.4	313.0
62.5°	319.3	309.2	299.1	292.7	290.0	287.3	284.5	281.9
65°	267.3	258.3	249.2	243.4	240.9	238.4	235.9	233.4
67.5°	219.6	211.9	204.0	198.8	196.0	193.1	190.4	187.6
70°	187.2	180.2	173.3	168.7	166.7	164.5	162.4	160.3
72.5°	158.1	152.1	146.2	142.2	140.4	138.4	136.4	134.5
75°	116.5	111.6	106.7	103.7	102.5	101.2	99.9	98.6
77.5°	82.4	79.5	76.7	75.1	74.7	74.4	74.0	73.6
80°	63.2	62.6	62.0	61.5	61.3	61.1	60.9	60.7
82.5°	49.1	48.7	48.2	47.9	47.7	47.4	47.3	47.1
85°	28.5	28.2	27.7	27.5	27.5	27.5	27.5	27.5
87.5°	16.9	17.1	17.3	17.6	17.8	18.1	18.4	18.7
90°	33.2	35.0	36.7	38.0	38.5	39.1	39.8	40.3
92.5°	32.1	33.9	35.7	36.6	36.7	36.9	37.0	37.1
95°	33.2	35.0	36.7	37.8	38.1	38.4	38.7	39.0
97.5°	35.8	36.0	36.2	36.5	36.7	37.1	37.4	37.6
100°	49.0	44.0	38.9	36.5	36.7	37.1	37.4	37.6
102.5°	175.5	120.6	65.9	38.5	38.5	38.6	38.7	38.7
105°	424.9	427.7	430.3	426.2	415.5	404.7	394.0	383.3
107.5°	525.8	527.1	528.3	529.6	530.7	531.8	533.0	534.1
110°	594.2	594.9	595.4	596.2	597.1	598.0	598.9	599.8





TEST NUMBER: P333073-940

CATALOG NUMBER: S124RDIW-S795D1560U940-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	660.6	660.4	660.3	660.8	662.0	663.1	664.2	665.4
115°	759.6	760.2	760.8	761.2	761.2	761.2	761.2	761.2
117.5°	859.3	859.2	859.1	859.0	858.8	858.7	858.6	858.4
120°	921.0	921.6	922.2	922.2	921.6	921.0	920.4	919.8
122.5°	981.9	982.2	982.6	982.4	981.9	981.2	980.6	980.1
125°	1066.8	1067.7	1068.6	1069.3	1069.5	1069.8	1070.1	1070.4
127.5°	1151.3	1151.1	1150.9	1150.7	1150.5	1150.2	1150.0	1149.8
130°	1202.8	1203.1	1203.4	1203.5	1203.5	1203.5	1203.5	1203.5
132.5°	1253.4	1253.7	1253.9	1254.0	1253.7	1253.5	1253.3	1253.0
135°	1323.0	1323.7	1324.3	1324.9	1325.4	1326.1	1326.7	1327.2
137.5°	1389.9	1390.5	1391.2	1391.4	1391.2	1391.1	1390.9	1390.7
140°	1431.3	1432.2	1433.1	1433.6	1434.0	1434.2	1434.5	1434.9
142.5°	1469.5	1470.2	1470.8	1471.1	1471.2	1471.3	1471.3	1471.4
145°	1524.2	1524.5	1524.7	1525.3	1525.8	1526.4	1527.1	1527.6
147.5°	1572.2	1572.4	1572.7	1573.0	1573.2	1573.5	1573.9	1574.1
150°	1602.9	1602.9	1602.9	1603.1	1603.4	1603.7	1604.0	1604.3
152.5°	1629.7	1630.1	1630.7	1630.8	1630.6	1630.4	1630.2	1630.0
155°	1665.8	1667.1	1668.2	1668.4	1667.5	1666.6	1665.7	1664.8
157.5°	1696.9	1698.5	1700.0	1700.0	1698.5	1696.9	1695.4	1693.8
160°	1716.8	1718.6	1720.4	1720.4	1718.6	1716.8	1715.0	1713.2
162.5°	1733.0	1734.7	1736.5	1736.3	1734.4	1732.3	1730.3	1728.2
165°	1755.6	1758.0	1760.4	1760.2	1757.6	1754.9	1752.2	1749.5
167.5°	1772.3	1774.9	1777.5	1777.4	1774.3	1771.4	1768.4	1765.4
170°	1782.5	1784.9	1787.3	1787.0	1784.0	1781.0	1778.1	1775.0
172.5°	1789.0	1791.4	1793.8	1793.3	1790.1	1786.9	1783.7	1780.4
175°	1796.5	1799.3	1802.0	1801.5	1797.9	1794.3	1790.7	1787.2
177.5°	1799.6	1801.5	1803.4	1803.0	1800.1	1797.2	1794.3	1791.4
180°	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9	1797.9

(END OF REPORT)