

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333466-930

Luminaire Tested: **S125DIW-S1270D770U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333466-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6729.5 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58	54
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	39
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9671	9671	9671	9671
5°	11199	9703	8496	9703
10°	13029	9653	7444	9653
15°	14422	9582	6867	9582
20°	16144	9470	6403	9470
25°	18912	9344	6178	9344
30°	20427	9219	5982	9219
35°	16796	8984	5852	8984
40°	11938	8658	5712	8658
45°	9171	8219	5630	8219
50°	7829	7675	5620	7675
55°	6971	7142	5668	7142
60°	6288	6559	5813	6559
65°	5809	5974	5963	5974
70°	5280	5365	6048	5365
75°	4664	4726	5996	4726
80°	3924	3853	5482	3853
85°	3105	2779	4431	2779



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.2	2.1
10°-20°	429.2	6.4
20°-30°	696.9	10.4
30°-40°	850.1	12.6
40°-50°	773.3	11.5
50°-60°	616.0	9.2
60°-70°	429.0	6.4
70°-80°	228.8	3.4
80°-90°	59.4	0.9
90°-100°	29.6	0.4
100°-110°	182.5	2.7
110°-120°	331.0	4.9
120°-130°	424.8	6.3
130°-140°	456.9	6.8
140°-150°	428.9	6.4
150°-160°	346.9	5.2
160°-170°	224.4	3.3
170°-180°	77.4	1.2
0°-30°	1270.2	18.9
0°-40°	2120.3	31.5
0°-60°	3509.7	52.2
0°-90°	4226.9	62.8
90°-120°	543.2	8.1
90°-150°	1853.8	27.5
90°-180°	2503.0	37.2
0°-180°	6729.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1497	1497	1497	1497	1497	
5°	1727	1497	1310	1497	1727	174
15°	2157	1433	1027	1433	2157	617
25°	2654	1311	867	1311	2654	1212
35°	2130	1140	742	1140	2130	1304
45°	1004	900	616	900	1004	804
55°	619	634	503	634	619	558
65°	380	391	390	391	380	377
75°	187	189	240	189	187	201
85°	42	38	60	38	42	49
90°	14	1	14	1	14	8
95°	13	34	13	34	13	10
105°	179	178	179	178	179	162
115°	331	334	331	334	331	329
125°	474	474	474	474	474	422
135°	589	591	589	591	589	455
145°	684	686	684	686	684	427
155°	750	755	750	755	750	346
165°	793	797	793	797	793	224
175°	811	815	811	815	811	77
180°	815	815	815	815	815	



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1583.8	1581.8	1579.7	1575.6	1578.7	1570.0	1565.9	1558.9	1550.2	1547.2	1543.6
5°	1727.4	1730.6	1733.7	1720.4	1721.7	1712.8	1692.5	1675.9	1662.6	1645.4	1633.4
7.5°	1900.3	1892.8	1892.1	1883.5	1868.7	1856.7	1835.3	1808.1	1781.8	1751.8	1727.0
10°	1986.7	1987.4	1981.7	1971.5	1955.6	1944.2	1916.2	1889.5	1857.1	1818.9	1791.6
12.5°	2051.8	2054.5	2047.2	2033.5	2025.7	2000.1	1978.2	1946.4	1907.9	1877.4	1835.8
15°	2157.0	2150.0	2145.0	2127.8	2114.5	2087.7	2052.8	2019.7	1977.8	1939.0	1900.3
17.5°	2258.5	2264.1	2254.5	2238.9	2197.5	2166.3	2119.5	2074.1	2021.9	1969.9	1923.7
20°	2349.0	2354.1	2339.4	2312.1	2262.5	2231.4	2169.8	2111.3	2050.9	1984.2	1933.3
22.5°	2461.9	2457.8	2438.1	2396.5	2353.5	2296.0	2229.3	2158.0	2082.4	2007.0	1939.4
25°	2654.0	2627.3	2615.2	2563.8	2507.2	2422.7	2331.2	2226.9	2132.9	2033.1	1946.7
27.5°	2760.5	2752.1	2738.7	2702.9	2643.4	2552.9	2445.1	2318.1	2185.4	2059.4	1946.3
30°	2739.2	2740.5	2741.8	2730.3	2692.2	2624.1	2516.7	2380.1	2222.5	2080.8	1949.9
32.5°	2550.1	2573.2	2595.3	2621.5	2632.2	2619.1	2551.8	2428.5	2266.2	2105.2	1947.8
35°	2130.4	2137.3	2209.1	2280.3	2376.9	2451.9	2502.2	2447.4	2310.8	2125.9	1945.4
37.5°	1661.1	1695.4	1745.1	1825.5	1965.0	2089.8	2250.3	2324.2	2280.1	2132.7	1941.0
40°	1416.0	1447.8	1480.2	1562.2	1679.8	1831.0	2013.4	2169.1	2205.3	2111.3	1925.7
42.5°	1226.9	1252.1	1288.0	1349.6	1447.9	1581.8	1756.2	1959.7	2084.8	2049.3	1893.7
45°	1004.1	1020.0	1048.0	1097.0	1168.2	1273.0	1426.8	1649.3	1843.1	1907.2	1817.6
47.5°	859.5	859.4	881.1	914.9	966.3	1055.4	1169.1	1343.5	1550.5	1703.6	1696.6
50°	779.2	776.0	793.1	822.4	863.1	922.2	1030.9	1170.0	1369.0	1542.5	1590.7
52.5°	710.0	710.4	721.0	742.6	776.7	827.1	908.3	1033.8	1203.7	1381.8	1472.8
55°	619.1	616.4	628.5	643.2	668.0	701.0	759.5	855.4	993.4	1168.7	1286.9
57.5°	535.7	542.7	547.5	557.7	578.2	600.3	649.6	720.1	829.5	980.0	1105.0
60°	486.8	493.8	497.7	507.8	524.3	543.4	581.6	638.7	730.9	860.5	984.5
62.5°	443.1	448.6	449.8	459.0	472.5	491.1	521.1	569.1	641.9	755.3	876.7
65°	380.1	380.1	382.6	392.2	398.5	415.0	437.9	472.9	531.3	619.6	723.3
67.5°	319.3	322.4	321.7	325.9	331.7	344.6	361.0	389.9	433.2	497.7	580.5
70°	279.6	282.2	281.5	284.7	291.1	299.4	312.7	340.0	371.1	426.5	497.7
72.5°	244.0	245.1	243.4	247.6	251.4	258.7	273.5	288.1	317.2	363.9	422.4
75°	186.9	188.1	189.4	191.9	195.8	199.6	207.2	221.8	240.8	275.8	313.3
77.5°	140.1	137.6	140.7	140.3	142.5	145.4	152.1	159.9	175.5	197.6	226.7
80°	105.5	106.2	106.2	106.8	110.0	111.9	117.6	123.3	135.3	151.9	172.3
82.5°	77.0	78.7	77.7	78.8	81.4	82.8	86.0	90.7	97.8	110.7	125.5
85°	41.9	38.8	40.0	41.3	41.3	41.9	44.5	46.4	50.2	55.3	61.0
87.5°	15.1	16.1	16.5	16.4	16.8	16.7	18.6	18.5	19.9	21.3	23.1
90°	14.5	14.1	13.7	13.3	12.9	12.3	11.7	11.0	10.4	9.7	8.7
92.5°	13.5	13.4	13.1	13.0	12.8	12.3	11.7	11.0	10.4	9.7	8.8
95°	12.7	12.7	12.7	12.7	12.7	12.3	11.7	11.0	10.4	9.7	14.8
97.5°	12.7	12.7	12.7	12.7	12.7	14.6	18.3	22.2	25.9	29.8	39.8
100°	12.7	13.2	13.8	14.3	14.8	25.1	45.1	65.1	85.1	105.1	104.6
102.5°	76.0	85.1	94.2	103.4	112.5	119.0	122.8	126.5	130.4	134.1	133.8
105°	179.4	179.5	179.7	179.9	179.9	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.2	226.6	227.0	227.4	227.8	228.0	228.0	228.0	227.9	227.9	227.6
110°	258.5	258.4	258.3	258.1	258.0	258.1	258.5	258.9	259.3	259.8	259.5



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	287.6	287.7	288.0	288.1	288.3	288.6	289.2	289.7	290.2	290.7	290.6
115°	331.0	331.8	332.6	333.5	334.3	334.9	335.5	336.0	336.6	337.1	337.0
117.5°	377.5	377.8	378.1	378.5	378.9	379.4	380.1	380.7	381.5	382.1	381.6
120°	405.9	406.7	407.3	408.0	408.6	409.1	409.4	409.7	409.9	410.2	409.8
122.5°	433.0	433.8	434.6	435.4	436.1	436.7	436.9	437.2	437.5	437.7	437.6
125°	474.3	474.7	475.0	475.4	475.8	476.3	476.9	477.4	477.9	478.4	478.4
127.5°	508.9	509.9	510.9	511.8	512.9	513.6	513.8	514.1	514.4	514.7	514.8
130°	534.0	534.7	535.4	536.1	536.7	537.3	537.7	538.1	538.4	538.8	538.7
132.5°	557.3	557.9	558.6	559.2	559.9	560.3	560.4	560.4	560.5	560.6	560.9
135°	589.0	589.8	590.6	591.4	592.2	592.8	593.0	593.3	593.5	593.9	594.1
137.5°	620.9	621.6	622.3	623.0	623.7	624.0	623.9	623.9	623.9	623.8	624.0
140°	639.8	640.6	641.4	642.1	642.9	643.3	642.9	642.7	642.5	642.1	642.3
142.5°	657.6	658.4	659.3	660.1	660.9	661.2	661.2	661.1	661.0	661.0	660.8
145°	683.9	684.7	685.4	686.2	687.1	687.4	687.3	687.1	687.0	686.9	686.9
147.5°	705.5	706.5	707.4	708.4	709.3	709.7	709.6	709.4	709.2	709.1	708.9
150°	719.5	720.6	721.6	722.7	723.8	724.2	723.9	723.7	723.4	723.1	722.8
152.5°	732.5	733.5	734.5	735.4	736.4	736.8	736.5	736.2	736.0	735.6	735.4
155°	749.7	750.8	751.9	752.9	754.0	754.3	753.9	753.5	753.1	752.7	752.4
157.5°	764.1	765.2	766.2	767.3	768.3	768.7	768.3	767.8	767.4	767.0	767.0
160°	773.2	774.4	775.4	776.5	777.6	777.8	777.3	776.7	776.2	775.7	775.5
162.5°	781.5	782.7	783.8	785.1	786.2	786.4	785.6	784.9	784.2	783.4	783.3
165°	792.6	793.7	794.8	795.8	796.9	797.0	796.2	795.4	794.6	793.8	793.7
167.5°	800.3	801.5	802.7	804.0	805.2	805.3	804.3	803.3	802.3	801.4	801.3
170°	804.7	805.8	807.1	808.3	809.5	809.6	808.5	807.4	806.3	805.3	805.1
172.5°	807.6	808.8	810.0	811.2	812.4	812.5	811.5	810.6	809.6	808.7	808.5
175°	811.3	812.5	813.8	815.0	816.1	816.2	815.1	814.1	813.0	812.0	811.8
177.5°	813.5	814.3	815.2	816.0	816.9	817.0	816.2	815.5	814.7	814.0	813.8
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1540.6	1537.0	1532.9	1525.8	1517.2	1512.6	1505.5	1500.9	1491.8	1484.1	1476.0
5°	1618.7	1602.2	1587.0	1567.2	1545.6	1531.6	1515.2	1496.7	1477.6	1457.9	1436.3
7.5°	1699.7	1670.5	1638.7	1604.5	1571.1	1540.3	1510.9	1482.1	1455.1	1422.6	1395.1
10°	1754.1	1717.3	1677.8	1631.4	1586.3	1546.9	1506.8	1471.9	1436.3	1398.2	1364.5
12.5°	1808.5	1759.4	1703.7	1652.8	1598.6	1550.9	1503.8	1459.2	1414.5	1372.2	1333.0
15°	1846.9	1803.7	1752.2	1679.8	1618.7	1553.3	1491.0	1433.1	1379.2	1332.1	1282.5
17.5°	1872.2	1816.5	1761.2	1691.7	1611.8	1538.6	1467.9	1401.7	1340.8	1281.2	1233.5
20°	1876.7	1819.6	1761.7	1693.7	1611.8	1527.9	1457.3	1377.9	1312.4	1250.8	1192.3
22.5°	1875.3	1810.4	1747.5	1677.5	1597.5	1520.2	1434.9	1354.0	1282.9	1222.3	1161.2
25°	1860.8	1791.6	1712.8	1642.3	1563.4	1481.5	1395.1	1311.2	1238.7	1169.4	1109.1
27.5°	1848.9	1759.1	1669.8	1587.6	1511.5	1436.3	1353.6	1267.6	1187.3	1117.1	1060.2
30°	1834.2	1735.7	1635.2	1549.5	1471.3	1398.2	1320.1	1236.2	1152.3	1083.6	1022.6
32.5°	1821.0	1706.2	1600.2	1506.8	1424.0	1352.9	1280.8	1201.0	1118.7	1049.0	988.0
35°	1795.5	1662.6	1541.2	1435.7	1347.4	1274.2	1213.9	1139.5	1063.9	996.5	938.1
37.5°	1763.0	1605.4	1475.1	1364.5	1267.6	1190.7	1134.4	1077.3	1004.8	939.9	887.0
40°	1737.6	1564.7	1426.8	1313.7	1213.2	1133.2	1081.1	1027.0	966.7	906.3	850.4
42.5°	1705.5	1528.1	1378.0	1256.2	1156.8	1078.8	1024.1	978.2	925.0	868.7	816.8
45°	1646.7	1461.8	1299.0	1168.2	1067.7	990.8	934.3	899.9	859.9	806.5	762.6
47.5°	1560.2	1382.0	1213.7	1078.6	975.0	903.8	850.8	817.8	789.6	749.9	710.1
50°	1483.4	1322.6	1152.3	1018.1	914.5	842.7	793.8	763.9	739.8	709.2	675.6
52.5°	1397.4	1247.8	1091.8	959.2	856.6	785.8	737.8	711.6	691.5	669.6	636.4
55°	1260.9	1133.8	988.9	863.1	768.3	699.1	657.1	634.3	617.8	601.2	580.9
57.5°	1110.5	1011.1	882.8	767.8	680.5	617.5	578.4	556.1	543.2	534.8	522.8
60°	1004.8	919.7	809.0	704.2	619.1	563.1	525.0	507.8	497.0	490.0	481.1
62.5°	906.7	836.7	734.3	638.6	564.1	511.2	477.2	460.5	450.2	446.8	439.4
65°	762.0	708.0	623.5	544.0	480.5	435.4	406.8	390.9	384.5	380.7	381.3
67.5°	619.5	586.6	518.7	450.9	400.2	362.4	339.5	327.3	324.2	319.0	318.9
70°	532.6	507.8	450.6	391.5	346.3	317.2	296.8	284.1	280.9	278.3	277.8
72.5°	455.8	434.1	384.5	337.1	296.5	270.8	254.1	246.5	241.2	239.7	239.6
75°	342.6	330.5	291.1	253.6	225.6	207.8	196.4	189.4	185.6	184.9	185.6
77.5°	243.5	233.0	208.0	181.4	163.7	150.3	140.6	138.2	133.9	134.0	133.3
80°	183.0	176.0	160.1	139.2	124.6	113.2	108.0	103.6	102.3	100.4	102.3
82.5°	132.7	125.2	114.4	101.0	88.9	82.1	77.0	75.7	74.8	73.9	74.4
85°	65.5	66.1	59.8	49.6	44.5	40.7	37.5	37.5	36.9	36.2	36.9
87.5°	23.9	22.7	20.5	18.8	16.0	14.3	13.5	13.9	12.6	12.2	13.0
90°	7.8	6.8	5.9	4.9	3.8	2.8	1.7	0.6	1.7	2.8	3.8
92.5°	8.0	7.2	6.4	6.3	7.0	7.8	8.6	9.3	8.6	7.8	7.0
95°	19.9	24.9	30.1	32.9	33.3	33.6	34.0	34.4	34.0	33.6	33.3
97.5°	49.9	60.0	70.1	74.8	74.0	73.4	72.6	71.9	72.6	73.4	74.0
100°	104.0	103.5	103.0	102.5	102.1	101.7	101.3	100.9	101.3	101.7	102.1
102.5°	133.5	133.1	132.8	132.4	131.9	131.4	130.9	130.4	130.9	131.4	131.9
105°	180.0	180.0	180.0	179.8	179.2	178.7	178.1	177.6	178.1	178.7	179.2
107.5°	227.3	227.1	226.8	226.7	226.7	226.7	226.7	226.7	226.7	226.7	226.7
110°	259.3	258.9	258.7	258.5	258.5	258.5	258.5	258.5	258.5	258.5	258.5



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	290.4	290.2	290.1	289.8	289.5	289.2	288.9	288.5	288.9	289.2	289.5
115°	336.8	336.7	336.6	336.1	335.5	334.8	334.1	333.5	334.1	334.8	335.5
117.5°	381.2	380.7	380.1	379.8	379.9	379.9	379.9	380.0	379.9	379.9	379.9
120°	409.4	409.0	408.5	408.5	408.5	408.7	408.9	409.0	408.9	408.7	408.5
122.5°	437.3	437.2	437.0	436.7	436.1	435.6	435.1	434.6	435.1	435.6	436.1
125°	478.4	478.4	478.4	478.0	477.0	476.1	475.2	474.3	475.2	476.1	477.0
127.5°	514.9	514.9	515.0	514.7	514.0	513.4	512.7	512.0	512.7	513.4	514.0
130°	538.6	538.4	538.3	537.9	537.3	536.5	535.9	535.2	535.9	536.5	537.3
132.5°	561.2	561.5	561.8	561.6	560.8	560.0	559.2	558.4	559.2	560.0	560.8
135°	594.4	594.7	594.9	594.7	593.9	593.0	592.2	591.4	592.2	593.0	593.9
137.5°	624.3	624.5	624.8	624.5	623.9	623.1	622.5	621.7	622.5	623.1	623.9
140°	642.5	642.5	642.7	642.6	642.4	642.1	641.8	641.6	641.8	642.1	642.4
142.5°	660.6	660.5	660.2	660.1	659.9	659.7	659.6	659.4	659.6	659.7	659.9
145°	686.9	686.9	686.9	686.7	686.5	686.2	685.9	685.7	685.9	686.2	686.5
147.5°	708.7	708.7	708.5	708.4	708.5	708.5	708.6	708.7	708.6	708.5	708.5
150°	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	722.8	722.6	722.3
152.5°	735.2	734.9	734.6	734.7	735.4	736.0	736.5	737.1	736.5	736.0	735.4
155°	752.2	752.0	751.6	752.0	752.7	753.5	754.3	755.1	754.3	753.5	752.7
157.5°	767.0	766.9	766.9	767.1	767.6	768.1	768.6	769.0	768.6	768.1	767.6
160°	775.4	775.3	775.1	775.5	776.2	777.1	777.9	778.7	777.9	777.1	776.2
162.5°	783.2	783.0	782.9	783.2	784.0	784.8	785.6	786.4	785.6	784.8	784.0
165°	793.5	793.4	793.3	793.6	794.4	795.2	796.0	796.8	796.0	795.2	794.4
167.5°	801.1	801.0	800.9	801.2	802.1	802.9	803.7	804.5	803.7	802.9	802.1
170°	805.0	804.9	804.7	805.1	806.1	807.0	808.0	808.9	808.0	807.0	806.1
172.5°	808.2	808.0	807.7	808.0	808.9	809.9	810.9	811.8	810.9	809.9	808.9
175°	811.6	811.5	811.4	811.7	812.5	813.3	814.2	815.0	814.2	813.3	812.5
177.5°	813.8	813.7	813.5	813.8	814.5	815.1	815.7	816.4	815.7	815.1	814.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1471.4	1465.8	1461.3	1451.1	1445.4	1437.9	1431.7	1438.4	1431.3	1434.3	1429.7
5°	1425.6	1407.7	1395.1	1376.6	1360.7	1346.1	1335.3	1333.3	1328.3	1325.8	1318.1
7.5°	1370.4	1348.1	1326.2	1302.1	1281.7	1261.0	1247.8	1236.9	1229.6	1220.1	1213.7
10°	1337.8	1308.0	1282.5	1253.3	1227.8	1205.7	1187.8	1178.9	1170.7	1158.6	1154.1
12.5°	1297.6	1266.7	1235.7	1204.5	1180.1	1155.3	1140.0	1126.6	1120.9	1107.3	1105.9
15°	1249.4	1203.1	1172.6	1140.8	1107.1	1086.8	1074.1	1059.5	1053.1	1043.6	1036.6
17.5°	1192.0	1150.6	1112.5	1079.5	1050.7	1033.6	1017.7	1007.7	996.8	990.6	979.1
20°	1150.3	1110.9	1072.8	1037.9	1015.6	995.9	983.2	973.6	962.2	959.0	947.6
22.5°	1115.2	1071.8	1035.2	1005.8	981.5	959.3	945.6	939.1	931.2	921.5	919.1
25°	1058.2	1013.1	981.9	952.7	931.1	910.8	901.2	892.9	885.3	878.3	875.8
27.5°	1008.9	968.6	931.6	905.1	886.3	867.8	859.4	849.4	843.8	838.1	831.3
30°	974.3	932.9	900.6	875.1	854.8	838.3	829.4	822.4	817.3	812.2	808.5
32.5°	938.7	900.4	869.0	844.2	823.8	811.3	803.5	798.5	792.9	786.8	782.0
35°	891.7	849.7	819.2	797.6	781.7	772.2	763.3	758.8	752.5	752.5	747.4
37.5°	838.7	802.4	775.5	755.8	741.5	733.0	723.4	720.3	716.2	713.5	711.8
40°	807.1	773.5	748.0	728.3	713.1	706.0	698.5	693.4	690.8	687.6	686.4
42.5°	774.6	742.4	718.0	699.9	686.6	680.7	673.5	670.0	664.9	660.7	660.0
45°	725.1	694.0	671.8	657.1	645.7	638.7	634.3	626.6	624.1	619.1	618.4
47.5°	678.2	648.4	626.6	614.6	604.5	598.8	591.8	584.2	581.3	578.7	578.5
50°	643.2	615.9	595.5	584.1	574.5	566.3	559.3	554.2	552.3	552.3	553.6
52.5°	607.6	584.3	567.0	553.0	544.0	535.2	528.8	525.7	522.8	525.9	528.2
55°	555.5	532.0	519.3	505.9	497.0	486.8	483.6	482.4	480.5	485.6	488.1
57.5°	500.3	483.8	468.9	455.7	447.7	441.8	437.5	436.8	440.3	442.7	450.9
60°	465.2	446.1	432.8	422.7	413.1	409.3	408.1	406.8	409.3	416.3	427.1
62.5°	426.6	411.1	396.7	389.1	382.0	375.8	375.4	376.3	381.3	389.3	400.1
65°	369.9	356.5	347.0	338.1	332.4	328.6	329.9	332.4	338.1	348.9	361.0
67.5°	312.3	303.1	294.6	287.4	281.9	281.9	283.2	287.0	293.8	306.2	317.2
70°	275.2	265.1	258.0	254.9	250.4	247.9	251.7	258.0	263.7	275.2	284.7
72.5°	238.1	229.4	224.0	221.8	219.9	217.8	219.2	226.0	233.7	245.2	256.2
75°	183.0	179.9	176.0	173.5	171.6	172.8	174.1	180.5	186.9	198.9	211.7
77.5°	133.6	130.3	128.0	127.3	126.4	126.9	130.5	135.3	141.5	150.3	159.9
80°	101.0	99.8	98.5	97.8	97.8	98.5	103.6	106.8	112.5	120.7	128.4
82.5°	73.6	72.8	72.6	72.5	73.0	73.1	76.1	80.3	85.0	91.2	97.8
85°	38.8	37.5	39.4	40.0	38.8	40.7	41.9	44.5	46.4	49.6	52.7
87.5°	13.7	14.9	14.6	15.2	15.5	16.7	16.3	18.5	19.6	20.8	20.4
90°	4.9	5.9	6.8	7.8	8.7	9.7	10.4	11.0	11.7	12.3	12.9
92.5°	6.3	6.4	7.2	8.0	8.8	9.7	10.4	11.0	11.7	12.3	12.8
95°	32.9	30.1	24.9	19.9	14.8	9.7	10.4	11.0	11.7	12.3	12.7
97.5°	74.8	70.1	60.0	49.9	39.8	29.8	25.9	22.2	18.3	14.6	12.7
100°	102.5	103.0	103.5	104.0	104.6	105.1	85.1	65.1	45.1	25.1	14.8
102.5°	132.4	132.8	133.1	133.5	133.8	134.1	130.4	126.5	122.8	119.0	112.5
105°	179.8	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0	180.0	179.9
107.5°	226.7	226.8	227.1	227.3	227.6	227.9	227.9	228.0	228.0	228.0	227.8
110°	258.5	258.7	258.9	259.3	259.5	259.8	259.3	258.9	258.5	258.1	258.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.8	290.1	290.2	290.4	290.6	290.7	290.2	289.7	289.2	288.6	288.3
115°	336.1	336.6	336.7	336.8	337.0	337.1	336.6	336.0	335.5	334.9	334.3
117.5°	379.8	380.1	380.7	381.2	381.6	382.1	381.5	380.7	380.1	379.4	378.9
120°	408.5	408.5	409.0	409.4	409.8	410.2	409.9	409.7	409.4	409.1	408.6
122.5°	436.7	437.0	437.2	437.3	437.6	437.7	437.5	437.2	436.9	436.7	436.1
125°	478.0	478.4	478.4	478.4	478.4	478.4	477.9	477.4	476.9	476.3	475.8
127.5°	514.7	515.0	514.9	514.9	514.8	514.7	514.4	514.1	513.8	513.6	512.9
130°	537.9	538.3	538.4	538.6	538.7	538.8	538.4	538.1	537.7	537.3	536.7
132.5°	561.6	561.8	561.5	561.2	560.9	560.6	560.5	560.4	560.4	560.3	559.9
135°	594.7	594.9	594.7	594.4	594.1	593.9	593.5	593.3	593.0	592.8	592.2
137.5°	624.5	624.8	624.5	624.3	624.0	623.8	623.9	623.9	623.9	624.0	623.7
140°	642.6	642.7	642.5	642.5	642.3	642.1	642.5	642.7	642.9	643.3	642.9
142.5°	660.1	660.2	660.5	660.6	660.8	661.0	661.0	661.1	661.2	661.2	660.9
145°	686.7	686.9	686.9	686.9	686.9	686.9	687.0	687.1	687.3	687.4	687.1
147.5°	708.4	708.5	708.7	708.7	708.9	709.1	709.2	709.4	709.6	709.7	709.3
150°	722.0	722.0	722.3	722.6	722.8	723.1	723.4	723.7	723.9	724.2	723.8
152.5°	734.7	734.6	734.9	735.2	735.4	735.6	736.0	736.2	736.5	736.8	736.4
155°	752.0	751.6	752.0	752.2	752.4	752.7	753.1	753.5	753.9	754.3	754.0
157.5°	767.1	766.9	766.9	767.0	767.0	767.0	767.4	767.8	768.3	768.7	768.3
160°	775.5	775.1	775.3	775.4	775.5	775.7	776.2	776.7	777.3	777.8	777.6
162.5°	783.2	782.9	783.0	783.2	783.3	783.4	784.2	784.9	785.6	786.4	786.2
165°	793.6	793.3	793.4	793.5	793.7	793.8	794.6	795.4	796.2	797.0	796.9
167.5°	801.2	800.9	801.0	801.1	801.3	801.4	802.3	803.3	804.3	805.3	805.2
170°	805.1	804.7	804.9	805.0	805.1	805.3	806.3	807.4	808.5	809.6	809.5
172.5°	808.0	807.7	808.0	808.2	808.5	808.7	809.6	810.6	811.5	812.5	812.4
175°	811.7	811.4	811.5	811.6	811.8	812.0	813.0	814.1	815.1	816.2	816.1
177.5°	813.8	813.5	813.7	813.8	813.8	814.0	814.7	815.5	816.2	817.0	816.9
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1426.7	1430.2	1427.2	1431.3	1427.2	1430.2	1426.7	1429.7	1434.3	1431.3	1438.4
5°	1314.9	1309.2	1313.0	1310.5	1313.0	1309.2	1314.9	1318.1	1325.8	1328.3	1333.3
7.5°	1211.7	1206.2	1200.0	1197.1	1200.0	1206.2	1211.7	1213.7	1220.1	1229.6	1236.9
10°	1147.1	1140.2	1139.5	1135.1	1139.5	1140.2	1147.1	1154.1	1158.6	1170.7	1178.9
12.5°	1099.8	1093.4	1086.1	1084.3	1086.1	1093.4	1099.8	1105.9	1107.3	1120.9	1126.6
15°	1032.7	1027.7	1023.2	1027.0	1023.2	1027.7	1032.7	1036.6	1043.6	1053.1	1059.5
17.5°	977.0	972.7	972.0	967.3	972.0	972.7	977.0	979.1	990.6	996.8	1007.7
20°	941.9	938.7	940.0	931.7	940.0	938.7	941.9	947.6	959.0	962.2	973.6
22.5°	914.0	907.7	906.9	905.3	906.9	907.7	914.0	919.1	921.5	931.2	939.1
25°	870.1	866.9	863.7	866.9	863.7	866.9	870.1	875.8	878.3	885.3	892.9
27.5°	831.8	828.0	827.1	827.4	827.1	828.0	831.8	831.3	838.1	843.8	849.4
30°	808.5	802.1	802.7	802.1	802.7	802.1	808.5	808.5	812.2	817.3	822.4
32.5°	783.0	778.7	777.8	776.7	777.8	778.7	783.0	782.0	786.8	792.9	798.5
35°	745.5	745.5	742.3	742.3	742.3	745.5	745.5	747.4	752.5	752.5	758.8
37.5°	710.3	709.6	707.8	708.0	707.8	709.6	710.3	711.8	713.5	716.2	720.3
40°	683.9	683.2	681.3	677.5	681.3	683.2	683.9	686.4	687.6	690.8	693.4
42.5°	658.4	656.2	655.3	654.1	655.3	656.2	658.4	660.0	660.7	664.9	670.0
45°	618.4	618.4	617.1	616.4	617.1	618.4	618.4	618.4	619.1	624.1	626.6
47.5°	579.5	580.7	583.0	582.7	583.0	580.7	579.5	578.5	578.7	581.3	584.2
50°	556.1	556.8	558.6	559.3	558.6	556.8	556.1	553.6	552.3	552.3	554.2
52.5°	530.2	533.9	536.3	535.9	536.3	533.9	530.2	528.2	525.9	522.8	525.7
55°	493.8	498.2	502.7	503.4	502.7	498.2	493.8	488.1	485.6	480.5	482.4
57.5°	457.9	464.1	468.8	470.3	468.8	464.1	457.9	450.9	442.7	440.3	436.8
60°	433.4	441.7	447.4	450.0	447.4	441.7	433.4	427.1	416.3	409.3	406.8
62.5°	410.0	419.3	425.0	425.6	425.0	419.3	410.0	400.1	389.3	381.3	376.3
65°	371.8	381.3	386.4	390.2	386.4	381.3	371.8	361.0	348.9	338.1	332.4
67.5°	330.6	340.1	345.8	348.8	345.8	340.1	330.6	317.2	306.2	293.8	287.0
70°	300.6	310.1	317.8	320.3	317.8	310.1	300.6	284.7	275.2	263.7	258.0
72.5°	271.1	279.6	285.8	288.8	285.8	279.6	271.1	256.2	245.2	233.7	226.0
75°	219.9	231.3	237.1	240.3	237.1	231.3	219.9	211.7	198.9	186.9	180.5
77.5°	169.6	180.0	183.4	185.1	183.4	180.0	169.6	159.9	150.3	141.5	135.3
80°	136.0	142.4	146.8	147.4	146.8	142.4	136.0	128.4	120.7	112.5	106.8
82.5°	104.5	109.8	111.2	112.8	111.2	109.8	104.5	97.8	91.2	85.0	80.3
85°	57.2	59.8	60.4	59.8	60.4	59.8	57.2	52.7	49.6	46.4	44.5
87.5°	21.4	21.0	21.1	22.3	21.1	21.0	21.4	20.4	20.8	19.6	18.5
90°	13.3	13.7	14.1	14.5	14.1	13.7	13.3	12.9	12.3	11.7	11.0
92.5°	13.0	13.1	13.4	13.5	13.4	13.1	13.0	12.8	12.3	11.7	11.0
95°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.3	11.7	11.0
97.5°	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	14.6	18.3	22.2
100°	14.3	13.8	13.2	12.7	13.2	13.8	14.3	14.8	25.1	45.1	65.1
102.5°	103.4	94.2	85.1	76.0	85.1	94.2	103.4	112.5	119.0	122.8	126.5
105°	179.9	179.7	179.5	179.4	179.5	179.7	179.9	179.9	180.0	180.0	180.0
107.5°	227.4	227.0	226.6	226.2	226.6	227.0	227.4	227.8	228.0	228.0	228.0
110°	258.1	258.3	258.4	258.5	258.4	258.3	258.1	258.0	258.1	258.5	258.9



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	288.1	288.0	287.7	287.6	287.7	288.0	288.1	288.3	288.6	289.2	289.7
115°	333.5	332.6	331.8	331.0	331.8	332.6	333.5	334.3	334.9	335.5	336.0
117.5°	378.5	378.1	377.8	377.5	377.8	378.1	378.5	378.9	379.4	380.1	380.7
120°	408.0	407.3	406.7	405.9	406.7	407.3	408.0	408.6	409.1	409.4	409.7
122.5°	435.4	434.6	433.8	433.0	433.8	434.6	435.4	436.1	436.7	436.9	437.2
125°	475.4	475.0	474.7	474.3	474.7	475.0	475.4	475.8	476.3	476.9	477.4
127.5°	511.8	510.9	509.9	508.9	509.9	510.9	511.8	512.9	513.6	513.8	514.1
130°	536.1	535.4	534.7	534.0	534.7	535.4	536.1	536.7	537.3	537.7	538.1
132.5°	559.2	558.6	557.9	557.3	557.9	558.6	559.2	559.9	560.3	560.4	560.4
135°	591.4	590.6	589.8	589.0	589.8	590.6	591.4	592.2	592.8	593.0	593.3
137.5°	623.0	622.3	621.6	620.9	621.6	622.3	623.0	623.7	624.0	623.9	623.9
140°	642.1	641.4	640.6	639.8	640.6	641.4	642.1	642.9	643.3	642.9	642.7
142.5°	660.1	659.3	658.4	657.6	658.4	659.3	660.1	660.9	661.2	661.2	661.1
145°	686.2	685.4	684.7	683.9	684.7	685.4	686.2	687.1	687.4	687.3	687.1
147.5°	708.4	707.4	706.5	705.5	706.5	707.4	708.4	709.3	709.7	709.6	709.4
150°	722.7	721.6	720.6	719.5	720.6	721.6	722.7	723.8	724.2	723.9	723.7
152.5°	735.4	734.5	733.5	732.5	733.5	734.5	735.4	736.4	736.8	736.5	736.2
155°	752.9	751.9	750.8	749.7	750.8	751.9	752.9	754.0	754.3	753.9	753.5
157.5°	767.3	766.2	765.2	764.1	765.2	766.2	767.3	768.3	768.7	768.3	767.8
160°	776.5	775.4	774.4	773.2	774.4	775.4	776.5	777.6	777.8	777.3	776.7
162.5°	785.1	783.8	782.7	781.5	782.7	783.8	785.1	786.2	786.4	785.6	784.9
165°	795.8	794.8	793.7	792.6	793.7	794.8	795.8	796.9	797.0	796.2	795.4
167.5°	804.0	802.7	801.5	800.3	801.5	802.7	804.0	805.2	805.3	804.3	803.3
170°	808.3	807.1	805.8	804.7	805.8	807.1	808.3	809.5	809.6	808.5	807.4
172.5°	811.2	810.0	808.8	807.6	808.8	810.0	811.2	812.4	812.5	811.5	810.6
175°	815.0	813.8	812.5	811.3	812.5	813.8	815.0	816.1	816.2	815.1	814.1
177.5°	816.0	815.2	814.3	813.5	814.3	815.2	816.0	816.9	817.0	816.2	815.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1431.7	1437.9	1445.4	1451.1	1461.3	1465.8	1471.4	1476.0	1484.1	1491.8	1500.9
5°	1335.3	1346.1	1360.7	1376.6	1395.1	1407.7	1425.6	1436.3	1457.9	1477.6	1496.7
7.5°	1247.8	1261.0	1281.7	1302.1	1326.2	1348.1	1370.4	1395.1	1422.6	1455.1	1482.1
10°	1187.8	1205.7	1227.8	1253.3	1282.5	1308.0	1337.8	1364.5	1398.2	1436.3	1471.9
12.5°	1140.0	1155.3	1180.1	1204.5	1235.7	1266.7	1297.6	1333.0	1372.2	1414.5	1459.2
15°	1074.1	1086.8	1107.1	1140.8	1172.6	1203.1	1249.4	1282.5	1332.1	1379.2	1433.1
17.5°	1017.7	1033.6	1050.7	1079.5	1112.5	1150.6	1192.0	1233.5	1281.2	1340.8	1401.7
20°	983.2	995.9	1015.6	1037.9	1072.8	1110.9	1150.3	1192.3	1250.8	1312.4	1377.9
22.5°	945.6	959.3	981.5	1005.8	1035.2	1071.8	1115.2	1161.2	1222.3	1282.9	1354.0
25°	901.2	910.8	931.1	952.7	981.9	1013.1	1058.2	1109.1	1169.4	1238.7	1311.2
27.5°	859.4	867.8	886.3	905.1	931.6	968.6	1008.9	1060.2	1117.1	1187.3	1267.6
30°	829.4	838.3	854.8	875.1	900.6	932.9	974.3	1022.6	1083.6	1152.3	1236.2
32.5°	803.5	811.3	823.8	844.2	869.0	900.4	938.7	988.0	1049.0	1118.7	1201.0
35°	763.3	772.2	781.7	797.6	819.2	849.7	891.7	938.1	996.5	1063.9	1139.5
37.5°	723.4	733.0	741.5	755.8	775.5	802.4	838.7	887.0	939.9	1004.8	1077.3
40°	698.5	706.0	713.1	728.3	748.0	773.5	807.1	850.4	906.3	966.7	1027.0
42.5°	673.5	680.7	686.6	699.9	718.0	742.4	774.6	816.8	868.7	925.0	978.2
45°	634.3	638.7	645.7	657.1	671.8	694.0	725.1	762.6	806.5	859.9	899.9
47.5°	591.8	598.8	604.5	614.6	626.6	648.4	678.2	710.1	749.9	789.6	817.8
50°	559.3	566.3	574.5	584.1	595.5	615.9	643.2	675.6	709.2	739.8	763.9
52.5°	528.8	535.2	544.0	553.0	567.0	584.3	607.6	636.4	669.6	691.5	711.6
55°	483.6	486.8	497.0	505.9	519.3	532.0	555.5	580.9	601.2	617.8	634.3
57.5°	437.5	441.8	447.7	455.7	468.9	483.8	500.3	522.8	534.8	543.2	556.1
60°	408.1	409.3	413.1	422.7	432.8	446.1	465.2	481.1	490.0	497.0	507.8
62.5°	375.4	375.8	382.0	389.1	396.7	411.1	426.6	439.4	446.8	450.2	460.5
65°	329.9	328.6	332.4	338.1	347.0	356.5	369.9	381.3	380.7	384.5	390.9
67.5°	283.2	281.9	281.9	287.4	294.6	303.1	312.3	318.9	319.0	324.2	327.3
70°	251.7	247.9	250.4	254.9	258.0	265.1	275.2	277.8	278.3	280.9	284.1
72.5°	219.2	217.8	219.9	221.8	224.0	229.4	238.1	239.6	239.7	241.2	246.5
75°	174.1	172.8	171.6	173.5	176.0	179.9	183.0	185.6	184.9	185.6	189.4
77.5°	130.5	126.9	126.4	127.3	128.0	130.3	133.6	133.3	134.0	133.9	138.2
80°	103.6	98.5	97.8	97.8	98.5	99.8	101.0	102.3	100.4	102.3	103.6
82.5°	76.1	73.1	73.0	72.5	72.6	72.8	73.6	74.4	73.9	74.8	75.7
85°	41.9	40.7	38.8	40.0	39.4	37.5	38.8	36.9	36.2	36.9	37.5
87.5°	16.3	16.7	15.5	15.2	14.6	14.9	13.7	13.0	12.2	12.6	13.9
90°	10.4	9.7	8.7	7.8	6.8	5.9	4.9	3.8	2.8	1.7	0.6
92.5°	10.4	9.7	8.8	8.0	7.2	6.4	6.3	7.0	7.8	8.6	9.3
95°	10.4	9.7	14.8	19.9	24.9	30.1	32.9	33.3	33.6	34.0	34.4
97.5°	25.9	29.8	39.8	49.9	60.0	70.1	74.8	74.0	73.4	72.6	71.9
100°	85.1	105.1	104.6	104.0	103.5	103.0	102.5	102.1	101.7	101.3	100.9
102.5°	130.4	134.1	133.8	133.5	133.1	132.8	132.4	131.9	131.4	130.9	130.4
105°	180.0	180.0	180.0	180.0	180.0	180.0	179.8	179.2	178.7	178.1	177.6
107.5°	227.9	227.9	227.6	227.3	227.1	226.8	226.7	226.7	226.7	226.7	226.7
110°	259.3	259.8	259.5	259.3	258.9	258.7	258.5	258.5	258.5	258.5	258.5



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	290.2	290.7	290.6	290.4	290.2	290.1	289.8	289.5	289.2	288.9	288.5
115°	336.6	337.1	337.0	336.8	336.7	336.6	336.1	335.5	334.8	334.1	333.5
117.5°	381.5	382.1	381.6	381.2	380.7	380.1	379.8	379.9	379.9	379.9	380.0
120°	409.9	410.2	409.8	409.4	409.0	408.5	408.5	408.5	408.7	408.9	409.0
122.5°	437.5	437.7	437.6	437.3	437.2	437.0	436.7	436.1	435.6	435.1	434.6
125°	477.9	478.4	478.4	478.4	478.4	478.4	478.0	477.0	476.1	475.2	474.3
127.5°	514.4	514.7	514.8	514.9	514.9	515.0	514.7	514.0	513.4	512.7	512.0
130°	538.4	538.8	538.7	538.6	538.4	538.3	537.9	537.3	536.5	535.9	535.2
132.5°	560.5	560.6	560.9	561.2	561.5	561.8	561.6	560.8	560.0	559.2	558.4
135°	593.5	593.9	594.1	594.4	594.7	594.9	594.7	593.9	593.0	592.2	591.4
137.5°	623.9	623.8	624.0	624.3	624.5	624.8	624.5	623.9	623.1	622.5	621.7
140°	642.5	642.1	642.3	642.5	642.5	642.7	642.6	642.4	642.1	641.8	641.6
142.5°	661.0	661.0	660.8	660.6	660.5	660.2	660.1	659.9	659.7	659.6	659.4
145°	687.0	686.9	686.9	686.9	686.9	686.9	686.7	686.5	686.2	685.9	685.7
147.5°	709.2	709.1	708.9	708.7	708.7	708.5	708.4	708.5	708.5	708.6	708.7
150°	723.4	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1
152.5°	736.0	735.6	735.4	735.2	734.9	734.6	734.7	735.4	736.0	736.5	737.1
155°	753.1	752.7	752.4	752.2	752.0	751.6	752.0	752.7	753.5	754.3	755.1
157.5°	767.4	767.0	767.0	767.0	766.9	766.9	767.1	767.6	768.1	768.6	769.0
160°	776.2	775.7	775.5	775.4	775.3	775.1	775.5	776.2	777.1	777.9	778.7
162.5°	784.2	783.4	783.3	783.2	783.0	782.9	783.2	784.0	784.8	785.6	786.4
165°	794.6	793.8	793.7	793.5	793.4	793.3	793.6	794.4	795.2	796.0	796.8
167.5°	802.3	801.4	801.3	801.1	801.0	800.9	801.2	802.1	802.9	803.7	804.5
170°	806.3	805.3	805.1	805.0	804.9	804.7	805.1	806.1	807.0	808.0	808.9
172.5°	809.6	808.7	808.5	808.2	808.0	807.7	808.0	808.9	809.9	810.9	811.8
175°	813.0	812.0	811.8	811.6	811.5	811.4	811.7	812.5	813.3	814.2	815.0
177.5°	814.7	814.0	813.8	813.8	813.7	813.5	813.8	814.5	815.1	815.7	816.4
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1505.5	1512.6	1517.2	1525.8	1532.9	1537.0	1540.6	1543.6	1547.2	1550.2	1558.9
5°	1515.2	1531.6	1545.6	1567.2	1587.0	1602.2	1618.7	1633.4	1645.4	1662.6	1675.9
7.5°	1510.9	1540.3	1571.1	1604.5	1638.7	1670.5	1699.7	1727.0	1751.8	1781.8	1808.1
10°	1506.8	1546.9	1586.3	1631.4	1677.8	1717.3	1754.1	1791.6	1818.9	1857.1	1889.5
12.5°	1503.8	1550.9	1598.6	1652.8	1703.7	1759.4	1808.5	1835.8	1877.4	1907.9	1946.4
15°	1491.0	1553.3	1618.7	1679.8	1752.2	1803.7	1846.9	1900.3	1939.0	1977.8	2019.7
17.5°	1467.9	1538.6	1611.8	1691.7	1761.2	1816.5	1872.2	1923.7	1969.9	2021.9	2074.1
20°	1457.3	1527.9	1611.8	1693.7	1761.7	1819.6	1876.7	1933.3	1984.2	2050.9	2111.3
22.5°	1434.9	1520.2	1597.5	1677.5	1747.5	1810.4	1875.3	1939.4	2007.0	2082.4	2158.0
25°	1395.1	1481.5	1563.4	1642.3	1712.8	1791.6	1860.8	1946.7	2033.1	2132.9	2226.9
27.5°	1353.6	1436.3	1511.5	1587.6	1669.8	1759.1	1848.9	1946.3	2059.4	2185.4	2318.1
30°	1320.1	1398.2	1471.3	1549.5	1635.2	1735.7	1834.2	1949.9	2080.8	2222.5	2380.1
32.5°	1280.8	1352.9	1424.0	1506.8	1600.2	1706.2	1821.0	1947.8	2105.2	2266.2	2428.5
35°	1213.9	1274.2	1347.4	1435.7	1541.2	1662.6	1795.5	1945.4	2125.9	2310.8	2447.4
37.5°	1134.4	1190.7	1267.6	1364.5	1475.1	1605.4	1763.0	1941.0	2132.7	2280.1	2324.2
40°	1081.1	1133.2	1213.2	1313.7	1426.8	1564.7	1737.6	1925.7	2111.3	2205.3	2169.1
42.5°	1024.1	1078.8	1156.8	1256.2	1378.0	1528.1	1705.5	1893.7	2049.3	2084.8	1959.7
45°	934.3	990.8	1067.7	1168.2	1299.0	1461.8	1646.7	1817.6	1907.2	1843.1	1649.3
47.5°	850.8	903.8	975.0	1078.6	1213.7	1382.0	1560.2	1696.6	1703.6	1550.5	1343.5
50°	793.8	842.7	914.5	1018.1	1152.3	1322.6	1483.4	1590.7	1542.5	1369.0	1170.0
52.5°	737.8	785.8	856.6	959.2	1091.8	1247.8	1397.4	1472.8	1381.8	1203.7	1033.8
55°	657.1	699.1	768.3	863.1	988.9	1133.8	1260.9	1286.9	1168.7	993.4	855.4
57.5°	578.4	617.5	680.5	767.8	882.8	1011.1	1110.5	1105.0	980.0	829.5	720.1
60°	525.0	563.1	619.1	704.2	809.0	919.7	1004.8	984.5	860.5	730.9	638.7
62.5°	477.2	511.2	564.1	638.6	734.3	836.7	906.7	876.7	755.3	641.9	569.1
65°	406.8	435.4	480.5	544.0	623.5	708.0	762.0	723.3	619.6	531.3	472.9
67.5°	339.5	362.4	400.2	450.9	518.7	586.6	619.5	580.5	497.7	433.2	389.9
70°	296.8	317.2	346.3	391.5	450.6	507.8	532.6	497.7	426.5	371.1	340.0
72.5°	254.1	270.8	296.5	337.1	384.5	434.1	455.8	422.4	363.9	317.2	288.1
75°	196.4	207.8	225.6	253.6	291.1	330.5	342.6	313.3	275.8	240.8	221.8
77.5°	140.6	150.3	163.7	181.4	208.0	233.0	243.5	226.7	197.6	175.5	159.9
80°	108.0	113.2	124.6	139.2	160.1	176.0	183.0	172.3	151.9	135.3	123.3
82.5°	77.0	82.1	88.9	101.0	114.4	125.2	132.7	125.5	110.7	97.8	90.7
85°	37.5	40.7	44.5	49.6	59.8	66.1	65.5	61.0	55.3	50.2	46.4
87.5°	13.5	14.3	16.0	18.8	20.5	22.7	23.9	23.1	21.3	19.9	18.5
90°	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4	11.0
92.5°	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4	11.0
95°	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4	11.0
97.5°	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9	22.2
100°	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1	65.1
102.5°	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4	126.5
105°	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9	228.0
110°	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3	258.9



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2	289.7
115°	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6	336.0
117.5°	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5	380.7
120°	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9	409.7
122.5°	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5	437.2
125°	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9	477.4
127.5°	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4	514.1
130°	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4	538.1
132.5°	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5	560.4
135°	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5	593.3
137.5°	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9	623.9
140°	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5	642.7
142.5°	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0	661.1
145°	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0	687.1
147.5°	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2	709.4
150°	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4	723.7
152.5°	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0	736.2
155°	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1	753.5
157.5°	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4	767.8
160°	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2	776.7
162.5°	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2	784.9
165°	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6	795.4
167.5°	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3	803.3
170°	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3	807.4
172.5°	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6	810.6
175°	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0	814.1
177.5°	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7	815.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4	1497.4
2.5°	1565.9	1570.0	1578.7	1575.6	1579.7	1581.8	1583.8
5°	1692.5	1712.8	1721.7	1720.4	1733.7	1730.6	1727.4
7.5°	1835.3	1856.7	1868.7	1883.5	1892.1	1892.8	1900.3
10°	1916.2	1944.2	1955.6	1971.5	1981.7	1987.4	1986.7
12.5°	1978.2	2000.1	2025.7	2033.5	2047.2	2054.5	2051.8
15°	2052.8	2087.7	2114.5	2127.8	2145.0	2150.0	2157.0
17.5°	2119.5	2166.3	2197.5	2238.9	2254.5	2264.1	2258.5
20°	2169.8	2231.4	2262.5	2312.1	2339.4	2354.1	2349.0
22.5°	2229.3	2296.0	2353.5	2396.5	2438.1	2457.8	2461.9
25°	2331.2	2422.7	2507.2	2563.8	2615.2	2627.3	2654.0
27.5°	2445.1	2552.9	2643.4	2702.9	2738.7	2752.1	2760.5
30°	2516.7	2624.1	2692.2	2730.3	2741.8	2740.5	2739.2
32.5°	2551.8	2619.1	2632.2	2621.5	2595.3	2573.2	2550.1
35°	2502.2	2451.9	2376.9	2280.3	2209.1	2137.3	2130.4
37.5°	2250.3	2089.8	1965.0	1825.5	1745.1	1695.4	1661.1
40°	2013.4	1831.0	1679.8	1562.2	1480.2	1447.8	1416.0
42.5°	1756.2	1581.8	1447.9	1349.6	1288.0	1252.1	1226.9
45°	1426.8	1273.0	1168.2	1097.0	1048.0	1020.0	1004.1
47.5°	1169.1	1055.4	966.3	914.9	881.1	859.4	859.5
50°	1030.9	922.2	863.1	822.4	793.1	776.0	779.2
52.5°	908.3	827.1	776.7	742.6	721.0	710.4	710.0
55°	759.5	701.0	668.0	643.2	628.5	616.4	619.1
57.5°	649.6	600.3	578.2	557.7	547.5	542.7	535.7
60°	581.6	543.4	524.3	507.8	497.7	493.8	486.8
62.5°	521.1	491.1	472.5	459.0	449.8	448.6	443.1
65°	437.9	415.0	398.5	392.2	382.6	380.1	380.1
67.5°	361.0	344.6	331.7	325.9	321.7	322.4	319.3
70°	312.7	299.4	291.1	284.7	281.5	282.2	279.6
72.5°	273.5	258.7	251.4	247.6	243.4	245.1	244.0
75°	207.2	199.6	195.8	191.9	189.4	188.1	186.9
77.5°	152.1	145.4	142.5	140.3	140.7	137.6	140.1
80°	117.6	111.9	110.0	106.8	106.2	106.2	105.5
82.5°	86.0	82.8	81.4	78.8	77.7	78.7	77.0
85°	44.5	41.9	41.3	41.3	40.0	38.8	41.9
87.5°	18.6	16.7	16.8	16.4	16.5	16.1	15.1
90°	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333466-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)