

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333471-930

Luminaire Tested: **S125DIW-S1270D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333471-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1270D770U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6352.9 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	101	97	93	89	95	91	88	84	81	78	76	71	69	67	62	61	60	55
2	92	84	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50	46
3	84	74	67	61	79	70	63	58	62	57	53	55	51	48	49	45	43	39
4	77	66	58	51	72	62	55	49	55	50	45	49	45	41	43	40	37	34
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	36	31	28	26
7	60	48	40	34	57	45	38	32	41	35	30	36	31	28	32	28	25	23
8	56	43	35	30	53	41	34	29	37	31	27	33	28	25	30	26	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	23	20	18
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	26	21	18	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10377	10377	10377
5°	10400	10301	10367
10°	10337	10228	10287
15°	10224	10105	10148
20°	10065	9933	9950
25°	9892	9728	9719
30°	9679	9508	9461
35°	9451	9270	9140
40°	9217	9012	8884
45°	8963	8777	8603
50°	8685	8493	8238
55°	8417	8173	7944
60°	8094	7848	7569
65°	7713	7459	7207
70°	7345	7009	6770
75°	6692	6470	6248
80°	5954	5861	5720
85°	5187	5276	4987



TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	151.5	2.4
10°-20°	427.9	6.7
20°-30°	631.9	9.9
30°-40°	737.3	11.6
40°-50°	740.5	11.7
50°-60°	650.0	10.2
60°-70°	484.3	7.6
70°-80°	276.9	4.4
80°-90°	82.3	1.3
90°-100°	52.1	0.8
100°-110°	153.8	2.4
110°-120°	260.5	4.1
120°-130°	342.9	5.4
130°-140°	384.2	6.0
140°-150°	376.6	5.9
150°-160°	316.3	5.0
160°-170°	210.2	3.3
170°-180°	73.6	1.2
0°-30°	1211.3	19.1
0°-40°	1948.6	30.7
0°-60°	3339.1	52.6
0°-90°	4182.7	65.8
90°-120°	466.4	7.3
90°-150°	1570.1	24.7
90°-180°	2170.0	34.2
0°-180°	6352.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1607	1607	1607	1607	1607	
5°	1604	1601	1589	1600	1599	152
15°	1529	1525	1511	1517	1518	431
25°	1388	1381	1365	1367	1364	638
35°	1199	1193	1176	1169	1159	749
45°	981	976	961	946	942	756
55°	748	743	726	715	706	667
65°	505	501	488	477	472	501
75°	268	266	259	255	250	286
85°	70	71	71	70	67	78
90°	1	5	10	13	14	6
95°	39	41	47	51	52	42
105°	138	141	145	148	150	147
115°	261	263	264	264	263	258
125°	381	384	385	384	383	341
135°	495	499	499	499	497	381
145°	600	602	604	604	602	375
155°	686	686	687	689	686	316
165°	746	745	746	748	744	210
175°	776	774	774	777	773	74
180°	778	778	778	778	778	



TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1610.8	1610.1	1609.5	1608.7	1608.1	1606.6	1604.3	1602.1	1599.9	1597.6	1599.9
5°	1604.2	1603.6	1603.0	1602.5	1601.9	1600.3	1597.4	1594.6	1591.8	1588.9	1591.5
7.5°	1589.4	1588.9	1588.3	1587.7	1587.1	1585.3	1582.3	1579.2	1576.1	1573.0	1575.4
10°	1576.2	1575.6	1575.1	1574.5	1573.9	1572.1	1569.0	1565.9	1562.8	1559.7	1562.0
12.5°	1559.9	1558.9	1558.0	1556.9	1555.9	1554.0	1551.0	1548.2	1545.3	1542.4	1544.3
15°	1529.2	1528.4	1527.5	1526.6	1525.8	1523.8	1520.7	1517.6	1514.5	1511.4	1512.8
17.5°	1493.9	1492.6	1491.3	1490.1	1488.9	1486.6	1483.4	1480.2	1477.0	1473.7	1475.5
20°	1464.4	1463.8	1463.2	1462.6	1462.1	1460.0	1456.3	1452.6	1448.9	1445.3	1447.2
22.5°	1434.8	1433.9	1432.8	1431.8	1430.8	1428.6	1425.1	1421.7	1418.2	1414.8	1416.1
25°	1388.1	1386.7	1385.3	1383.9	1382.4	1379.9	1376.2	1372.6	1368.9	1365.2	1365.8
27.5°	1333.4	1332.6	1331.7	1330.9	1330.1	1327.7	1324.0	1320.1	1316.4	1312.6	1312.7
30°	1297.9	1297.0	1296.2	1295.3	1294.5	1291.9	1287.7	1283.4	1279.2	1275.0	1274.4
32.5°	1259.2	1257.9	1256.6	1255.3	1254.0	1251.5	1247.7	1243.9	1240.1	1236.3	1235.3
35°	1198.7	1197.6	1196.5	1195.3	1194.2	1191.6	1187.6	1183.7	1179.7	1175.8	1174.4
37.5°	1135.9	1134.5	1133.1	1131.6	1130.2	1127.6	1124.0	1120.2	1116.5	1112.8	1110.7
40°	1093.2	1091.8	1090.4	1088.9	1087.5	1084.8	1080.9	1076.9	1073.0	1069.0	1066.5
42.5°	1047.4	1046.3	1045.1	1043.8	1042.7	1040.1	1036.2	1032.2	1028.3	1024.3	1022.0
45°	981.3	980.2	979.1	978.0	976.8	974.5	971.2	967.8	964.4	961.0	957.6
47.5°	910.1	910.2	910.3	910.3	910.4	908.3	904.3	900.3	896.2	892.1	888.7
50°	864.4	863.6	862.7	861.9	861.0	858.8	855.5	852.1	848.7	845.3	841.6
52.5°	817.6	817.0	816.4	815.7	815.1	813.0	809.3	805.8	802.2	798.5	795.3
55°	747.5	746.6	745.8	744.9	744.0	741.7	737.7	733.8	729.8	725.9	723.3
57.5°	673.4	673.0	672.5	672.1	671.6	669.8	666.4	663.1	659.7	656.4	653.1
60°	626.6	625.6	624.4	623.3	622.2	620.0	616.9	613.8	610.7	607.6	604.8
62.5°	577.9	577.0	576.1	575.1	574.2	572.5	569.8	567.1	564.5	561.8	558.8
65°	504.7	504.1	503.5	503.0	502.4	500.5	497.4	494.3	491.2	488.1	485.6
67.5°	433.7	432.5	431.4	430.2	429.0	427.2	424.9	422.6	420.3	417.9	415.8
70°	389.0	387.6	386.1	384.7	383.4	381.3	378.8	376.3	373.7	371.2	369.5
72.5°	340.1	339.2	338.3	337.3	336.3	335.0	333.4	331.7	330.1	328.5	326.5
75°	268.2	267.7	267.1	266.5	266.0	265.0	263.6	262.1	260.7	259.3	258.4
77.5°	201.9	201.6	201.4	201.2	201.0	200.5	199.7	198.9	198.0	197.3	196.8
80°	160.1	160.1	160.1	160.1	160.1	159.9	159.3	158.7	158.2	157.6	157.4
82.5°	123.5	123.1	122.6	122.2	121.7	121.5	121.3	121.2	121.2	121.0	120.5
85°	70.0	70.2	70.4	70.8	71.0	71.2	71.2	71.2	71.2	71.2	70.9
87.5°	27.6	27.8	28.0	28.2	28.5	28.5	28.5	28.5	28.5	28.4	28.5
90°	0.6	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4
92.5°	14.7	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1
95°	39.4	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5
97.5°	65.4	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1
100°	84.7	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8
102.5°	105.6	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3
105°	138.0	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4
107.5°	173.8	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0
110°	198.5	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7



TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	223.7	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8
115°	260.9	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3
117.5°	298.2	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4
120°	321.4	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0
122.5°	346.6	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1
125°	380.7	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7
127.5°	417.0	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6
130°	438.8	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9
132.5°	460.6	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2
135°	495.0	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3
137.5°	527.5	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6
140°	548.4	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4
142.5°	569.2	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1
145°	599.8	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1
147.5°	628.1	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2
150°	647.0	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8
152.5°	662.5	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6
155°	686.3	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5
157.5°	707.7	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4
160°	720.2	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6
162.5°	731.4	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8
165°	746.2	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2
167.5°	758.9	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2
170°	765.6	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0
172.5°	770.5	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8
175°	775.9	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3
177.5°	778.7	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7	1606.7
2.5°	1602.1	1604.3	1606.6	1607.6	1607.4	1607.2	1607.0	1606.7
5°	1594.0	1596.6	1599.1	1600.3	1599.9	1599.7	1599.4	1599.1
7.5°	1577.8	1580.4	1582.8	1584.0	1583.7	1583.4	1583.1	1582.8
10°	1564.2	1566.5	1568.7	1569.7	1569.5	1569.1	1568.9	1568.6
12.5°	1546.1	1547.8	1549.6	1550.5	1550.5	1550.4	1550.4	1550.3
15°	1514.3	1515.6	1517.0	1517.8	1517.8	1517.8	1517.8	1517.8
17.5°	1477.2	1479.0	1480.7	1480.9	1479.5	1478.1	1476.7	1475.3
20°	1449.3	1451.2	1453.2	1453.5	1452.0	1450.7	1449.3	1447.8
22.5°	1417.4	1418.7	1420.0	1420.2	1419.2	1418.2	1417.2	1416.3
25°	1366.4	1366.9	1367.5	1367.3	1366.5	1365.6	1364.8	1363.9
27.5°	1312.8	1313.0	1313.0	1312.6	1311.8	1311.0	1310.1	1309.3
30°	1273.8	1273.3	1272.7	1272.0	1271.1	1270.3	1269.4	1268.6
32.5°	1234.3	1233.3	1232.2	1230.9	1229.5	1227.9	1226.4	1224.9
35°	1173.0	1171.6	1170.2	1168.3	1166.0	1163.8	1161.6	1159.3
37.5°	1108.6	1106.5	1104.4	1102.7	1101.4	1100.1	1098.8	1097.5
40°	1064.0	1061.4	1058.8	1057.2	1056.3	1055.5	1054.6	1053.8
42.5°	1019.7	1017.3	1015.0	1013.3	1011.9	1010.6	1009.3	1008.0
45°	954.2	950.8	947.5	945.3	944.4	943.6	942.7	941.9
47.5°	885.2	881.7	878.3	875.6	873.6	871.6	869.7	867.7
50°	838.0	834.3	830.6	827.8	825.8	823.9	821.9	819.9
52.5°	792.1	788.9	785.6	782.9	780.7	778.5	776.3	774.1
55°	720.7	718.2	715.7	713.4	711.4	709.5	707.4	705.5
57.5°	649.9	646.6	643.4	641.2	640.1	639.0	637.9	636.8
60°	601.9	599.2	596.3	593.9	591.9	590.0	588.0	586.0
62.5°	555.7	552.7	549.7	547.4	545.8	544.3	542.7	541.3
65°	483.1	480.5	477.9	476.1	475.0	473.9	472.7	471.6
67.5°	413.7	411.5	409.4	408.0	407.2	406.6	405.9	405.2
70°	367.8	366.1	364.4	363.0	361.8	360.7	359.6	358.5
72.5°	324.7	322.7	320.8	319.3	318.1	317.0	315.8	314.7
75°	257.6	256.7	255.9	254.9	253.8	252.7	251.5	250.4
77.5°	196.2	195.8	195.3	194.6	193.8	193.0	192.2	191.4
80°	157.0	156.8	156.5	156.0	155.5	154.9	154.3	153.8
82.5°	120.0	119.5	119.0	118.7	118.5	118.5	118.3	118.2
85°	70.6	70.4	70.0	69.6	69.1	68.5	67.9	67.3
87.5°	28.6	28.8	28.9	28.8	28.5	28.0	27.7	27.3
90°	11.0	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.0	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	48.5	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.0	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	95.0	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	114.6	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	146.3	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.4	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.2	204.6	205.0	205.1	205.0	204.8	204.7	204.6





TEST NUMBER: P333471-930

CATALOG NUMBER: S125DIW-S1270D770U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.0	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.2	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.5	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	349.0	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.4	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.6	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.8	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	465.0	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.7	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	553.8	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.3	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.5	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.0	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.0	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.0	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.1	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	731.5	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	746.7	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.1	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	764.8	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	769.6	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.1	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	777.6	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)