

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333392-930

Luminaire Tested: **S125DIW-S610D1340U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333392-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S610D1340U930-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6413.3 lumens  
Efficiency: N/A  
Efficacy: 119.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	92	92	92	92	73	73	73	56	56	56	39	39	39	32
1	94	89	86	82	84	81	77	75	64	62	60	49	47	46	35	34	33	27
2	85	78	72	67	76	70	65	61	56	53	49	43	40	38	31	29	28	22
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11
8	51	39	32	27	46	36	29	24	29	24	20	22	19	16	16	14	12	10
9	48	36	28	24	43	32	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	19	16	19	16	13	14	12	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5057	5057	5057
5°	5068	5020	5052
10°	5037	4985	5013
15°	4983	4924	4945
20°	4904	4841	4849
25°	4821	4741	4737
30°	4716	4633	4610
35°	4606	4518	4454
40°	4491	4392	4330
45°	4369	4277	4192
50°	4233	4140	4015
55°	4102	3983	3871
60°	3945	3825	3689
65°	3758	3636	3512
70°	3580	3416	3299
75°	3261	3154	3047
80°	2901	2856	2786
85°	2527	2571	2438



TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.8	1.2
10°-20°	208.5	3.3
20°-30°	307.9	4.8
30°-40°	359.3	5.6
40°-50°	360.9	5.6
50°-60°	316.8	4.9
60°-70°	236.0	3.7
70°-80°	135.0	2.1
80°-90°	42.2	0.7
90°-100°	51.7	0.8
100°-110°	318.9	5.0
110°-120°	578.4	9.0
120°-130°	742.3	11.6
130°-140°	798.4	12.4
140°-150°	749.4	11.7
150°-160°	606.3	9.5
160°-170°	392.1	6.1
170°-180°	135.2	2.1
0°-30°	590.3	9.2
0°-40°	949.6	14.8
0°-60°	1627.2	25.4
0°-90°	2040.4	31.8
90°-120°	949.1	14.8
90°-150°	3239.3	50.5
90°-180°	4373.0	68.2
0°-180°	6413.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	783	783	783	783	783	
5°	782	780	774	780	779	74
15°	745	743	736	739	740	210
25°	676	673	665	666	665	311
35°	584	581	573	570	565	365
45°	478	476	468	461	459	368
55°	364	362	354	348	344	325
65°	246	244	238	232	230	244
75°	131	129	126	124	122	139
85°	34	35	35	34	33	38
90°	1	10	17	22	25	4
95°	60	55	17	22	22	77
105°	310	314	314	314	314	329
115°	583	588	589	585	578	577
125°	829	836	836	832	829	740
135°	1034	1039	1038	1035	1029	796
145°	1198	1200	1200	1201	1195	749
155°	1320	1314	1315	1318	1310	608
165°	1392	1386	1387	1393	1385	393
175°	1424	1418	1419	1426	1418	136
180°	1424	1424	1424	1424	1424	



TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	785.0	784.6	784.3	784.0	783.7	782.9	781.9	780.7	779.7	778.5	779.7
5°	781.8	781.5	781.2	780.9	780.6	779.8	778.4	777.1	775.7	774.3	775.6
7.5°	774.5	774.3	774.0	773.7	773.5	772.6	771.0	769.6	768.0	766.5	767.7
10°	768.1	767.8	767.6	767.3	767.0	766.1	764.6	763.1	761.6	760.1	761.2
12.5°	760.2	759.7	759.2	758.7	758.2	757.2	755.9	754.5	753.0	751.6	752.5
15°	745.2	744.8	744.4	744.0	743.6	742.6	741.1	739.6	738.0	736.5	737.2
17.5°	728.0	727.4	726.8	726.2	725.5	724.5	722.9	721.3	719.7	718.2	719.0
20°	713.6	713.3	713.1	712.8	712.5	711.5	709.7	707.9	706.1	704.3	705.3
22.5°	699.2	698.7	698.2	697.7	697.2	696.2	694.5	692.8	691.1	689.4	690.1
25°	676.5	675.7	675.1	674.4	673.7	672.5	670.7	668.9	667.1	665.3	665.6
27.5°	649.8	649.4	649.0	648.6	648.2	647.0	645.1	643.4	641.5	639.7	639.7
30°	632.4	632.0	631.6	631.2	630.8	629.6	627.5	625.4	623.4	621.3	621.0
32.5°	613.6	613.0	612.4	611.7	611.1	609.8	608.1	606.2	604.3	602.5	602.0
35°	584.2	583.6	583.0	582.5	582.0	580.7	578.8	576.8	574.9	573.0	572.3
37.5°	553.5	552.9	552.2	551.5	550.8	549.5	547.7	545.9	544.0	542.3	541.3
40°	532.7	532.1	531.3	530.7	529.9	528.6	526.8	524.8	522.9	521.0	519.8
42.5°	510.5	509.9	509.2	508.7	508.1	506.9	504.9	503.0	501.1	499.1	498.1
45°	478.3	477.7	477.1	476.5	476.1	474.9	473.3	471.7	469.9	468.3	466.7
47.5°	443.5	443.5	443.6	443.6	443.6	442.6	440.7	438.7	436.8	434.7	433.1
50°	421.3	420.8	420.4	420.0	419.6	418.6	416.9	415.2	413.6	412.0	410.2
52.5°	398.4	398.1	397.9	397.5	397.2	396.2	394.4	392.6	390.9	389.1	387.6
55°	364.3	363.8	363.4	363.0	362.6	361.4	359.5	357.6	355.6	353.7	352.5
57.5°	328.2	328.0	327.8	327.5	327.3	326.4	324.7	323.1	321.5	319.9	318.3
60°	305.4	304.8	304.3	303.7	303.2	302.1	300.7	299.1	297.6	296.1	294.7
62.5°	281.6	281.2	280.7	280.3	279.8	279.0	277.7	276.4	275.1	273.8	272.3
65°	245.9	245.6	245.4	245.1	244.8	243.9	242.4	240.9	239.4	237.9	236.6
67.5°	211.3	210.8	210.2	209.6	209.0	208.2	207.1	205.9	204.8	203.7	202.6
70°	189.6	188.9	188.2	187.5	186.8	185.8	184.6	183.4	182.1	180.9	180.0
72.5°	165.8	165.3	164.9	164.4	163.9	163.2	162.5	161.7	160.9	160.0	159.1
75°	130.7	130.4	130.1	129.9	129.6	129.1	128.4	127.8	127.0	126.4	126.0
77.5°	98.4	98.2	98.2	98.0	97.9	97.7	97.3	96.9	96.5	96.1	95.9
80°	78.0	78.0	78.0	78.0	78.0	77.9	77.6	77.4	77.1	76.8	76.6
82.5°	60.3	60.0	59.8	59.5	59.4	59.2	59.1	59.1	59.0	58.9	58.7
85°	34.1	34.2	34.3	34.5	34.7	34.7	34.7	34.7	34.7	34.7	34.6
87.5°	13.6	13.9	14.3	14.8	15.1	15.4	15.6	15.8	16.1	16.2	16.5
90°	1.1	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	16.9	18.1
92.5°	16.2	14.9	13.6	12.3	11.0	11.1	12.6	13.9	15.4	16.9	18.1
95°	60.2	59.4	58.8	58.0	57.3	52.5	43.6	34.7	25.8	16.9	18.1
97.5°	125.6	126.9	128.2	129.4	130.7	122.5	104.8	87.2	69.5	51.9	45.3
100°	176.3	177.0	177.7	178.4	179.1	179.9	180.8	181.8	182.7	183.7	148.7
102.5°	227.8	228.7	229.6	230.5	231.4	232.1	232.7	233.3	233.7	234.3	227.7
105°	310.4	311.3	312.3	313.2	314.1	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.1	396.1	396.1	396.1	396.3	396.8	397.2	397.7	398.2	398.2
110°	451.8	451.8	451.8	451.8	451.8	452.0	452.5	453.0	453.5	453.9	453.2



TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	504.2	504.8	505.3	505.8	506.4	506.9	507.1	507.4	507.7	507.9	507.0
115°	582.7	583.8	585.1	586.2	587.4	588.1	588.3	588.6	588.8	589.1	588.1
117.5°	664.0	663.9	663.9	663.8	663.8	664.2	665.1	666.0	666.9	667.8	666.6
120°	714.6	714.4	714.2	714.0	713.7	714.0	714.6	715.3	716.1	716.7	716.3
122.5°	759.4	760.3	761.2	762.1	763.0	763.6	763.9	764.3	764.6	764.9	764.4
125°	828.7	830.3	831.9	833.6	835.2	836.0	836.0	836.0	836.0	836.0	835.1
127.5°	894.7	895.9	897.1	898.2	899.4	899.9	899.8	899.7	899.5	899.4	898.9
130°	935.2	936.5	937.6	938.8	940.0	940.7	940.9	941.1	941.3	941.6	940.9
132.5°	975.8	977.1	978.5	979.9	981.2	981.7	981.1	980.6	980.2	979.6	979.5
135°	1033.5	1034.9	1036.2	1037.6	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2
137.5°	1086.5	1087.6	1088.8	1090.1	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1
140°	1121.0	1121.5	1122.0	1122.4	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6
142.5°	1152.3	1152.6	1152.8	1153.2	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1
145°	1198.1	1198.6	1199.1	1199.5	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4
147.5°	1238.2	1238.1	1238.0	1238.0	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3
150°	1263.6	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0
152.5°	1288.0	1287.0	1286.0	1285.0	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0
155°	1319.5	1318.1	1316.7	1315.3	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0
157.5°	1343.8	1343.0	1342.1	1341.2	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9
160°	1360.7	1359.3	1357.9	1356.4	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3
162.5°	1374.2	1372.8	1371.3	1369.9	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2
165°	1392.4	1390.9	1389.5	1388.1	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5
167.5°	1405.8	1404.4	1403.0	1401.5	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1
170°	1413.5	1411.9	1410.1	1408.5	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0
172.5°	1418.5	1416.9	1415.3	1413.6	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7
175°	1424.0	1422.6	1421.2	1419.8	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6
177.5°	1426.5	1425.4	1424.3	1423.2	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	783.0	783.0	783.0	783.0	783.0	783.0	783.0	783.0
2.5°	780.7	781.9	782.9	783.4	783.3	783.2	783.1	783.0
5°	776.8	778.0	779.3	779.8	779.7	779.6	779.4	779.3
7.5°	768.9	770.1	771.4	771.9	771.8	771.6	771.5	771.4
10°	762.3	763.4	764.5	765.0	764.8	764.7	764.5	764.4
12.5°	753.4	754.3	755.1	755.6	755.5	755.5	755.5	755.5
15°	737.9	738.6	739.3	739.6	739.6	739.6	739.6	739.6
17.5°	719.9	720.7	721.6	721.7	721.0	720.3	719.7	718.9
20°	706.2	707.2	708.2	708.3	707.6	706.9	706.2	705.6
22.5°	690.7	691.4	692.0	692.1	691.6	691.1	690.6	690.2
25°	665.9	666.1	666.4	666.3	665.9	665.5	665.1	664.7
27.5°	639.8	639.8	639.8	639.7	639.3	638.9	638.5	638.1
30°	620.8	620.5	620.2	619.9	619.5	619.1	618.6	618.2
32.5°	601.5	601.0	600.5	599.9	599.2	598.4	597.6	596.9
35°	571.6	571.0	570.2	569.3	568.3	567.1	566.1	564.9
37.5°	540.2	539.2	538.2	537.4	536.7	536.1	535.5	534.8
40°	518.4	517.2	516.0	515.2	514.8	514.4	514.0	513.6
42.5°	496.9	495.8	494.6	493.7	493.1	492.5	491.9	491.2
45°	465.0	463.3	461.7	460.6	460.2	459.8	459.4	459.0
47.5°	431.4	429.7	428.0	426.7	425.7	424.8	423.8	422.8
50°	408.4	406.6	404.8	403.4	402.4	401.5	400.5	399.6
52.5°	386.0	384.4	382.9	381.6	380.5	379.4	378.3	377.2
55°	351.2	350.0	348.8	347.6	346.7	345.7	344.8	343.8
57.5°	316.7	315.1	313.5	312.4	311.9	311.4	310.9	310.4
60°	293.3	292.0	290.6	289.4	288.5	287.5	286.5	285.6
62.5°	270.8	269.4	267.8	266.8	266.0	265.2	264.5	263.7
65°	235.4	234.2	232.9	232.0	231.5	230.9	230.4	229.8
67.5°	201.6	200.6	199.5	198.8	198.4	198.1	197.8	197.5
70°	179.2	178.4	177.6	176.9	176.3	175.8	175.2	174.7
72.5°	158.2	157.3	156.3	155.6	155.0	154.5	153.9	153.4
75°	125.6	125.1	124.7	124.3	123.7	123.1	122.6	122.1
77.5°	95.6	95.4	95.1	94.8	94.4	94.1	93.7	93.3
80°	76.6	76.4	76.2	76.1	75.7	75.5	75.3	74.9
82.5°	58.5	58.2	58.0	57.8	57.8	57.7	57.6	57.6
85°	34.4	34.2	34.2	33.9	33.7	33.3	33.1	32.9
87.5°	16.7	17.0	17.2	17.3	17.2	17.1	17.0	17.0
90°	19.2	20.4	21.6	22.5	23.2	23.9	24.6	25.4
92.5°	19.2	20.4	21.6	22.3	22.7	23.0	23.3	23.6
95°	19.2	20.4	21.6	22.2	22.2	22.2	22.2	22.2
97.5°	38.7	32.1	25.4	22.2	22.2	22.2	22.2	22.2
100°	113.7	78.8	43.9	25.9	24.9	24.1	23.1	22.2
102.5°	221.1	214.5	207.9	196.6	180.7	164.7	148.7	132.8
105°	314.5	314.5	314.5	314.5	314.2	314.0	313.7	313.5
107.5°	398.3	398.4	398.4	398.0	397.3	396.6	395.9	395.3
110°	452.5	451.8	451.1	450.9	451.1	451.3	451.6	451.8





TEST NUMBER: P333392-930

CATALOG NUMBER: S125DIW-S610D1340U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	506.1	505.3	504.4	503.8	503.4	503.1	502.8	502.5
115°	587.2	586.2	585.3	584.1	582.7	581.3	579.8	578.5
117.5°	665.4	664.1	662.9	661.9	661.4	660.8	660.1	659.6
120°	715.8	715.3	714.9	714.0	712.9	711.7	710.5	709.4
122.5°	763.9	763.4	763.0	762.1	760.8	759.4	758.0	756.7
125°	834.1	833.2	832.3	831.4	830.8	830.1	829.3	828.7
127.5°	898.4	897.8	897.3	896.2	894.5	892.8	891.0	889.2
130°	940.2	939.5	938.8	937.8	936.7	935.5	934.3	933.2
132.5°	979.3	979.2	979.0	978.4	977.2	976.1	974.9	973.7
135°	1036.7	1036.2	1035.8	1034.9	1033.5	1032.0	1030.6	1029.2
137.5°	1090.2	1090.3	1090.4	1089.8	1088.6	1087.4	1086.1	1084.9
140°	1123.1	1123.5	1124.0	1123.5	1122.1	1120.7	1119.3	1117.9
142.5°	1155.2	1155.4	1155.4	1154.8	1153.3	1151.9	1150.6	1149.2
145°	1200.7	1200.9	1201.2	1200.6	1199.1	1197.8	1196.4	1195.0
147.5°	1239.7	1239.9	1240.2	1239.5	1237.8	1236.1	1234.4	1232.7
150°	1264.5	1264.9	1265.4	1264.7	1262.8	1260.9	1259.1	1257.2
152.5°	1286.5	1286.9	1287.4	1286.8	1285.1	1283.4	1281.7	1280.0
155°	1316.7	1317.4	1318.1	1317.5	1315.6	1313.8	1311.9	1310.0
157.5°	1341.7	1342.5	1343.2	1342.6	1340.8	1338.9	1337.0	1335.1
160°	1357.3	1358.2	1359.2	1358.7	1356.8	1354.9	1353.1	1351.2
162.5°	1371.5	1372.9	1374.2	1373.8	1371.7	1369.6	1367.6	1365.5
165°	1389.8	1391.3	1392.7	1392.4	1390.6	1388.7	1386.8	1384.9
167.5°	1403.8	1405.4	1407.1	1406.9	1404.8	1402.7	1400.6	1398.5
170°	1410.9	1412.8	1414.6	1414.5	1412.4	1410.3	1408.2	1406.1
172.5°	1416.4	1418.1	1419.8	1419.6	1417.5	1415.4	1413.2	1411.1
175°	1422.5	1424.3	1426.2	1426.1	1424.0	1421.9	1419.8	1417.6
177.5°	1425.0	1426.3	1427.6	1427.5	1426.0	1424.5	1422.9	1421.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0

(END OF REPORT)