

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333418-930

Luminaire Tested: **S125DIW-S850D1340U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333418-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1340U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7190.4 lumens  
Efficiency: N/A  
Efficacy: 117.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 61.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6442	6442	6442	6442
5°	7459	6463	5659	6463
10°	8679	6430	4958	6430
15°	9607	6383	4574	6383
20°	10754	6308	4265	6308
25°	12598	6223	4115	6223
30°	13607	6141	3985	6141
35°	11188	5984	3899	5984
40°	7952	5767	3805	5767
45°	6109	5476	3751	5476
50°	5215	5112	3743	5112
55°	4644	4757	3775	4757
60°	4188	4370	3871	4370
65°	3869	3978	3972	3978
70°	3518	3573	4030	3573
75°	3107	3147	3992	3147
80°	2615	2566	3652	2566
85°	2075	1845	2949	1845



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.0	1.3
10°-20°	285.9	4.0
20°-30°	464.2	6.5
30°-40°	566.3	7.9
40°-50°	515.1	7.2
50°-60°	410.3	5.7
60°-70°	285.8	4.0
70°-80°	152.4	2.1
80°-90°	41.4	0.6
90°-100°	51.7	0.7
100°-110°	318.9	4.4
110°-120°	578.4	8.0
120°-130°	742.3	10.3
130°-140°	798.4	11.1
140°-150°	749.4	10.4
150°-160°	606.3	8.4
160°-170°	392.1	5.5
170°-180°	135.2	1.9
0°-30°	846.1	11.8
0°-40°	1412.4	19.6
0°-60°	2337.8	32.5
0°-90°	2817.5	39.2
90°-120°	949.1	13.2
90°-150°	3239.3	45.1
90°-180°	4373.0	60.8
0°-180°	7190.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	997	997	997	997	997	
5°	1151	997	873	997	1151	116
15°	1437	955	684	955	1437	411
25°	1768	873	578	873	1768	807
35°	1419	759	494	759	1419	868
45°	669	600	411	600	669	535
55°	412	422	335	422	412	371
65°	253	260	260	260	253	251
75°	124	126	160	126	124	134
85°	28	25	40	25	28	33
90°	25	1	25	1	25	12
95°	22	60	22	60	22	18
105°	314	310	314	310	314	283
115°	578	583	578	583	578	574
125°	829	829	829	829	829	737
135°	1029	1034	1029	1034	1029	794
145°	1195	1198	1195	1198	1195	746
155°	1310	1320	1310	1320	1310	604
165°	1385	1392	1385	1392	1385	391
175°	1418	1424	1418	1424	1418	135
180°	1424	1424	1424	1424	1424	



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1055.0	1053.6	1052.3	1049.5	1051.6	1045.9	1043.1	1038.4	1032.7	1030.6	1028.3
5°	1150.6	1152.8	1154.9	1146.0	1146.9	1140.9	1127.4	1116.4	1107.5	1096.1	1088.0
7.5°	1265.8	1260.8	1260.4	1254.7	1244.7	1236.8	1222.5	1204.4	1186.9	1166.9	1150.4
10°	1323.4	1323.8	1320.0	1313.2	1302.7	1295.0	1276.4	1258.6	1237.1	1211.6	1193.4
12.5°	1366.8	1368.5	1363.7	1354.5	1349.4	1332.3	1317.7	1296.6	1270.9	1250.6	1222.9
15°	1436.9	1432.2	1428.8	1417.4	1408.5	1390.7	1367.4	1345.4	1317.4	1291.6	1265.8
17.5°	1504.4	1508.1	1501.8	1491.3	1463.8	1443.0	1411.8	1381.6	1346.9	1312.2	1281.4
20°	1564.7	1568.1	1558.4	1540.2	1507.2	1486.4	1445.3	1406.4	1366.1	1321.7	1287.8
22.5°	1639.9	1637.2	1624.1	1596.4	1567.7	1529.4	1484.9	1437.5	1387.2	1336.9	1291.9
25°	1767.9	1750.1	1742.1	1707.8	1670.1	1613.8	1552.8	1483.4	1420.7	1354.3	1296.7
27.5°	1838.8	1833.3	1824.3	1800.4	1760.8	1700.6	1628.7	1544.1	1455.7	1371.8	1296.5
30°	1824.6	1825.5	1826.4	1818.7	1793.3	1748.0	1676.5	1585.4	1480.4	1386.0	1298.9
32.5°	1698.7	1714.1	1728.8	1746.2	1753.3	1744.7	1699.8	1617.6	1509.6	1402.3	1297.5
35°	1419.0	1423.8	1471.5	1519.0	1583.3	1633.3	1666.7	1630.4	1539.3	1416.1	1295.8
37.5°	1106.4	1129.4	1162.5	1216.0	1308.9	1392.0	1499.0	1548.2	1518.8	1420.6	1292.9
40°	943.2	964.4	985.9	1040.6	1118.9	1219.7	1341.2	1444.9	1469.0	1406.4	1282.7
42.5°	817.3	834.0	857.9	899.0	964.5	1053.7	1169.8	1305.4	1388.8	1365.1	1261.4
45°	668.9	679.5	698.1	730.7	778.1	848.0	950.4	1098.6	1227.7	1270.5	1210.8
47.5°	572.5	572.4	586.9	609.4	643.7	703.0	778.8	894.9	1032.8	1134.8	1130.1
50°	519.0	516.9	528.3	547.8	574.9	614.2	686.6	779.3	911.9	1027.4	1059.6
52.5°	473.0	473.2	480.2	494.6	517.3	551.0	605.0	688.6	801.8	920.5	981.0
55°	412.4	410.7	418.7	428.4	444.9	466.9	505.9	569.8	661.7	778.5	857.3
57.5°	356.8	361.4	364.7	371.5	385.1	399.9	432.8	479.6	552.5	652.8	736.1
60°	324.2	329.0	331.5	338.3	349.3	362.0	387.3	425.5	486.8	573.2	655.7
62.5°	295.1	298.8	299.6	305.7	314.7	327.1	347.1	379.0	427.5	503.1	584.0
65°	253.2	253.2	254.9	261.2	265.5	276.5	291.7	315.0	353.9	412.8	481.8
67.5°	212.7	214.7	214.3	217.1	221.0	229.5	240.4	259.7	288.5	331.5	386.7
70°	186.3	187.9	187.5	189.6	193.9	199.4	208.3	226.5	247.2	284.1	331.5
72.5°	162.6	163.2	162.2	164.9	167.5	172.3	182.2	191.9	211.3	242.4	281.4
75°	124.5	125.3	126.1	127.8	130.4	132.9	138.0	147.7	160.5	183.8	208.7
77.5°	93.3	91.7	93.8	93.5	94.9	96.9	101.3	106.5	116.9	131.7	151.0
80°	70.3	70.7	70.7	71.1	73.2	74.5	78.4	82.1	90.2	101.2	114.7
82.5°	51.3	52.4	51.8	52.5	54.3	55.2	57.3	60.4	65.1	73.8	83.6
85°	28.0	25.8	26.7	27.6	27.6	28.0	29.6	30.9	33.4	36.9	40.6
87.5°	13.2	13.7	13.9	13.8	14.0	13.8	14.9	14.7	15.5	16.2	17.3
90°	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2	18.1	16.9	15.2
92.5°	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2	18.1	16.9	15.4
95°	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2	18.1	16.9	25.8
97.5°	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7	45.3	51.9	69.5
100°	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7	148.7	183.7	182.7
102.5°	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1	227.7	234.3	233.7
105°	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3	398.2	398.2	397.7
110°	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5	453.2	453.9	453.5



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1	507.0	507.9	507.7
115°	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2	588.1	589.1	588.8
117.5°	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4	666.6	667.8	666.9
120°	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8	716.3	716.7	716.1
122.5°	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9	764.4	764.9	764.6
125°	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1	835.1	836.0	836.0
127.5°	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4	898.9	899.4	899.5
130°	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2	940.9	941.6	941.3
132.5°	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3	979.5	979.6	980.2
135°	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7	1037.2	1037.6	1038.1
137.5°	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2	1090.1	1090.1	1090.5
140°	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1	1122.6	1122.1	1122.3
142.5°	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2	1155.1	1155.0	1154.7
145°	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7	1200.4	1200.2	1200.2
147.5°	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7	1239.3	1239.1	1238.8
150°	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5	1264.0	1263.6	1263.1
152.5°	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5	1286.0	1285.5	1285.1
155°	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7	1316.0	1315.3	1314.8
157.5°	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7	1340.9	1340.2	1340.2
160°	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3	1356.3	1355.4	1355.2
162.5°	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5	1370.2	1368.9	1368.6
165°	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8	1388.5	1387.1	1386.8
167.5°	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8	1402.1	1400.4	1400.1
170°	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9	1409.0	1407.1	1406.9
172.5°	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4	1414.7	1413.0	1412.6
175°	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5	1420.6	1418.7	1418.5
177.5°	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0	1423.7	1422.3	1422.1
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1026.2	1023.9	1021.1	1016.4	1010.6	1007.5	1002.8	999.8	993.7	988.6	983.2
5°	1078.2	1067.2	1057.1	1044.0	1029.6	1020.3	1009.3	996.9	984.3	971.2	956.8
7.5°	1132.2	1112.7	1091.5	1068.8	1046.5	1026.1	1006.5	987.2	969.3	947.6	929.3
10°	1168.4	1143.9	1117.6	1086.7	1056.7	1030.5	1003.8	980.5	956.8	931.4	908.9
12.5°	1204.7	1172.0	1134.9	1101.0	1064.8	1033.1	1001.8	972.0	942.2	914.1	887.9
15°	1230.3	1201.4	1167.2	1118.9	1078.2	1034.7	993.2	954.6	918.7	887.4	854.4
17.5°	1247.1	1210.0	1173.2	1126.9	1073.6	1024.8	977.9	933.8	893.2	853.5	821.7
20°	1250.2	1212.0	1173.5	1128.2	1073.6	1017.7	970.8	917.8	874.2	833.2	794.2
22.5°	1249.1	1206.0	1164.0	1117.4	1064.1	1012.7	955.9	901.9	854.6	814.2	773.6
25°	1239.6	1193.4	1140.9	1094.0	1041.5	986.8	929.3	873.3	825.1	778.9	738.7
27.5°	1231.6	1171.7	1112.3	1057.5	1006.8	956.8	901.6	844.4	790.9	744.1	706.2
30°	1221.8	1156.2	1089.2	1032.1	980.1	931.4	879.3	823.5	767.5	721.8	681.2
32.5°	1213.0	1136.5	1065.9	1003.7	948.5	901.2	853.2	800.1	745.2	698.8	658.1
35°	1196.0	1107.5	1026.6	956.3	897.5	848.8	808.6	759.0	708.7	663.8	624.8
37.5°	1174.4	1069.3	982.6	908.9	844.4	793.1	755.7	717.6	669.3	626.1	590.8
40°	1157.4	1042.3	950.4	875.1	808.2	754.8	720.2	684.1	643.9	603.7	566.5
42.5°	1136.1	1017.9	917.9	836.8	770.5	718.6	682.2	651.6	616.1	578.6	544.0
45°	1096.9	973.7	865.4	778.1	711.2	660.0	622.3	599.5	572.8	537.2	508.0
47.5°	1039.3	920.6	808.5	718.5	649.5	602.0	566.7	544.8	525.9	499.5	473.0
50°	988.1	881.0	767.5	678.2	609.2	561.3	528.8	508.8	492.8	472.5	450.0
52.5°	930.8	831.2	727.2	639.0	570.6	523.4	491.5	474.0	460.6	446.1	424.0
55°	839.9	755.3	658.8	574.9	511.8	465.7	437.7	422.5	411.5	400.5	386.9
57.5°	739.7	673.5	588.0	511.4	453.3	411.3	385.2	370.4	361.9	356.2	348.2
60°	669.3	612.6	538.9	469.0	412.4	375.1	349.7	338.3	331.1	326.4	320.5
62.5°	604.0	557.4	489.1	425.3	375.8	340.6	317.9	306.8	299.9	297.6	292.7
65°	507.6	471.7	415.3	362.4	320.1	290.0	270.9	260.3	256.1	253.6	254.0
67.5°	412.7	390.8	345.5	300.4	266.6	241.4	226.2	218.0	215.9	212.5	212.5
70°	354.7	338.3	300.2	260.8	230.7	211.2	197.7	189.2	187.1	185.4	185.0
72.5°	303.6	289.2	256.1	224.5	197.5	180.4	169.3	164.2	160.7	159.7	159.6
75°	228.2	220.1	193.9	168.9	150.3	138.4	130.9	126.1	123.6	123.2	123.6
77.5°	162.2	155.2	138.5	120.8	109.1	100.1	93.7	92.0	89.2	89.3	88.8
80°	121.9	117.2	106.7	92.7	83.0	75.3	72.0	69.0	68.2	66.9	68.2
82.5°	88.4	83.4	76.2	67.3	59.3	54.7	51.3	50.4	49.9	49.2	49.6
85°	43.6	44.0	39.8	33.0	29.6	27.1	24.9	24.9	24.5	24.1	24.5
87.5°	17.6	16.6	14.9	13.5	11.5	10.1	9.4	9.4	8.7	8.7	9.5
90°	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1	2.9	4.8	6.7
92.5°	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2	14.9	13.6	12.3
95°	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2	59.4	58.8	58.0
97.5°	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6	126.9	128.2	129.4
100°	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3	177.0	177.7	178.4
102.5°	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8	228.7	229.6	230.5
105°	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4	311.3	312.3	313.2
107.5°	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1	396.1	396.1	396.1
110°	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8	451.8	451.8	451.8





TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2	504.8	505.3	505.8
115°	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7	583.8	585.1	586.2
117.5°	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0	663.9	663.9	663.8
120°	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6	714.4	714.2	714.0
122.5°	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4	760.3	761.2	762.1
125°	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7	830.3	831.9	833.6
127.5°	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7	895.9	897.1	898.2
130°	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2	936.5	937.6	938.8
132.5°	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8	977.1	978.5	979.9
135°	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5	1034.9	1036.2	1037.6
137.5°	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5	1087.6	1088.8	1090.1
140°	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0	1121.5	1122.0	1122.4
142.5°	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3	1152.6	1152.8	1153.2
145°	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1	1198.6	1199.1	1199.5
147.5°	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2	1238.1	1238.0	1238.0
150°	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1263.1	1262.7	1262.2
152.5°	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0	1287.0	1286.0	1285.0
155°	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5	1318.1	1316.7	1315.3
157.5°	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8	1343.0	1342.1	1341.2
160°	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7	1359.3	1357.9	1356.4
162.5°	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2	1372.8	1371.3	1369.9
165°	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4	1390.9	1389.5	1388.1
167.5°	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8	1404.4	1403.0	1401.5
170°	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5	1411.9	1410.1	1408.5
172.5°	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5	1416.9	1415.3	1413.6
175°	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0	1422.6	1421.2	1419.8
177.5°	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5	1425.4	1424.3	1423.2
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	980.2	976.4	973.4	966.6	962.9	957.8	953.7	958.1	953.4	955.4	952.4
5°	949.6	937.8	929.3	917.0	906.4	896.7	889.5	888.2	884.8	883.1	878.0
7.5°	912.8	898.0	883.5	867.4	853.8	840.0	831.2	823.9	819.1	812.8	808.5
10°	891.1	871.2	854.4	834.9	817.9	803.1	791.2	785.3	779.8	771.8	768.8
12.5°	864.4	843.8	823.1	802.3	786.1	769.6	759.4	750.4	746.7	737.5	736.6
15°	832.3	801.4	781.1	759.9	737.4	723.9	715.4	705.7	701.5	695.1	690.5
17.5°	794.0	766.5	741.0	719.1	699.9	688.4	677.9	671.2	664.0	659.8	652.2
20°	766.3	740.0	714.6	691.3	676.5	663.4	654.9	648.6	641.0	638.9	631.2
22.5°	742.9	714.0	689.6	670.0	653.8	639.0	629.8	625.6	620.3	613.8	612.2
25°	704.9	674.8	654.1	634.6	620.2	606.7	600.3	594.8	589.7	585.1	583.3
27.5°	672.1	645.1	620.5	602.9	590.4	578.0	572.4	565.7	562.1	558.3	553.8
30°	649.0	621.5	599.9	582.9	569.4	558.4	552.4	547.8	544.5	541.0	538.5
32.5°	625.3	599.8	578.9	562.3	548.8	540.5	535.2	531.9	528.2	524.1	520.9
35°	593.9	566.0	545.7	531.3	520.7	514.4	508.4	505.5	501.2	501.2	497.8
37.5°	558.6	534.5	516.6	503.4	494.0	488.3	481.8	479.8	477.1	475.3	474.2
40°	537.7	515.2	498.3	485.2	475.0	470.3	465.3	461.9	460.2	458.0	457.2
42.5°	516.0	494.6	478.3	466.2	457.4	453.4	448.7	446.3	442.9	440.1	439.6
45°	483.1	462.3	447.5	437.7	430.2	425.5	422.5	417.4	415.7	412.4	411.9
47.5°	451.8	431.9	417.4	409.4	402.7	398.8	394.2	389.1	387.2	385.5	385.3
50°	428.4	410.3	396.6	389.1	382.7	377.2	372.5	369.2	367.9	367.9	368.8
52.5°	404.7	389.2	377.7	368.4	362.4	356.5	352.2	350.2	348.2	350.3	351.8
55°	370.0	354.3	345.8	337.0	331.1	324.2	322.2	321.3	320.1	323.4	325.1
57.5°	333.3	322.3	312.3	303.5	298.2	294.3	291.5	290.9	293.3	294.9	300.4
60°	309.9	297.2	288.3	281.5	275.2	272.6	271.8	270.9	272.6	277.3	284.5
62.5°	284.1	273.9	264.2	259.2	254.5	250.3	250.1	250.6	254.0	259.3	266.5
65°	246.4	237.5	231.1	225.2	221.4	218.9	219.7	221.4	225.2	232.4	240.4
67.5°	208.1	201.9	196.2	191.4	187.8	187.8	188.7	191.2	195.7	204.0	211.3
70°	183.3	176.5	171.9	169.7	166.8	165.1	167.6	171.9	175.7	183.3	189.6
72.5°	158.6	152.9	149.2	147.7	146.5	145.1	145.9	150.5	155.7	163.3	170.7
75°	121.9	119.8	117.2	115.6	114.3	115.1	116.0	120.3	124.5	132.5	141.0
77.5°	88.9	86.7	85.3	84.9	84.1	84.5	87.0	90.1	94.2	100.1	106.5
80°	67.3	66.4	65.6	65.2	65.2	65.6	69.0	71.1	74.9	80.5	85.5
82.5°	49.0	48.5	48.3	48.3	48.6	48.7	50.7	53.5	56.7	60.8	65.2
85°	25.8	24.9	26.3	26.7	25.8	27.1	28.0	29.6	30.9	33.0	35.1
87.5°	10.2	11.2	11.2	11.9	12.2	13.2	13.1	14.7	15.6	16.5	16.4
90°	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2	20.4	21.6	22.5
92.5°	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2	20.4	21.6	22.3
95°	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2	20.4	21.6	22.2
97.5°	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7	32.1	25.4	22.2
100°	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7	78.8	43.9	25.9
102.5°	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1	214.5	207.9	196.6
105°	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3	398.4	398.4	398.0
110°	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5	451.8	451.1	450.9



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1	505.3	504.4	503.8
115°	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2	586.2	585.3	584.1
117.5°	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4	664.1	662.9	661.9
120°	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8	715.3	714.9	714.0
122.5°	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9	763.4	763.0	762.1
125°	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1	833.2	832.3	831.4
127.5°	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4	897.8	897.3	896.2
130°	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2	939.5	938.8	937.8
132.5°	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3	979.2	979.0	978.4
135°	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7	1036.2	1035.8	1034.9
137.5°	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2	1090.3	1090.4	1089.8
140°	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1	1123.5	1124.0	1123.5
142.5°	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2	1155.4	1155.4	1154.8
145°	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7	1200.9	1201.2	1200.6
147.5°	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7	1239.9	1240.2	1239.5
150°	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5	1264.9	1265.4	1264.7
152.5°	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5	1286.9	1287.4	1286.8
155°	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7	1317.4	1318.1	1317.5
157.5°	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7	1342.5	1343.2	1342.6
160°	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3	1358.2	1359.2	1358.7
162.5°	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5	1372.9	1374.2	1373.8
165°	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8	1391.3	1392.7	1392.4
167.5°	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8	1405.4	1407.1	1406.9
170°	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9	1412.8	1414.6	1414.5
172.5°	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4	1418.1	1419.8	1419.6
175°	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5	1424.3	1426.2	1426.1
177.5°	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0	1426.3	1427.6	1427.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	950.3	952.7	950.6	953.4	950.6	952.7	950.3	952.4	955.4	953.4	958.1
5°	875.9	872.1	874.7	872.9	874.7	872.1	875.9	878.0	883.1	884.8	888.2
7.5°	807.1	803.5	799.4	797.4	799.4	803.5	807.1	808.5	812.8	819.1	823.9
10°	764.2	759.5	759.0	756.1	759.0	759.5	764.2	768.8	771.8	779.8	785.3
12.5°	732.6	728.3	723.5	722.3	723.5	728.3	732.6	736.6	737.5	746.7	750.4
15°	687.9	684.5	681.6	684.1	681.6	684.5	687.9	690.5	695.1	701.5	705.7
17.5°	650.8	648.0	647.4	644.3	647.4	648.0	650.8	652.2	659.8	664.0	671.2
20°	627.4	625.3	626.1	620.6	626.1	625.3	627.4	631.2	638.9	641.0	648.6
22.5°	608.8	604.6	604.1	603.0	604.1	604.6	608.8	612.2	613.8	620.3	625.6
25°	579.6	577.5	575.4	577.5	575.4	577.5	579.6	583.3	585.1	589.7	594.8
27.5°	554.1	551.5	551.0	551.2	551.0	551.5	554.1	553.8	558.3	562.1	565.7
30°	538.5	534.3	534.7	534.3	534.7	534.3	538.5	538.5	541.0	544.5	547.8
32.5°	521.5	518.7	518.1	517.3	518.1	518.7	521.5	520.9	524.1	528.2	531.9
35°	496.6	496.6	494.5	494.5	494.5	496.6	496.6	497.8	501.2	501.2	505.5
37.5°	473.1	472.7	471.4	471.7	471.4	472.7	473.1	474.2	475.3	477.1	479.8
40°	455.5	455.1	453.8	451.3	453.8	455.1	455.5	457.2	458.0	460.2	461.9
42.5°	438.5	437.2	436.6	435.7	436.6	437.2	438.5	439.6	440.1	442.9	446.3
45°	411.9	411.9	411.1	410.7	411.1	411.9	411.9	411.9	412.4	415.7	417.4
47.5°	386.0	386.8	388.4	388.2	388.4	386.8	386.0	385.3	385.5	387.2	389.1
50°	370.4	370.9	372.1	372.5	372.1	370.9	370.4	368.8	367.9	367.9	369.2
52.5°	353.2	355.6	357.2	356.9	357.2	355.6	353.2	351.8	350.3	348.2	350.2
55°	329.0	331.9	334.8	335.3	334.8	331.9	329.0	325.1	323.4	320.1	321.3
57.5°	305.0	309.2	312.3	313.2	312.3	309.2	305.0	300.4	294.9	293.3	290.9
60°	288.7	294.2	298.1	299.7	298.1	294.2	288.7	284.5	277.3	272.6	270.9
62.5°	273.1	279.3	283.2	283.5	283.2	279.3	273.1	266.5	259.3	254.0	250.6
65°	247.7	254.0	257.4	259.9	257.4	254.0	247.7	240.4	232.4	225.2	221.4
67.5°	220.2	226.6	230.3	232.4	230.3	226.6	220.2	211.3	204.0	195.7	191.2
70°	200.2	206.6	211.7	213.4	211.7	206.6	200.2	189.6	183.3	175.7	171.9
72.5°	180.6	186.3	190.4	192.3	190.4	186.3	180.6	170.7	163.3	155.7	150.5
75°	146.5	154.1	157.9	160.0	157.9	154.1	146.5	141.0	132.5	124.5	120.3
77.5°	112.9	119.9	122.2	123.3	122.2	119.9	112.9	106.5	100.1	94.2	90.1
80°	90.6	94.8	97.8	98.2	97.8	94.8	90.6	85.5	80.5	74.9	71.1
82.5°	69.6	73.1	74.1	75.2	74.1	73.1	69.6	65.2	60.8	56.7	53.5
85°	38.1	39.8	40.2	39.8	40.2	39.8	38.1	35.1	33.0	30.9	29.6
87.5°	17.2	17.0	17.1	17.9	17.1	17.0	17.2	16.4	16.5	15.6	14.7
90°	23.2	23.9	24.6	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2
92.5°	22.7	23.0	23.3	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2
97.5°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7
100°	24.9	24.1	23.1	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7
102.5°	180.7	164.7	148.7	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1
105°	314.2	314.0	313.7	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5
107.5°	397.3	396.6	395.9	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3
110°	451.1	451.3	451.6	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.4	503.1	502.8	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1
115°	582.7	581.3	579.8	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2
117.5°	661.4	660.8	660.1	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4
120°	712.9	711.7	710.5	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8
122.5°	760.8	759.4	758.0	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9
125°	830.8	830.1	829.3	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1
127.5°	894.5	892.8	891.0	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4
130°	936.7	935.5	934.3	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2
132.5°	977.2	976.1	974.9	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3
135°	1033.5	1032.0	1030.6	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7
137.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2
140°	1122.1	1120.7	1119.3	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1
142.5°	1153.3	1151.9	1150.6	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2
145°	1199.1	1197.8	1196.4	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7
147.5°	1237.8	1236.1	1234.4	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7
150°	1262.8	1260.9	1259.1	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5
152.5°	1285.1	1283.4	1281.7	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5
155°	1315.6	1313.8	1311.9	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7
157.5°	1340.8	1338.9	1337.0	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7
160°	1356.8	1354.9	1353.1	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3
162.5°	1371.7	1369.6	1367.6	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5
165°	1390.6	1388.7	1386.8	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8
167.5°	1404.8	1402.7	1400.6	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8
170°	1412.4	1410.3	1408.2	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9
172.5°	1417.5	1415.4	1413.2	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4
175°	1424.0	1421.9	1419.8	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5
177.5°	1426.0	1424.5	1422.9	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	953.7	957.8	962.9	966.6	973.4	976.4	980.2	983.2	988.6	993.7	999.8
5°	889.5	896.7	906.4	917.0	929.3	937.8	949.6	956.8	971.2	984.3	996.9
7.5°	831.2	840.0	853.8	867.4	883.5	898.0	912.8	929.3	947.6	969.3	987.2
10°	791.2	803.1	817.9	834.9	854.4	871.2	891.1	908.9	931.4	956.8	980.5
12.5°	759.4	769.6	786.1	802.3	823.1	843.8	864.4	887.9	914.1	942.2	972.0
15°	715.4	723.9	737.4	759.9	781.1	801.4	832.3	854.4	887.4	918.7	954.6
17.5°	677.9	688.4	699.9	719.1	741.0	766.5	794.0	821.7	853.5	893.2	933.8
20°	654.9	663.4	676.5	691.3	714.6	740.0	766.3	794.2	833.2	874.2	917.8
22.5°	629.8	639.0	653.8	670.0	689.6	714.0	742.9	773.6	814.2	854.6	901.9
25°	600.3	606.7	620.2	634.6	654.1	674.8	704.9	738.7	778.9	825.1	873.3
27.5°	572.4	578.0	590.4	602.9	620.5	645.1	672.1	706.2	744.1	790.9	844.4
30°	552.4	558.4	569.4	582.9	599.9	621.5	649.0	681.2	721.8	767.5	823.5
32.5°	535.2	540.5	548.8	562.3	578.9	599.8	625.3	658.1	698.8	745.2	800.1
35°	508.4	514.4	520.7	531.3	545.7	566.0	593.9	624.8	663.8	708.7	759.0
37.5°	481.8	488.3	494.0	503.4	516.6	534.5	558.6	590.8	626.1	669.3	717.6
40°	465.3	470.3	475.0	485.2	498.3	515.2	537.7	566.5	603.7	643.9	684.1
42.5°	448.7	453.4	457.4	466.2	478.3	494.6	516.0	544.0	578.6	616.1	651.6
45°	422.5	425.5	430.2	437.7	447.5	462.3	483.1	508.0	537.2	572.8	599.5
47.5°	394.2	398.8	402.7	409.4	417.4	431.9	451.8	473.0	499.5	525.9	544.8
50°	372.5	377.2	382.7	389.1	396.6	410.3	428.4	450.0	472.5	492.8	508.8
52.5°	352.2	356.5	362.4	368.4	377.7	389.2	404.7	424.0	446.1	460.6	474.0
55°	322.2	324.2	331.1	337.0	345.8	354.3	370.0	386.9	400.5	411.5	422.5
57.5°	291.5	294.3	298.2	303.5	312.3	322.3	333.3	348.2	356.2	361.9	370.4
60°	271.8	272.6	275.2	281.5	288.3	297.2	309.9	320.5	326.4	331.1	338.3
62.5°	250.1	250.3	254.5	259.2	264.2	273.9	284.1	292.7	297.6	299.9	306.8
65°	219.7	218.9	221.4	225.2	231.1	237.5	246.4	254.0	253.6	256.1	260.3
67.5°	188.7	187.8	187.8	191.4	196.2	201.9	208.1	212.5	212.5	215.9	218.0
70°	167.6	165.1	166.8	169.7	171.9	176.5	183.3	185.0	185.4	187.1	189.2
72.5°	145.9	145.1	146.5	147.7	149.2	152.9	158.6	159.6	159.7	160.7	164.2
75°	116.0	115.1	114.3	115.6	117.2	119.8	121.9	123.6	123.2	123.6	126.1
77.5°	87.0	84.5	84.1	84.9	85.3	86.7	88.9	88.8	89.3	89.2	92.0
80°	69.0	65.6	65.2	65.2	65.6	66.4	67.3	68.2	66.9	68.2	69.0
82.5°	50.7	48.7	48.6	48.3	48.3	48.5	49.0	49.6	49.2	49.9	50.4
85°	28.0	27.1	25.8	26.7	26.3	24.9	25.8	24.5	24.1	24.5	24.9
87.5°	13.1	13.2	12.2	11.9	11.2	11.2	10.2	9.5	8.7	8.7	9.4
90°	18.1	16.9	15.2	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1
92.5°	18.1	16.9	15.4	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2
95°	18.1	16.9	25.8	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2
97.5°	45.3	51.9	69.5	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6
100°	148.7	183.7	182.7	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3
102.5°	227.7	234.3	233.7	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8
105°	314.5	314.5	314.5	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4
107.5°	398.2	398.2	397.7	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1
110°	453.2	453.9	453.5	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	507.0	507.9	507.7	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2
115°	588.1	589.1	588.8	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7
117.5°	666.6	667.8	666.9	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0
120°	716.3	716.7	716.1	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6
122.5°	764.4	764.9	764.6	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4
125°	835.1	836.0	836.0	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7
127.5°	898.9	899.4	899.5	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7
130°	940.9	941.6	941.3	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2
132.5°	979.5	979.6	980.2	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8
135°	1037.2	1037.6	1038.1	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5
137.5°	1090.1	1090.1	1090.5	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5
140°	1122.6	1122.1	1122.3	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0
142.5°	1155.1	1155.0	1154.7	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3
145°	1200.4	1200.2	1200.2	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1
147.5°	1239.3	1239.1	1238.8	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2
150°	1264.0	1263.6	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6
152.5°	1286.0	1285.5	1285.1	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0
155°	1316.0	1315.3	1314.8	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5
157.5°	1340.9	1340.2	1340.2	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8
160°	1356.3	1355.4	1355.2	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7
162.5°	1370.2	1368.9	1368.6	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2
165°	1388.5	1387.1	1386.8	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4
167.5°	1402.1	1400.4	1400.1	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8
170°	1409.0	1407.1	1406.9	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5
172.5°	1414.7	1413.0	1412.6	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5
175°	1420.6	1418.7	1418.5	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0
177.5°	1423.7	1422.3	1422.1	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1002.8	1007.5	1010.6	1016.4	1021.1	1023.9	1026.2	1028.3	1030.6	1032.7	1038.4
5°	1009.3	1020.3	1029.6	1044.0	1057.1	1067.2	1078.2	1088.0	1096.1	1107.5	1116.4
7.5°	1006.5	1026.1	1046.5	1068.8	1091.5	1112.7	1132.2	1150.4	1166.9	1186.9	1204.4
10°	1003.8	1030.5	1056.7	1086.7	1117.6	1143.9	1168.4	1193.4	1211.6	1237.1	1258.6
12.5°	1001.8	1033.1	1064.8	1101.0	1134.9	1172.0	1204.7	1222.9	1250.6	1270.9	1296.6
15°	993.2	1034.7	1078.2	1118.9	1167.2	1201.4	1230.3	1265.8	1291.6	1317.4	1345.4
17.5°	977.9	1024.8	1073.6	1126.9	1173.2	1210.0	1247.1	1281.4	1312.2	1346.9	1381.6
20°	970.8	1017.7	1073.6	1128.2	1173.5	1212.0	1250.2	1287.8	1321.7	1366.1	1406.4
22.5°	955.9	1012.7	1064.1	1117.4	1164.0	1206.0	1249.1	1291.9	1336.9	1387.2	1437.5
25°	929.3	986.8	1041.5	1094.0	1140.9	1193.4	1239.6	1296.7	1354.3	1420.7	1483.4
27.5°	901.6	956.8	1006.8	1057.5	1112.3	1171.7	1231.6	1296.5	1371.8	1455.7	1544.1
30°	879.3	931.4	980.1	1032.1	1089.2	1156.2	1221.8	1298.9	1386.0	1480.4	1585.4
32.5°	853.2	901.2	948.5	1003.7	1065.9	1136.5	1213.0	1297.5	1402.3	1509.6	1617.6
35°	808.6	848.8	897.5	956.3	1026.6	1107.5	1196.0	1295.8	1416.1	1539.3	1630.4
37.5°	755.7	793.1	844.4	908.9	982.6	1069.3	1174.4	1292.9	1420.6	1518.8	1548.2
40°	720.2	754.8	808.2	875.1	950.4	1042.3	1157.4	1282.7	1406.4	1469.0	1444.9
42.5°	682.2	718.6	770.5	836.8	917.9	1017.9	1136.1	1261.4	1365.1	1388.8	1305.4
45°	622.3	660.0	711.2	778.1	865.4	973.7	1096.9	1210.8	1270.5	1227.7	1098.6
47.5°	566.7	602.0	649.5	718.5	808.5	920.6	1039.3	1130.1	1134.8	1032.8	894.9
50°	528.8	561.3	609.2	678.2	767.5	881.0	988.1	1059.6	1027.4	911.9	779.3
52.5°	491.5	523.4	570.6	639.0	727.2	831.2	930.8	981.0	920.5	801.8	688.6
55°	437.7	465.7	511.8	574.9	658.8	755.3	839.9	857.3	778.5	661.7	569.8
57.5°	385.2	411.3	453.3	511.4	588.0	673.5	739.7	736.1	652.8	552.5	479.6
60°	349.7	375.1	412.4	469.0	538.9	612.6	669.3	655.7	573.2	486.8	425.5
62.5°	317.9	340.6	375.8	425.3	489.1	557.4	604.0	584.0	503.1	427.5	379.0
65°	270.9	290.0	320.1	362.4	415.3	471.7	507.6	481.8	412.8	353.9	315.0
67.5°	226.2	241.4	266.6	300.4	345.5	390.8	412.7	386.7	331.5	288.5	259.7
70°	197.7	211.2	230.7	260.8	300.2	338.3	354.7	331.5	284.1	247.2	226.5
72.5°	169.3	180.4	197.5	224.5	256.1	289.2	303.6	281.4	242.4	211.3	191.9
75°	130.9	138.4	150.3	168.9	193.9	220.1	228.2	208.7	183.8	160.5	147.7
77.5°	93.7	100.1	109.1	120.8	138.5	155.2	162.2	151.0	131.7	116.9	106.5
80°	72.0	75.3	83.0	92.7	106.7	117.2	121.9	114.7	101.2	90.2	82.1
82.5°	51.3	54.7	59.3	67.3	76.2	83.4	88.4	83.6	73.8	65.1	60.4
85°	24.9	27.1	29.6	33.0	39.8	44.0	43.6	40.6	36.9	33.4	30.9
87.5°	9.4	10.1	11.5	13.5	14.9	16.6	17.6	17.3	16.2	15.5	14.7
90°	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2
92.5°	14.9	13.6	12.3	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2
95°	59.4	58.8	58.0	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2
97.5°	126.9	128.2	129.4	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7
100°	177.0	177.7	178.4	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7
102.5°	228.7	229.6	230.5	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1
105°	311.3	312.3	313.2	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.1	396.1	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3
110°	451.8	451.8	451.8	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5





TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	504.8	505.3	505.8	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1
115°	583.8	585.1	586.2	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2
117.5°	663.9	663.9	663.8	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4
120°	714.4	714.2	714.0	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8
122.5°	760.3	761.2	762.1	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9
125°	830.3	831.9	833.6	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1
127.5°	895.9	897.1	898.2	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4
130°	936.5	937.6	938.8	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2
132.5°	977.1	978.5	979.9	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3
135°	1034.9	1036.2	1037.6	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7
137.5°	1087.6	1088.8	1090.1	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2
140°	1121.5	1122.0	1122.4	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1
142.5°	1152.6	1152.8	1153.2	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2
145°	1198.6	1199.1	1199.5	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7
147.5°	1238.1	1238.0	1238.0	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7
150°	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5
152.5°	1287.0	1286.0	1285.0	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5
155°	1318.1	1316.7	1315.3	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7
157.5°	1343.0	1342.1	1341.2	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7
160°	1359.3	1357.9	1356.4	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3
162.5°	1372.8	1371.3	1369.9	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5
165°	1390.9	1389.5	1388.1	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8
167.5°	1404.4	1403.0	1401.5	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8
170°	1411.9	1410.1	1408.5	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9
172.5°	1416.9	1415.3	1413.6	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4
175°	1422.6	1421.2	1419.8	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5
177.5°	1425.4	1424.3	1423.2	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	997.4	997.4	997.4	997.4	997.4	997.4	997.4
2.5°	1043.1	1045.9	1051.6	1049.5	1052.3	1053.6	1055.0
5°	1127.4	1140.9	1146.9	1146.0	1154.9	1152.8	1150.6
7.5°	1222.5	1236.8	1244.7	1254.7	1260.4	1260.8	1265.8
10°	1276.4	1295.0	1302.7	1313.2	1320.0	1323.8	1323.4
12.5°	1317.7	1332.3	1349.4	1354.5	1363.7	1368.5	1366.8
15°	1367.4	1390.7	1408.5	1417.4	1428.8	1432.2	1436.9
17.5°	1411.8	1443.0	1463.8	1491.3	1501.8	1508.1	1504.4
20°	1445.3	1486.4	1507.2	1540.2	1558.4	1568.1	1564.7
22.5°	1484.9	1529.4	1567.7	1596.4	1624.1	1637.2	1639.9
25°	1552.8	1613.8	1670.1	1707.8	1742.1	1750.1	1767.9
27.5°	1628.7	1700.6	1760.8	1800.4	1824.3	1833.3	1838.8
30°	1676.5	1748.0	1793.3	1818.7	1826.4	1825.5	1824.6
32.5°	1699.8	1744.7	1753.3	1746.2	1728.8	1714.1	1698.7
35°	1666.7	1633.3	1583.3	1519.0	1471.5	1423.8	1419.0
37.5°	1499.0	1392.0	1308.9	1216.0	1162.5	1129.4	1106.4
40°	1341.2	1219.7	1118.9	1040.6	985.9	964.4	943.2
42.5°	1169.8	1053.7	964.5	899.0	857.9	834.0	817.3
45°	950.4	848.0	778.1	730.7	698.1	679.5	668.9
47.5°	778.8	703.0	643.7	609.4	586.9	572.4	572.5
50°	686.6	614.2	574.9	547.8	528.3	516.9	519.0
52.5°	605.0	551.0	517.3	494.6	480.2	473.2	473.0
55°	505.9	466.9	444.9	428.4	418.7	410.7	412.4
57.5°	432.8	399.9	385.1	371.5	364.7	361.4	356.8
60°	387.3	362.0	349.3	338.3	331.5	329.0	324.2
62.5°	347.1	327.1	314.7	305.7	299.6	298.8	295.1
65°	291.7	276.5	265.5	261.2	254.9	253.2	253.2
67.5°	240.4	229.5	221.0	217.1	214.3	214.7	212.7
70°	208.3	199.4	193.9	189.6	187.5	187.9	186.3
72.5°	182.2	172.3	167.5	164.9	162.2	163.2	162.6
75°	138.0	132.9	130.4	127.8	126.1	125.3	124.5
77.5°	101.3	96.9	94.9	93.5	93.8	91.7	93.3
80°	78.4	74.5	73.2	71.1	70.7	70.7	70.3
82.5°	57.3	55.2	54.3	52.5	51.8	52.4	51.3
85°	29.6	28.0	27.6	27.6	26.7	25.8	28.0
87.5°	14.9	13.8	14.0	13.8	13.9	13.7	13.2
90°	20.4	21.6	22.5	23.2	23.9	24.6	25.4
92.5°	20.4	21.6	22.3	22.7	23.0	23.3	23.6
95°	20.4	21.6	22.2	22.2	22.2	22.2	22.2
97.5°	32.1	25.4	22.2	22.2	22.2	22.2	22.2
100°	78.8	43.9	25.9	24.9	24.1	23.1	22.2
102.5°	214.5	207.9	196.6	180.7	164.7	148.7	132.8
105°	314.5	314.5	314.5	314.2	314.0	313.7	313.5
107.5°	398.4	398.4	398.0	397.3	396.6	395.9	395.3
110°	451.8	451.1	450.9	451.1	451.3	451.6	451.8



TEST NUMBER: P333418-930

CATALOG NUMBER: S125DIW-S850D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	505.3	504.4	503.8	503.4	503.1	502.8	502.5
115°	586.2	585.3	584.1	582.7	581.3	579.8	578.5
117.5°	664.1	662.9	661.9	661.4	660.8	660.1	659.6
120°	715.3	714.9	714.0	712.9	711.7	710.5	709.4
122.5°	763.4	763.0	762.1	760.8	759.4	758.0	756.7
125°	833.2	832.3	831.4	830.8	830.1	829.3	828.7
127.5°	897.8	897.3	896.2	894.5	892.8	891.0	889.2
130°	939.5	938.8	937.8	936.7	935.5	934.3	933.2
132.5°	979.2	979.0	978.4	977.2	976.1	974.9	973.7
135°	1036.2	1035.8	1034.9	1033.5	1032.0	1030.6	1029.2
137.5°	1090.3	1090.4	1089.8	1088.6	1087.4	1086.1	1084.9
140°	1123.5	1124.0	1123.5	1122.1	1120.7	1119.3	1117.9
142.5°	1155.4	1155.4	1154.8	1153.3	1151.9	1150.6	1149.2
145°	1200.9	1201.2	1200.6	1199.1	1197.8	1196.4	1195.0
147.5°	1239.9	1240.2	1239.5	1237.8	1236.1	1234.4	1232.7
150°	1264.9	1265.4	1264.7	1262.8	1260.9	1259.1	1257.2
152.5°	1286.9	1287.4	1286.8	1285.1	1283.4	1281.7	1280.0
155°	1317.4	1318.1	1317.5	1315.6	1313.8	1311.9	1310.0
157.5°	1342.5	1343.2	1342.6	1340.8	1338.9	1337.0	1335.1
160°	1358.2	1359.2	1358.7	1356.8	1354.9	1353.1	1351.2
162.5°	1372.9	1374.2	1373.8	1371.7	1369.6	1367.6	1365.5
165°	1391.3	1392.7	1392.4	1390.6	1388.7	1386.8	1384.9
167.5°	1405.4	1407.1	1406.9	1404.8	1402.7	1400.6	1398.5
170°	1412.8	1414.6	1414.5	1412.4	1410.3	1408.2	1406.1
172.5°	1418.1	1419.8	1419.6	1417.5	1415.4	1413.2	1411.1
175°	1424.3	1426.2	1426.1	1424.0	1421.9	1419.8	1417.6
177.5°	1426.3	1427.6	1427.5	1426.0	1424.5	1422.9	1421.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0

(END OF REPORT)