

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333410-930

Luminaire Tested: **S125DIW-S850D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333410-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D770U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5289.3 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53
1	98	94	90	86	91	87	84	81	74	72	70	63	61	59	52	50	49	44
2	89	82	76	71	83	76	71	66	65	61	58	55	52	49	45	43	41	37
3	82	72	65	59	75	67	60	55	57	52	48	48	45	42	40	38	35	31
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	30	27
5	69	57	49	43	63	53	46	40	46	40	36	39	34	31	32	29	26	23
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	29	26	23	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	27	23	21	18
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19	16
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17	15
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6912	6912	6912
5°	6928	6862	6906
10°	6885	6813	6852
15°	6811	6731	6760
20°	6704	6616	6628
25°	6589	6480	6475
30°	6447	6334	6302
35°	6296	6176	6089
40°	6139	6004	5918
45°	5971	5847	5731
50°	5785	5657	5488
55°	5606	5444	5291
60°	5391	5227	5043
65°	5136	4968	4800
70°	4893	4670	4509
75°	4457	4312	4162
80°	3968	3905	3812
85°	3453	3520	3320



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.9
10°-20°	285.1	5.4
20°-30°	420.9	8.0
30°-40°	491.1	9.3
40°-50°	493.3	9.3
50°-60°	433.0	8.2
60°-70°	322.6	6.1
70°-80°	184.5	3.5
80°-90°	55.4	1.0
90°-100°	29.6	0.6
100°-110°	182.5	3.5
110°-120°	331.0	6.3
120°-130°	424.8	8.0
130°-140°	456.9	8.6
140°-150°	428.9	8.1
150°-160°	346.9	6.6
160°-170°	224.4	4.2
170°-180°	77.4	1.5
0°-30°	806.9	15.3
0°-40°	1298.0	24.5
0°-60°	2224.3	42.1
0°-90°	2786.8	52.7
90°-120°	543.2	10.3
90°-150°	1853.8	35.0
90°-180°	2503.0	47.3
0°-180°	5289.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1069	1066	1058	1066	1065	101
15°	1019	1016	1007	1011	1011	287
25°	925	920	909	911	909	425
35°	798	795	783	779	772	499
45°	654	650	640	630	628	504
55°	498	495	484	476	470	444
65°	336	334	325	318	314	333
75°	179	177	173	170	167	190
85°	47	47	48	46	45	52
90°	1	5	10	13	14	4
95°	34	32	10	12	13	44
105°	178	180	180	180	179	188
115°	334	336	337	335	331	330
125°	474	478	478	476	474	423
135°	591	595	594	592	589	456
145°	686	687	687	687	684	429
155°	755	752	753	754	750	348
165°	797	793	794	797	793	225
175°	815	812	812	816	811	78
180°	815	815	815	815	815	



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1073.0	1072.5	1072.1	1071.6	1071.1	1070.2	1068.7	1067.2	1065.7	1064.2	1065.7
5°	1068.6	1068.2	1067.8	1067.5	1067.1	1065.9	1064.0	1062.2	1060.3	1058.4	1060.1
7.5°	1058.7	1058.4	1058.0	1057.6	1057.3	1056.1	1053.9	1051.9	1049.9	1047.7	1049.4
10°	1049.9	1049.6	1049.2	1048.8	1048.5	1047.3	1045.1	1043.1	1041.1	1038.9	1040.5
12.5°	1039.1	1038.4	1037.8	1037.1	1036.4	1035.1	1033.2	1031.3	1029.3	1027.4	1028.7
15°	1018.6	1018.1	1017.5	1016.9	1016.4	1015.0	1013.0	1010.9	1008.9	1006.7	1007.7
17.5°	995.1	994.3	993.4	992.6	991.8	990.3	988.1	986.0	983.8	981.7	982.8
20°	975.4	975.1	974.7	974.3	974.0	972.5	970.0	967.6	965.2	962.7	964.1
22.5°	955.8	955.1	954.5	953.7	953.1	951.6	949.3	947.0	944.7	942.4	943.3
25°	924.6	923.7	922.8	921.8	920.9	919.2	916.7	914.3	911.8	909.4	909.8
27.5°	888.2	887.7	887.1	886.6	886.0	884.4	881.9	879.4	876.9	874.3	874.4
30°	864.5	864.0	863.4	862.8	862.3	860.5	857.8	854.9	852.1	849.3	848.9
32.5°	838.8	837.9	837.1	836.2	835.4	833.6	831.1	828.6	826.1	823.5	822.9
35°	798.5	797.7	797.0	796.2	795.5	793.8	791.2	788.5	785.9	783.3	782.3
37.5°	756.7	755.7	754.7	753.8	752.8	751.1	748.7	746.2	743.7	741.3	739.8
40°	728.2	727.2	726.4	725.4	724.4	722.7	720.0	717.4	714.8	712.1	710.5
42.5°	697.7	696.9	696.1	695.4	694.6	692.8	690.2	687.5	684.9	682.3	680.8
45°	653.7	652.9	652.2	651.4	650.7	649.1	646.9	644.7	642.4	640.2	637.9
47.5°	606.3	606.3	606.3	606.3	606.4	605.1	602.3	599.7	597.0	594.3	591.9
50°	575.8	575.2	574.6	574.1	573.6	572.1	569.9	567.6	565.3	563.0	560.6
52.5°	544.6	544.2	543.8	543.4	543.0	541.5	539.2	536.7	534.3	531.9	529.8
55°	497.9	497.3	496.8	496.2	495.6	494.0	491.4	488.8	486.1	483.5	481.8
57.5°	448.6	448.3	448.0	447.7	447.4	446.1	443.9	441.7	439.4	437.2	435.0
60°	417.4	416.7	416.0	415.2	414.4	413.0	410.9	408.9	406.8	404.7	402.8
62.5°	384.9	384.3	383.8	383.1	382.5	381.3	379.6	377.8	376.0	374.2	372.3
65°	336.1	335.7	335.4	335.0	334.7	333.5	331.3	329.3	327.2	325.1	323.4
67.5°	288.9	288.1	287.3	286.5	285.8	284.5	283.1	281.5	280.0	278.4	277.0
70°	259.1	258.1	257.2	256.2	255.4	254.0	252.3	250.6	248.9	247.3	246.1
72.5°	226.6	225.9	225.3	224.7	224.0	223.1	222.1	220.9	219.9	218.8	217.5
75°	178.6	178.3	177.9	177.6	177.2	176.5	175.5	174.6	173.7	172.8	172.2
77.5°	134.4	134.3	134.2	134.0	133.9	133.5	133.0	132.5	131.9	131.4	131.1
80°	106.7	106.7	106.7	106.7	106.7	106.5	106.2	105.7	105.3	105.0	104.8
82.5°	82.3	82.0	81.7	81.4	81.1	80.9	80.8	80.8	80.7	80.6	80.3
85°	46.6	46.8	47.0	47.1	47.3	47.5	47.5	47.5	47.5	47.5	47.2
87.5°	18.4	18.6	18.8	19.1	19.2	19.4	19.4	19.5	19.5	19.6	19.6
90°	0.6	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4
92.5°	9.3	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4
95°	34.4	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4
97.5°	71.9	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9
100°	100.9	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1
102.5°	130.4	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4
105°	177.6	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9
110°	258.5	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.5	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2
115°	333.5	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6
117.5°	380.0	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5
120°	409.0	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9
122.5°	434.6	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5
125°	474.3	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9
127.5°	512.0	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4
130°	535.2	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4
132.5°	558.4	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5
135°	591.4	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5
137.5°	621.7	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9
140°	641.6	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5
142.5°	659.4	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0
145°	685.7	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0
147.5°	708.7	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2
150°	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4
152.5°	737.1	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0
155°	755.1	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1
157.5°	769.0	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4
160°	778.7	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2
162.5°	786.4	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2
165°	796.8	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6
167.5°	804.5	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3
170°	808.9	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3
172.5°	811.8	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6
175°	815.0	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0
177.5°	816.4	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1067.2	1068.7	1070.2	1070.9	1070.7	1070.6	1070.4	1070.2
5°	1061.8	1063.5	1065.2	1065.9	1065.8	1065.6	1065.4	1065.2
7.5°	1051.1	1052.7	1054.3	1055.1	1054.9	1054.8	1054.5	1054.3
10°	1042.0	1043.5	1045.0	1045.6	1045.5	1045.2	1045.1	1044.9
12.5°	1029.8	1031.0	1032.3	1032.8	1032.8	1032.7	1032.7	1032.7
15°	1008.7	1009.6	1010.6	1011.0	1011.0	1011.0	1011.0	1011.0
17.5°	984.1	985.2	986.3	986.5	985.5	984.6	983.7	982.8
20°	965.4	966.7	968.0	968.2	967.3	966.3	965.4	964.4
22.5°	944.1	945.0	945.9	946.0	945.3	944.7	944.0	943.5
25°	910.1	910.5	910.9	910.8	910.3	909.7	909.1	908.6
27.5°	874.5	874.6	874.7	874.4	873.8	873.3	872.7	872.1
30°	848.6	848.2	847.7	847.3	846.8	846.2	845.6	845.1
32.5°	822.1	821.5	820.8	819.9	819.0	817.9	816.9	816.0
35°	781.4	780.4	779.5	778.3	776.7	775.3	773.7	772.3
37.5°	738.4	737.0	735.6	734.5	733.7	732.8	732.0	731.1
40°	708.7	707.0	705.3	704.2	703.6	703.1	702.5	702.0
42.5°	679.2	677.7	676.1	674.9	674.1	673.2	672.3	671.5
45°	635.6	633.3	631.1	629.7	629.2	628.6	628.0	627.5
47.5°	589.6	587.3	585.1	583.3	582.0	580.7	579.3	578.0
50°	558.2	555.7	553.3	551.4	550.1	548.8	547.5	546.2
52.5°	527.7	525.5	523.3	521.5	520.1	518.6	517.1	515.7
55°	480.1	478.4	476.7	475.2	473.9	472.5	471.2	469.9
57.5°	432.9	430.7	428.5	427.1	426.3	425.7	424.9	424.2
60°	401.0	399.1	397.2	395.6	394.3	393.0	391.7	390.4
62.5°	370.2	368.2	366.2	364.6	363.6	362.6	361.6	360.5
65°	321.8	320.1	318.4	317.2	316.4	315.7	314.9	314.1
67.5°	275.6	274.1	272.7	271.7	271.3	270.8	270.4	269.9
70°	245.0	243.9	242.7	241.8	241.0	240.3	239.5	238.8
72.5°	216.2	215.0	213.7	212.6	211.9	211.2	210.4	209.6
75°	171.6	171.0	170.5	169.8	169.1	168.3	167.5	166.8
77.5°	130.8	130.4	130.0	129.6	129.1	128.6	128.1	127.5
80°	104.6	104.4	104.3	104.0	103.6	103.2	102.8	102.5
82.5°	79.9	79.6	79.2	79.1	79.0	78.9	78.8	78.8
85°	47.0	46.9	46.6	46.4	46.0	45.7	45.2	44.8
87.5°	19.8	20.0	20.1	20.1	19.8	19.6	19.4	19.2
90°	11.0	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.0	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.0	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	22.2	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	65.1	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	126.5	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.9	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333410-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	289.7	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	336.0	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.7	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.7	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	437.2	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	477.4	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	514.1	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	538.1	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.3	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.7	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.1	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.1	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.4	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.7	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.2	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.5	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	767.8	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	776.7	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	784.9	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	795.4	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	803.3	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	807.4	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	810.6	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	814.1	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	815.5	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)