

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333411-930

Luminaire Tested: **S125DIW-S850D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333411-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D770U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4956.9 lumens
Efficiency: N/A
Efficacy: 110.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 45
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6912	6912	6912
5°	6928	6862	6906
10°	6885	6813	6852
15°	6811	6731	6760
20°	6704	6616	6628
25°	6589	6480	6475
30°	6447	6334	6302
35°	6296	6176	6089
40°	6139	6004	5918
45°	5971	5847	5731
50°	5785	5657	5488
55°	5606	5444	5291
60°	5391	5227	5043
65°	5136	4968	4800
70°	4893	4670	4509
75°	4457	4312	4162
80°	3968	3905	3812
85°	3453	3520	3320



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	2.0
10°-20°	285.1	5.8
20°-30°	420.9	8.5
30°-40°	491.1	9.9
40°-50°	493.3	10.0
50°-60°	433.0	8.7
60°-70°	322.6	6.5
70°-80°	184.5	3.7
80°-90°	55.4	1.1
90°-100°	52.1	1.1
100°-110°	153.8	3.1
110°-120°	260.5	5.3
120°-130°	342.9	6.9
130°-140°	384.2	7.8
140°-150°	376.6	7.6
150°-160°	316.3	6.4
160°-170°	210.2	4.2
170°-180°	73.6	1.5
0°-30°	806.9	16.3
0°-40°	1298.0	26.2
0°-60°	2224.3	44.9
0°-90°	2786.8	56.2
90°-120°	466.4	9.4
90°-150°	1570.1	31.7
90°-180°	2170.0	43.8
0°-180°	4956.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1070	1070	1070	1070	1070	
5°	1069	1066	1058	1066	1065	101
15°	1019	1016	1007	1011	1011	287
25°	925	920	909	911	909	425
35°	798	795	783	779	772	499
45°	654	650	640	630	628	504
55°	498	495	484	476	470	444
65°	336	334	325	318	314	333
75°	179	177	173	170	167	190
85°	47	47	48	46	45	52
90°	1	5	10	13	14	5
95°	39	41	47	51	52	42
105°	138	141	145	148	150	147
115°	261	263	264	264	263	258
125°	381	384	385	384	383	341
135°	495	499	499	499	497	381
145°	600	602	604	604	602	375
155°	686	686	687	689	686	316
165°	746	745	746	748	744	210
175°	776	774	774	777	773	74
180°	778	778	778	778	778	



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1073.0	1072.5	1072.1	1071.6	1071.1	1070.2	1068.7	1067.2	1065.7	1064.2	1065.7
5°	1068.6	1068.2	1067.8	1067.5	1067.1	1065.9	1064.0	1062.2	1060.3	1058.4	1060.1
7.5°	1058.7	1058.4	1058.0	1057.6	1057.3	1056.1	1053.9	1051.9	1049.9	1047.7	1049.4
10°	1049.9	1049.6	1049.2	1048.8	1048.5	1047.3	1045.1	1043.1	1041.1	1038.9	1040.5
12.5°	1039.1	1038.4	1037.8	1037.1	1036.4	1035.1	1033.2	1031.3	1029.3	1027.4	1028.7
15°	1018.6	1018.1	1017.5	1016.9	1016.4	1015.0	1013.0	1010.9	1008.9	1006.7	1007.7
17.5°	995.1	994.3	993.4	992.6	991.8	990.3	988.1	986.0	983.8	981.7	982.8
20°	975.4	975.1	974.7	974.3	974.0	972.5	970.0	967.6	965.2	962.7	964.1
22.5°	955.8	955.1	954.5	953.7	953.1	951.6	949.3	947.0	944.7	942.4	943.3
25°	924.6	923.7	922.8	921.8	920.9	919.2	916.7	914.3	911.8	909.4	909.8
27.5°	888.2	887.7	887.1	886.6	886.0	884.4	881.9	879.4	876.9	874.3	874.4
30°	864.5	864.0	863.4	862.8	862.3	860.5	857.8	854.9	852.1	849.3	848.9
32.5°	838.8	837.9	837.1	836.2	835.4	833.6	831.1	828.6	826.1	823.5	822.9
35°	798.5	797.7	797.0	796.2	795.5	793.8	791.2	788.5	785.9	783.3	782.3
37.5°	756.7	755.7	754.7	753.8	752.8	751.1	748.7	746.2	743.7	741.3	739.8
40°	728.2	727.2	726.4	725.4	724.4	722.7	720.0	717.4	714.8	712.1	710.5
42.5°	697.7	696.9	696.1	695.4	694.6	692.8	690.2	687.5	684.9	682.3	680.8
45°	653.7	652.9	652.2	651.4	650.7	649.1	646.9	644.7	642.4	640.2	637.9
47.5°	606.3	606.3	606.3	606.3	606.4	605.1	602.3	599.7	597.0	594.3	591.9
50°	575.8	575.2	574.6	574.1	573.6	572.1	569.9	567.6	565.3	563.0	560.6
52.5°	544.6	544.2	543.8	543.4	543.0	541.5	539.2	536.7	534.3	531.9	529.8
55°	497.9	497.3	496.8	496.2	495.6	494.0	491.4	488.8	486.1	483.5	481.8
57.5°	448.6	448.3	448.0	447.7	447.4	446.1	443.9	441.7	439.4	437.2	435.0
60°	417.4	416.7	416.0	415.2	414.4	413.0	410.9	408.9	406.8	404.7	402.8
62.5°	384.9	384.3	383.8	383.1	382.5	381.3	379.6	377.8	376.0	374.2	372.3
65°	336.1	335.7	335.4	335.0	334.7	333.5	331.3	329.3	327.2	325.1	323.4
67.5°	288.9	288.1	287.3	286.5	285.8	284.5	283.1	281.5	280.0	278.4	277.0
70°	259.1	258.1	257.2	256.2	255.4	254.0	252.3	250.6	248.9	247.3	246.1
72.5°	226.6	225.9	225.3	224.7	224.0	223.1	222.1	220.9	219.9	218.8	217.5
75°	178.6	178.3	177.9	177.6	177.2	176.5	175.5	174.6	173.7	172.8	172.2
77.5°	134.4	134.3	134.2	134.0	133.9	133.5	133.0	132.5	131.9	131.4	131.1
80°	106.7	106.7	106.7	106.7	106.7	106.5	106.2	105.7	105.3	105.0	104.8
82.5°	82.3	82.0	81.7	81.4	81.1	80.9	80.8	80.8	80.7	80.6	80.3
85°	46.6	46.8	47.0	47.1	47.3	47.5	47.5	47.5	47.5	47.5	47.2
87.5°	18.4	18.6	18.8	19.1	19.2	19.4	19.4	19.5	19.5	19.6	19.6
90°	0.6	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4
92.5°	14.7	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1
95°	39.4	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5
97.5°	65.4	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1
100°	84.7	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8
102.5°	105.6	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3
105°	138.0	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4
107.5°	173.8	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0
110°	198.5	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	223.7	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8
115°	260.9	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3
117.5°	298.2	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4
120°	321.4	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0
122.5°	346.6	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1
125°	380.7	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7
127.5°	417.0	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6
130°	438.8	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9
132.5°	460.6	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2
135°	495.0	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3
137.5°	527.5	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6
140°	548.4	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4
142.5°	569.2	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1
145°	599.8	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1
147.5°	628.1	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2
150°	647.0	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8
152.5°	662.5	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6
155°	686.3	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5
157.5°	707.7	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4
160°	720.2	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6
162.5°	731.4	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8
165°	746.2	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2
167.5°	758.9	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2
170°	765.6	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0
172.5°	770.5	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8
175°	775.9	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3
177.5°	778.7	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2	1070.2
2.5°	1067.2	1068.7	1070.2	1070.9	1070.7	1070.6	1070.4	1070.2
5°	1061.8	1063.5	1065.2	1065.9	1065.8	1065.6	1065.4	1065.2
7.5°	1051.1	1052.7	1054.3	1055.1	1054.9	1054.8	1054.5	1054.3
10°	1042.0	1043.5	1045.0	1045.6	1045.5	1045.2	1045.1	1044.9
12.5°	1029.8	1031.0	1032.3	1032.8	1032.8	1032.7	1032.7	1032.7
15°	1008.7	1009.6	1010.6	1011.0	1011.0	1011.0	1011.0	1011.0
17.5°	984.1	985.2	986.3	986.5	985.5	984.6	983.7	982.8
20°	965.4	966.7	968.0	968.2	967.3	966.3	965.4	964.4
22.5°	944.1	945.0	945.9	946.0	945.3	944.7	944.0	943.5
25°	910.1	910.5	910.9	910.8	910.3	909.7	909.1	908.6
27.5°	874.5	874.6	874.7	874.4	873.8	873.3	872.7	872.1
30°	848.6	848.2	847.7	847.3	846.8	846.2	845.6	845.1
32.5°	822.1	821.5	820.8	819.9	819.0	817.9	816.9	816.0
35°	781.4	780.4	779.5	778.3	776.7	775.3	773.7	772.3
37.5°	738.4	737.0	735.6	734.5	733.7	732.8	732.0	731.1
40°	708.7	707.0	705.3	704.2	703.6	703.1	702.5	702.0
42.5°	679.2	677.7	676.1	674.9	674.1	673.2	672.3	671.5
45°	635.6	633.3	631.1	629.7	629.2	628.6	628.0	627.5
47.5°	589.6	587.3	585.1	583.3	582.0	580.7	579.3	578.0
50°	558.2	555.7	553.3	551.4	550.1	548.8	547.5	546.2
52.5°	527.7	525.5	523.3	521.5	520.1	518.6	517.1	515.7
55°	480.1	478.4	476.7	475.2	473.9	472.5	471.2	469.9
57.5°	432.9	430.7	428.5	427.1	426.3	425.7	424.9	424.2
60°	401.0	399.1	397.2	395.6	394.3	393.0	391.7	390.4
62.5°	370.2	368.2	366.2	364.6	363.6	362.6	361.6	360.5
65°	321.8	320.1	318.4	317.2	316.4	315.7	314.9	314.1
67.5°	275.6	274.1	272.7	271.7	271.3	270.8	270.4	269.9
70°	245.0	243.9	242.7	241.8	241.0	240.3	239.5	238.8
72.5°	216.2	215.0	213.7	212.6	211.9	211.2	210.4	209.6
75°	171.6	171.0	170.5	169.8	169.1	168.3	167.5	166.8
77.5°	130.8	130.4	130.0	129.6	129.1	128.6	128.1	127.5
80°	104.6	104.4	104.3	104.0	103.6	103.2	102.8	102.5
82.5°	79.9	79.6	79.2	79.1	79.0	78.9	78.8	78.8
85°	47.0	46.9	46.6	46.4	46.0	45.7	45.2	44.8
87.5°	19.8	20.0	20.1	20.1	19.8	19.6	19.4	19.2
90°	11.0	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.0	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	48.5	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.0	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	95.0	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	114.6	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	146.3	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.4	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.2	204.6	205.0	205.1	205.0	204.8	204.7	204.6



TEST NUMBER: P333411-930

CATALOG NUMBER: S125DIW-S850D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.0	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.2	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.5	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	349.0	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.4	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.6	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.8	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	465.0	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.7	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	553.8	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.3	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.5	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.0	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.0	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.0	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.1	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	731.5	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	746.7	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.1	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	764.8	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	769.6	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.1	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	777.6	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)