

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333717-930

Luminaire Tested: **S125RDIW-S1090D1560U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333717-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7885.4 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44
1	97	93	89	86	89	85	82	79	71	68	66	58	56	55	45	44	44	38
2	88	81	75	71	81	75	70	65	62	59	56	51	48	46	40	39	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	52	45	40	44	39	35	36	33	30	29	27	24	21
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	22	19
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	16
8	54	42	34	29	49	39	32	27	33	28	24	27	23	21	22	19	17	15
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8657	8657	8657	8657
5°	9961	8669	7656	8669
10°	11425	8625	6755	8625
15°	12341	8536	6005	8536
20°	13608	8434	5544	8434
25°	15748	8298	5144	8298
30°	17137	8154	4883	8154
35°	14456	7987	4642	7987
40°	10095	7687	4435	7687
45°	7489	7283	4232	7283
50°	5971	6861	4058	6861
55°	5068	6339	3904	6339
60°	4379	5871	3653	5871
65°	3903	5365	3145	5365
70°	3429	4913	2868	4913
75°	2967	4257	2692	4257
80°	2250	3582	2250	3582
85°	1875	2816	2119	2816



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.5	1.6
10°-20°	376.7	4.8
20°-30°	597.3	7.6
30°-40°	720.3	9.1
40°-50°	643.2	8.2
50°-60°	493.3	6.3
60°-70°	320.6	4.1
70°-80°	155.9	2.0
80°-90°	40.7	0.5
90°-100°	105.8	1.3
100°-110°	312.5	4.0
110°-120°	529.3	6.7
120°-130°	696.6	8.8
130°-140°	780.6	9.9
140°-150°	765.0	9.7
150°-160°	642.6	8.1
160°-170°	427.1	5.4
170°-180°	149.5	1.9
0°-30°	1102.6	14.0
0°-40°	1822.8	23.1
0°-60°	2959.4	37.5
0°-90°	3476.4	44.1
90°-120°	947.6	12.0
90°-150°	3189.8	40.5
90°-180°	4409.0	55.9
0°-180°	7885.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1340	1340	1340	1340	1340	
5°	1536	1337	1181	1337	1536	154
15°	1846	1277	898	1277	1846	529
25°	2210	1164	722	1164	2210	1015
35°	1834	1013	589	1013	1834	1108
45°	820	797	463	797	820	654
55°	450	563	347	563	450	408
65°	255	351	206	351	255	254
75°	119	171	108	171	119	127
85°	25	38	29	38	25	30
90°	30	1	30	1	30	18
95°	106	80	106	80	106	108
105°	305	280	305	280	305	323
115°	535	530	535	530	535	529
125°	778	773	778	773	778	695
135°	1010	1006	1010	1006	1010	779
145°	1223	1218	1223	1218	1223	764
155°	1394	1394	1394	1394	1394	642
165°	1512	1516	1512	1516	1512	426
175°	1570	1576	1570	1576	1570	149
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1410.1	1409.2	1411.0	1406.1	1406.6	1399.1	1399.1	1393.3	1385.8	1380.1	1377.4
5°	1536.4	1537.5	1535.3	1527.1	1521.5	1513.3	1503.9	1487.4	1473.7	1460.4	1450.0
7.5°	1666.5	1667.2	1659.9	1657.4	1643.6	1633.5	1612.7	1590.2	1570.3	1545.0	1525.6
10°	1742.2	1741.6	1733.9	1727.9	1715.8	1700.4	1680.0	1653.6	1628.8	1601.3	1574.9
12.5°	1786.2	1784.8	1782.3	1775.0	1763.7	1750.1	1732.8	1706.8	1676.3	1646.3	1615.4
15°	1845.7	1841.8	1834.7	1825.3	1809.3	1793.3	1774.1	1751.0	1721.8	1687.7	1659.1
17.5°	1919.1	1919.3	1908.3	1895.2	1873.6	1845.4	1815.7	1778.4	1738.8	1701.3	1670.8
20°	1979.9	1978.2	1967.2	1942.0	1917.2	1882.0	1847.9	1802.1	1753.7	1704.8	1666.8
22.5°	2067.1	2062.8	2051.3	2018.1	1979.7	1934.4	1882.2	1826.4	1767.8	1712.2	1662.4
25°	2210.0	2206.6	2184.0	2145.5	2091.7	2021.7	1953.5	1877.0	1792.8	1719.6	1659.1
27.5°	2307.6	2304.0	2287.3	2255.3	2205.5	2132.0	2039.6	1937.4	1832.3	1731.6	1644.4
30°	2298.0	2306.2	2304.0	2289.2	2251.8	2185.7	2100.5	1985.4	1860.5	1742.2	1638.2
32.5°	2159.7	2167.1	2186.5	2215.7	2217.9	2191.4	2127.7	2021.5	1892.2	1757.6	1633.4
35°	1833.5	1843.5	1880.9	1939.8	2016.8	2081.1	2094.3	2037.1	1921.0	1776.3	1626.1
37.5°	1409.6	1463.7	1495.3	1557.2	1673.6	1792.0	1905.9	1947.9	1898.4	1768.6	1614.3
40°	1197.4	1210.6	1266.7	1336.6	1434.6	1557.9	1720.2	1837.4	1841.3	1751.0	1595.8
42.5°	1024.8	1041.5	1080.1	1135.9	1219.8	1343.0	1510.7	1665.2	1736.9	1702.6	1571.6
45°	819.9	832.6	860.6	903.6	967.9	1069.8	1213.9	1392.8	1534.7	1590.3	1506.7
47.5°	673.5	680.4	704.8	737.5	785.1	859.3	970.9	1126.2	1296.5	1415.8	1404.1
50°	594.3	602.0	620.7	645.5	685.7	748.4	837.6	966.9	1142.4	1288.2	1317.4
52.5°	532.6	539.1	550.7	574.1	607.3	655.5	727.5	844.5	1002.4	1157.5	1224.9
55°	450.1	454.5	463.9	477.1	503.5	538.2	600.4	681.3	808.9	965.2	1064.2
57.5°	382.1	384.3	390.3	402.5	420.8	446.1	491.0	559.5	651.1	791.8	901.2
60°	339.0	341.2	348.9	357.1	371.5	394.5	429.7	477.6	565.7	681.8	792.4
62.5°	304.6	306.0	309.2	317.5	330.0	347.9	375.6	414.7	484.7	586.7	691.1
65°	255.4	255.8	257.0	263.6	271.3	284.5	302.6	330.2	383.0	460.1	552.4
67.5°	208.0	208.8	212.6	214.9	223.0	229.9	240.6	261.6	298.8	350.7	422.7
70°	181.6	181.1	184.9	187.7	190.4	198.7	205.8	222.9	246.0	285.6	345.6
72.5°	156.9	155.5	157.2	158.2	161.8	167.4	174.6	185.0	202.8	230.2	276.1
75°	118.9	119.4	119.4	120.5	123.3	125.5	127.7	133.1	143.1	161.3	186.0
77.5°	83.4	82.5	84.9	85.2	86.8	89.3	91.2	93.4	97.4	104.8	117.6
80°	60.5	60.5	61.1	62.7	62.2	63.3	66.0	68.2	73.2	77.6	82.0
82.5°	46.5	46.0	46.6	46.9	46.8	47.9	48.8	49.3	51.2	53.4	56.4
85°	25.3	25.3	25.8	25.8	26.4	26.4	27.0	27.0	27.0	27.5	28.0
87.5°	15.6	15.0	14.3	14.2	14.5	15.2	14.4	13.7	13.5	13.2	13.2
90°	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4	21.0	19.6	17.8
92.5°	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8	49.0	47.2	44.8
95°	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5	96.6	94.7	92.0
97.5°	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3	152.5	150.7	147.0
100°	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1	190.6	188.1	184.6
102.5°	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8	230.2	227.5	225.7
105°	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2	295.5	293.9	292.2
107.5°	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6	365.7	364.9	363.7
110°	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8	413.9	413.1	412.3



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1	462.7	462.4	461.3
115°	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8	537.0	537.4	536.8
117.5°	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6	610.3	610.2	609.6
120°	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3	660.3	660.3	660.0
122.5°	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1	709.2	709.5	708.7
125°	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0	781.5	782.0	781.8
127.5°	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3	852.6	852.9	852.6
130°	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5	899.8	900.1	899.5
132.5°	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8	945.0	945.3	945.4
135°	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4	1014.4	1014.4	1014.2
137.5°	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2	1081.9	1081.6	1080.9
140°	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9	1124.4	1123.9	1123.1
142.5°	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8	1166.4	1166.1	1165.1
145°	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1	1227.1	1227.1	1226.3
147.5°	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0	1282.4	1281.7	1281.1
150°	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2	1318.2	1318.2	1317.0
152.5°	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0	1350.3	1349.6	1349.2
155°	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7	1396.7	1395.6	1395.3
157.5°	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4	1437.3	1436.1	1435.9
160°	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0	1461.8	1460.8	1460.5
162.5°	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0	1484.7	1483.4	1483.4
165°	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0	1516.0	1514.9	1514.6
167.5°	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0	1538.4	1536.8	1536.8
170°	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8	1552.2	1550.5	1550.5
172.5°	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7	1562.0	1560.4	1560.4
175°	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8	1573.0	1571.4	1571.4
177.5°	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7	1578.4	1577.1	1577.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1377.4	1374.4	1368.6	1363.3	1356.7	1351.0	1347.1	1342.2	1336.1	1328.6	1322.4
5°	1438.4	1426.3	1410.4	1396.6	1379.0	1365.2	1351.0	1337.2	1323.4	1305.8	1290.4
7.5°	1506.0	1481.0	1456.7	1426.1	1398.4	1373.6	1349.8	1325.8	1302.2	1277.2	1253.1
10°	1547.4	1517.1	1483.5	1445.0	1409.8	1376.2	1345.4	1315.2	1283.3	1255.2	1224.9
12.5°	1586.2	1547.0	1508.6	1460.0	1417.7	1376.7	1337.5	1299.8	1265.7	1229.2	1196.8
15°	1621.1	1582.6	1539.7	1480.3	1421.4	1371.8	1325.6	1276.7	1234.3	1193.5	1157.2
17.5°	1634.7	1594.2	1544.4	1487.3	1422.9	1360.7	1301.1	1247.4	1197.5	1150.1	1109.2
20°	1629.4	1590.3	1539.1	1484.7	1415.8	1351.0	1286.5	1227.1	1171.6	1121.4	1078.0
22.5°	1616.6	1576.2	1526.8	1469.3	1403.9	1335.1	1266.3	1202.9	1144.7	1092.8	1045.5
25°	1597.5	1542.5	1491.8	1435.7	1373.5	1305.3	1234.3	1164.4	1102.2	1049.4	997.7
27.5°	1577.5	1508.9	1444.5	1388.7	1323.0	1262.1	1193.7	1122.0	1056.6	1002.8	949.7
30°	1559.5	1482.5	1411.4	1348.2	1286.0	1228.2	1163.3	1093.4	1026.3	970.7	916.8
32.5°	1537.0	1455.1	1377.1	1304.2	1244.1	1186.8	1128.0	1061.3	995.9	938.6	883.8
35°	1508.9	1404.4	1319.6	1241.9	1175.4	1119.8	1067.0	1013.1	947.6	888.2	834.8
37.5°	1471.9	1353.2	1255.2	1170.7	1100.4	1044.6	1002.9	953.7	893.9	837.0	787.4
40°	1449.4	1316.3	1208.9	1125.4	1051.6	992.7	953.7	911.8	857.4	804.0	754.4
42.5°	1419.5	1282.4	1162.3	1075.1	1000.9	944.3	904.7	868.2	822.6	772.3	719.2
45°	1360.8	1216.7	1090.6	997.1	922.3	866.7	829.8	797.4	762.7	716.5	670.3
47.5°	1284.4	1148.1	1016.3	914.1	840.8	789.2	753.4	727.8	703.0	663.7	618.8
50°	1223.3	1091.8	963.0	864.0	785.8	736.8	703.3	682.9	660.3	624.6	587.2
52.5°	1151.0	1033.6	907.5	806.2	732.5	686.6	654.4	634.1	615.5	586.3	550.6
55°	1037.3	934.4	818.8	726.9	659.3	613.0	582.2	563.0	552.0	527.2	499.1
57.5°	906.0	832.3	730.3	641.7	581.9	536.2	513.6	497.3	484.8	467.3	447.5
60°	814.4	762.7	671.3	587.2	532.1	488.6	468.3	454.5	443.0	428.1	412.7
62.5°	721.5	683.9	604.5	532.1	481.5	445.1	426.0	413.6	400.3	390.3	375.3
65°	597.0	563.5	508.4	451.8	405.0	375.9	362.1	351.1	342.8	331.8	321.4
67.5°	464.5	450.8	412.8	373.7	340.1	314.2	302.3	294.6	284.7	278.1	270.9
70°	383.0	376.4	349.4	323.6	292.2	274.6	263.6	260.2	248.2	241.6	236.6
72.5°	310.8	307.7	292.2	274.3	252.2	236.8	226.6	222.9	215.2	209.9	206.7
75°	213.0	214.1	211.3	199.7	191.5	181.6	172.8	170.6	165.1	160.7	157.9
77.5°	134.7	140.3	140.6	140.0	136.7	130.6	127.0	125.4	119.9	118.3	117.6
80°	92.5	98.5	104.0	103.5	102.3	100.7	97.9	96.3	93.5	91.9	90.8
82.5°	61.6	67.3	71.8	74.8	74.6	73.0	71.1	70.4	69.8	68.6	68.3
85°	29.2	30.2	31.9	35.8	38.5	39.1	38.5	38.0	36.3	36.9	37.4
87.5°	13.3	12.9	13.0	12.6	11.7	13.5	14.3	14.3	13.9	13.5	13.0
90°	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2	3.4	5.6	7.8
92.5°	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8	31.3	32.9	34.3
95°	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9	80.5	81.0	81.5
97.5°	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8	133.0	133.2	133.5
100°	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1	172.1	172.1	172.1
102.5°	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4	215.6	216.6	217.7
105°	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4	281.7	283.1	284.5
107.5°	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1	354.5	355.9	357.3
110°	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3	404.7	406.0	407.4



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4	455.2	455.9	456.6
115°	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9	531.1	532.1	533.2
117.5°	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7	606.2	606.7	607.2
120°	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9	654.3	655.7	657.0
122.5°	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1	704.6	705.1	705.6
125°	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4	775.0	776.7	778.4
127.5°	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2	848.2	849.1	849.9
130°	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4	892.8	894.2	895.5
132.5°	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7	938.0	940.2	942.5
135°	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8	1007.5	1009.1	1010.7
137.5°	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7	1073.3	1074.9	1076.4
140°	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0	1115.4	1116.7	1118.1
142.5°	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3	1157.5	1158.6	1159.8
145°	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5	1219.6	1220.7	1221.8
147.5°	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1	1276.7	1277.2	1277.9
150°	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4	1314.2	1313.9	1313.6
152.5°	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9	1346.3	1346.7	1347.0
155°	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6	1437.0	1436.5	1435.8
160°	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2	1462.4	1461.6	1460.8
162.5°	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9	1485.2	1484.7	1484.1
165°	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1	1515.6	1515.0	1514.5
167.5°	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6	1540.6	1539.5	1538.4
170°	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4	1554.4	1553.2	1552.2
172.5°	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3	1564.2	1563.1	1562.0
175°	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4	1575.2	1574.2	1573.0
177.5°	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0	1581.1	1580.3	1579.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1318.0	1311.9	1307.5	1298.7	1292.5	1289.9	1285.0	1283.7	1288.5	1285.0	1284.6
5°	1278.9	1262.9	1250.3	1237.5	1223.8	1215.0	1201.8	1199.6	1196.3	1191.3	1190.3
7.5°	1231.8	1211.0	1194.7	1173.9	1155.7	1141.1	1124.5	1116.7	1112.5	1106.0	1097.5
10°	1200.1	1175.4	1153.4	1132.5	1109.9	1091.8	1075.2	1062.6	1054.3	1046.6	1043.3
12.5°	1168.9	1143.7	1115.5	1090.2	1065.0	1044.6	1026.4	1018.1	1009.0	1000.0	992.3
15°	1120.4	1086.8	1056.0	1026.8	1005.3	983.3	965.7	953.7	939.9	936.0	921.2
17.5°	1068.9	1035.9	999.9	969.1	944.3	920.1	900.7	887.0	876.6	862.4	855.6
20°	1036.7	997.7	962.5	934.4	906.9	878.2	858.4	846.9	837.0	825.4	819.9
22.5°	1002.4	964.2	928.1	895.2	867.2	839.1	825.0	813.0	801.8	791.1	783.8
25°	951.9	913.5	875.5	841.4	812.2	791.8	775.3	761.6	755.5	745.1	737.4
27.5°	902.1	861.2	821.8	787.7	764.9	744.8	731.2	720.3	709.4	700.3	693.6
30°	870.0	828.2	785.2	758.3	734.1	714.8	699.9	689.5	681.3	673.0	668.1
32.5°	837.9	794.8	756.6	727.5	704.6	687.9	672.6	662.7	654.0	644.8	639.0
35°	786.4	742.3	711.5	682.9	660.3	644.9	634.5	620.2	613.0	606.4	600.4
37.5°	738.5	697.6	664.2	639.1	619.5	604.2	590.7	582.9	574.1	568.2	563.1
40°	703.3	665.9	635.6	609.2	594.8	577.8	565.2	555.2	548.6	541.0	535.4
42.5°	671.6	636.7	607.4	583.6	565.8	551.4	539.2	529.3	520.9	515.4	510.8
45°	626.8	592.1	563.5	541.4	525.0	511.2	498.6	493.6	482.6	476.0	473.8
47.5°	580.4	549.4	521.8	501.5	484.6	471.6	459.7	449.6	443.5	437.0	433.5
50°	549.2	519.4	493.6	473.8	457.3	443.0	431.9	425.3	417.1	411.1	406.7
52.5°	518.0	490.4	464.6	445.6	431.3	417.0	404.7	398.1	390.3	386.4	383.4
55°	473.3	444.1	422.1	403.3	388.5	375.3	363.7	357.1	352.2	348.3	347.2
57.5°	422.7	399.5	379.0	362.2	346.7	334.4	324.2	318.0	313.6	313.0	309.7
60°	389.6	368.7	350.0	331.8	318.6	307.0	298.2	291.1	286.7	286.2	285.0
62.5°	356.6	336.6	319.2	303.2	291.3	280.2	271.8	263.8	261.1	258.4	256.0
65°	307.6	289.4	275.2	262.4	249.8	240.4	232.2	227.3	221.2	217.9	211.9
67.5°	259.5	245.4	231.7	221.0	211.1	202.2	195.3	188.0	183.9	181.2	176.8
70°	227.8	216.8	203.1	191.5	183.8	176.7	171.1	162.9	160.1	157.9	155.7
72.5°	197.9	188.2	176.7	167.3	159.6	152.9	146.5	142.6	139.9	137.7	136.4
75°	155.7	146.3	136.5	129.9	124.3	118.9	115.5	112.8	111.7	111.1	108.9
77.5°	114.4	109.4	101.5	96.2	92.5	90.3	87.4	85.9	85.9	83.4	82.7
80°	87.5	84.7	78.1	75.9	73.2	71.0	69.3	66.6	63.8	62.7	61.1
82.5°	65.1	62.3	59.7	56.1	53.8	52.5	50.9	49.8	50.2	48.7	47.9
85°	34.7	31.9	30.8	30.2	29.2	30.2	29.7	29.2	28.6	28.0	28.6
87.5°	13.0	13.4	13.4	14.6	13.7	14.5	14.8	14.6	14.9	15.2	14.9
90°	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4	23.8	25.1	26.3
92.5°	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8	52.6	54.5	55.6
95°	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5	100.4	102.3	103.5
97.5°	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3	156.1	157.9	159.1
100°	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1	195.5	198.0	199.5
102.5°	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8	235.5	238.1	239.9
105°	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2	298.8	300.4	301.7
107.5°	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6	367.4	368.2	368.6
110°	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8	415.6	416.5	416.7



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1	463.5	463.8	463.8
115°	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8	536.5	536.2	536.0
117.5°	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6	610.8	611.0	610.6
120°	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3	660.3	660.3	659.7
122.5°	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1	708.8	708.6	708.1
125°	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0	780.4	779.8	779.4
127.5°	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3	852.1	851.7	851.3
130°	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5	899.3	898.9	898.5
132.5°	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8	944.5	944.2	943.7
135°	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4	1014.4	1014.4	1013.9
137.5°	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2	1082.6	1082.9	1082.4
140°	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9	1125.5	1126.0	1125.6
142.5°	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8	1167.1	1167.5	1166.9
145°	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1	1227.1	1227.1	1226.7
147.5°	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0	1283.7	1284.3	1283.8
150°	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2	1318.2	1318.2	1317.8
152.5°	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0	1351.6	1352.3	1352.1
155°	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7	1398.9	1400.0	1399.9
157.5°	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4	1439.5	1440.6	1440.2
160°	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0	1464.0	1465.2	1465.0
162.5°	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0	1487.4	1488.7	1488.5
165°	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0	1518.2	1519.2	1519.0
167.5°	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0	1541.6	1543.3	1543.3
170°	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8	1555.4	1557.1	1557.0
172.5°	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7	1565.3	1566.9	1566.9
175°	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8	1576.4	1578.0	1577.8
177.5°	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7	1581.0	1582.3	1582.3
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1284.1	1279.3	1278.0	1279.7	1278.0	1279.3	1284.1	1284.6	1285.0	1288.5	1283.7
5°	1184.8	1179.2	1182.0	1180.9	1182.0	1179.2	1184.8	1190.3	1191.3	1196.3	1199.6
7.5°	1097.4	1090.5	1083.3	1085.6	1083.3	1090.5	1097.4	1097.5	1106.0	1112.5	1116.7
10°	1036.2	1030.7	1027.4	1030.1	1027.4	1030.7	1036.2	1043.3	1046.6	1054.3	1062.6
12.5°	984.6	981.4	978.5	977.3	978.5	981.4	984.6	992.3	1000.0	1009.0	1018.1
15°	914.6	908.0	905.2	898.1	905.2	908.0	914.6	921.2	936.0	939.9	953.7
17.5°	849.9	847.7	840.6	837.6	840.6	847.7	849.9	855.6	862.4	876.6	887.0
20°	811.6	809.4	802.3	806.7	802.3	809.4	811.6	819.9	825.4	837.0	846.9
22.5°	780.0	775.1	772.8	771.5	772.8	775.1	780.0	783.8	791.1	801.8	813.0
25°	735.2	728.0	725.3	721.9	725.3	728.0	735.2	737.4	745.1	755.5	761.6
27.5°	690.5	686.6	683.0	682.2	683.0	686.6	690.5	693.6	700.3	709.4	720.3
30°	661.5	657.6	654.8	654.8	654.8	657.6	661.5	668.1	673.0	681.3	689.5
32.5°	635.4	632.5	629.7	629.3	629.7	632.5	635.4	639.0	644.8	654.0	662.7
35°	597.6	593.2	592.1	588.8	592.1	593.2	597.6	600.4	606.4	613.0	620.2
37.5°	558.3	554.6	554.6	554.2	554.6	554.6	558.3	563.1	568.2	574.1	582.9
40°	533.2	530.4	529.9	526.0	529.9	530.4	533.2	535.4	541.0	548.6	555.2
42.5°	506.4	504.9	503.0	501.4	503.0	504.9	506.4	510.8	515.4	520.9	529.3
45°	469.9	466.1	466.1	463.3	466.1	466.1	469.9	473.8	476.0	482.6	493.6
47.5°	432.3	429.3	429.7	426.8	429.7	429.3	432.3	433.5	437.0	443.5	449.6
50°	407.2	405.5	405.0	403.9	405.0	405.5	407.2	406.7	411.1	417.1	425.3
52.5°	382.1	381.3	383.4	381.0	383.4	381.3	382.1	383.4	386.4	390.3	398.1
55°	348.3	346.7	350.0	346.7	350.0	346.7	348.3	347.2	348.3	352.2	357.1
57.5°	309.5	307.9	310.9	309.2	310.9	307.9	309.5	309.7	313.0	313.6	318.0
60°	284.0	280.6	282.3	282.8	282.3	280.6	284.0	285.0	286.2	286.7	291.1
62.5°	253.6	251.6	252.8	250.3	252.8	251.6	253.6	256.0	258.4	261.1	263.8
65°	210.8	209.1	206.9	205.8	206.9	209.1	210.8	211.9	217.9	221.2	227.3
67.5°	177.1	173.1	173.0	173.9	173.0	173.1	177.1	176.8	181.2	183.9	188.0
70°	152.5	152.5	151.9	151.9	151.9	152.5	152.5	155.7	157.9	160.1	162.9
72.5°	135.3	134.9	133.8	133.4	133.8	134.9	135.3	136.4	137.7	139.9	142.6
75°	108.9	109.5	108.4	107.9	108.4	109.5	108.9	108.9	111.1	111.7	112.8
77.5°	80.5	78.1	79.3	78.1	79.3	78.1	80.5	82.7	83.4	85.9	85.9
80°	61.1	60.5	62.2	60.5	62.2	60.5	61.1	61.1	62.7	63.8	66.6
82.5°	48.3	47.8	48.5	47.3	48.5	47.8	48.3	47.9	48.7	50.2	49.8
85°	29.2	28.6	28.0	28.6	28.0	28.6	29.2	28.6	28.0	28.6	29.2
87.5°	15.6	15.2	15.4	15.6	15.4	15.2	15.6	14.9	15.2	14.9	14.6
90°	27.1	27.9	28.7	29.5	28.7	27.9	27.1	26.3	25.1	23.8	22.4
92.5°	56.3	56.8	57.4	58.0	57.4	56.8	56.3	55.6	54.5	52.6	50.8
95°	104.1	104.7	105.2	105.7	105.2	104.7	104.1	103.5	102.3	100.4	98.5
97.5°	159.4	159.7	160.0	160.4	160.0	159.7	159.4	159.1	157.9	156.1	154.3
100°	200.0	200.6	201.1	201.6	201.1	200.6	200.0	199.5	198.0	195.5	193.1
102.5°	240.7	241.4	242.2	243.0	242.2	241.4	240.7	239.9	238.1	235.5	232.8
105°	302.5	303.3	304.1	304.9	304.1	303.3	302.5	301.7	300.4	298.8	297.2
107.5°	368.5	368.5	368.4	368.4	368.4	368.5	368.5	368.6	368.2	367.4	366.6
110°	416.5	416.1	415.9	415.6	415.9	416.1	416.5	416.7	416.5	415.6	414.8



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	463.3	462.8	462.4	461.9	462.4	462.8	463.3	463.8	463.8	463.5	463.1
115°	535.7	535.4	535.2	534.9	535.2	535.4	535.7	536.0	536.2	536.5	536.8
117.5°	609.4	608.4	607.3	606.2	607.3	608.4	609.4	610.6	611.0	610.8	610.6
120°	658.7	657.5	656.5	655.4	656.5	657.5	658.7	659.7	660.3	660.3	660.3
122.5°	707.2	706.3	705.4	704.6	705.4	706.3	707.2	708.1	708.6	708.8	709.1
125°	779.2	778.9	778.6	778.4	778.6	778.9	779.2	779.4	779.8	780.4	781.0
127.5°	850.8	850.3	849.7	849.1	849.7	850.3	850.8	851.3	851.7	852.1	852.3
130°	898.1	897.5	896.9	896.4	896.9	897.5	898.1	898.5	898.9	899.3	899.5
132.5°	943.0	942.2	941.4	940.6	941.4	942.2	943.0	943.7	944.2	944.5	944.8
135°	1012.8	1011.7	1010.6	1009.5	1010.6	1011.7	1012.8	1013.9	1014.4	1014.4	1014.4
137.5°	1081.0	1079.6	1078.2	1076.8	1078.2	1079.6	1081.0	1082.4	1082.9	1082.6	1082.2
140°	1124.3	1122.9	1121.5	1120.1	1121.5	1122.9	1124.3	1125.6	1126.0	1125.5	1124.9
142.5°	1165.6	1164.2	1162.9	1161.5	1162.9	1164.2	1165.6	1166.9	1167.5	1167.1	1166.8
145°	1225.9	1225.1	1224.3	1223.4	1224.3	1225.1	1225.9	1226.7	1227.1	1227.1	1227.1
147.5°	1281.9	1280.0	1278.2	1276.4	1278.2	1280.0	1281.9	1283.8	1284.3	1283.7	1283.0
150°	1317.3	1316.8	1316.2	1315.6	1316.2	1316.8	1317.3	1317.8	1318.2	1318.2	1318.2
152.5°	1351.1	1350.1	1349.2	1348.2	1349.2	1350.1	1351.1	1352.1	1352.3	1351.6	1351.0
155°	1398.5	1397.1	1395.7	1394.4	1395.7	1397.1	1398.5	1399.9	1400.0	1398.9	1397.7
157.5°	1438.4	1436.6	1434.8	1433.0	1434.8	1436.6	1438.4	1440.2	1440.6	1439.5	1438.4
160°	1463.6	1462.2	1460.9	1459.5	1460.9	1462.2	1463.6	1465.0	1465.2	1464.0	1463.0
162.5°	1486.9	1485.3	1483.8	1482.1	1483.8	1485.3	1486.9	1488.5	1488.7	1487.4	1486.0
165°	1517.4	1515.7	1514.1	1512.4	1514.1	1515.7	1517.4	1519.0	1519.2	1518.2	1517.0
167.5°	1541.6	1539.9	1538.2	1536.5	1538.2	1539.9	1541.6	1543.3	1543.3	1541.6	1540.0
170°	1555.0	1553.1	1551.2	1549.3	1551.2	1553.1	1555.0	1557.0	1557.1	1555.4	1553.8
172.5°	1565.2	1563.5	1561.8	1560.2	1561.8	1563.5	1565.2	1566.9	1566.9	1565.3	1563.7
175°	1576.0	1574.0	1572.1	1570.2	1572.1	1574.0	1576.0	1577.8	1578.0	1576.4	1574.8
177.5°	1580.7	1579.2	1577.6	1576.1	1577.6	1579.2	1580.7	1582.3	1582.3	1581.0	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1285.0	1289.9	1292.5	1298.7	1307.5	1311.9	1318.0	1322.4	1328.6	1336.1	1342.2
5°	1201.8	1215.0	1223.8	1237.5	1250.3	1262.9	1278.9	1290.4	1305.8	1323.4	1337.2
7.5°	1124.5	1141.1	1155.7	1173.9	1194.7	1211.0	1231.8	1253.1	1277.2	1302.2	1325.8
10°	1075.2	1091.8	1109.9	1132.5	1153.4	1175.4	1200.1	1224.9	1255.2	1283.3	1315.2
12.5°	1026.4	1044.6	1065.0	1090.2	1115.5	1143.7	1168.9	1196.8	1229.2	1265.7	1299.8
15°	965.7	983.3	1005.3	1026.8	1056.0	1086.8	1120.4	1157.2	1193.5	1234.3	1276.7
17.5°	900.7	920.1	944.3	969.1	999.9	1035.9	1068.9	1109.2	1150.1	1197.5	1247.4
20°	858.4	878.2	906.9	934.4	962.5	997.7	1036.7	1078.0	1121.4	1171.6	1227.1
22.5°	825.0	839.1	867.2	895.2	928.1	964.2	1002.4	1045.5	1092.8	1144.7	1202.9
25°	775.3	791.8	812.2	841.4	875.5	913.5	951.9	997.7	1049.4	1102.2	1164.4
27.5°	731.2	744.8	764.9	787.7	821.8	861.2	902.1	949.7	1002.8	1056.6	1122.0
30°	699.9	714.8	734.1	758.3	785.2	828.2	870.0	916.8	970.7	1026.3	1093.4
32.5°	672.6	687.9	704.6	727.5	756.6	794.8	837.9	883.8	938.6	995.9	1061.3
35°	634.5	644.9	660.3	682.9	711.5	742.3	786.4	834.8	888.2	947.6	1013.1
37.5°	590.7	604.2	619.5	639.1	664.2	697.6	738.5	787.4	837.0	893.9	953.7
40°	565.2	577.8	594.8	609.2	635.6	665.9	703.3	754.4	804.0	857.4	911.8
42.5°	539.2	551.4	565.8	583.6	607.4	636.7	671.6	719.2	772.3	822.6	868.2
45°	498.6	511.2	525.0	541.4	563.5	592.1	626.8	670.3	716.5	762.7	797.4
47.5°	459.7	471.6	484.6	501.5	521.8	549.4	580.4	618.8	663.7	703.0	727.8
50°	431.9	443.0	457.3	473.8	493.6	519.4	549.2	587.2	624.6	660.3	682.9
52.5°	404.7	417.0	431.3	445.6	464.6	490.4	518.0	550.6	586.3	615.5	634.1
55°	363.7	375.3	388.5	403.3	422.1	444.1	473.3	499.1	527.2	552.0	563.0
57.5°	324.2	334.4	346.7	362.2	379.0	399.5	422.7	447.5	467.3	484.8	497.3
60°	298.2	307.0	318.6	331.8	350.0	368.7	389.6	412.7	428.1	443.0	454.5
62.5°	271.8	280.2	291.3	303.2	319.2	336.6	356.6	375.3	390.3	400.3	413.6
65°	232.2	240.4	249.8	262.4	275.2	289.4	307.6	321.4	331.8	342.8	351.1
67.5°	195.3	202.2	211.1	221.0	231.7	245.4	259.5	270.9	278.1	284.7	294.6
70°	171.1	176.7	183.8	191.5	203.1	216.8	227.8	236.6	241.6	248.2	260.2
72.5°	146.5	152.9	159.6	167.3	176.7	188.2	197.9	206.7	209.9	215.2	222.9
75°	115.5	118.9	124.3	129.9	136.5	146.3	155.7	157.9	160.7	165.1	170.6
77.5°	87.4	90.3	92.5	96.2	101.5	109.4	114.4	117.6	118.3	119.9	125.4
80°	69.3	71.0	73.2	75.9	78.1	84.7	87.5	90.8	91.9	93.5	96.3
82.5°	50.9	52.5	53.8	56.1	59.7	62.3	65.1	68.3	68.6	69.8	70.4
85°	29.7	30.2	29.2	30.2	30.8	31.9	34.7	37.4	36.9	36.3	38.0
87.5°	14.8	14.5	13.7	14.6	13.4	13.4	13.0	13.0	13.5	13.9	14.3
90°	21.0	19.6	17.8	15.8	13.9	12.0	9.9	7.8	5.6	3.4	1.2
92.5°	49.0	47.2	44.8	42.5	40.2	37.8	35.9	34.3	32.9	31.3	29.8
95°	96.6	94.7	92.0	89.2	86.5	83.7	82.1	81.5	81.0	80.5	79.9
97.5°	152.5	150.7	147.0	143.2	139.4	135.7	133.7	133.5	133.2	133.0	132.8
100°	190.6	188.1	184.6	181.0	177.5	173.9	172.1	172.1	172.1	172.1	172.1
102.5°	230.2	227.5	225.7	223.9	222.1	220.3	218.8	217.7	216.6	215.6	214.4
105°	295.5	293.9	292.2	290.6	288.9	287.3	285.8	284.5	283.1	281.7	280.4
107.5°	365.7	364.9	363.7	362.4	361.2	360.0	358.6	357.3	355.9	354.5	353.1
110°	413.9	413.1	412.3	411.5	410.7	409.9	408.8	407.4	406.0	404.7	403.3



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	462.7	462.4	461.3	460.2	459.2	458.2	457.3	456.6	455.9	455.2	454.4
115°	537.0	537.4	536.8	536.2	535.7	535.2	534.3	533.2	532.1	531.1	529.9
117.5°	610.3	610.2	609.6	609.1	608.6	608.1	607.6	607.2	606.7	606.2	605.7
120°	660.3	660.3	660.0	659.7	659.5	659.2	658.4	657.0	655.7	654.3	652.9
122.5°	709.2	709.5	708.7	708.1	707.4	706.6	706.0	705.6	705.1	704.6	704.1
125°	781.5	782.0	781.8	781.5	781.2	781.0	780.0	778.4	776.7	775.0	773.4
127.5°	852.6	852.9	852.6	852.2	851.9	851.6	850.9	849.9	849.1	848.2	847.2
130°	899.8	900.1	899.5	898.9	898.5	897.9	896.9	895.5	894.2	892.8	891.4
132.5°	945.0	945.3	945.4	945.5	945.7	945.7	944.7	942.5	940.2	938.0	935.7
135°	1014.4	1014.4	1014.2	1013.9	1013.6	1013.3	1012.4	1010.7	1009.1	1007.5	1005.8
137.5°	1081.9	1081.6	1080.9	1080.4	1079.8	1079.1	1078.1	1076.4	1074.9	1073.3	1071.7
140°	1124.4	1123.9	1123.1	1122.3	1121.4	1120.5	1119.5	1118.1	1116.7	1115.4	1114.0
142.5°	1166.4	1166.1	1165.1	1164.1	1163.0	1162.0	1160.9	1159.8	1158.6	1157.5	1156.3
145°	1227.1	1227.1	1226.3	1225.5	1224.7	1223.8	1222.9	1221.8	1220.7	1219.6	1218.5
147.5°	1282.4	1281.7	1281.1	1280.4	1279.8	1279.1	1278.5	1277.9	1277.2	1276.7	1276.1
150°	1318.2	1318.2	1317.0	1316.0	1314.8	1313.8	1313.4	1313.6	1313.9	1314.2	1314.4
152.5°	1350.3	1349.6	1349.2	1348.7	1348.3	1347.9	1347.4	1347.0	1346.7	1346.3	1345.9
155°	1396.7	1395.6	1395.3	1395.1	1394.8	1394.5	1394.4	1394.4	1394.4	1394.4	1394.4
157.5°	1437.3	1436.1	1435.9	1435.7	1435.3	1435.1	1435.3	1435.8	1436.5	1437.0	1437.6
160°	1461.8	1460.8	1460.5	1460.2	1460.0	1459.7	1460.0	1460.8	1461.6	1462.4	1463.2
162.5°	1484.7	1483.4	1483.4	1483.3	1483.2	1483.2	1483.4	1484.1	1484.7	1485.2	1485.9
165°	1516.0	1514.9	1514.6	1514.3	1514.1	1513.8	1513.9	1514.5	1515.0	1515.6	1516.1
167.5°	1538.4	1536.8	1536.8	1536.8	1536.8	1536.8	1537.3	1538.4	1539.5	1540.6	1541.6
170°	1552.2	1550.5	1550.5	1550.5	1550.5	1550.5	1551.1	1552.2	1553.2	1554.4	1555.4
172.5°	1562.0	1560.4	1560.4	1560.4	1560.4	1560.4	1560.9	1562.0	1563.1	1564.2	1565.3
175°	1573.0	1571.4	1571.4	1571.4	1571.4	1571.4	1572.0	1573.0	1574.2	1575.2	1576.4
177.5°	1578.4	1577.1	1577.3	1577.5	1577.8	1577.9	1578.5	1579.4	1580.3	1581.1	1582.0
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1347.1	1351.0	1356.7	1363.3	1368.6	1374.4	1377.4	1377.4	1380.1	1385.8	1393.3
5°	1351.0	1365.2	1379.0	1396.6	1410.4	1426.3	1438.4	1450.0	1460.4	1473.7	1487.4
7.5°	1349.8	1373.6	1398.4	1426.1	1456.7	1481.0	1506.0	1525.6	1545.0	1570.3	1590.2
10°	1345.4	1376.2	1409.8	1445.0	1483.5	1517.1	1547.4	1574.9	1601.3	1628.8	1653.6
12.5°	1337.5	1376.7	1417.7	1460.0	1508.6	1547.0	1586.2	1615.4	1646.3	1676.3	1706.8
15°	1325.6	1371.8	1421.4	1480.3	1539.7	1582.6	1621.1	1659.1	1687.7	1721.8	1751.0
17.5°	1301.1	1360.7	1422.9	1487.3	1544.4	1594.2	1634.7	1670.8	1701.3	1738.8	1778.4
20°	1286.5	1351.0	1415.8	1484.7	1539.1	1590.3	1629.4	1666.8	1704.8	1753.7	1802.1
22.5°	1266.3	1335.1	1403.9	1469.3	1526.8	1576.2	1616.6	1662.4	1712.2	1767.8	1826.4
25°	1234.3	1305.3	1373.5	1435.7	1491.8	1542.5	1597.5	1659.1	1719.6	1792.8	1877.0
27.5°	1193.7	1262.1	1323.0	1388.7	1444.5	1508.9	1577.5	1644.4	1731.6	1832.3	1937.4
30°	1163.3	1228.2	1286.0	1348.2	1411.4	1482.5	1559.5	1638.2	1742.2	1860.5	1985.4
32.5°	1128.0	1186.8	1244.1	1304.2	1377.1	1455.1	1537.0	1633.4	1757.6	1892.2	2021.5
35°	1067.0	1119.8	1175.4	1241.9	1319.6	1404.4	1508.9	1626.1	1776.3	1921.0	2037.1
37.5°	1002.9	1044.6	1100.4	1170.7	1255.2	1353.2	1471.9	1614.3	1768.6	1898.4	1947.9
40°	953.7	992.7	1051.6	1125.4	1208.9	1316.3	1449.4	1595.8	1751.0	1841.3	1837.4
42.5°	904.7	944.3	1000.9	1075.1	1162.3	1282.4	1419.5	1571.6	1702.6	1736.9	1665.2
45°	829.8	866.7	922.3	997.1	1090.6	1216.7	1360.8	1506.7	1590.3	1534.7	1392.8
47.5°	753.4	789.2	840.8	914.1	1016.3	1148.1	1284.4	1404.1	1415.8	1296.5	1126.2
50°	703.3	736.8	785.8	864.0	963.0	1091.8	1223.3	1317.4	1288.2	1142.4	966.9
52.5°	654.4	686.6	732.5	806.2	907.5	1033.6	1151.0	1224.9	1157.5	1002.4	844.5
55°	582.2	613.0	659.3	726.9	818.8	934.4	1037.3	1064.2	965.2	808.9	681.3
57.5°	513.6	536.2	581.9	641.7	730.3	832.3	906.0	901.2	791.8	651.1	559.5
60°	468.3	488.6	532.1	587.2	671.3	762.7	814.4	792.4	681.8	565.7	477.6
62.5°	426.0	445.1	481.5	532.1	604.5	683.9	721.5	691.1	586.7	484.7	414.7
65°	362.1	375.9	405.0	451.8	508.4	563.5	597.0	552.4	460.1	383.0	330.2
67.5°	302.3	314.2	340.1	373.7	412.8	450.8	464.5	422.7	350.7	298.8	261.6
70°	263.6	274.6	292.2	323.6	349.4	376.4	383.0	345.6	285.6	246.0	222.9
72.5°	226.6	236.8	252.2	274.3	292.2	307.7	310.8	276.1	230.2	202.8	185.0
75°	172.8	181.6	191.5	199.7	211.3	214.1	213.0	186.0	161.3	143.1	133.1
77.5°	127.0	130.6	136.7	140.0	140.6	140.3	134.7	117.6	104.8	97.4	93.4
80°	97.9	100.7	102.3	103.5	104.0	98.5	92.5	82.0	77.6	73.2	68.2
82.5°	71.1	73.0	74.6	74.8	71.8	67.3	61.6	56.4	53.4	51.2	49.3
85°	38.5	39.1	38.5	35.8	31.9	30.2	29.2	28.0	27.5	27.0	27.0
87.5°	14.3	13.5	11.7	12.6	13.0	12.9	13.3	13.2	13.2	13.5	13.7
90°	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0	22.4
92.5°	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0	50.8
95°	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6	98.5
97.5°	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5	154.3
100°	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6	193.1
102.5°	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2	232.8
105°	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5	297.2
107.5°	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7	366.6
110°	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9	414.8



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7	463.1
115°	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0	536.8
117.5°	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3	610.6
120°	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3	660.3
122.5°	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2	709.1
125°	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5	781.0
127.5°	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6	852.3
130°	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8	899.5
132.5°	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0	944.8
135°	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4	1014.4
137.5°	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9	1082.2
140°	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4	1124.9
142.5°	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4	1166.8
145°	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1	1227.1
147.5°	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4	1283.0
150°	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2	1318.2
152.5°	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3	1351.0
155°	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7	1397.7
157.5°	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3	1438.4
160°	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8	1463.0
162.5°	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7	1486.0
165°	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0	1517.0
167.5°	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4	1540.0
170°	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2	1553.8
172.5°	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0	1563.7
175°	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0	1574.8
177.5°	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4	1579.7
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5	1340.5
2.5°	1399.1	1399.1	1406.6	1406.1	1411.0	1409.2	1410.1
5°	1503.9	1513.3	1521.5	1527.1	1535.3	1537.5	1536.4
7.5°	1612.7	1633.5	1643.6	1657.4	1659.9	1667.2	1666.5
10°	1680.0	1700.4	1715.8	1727.9	1733.9	1741.6	1742.2
12.5°	1732.8	1750.1	1763.7	1775.0	1782.3	1784.8	1786.2
15°	1774.1	1793.3	1809.3	1825.3	1834.7	1841.8	1845.7
17.5°	1815.7	1845.4	1873.6	1895.2	1908.3	1919.3	1919.1
20°	1847.9	1882.0	1917.2	1942.0	1967.2	1978.2	1979.9
22.5°	1882.2	1934.4	1979.7	2018.1	2051.3	2062.8	2067.1
25°	1953.5	2021.7	2091.7	2145.5	2184.0	2206.6	2210.0
27.5°	2039.6	2132.0	2205.5	2255.3	2287.3	2304.0	2307.6
30°	2100.5	2185.7	2251.8	2289.2	2304.0	2306.2	2298.0
32.5°	2127.7	2191.4	2217.9	2215.7	2186.5	2167.1	2159.7
35°	2094.3	2081.1	2016.8	1939.8	1880.9	1843.5	1833.5
37.5°	1905.9	1792.0	1673.6	1557.2	1495.3	1463.7	1409.6
40°	1720.2	1557.9	1434.6	1336.6	1266.7	1210.6	1197.4
42.5°	1510.7	1343.0	1219.8	1135.9	1080.1	1041.5	1024.8
45°	1213.9	1069.8	967.9	903.6	860.6	832.6	819.9
47.5°	970.9	859.3	785.1	737.5	704.8	680.4	673.5
50°	837.6	748.4	685.7	645.5	620.7	602.0	594.3
52.5°	727.5	655.5	607.3	574.1	550.7	539.1	532.6
55°	600.4	538.2	503.5	477.1	463.9	454.5	450.1
57.5°	491.0	446.1	420.8	402.5	390.3	384.3	382.1
60°	429.7	394.5	371.5	357.1	348.9	341.2	339.0
62.5°	375.6	347.9	330.0	317.5	309.2	306.0	304.6
65°	302.6	284.5	271.3	263.6	257.0	255.8	255.4
67.5°	240.6	229.9	223.0	214.9	212.6	208.8	208.0
70°	205.8	198.7	190.4	187.7	184.9	181.1	181.6
72.5°	174.6	167.4	161.8	158.2	157.2	155.5	156.9
75°	127.7	125.5	123.3	120.5	119.4	119.4	118.9
77.5°	91.2	89.3	86.8	85.2	84.9	82.5	83.4
80°	66.0	63.3	62.2	62.7	61.1	60.5	60.5
82.5°	48.8	47.9	46.8	46.9	46.6	46.0	46.5
85°	27.0	26.4	26.4	25.8	25.8	25.3	25.3
87.5°	14.4	15.2	14.5	14.2	14.3	15.0	15.6
90°	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333717-930

CATALOG NUMBER: S125RDIW-S1090D1560U930-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)