

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P333732-930

Luminaire Tested: **S125RDIW-S1270D1340U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333732-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1270D1340U930-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8386.9 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48																				
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47	41																				
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35																				
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34	30																				
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26																				
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23																				
6	63	52	44	38	58	48	41	36	41	36	31	35	30	27	28	25	23	20																				
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18																				
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16																				
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14																				
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	9999	9999	9999	9999
5°	11503	10012	8842	10012
10°	13195	9961	7802	9961
15°	14252	9859	6935	9859
20°	15716	9740	6403	9740
25°	18188	9583	5942	9583
30°	19792	9417	5640	9417
35°	16696	9224	5361	9224
40°	11659	8878	5123	8878
45°	8649	8411	4887	8411
50°	6897	7924	4687	7924
55°	5853	7320	4508	7320
60°	5057	6781	4220	6781
65°	4507	6195	3632	6195
70°	3960	5676	3312	5676
75°	3426	4916	3109	4916
80°	2600	4136	2600	4136
85°	2171	3253	2445	3253



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	148.5	1.8
10°-20°	435.1	5.2
20°-30°	689.8	8.2
30°-40°	831.9	9.9
40°-50°	742.9	8.9
50°-60°	569.7	6.8
60°-70°	370.2	4.4
70°-80°	180.0	2.1
80°-90°	45.9	0.5
90°-100°	51.7	0.6
100°-110°	318.9	3.8
110°-120°	578.4	6.9
120°-130°	742.3	8.9
130°-140°	798.4	9.5
140°-150°	749.4	8.9
150°-160°	606.3	7.2
160°-170°	392.1	4.7
170°-180°	135.2	1.6
0°-30°	1273.4	15.2
0°-40°	2105.3	25.1
0°-60°	3417.9	40.8
0°-90°	4014.0	47.9
90°-120°	949.1	11.3
90°-150°	3239.3	38.6
90°-180°	4373.0	52.1
0°-180°	8386.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1548	1548	1548	1548	1548	
5°	1774	1544	1364	1544	1774	177
15°	2132	1474	1037	1474	2132	611
25°	2552	1345	834	1345	2552	1172
35°	2118	1170	680	1170	2118	1279
45°	947	921	535	921	947	756
55°	520	650	400	650	520	472
65°	295	405	238	405	295	293
75°	137	197	125	197	137	146
85°	29	44	33	44	29	34
90°	25	1	25	1	25	12
95°	22	60	22	60	22	18
105°	314	310	314	310	314	283
115°	578	583	578	583	578	574
125°	829	829	829	829	829	737
135°	1029	1034	1029	1034	1029	794
145°	1195	1198	1195	1198	1195	746
155°	1310	1320	1310	1320	1310	604
165°	1385	1392	1385	1392	1385	391
175°	1418	1424	1418	1424	1418	135
180°	1424	1424	1424	1424	1424	



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1628.5	1627.5	1629.5	1623.9	1624.4	1615.8	1615.8	1609.2	1600.5	1593.9	1590.9
5°	1774.4	1775.7	1773.1	1763.6	1757.3	1747.8	1736.9	1717.8	1701.9	1686.7	1674.6
7.5°	1924.7	1925.6	1917.2	1914.2	1898.2	1886.5	1862.5	1836.5	1813.6	1784.4	1761.9
10°	2012.1	2011.5	2002.5	1995.6	1981.6	1963.8	1940.3	1909.8	1881.2	1849.4	1818.9
12.5°	2063.0	2061.3	2058.5	2050.0	2037.0	2021.3	2001.3	1971.3	1936.1	1901.3	1865.6
15°	2131.6	2127.1	2118.9	2108.0	2089.6	2071.2	2048.9	2022.3	1988.6	1949.2	1916.1
17.5°	2216.5	2216.6	2203.9	2188.9	2163.9	2131.4	2097.0	2053.9	2008.2	1964.8	1929.7
20°	2286.7	2284.7	2272.1	2242.8	2214.2	2173.5	2134.1	2081.4	2025.4	1968.9	1925.0
22.5°	2387.4	2382.4	2369.2	2330.8	2286.4	2234.0	2173.8	2109.3	2041.8	1977.5	1919.9
25°	2552.3	2548.5	2522.5	2477.9	2415.7	2334.9	2256.2	2167.8	2070.6	1986.1	1916.1
27.5°	2665.2	2661.0	2641.7	2604.7	2547.2	2462.3	2355.6	2237.6	2116.2	1999.9	1899.1
30°	2654.0	2663.5	2661.0	2643.9	2600.6	2524.3	2425.8	2293.0	2148.7	2012.1	1892.0
32.5°	2494.3	2502.9	2525.2	2558.9	2561.4	2530.9	2457.4	2334.7	2185.3	2029.9	1886.4
35°	2117.6	2129.1	2172.3	2240.3	2329.2	2403.6	2418.8	2352.8	2218.7	2051.5	1878.0
37.5°	1628.0	1690.5	1726.9	1798.5	1932.9	2069.7	2201.2	2249.7	2192.6	2042.7	1864.4
40°	1382.9	1398.2	1463.0	1543.7	1656.9	1799.2	1986.7	2122.1	2126.5	2022.3	1843.1
42.5°	1183.7	1203.0	1247.4	1311.9	1408.8	1551.1	1744.7	1923.3	2006.0	1966.3	1815.1
45°	947.0	961.6	994.0	1043.6	1117.9	1235.5	1402.0	1608.5	1772.5	1836.7	1740.1
47.5°	777.9	785.8	814.0	851.7	906.8	992.5	1121.4	1300.6	1497.3	1635.2	1621.6
50°	686.4	695.3	716.9	745.5	791.9	864.3	967.3	1116.6	1319.4	1487.8	1521.5
52.5°	615.2	622.6	636.0	663.1	701.4	757.1	840.2	975.3	1157.7	1336.8	1414.7
55°	519.8	525.0	535.7	551.0	581.6	621.6	693.3	786.8	934.3	1114.8	1229.1
57.5°	441.3	443.8	450.7	464.8	485.9	515.2	567.0	646.2	752.0	914.5	1040.7
60°	391.5	394.0	402.9	412.5	429.0	455.7	496.4	551.6	653.3	787.4	915.2
62.5°	351.8	353.4	357.2	366.7	381.2	401.8	433.8	478.9	559.8	677.6	798.3
65°	294.9	295.5	296.8	304.4	313.3	328.6	349.5	381.3	442.3	531.3	638.1
67.5°	240.3	241.1	245.6	248.3	257.6	265.5	277.9	302.1	345.1	405.1	488.1
70°	209.7	209.1	213.5	216.7	219.9	229.4	237.7	257.4	284.1	329.9	399.1
72.5°	181.2	179.6	181.5	182.6	186.9	193.3	201.6	213.7	234.2	265.8	318.8
75°	137.3	137.9	137.9	139.2	142.4	144.9	147.4	153.8	165.3	186.2	214.8
77.5°	96.4	95.3	98.0	98.4	100.3	103.1	105.3	107.8	112.5	121.2	135.9
80°	69.9	69.9	70.5	72.5	71.8	73.1	76.2	78.8	84.5	89.6	94.7
82.5°	53.6	53.2	53.7	54.1	54.1	55.3	56.4	56.9	59.1	61.6	65.2
85°	29.3	29.3	29.8	29.8	30.5	30.5	31.1	31.1	31.1	31.8	32.4
87.5°	16.2	15.6	14.9	14.8	15.2	16.0	15.2	14.5	14.3	14.0	14.3
90°	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2	18.1	16.9	15.2
92.5°	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2	18.1	16.9	15.4
95°	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2	18.1	16.9	25.8
97.5°	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7	45.3	51.9	69.5
100°	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7	148.7	183.7	182.7
102.5°	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1	227.7	234.3	233.7
105°	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3	398.2	398.2	397.7
110°	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5	453.2	453.9	453.5



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1	507.0	507.9	507.7
115°	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2	588.1	589.1	588.8
117.5°	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4	666.6	667.8	666.9
120°	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8	716.3	716.7	716.1
122.5°	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9	764.4	764.9	764.6
125°	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1	835.1	836.0	836.0
127.5°	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4	898.9	899.4	899.5
130°	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2	940.9	941.6	941.3
132.5°	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3	979.5	979.6	980.2
135°	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7	1037.2	1037.6	1038.1
137.5°	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2	1090.1	1090.1	1090.5
140°	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1	1122.6	1122.1	1122.3
142.5°	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2	1155.1	1155.0	1154.7
145°	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7	1200.4	1200.2	1200.2
147.5°	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7	1239.3	1239.1	1238.8
150°	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5	1264.0	1263.6	1263.1
152.5°	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5	1286.0	1285.5	1285.1
155°	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7	1316.0	1315.3	1314.8
157.5°	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7	1340.9	1340.2	1340.2
160°	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3	1356.3	1355.4	1355.2
162.5°	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5	1370.2	1368.9	1368.6
165°	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8	1388.5	1387.1	1386.8
167.5°	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8	1402.1	1400.4	1400.1
170°	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9	1409.0	1407.1	1406.9
172.5°	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4	1414.7	1413.0	1412.6
175°	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5	1420.6	1418.7	1418.5
177.5°	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0	1423.7	1422.3	1422.1
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1590.9	1587.3	1580.7	1574.6	1567.0	1560.4	1555.8	1550.2	1543.1	1534.5	1527.3
5°	1661.3	1647.3	1628.9	1613.0	1592.7	1576.8	1560.2	1544.3	1528.4	1508.1	1490.4
7.5°	1739.4	1710.5	1682.4	1647.1	1615.0	1586.4	1558.9	1531.1	1503.9	1475.0	1447.2
10°	1787.1	1752.2	1713.4	1668.9	1628.2	1589.5	1553.9	1518.9	1482.1	1449.7	1414.7
12.5°	1831.9	1786.7	1742.4	1686.2	1637.4	1590.0	1544.7	1501.1	1461.8	1419.7	1382.2
15°	1872.3	1827.8	1778.2	1709.6	1641.6	1584.4	1531.0	1474.5	1425.5	1378.5	1336.5
17.5°	1887.9	1841.3	1783.7	1717.8	1643.4	1571.4	1502.7	1440.6	1383.1	1328.3	1281.1
20°	1881.8	1836.7	1777.6	1714.7	1635.2	1560.2	1485.9	1417.2	1353.1	1295.2	1245.0
22.5°	1867.1	1820.4	1763.3	1696.9	1621.5	1542.0	1462.5	1389.3	1322.0	1262.2	1207.4
25°	1844.9	1781.4	1723.0	1658.1	1586.3	1507.5	1425.5	1344.8	1273.0	1211.9	1152.3
27.5°	1821.9	1742.6	1668.3	1603.9	1528.0	1457.7	1378.6	1295.8	1220.3	1158.2	1096.9
30°	1801.1	1712.1	1630.1	1557.1	1485.2	1418.5	1343.5	1262.8	1185.3	1121.1	1058.8
32.5°	1775.2	1680.6	1590.5	1506.2	1437.0	1370.8	1302.8	1225.7	1150.2	1083.9	1020.7
35°	1742.6	1621.9	1524.0	1434.4	1357.5	1293.3	1232.3	1170.0	1094.4	1025.7	964.1
37.5°	1699.9	1562.9	1449.7	1352.0	1271.0	1206.5	1158.3	1101.4	1032.3	966.6	909.5
40°	1674.0	1520.2	1396.3	1299.7	1214.5	1146.5	1101.4	1053.1	990.2	928.5	871.3
42.5°	1639.4	1481.1	1342.4	1241.7	1156.0	1090.5	1045.0	1002.7	950.0	891.9	830.6
45°	1571.7	1405.2	1259.6	1151.6	1065.2	1000.9	958.4	920.9	880.8	827.4	774.0
47.5°	1483.4	1326.0	1173.7	1055.7	971.1	911.5	870.2	840.6	812.0	766.5	714.7
50°	1412.8	1260.9	1112.1	997.8	907.5	851.0	812.2	788.7	762.6	721.3	678.1
52.5°	1329.4	1193.8	1048.1	931.2	846.0	793.0	755.8	732.3	710.8	677.1	635.9
55°	1198.0	1079.1	945.7	839.5	761.4	708.0	672.4	650.1	637.5	608.9	576.4
57.5°	1046.4	961.2	843.5	741.2	672.1	619.3	593.2	574.3	559.9	539.7	516.8
60°	940.6	880.8	775.3	678.1	614.6	564.4	540.9	525.0	511.6	494.5	476.6
62.5°	833.3	789.9	698.1	614.6	556.1	514.0	492.0	477.7	462.3	450.7	433.4
65°	689.6	650.8	587.3	521.8	467.7	434.1	418.2	405.4	395.9	383.2	371.1
67.5°	536.4	520.7	476.8	431.6	392.9	362.9	349.2	340.3	328.8	321.2	312.9
70°	442.3	434.7	403.6	373.7	337.5	317.2	304.4	300.6	286.7	279.0	273.3
72.5°	359.0	355.4	337.5	316.7	291.2	273.4	261.7	257.4	248.5	242.4	238.7
75°	246.0	247.2	244.0	230.7	221.2	209.7	199.6	197.0	190.7	185.6	182.4
77.5°	155.6	162.1	162.3	161.7	157.8	150.9	146.7	144.8	138.5	136.6	135.9
80°	106.8	113.7	120.1	119.4	118.2	116.3	113.2	111.2	108.0	106.2	104.8
82.5°	71.2	77.7	83.0	86.4	86.2	84.3	82.1	81.2	80.6	79.2	78.9
85°	33.7	35.0	36.9	41.3	44.5	45.1	44.5	43.9	41.9	42.6	43.2
87.5°	14.4	14.1	14.3	13.9	13.0	15.2	16.4	16.5	15.8	15.2	14.6
90°	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1	2.9	4.8	6.7
92.5°	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2	14.9	13.6	12.3
95°	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2	59.4	58.8	58.0
97.5°	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6	126.9	128.2	129.4
100°	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3	177.0	177.7	178.4
102.5°	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8	228.7	229.6	230.5
105°	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4	311.3	312.3	313.2
107.5°	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1	396.1	396.1	396.1
110°	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8	451.8	451.8	451.8





TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2	504.8	505.3	505.8
115°	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7	583.8	585.1	586.2
117.5°	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0	663.9	663.9	663.8
120°	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6	714.4	714.2	714.0
122.5°	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4	760.3	761.2	762.1
125°	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7	830.3	831.9	833.6
127.5°	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7	895.9	897.1	898.2
130°	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2	936.5	937.6	938.8
132.5°	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8	977.1	978.5	979.9
135°	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5	1034.9	1036.2	1037.6
137.5°	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5	1087.6	1088.8	1090.1
140°	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0	1121.5	1122.0	1122.4
142.5°	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3	1152.6	1152.8	1153.2
145°	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1	1198.6	1199.1	1199.5
147.5°	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2	1238.1	1238.0	1238.0
150°	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1263.1	1262.7	1262.2
152.5°	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0	1287.0	1286.0	1285.0
155°	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5	1318.1	1316.7	1315.3
157.5°	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8	1343.0	1342.1	1341.2
160°	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7	1359.3	1357.9	1356.4
162.5°	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2	1372.8	1371.3	1369.9
165°	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4	1390.9	1389.5	1388.1
167.5°	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8	1404.4	1403.0	1401.5
170°	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5	1411.9	1410.1	1408.5
172.5°	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5	1416.9	1415.3	1413.6
175°	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0	1422.6	1421.2	1419.8
177.5°	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5	1425.4	1424.3	1423.2
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1522.2	1515.2	1510.0	1499.8	1492.7	1489.7	1484.1	1482.5	1488.2	1484.1	1483.6
5°	1477.0	1458.6	1444.0	1429.3	1413.4	1403.3	1388.0	1385.4	1381.7	1375.9	1374.7
7.5°	1422.7	1398.7	1379.9	1355.8	1334.7	1317.8	1298.8	1289.7	1284.8	1277.4	1267.5
10°	1386.1	1357.5	1332.1	1307.9	1281.9	1260.9	1241.9	1227.2	1217.6	1208.8	1205.0
12.5°	1350.0	1320.9	1288.3	1259.1	1230.0	1206.5	1185.4	1175.9	1165.3	1154.9	1146.0
15°	1294.0	1255.2	1219.6	1185.9	1161.1	1135.7	1115.3	1101.4	1085.5	1081.1	1063.9
17.5°	1234.4	1196.5	1154.8	1119.3	1090.5	1062.6	1040.2	1024.3	1012.4	996.1	988.1
20°	1197.3	1152.3	1111.6	1079.1	1047.3	1014.3	991.4	978.1	966.6	953.3	947.0
22.5°	1157.7	1113.6	1071.9	1033.9	1001.6	969.1	952.8	939.0	925.9	913.6	905.2
25°	1099.5	1055.0	1011.1	971.8	938.1	914.5	895.4	879.5	872.6	860.5	851.6
27.5°	1041.9	994.6	949.1	909.8	883.4	860.1	844.5	831.9	819.3	808.8	801.0
30°	1004.8	956.5	906.9	875.8	847.8	825.6	808.4	796.3	786.8	777.2	771.5
32.5°	967.7	917.9	873.8	840.2	813.8	794.5	776.9	765.3	755.3	744.7	738.0
35°	908.2	857.4	821.7	788.7	762.6	744.9	732.8	716.2	708.0	700.3	693.3
37.5°	852.9	805.6	767.1	738.1	715.5	697.8	682.2	673.3	663.1	656.2	650.4
40°	812.2	769.0	734.0	703.5	687.1	667.3	652.7	641.2	633.7	624.8	618.4
42.5°	775.6	735.5	701.5	674.1	653.5	636.8	622.7	611.2	601.6	595.3	589.9
45°	723.9	683.9	650.8	625.3	606.3	590.4	575.8	570.1	557.3	549.8	547.2
47.5°	670.3	634.5	602.6	579.2	559.6	544.6	530.9	519.3	512.3	504.8	500.7
50°	634.3	600.0	570.1	547.2	528.2	511.6	498.9	491.3	481.8	474.7	469.7
52.5°	598.2	566.4	536.5	514.6	498.1	481.6	467.4	459.7	450.7	446.3	442.7
55°	546.6	512.9	487.5	465.9	448.7	433.4	420.1	412.5	406.8	402.3	401.0
57.5°	488.1	461.4	437.7	418.3	400.5	386.1	374.5	367.2	362.2	361.5	357.7
60°	450.0	425.8	404.2	383.2	367.9	354.7	344.5	336.2	331.1	330.4	329.2
62.5°	411.8	388.7	368.6	350.2	336.5	323.6	314.0	304.7	301.7	298.5	295.6
65°	355.2	334.3	317.8	303.1	288.5	277.7	268.2	262.4	255.5	251.7	244.7
67.5°	299.7	283.5	267.6	255.3	243.8	233.5	225.6	217.1	212.4	209.4	204.2
70°	263.1	250.4	234.5	221.2	212.3	204.0	197.6	188.1	184.9	182.4	179.9
72.5°	228.5	217.4	204.0	193.2	184.3	176.5	169.2	164.7	161.6	159.0	157.5
75°	179.9	169.1	157.6	150.0	143.7	137.3	133.5	130.3	129.0	128.4	125.8
77.5°	132.1	126.4	117.2	111.1	106.9	104.4	100.9	99.3	99.1	96.4	95.5
80°	101.0	97.8	90.3	87.7	84.5	82.0	80.1	76.9	73.7	72.5	70.5
82.5°	75.1	71.9	68.9	64.8	62.1	60.7	58.7	57.6	58.0	56.2	55.3
85°	40.0	36.9	35.6	35.0	33.7	35.0	34.3	33.7	33.0	32.4	33.0
87.5°	14.4	14.8	14.6	16.0	14.8	15.6	15.8	15.6	15.7	16.0	15.7
90°	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2	20.4	21.6	22.5
92.5°	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2	20.4	21.6	22.3
95°	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2	20.4	21.6	22.2
97.5°	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7	32.1	25.4	22.2
100°	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7	78.8	43.9	25.9
102.5°	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1	214.5	207.9	196.6
105°	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3	398.4	398.4	398.0
110°	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5	451.8	451.1	450.9



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1	505.3	504.4	503.8
115°	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2	586.2	585.3	584.1
117.5°	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4	664.1	662.9	661.9
120°	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8	715.3	714.9	714.0
122.5°	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9	763.4	763.0	762.1
125°	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1	833.2	832.3	831.4
127.5°	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4	897.8	897.3	896.2
130°	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2	939.5	938.8	937.8
132.5°	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3	979.2	979.0	978.4
135°	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7	1036.2	1035.8	1034.9
137.5°	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2	1090.3	1090.4	1089.8
140°	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1	1123.5	1124.0	1123.5
142.5°	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2	1155.4	1155.4	1154.8
145°	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7	1200.9	1201.2	1200.6
147.5°	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7	1239.9	1240.2	1239.5
150°	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5	1264.9	1265.4	1264.7
152.5°	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5	1286.9	1287.4	1286.8
155°	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7	1317.4	1318.1	1317.5
157.5°	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7	1342.5	1343.2	1342.6
160°	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3	1358.2	1359.2	1358.7
162.5°	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5	1372.9	1374.2	1373.8
165°	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8	1391.3	1392.7	1392.4
167.5°	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8	1405.4	1407.1	1406.9
170°	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9	1412.8	1414.6	1414.5
172.5°	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4	1418.1	1419.8	1419.6
175°	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5	1424.3	1426.2	1426.1
177.5°	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0	1426.3	1427.6	1427.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1483.1	1477.5	1475.9	1478.0	1475.9	1477.5	1483.1	1483.6	1484.1	1488.2	1482.5
5°	1368.3	1362.0	1365.1	1363.8	1365.1	1362.0	1368.3	1374.7	1375.9	1381.7	1385.4
7.5°	1267.4	1259.5	1251.1	1253.8	1251.1	1259.5	1267.4	1267.5	1277.4	1284.8	1289.7
10°	1196.7	1190.3	1186.5	1189.7	1186.5	1190.3	1196.7	1205.0	1208.8	1217.6	1227.2
12.5°	1137.3	1133.4	1130.1	1128.7	1130.1	1133.4	1137.3	1146.0	1154.9	1165.3	1175.9
15°	1056.2	1048.6	1045.5	1037.2	1045.5	1048.6	1056.2	1063.9	1081.1	1085.5	1101.4
17.5°	981.6	979.1	970.9	967.3	970.9	979.1	981.6	988.1	996.1	1012.4	1024.3
20°	937.4	934.9	926.6	931.7	926.6	934.9	937.4	947.0	953.3	966.6	978.1
22.5°	900.8	895.2	892.5	891.0	892.5	895.2	900.8	905.2	913.6	925.9	939.0
25°	849.1	840.8	837.6	833.8	837.6	840.8	849.1	851.6	860.5	872.6	879.5
27.5°	797.4	793.0	788.8	787.8	788.8	793.0	797.4	801.0	808.8	819.3	831.9
30°	763.9	759.5	756.3	756.3	756.3	759.5	763.9	771.5	777.2	786.8	796.3
32.5°	733.9	730.5	727.3	726.8	727.3	730.5	733.9	738.0	744.7	755.3	765.3
35°	690.2	685.1	683.9	680.0	683.9	685.1	690.2	693.3	700.3	708.0	716.2
37.5°	644.8	640.6	640.5	640.1	640.5	640.6	644.8	650.4	656.2	663.1	673.3
40°	615.8	612.6	612.0	607.6	612.0	612.6	615.8	618.4	624.8	633.7	641.2
42.5°	584.8	583.2	581.0	579.1	581.0	583.2	584.8	589.9	595.3	601.6	611.2
45°	542.7	538.3	538.3	535.1	538.3	538.3	542.7	547.2	549.8	557.3	570.1
47.5°	499.3	495.9	496.2	492.9	496.2	495.9	499.3	500.7	504.8	512.3	519.3
50°	470.3	468.4	467.7	466.5	467.7	468.4	470.3	469.7	474.7	481.8	491.3
52.5°	441.3	440.4	442.9	440.0	442.9	440.4	441.3	442.7	446.3	450.7	459.7
55°	402.3	400.4	404.2	400.4	404.2	400.4	402.3	401.0	402.3	406.8	412.5
57.5°	357.4	355.6	359.1	357.2	359.1	355.6	357.4	357.7	361.5	362.2	367.2
60°	327.9	324.2	326.0	326.7	326.0	324.2	327.9	329.2	330.4	331.1	336.2
62.5°	292.9	290.6	292.0	289.0	292.0	290.6	292.9	295.6	298.5	301.7	304.7
65°	243.4	241.5	239.0	237.7	239.0	241.5	243.4	244.7	251.7	255.5	262.4
67.5°	204.5	199.9	199.8	200.8	199.8	199.9	204.5	204.2	209.4	212.4	217.1
70°	176.0	176.0	175.4	175.4	175.4	176.0	176.0	179.9	182.4	184.9	188.1
72.5°	156.2	155.7	154.6	154.1	154.6	155.7	156.2	157.5	159.0	161.6	164.7
75°	125.8	126.5	125.2	124.6	125.2	126.5	125.8	125.8	128.4	129.0	130.3
77.5°	92.9	90.3	91.6	90.3	91.6	90.3	92.9	95.5	96.4	99.1	99.3
80°	70.5	69.9	71.8	69.9	71.8	69.9	70.5	70.5	72.5	73.7	76.9
82.5°	55.8	55.2	56.1	54.6	56.1	55.2	55.8	55.3	56.2	58.0	57.6
85°	33.7	33.0	32.4	33.0	32.4	33.0	33.7	33.0	32.4	33.0	33.7
87.5°	16.3	16.0	16.1	16.2	16.1	16.0	16.3	15.7	16.0	15.7	15.6
90°	23.2	23.9	24.6	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2
92.5°	22.7	23.0	23.3	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2
97.5°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7
100°	24.9	24.1	23.1	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7
102.5°	180.7	164.7	148.7	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1
105°	314.2	314.0	313.7	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5
107.5°	397.3	396.6	395.9	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3
110°	451.1	451.3	451.6	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.4	503.1	502.8	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1
115°	582.7	581.3	579.8	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2
117.5°	661.4	660.8	660.1	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4
120°	712.9	711.7	710.5	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8
122.5°	760.8	759.4	758.0	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9
125°	830.8	830.1	829.3	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1
127.5°	894.5	892.8	891.0	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4
130°	936.7	935.5	934.3	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2
132.5°	977.2	976.1	974.9	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3
135°	1033.5	1032.0	1030.6	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7
137.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2
140°	1122.1	1120.7	1119.3	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1
142.5°	1153.3	1151.9	1150.6	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2
145°	1199.1	1197.8	1196.4	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7
147.5°	1237.8	1236.1	1234.4	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7
150°	1262.8	1260.9	1259.1	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5
152.5°	1285.1	1283.4	1281.7	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5
155°	1315.6	1313.8	1311.9	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7
157.5°	1340.8	1338.9	1337.0	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7
160°	1356.8	1354.9	1353.1	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3
162.5°	1371.7	1369.6	1367.6	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5
165°	1390.6	1388.7	1386.8	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8
167.5°	1404.8	1402.7	1400.6	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8
170°	1412.4	1410.3	1408.2	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9
172.5°	1417.5	1415.4	1413.2	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4
175°	1424.0	1421.9	1419.8	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5
177.5°	1426.0	1424.5	1422.9	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1484.1	1489.7	1492.7	1499.8	1510.0	1515.2	1522.2	1527.3	1534.5	1543.1	1550.2
5°	1388.0	1403.3	1413.4	1429.3	1444.0	1458.6	1477.0	1490.4	1508.1	1528.4	1544.3
7.5°	1298.8	1317.8	1334.7	1355.8	1379.9	1398.7	1422.7	1447.2	1475.0	1503.9	1531.1
10°	1241.9	1260.9	1281.9	1307.9	1332.1	1357.5	1386.1	1414.7	1449.7	1482.1	1518.9
12.5°	1185.4	1206.5	1230.0	1259.1	1288.3	1320.9	1350.0	1382.2	1419.7	1461.8	1501.1
15°	1115.3	1135.7	1161.1	1185.9	1219.6	1255.2	1294.0	1336.5	1378.5	1425.5	1474.5
17.5°	1040.2	1062.6	1090.5	1119.3	1154.8	1196.5	1234.4	1281.1	1328.3	1383.1	1440.6
20°	991.4	1014.3	1047.3	1079.1	1111.6	1152.3	1197.3	1245.0	1295.2	1353.1	1417.2
22.5°	952.8	969.1	1001.6	1033.9	1071.9	1113.6	1157.7	1207.4	1262.2	1322.0	1389.3
25°	895.4	914.5	938.1	971.8	1011.1	1055.0	1099.5	1152.3	1211.9	1273.0	1344.8
27.5°	844.5	860.1	883.4	909.8	949.1	994.6	1041.9	1096.9	1158.2	1220.3	1295.8
30°	808.4	825.6	847.8	875.8	906.9	956.5	1004.8	1058.8	1121.1	1185.3	1262.8
32.5°	776.9	794.5	813.8	840.2	873.8	917.9	967.7	1020.7	1083.9	1150.2	1225.7
35°	732.8	744.9	762.6	788.7	821.7	857.4	908.2	964.1	1025.7	1094.4	1170.0
37.5°	682.2	697.8	715.5	738.1	767.1	805.6	852.9	909.5	966.6	1032.3	1101.4
40°	652.7	667.3	687.1	703.5	734.0	769.0	812.2	871.3	928.5	990.2	1053.1
42.5°	622.7	636.8	653.5	674.1	701.5	735.5	775.6	830.6	891.9	950.0	1002.7
45°	575.8	590.4	606.3	625.3	650.8	683.9	723.9	774.0	827.4	880.8	920.9
47.5°	530.9	544.6	559.6	579.2	602.6	634.5	670.3	714.7	766.5	812.0	840.6
50°	498.9	511.6	528.2	547.2	570.1	600.0	634.3	678.1	721.3	762.6	788.7
52.5°	467.4	481.6	498.1	514.6	536.5	566.4	598.2	635.9	677.1	710.8	732.3
55°	420.1	433.4	448.7	465.9	487.5	512.9	546.6	576.4	608.9	637.5	650.1
57.5°	374.5	386.1	400.5	418.3	437.7	461.4	488.1	516.8	539.7	559.9	574.3
60°	344.5	354.7	367.9	383.2	404.2	425.8	450.0	476.6	494.5	511.6	525.0
62.5°	314.0	323.6	336.5	350.2	368.6	388.7	411.8	433.4	450.7	462.3	477.7
65°	268.2	277.7	288.5	303.1	317.8	334.3	355.2	371.1	383.2	395.9	405.4
67.5°	225.6	233.5	243.8	255.3	267.6	283.5	299.7	312.9	321.2	328.8	340.3
70°	197.6	204.0	212.3	221.2	234.5	250.4	263.1	273.3	279.0	286.7	300.6
72.5°	169.2	176.5	184.3	193.2	204.0	217.4	228.5	238.7	242.4	248.5	257.4
75°	133.5	137.3	143.7	150.0	157.6	169.1	179.9	182.4	185.6	190.7	197.0
77.5°	100.9	104.4	106.9	111.1	117.2	126.4	132.1	135.9	136.6	138.5	144.8
80°	80.1	82.0	84.5	87.7	90.3	97.8	101.0	104.8	106.2	108.0	111.2
82.5°	58.7	60.7	62.1	64.8	68.9	71.9	75.1	78.9	79.2	80.6	81.2
85°	34.3	35.0	33.7	35.0	35.6	36.9	40.0	43.2	42.6	41.9	43.9
87.5°	15.8	15.6	14.8	16.0	14.6	14.8	14.4	14.6	15.2	15.8	16.5
90°	18.1	16.9	15.2	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1
92.5°	18.1	16.9	15.4	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2
95°	18.1	16.9	25.8	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2
97.5°	45.3	51.9	69.5	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6
100°	148.7	183.7	182.7	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3
102.5°	227.7	234.3	233.7	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8
105°	314.5	314.5	314.5	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4
107.5°	398.2	398.2	397.7	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1
110°	453.2	453.9	453.5	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	507.0	507.9	507.7	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2
115°	588.1	589.1	588.8	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7
117.5°	666.6	667.8	666.9	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0
120°	716.3	716.7	716.1	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6
122.5°	764.4	764.9	764.6	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4
125°	835.1	836.0	836.0	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7
127.5°	898.9	899.4	899.5	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7
130°	940.9	941.6	941.3	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2
132.5°	979.5	979.6	980.2	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8
135°	1037.2	1037.6	1038.1	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5
137.5°	1090.1	1090.1	1090.5	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5
140°	1122.6	1122.1	1122.3	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0
142.5°	1155.1	1155.0	1154.7	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3
145°	1200.4	1200.2	1200.2	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1
147.5°	1239.3	1239.1	1238.8	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2
150°	1264.0	1263.6	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6
152.5°	1286.0	1285.5	1285.1	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0
155°	1316.0	1315.3	1314.8	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5
157.5°	1340.9	1340.2	1340.2	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8
160°	1356.3	1355.4	1355.2	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7
162.5°	1370.2	1368.9	1368.6	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2
165°	1388.5	1387.1	1386.8	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4
167.5°	1402.1	1400.4	1400.1	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8
170°	1409.0	1407.1	1406.9	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5
172.5°	1414.7	1413.0	1412.6	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5
175°	1420.6	1418.7	1418.5	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0
177.5°	1423.7	1422.3	1422.1	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1555.8	1560.4	1567.0	1574.6	1580.7	1587.3	1590.9	1590.9	1593.9	1600.5	1609.2
5°	1560.2	1576.8	1592.7	1613.0	1628.9	1647.3	1661.3	1674.6	1686.7	1701.9	1717.8
7.5°	1558.9	1586.4	1615.0	1647.1	1682.4	1710.5	1739.4	1761.9	1784.4	1813.6	1836.5
10°	1553.9	1589.5	1628.2	1668.9	1713.4	1752.2	1787.1	1818.9	1849.4	1881.2	1909.8
12.5°	1544.7	1590.0	1637.4	1686.2	1742.4	1786.7	1831.9	1865.6	1901.3	1936.1	1971.3
15°	1531.0	1584.4	1641.6	1709.6	1778.2	1827.8	1872.3	1916.1	1949.2	1988.6	2022.3
17.5°	1502.7	1571.4	1643.4	1717.8	1783.7	1841.3	1887.9	1929.7	1964.8	2008.2	2053.9
20°	1485.9	1560.2	1635.2	1714.7	1777.6	1836.7	1881.8	1925.0	1968.9	2025.4	2081.4
22.5°	1462.5	1542.0	1621.5	1696.9	1763.3	1820.4	1867.1	1919.9	1977.5	2041.8	2109.3
25°	1425.5	1507.5	1586.3	1658.1	1723.0	1781.4	1844.9	1916.1	1986.1	2070.6	2167.8
27.5°	1378.6	1457.7	1528.0	1603.9	1668.3	1742.6	1821.9	1899.1	1999.9	2116.2	2237.6
30°	1343.5	1418.5	1485.2	1557.1	1630.1	1712.1	1801.1	1892.0	2012.1	2148.7	2293.0
32.5°	1302.8	1370.8	1437.0	1506.2	1590.5	1680.6	1775.2	1886.4	2029.9	2185.3	2334.7
35°	1232.3	1293.3	1357.5	1434.4	1524.0	1621.9	1742.6	1878.0	2051.5	2218.7	2352.8
37.5°	1158.3	1206.5	1271.0	1352.0	1449.7	1562.9	1699.9	1864.4	2042.7	2192.6	2249.7
40°	1101.4	1146.5	1214.5	1299.7	1396.3	1520.2	1674.0	1843.1	2022.3	2126.5	2122.1
42.5°	1045.0	1090.5	1156.0	1241.7	1342.4	1481.1	1639.4	1815.1	1966.3	2006.0	1923.3
45°	958.4	1000.9	1065.2	1151.6	1259.6	1405.2	1571.7	1740.1	1836.7	1772.5	1608.5
47.5°	870.2	911.5	971.1	1055.7	1173.7	1326.0	1483.4	1621.6	1635.2	1497.3	1300.6
50°	812.2	851.0	907.5	997.8	1112.1	1260.9	1412.8	1521.5	1487.8	1319.4	1116.6
52.5°	755.8	793.0	846.0	931.2	1048.1	1193.8	1329.4	1414.7	1336.8	1157.7	975.3
55°	672.4	708.0	761.4	839.5	945.7	1079.1	1198.0	1229.1	1114.8	934.3	786.8
57.5°	593.2	619.3	672.1	741.2	843.5	961.2	1046.4	1040.7	914.5	752.0	646.2
60°	540.9	564.4	614.6	678.1	775.3	880.8	940.6	915.2	787.4	653.3	551.6
62.5°	492.0	514.0	556.1	614.6	698.1	789.9	833.3	798.3	677.6	559.8	478.9
65°	418.2	434.1	467.7	521.8	587.3	650.8	689.6	638.1	531.3	442.3	381.3
67.5°	349.2	362.9	392.9	431.6	476.8	520.7	536.4	488.1	405.1	345.1	302.1
70°	304.4	317.2	337.5	373.7	403.6	434.7	442.3	399.1	329.9	284.1	257.4
72.5°	261.7	273.4	291.2	316.7	337.5	355.4	359.0	318.8	265.8	234.2	213.7
75°	199.6	209.7	221.2	230.7	244.0	247.2	246.0	214.8	186.2	165.3	153.8
77.5°	146.7	150.9	157.8	161.7	162.3	162.1	155.6	135.9	121.2	112.5	107.8
80°	113.2	116.3	118.2	119.4	120.1	113.7	106.8	94.7	89.6	84.5	78.8
82.5°	82.1	84.3	86.2	86.4	83.0	77.7	71.2	65.2	61.6	59.1	56.9
85°	44.5	45.1	44.5	41.3	36.9	35.0	33.7	32.4	31.8	31.1	31.1
87.5°	16.4	15.2	13.0	13.9	14.3	14.1	14.4	14.3	14.0	14.3	14.5
90°	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2
92.5°	14.9	13.6	12.3	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2
95°	59.4	58.8	58.0	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2
97.5°	126.9	128.2	129.4	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7
100°	177.0	177.7	178.4	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7
102.5°	228.7	229.6	230.5	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1
105°	311.3	312.3	313.2	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.1	396.1	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3
110°	451.8	451.8	451.8	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5





TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	504.8	505.3	505.8	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1
115°	583.8	585.1	586.2	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2
117.5°	663.9	663.9	663.8	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4
120°	714.4	714.2	714.0	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8
122.5°	760.3	761.2	762.1	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9
125°	830.3	831.9	833.6	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1
127.5°	895.9	897.1	898.2	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4
130°	936.5	937.6	938.8	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2
132.5°	977.1	978.5	979.9	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3
135°	1034.9	1036.2	1037.6	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7
137.5°	1087.6	1088.8	1090.1	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2
140°	1121.5	1122.0	1122.4	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1
142.5°	1152.6	1152.8	1153.2	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2
145°	1198.6	1199.1	1199.5	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7
147.5°	1238.1	1238.0	1238.0	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7
150°	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5
152.5°	1287.0	1286.0	1285.0	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5
155°	1318.1	1316.7	1315.3	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7
157.5°	1343.0	1342.1	1341.2	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7
160°	1359.3	1357.9	1356.4	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3
162.5°	1372.8	1371.3	1369.9	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5
165°	1390.9	1389.5	1388.1	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8
167.5°	1404.4	1403.0	1401.5	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8
170°	1411.9	1410.1	1408.5	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9
172.5°	1416.9	1415.3	1413.6	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4
175°	1422.6	1421.2	1419.8	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5
177.5°	1425.4	1424.3	1423.2	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2	1548.2
2.5°	1615.8	1615.8	1624.4	1623.9	1629.5	1627.5	1628.5
5°	1736.9	1747.8	1757.3	1763.6	1773.1	1775.7	1774.4
7.5°	1862.5	1886.5	1898.2	1914.2	1917.2	1925.6	1924.7
10°	1940.3	1963.8	1981.6	1995.6	2002.5	2011.5	2012.1
12.5°	2001.3	2021.3	2037.0	2050.0	2058.5	2061.3	2063.0
15°	2048.9	2071.2	2089.6	2108.0	2118.9	2127.1	2131.6
17.5°	2097.0	2131.4	2163.9	2188.9	2203.9	2216.6	2216.5
20°	2134.1	2173.5	2214.2	2242.8	2272.1	2284.7	2286.7
22.5°	2173.8	2234.0	2286.4	2330.8	2369.2	2382.4	2387.4
25°	2256.2	2334.9	2415.7	2477.9	2522.5	2548.5	2552.3
27.5°	2355.6	2462.3	2547.2	2604.7	2641.7	2661.0	2665.2
30°	2425.8	2524.3	2600.6	2643.9	2661.0	2663.5	2654.0
32.5°	2457.4	2530.9	2561.4	2558.9	2525.2	2502.9	2494.3
35°	2418.8	2403.6	2329.2	2240.3	2172.3	2129.1	2117.6
37.5°	2201.2	2069.7	1932.9	1798.5	1726.9	1690.5	1628.0
40°	1986.7	1799.2	1656.9	1543.7	1463.0	1398.2	1382.9
42.5°	1744.7	1551.1	1408.8	1311.9	1247.4	1203.0	1183.7
45°	1402.0	1235.5	1117.9	1043.6	994.0	961.6	947.0
47.5°	1121.4	992.5	906.8	851.7	814.0	785.8	777.9
50°	967.3	864.3	791.9	745.5	716.9	695.3	686.4
52.5°	840.2	757.1	701.4	663.1	636.0	622.6	615.2
55°	693.3	621.6	581.6	551.0	535.7	525.0	519.8
57.5°	567.0	515.2	485.9	464.8	450.7	443.8	441.3
60°	496.4	455.7	429.0	412.5	402.9	394.0	391.5
62.5°	433.8	401.8	381.2	366.7	357.2	353.4	351.8
65°	349.5	328.6	313.3	304.4	296.8	295.5	294.9
67.5°	277.9	265.5	257.6	248.3	245.6	241.1	240.3
70°	237.7	229.4	219.9	216.7	213.5	209.1	209.7
72.5°	201.6	193.3	186.9	182.6	181.5	179.6	181.2
75°	147.4	144.9	142.4	139.2	137.9	137.9	137.3
77.5°	105.3	103.1	100.3	98.4	98.0	95.3	96.4
80°	76.2	73.1	71.8	72.5	70.5	69.9	69.9
82.5°	56.4	55.3	54.1	54.1	53.7	53.2	53.6
85°	31.1	30.5	30.5	29.8	29.8	29.3	29.3
87.5°	15.2	16.0	15.2	14.8	14.9	15.6	16.2
90°	20.4	21.6	22.5	23.2	23.9	24.6	25.4
92.5°	20.4	21.6	22.3	22.7	23.0	23.3	23.6
95°	20.4	21.6	22.2	22.2	22.2	22.2	22.2
97.5°	32.1	25.4	22.2	22.2	22.2	22.2	22.2
100°	78.8	43.9	25.9	24.9	24.1	23.1	22.2
102.5°	214.5	207.9	196.6	180.7	164.7	148.7	132.8
105°	314.5	314.5	314.5	314.2	314.0	313.7	313.5
107.5°	398.4	398.4	398.0	397.3	396.6	395.9	395.3
110°	451.8	451.1	450.9	451.1	451.3	451.6	451.8



TEST NUMBER: P333732-930

CATALOG NUMBER: S125RDIW-S1270D1340U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	505.3	504.4	503.8	503.4	503.1	502.8	502.5
115°	586.2	585.3	584.1	582.7	581.3	579.8	578.5
117.5°	664.1	662.9	661.9	661.4	660.8	660.1	659.6
120°	715.3	714.9	714.0	712.9	711.7	710.5	709.4
122.5°	763.4	763.0	762.1	760.8	759.4	758.0	756.7
125°	833.2	832.3	831.4	830.8	830.1	829.3	828.7
127.5°	897.8	897.3	896.2	894.5	892.8	891.0	889.2
130°	939.5	938.8	937.8	936.7	935.5	934.3	933.2
132.5°	979.2	979.0	978.4	977.2	976.1	974.9	973.7
135°	1036.2	1035.8	1034.9	1033.5	1032.0	1030.6	1029.2
137.5°	1090.3	1090.4	1089.8	1088.6	1087.4	1086.1	1084.9
140°	1123.5	1124.0	1123.5	1122.1	1120.7	1119.3	1117.9
142.5°	1155.4	1155.4	1154.8	1153.3	1151.9	1150.6	1149.2
145°	1200.9	1201.2	1200.6	1199.1	1197.8	1196.4	1195.0
147.5°	1239.9	1240.2	1239.5	1237.8	1236.1	1234.4	1232.7
150°	1264.9	1265.4	1264.7	1262.8	1260.9	1259.1	1257.2
152.5°	1286.9	1287.4	1286.8	1285.1	1283.4	1281.7	1280.0
155°	1317.4	1318.1	1317.5	1315.6	1313.8	1311.9	1310.0
157.5°	1342.5	1343.2	1342.6	1340.8	1338.9	1337.0	1335.1
160°	1358.2	1359.2	1358.7	1356.8	1354.9	1353.1	1351.2
162.5°	1372.9	1374.2	1373.8	1371.7	1369.6	1367.6	1365.5
165°	1391.3	1392.7	1392.4	1390.6	1388.7	1386.8	1384.9
167.5°	1405.4	1407.1	1406.9	1404.8	1402.7	1400.6	1398.5
170°	1412.8	1414.6	1414.5	1412.4	1410.3	1408.2	1406.1
172.5°	1418.1	1419.8	1419.6	1417.5	1415.4	1413.2	1411.1
175°	1424.3	1426.2	1426.1	1424.0	1421.9	1419.8	1417.6
177.5°	1426.3	1427.6	1427.5	1426.0	1424.5	1422.9	1421.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0

(END OF REPORT)