

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333722-930

Luminaire Tested: **S125RDIW-S1270D470U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333722-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D470U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5504.9 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	107	107	107	107	96	96	96	86	86	86	77	77	77	72
1	103	99	95	91	98	94	90	87	85	82	80	76	74	72	68	67	65	62
2	94	87	80	75	89	82	77	72	74	70	66	67	64	61	60	58	56	52
3	86	76	69	63	81	73	66	61	66	61	56	60	55	52	54	50	48	44
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	44	41	38
5	73	61	52	46	69	58	51	45	53	47	42	48	43	39	44	39	36	33
6	67	55	46	41	64	52	45	39	48	42	37	44	38	34	40	35	32	29
7	62	50	42	36	59	48	40	35	44	37	33	40	35	31	36	32	29	26
8	58	45	37	32	55	43	36	31	40	34	29	37	31	27	33	29	26	24
9	54	42	34	29	51	40	33	28	37	31	26	34	29	25	31	27	23	21
10	51	38	31	26	48	37	30	25	34	28	24	31	26	23	29	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10869	10869	10869
5°	10895	10771	10836
10°	10812	10670	10670
15°	10683	10454	10369
20°	10519	10152	10030
25°	10326	9855	9638
30°	10086	9508	9205
35°	9842	9150	8719
40°	9613	8777	8241
45°	9334	8360	7721
50°	9055	7905	7178
55°	8731	7472	6598
60°	8407	6945	5977
65°	8023	6333	5265
70°	7585	5569	4538
75°	6977	4694	3773
80°	6148	3686	3169
85°	5187	3016	2831



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.3	2.9
10°-20°	442.3	8.0
20°-30°	641.3	11.7
30°-40°	730.9	13.3
40°-50°	712.5	12.9
50°-60°	599.7	10.9
60°-70°	420.4	7.6
70°-80°	216.1	3.9
80°-90°	55.6	1.0
90°-100°	18.1	0.3
100°-110°	111.4	2.0
110°-120°	202.1	3.7
120°-130°	259.4	4.7
130°-140°	279.0	5.1
140°-150°	261.9	4.8
150°-160°	211.8	3.8
160°-170°	137.0	2.5
170°-180°	47.3	0.9
0°-30°	1241.9	22.6
0°-40°	1972.8	35.8
0°-60°	3284.9	59.7
0°-90°	3977.0	72.2
90°-120°	331.6	6.0
90°-150°	1131.8	20.6
90°-180°	1528.0	27.8
0°-180°	5504.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1683	1683	1683	1683	1683	
5°	1680	1675	1661	1673	1672	159
15°	1598	1589	1564	1562	1551	450
25°	1449	1428	1383	1367	1352	666
35°	1248	1216	1161	1125	1106	781
45°	1022	983	915	866	845	788
55°	775	733	664	608	586	693
65°	525	480	414	365	344	520
75°	280	241	188	161	151	296
85°	70	48	41	39	38	79
90°	0	3	6	8	9	4
95°	21	19	6	8	8	27
105°	108	110	110	110	110	115
115°	204	205	206	204	202	202
125°	290	292	292	291	290	259
135°	361	363	363	362	360	278
145°	419	419	419	420	418	262
155°	461	459	460	460	458	212
165°	486	484	485	487	484	137
175°	498	496	496	498	495	47
180°	498	498	498	498	498	



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1686.0	1685.4	1684.7	1684.0	1683.3	1681.9	1679.6	1677.3	1675.1	1672.8	1675.1
5°	1680.5	1679.4	1678.2	1677.1	1675.9	1673.8	1670.7	1667.6	1664.5	1661.4	1664.2
7.5°	1663.9	1662.9	1661.8	1660.7	1659.6	1657.3	1653.5	1649.8	1646.1	1642.3	1644.3
10°	1648.7	1647.8	1647.0	1646.2	1645.3	1642.9	1638.9	1635.0	1631.0	1627.1	1627.9
12.5°	1631.4	1630.4	1629.2	1628.2	1627.1	1623.9	1618.6	1613.3	1607.9	1602.6	1603.3
15°	1597.8	1596.1	1594.5	1592.8	1591.1	1587.2	1581.3	1575.4	1569.5	1563.5	1563.3
17.5°	1559.9	1557.4	1554.8	1552.2	1549.6	1544.5	1537.1	1529.6	1522.2	1514.7	1513.3
20°	1530.5	1527.6	1524.8	1522.0	1519.1	1513.2	1504.2	1495.2	1486.1	1477.1	1475.7
22.5°	1497.9	1495.1	1492.2	1489.5	1486.6	1480.5	1471.0	1461.5	1452.0	1442.5	1439.7
25°	1449.1	1444.9	1440.6	1436.4	1432.2	1424.8	1414.4	1403.9	1393.4	1383.0	1379.3
27.5°	1393.2	1388.0	1382.9	1377.8	1372.6	1364.5	1353.2	1342.1	1330.9	1319.7	1314.6
30°	1352.5	1347.1	1341.7	1336.4	1331.1	1322.4	1310.5	1298.7	1286.8	1275.0	1268.4
32.5°	1312.9	1306.6	1300.3	1294.0	1287.8	1278.6	1266.5	1254.4	1242.3	1230.2	1223.0
35°	1248.3	1241.5	1234.7	1227.9	1221.2	1211.4	1198.7	1186.0	1173.3	1160.6	1152.3
37.5°	1185.0	1176.7	1168.5	1160.3	1151.9	1141.3	1128.2	1115.1	1102.0	1088.8	1079.0
40°	1140.2	1131.7	1123.2	1114.8	1106.4	1095.3	1081.7	1068.2	1054.6	1041.1	1030.4
42.5°	1093.5	1084.8	1076.0	1067.3	1058.7	1047.3	1033.3	1019.3	1005.3	991.2	981.0
45°	1022.0	1013.8	1005.6	997.4	989.2	977.4	961.8	946.3	930.7	915.3	903.9
47.5°	948.0	939.4	930.7	922.1	913.5	901.3	885.7	870.0	854.4	838.7	827.0
50°	901.2	891.9	882.6	873.3	864.0	851.3	835.1	819.0	802.9	786.8	774.9
52.5°	850.4	840.8	831.3	821.7	812.2	799.8	784.6	769.5	754.2	739.1	726.3
55°	775.4	766.4	757.3	748.3	739.2	726.8	711.0	695.2	679.4	663.6	650.9
57.5°	699.6	690.0	680.3	670.7	661.0	648.6	633.3	618.0	602.8	587.5	575.1
60°	650.9	640.9	631.0	621.2	611.3	598.7	583.4	568.2	552.9	537.7	525.3
62.5°	599.0	589.5	580.1	570.6	561.3	548.8	533.3	517.8	502.3	486.8	475.3
65°	525.0	515.4	505.8	496.2	486.6	474.3	459.3	444.3	429.3	414.4	403.1
67.5°	451.5	441.9	432.3	422.7	413.1	401.1	386.8	372.4	358.1	343.7	333.4
70°	401.7	392.1	382.5	372.8	363.3	351.4	337.3	323.2	309.0	294.9	286.2
72.5°	352.9	343.5	334.1	324.7	315.4	304.0	290.8	277.6	264.4	251.2	243.1
75°	279.6	271.2	262.7	254.2	245.7	235.6	223.7	211.9	200.0	188.1	181.9
77.5°	206.9	200.2	193.4	186.6	179.9	171.7	162.2	152.7	143.2	133.7	129.4
80°	165.3	158.5	151.7	144.9	138.1	130.8	122.9	115.0	107.0	99.1	96.6
82.5°	124.6	118.5	112.3	106.2	100.2	94.4	88.9	83.6	78.1	72.7	71.5
85°	70.0	64.8	59.8	54.6	49.6	46.3	44.9	43.5	42.1	40.7	40.4
87.5°	23.5	22.0	20.5	19.1	17.7	16.9	16.8	16.6	16.6	16.5	16.6
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	5.9	6.3
92.5°	5.7	5.2	4.7	4.3	3.8	3.8	4.4	4.9	5.4	5.9	6.3
95°	21.0	20.8	20.5	20.3	20.1	18.3	15.2	12.1	9.0	5.9	6.3
97.5°	43.9	44.4	44.8	45.2	45.7	42.8	36.6	30.5	24.3	18.2	15.8
100°	61.6	61.9	62.1	62.4	62.6	62.9	63.2	63.5	63.8	64.2	51.9
102.5°	79.6	79.9	80.2	80.6	80.9	81.1	81.3	81.4	81.7	81.9	79.6
105°	108.4	108.8	109.1	109.4	109.7	109.9	109.9	109.9	109.9	109.9	109.9
107.5°	138.4	138.4	138.4	138.4	138.4	138.4	138.6	138.8	138.9	139.1	139.2
110°	157.8	157.8	157.8	157.8	157.8	157.9	158.1	158.2	158.4	158.6	158.3



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	176.2	176.3	176.5	176.8	176.9	177.1	177.2	177.3	177.4	177.5	177.2
115°	203.6	204.0	204.4	204.8	205.2	205.5	205.5	205.6	205.7	205.8	205.5
117.5°	232.0	232.0	232.0	232.0	232.0	232.1	232.4	232.7	233.0	233.3	232.9
120°	249.7	249.6	249.6	249.5	249.4	249.5	249.7	250.0	250.2	250.5	250.3
122.5°	265.4	265.6	266.0	266.3	266.6	266.8	266.9	267.0	267.2	267.3	267.1
125°	289.5	290.1	290.7	291.2	291.8	292.1	292.1	292.1	292.1	292.1	291.8
127.5°	312.6	313.1	313.5	313.9	314.3	314.5	314.4	314.4	314.3	314.2	314.1
130°	326.8	327.2	327.6	328.0	328.4	328.6	328.7	328.8	328.9	329.0	328.7
132.5°	341.0	341.4	341.9	342.3	342.8	343.0	342.8	342.7	342.4	342.3	342.3
135°	361.1	361.6	362.1	362.6	363.1	363.2	363.1	362.9	362.7	362.6	362.4
137.5°	379.6	380.0	380.4	380.9	381.3	381.5	381.3	381.2	381.0	380.8	380.9
140°	391.7	391.8	392.0	392.2	392.3	392.4	392.3	392.2	392.2	392.1	392.2
142.5°	402.6	402.8	402.8	402.9	403.0	403.1	403.2	403.3	403.5	403.6	403.6
145°	418.7	418.8	419.0	419.1	419.3	419.4	419.4	419.4	419.4	419.4	419.5
147.5°	432.7	432.6	432.6	432.5	432.5	432.5	432.7	432.8	432.8	432.9	433.0
150°	441.5	441.3	441.2	441.0	440.8	440.8	441.0	441.2	441.3	441.5	441.6
152.5°	450.0	449.7	449.3	449.0	448.6	448.5	448.7	448.8	449.0	449.1	449.3
155°	461.1	460.6	460.1	459.6	459.1	458.9	459.1	459.3	459.4	459.6	459.8
157.5°	469.5	469.2	469.0	468.6	468.3	468.2	468.2	468.2	468.2	468.3	468.6
160°	475.4	474.9	474.4	473.9	473.4	473.3	473.4	473.4	473.5	473.6	473.9
162.5°	480.1	479.6	479.2	478.7	478.2	478.0	478.1	478.2	478.3	478.3	478.7
165°	486.5	486.0	485.5	485.0	484.5	484.3	484.4	484.5	484.5	484.6	485.1
167.5°	491.2	490.7	490.2	489.7	489.2	488.9	489.0	489.1	489.2	489.3	489.9
170°	493.9	493.3	492.7	492.1	491.5	491.3	491.4	491.5	491.5	491.6	492.3
172.5°	495.6	495.0	494.5	493.9	493.3	493.2	493.3	493.4	493.6	493.7	494.3
175°	497.6	497.1	496.6	496.1	495.6	495.4	495.5	495.5	495.6	495.7	496.4
177.5°	498.5	498.1	497.7	497.3	496.8	496.7	496.8	496.8	496.9	497.0	497.4
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0	1683.0
2.5°	1677.3	1679.6	1681.9	1682.9	1682.7	1682.5	1682.2	1682.0
5°	1667.0	1669.9	1672.7	1673.8	1673.2	1672.7	1672.1	1671.5
7.5°	1646.3	1648.3	1650.2	1650.9	1650.2	1649.7	1649.0	1648.5
10°	1628.7	1629.6	1630.4	1630.4	1629.6	1628.7	1627.9	1627.1
12.5°	1603.9	1604.5	1605.2	1604.8	1603.5	1602.2	1600.9	1599.6
15°	1562.9	1562.7	1562.4	1561.0	1558.4	1555.9	1553.3	1550.8
17.5°	1511.9	1510.4	1509.0	1507.3	1505.2	1503.1	1501.0	1498.9
20°	1474.2	1472.8	1471.5	1469.4	1466.9	1464.4	1461.8	1459.3
22.5°	1437.0	1434.2	1431.4	1429.0	1426.9	1424.8	1422.7	1420.7
25°	1375.7	1372.0	1368.3	1364.9	1361.8	1358.7	1355.6	1352.5
27.5°	1309.5	1304.3	1299.2	1295.1	1292.1	1289.1	1286.1	1283.1
30°	1262.0	1255.5	1249.0	1244.5	1241.9	1239.3	1236.8	1234.3
32.5°	1215.9	1208.7	1201.5	1196.3	1193.1	1189.8	1186.7	1183.4
35°	1144.2	1136.0	1127.8	1121.7	1117.8	1113.8	1109.9	1105.9
37.5°	1069.2	1059.4	1049.5	1042.7	1038.9	1035.0	1031.2	1027.4
40°	1019.6	1008.9	998.2	991.1	987.7	984.3	980.9	977.5
42.5°	970.7	960.4	950.1	942.5	937.5	932.5	927.6	922.6
45°	892.6	881.3	870.0	862.3	858.0	853.8	849.5	845.3
47.5°	815.5	803.8	792.1	784.0	779.3	774.6	769.9	765.2
50°	763.1	751.2	739.4	731.3	727.1	722.8	718.6	714.4
52.5°	713.5	700.7	687.9	679.5	675.2	671.0	666.8	662.5
55°	638.1	625.4	612.7	604.1	599.6	595.0	590.5	586.0
57.5°	562.6	550.2	537.8	529.6	525.5	521.5	517.6	513.6
60°	512.8	500.4	488.0	479.6	475.4	471.2	466.9	462.7
62.5°	463.8	452.2	440.8	432.8	428.6	424.4	420.1	415.9
65°	391.8	380.5	369.2	361.4	357.2	352.9	348.7	344.5
67.5°	323.0	312.7	302.4	295.5	292.1	288.7	285.4	281.9
70°	277.4	268.6	259.9	253.8	250.4	247.0	243.6	240.3
72.5°	235.1	227.0	218.8	213.7	211.4	209.2	206.9	204.6
75°	175.7	169.5	163.3	159.1	157.2	155.2	153.3	151.2
77.5°	125.0	120.7	116.3	113.4	111.9	110.5	109.0	107.5
80°	94.1	91.6	88.9	87.4	86.8	86.3	85.8	85.2
82.5°	70.4	69.1	68.0	67.2	66.9	66.5	66.2	65.9
85°	40.1	39.9	39.5	39.3	39.0	38.7	38.4	38.2
87.5°	16.6	16.7	16.8	16.7	16.6	16.4	16.2	16.0
90°	6.7	7.1	7.5	7.9	8.2	8.4	8.6	8.9
92.5°	6.7	7.1	7.5	7.8	7.9	8.1	8.2	8.2
95°	6.7	7.1	7.5	7.7	7.7	7.7	7.7	7.7
97.5°	13.5	11.3	8.9	7.7	7.7	7.7	7.7	7.7
100°	39.8	27.6	15.3	9.0	8.7	8.4	8.1	7.7
102.5°	77.3	74.9	72.6	68.7	63.1	57.6	51.9	46.4
105°	109.9	109.9	109.9	109.9	109.8	109.7	109.7	109.6
107.5°	139.2	139.2	139.2	139.1	138.8	138.6	138.4	138.1
110°	158.1	157.8	157.6	157.5	157.6	157.7	157.8	157.8



TEST NUMBER: P333722-930

CATALOG NUMBER: S125RDIW-S1270D470U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	176.8	176.5	176.3	176.0	175.9	175.8	175.7	175.5
115°	205.1	204.8	204.5	204.1	203.6	203.1	202.6	202.1
117.5°	232.4	232.0	231.6	231.3	231.1	230.9	230.6	230.5
120°	250.1	250.0	249.8	249.5	249.1	248.7	248.3	247.9
122.5°	266.9	266.8	266.6	266.3	265.8	265.3	264.9	264.4
125°	291.5	291.1	290.8	290.5	290.2	290.0	289.8	289.5
127.5°	313.9	313.7	313.6	313.2	312.5	311.9	311.3	310.7
130°	328.5	328.2	328.0	327.7	327.3	326.9	326.4	326.0
132.5°	342.2	342.1	342.1	341.9	341.4	341.0	340.6	340.2
135°	362.2	362.1	361.9	361.6	361.1	360.6	360.1	359.6
137.5°	380.9	381.0	381.0	380.8	380.3	379.9	379.5	379.1
140°	392.4	392.6	392.7	392.6	392.1	391.6	391.1	390.6
142.5°	403.7	403.7	403.7	403.5	403.0	402.5	402.0	401.5
145°	419.6	419.6	419.7	419.5	419.0	418.5	418.0	417.5
147.5°	433.2	433.3	433.3	433.1	432.5	431.9	431.3	430.7
150°	441.8	442.0	442.1	441.9	441.2	440.6	439.9	439.3
152.5°	449.5	449.6	449.8	449.6	449.0	448.4	447.8	447.3
155°	460.1	460.3	460.6	460.3	459.7	459.0	458.4	457.7
157.5°	468.8	469.0	469.3	469.1	468.5	467.8	467.2	466.5
160°	474.3	474.6	474.9	474.7	474.1	473.4	472.8	472.1
162.5°	479.2	479.7	480.1	480.0	479.3	478.6	477.8	477.1
165°	485.7	486.2	486.7	486.6	485.9	485.2	484.5	483.9
167.5°	490.5	491.1	491.6	491.6	490.8	490.1	489.3	488.6
170°	492.9	493.7	494.3	494.2	493.5	492.8	492.0	491.3
172.5°	494.9	495.5	496.1	496.0	495.3	494.6	493.8	493.1
175°	497.0	497.7	498.3	498.3	497.6	496.8	496.1	495.4
177.5°	497.9	498.3	498.8	498.8	498.2	497.7	497.2	496.7
180°	497.6	497.6	497.6	497.6	497.6	497.6	497.6	497.6

(END OF REPORT)