

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333652-930

Luminaire Tested: **S125RDIW-S375D1340U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333652-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1340U930-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5564.8 lumens
Efficiency: N/A
Efficacy: 119.4 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 46.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30
1	92	87	84	81	81	78	75	72	59	57	55	42	41	40	27	26	25
2	83	77	71	66	74	68	63	59	52	49	46	37	35	34	24	23	22
3	76	67	60	55	67	60	54	50	46	42	39	33	31	29	21	20	19
4	70	60	52	46	61	53	47	42	41	36	33	29	27	24	19	17	16
5	64	53	45	40	56	47	41	36	36	32	28	26	23	21	17	15	14
6	59	47	40	34	52	42	36	31	33	28	25	24	21	18	15	14	12
7	54	43	35	30	48	38	32	27	30	25	22	22	18	16	14	12	11
8	50	38	31	26	44	34	28	24	27	22	19	20	17	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	19	22	18	15	17	14	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	2964	2964	2964	2964
5°	3409	2968	2621	2968
10°	3912	2952	2313	2952
15°	4225	2923	2055	2923
20°	4658	2887	1898	2887
25°	5392	2840	1762	2840
30°	5867	2791	1672	2791
35°	4949	2734	1589	2734
40°	3456	2632	1518	2632
45°	2564	2493	1449	2493
50°	2045	2349	1390	2349
55°	1735	2170	1337	2170
60°	1498	2010	1252	2010
65°	1336	1837	1076	1837
70°	1175	1682	982	1682
75°	1016	1457	921	1457
80°	770	1224	770	1224
85°	637	963	726	963



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.0	0.8
10°-20°	129.0	2.3
20°-30°	204.5	3.7
30°-40°	246.6	4.4
40°-50°	220.2	4.0
50°-60°	168.9	3.0
60°-70°	109.7	2.0
70°-80°	53.3	1.0
80°-90°	15.7	0.3
90°-100°	51.7	0.9
100°-110°	318.9	5.7
110°-120°	578.4	10.4
120°-130°	742.3	13.3
130°-140°	798.4	14.3
140°-150°	749.4	13.5
150°-160°	606.3	10.9
160°-170°	392.1	7.0
170°-180°	135.2	2.4
0°-30°	377.5	6.8
0°-40°	624.0	11.2
0°-60°	1013.1	18.2
0°-90°	1191.9	21.4
90°-120°	949.1	17.1
90°-150°	3239.3	58.2
90°-180°	4373.0	78.6
0°-180°	5564.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	459	459	459	459	459	
5°	526	458	404	458	526	53
15°	632	437	307	437	632	181
25°	757	399	247	399	757	347
35°	628	347	202	347	628	379
45°	281	273	159	273	281	224
55°	154	193	119	193	154	140
65°	87	120	70	120	87	87
75°	41	58	37	58	41	43
85°	9	13	10	13	9	11
90°	25	1	25	1	25	11
95°	22	60	22	60	22	18
105°	314	310	314	310	314	283
115°	578	583	578	583	578	574
125°	829	829	829	829	829	737
135°	1029	1034	1029	1034	1029	794
145°	1195	1198	1195	1198	1195	746
155°	1310	1320	1310	1320	1310	604
165°	1385	1392	1385	1392	1385	391
175°	1418	1424	1418	1424	1418	135
180°	1424	1424	1424	1424	1424	



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	482.7	482.4	483.1	481.4	481.5	479.0	479.0	477.0	474.4	472.5	471.6
5°	525.9	526.4	525.6	522.8	520.9	518.0	514.9	509.2	504.5	499.9	496.4
7.5°	570.5	570.8	568.3	567.4	562.6	559.2	552.1	544.4	537.6	528.9	522.3
10°	596.5	596.2	593.6	591.5	587.4	582.1	575.1	566.1	557.7	548.2	539.2
12.5°	611.5	611.0	610.2	607.6	603.8	599.2	593.2	584.3	573.9	563.6	553.0
15°	631.9	630.6	628.1	624.8	619.4	613.9	607.4	599.5	589.5	577.8	568.0
17.5°	657.0	657.0	653.3	648.8	641.4	631.8	621.6	608.9	595.3	582.4	572.0
20°	677.8	677.3	673.5	664.8	656.3	644.2	632.6	616.9	600.4	583.6	570.6
22.5°	707.7	706.2	702.3	690.9	677.8	662.2	644.3	625.3	605.2	586.2	569.1
25°	756.6	755.5	747.7	734.5	716.1	692.1	668.8	642.6	613.8	588.7	568.0
27.5°	790.0	788.8	783.0	772.1	755.0	729.9	698.3	663.2	627.3	592.8	563.0
30°	786.7	789.5	788.8	783.7	770.9	748.3	719.1	679.7	636.9	596.5	560.8
32.5°	739.4	741.9	748.5	758.6	759.3	750.2	728.4	692.0	647.8	601.7	559.1
35°	627.7	631.1	643.9	664.1	690.5	712.5	717.0	697.4	657.6	608.1	556.7
37.5°	482.6	501.1	511.9	533.1	573.0	613.5	652.5	666.8	650.0	605.4	552.7
40°	409.9	414.4	433.7	457.6	491.1	533.3	588.9	629.0	630.3	599.5	546.3
42.5°	350.8	356.6	369.7	388.9	417.6	459.7	517.1	570.1	594.6	582.9	538.0
45°	280.7	285.0	294.6	309.3	331.3	366.2	415.6	476.8	525.4	544.5	515.8
47.5°	230.6	232.9	241.2	252.5	268.8	294.2	332.4	385.6	443.8	484.7	480.7
50°	203.5	206.1	212.5	220.9	234.7	256.2	286.7	331.0	391.1	441.0	451.0
52.5°	182.4	184.6	188.6	196.6	207.9	224.4	249.1	289.1	343.2	396.2	419.4
55°	154.1	155.6	158.8	163.3	172.4	184.3	205.5	233.3	277.0	330.4	364.4
57.5°	130.9	131.6	133.6	137.8	144.1	152.7	168.1	191.5	222.9	271.1	308.5
60°	116.0	116.8	119.4	122.3	127.2	135.1	147.2	163.5	193.6	233.4	271.3
62.5°	104.3	104.8	105.9	108.7	113.0	119.1	128.6	141.9	165.9	200.9	236.6
65°	87.4	87.6	88.0	90.3	92.9	97.4	103.6	113.0	131.1	157.5	189.1
67.5°	71.2	71.5	72.8	73.6	76.3	78.7	82.3	89.5	102.3	120.1	144.7
70°	62.2	62.0	63.3	64.2	65.1	68.0	70.4	76.3	84.2	97.8	118.3
72.5°	53.7	53.2	53.8	54.1	55.4	57.3	59.8	63.3	69.5	78.8	94.5
75°	40.7	40.8	40.8	41.3	42.2	43.0	43.7	45.6	49.0	55.2	63.7
77.5°	28.5	28.3	29.0	29.2	29.8	30.6	31.2	32.0	33.3	35.9	40.3
80°	20.7	20.7	20.9	21.4	21.3	21.7	22.6	23.4	25.0	26.6	28.0
82.5°	15.9	15.7	15.9	16.1	16.0	16.4	16.7	16.9	17.5	18.3	19.3
85°	8.6	8.6	8.9	8.9	9.0	9.0	9.2	9.2	9.2	9.5	9.6
87.5°	8.4	8.1	7.8	7.7	7.7	7.7	7.4	7.0	6.8	6.5	6.4
90°	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2	18.1	16.9	15.2
92.5°	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2	18.1	16.9	15.4
95°	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2	18.1	16.9	25.8
97.5°	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7	45.3	51.9	69.5
100°	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7	148.7	183.7	182.7
102.5°	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1	227.7	234.3	233.7
105°	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3	398.2	398.2	397.7
110°	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5	453.2	453.9	453.5



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1	507.0	507.9	507.7
115°	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2	588.1	589.1	588.8
117.5°	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4	666.6	667.8	666.9
120°	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8	716.3	716.7	716.1
122.5°	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9	764.4	764.9	764.6
125°	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1	835.1	836.0	836.0
127.5°	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4	898.9	899.4	899.5
130°	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2	940.9	941.6	941.3
132.5°	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3	979.5	979.6	980.2
135°	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7	1037.2	1037.6	1038.1
137.5°	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2	1090.1	1090.1	1090.5
140°	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1	1122.6	1122.1	1122.3
142.5°	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2	1155.1	1155.0	1154.7
145°	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7	1200.4	1200.2	1200.2
147.5°	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7	1239.3	1239.1	1238.8
150°	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5	1264.0	1263.6	1263.1
152.5°	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5	1286.0	1285.5	1285.1
155°	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7	1316.0	1315.3	1314.8
157.5°	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7	1340.9	1340.2	1340.2
160°	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3	1356.3	1355.4	1355.2
162.5°	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5	1370.2	1368.9	1368.6
165°	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8	1388.5	1387.1	1386.8
167.5°	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8	1402.1	1400.4	1400.1
170°	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9	1409.0	1407.1	1406.9
172.5°	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4	1414.7	1413.0	1412.6
175°	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5	1420.6	1418.7	1418.5
177.5°	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0	1423.7	1422.3	1422.1
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	471.6	470.5	468.6	466.8	464.5	462.5	461.1	459.5	457.4	454.9	452.7
5°	492.4	488.3	482.8	478.1	472.1	467.4	462.5	457.8	453.1	447.0	441.7
7.5°	515.6	507.0	498.7	488.2	478.7	470.3	462.1	453.9	445.8	437.2	429.0
10°	529.8	519.3	507.9	494.7	482.7	471.2	460.6	450.2	439.3	429.7	419.4
12.5°	543.0	529.6	516.5	499.9	485.3	471.3	457.9	445.0	433.3	420.9	409.7
15°	555.0	541.8	527.1	506.8	486.6	469.6	453.8	437.1	422.6	408.6	396.2
17.5°	559.6	545.8	528.7	509.2	487.1	465.8	445.4	427.1	409.9	393.7	379.8
20°	557.8	544.5	526.9	508.3	484.7	462.5	440.4	420.1	401.0	383.9	369.1
22.5°	553.4	539.6	522.7	503.0	480.6	457.1	433.5	411.8	391.9	374.1	357.9
25°	546.9	528.1	510.7	491.5	470.2	446.9	422.6	398.6	377.3	359.2	341.5
27.5°	540.1	516.6	494.5	475.4	452.9	432.1	408.6	384.1	361.7	343.3	325.1
30°	533.9	507.5	483.2	461.5	440.3	420.4	398.3	374.3	351.3	332.3	313.9
32.5°	526.2	498.1	471.5	446.5	425.9	406.3	386.2	363.3	341.0	321.3	302.6
35°	516.6	480.8	451.8	425.2	402.4	383.4	365.3	346.8	324.4	304.0	285.8
37.5°	503.9	463.3	429.7	400.8	376.7	357.7	343.3	326.4	306.0	286.6	269.6
40°	496.2	450.6	413.9	385.2	360.0	339.8	326.4	312.2	293.5	275.2	258.3
42.5°	486.0	439.0	397.9	368.1	342.7	323.3	309.7	297.3	281.6	264.4	246.2
45°	465.9	416.5	373.4	341.4	315.8	296.7	284.1	273.0	261.1	245.2	229.4
47.5°	439.8	393.1	347.9	312.9	287.9	270.2	258.0	249.2	240.7	227.2	211.9
50°	418.8	373.7	329.7	295.8	269.0	252.3	240.8	233.8	226.1	213.9	201.0
52.5°	394.0	353.8	310.7	276.1	250.8	235.1	224.0	217.0	210.7	200.7	188.5
55°	355.1	319.8	280.3	248.8	225.7	209.9	199.3	192.7	189.0	180.5	170.9
57.5°	310.1	284.9	250.1	219.7	199.2	183.6	175.9	170.2	166.0	160.0	153.2
60°	278.8	261.1	229.8	201.0	182.1	167.3	160.3	155.6	151.6	146.6	141.3
62.5°	247.0	234.2	206.9	182.1	164.9	152.4	145.9	141.6	137.1	133.6	128.5
65°	204.4	192.9	174.1	154.7	138.7	128.7	123.9	120.2	117.4	113.6	110.0
67.5°	159.0	154.3	141.3	127.9	116.4	107.5	103.5	100.9	97.5	95.2	92.8
70°	131.1	128.8	119.6	110.8	100.0	94.0	90.3	89.1	85.0	82.7	81.0
72.5°	106.4	105.3	100.0	93.9	86.3	81.0	77.6	76.3	73.6	71.8	70.8
75°	72.9	73.3	72.3	68.4	65.6	62.2	59.2	58.4	56.5	55.0	54.1
77.5°	46.1	48.0	48.1	47.9	46.8	44.8	43.5	42.9	41.1	40.5	40.3
80°	31.6	33.8	35.6	35.4	35.1	34.5	33.5	32.9	32.0	31.5	31.1
82.5°	21.1	23.0	24.6	25.6	25.5	24.9	24.4	24.1	23.9	23.5	23.4
85°	9.9	10.4	10.9	12.2	13.2	13.4	13.2	13.0	12.5	12.6	12.8
87.5°	6.2	5.9	5.7	5.3	4.8	5.2	5.2	5.1	5.1	5.2	5.2
90°	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1	2.9	4.8	6.7
92.5°	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2	14.9	13.6	12.3
95°	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2	59.4	58.8	58.0
97.5°	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6	126.9	128.2	129.4
100°	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3	177.0	177.7	178.4
102.5°	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8	228.7	229.6	230.5
105°	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4	311.3	312.3	313.2
107.5°	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1	396.1	396.1	396.1
110°	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8	451.8	451.8	451.8



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2	504.8	505.3	505.8
115°	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7	583.8	585.1	586.2
117.5°	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0	663.9	663.9	663.8
120°	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6	714.4	714.2	714.0
122.5°	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4	760.3	761.2	762.1
125°	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7	830.3	831.9	833.6
127.5°	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7	895.9	897.1	898.2
130°	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2	936.5	937.6	938.8
132.5°	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8	977.1	978.5	979.9
135°	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5	1034.9	1036.2	1037.6
137.5°	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5	1087.6	1088.8	1090.1
140°	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0	1121.5	1122.0	1122.4
142.5°	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3	1152.6	1152.8	1153.2
145°	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1	1198.6	1199.1	1199.5
147.5°	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2	1238.1	1238.0	1238.0
150°	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1263.1	1262.7	1262.2
152.5°	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0	1287.0	1286.0	1285.0
155°	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5	1318.1	1316.7	1315.3
157.5°	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8	1343.0	1342.1	1341.2
160°	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7	1359.3	1357.9	1356.4
162.5°	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2	1372.8	1371.3	1369.9
165°	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4	1390.9	1389.5	1388.1
167.5°	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8	1404.4	1403.0	1401.5
170°	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5	1411.9	1410.1	1408.5
172.5°	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5	1416.9	1415.3	1413.6
175°	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0	1422.6	1421.2	1419.8
177.5°	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5	1425.4	1424.3	1423.2
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	451.2	449.1	447.6	444.6	442.5	441.6	439.9	439.4	441.2	439.9	439.8
5°	437.8	432.4	428.0	423.7	419.0	416.0	411.4	410.7	409.5	407.9	407.5
7.5°	421.8	414.6	409.0	401.9	395.7	390.6	385.0	382.3	380.8	378.6	375.7
10°	410.9	402.4	394.8	387.7	380.0	373.7	368.1	363.8	360.9	358.3	357.2
12.5°	400.1	391.5	381.9	373.2	364.6	357.7	351.4	348.5	345.4	342.3	339.7
15°	383.5	372.1	361.5	351.6	344.2	336.6	330.6	326.4	321.8	320.4	315.4
17.5°	365.9	354.7	342.3	331.8	323.3	315.0	308.3	303.6	300.1	295.2	292.9
20°	354.9	341.5	329.5	319.8	310.5	300.7	293.9	289.9	286.6	282.6	280.7
22.5°	343.2	330.1	317.7	306.5	296.9	287.2	282.4	278.3	274.5	270.8	268.3
25°	325.9	312.7	299.7	288.0	278.1	271.1	265.5	260.7	258.7	255.1	252.4
27.5°	308.8	294.8	281.4	269.7	261.9	254.9	250.3	246.6	242.9	239.8	237.4
30°	297.8	283.6	268.8	259.6	251.3	244.8	239.6	236.0	233.3	230.4	228.7
32.5°	286.8	272.1	259.0	249.1	241.2	235.5	230.3	226.8	223.9	220.8	218.7
35°	269.2	254.1	243.6	233.8	226.1	220.8	217.2	212.3	209.9	207.6	205.5
37.5°	252.8	238.8	227.4	218.8	212.1	206.8	202.2	199.6	196.6	194.5	192.8
40°	240.8	228.0	217.6	208.6	203.7	197.8	193.5	190.0	187.8	185.2	183.3
42.5°	229.9	218.0	207.9	199.8	193.7	188.7	184.6	181.2	178.3	176.4	174.9
45°	214.6	202.7	192.9	185.4	179.7	175.0	170.6	169.0	165.2	163.0	162.2
47.5°	198.7	188.1	178.6	171.7	165.9	161.4	157.4	153.9	151.8	149.6	148.4
50°	188.0	177.8	169.0	162.2	156.5	151.6	147.9	145.6	142.8	140.7	139.3
52.5°	177.3	167.9	159.1	152.5	147.7	142.8	138.5	136.3	133.6	132.3	131.3
55°	162.0	152.1	144.5	138.1	133.0	128.5	124.5	122.3	120.6	119.3	118.9
57.5°	144.7	136.8	129.8	124.0	118.7	114.5	111.0	108.8	107.4	107.1	106.0
60°	133.4	126.2	119.8	113.6	109.1	105.1	102.1	99.6	98.2	98.0	97.6
62.5°	122.1	115.2	109.3	103.8	99.7	96.0	93.0	90.3	89.4	88.5	87.6
65°	105.3	99.1	94.2	89.8	85.5	82.3	79.5	77.8	75.7	74.6	72.6
67.5°	88.9	84.1	79.3	75.7	72.2	69.2	66.9	64.3	62.9	62.0	60.6
70°	78.0	74.2	69.5	65.6	62.9	60.5	58.6	55.8	54.8	54.1	53.3
72.5°	67.8	64.4	60.5	57.2	54.6	52.3	50.1	48.8	47.9	47.1	46.7
75°	53.3	50.1	46.7	44.4	42.6	40.7	39.5	38.6	38.2	38.1	37.3
77.5°	39.1	37.4	34.7	32.9	31.7	30.9	29.9	29.4	29.4	28.5	28.3
80°	29.9	29.0	26.7	26.0	25.0	24.3	23.7	22.8	21.9	21.4	20.9
82.5°	22.3	21.4	20.4	19.2	18.4	17.9	17.4	17.0	17.2	16.6	16.4
85°	11.9	10.9	10.5	10.4	9.9	10.4	10.2	9.9	9.8	9.6	9.8
87.5°	5.5	5.9	6.0	6.6	6.5	7.0	7.3	7.3	7.6	7.7	7.8
90°	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2	20.4	21.6	22.5
92.5°	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2	20.4	21.6	22.3
95°	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2	20.4	21.6	22.2
97.5°	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7	32.1	25.4	22.2
100°	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7	78.8	43.9	25.9
102.5°	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1	214.5	207.9	196.6
105°	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3	398.4	398.4	398.0
110°	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5	451.8	451.1	450.9



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1	505.3	504.4	503.8
115°	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2	586.2	585.3	584.1
117.5°	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4	664.1	662.9	661.9
120°	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8	715.3	714.9	714.0
122.5°	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9	763.4	763.0	762.1
125°	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1	833.2	832.3	831.4
127.5°	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4	897.8	897.3	896.2
130°	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2	939.5	938.8	937.8
132.5°	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3	979.2	979.0	978.4
135°	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7	1036.2	1035.8	1034.9
137.5°	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2	1090.3	1090.4	1089.8
140°	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1	1123.5	1124.0	1123.5
142.5°	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2	1155.4	1155.4	1154.8
145°	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7	1200.9	1201.2	1200.6
147.5°	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7	1239.9	1240.2	1239.5
150°	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5	1264.9	1265.4	1264.7
152.5°	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5	1286.9	1287.4	1286.8
155°	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7	1317.4	1318.1	1317.5
157.5°	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7	1342.5	1343.2	1342.6
160°	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3	1358.2	1359.2	1358.7
162.5°	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5	1372.9	1374.2	1373.8
165°	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8	1391.3	1392.7	1392.4
167.5°	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8	1405.4	1407.1	1406.9
170°	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9	1412.8	1414.6	1414.5
172.5°	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4	1418.1	1419.8	1419.6
175°	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5	1424.3	1426.2	1426.1
177.5°	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0	1426.3	1427.6	1427.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.6	438.0	437.5	438.1	437.5	438.0	439.6	439.8	439.9	441.2	439.4
5°	405.6	403.7	404.6	404.3	404.6	403.7	405.6	407.5	407.9	409.5	410.7
7.5°	375.7	373.3	370.9	371.6	370.9	373.3	375.7	375.7	378.6	380.8	382.3
10°	354.7	352.9	351.7	352.7	351.7	352.9	354.7	357.2	358.3	360.9	363.8
12.5°	337.1	336.0	335.0	334.6	335.0	336.0	337.1	339.7	342.3	345.4	348.5
15°	313.1	310.9	309.9	307.4	309.9	310.9	313.1	315.4	320.4	321.8	326.4
17.5°	291.0	290.2	287.8	286.7	287.8	290.2	291.0	292.9	295.2	300.1	303.6
20°	277.9	277.1	274.7	276.1	274.7	277.1	277.9	280.7	282.6	286.6	289.9
22.5°	267.0	265.4	264.6	264.2	264.6	265.4	267.0	268.3	270.8	274.5	278.3
25°	251.7	249.2	248.3	247.2	248.3	249.2	251.7	252.4	255.1	258.7	260.7
27.5°	236.4	235.1	233.8	233.5	233.8	235.1	236.4	237.4	239.8	242.9	246.6
30°	226.4	225.1	224.2	224.2	224.2	225.1	226.4	228.7	230.4	233.3	236.0
32.5°	217.5	216.5	215.6	215.4	215.6	216.5	217.5	218.7	220.8	223.9	226.8
35°	204.6	203.1	202.7	201.5	202.7	203.1	204.6	205.5	207.6	209.9	212.3
37.5°	191.1	189.9	189.9	189.7	189.9	189.9	191.1	192.8	194.5	196.6	199.6
40°	182.5	181.6	181.4	180.1	181.4	181.6	182.5	183.3	185.2	187.8	190.0
42.5°	173.3	172.8	172.2	171.6	172.2	172.8	173.3	174.9	176.4	178.3	181.2
45°	160.9	159.6	159.6	158.7	159.6	159.6	160.9	162.2	163.0	165.2	169.0
47.5°	148.0	147.0	147.1	146.1	147.1	147.0	148.0	148.4	149.6	151.8	153.9
50°	139.4	138.8	138.7	138.3	138.7	138.8	139.4	139.3	140.7	142.8	145.6
52.5°	130.9	130.5	131.3	130.4	131.3	130.5	130.9	131.3	132.3	133.6	136.3
55°	119.3	118.7	119.8	118.7	119.8	118.7	119.3	118.9	119.3	120.6	122.3
57.5°	106.0	105.4	106.5	105.9	106.5	105.4	106.0	106.0	107.1	107.4	108.8
60°	97.2	96.0	96.6	96.9	96.6	96.0	97.2	97.6	98.0	98.2	99.6
62.5°	86.8	86.1	86.6	85.7	86.6	86.1	86.8	87.6	88.5	89.4	90.3
65°	72.2	71.6	70.8	70.4	70.8	71.6	72.2	72.6	74.6	75.7	77.8
67.5°	60.7	59.3	59.2	59.5	59.2	59.3	60.7	60.6	62.0	62.9	64.3
70°	52.2	52.2	52.0	52.0	52.0	52.2	52.2	53.3	54.1	54.8	55.8
72.5°	46.3	46.1	45.8	45.7	45.8	46.1	46.3	46.7	47.1	47.9	48.8
75°	37.3	37.5	37.1	36.9	37.1	37.5	37.3	37.3	38.1	38.2	38.6
77.5°	27.6	26.7	27.1	26.7	27.1	26.7	27.6	28.3	28.5	29.4	29.4
80°	20.9	20.7	21.3	20.7	21.3	20.7	20.9	20.9	21.4	21.9	22.8
82.5°	16.6	16.4	16.6	16.2	16.6	16.4	16.6	16.4	16.6	17.2	17.0
85°	9.9	9.8	9.6	9.8	9.6	9.8	9.9	9.8	9.6	9.8	9.9
87.5°	8.1	8.1	8.2	8.4	8.2	8.1	8.1	7.8	7.7	7.6	7.3
90°	23.2	23.9	24.6	25.4	24.6	23.9	23.2	22.5	21.6	20.4	19.2
92.5°	22.7	23.0	23.3	23.6	23.3	23.0	22.7	22.3	21.6	20.4	19.2
95°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	21.6	20.4	19.2
97.5°	22.2	22.2	22.2	22.2	22.2	22.2	22.2	22.2	25.4	32.1	38.7
100°	24.9	24.1	23.1	22.2	23.1	24.1	24.9	25.9	43.9	78.8	113.7
102.5°	180.7	164.7	148.7	132.8	148.7	164.7	180.7	196.6	207.9	214.5	221.1
105°	314.2	314.0	313.7	313.5	313.7	314.0	314.2	314.5	314.5	314.5	314.5
107.5°	397.3	396.6	395.9	395.3	395.9	396.6	397.3	398.0	398.4	398.4	398.3
110°	451.1	451.3	451.6	451.8	451.6	451.3	451.1	450.9	451.1	451.8	452.5



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	503.4	503.1	502.8	502.5	502.8	503.1	503.4	503.8	504.4	505.3	506.1
115°	582.7	581.3	579.8	578.5	579.8	581.3	582.7	584.1	585.3	586.2	587.2
117.5°	661.4	660.8	660.1	659.6	660.1	660.8	661.4	661.9	662.9	664.1	665.4
120°	712.9	711.7	710.5	709.4	710.5	711.7	712.9	714.0	714.9	715.3	715.8
122.5°	760.8	759.4	758.0	756.7	758.0	759.4	760.8	762.1	763.0	763.4	763.9
125°	830.8	830.1	829.3	828.7	829.3	830.1	830.8	831.4	832.3	833.2	834.1
127.5°	894.5	892.8	891.0	889.2	891.0	892.8	894.5	896.2	897.3	897.8	898.4
130°	936.7	935.5	934.3	933.2	934.3	935.5	936.7	937.8	938.8	939.5	940.2
132.5°	977.2	976.1	974.9	973.7	974.9	976.1	977.2	978.4	979.0	979.2	979.3
135°	1033.5	1032.0	1030.6	1029.2	1030.6	1032.0	1033.5	1034.9	1035.8	1036.2	1036.7
137.5°	1088.6	1087.4	1086.1	1084.9	1086.1	1087.4	1088.6	1089.8	1090.4	1090.3	1090.2
140°	1122.1	1120.7	1119.3	1117.9	1119.3	1120.7	1122.1	1123.5	1124.0	1123.5	1123.1
142.5°	1153.3	1151.9	1150.6	1149.2	1150.6	1151.9	1153.3	1154.8	1155.4	1155.4	1155.2
145°	1199.1	1197.8	1196.4	1195.0	1196.4	1197.8	1199.1	1200.6	1201.2	1200.9	1200.7
147.5°	1237.8	1236.1	1234.4	1232.7	1234.4	1236.1	1237.8	1239.5	1240.2	1239.9	1239.7
150°	1262.8	1260.9	1259.1	1257.2	1259.1	1260.9	1262.8	1264.7	1265.4	1264.9	1264.5
152.5°	1285.1	1283.4	1281.7	1280.0	1281.7	1283.4	1285.1	1286.8	1287.4	1286.9	1286.5
155°	1315.6	1313.8	1311.9	1310.0	1311.9	1313.8	1315.6	1317.5	1318.1	1317.4	1316.7
157.5°	1340.8	1338.9	1337.0	1335.1	1337.0	1338.9	1340.8	1342.6	1343.2	1342.5	1341.7
160°	1356.8	1354.9	1353.1	1351.2	1353.1	1354.9	1356.8	1358.7	1359.2	1358.2	1357.3
162.5°	1371.7	1369.6	1367.6	1365.5	1367.6	1369.6	1371.7	1373.8	1374.2	1372.9	1371.5
165°	1390.6	1388.7	1386.8	1384.9	1386.8	1388.7	1390.6	1392.4	1392.7	1391.3	1389.8
167.5°	1404.8	1402.7	1400.6	1398.5	1400.6	1402.7	1404.8	1406.9	1407.1	1405.4	1403.8
170°	1412.4	1410.3	1408.2	1406.1	1408.2	1410.3	1412.4	1414.5	1414.6	1412.8	1410.9
172.5°	1417.5	1415.4	1413.2	1411.1	1413.2	1415.4	1417.5	1419.6	1419.8	1418.1	1416.4
175°	1424.0	1421.9	1419.8	1417.6	1419.8	1421.9	1424.0	1426.1	1426.2	1424.3	1422.5
177.5°	1426.0	1424.5	1422.9	1421.5	1422.9	1424.5	1426.0	1427.5	1427.6	1426.3	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	439.9	441.6	442.5	444.6	447.6	449.1	451.2	452.7	454.9	457.4	459.5
5°	411.4	416.0	419.0	423.7	428.0	432.4	437.8	441.7	447.0	453.1	457.8
7.5°	385.0	390.6	395.7	401.9	409.0	414.6	421.8	429.0	437.2	445.8	453.9
10°	368.1	373.7	380.0	387.7	394.8	402.4	410.9	419.4	429.7	439.3	450.2
12.5°	351.4	357.7	364.6	373.2	381.9	391.5	400.1	409.7	420.9	433.3	445.0
15°	330.6	336.6	344.2	351.6	361.5	372.1	383.5	396.2	408.6	422.6	437.1
17.5°	308.3	315.0	323.3	331.8	342.3	354.7	365.9	379.8	393.7	409.9	427.1
20°	293.9	300.7	310.5	319.8	329.5	341.5	354.9	369.1	383.9	401.0	420.1
22.5°	282.4	287.2	296.9	306.5	317.7	330.1	343.2	357.9	374.1	391.9	411.8
25°	265.5	271.1	278.1	288.0	299.7	312.7	325.9	341.5	359.2	377.3	398.6
27.5°	250.3	254.9	261.9	269.7	281.4	294.8	308.8	325.1	343.3	361.7	384.1
30°	239.6	244.8	251.3	259.6	268.8	283.6	297.8	313.9	332.3	351.3	374.3
32.5°	230.3	235.5	241.2	249.1	259.0	272.1	286.8	302.6	321.3	341.0	363.3
35°	217.2	220.8	226.1	233.8	243.6	254.1	269.2	285.8	304.0	324.4	346.8
37.5°	202.2	206.8	212.1	218.8	227.4	238.8	252.8	269.6	286.6	306.0	326.4
40°	193.5	197.8	203.7	208.6	217.6	228.0	240.8	258.3	275.2	293.5	312.2
42.5°	184.6	188.7	193.7	199.8	207.9	218.0	229.9	246.2	264.4	281.6	297.3
45°	170.6	175.0	179.7	185.4	192.9	202.7	214.6	229.4	245.2	261.1	273.0
47.5°	157.4	161.4	165.9	171.7	178.6	188.1	198.7	211.9	227.2	240.7	249.2
50°	147.9	151.6	156.5	162.2	169.0	177.8	188.0	201.0	213.9	226.1	233.8
52.5°	138.5	142.8	147.7	152.5	159.1	167.9	177.3	188.5	200.7	210.7	217.0
55°	124.5	128.5	133.0	138.1	144.5	152.1	162.0	170.9	180.5	189.0	192.7
57.5°	111.0	114.5	118.7	124.0	129.8	136.8	144.7	153.2	160.0	166.0	170.2
60°	102.1	105.1	109.1	113.6	119.8	126.2	133.4	141.3	146.6	151.6	155.6
62.5°	93.0	96.0	99.7	103.8	109.3	115.2	122.1	128.5	133.6	137.1	141.6
65°	79.5	82.3	85.5	89.8	94.2	99.1	105.3	110.0	113.6	117.4	120.2
67.5°	66.9	69.2	72.2	75.7	79.3	84.1	88.9	92.8	95.2	97.5	100.9
70°	58.6	60.5	62.9	65.6	69.5	74.2	78.0	81.0	82.7	85.0	89.1
72.5°	50.1	52.3	54.6	57.2	60.5	64.4	67.8	70.8	71.8	73.6	76.3
75°	39.5	40.7	42.6	44.4	46.7	50.1	53.3	54.1	55.0	56.5	58.4
77.5°	29.9	30.9	31.7	32.9	34.7	37.4	39.1	40.3	40.5	41.1	42.9
80°	23.7	24.3	25.0	26.0	26.7	29.0	29.9	31.1	31.5	32.0	32.9
82.5°	17.4	17.9	18.4	19.2	20.4	21.4	22.3	23.4	23.5	23.9	24.1
85°	10.2	10.4	9.9	10.4	10.5	10.9	11.9	12.8	12.6	12.5	13.0
87.5°	7.3	7.0	6.5	6.6	6.0	5.9	5.5	5.2	5.2	5.1	5.1
90°	18.1	16.9	15.2	13.6	12.0	10.4	8.6	6.7	4.8	2.9	1.1
92.5°	18.1	16.9	15.4	13.9	12.6	11.1	11.0	12.3	13.6	14.9	16.2
95°	18.1	16.9	25.8	34.7	43.6	52.5	57.3	58.0	58.8	59.4	60.2
97.5°	45.3	51.9	69.5	87.2	104.8	122.5	130.7	129.4	128.2	126.9	125.6
100°	148.7	183.7	182.7	181.8	180.8	179.9	179.1	178.4	177.7	177.0	176.3
102.5°	227.7	234.3	233.7	233.3	232.7	232.1	231.4	230.5	229.6	228.7	227.8
105°	314.5	314.5	314.5	314.5	314.5	314.5	314.1	313.2	312.3	311.3	310.4
107.5°	398.2	398.2	397.7	397.2	396.8	396.3	396.1	396.1	396.1	396.1	396.1
110°	453.2	453.9	453.5	453.0	452.5	452.0	451.8	451.8	451.8	451.8	451.8



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	507.0	507.9	507.7	507.4	507.1	506.9	506.4	505.8	505.3	504.8	504.2
115°	588.1	589.1	588.8	588.6	588.3	588.1	587.4	586.2	585.1	583.8	582.7
117.5°	666.6	667.8	666.9	666.0	665.1	664.2	663.8	663.8	663.9	663.9	664.0
120°	716.3	716.7	716.1	715.3	714.6	714.0	713.7	714.0	714.2	714.4	714.6
122.5°	764.4	764.9	764.6	764.3	763.9	763.6	763.0	762.1	761.2	760.3	759.4
125°	835.1	836.0	836.0	836.0	836.0	836.0	835.2	833.6	831.9	830.3	828.7
127.5°	898.9	899.4	899.5	899.7	899.8	899.9	899.4	898.2	897.1	895.9	894.7
130°	940.9	941.6	941.3	941.1	940.9	940.7	940.0	938.8	937.6	936.5	935.2
132.5°	979.5	979.6	980.2	980.6	981.1	981.7	981.2	979.9	978.5	977.1	975.8
135°	1037.2	1037.6	1038.1	1038.6	1039.1	1039.5	1039.1	1037.6	1036.2	1034.9	1033.5
137.5°	1090.1	1090.1	1090.5	1090.9	1091.3	1091.7	1091.3	1090.1	1088.8	1087.6	1086.5
140°	1122.6	1122.1	1122.3	1122.6	1122.8	1123.1	1122.9	1122.4	1122.0	1121.5	1121.0
142.5°	1155.1	1155.0	1154.7	1154.4	1154.1	1153.7	1153.4	1153.2	1152.8	1152.6	1152.3
145°	1200.4	1200.2	1200.2	1200.2	1200.2	1200.2	1200.0	1199.5	1199.1	1198.6	1198.1
147.5°	1239.3	1239.1	1238.8	1238.5	1238.2	1238.0	1237.9	1238.0	1238.0	1238.1	1238.2
150°	1264.0	1263.6	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6
152.5°	1286.0	1285.5	1285.1	1284.6	1284.1	1283.6	1283.9	1285.0	1286.0	1287.0	1288.0
155°	1316.0	1315.3	1314.8	1314.3	1313.9	1313.4	1313.9	1315.3	1316.7	1318.1	1319.5
157.5°	1340.9	1340.2	1340.2	1340.1	1340.0	1340.0	1340.4	1341.2	1342.1	1343.0	1343.8
160°	1356.3	1355.4	1355.2	1354.9	1354.7	1354.5	1355.0	1356.4	1357.9	1359.3	1360.7
162.5°	1370.2	1368.9	1368.6	1368.5	1368.2	1368.0	1368.6	1369.9	1371.3	1372.8	1374.2
165°	1388.5	1387.1	1386.8	1386.6	1386.3	1386.1	1386.7	1388.1	1389.5	1390.9	1392.4
167.5°	1402.1	1400.4	1400.1	1399.9	1399.6	1399.5	1400.0	1401.5	1403.0	1404.4	1405.8
170°	1409.0	1407.1	1406.9	1406.6	1406.4	1406.1	1406.9	1408.5	1410.1	1411.9	1413.5
172.5°	1414.7	1413.0	1412.6	1412.2	1411.8	1411.4	1411.9	1413.6	1415.3	1416.9	1418.5
175°	1420.6	1418.7	1418.5	1418.3	1418.1	1417.8	1418.4	1419.8	1421.2	1422.6	1424.0
177.5°	1423.7	1422.3	1422.1	1422.0	1421.8	1421.6	1422.0	1423.2	1424.3	1425.4	1426.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	461.1	462.5	464.5	466.8	468.6	470.5	471.6	471.6	472.5	474.4	477.0
5°	462.5	467.4	472.1	478.1	482.8	488.3	492.4	496.4	499.9	504.5	509.2
7.5°	462.1	470.3	478.7	488.2	498.7	507.0	515.6	522.3	528.9	537.6	544.4
10°	460.6	471.2	482.7	494.7	507.9	519.3	529.8	539.2	548.2	557.7	566.1
12.5°	457.9	471.3	485.3	499.9	516.5	529.6	543.0	553.0	563.6	573.9	584.3
15°	453.8	469.6	486.6	506.8	527.1	541.8	555.0	568.0	577.8	589.5	599.5
17.5°	445.4	465.8	487.1	509.2	528.7	545.8	559.6	572.0	582.4	595.3	608.9
20°	440.4	462.5	484.7	508.3	526.9	544.5	557.8	570.6	583.6	600.4	616.9
22.5°	433.5	457.1	480.6	503.0	522.7	539.6	553.4	569.1	586.2	605.2	625.3
25°	422.6	446.9	470.2	491.5	510.7	528.1	546.9	568.0	588.7	613.8	642.6
27.5°	408.6	432.1	452.9	475.4	494.5	516.6	540.1	563.0	592.8	627.3	663.2
30°	398.3	420.4	440.3	461.5	483.2	507.5	533.9	560.8	596.5	636.9	679.7
32.5°	386.2	406.3	425.9	446.5	471.5	498.1	526.2	559.1	601.7	647.8	692.0
35°	365.3	383.4	402.4	425.2	451.8	480.8	516.6	556.7	608.1	657.6	697.4
37.5°	343.3	357.7	376.7	400.8	429.7	463.3	503.9	552.7	605.4	650.0	666.8
40°	326.4	339.8	360.0	385.2	413.9	450.6	496.2	546.3	599.5	630.3	629.0
42.5°	309.7	323.3	342.7	368.1	397.9	439.0	486.0	538.0	582.9	594.6	570.1
45°	284.1	296.7	315.8	341.4	373.4	416.5	465.9	515.8	544.5	525.4	476.8
47.5°	258.0	270.2	287.9	312.9	347.9	393.1	439.8	480.7	484.7	443.8	385.6
50°	240.8	252.3	269.0	295.8	329.7	373.7	418.8	451.0	441.0	391.1	331.0
52.5°	224.0	235.1	250.8	276.1	310.7	353.8	394.0	419.4	396.2	343.2	289.1
55°	199.3	209.9	225.7	248.8	280.3	319.8	355.1	364.4	330.4	277.0	233.3
57.5°	175.9	183.6	199.2	219.7	250.1	284.9	310.1	308.5	271.1	222.9	191.5
60°	160.3	167.3	182.1	201.0	229.8	261.1	278.8	271.3	233.4	193.6	163.5
62.5°	145.9	152.4	164.9	182.1	206.9	234.2	247.0	236.6	200.9	165.9	141.9
65°	123.9	128.7	138.7	154.7	174.1	192.9	204.4	189.1	157.5	131.1	113.0
67.5°	103.5	107.5	116.4	127.9	141.3	154.3	159.0	144.7	120.1	102.3	89.5
70°	90.3	94.0	100.0	110.8	119.6	128.8	131.1	118.3	97.8	84.2	76.3
72.5°	77.6	81.0	86.3	93.9	100.0	105.3	106.4	94.5	78.8	69.5	63.3
75°	59.2	62.2	65.6	68.4	72.3	73.3	72.9	63.7	55.2	49.0	45.6
77.5°	43.5	44.8	46.8	47.9	48.1	48.0	46.1	40.3	35.9	33.3	32.0
80°	33.5	34.5	35.1	35.4	35.6	33.8	31.6	28.0	26.6	25.0	23.4
82.5°	24.4	24.9	25.5	25.6	24.6	23.0	21.1	19.3	18.3	17.5	16.9
85°	13.2	13.4	13.2	12.2	10.9	10.4	9.9	9.6	9.5	9.2	9.2
87.5°	5.2	5.2	4.8	5.3	5.7	5.9	6.2	6.4	6.5	6.8	7.0
90°	2.9	4.8	6.7	8.6	10.4	12.0	13.6	15.2	16.9	18.1	19.2
92.5°	14.9	13.6	12.3	11.0	11.1	12.6	13.9	15.4	16.9	18.1	19.2
95°	59.4	58.8	58.0	57.3	52.5	43.6	34.7	25.8	16.9	18.1	19.2
97.5°	126.9	128.2	129.4	130.7	122.5	104.8	87.2	69.5	51.9	45.3	38.7
100°	177.0	177.7	178.4	179.1	179.9	180.8	181.8	182.7	183.7	148.7	113.7
102.5°	228.7	229.6	230.5	231.4	232.1	232.7	233.3	233.7	234.3	227.7	221.1
105°	311.3	312.3	313.2	314.1	314.5	314.5	314.5	314.5	314.5	314.5	314.5
107.5°	396.1	396.1	396.1	396.1	396.3	396.8	397.2	397.7	398.2	398.2	398.3
110°	451.8	451.8	451.8	451.8	452.0	452.5	453.0	453.5	453.9	453.2	452.5



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	504.8	505.3	505.8	506.4	506.9	507.1	507.4	507.7	507.9	507.0	506.1
115°	583.8	585.1	586.2	587.4	588.1	588.3	588.6	588.8	589.1	588.1	587.2
117.5°	663.9	663.9	663.8	663.8	664.2	665.1	666.0	666.9	667.8	666.6	665.4
120°	714.4	714.2	714.0	713.7	714.0	714.6	715.3	716.1	716.7	716.3	715.8
122.5°	760.3	761.2	762.1	763.0	763.6	763.9	764.3	764.6	764.9	764.4	763.9
125°	830.3	831.9	833.6	835.2	836.0	836.0	836.0	836.0	836.0	835.1	834.1
127.5°	895.9	897.1	898.2	899.4	899.9	899.8	899.7	899.5	899.4	898.9	898.4
130°	936.5	937.6	938.8	940.0	940.7	940.9	941.1	941.3	941.6	940.9	940.2
132.5°	977.1	978.5	979.9	981.2	981.7	981.1	980.6	980.2	979.6	979.5	979.3
135°	1034.9	1036.2	1037.6	1039.1	1039.5	1039.1	1038.6	1038.1	1037.6	1037.2	1036.7
137.5°	1087.6	1088.8	1090.1	1091.3	1091.7	1091.3	1090.9	1090.5	1090.1	1090.1	1090.2
140°	1121.5	1122.0	1122.4	1122.9	1123.1	1122.8	1122.6	1122.3	1122.1	1122.6	1123.1
142.5°	1152.6	1152.8	1153.2	1153.4	1153.7	1154.1	1154.4	1154.7	1155.0	1155.1	1155.2
145°	1198.6	1199.1	1199.5	1200.0	1200.2	1200.2	1200.2	1200.2	1200.2	1200.4	1200.7
147.5°	1238.1	1238.0	1238.0	1237.9	1238.0	1238.2	1238.5	1238.8	1239.1	1239.3	1239.7
150°	1263.1	1262.7	1262.2	1261.7	1261.7	1262.2	1262.7	1263.1	1263.6	1264.0	1264.5
152.5°	1287.0	1286.0	1285.0	1283.9	1283.6	1284.1	1284.6	1285.1	1285.5	1286.0	1286.5
155°	1318.1	1316.7	1315.3	1313.9	1313.4	1313.9	1314.3	1314.8	1315.3	1316.0	1316.7
157.5°	1343.0	1342.1	1341.2	1340.4	1340.0	1340.0	1340.1	1340.2	1340.2	1340.9	1341.7
160°	1359.3	1357.9	1356.4	1355.0	1354.5	1354.7	1354.9	1355.2	1355.4	1356.3	1357.3
162.5°	1372.8	1371.3	1369.9	1368.6	1368.0	1368.2	1368.5	1368.6	1368.9	1370.2	1371.5
165°	1390.9	1389.5	1388.1	1386.7	1386.1	1386.3	1386.6	1386.8	1387.1	1388.5	1389.8
167.5°	1404.4	1403.0	1401.5	1400.0	1399.5	1399.6	1399.9	1400.1	1400.4	1402.1	1403.8
170°	1411.9	1410.1	1408.5	1406.9	1406.1	1406.4	1406.6	1406.9	1407.1	1409.0	1410.9
172.5°	1416.9	1415.3	1413.6	1411.9	1411.4	1411.8	1412.2	1412.6	1413.0	1414.7	1416.4
175°	1422.6	1421.2	1419.8	1418.4	1417.8	1418.1	1418.3	1418.5	1418.7	1420.6	1422.5
177.5°	1425.4	1424.3	1423.2	1422.0	1421.6	1421.8	1422.0	1422.1	1422.3	1423.7	1425.0
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	458.9	458.9	458.9	458.9	458.9	458.9	458.9
2.5°	479.0	479.0	481.5	481.4	483.1	482.4	482.7
5°	514.9	518.0	520.9	522.8	525.6	526.4	525.9
7.5°	552.1	559.2	562.6	567.4	568.3	570.8	570.5
10°	575.1	582.1	587.4	591.5	593.6	596.2	596.5
12.5°	593.2	599.2	603.8	607.6	610.2	611.0	611.5
15°	607.4	613.9	619.4	624.8	628.1	630.6	631.9
17.5°	621.6	631.8	641.4	648.8	653.3	657.0	657.0
20°	632.6	644.2	656.3	664.8	673.5	677.3	677.8
22.5°	644.3	662.2	677.8	690.9	702.3	706.2	707.7
25°	668.8	692.1	716.1	734.5	747.7	755.5	756.6
27.5°	698.3	729.9	755.0	772.1	783.0	788.8	790.0
30°	719.1	748.3	770.9	783.7	788.8	789.5	786.7
32.5°	728.4	750.2	759.3	758.6	748.5	741.9	739.4
35°	717.0	712.5	690.5	664.1	643.9	631.1	627.7
37.5°	652.5	613.5	573.0	533.1	511.9	501.1	482.6
40°	588.9	533.3	491.1	457.6	433.7	414.4	409.9
42.5°	517.1	459.7	417.6	388.9	369.7	356.6	350.8
45°	415.6	366.2	331.3	309.3	294.6	285.0	280.7
47.5°	332.4	294.2	268.8	252.5	241.2	232.9	230.6
50°	286.7	256.2	234.7	220.9	212.5	206.1	203.5
52.5°	249.1	224.4	207.9	196.6	188.6	184.6	182.4
55°	205.5	184.3	172.4	163.3	158.8	155.6	154.1
57.5°	168.1	152.7	144.1	137.8	133.6	131.6	130.9
60°	147.2	135.1	127.2	122.3	119.4	116.8	116.0
62.5°	128.6	119.1	113.0	108.7	105.9	104.8	104.3
65°	103.6	97.4	92.9	90.3	88.0	87.6	87.4
67.5°	82.3	78.7	76.3	73.6	72.8	71.5	71.2
70°	70.4	68.0	65.1	64.2	63.3	62.0	62.2
72.5°	59.8	57.3	55.4	54.1	53.8	53.2	53.7
75°	43.7	43.0	42.2	41.3	40.8	40.8	40.7
77.5°	31.2	30.6	29.8	29.2	29.0	28.3	28.5
80°	22.6	21.7	21.3	21.4	20.9	20.7	20.7
82.5°	16.7	16.4	16.0	16.1	15.9	15.7	15.9
85°	9.2	9.0	9.0	8.9	8.9	8.6	8.6
87.5°	7.4	7.7	7.7	7.7	7.8	8.1	8.4
90°	20.4	21.6	22.5	23.2	23.9	24.6	25.4
92.5°	20.4	21.6	22.3	22.7	23.0	23.3	23.6
95°	20.4	21.6	22.2	22.2	22.2	22.2	22.2
97.5°	32.1	25.4	22.2	22.2	22.2	22.2	22.2
100°	78.8	43.9	25.9	24.9	24.1	23.1	22.2
102.5°	214.5	207.9	196.6	180.7	164.7	148.7	132.8
105°	314.5	314.5	314.5	314.2	314.0	313.7	313.5
107.5°	398.4	398.4	398.0	397.3	396.6	395.9	395.3
110°	451.8	451.1	450.9	451.1	451.3	451.6	451.8



TEST NUMBER: P333652-930

CATALOG NUMBER: S125RDIW-S375D1340U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	505.3	504.4	503.8	503.4	503.1	502.8	502.5
115°	586.2	585.3	584.1	582.7	581.3	579.8	578.5
117.5°	664.1	662.9	661.9	661.4	660.8	660.1	659.6
120°	715.3	714.9	714.0	712.9	711.7	710.5	709.4
122.5°	763.4	763.0	762.1	760.8	759.4	758.0	756.7
125°	833.2	832.3	831.4	830.8	830.1	829.3	828.7
127.5°	897.8	897.3	896.2	894.5	892.8	891.0	889.2
130°	939.5	938.8	937.8	936.7	935.5	934.3	933.2
132.5°	979.2	979.0	978.4	977.2	976.1	974.9	973.7
135°	1036.2	1035.8	1034.9	1033.5	1032.0	1030.6	1029.2
137.5°	1090.3	1090.4	1089.8	1088.6	1087.4	1086.1	1084.9
140°	1123.5	1124.0	1123.5	1122.1	1120.7	1119.3	1117.9
142.5°	1155.4	1155.4	1154.8	1153.3	1151.9	1150.6	1149.2
145°	1200.9	1201.2	1200.6	1199.1	1197.8	1196.4	1195.0
147.5°	1239.9	1240.2	1239.5	1237.8	1236.1	1234.4	1232.7
150°	1264.9	1265.4	1264.7	1262.8	1260.9	1259.1	1257.2
152.5°	1286.9	1287.4	1286.8	1285.1	1283.4	1281.7	1280.0
155°	1317.4	1318.1	1317.5	1315.6	1313.8	1311.9	1310.0
157.5°	1342.5	1343.2	1342.6	1340.8	1338.9	1337.0	1335.1
160°	1358.2	1359.2	1358.7	1356.8	1354.9	1353.1	1351.2
162.5°	1372.9	1374.2	1373.8	1371.7	1369.6	1367.6	1365.5
165°	1391.3	1392.7	1392.4	1390.6	1388.7	1386.8	1384.9
167.5°	1405.4	1407.1	1406.9	1404.8	1402.7	1400.6	1398.5
170°	1412.8	1414.6	1414.5	1412.4	1410.3	1408.2	1406.1
172.5°	1418.1	1419.8	1419.6	1417.5	1415.4	1413.2	1411.1
175°	1424.3	1426.2	1426.1	1424.0	1421.9	1419.8	1417.6
177.5°	1426.3	1427.6	1427.5	1426.0	1424.5	1422.9	1421.5
180°	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0	1424.0

(END OF REPORT)