

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333659-930

Luminaire Tested: **S125RDIW-S375D1560U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333659-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1560U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5591.0 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	30	30	30	21
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25	18
2	83	76	70	66	73	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	55	67	60	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	52	46	61	53	46	42	40	36	33	29	26	24	18	17	16	11
5	64	53	45	39	56	47	40	35	36	32	28	26	23	21	17	15	14	10
6	58	47	39	34	52	42	35	31	32	28	24	23	20	18	15	13	12	9
7	54	42	35	29	48	38	31	27	29	25	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	27	22	19	19	16	14	13	11	10	7
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9	6
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3222	3222	3222
5°	3229	3192	3212
10°	3205	3163	3163
15°	3167	3099	3074
20°	3118	3009	2973
25°	3061	2921	2857
30°	2990	2818	2729
35°	2917	2713	2584
40°	2850	2602	2443
45°	2767	2478	2288
50°	2685	2344	2127
55°	2587	2215	1956
60°	2492	2059	1771
65°	2378	1878	1560
70°	2247	1650	1344
75°	2069	1392	1118
80°	1822	1093	941
85°	1534	897	837



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.9	0.8
10°-20°	131.1	2.3
20°-30°	190.1	3.4
30°-40°	216.7	3.9
40°-50°	211.2	3.8
50°-60°	177.8	3.2
60°-70°	124.6	2.2
70°-80°	64.1	1.1
80°-90°	19.6	0.4
90°-100°	105.8	1.9
100°-110°	312.5	5.6
110°-120°	529.3	9.5
120°-130°	696.6	12.5
130°-140°	780.6	14.0
140°-150°	765.0	13.7
150°-160°	642.6	11.5
160°-170°	427.1	7.6
170°-180°	149.5	2.7
0°-30°	368.1	6.6
0°-40°	584.8	10.5
0°-60°	973.7	17.4
0°-90°	1182.0	21.1
90°-120°	947.6	16.9
90°-150°	3189.8	57.1
90°-180°	4409.0	78.9
0°-180°	5591.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	499	499	499	499	499	
5°	498	496	492	496	496	47
15°	474	471	464	463	460	133
25°	430	423	410	405	401	198
35°	370	361	344	333	328	232
45°	303	292	271	257	250	234
55°	230	217	197	180	174	206
65°	156	142	123	108	102	154
75°	83	71	56	48	45	88
85°	21	14	12	12	11	23
90°	1	11	20	26	30	5
95°	80	83	95	103	106	85
105°	280	287	294	301	305	299
115°	530	535	537	536	535	524
125°	773	780	782	780	778	692
135°	1006	1013	1014	1014	1010	775
145°	1218	1223	1227	1227	1223	761
155°	1394	1394	1396	1400	1394	642
165°	1516	1514	1515	1519	1512	428
175°	1576	1572	1571	1578	1570	150
180°	1580	1580	1580	1580	1580	



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9
2.5°	499.8	499.6	499.4	499.2	499.0	498.6	497.9	497.2	496.5	495.9	496.5
5°	498.1	497.8	497.5	497.1	496.8	496.2	495.2	494.3	493.4	492.4	493.3
7.5°	493.3	492.9	492.6	492.3	492.0	491.2	490.2	489.0	488.0	486.8	487.4
10°	488.7	488.4	488.2	488.0	487.7	487.0	485.8	484.6	483.5	482.3	482.6
12.5°	483.6	483.2	483.0	482.7	482.3	481.4	479.8	478.3	476.6	475.1	475.2
15°	473.6	473.1	472.6	472.1	471.7	470.5	468.7	467.0	465.2	463.5	463.4
17.5°	462.4	461.6	460.9	460.1	459.3	457.9	455.6	453.4	451.2	449.0	448.6
20°	453.6	452.8	452.0	451.2	450.3	448.6	445.9	443.2	440.5	437.8	437.4
22.5°	444.0	443.2	442.4	441.5	440.7	438.9	436.0	433.3	430.4	427.6	426.8
25°	429.6	428.3	427.1	425.7	424.5	422.3	419.2	416.1	413.0	409.9	408.9
27.5°	412.9	411.5	409.9	408.4	406.8	404.5	401.1	397.8	394.5	391.2	389.6
30°	400.9	399.3	397.7	396.2	394.5	392.0	388.5	385.0	381.5	377.9	376.0
32.5°	389.1	387.3	385.5	383.6	381.7	379.0	375.4	371.9	368.3	364.7	362.6
35°	370.0	368.0	366.0	363.9	362.0	359.1	355.3	351.6	347.8	344.1	341.6
37.5°	351.2	348.8	346.3	343.9	341.4	338.3	334.4	330.5	326.7	322.8	319.8
40°	338.0	335.5	333.0	330.4	327.9	324.7	320.7	316.7	312.6	308.6	305.4
42.5°	324.1	321.6	318.9	316.4	313.8	310.5	306.3	302.1	298.0	293.8	290.8
45°	303.0	300.5	298.1	295.6	293.3	289.7	285.1	280.5	275.9	271.3	267.9
47.5°	281.0	278.4	275.9	273.3	270.8	267.2	262.5	257.9	253.2	248.6	245.2
50°	267.2	264.4	261.6	258.9	256.1	252.3	247.5	242.8	238.0	233.3	229.8
52.5°	252.1	249.2	246.4	243.6	240.8	237.1	232.6	228.0	223.6	219.1	215.3
55°	229.8	227.1	224.5	221.8	219.2	215.5	210.8	206.0	201.4	196.7	192.9
57.5°	207.4	204.6	201.6	198.8	195.9	192.2	187.7	183.2	178.7	174.1	170.5
60°	192.9	190.0	187.0	184.1	181.2	177.5	172.9	168.4	163.9	159.4	155.7
62.5°	177.6	174.7	171.9	169.2	166.3	162.7	158.1	153.5	148.9	144.3	140.9
65°	155.6	152.8	149.9	147.1	144.2	140.6	136.2	131.8	127.3	122.9	119.5
67.5°	133.9	131.0	128.2	125.3	122.5	118.9	114.6	110.4	106.2	101.9	98.8
70°	119.0	116.3	113.4	110.6	107.7	104.2	100.0	95.8	91.6	87.4	84.8
72.5°	104.6	101.8	99.1	96.3	93.5	90.1	86.2	82.3	78.4	74.4	72.1
75°	82.9	80.4	77.9	75.3	72.9	69.9	66.3	62.8	59.3	55.8	53.9
77.5°	61.3	59.4	57.3	55.3	53.3	50.9	48.1	45.2	42.5	39.6	38.3
80°	49.0	47.0	45.0	43.0	40.9	38.8	36.4	34.1	31.7	29.4	28.6
82.5°	36.9	35.1	33.3	31.5	29.7	28.0	26.4	24.8	23.2	21.5	21.2
85°	20.7	19.2	17.7	16.2	14.7	13.7	13.3	12.9	12.5	12.1	12.0
87.5°	7.2	7.2	7.1	7.1	7.0	7.2	7.5	7.8	8.2	8.5	8.7
90°	1.2	3.4	5.6	7.8	9.9	12.0	13.9	15.8	17.8	19.6	21.0
92.5°	29.8	31.3	32.9	34.3	35.9	37.8	40.2	42.5	44.8	47.2	49.0
95°	79.9	80.5	81.0	81.5	82.1	83.7	86.5	89.2	92.0	94.7	96.6
97.5°	132.8	133.0	133.2	133.5	133.7	135.7	139.4	143.2	147.0	150.7	152.5
100°	172.1	172.1	172.1	172.1	172.1	173.9	177.5	181.0	184.6	188.1	190.6
102.5°	214.4	215.6	216.6	217.7	218.8	220.3	222.1	223.9	225.7	227.5	230.2
105°	280.4	281.7	283.1	284.5	285.8	287.3	288.9	290.6	292.2	293.9	295.5
107.5°	353.1	354.5	355.9	357.3	358.6	360.0	361.2	362.4	363.7	364.9	365.7
110°	403.3	404.7	406.0	407.4	408.8	409.9	410.7	411.5	412.3	413.1	413.9



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	454.4	455.2	455.9	456.6	457.3	458.2	459.2	460.2	461.3	462.4	462.7
115°	529.9	531.1	532.1	533.2	534.3	535.2	535.7	536.2	536.8	537.4	537.0
117.5°	605.7	606.2	606.7	607.2	607.6	608.1	608.6	609.1	609.6	610.2	610.3
120°	652.9	654.3	655.7	657.0	658.4	659.2	659.5	659.7	660.0	660.3	660.3
122.5°	704.1	704.6	705.1	705.6	706.0	706.6	707.4	708.1	708.7	709.5	709.2
125°	773.4	775.0	776.7	778.4	780.0	781.0	781.2	781.5	781.8	782.0	781.5
127.5°	847.2	848.2	849.1	849.9	850.9	851.6	851.9	852.2	852.6	852.9	852.6
130°	891.4	892.8	894.2	895.5	896.9	897.9	898.5	898.9	899.5	900.1	899.8
132.5°	935.7	938.0	940.2	942.5	944.7	945.7	945.7	945.5	945.4	945.3	945.0
135°	1005.8	1007.5	1009.1	1010.7	1012.4	1013.3	1013.6	1013.9	1014.2	1014.4	1014.4
137.5°	1071.7	1073.3	1074.9	1076.4	1078.1	1079.1	1079.8	1080.4	1080.9	1081.6	1081.9
140°	1114.0	1115.4	1116.7	1118.1	1119.5	1120.5	1121.4	1122.3	1123.1	1123.9	1124.4
142.5°	1156.3	1157.5	1158.6	1159.8	1160.9	1162.0	1163.0	1164.1	1165.1	1166.1	1166.4
145°	1218.5	1219.6	1220.7	1221.8	1222.9	1223.8	1224.7	1225.5	1226.3	1227.1	1227.1
147.5°	1276.1	1276.7	1277.2	1277.9	1278.5	1279.1	1279.8	1280.4	1281.1	1281.7	1282.4
150°	1314.4	1314.2	1313.9	1313.6	1313.4	1313.8	1314.8	1316.0	1317.0	1318.2	1318.2
152.5°	1345.9	1346.3	1346.7	1347.0	1347.4	1347.9	1348.3	1348.7	1349.2	1349.6	1350.3
155°	1394.4	1394.4	1394.4	1394.4	1394.4	1394.5	1394.8	1395.1	1395.3	1395.6	1396.7
157.5°	1437.6	1437.0	1436.5	1435.8	1435.3	1435.1	1435.3	1435.7	1435.9	1436.1	1437.3
160°	1463.2	1462.4	1461.6	1460.8	1460.0	1459.7	1460.0	1460.2	1460.5	1460.8	1461.8
162.5°	1485.9	1485.2	1484.7	1484.1	1483.4	1483.2	1483.2	1483.3	1483.4	1483.4	1484.7
165°	1516.1	1515.6	1515.0	1514.5	1513.9	1513.8	1514.1	1514.3	1514.6	1514.9	1516.0
167.5°	1541.6	1540.6	1539.5	1538.4	1537.3	1536.8	1536.8	1536.8	1536.8	1536.8	1538.4
170°	1555.4	1554.4	1553.2	1552.2	1551.1	1550.5	1550.5	1550.5	1550.5	1550.5	1552.2
172.5°	1565.3	1564.2	1563.1	1562.0	1560.9	1560.4	1560.4	1560.4	1560.4	1560.4	1562.0
175°	1576.4	1575.2	1574.2	1573.0	1572.0	1571.4	1571.4	1571.4	1571.4	1571.4	1573.0
177.5°	1582.0	1581.1	1580.3	1579.4	1578.5	1577.9	1577.8	1577.5	1577.3	1577.1	1578.4
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	498.9	498.9	498.9	498.9	498.9	498.9	498.9	498.9
2.5°	497.2	497.9	498.6	498.9	498.8	498.7	498.6	498.6
5°	494.2	495.0	495.8	496.2	496.0	495.8	495.6	495.5
7.5°	488.0	488.6	489.2	489.3	489.2	489.0	488.9	488.6
10°	482.8	483.1	483.3	483.3	483.1	482.8	482.6	482.3
12.5°	475.4	475.6	475.8	475.7	475.3	474.9	474.6	474.2
15°	463.3	463.2	463.1	462.7	461.9	461.2	460.5	459.7
17.5°	448.2	447.8	447.4	446.8	446.2	445.6	444.9	444.3
20°	437.0	436.6	436.2	435.6	434.8	434.1	433.3	432.6
22.5°	425.9	425.1	424.3	423.5	423.0	422.3	421.8	421.1
25°	407.8	406.7	405.6	404.6	403.7	402.8	401.9	400.9
27.5°	388.2	386.6	385.1	383.9	383.0	382.1	381.2	380.3
30°	374.1	372.2	370.2	368.9	368.1	367.4	366.6	365.9
32.5°	360.4	358.3	356.1	354.7	353.7	352.7	351.7	350.8
35°	339.2	336.7	334.3	332.5	331.3	330.2	329.0	327.8
37.5°	316.9	314.1	311.1	309.1	307.9	306.8	305.7	304.5
40°	302.2	299.1	295.9	293.8	292.8	291.8	290.7	289.8
42.5°	287.7	284.7	281.6	279.4	277.9	276.4	274.9	273.5
45°	264.6	261.2	257.9	255.6	254.4	253.1	251.8	250.5
47.5°	241.7	238.2	234.8	232.4	231.0	229.6	228.2	226.8
50°	226.2	222.7	219.2	216.8	215.6	214.3	213.0	211.7
52.5°	211.5	207.7	203.9	201.4	200.2	198.9	197.6	196.4
55°	189.1	185.4	181.6	179.0	177.7	176.3	175.0	173.7
57.5°	166.8	163.1	159.4	156.9	155.8	154.6	153.4	152.2
60°	152.1	148.3	144.6	142.2	140.9	139.7	138.4	137.1
62.5°	137.5	134.0	130.6	128.3	127.0	125.8	124.6	123.3
65°	116.1	112.8	109.4	107.1	105.9	104.6	103.4	102.1
67.5°	95.7	92.7	89.6	87.6	86.6	85.6	84.5	83.6
70°	82.3	79.7	77.0	75.3	74.2	73.2	72.2	71.2
72.5°	69.6	67.3	64.9	63.3	62.7	62.0	61.3	60.7
75°	52.1	50.2	48.4	47.2	46.6	46.0	45.4	44.8
77.5°	37.1	35.8	34.5	33.6	33.2	32.8	32.3	31.9
80°	27.9	27.1	26.4	25.9	25.8	25.6	25.4	25.3
82.5°	20.9	20.5	20.1	19.9	19.8	19.7	19.6	19.5
85°	11.9	11.8	11.7	11.7	11.6	11.5	11.4	11.3
87.5°	9.0	9.3	9.5	9.7	9.9	9.9	10.0	10.1
90°	22.4	23.8	25.1	26.3	27.1	27.9	28.7	29.5
92.5°	50.8	52.6	54.5	55.6	56.3	56.8	57.4	58.0
95°	98.5	100.4	102.3	103.5	104.1	104.7	105.2	105.7
97.5°	154.3	156.1	157.9	159.1	159.4	159.7	160.0	160.4
100°	193.1	195.5	198.0	199.5	200.0	200.6	201.1	201.6
102.5°	232.8	235.5	238.1	239.9	240.7	241.4	242.2	243.0
105°	297.2	298.8	300.4	301.7	302.5	303.3	304.1	304.9
107.5°	366.6	367.4	368.2	368.6	368.5	368.5	368.4	368.4
110°	414.8	415.6	416.5	416.7	416.5	416.1	415.9	415.6



TEST NUMBER: P333659-930

CATALOG NUMBER: S125RDIW-S375D1560U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	463.1	463.5	463.8	463.8	463.3	462.8	462.4	461.9
115°	536.8	536.5	536.2	536.0	535.7	535.4	535.2	534.9
117.5°	610.6	610.8	611.0	610.6	609.4	608.4	607.3	606.2
120°	660.3	660.3	660.3	659.7	658.7	657.5	656.5	655.4
122.5°	709.1	708.8	708.6	708.1	707.2	706.3	705.4	704.6
125°	781.0	780.4	779.8	779.4	779.2	778.9	778.6	778.4
127.5°	852.3	852.1	851.7	851.3	850.8	850.3	849.7	849.1
130°	899.5	899.3	898.9	898.5	898.1	897.5	896.9	896.4
132.5°	944.8	944.5	944.2	943.7	943.0	942.2	941.4	940.6
135°	1014.4	1014.4	1014.4	1013.9	1012.8	1011.7	1010.6	1009.5
137.5°	1082.2	1082.6	1082.9	1082.4	1081.0	1079.6	1078.2	1076.8
140°	1124.9	1125.5	1126.0	1125.6	1124.3	1122.9	1121.5	1120.1
142.5°	1166.8	1167.1	1167.5	1166.9	1165.6	1164.2	1162.9	1161.5
145°	1227.1	1227.1	1227.1	1226.7	1225.9	1225.1	1224.3	1223.4
147.5°	1283.0	1283.7	1284.3	1283.8	1281.9	1280.0	1278.2	1276.4
150°	1318.2	1318.2	1318.2	1317.8	1317.3	1316.8	1316.2	1315.6
152.5°	1351.0	1351.6	1352.3	1352.1	1351.1	1350.1	1349.2	1348.2
155°	1397.7	1398.9	1400.0	1399.9	1398.5	1397.1	1395.7	1394.4
157.5°	1438.4	1439.5	1440.6	1440.2	1438.4	1436.6	1434.8	1433.0
160°	1463.0	1464.0	1465.2	1465.0	1463.6	1462.2	1460.9	1459.5
162.5°	1486.0	1487.4	1488.7	1488.5	1486.9	1485.3	1483.8	1482.1
165°	1517.0	1518.2	1519.2	1519.0	1517.4	1515.7	1514.1	1512.4
167.5°	1540.0	1541.6	1543.3	1543.3	1541.6	1539.9	1538.2	1536.5
170°	1553.8	1555.4	1557.1	1557.0	1555.0	1553.1	1551.2	1549.3
172.5°	1563.7	1565.3	1566.9	1566.9	1565.2	1563.5	1561.8	1560.2
175°	1574.8	1576.4	1578.0	1577.8	1576.0	1574.0	1572.1	1570.2
177.5°	1579.7	1581.0	1582.3	1582.3	1580.7	1579.2	1577.6	1576.1
180°	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1	1580.1

(END OF REPORT)