

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333671-930

Luminaire Tested: **S125RDIW-S610D1050U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333671-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1050U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4902.1 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	37	35	34	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	37	33	31	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	26	24	22	18
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	38	31	26	31	26	23	26	22	19	20	17	15	13
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	22	18	22	18	15	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5297	5297	5297
5°	5309	5249	5281
10°	5269	5200	5200
15°	5207	5094	5053
20°	5126	4947	4887
25°	5032	4802	4697
30°	4915	4633	4486
35°	4796	4459	4249
40°	4684	4278	4016
45°	4549	4074	3763
50°	4413	3852	3497
55°	4255	3640	3216
60°	4097	3384	2913
65°	3909	3085	2566
70°	3697	2713	2211
75°	3401	2286	1839
80°	2998	1796	1543
85°	2527	1467	1378



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	1.6
10°-20°	215.5	4.4
20°-30°	312.5	6.4
30°-40°	356.2	7.3
40°-50°	347.2	7.1
50°-60°	292.3	6.0
60°-70°	204.9	4.2
70°-80°	105.3	2.1
80°-90°	28.9	0.6
90°-100°	71.1	1.5
100°-110°	210.0	4.3
110°-120°	355.6	7.3
120°-130°	468.0	9.5
130°-140°	524.4	10.7
140°-150°	514.0	10.5
150°-160°	431.7	8.8
160°-170°	287.0	5.9
170°-180°	100.4	2.0
0°-30°	605.2	12.3
0°-40°	961.4	19.6
0°-60°	1600.8	32.7
0°-90°	1939.9	39.6
90°-120°	636.7	13.0
90°-150°	2143.1	43.7
90°-180°	2962.0	60.4
0°-180°	4902.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	820	820	820	820	820	
5°	819	816	810	815	815	78
15°	779	774	762	761	756	219
25°	706	696	674	666	659	325
35°	608	593	566	548	539	381
45°	498	479	446	422	412	384
55°	378	357	323	296	286	338
65°	256	234	202	178	168	253
75°	136	117	92	79	74	144
85°	34	23	20	19	19	38
90°	1	7	13	17	20	5
95°	54	56	64	69	71	57
105°	188	193	198	202	205	201
115°	356	359	361	360	359	352
125°	520	524	525	524	523	465
135°	676	680	682	681	678	521
145°	819	822	824	824	822	512
155°	937	937	938	940	937	431
165°	1019	1017	1018	1021	1016	287
175°	1059	1056	1056	1060	1055	101
180°	1062	1062	1062	1062	1062	



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	821.7	821.3	821.0	820.7	820.4	819.6	818.5	817.4	816.3	815.2	816.3
5°	818.9	818.4	817.8	817.3	816.7	815.7	814.2	812.7	811.1	809.6	811.0
7.5°	810.9	810.3	809.8	809.3	808.8	807.6	805.8	804.0	802.2	800.3	801.3
10°	803.4	803.0	802.6	802.2	801.8	800.6	798.7	796.8	794.8	792.9	793.3
12.5°	795.0	794.5	793.9	793.4	792.9	791.3	788.8	786.2	783.6	781.0	781.3
15°	778.7	777.8	777.0	776.2	775.3	773.5	770.6	767.7	764.8	761.9	761.8
17.5°	760.2	759.0	757.7	756.4	755.1	752.7	749.0	745.4	741.8	738.2	737.4
20°	745.8	744.4	743.1	741.7	740.3	737.4	733.0	728.6	724.2	719.8	719.1
22.5°	729.9	728.6	727.2	725.9	724.5	721.5	716.8	712.2	707.6	703.0	701.6
25°	706.2	704.1	702.1	700.0	697.9	694.3	689.3	684.1	679.1	673.9	672.2
27.5°	678.9	676.5	673.9	671.4	668.9	665.0	659.5	654.0	648.6	643.1	640.6
30°	659.1	656.5	653.9	651.3	648.7	644.4	638.6	632.9	627.1	621.3	618.2
32.5°	639.8	636.7	633.7	630.6	627.5	623.1	617.2	611.3	605.4	599.5	596.0
35°	608.3	605.0	601.7	598.4	595.1	590.4	584.2	578.0	571.8	565.6	561.6
37.5°	577.5	573.4	569.4	565.4	561.4	556.2	549.8	543.4	537.0	530.6	525.9
40°	555.6	551.5	547.4	543.2	539.2	533.8	527.2	520.6	514.0	507.4	502.1
42.5°	532.9	528.6	524.4	520.2	515.9	510.4	503.5	496.7	489.9	483.1	478.0
45°	498.1	494.1	490.1	486.1	482.1	476.3	468.7	461.1	453.6	446.0	440.5
47.5°	462.0	457.8	453.6	449.4	445.2	439.2	431.6	424.0	416.4	408.7	403.1
50°	439.2	434.6	430.1	425.6	421.0	414.8	407.0	399.2	391.3	383.4	377.6
52.5°	414.4	409.8	405.1	400.5	395.8	389.8	382.4	375.0	367.5	360.1	353.9
55°	377.9	373.5	369.1	364.7	360.3	354.2	346.5	338.8	331.1	323.3	317.2
57.5°	341.0	336.2	331.5	326.9	322.1	316.0	308.6	301.2	293.8	286.3	280.2
60°	317.2	312.3	307.5	302.7	297.9	291.8	284.3	276.9	269.5	262.0	256.0
62.5°	291.9	287.3	282.7	278.1	273.5	267.4	259.9	252.3	244.8	237.3	231.6
65°	255.8	251.2	246.5	241.8	237.1	231.1	223.8	216.5	209.2	201.9	196.4
67.5°	220.0	215.3	210.7	206.0	201.3	195.5	188.5	181.5	174.5	167.5	162.5
70°	195.8	191.1	186.4	181.7	177.0	171.2	164.4	157.5	150.6	143.7	139.4
72.5°	171.9	167.4	162.8	158.2	153.7	148.1	141.7	135.3	128.8	122.4	118.5
75°	136.3	132.2	128.0	123.9	119.8	114.8	109.0	103.2	97.4	91.6	88.6
77.5°	100.9	97.5	94.2	90.9	87.6	83.6	79.0	74.4	69.8	65.1	63.0
80°	80.6	77.2	73.9	70.6	67.3	63.8	59.8	56.0	52.2	48.3	47.0
82.5°	60.7	57.7	54.8	51.8	48.8	46.0	43.4	40.7	38.1	35.5	34.9
85°	34.1	31.6	29.1	26.7	24.1	22.6	21.9	21.2	20.5	19.8	19.6
87.5°	11.6	11.1	10.6	10.1	9.6	9.5	9.6	9.8	9.9	10.1	10.3
90°	0.8	2.3	3.8	5.2	6.7	8.1	9.4	10.7	11.9	13.2	14.1
92.5°	20.0	21.0	22.0	23.1	24.1	25.4	27.0	28.5	30.2	31.7	32.9
95°	53.7	54.1	54.5	54.8	55.2	56.3	58.1	59.9	61.8	63.6	64.9
97.5°	89.2	89.4	89.5	89.7	89.8	91.2	93.7	96.2	98.7	101.3	102.5
100°	115.7	115.7	115.7	115.7	115.7	116.8	119.2	121.6	124.0	126.4	128.1
102.5°	144.1	144.8	145.5	146.3	147.0	148.0	149.2	150.4	151.6	152.9	154.7
105°	188.3	189.2	190.2	191.1	192.0	193.1	194.1	195.3	196.3	197.5	198.5
107.5°	237.3	238.1	239.1	240.0	240.9	241.8	242.6	243.5	244.3	245.2	245.7
110°	270.9	271.9	272.8	273.7	274.7	275.4	275.9	276.5	277.0	277.6	278.1



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	305.3	305.8	306.3	306.8	307.2	307.9	308.5	309.2	309.9	310.6	310.9
115°	356.0	356.8	357.5	358.2	359.0	359.5	359.9	360.3	360.6	361.0	360.9
117.5°	406.9	407.2	407.6	407.9	408.3	408.6	409.0	409.3	409.6	409.9	410.1
120°	438.6	439.6	440.5	441.4	442.3	442.9	443.0	443.3	443.4	443.6	443.6
122.5°	473.0	473.4	473.7	474.0	474.3	474.7	475.2	475.7	476.2	476.7	476.5
125°	519.6	520.7	521.8	522.9	524.0	524.6	524.9	525.1	525.2	525.4	525.1
127.5°	569.2	569.8	570.5	571.0	571.7	572.1	572.3	572.6	572.7	573.0	572.8
130°	598.9	599.8	600.8	601.7	602.6	603.2	603.6	604.0	604.4	604.7	604.5
132.5°	628.7	630.1	631.7	633.2	634.7	635.4	635.4	635.3	635.2	635.1	635.0
135°	675.7	676.9	677.9	679.1	680.2	680.8	681.0	681.2	681.3	681.5	681.5
137.5°	720.1	721.1	722.2	723.3	724.3	725.0	725.5	725.9	726.3	726.7	726.8
140°	748.4	749.3	750.3	751.2	752.1	752.8	753.4	754.0	754.5	755.0	755.5
142.5°	776.9	777.6	778.4	779.2	780.0	780.7	781.4	782.1	782.8	783.5	783.7
145°	818.6	819.4	820.1	820.8	821.6	822.2	822.8	823.4	823.9	824.4	824.4
147.5°	857.4	857.8	858.2	858.5	858.9	859.4	859.8	860.2	860.7	861.1	861.6
150°	883.1	883.0	882.7	882.6	882.4	882.6	883.4	884.1	884.8	885.6	885.6
152.5°	904.2	904.5	904.7	905.1	905.3	905.6	905.9	906.1	906.4	906.8	907.2
155°	936.8	936.8	936.8	936.8	936.8	936.9	937.1	937.3	937.4	937.7	938.4
157.5°	965.9	965.5	965.1	964.7	964.3	964.2	964.3	964.5	964.7	964.9	965.6
160°	983.1	982.5	981.9	981.5	980.9	980.7	980.9	981.0	981.2	981.5	982.2
162.5°	998.3	997.8	997.4	997.0	996.6	996.5	996.5	996.5	996.6	996.6	997.5
165°	1018.6	1018.2	1017.8	1017.5	1017.1	1017.0	1017.2	1017.4	1017.6	1017.7	1018.5
167.5°	1035.8	1035.0	1034.3	1033.6	1032.8	1032.5	1032.5	1032.5	1032.5	1032.5	1033.6
170°	1045.1	1044.3	1043.6	1042.8	1042.1	1041.7	1041.7	1041.7	1041.7	1041.7	1042.8
172.5°	1051.7	1050.9	1050.2	1049.5	1048.7	1048.3	1048.3	1048.3	1048.3	1048.3	1049.5
175°	1059.1	1058.3	1057.6	1056.9	1056.1	1055.7	1055.7	1055.7	1055.7	1055.7	1056.9
177.5°	1062.9	1062.3	1061.7	1061.1	1060.5	1060.1	1060.0	1059.9	1059.7	1059.6	1060.5
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	817.4	818.5	819.6	820.1	820.0	819.9	819.8	819.7
5°	812.4	813.8	815.1	815.7	815.4	815.1	814.9	814.6
7.5°	802.3	803.2	804.2	804.5	804.2	803.9	803.6	803.3
10°	793.7	794.1	794.6	794.6	794.1	793.7	793.3	792.9
12.5°	781.6	782.0	782.2	782.0	781.4	780.8	780.2	779.5
15°	761.7	761.5	761.4	760.7	759.5	758.2	757.0	755.7
17.5°	736.8	736.1	735.4	734.5	733.5	732.5	731.5	730.4
20°	718.4	717.7	717.1	716.1	714.9	713.6	712.4	711.1
22.5°	700.3	698.9	697.6	696.3	695.4	694.3	693.3	692.3
25°	670.4	668.6	666.8	665.1	663.7	662.1	660.6	659.1
27.5°	638.1	635.6	633.1	631.1	629.7	628.2	626.7	625.3
30°	615.0	611.8	608.6	606.4	605.2	604.0	602.8	601.5
32.5°	592.5	589.1	585.5	583.0	581.4	579.8	578.3	576.7
35°	557.6	553.6	549.6	546.7	544.7	542.7	540.9	538.9
37.5°	521.1	516.2	511.4	508.1	506.2	504.4	502.6	500.7
40°	496.8	491.6	486.4	483.0	481.4	479.6	478.0	476.4
42.5°	473.0	468.0	463.0	459.3	456.9	454.4	452.0	449.6
45°	435.0	429.5	424.0	420.2	418.2	416.0	414.0	412.0
47.5°	397.4	391.7	386.0	382.0	379.8	377.5	375.2	372.9
50°	371.9	366.1	360.3	356.4	354.3	352.3	350.2	348.1
52.5°	347.7	341.4	335.3	331.1	329.1	327.0	324.9	322.9
55°	311.0	304.8	298.6	294.4	292.2	290.0	287.8	285.6
57.5°	274.2	268.2	262.1	258.0	256.1	254.1	252.3	250.3
60°	249.9	243.9	237.8	233.7	231.7	229.6	227.6	225.5
62.5°	226.0	220.4	214.7	210.9	208.9	206.8	204.7	202.7
65°	190.9	185.4	179.9	176.1	174.1	172.0	169.9	167.9
67.5°	157.4	152.4	147.3	144.0	142.4	140.7	139.0	137.4
70°	135.2	130.9	126.6	123.7	122.1	120.4	118.7	117.1
72.5°	114.5	110.6	106.6	104.1	103.1	101.9	100.9	99.7
75°	85.6	82.6	79.6	77.5	76.6	75.7	74.7	73.7
77.5°	60.9	58.8	56.7	55.3	54.5	53.8	53.2	52.4
80°	45.8	44.6	43.4	42.6	42.3	42.1	41.7	41.5
82.5°	34.2	33.7	33.1	32.8	32.6	32.4	32.3	32.1
85°	19.6	19.4	19.2	19.2	19.0	18.8	18.8	18.6
87.5°	10.4	10.6	10.8	10.9	10.9	10.9	10.9	10.9
90°	15.1	16.0	16.9	17.6	18.2	18.8	19.2	19.8
92.5°	34.2	35.4	36.6	37.3	37.7	38.2	38.6	39.0
95°	66.2	67.4	68.7	69.5	70.0	70.3	70.7	71.0
97.5°	103.7	104.9	106.2	106.8	107.0	107.3	107.5	107.7
100°	129.7	131.3	133.0	134.0	134.4	134.8	135.1	135.5
102.5°	156.5	158.2	160.0	161.2	161.7	162.2	162.7	163.2
105°	199.7	200.7	201.9	202.7	203.3	203.7	204.3	204.9
107.5°	246.3	246.9	247.4	247.7	247.6	247.6	247.5	247.5
110°	278.7	279.2	279.8	280.0	279.8	279.6	279.4	279.2



TEST NUMBER: P333671-930

CATALOG NUMBER: S125RDIW-S610D1050U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	311.1	311.4	311.6	311.6	311.3	311.0	310.6	310.3
115°	360.6	360.4	360.3	360.1	359.9	359.7	359.5	359.4
117.5°	410.2	410.3	410.5	410.2	409.4	408.7	408.0	407.2
120°	443.6	443.6	443.6	443.3	442.5	441.8	441.1	440.3
122.5°	476.4	476.2	476.1	475.7	475.2	474.5	473.9	473.4
125°	524.6	524.3	523.9	523.7	523.5	523.3	523.1	522.9
127.5°	572.6	572.4	572.3	572.0	571.6	571.3	570.9	570.5
130°	604.4	604.1	604.0	603.7	603.3	603.0	602.6	602.3
132.5°	634.7	634.5	634.4	634.1	633.5	633.0	632.5	631.9
135°	681.5	681.5	681.5	681.2	680.4	679.7	679.0	678.2
137.5°	727.1	727.3	727.5	727.2	726.3	725.4	724.4	723.5
140°	755.8	756.2	756.5	756.3	755.4	754.4	753.5	752.6
142.5°	783.9	784.2	784.4	784.0	783.1	782.2	781.3	780.3
145°	824.4	824.4	824.4	824.2	823.6	823.0	822.6	822.0
147.5°	862.0	862.4	862.9	862.5	861.3	860.0	858.8	857.5
150°	885.6	885.6	885.6	885.4	885.0	884.7	884.3	883.9
152.5°	907.6	908.1	908.5	908.4	907.8	907.1	906.4	905.7
155°	939.1	939.9	940.6	940.4	939.6	938.7	937.8	936.8
157.5°	966.4	967.1	967.8	967.6	966.4	965.2	963.9	962.8
160°	982.9	983.7	984.4	984.2	983.3	982.4	981.5	980.6
162.5°	998.4	999.2	1000.1	1000.0	999.0	997.9	996.9	995.8
165°	1019.2	1019.9	1020.7	1020.5	1019.5	1018.3	1017.2	1016.1
167.5°	1034.7	1035.8	1036.9	1036.9	1035.8	1034.6	1033.5	1032.3
170°	1043.9	1045.1	1046.1	1046.0	1044.7	1043.5	1042.2	1040.9
172.5°	1050.5	1051.7	1052.7	1052.7	1051.6	1050.4	1049.3	1048.1
175°	1057.9	1059.1	1060.2	1060.1	1058.8	1057.5	1056.2	1054.9
177.5°	1061.4	1062.3	1063.1	1063.0	1062.0	1060.9	1060.0	1058.9
180°	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5	1061.5

(END OF REPORT)