

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333663-930

Luminaire Tested: **S125RDIW-S610D470U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333663-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S610D470U930-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3263.7 lumens  
Efficiency: N/A  
Efficacy: 108.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 30.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20		
RC	80					70					50					30					10	0	
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10			50	30	10	0
RCR																							
0	109	109	109	109		102	102	102	102		89	89	89		76	76	76			65	65	65	59
1	100	96	92	89		93	90	86	83		78	76	73		67	66	64			58	56	55	51
2	91	84	78	73		85	79	73	69		69	65	61		60	57	54			51	49	47	43
3	84	74	67	61		78	69	63	58		61	56	52		53	49	46			45	43	40	36
4	77	66	58	52		71	62	55	49		54	49	44		47	43	39			41	38	35	31
5	70	59	51	45		66	55	48	42		49	43	38		43	38	34			37	33	30	27
6	65	53	45	39		61	50	42	37		44	38	34		39	34	30			33	30	27	24
7	60	48	40	34		56	45	38	33		40	34	30		35	30	27			31	27	24	22
8	56	44	36	30		52	41	34	29		37	31	27		32	28	24			28	24	22	19
9	52	40	32	27		49	38	31	26		34	28	24		30	25	22			26	22	20	18
10	49	37	29	25		46	35	28	24		31	25	22		28	23	20			24	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	5297	5297	5297
5°	5309	5249	5281
10°	5269	5200	5200
15°	5207	5094	5053
20°	5126	4947	4887
25°	5032	4802	4697
30°	4915	4633	4486
35°	4796	4459	4249
40°	4684	4278	4016
45°	4549	4074	3763
50°	4413	3852	3497
55°	4255	3640	3216
60°	4097	3384	2913
65°	3909	3085	2566
70°	3697	2713	2211
75°	3401	2286	1839
80°	2998	1796	1543
85°	2527	1467	1378



TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.1	2.4
10°-20°	215.5	6.6
20°-30°	312.5	9.6
30°-40°	356.2	10.9
40°-50°	347.2	10.6
50°-60°	292.3	9.0
60°-70°	204.9	6.3
70°-80°	105.3	3.2
80°-90°	27.6	0.8
90°-100°	31.8	1.0
100°-110°	93.9	2.9
110°-120°	159.1	4.9
120°-130°	209.4	6.4
130°-140°	234.6	7.2
140°-150°	229.9	7.0
150°-160°	193.1	5.9
160°-170°	128.4	3.9
170°-180°	44.9	1.4
0°-30°	605.2	18.5
0°-40°	961.4	29.5
0°-60°	1600.8	49.1
0°-90°	1938.6	59.4
90°-120°	284.8	8.7
90°-150°	958.7	29.4
90°-180°	1325.0	40.6
0°-180°	3263.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	820	820	820	820	820	
5°	819	816	810	815	815	78
15°	779	774	762	761	756	219
25°	706	696	674	666	659	325
35°	608	593	566	548	539	381
45°	498	479	446	422	412	384
55°	378	357	323	296	286	338
65°	256	234	202	178	168	253
75°	136	117	92	79	74	144
85°	34	23	20	19	19	38
90°	0	3	6	8	9	3
95°	24	25	28	31	32	26
105°	84	86	88	90	92	90
115°	159	161	162	161	161	157
125°	232	235	235	234	234	208
135°	302	304	305	305	303	233
145°	366	368	369	369	368	229
155°	419	419	419	421	419	193
165°	456	455	455	457	454	128
175°	474	472	472	474	472	45
180°	475	475	475	475	475	



TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	821.7	821.3	821.0	820.7	820.4	819.6	818.5	817.4	816.3	815.2	816.3
5°	818.9	818.4	817.8	817.3	816.7	815.7	814.2	812.7	811.1	809.6	811.0
7.5°	810.9	810.3	809.8	809.3	808.8	807.6	805.8	804.0	802.2	800.3	801.3
10°	803.4	803.0	802.6	802.2	801.8	800.6	798.7	796.8	794.8	792.9	793.3
12.5°	795.0	794.5	793.9	793.4	792.9	791.3	788.8	786.2	783.6	781.0	781.3
15°	778.7	777.8	777.0	776.2	775.3	773.5	770.6	767.7	764.8	761.9	761.8
17.5°	760.2	759.0	757.7	756.4	755.1	752.7	749.0	745.4	741.8	738.2	737.4
20°	745.8	744.4	743.1	741.7	740.3	737.4	733.0	728.6	724.2	719.8	719.1
22.5°	729.9	728.6	727.2	725.9	724.5	721.5	716.8	712.2	707.6	703.0	701.6
25°	706.2	704.1	702.1	700.0	697.9	694.3	689.3	684.1	679.1	673.9	672.2
27.5°	678.9	676.5	673.9	671.4	668.9	665.0	659.5	654.0	648.6	643.1	640.6
30°	659.1	656.5	653.9	651.3	648.7	644.4	638.6	632.9	627.1	621.3	618.2
32.5°	639.8	636.7	633.7	630.6	627.5	623.1	617.2	611.3	605.4	599.5	596.0
35°	608.3	605.0	601.7	598.4	595.1	590.4	584.2	578.0	571.8	565.6	561.6
37.5°	577.5	573.4	569.4	565.4	561.4	556.2	549.8	543.4	537.0	530.6	525.9
40°	555.6	551.5	547.4	543.2	539.2	533.8	527.2	520.6	514.0	507.4	502.1
42.5°	532.9	528.6	524.4	520.2	515.9	510.4	503.5	496.7	489.9	483.1	478.0
45°	498.1	494.1	490.1	486.1	482.1	476.3	468.7	461.1	453.6	446.0	440.5
47.5°	462.0	457.8	453.6	449.4	445.2	439.2	431.6	424.0	416.4	408.7	403.1
50°	439.2	434.6	430.1	425.6	421.0	414.8	407.0	399.2	391.3	383.4	377.6
52.5°	414.4	409.8	405.1	400.5	395.8	389.8	382.4	375.0	367.5	360.1	353.9
55°	377.9	373.5	369.1	364.7	360.3	354.2	346.5	338.8	331.1	323.3	317.2
57.5°	341.0	336.2	331.5	326.9	322.1	316.0	308.6	301.2	293.8	286.3	280.2
60°	317.2	312.3	307.5	302.7	297.9	291.8	284.3	276.9	269.5	262.0	256.0
62.5°	291.9	287.3	282.7	278.1	273.5	267.4	259.9	252.3	244.8	237.3	231.6
65°	255.8	251.2	246.5	241.8	237.1	231.1	223.8	216.5	209.2	201.9	196.4
67.5°	220.0	215.3	210.7	206.0	201.3	195.5	188.5	181.5	174.5	167.5	162.5
70°	195.8	191.1	186.4	181.7	177.0	171.2	164.4	157.5	150.6	143.7	139.4
72.5°	171.9	167.4	162.8	158.2	153.7	148.1	141.7	135.3	128.8	122.4	118.5
75°	136.3	132.2	128.0	123.9	119.8	114.8	109.0	103.2	97.4	91.6	88.6
77.5°	100.9	97.5	94.2	90.9	87.6	83.6	79.0	74.4	69.8	65.1	63.0
80°	80.6	77.2	73.9	70.6	67.3	63.8	59.8	56.0	52.2	48.3	47.0
82.5°	60.7	57.7	54.8	51.8	48.8	46.0	43.4	40.7	38.1	35.5	34.9
85°	34.1	31.6	29.1	26.7	24.1	22.6	21.9	21.2	20.5	19.8	19.6
87.5°	11.5	10.8	10.2	9.5	8.9	8.6	8.6	8.6	8.6	8.6	8.7
90°	0.4	1.1	1.7	2.4	3.0	3.6	4.2	4.7	5.3	6.0	6.4
92.5°	9.0	9.4	9.9	10.4	10.8	11.3	12.1	12.8	13.5	14.2	14.8
95°	24.1	24.2	24.4	24.5	24.7	25.2	26.0	26.8	27.6	28.5	29.0
97.5°	39.9	39.9	40.0	40.1	40.2	40.8	41.9	43.0	44.2	45.3	45.8
100°	51.8	51.8	51.8	51.8	51.8	52.3	53.3	54.4	55.4	56.5	57.3
102.5°	64.4	64.7	65.1	65.5	65.8	66.2	66.8	67.3	67.8	68.3	69.1
105°	84.2	84.6	85.0	85.4	85.9	86.3	86.8	87.3	87.8	88.3	88.8
107.5°	106.2	106.6	107.0	107.4	107.8	108.2	108.5	108.9	109.3	109.7	109.9
110°	121.2	121.6	122.1	122.5	122.9	123.2	123.4	123.7	123.9	124.2	124.4



TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	136.6	136.8	137.0	137.2	137.5	137.7	138.0	138.4	138.6	138.9	139.1
115°	159.2	159.6	160.0	160.3	160.6	160.9	161.0	161.2	161.3	161.5	161.4
117.5°	182.1	182.1	182.3	182.5	182.6	182.8	183.0	183.0	183.2	183.4	183.4
120°	196.2	196.7	197.1	197.5	197.9	198.1	198.2	198.3	198.4	198.4	198.4
122.5°	211.6	211.7	211.9	212.1	212.1	212.4	212.5	212.8	213.0	213.2	213.1
125°	232.4	232.9	233.4	233.9	234.4	234.7	234.8	234.9	235.0	235.1	234.9
127.5°	254.6	254.9	255.2	255.4	255.8	255.9	256.0	256.1	256.2	256.3	256.2
130°	267.9	268.3	268.7	269.1	269.5	269.9	270.0	270.2	270.4	270.5	270.4
132.5°	281.2	281.8	282.6	283.2	283.9	284.2	284.2	284.1	284.1	284.1	284.0
135°	302.2	302.8	303.3	303.8	304.3	304.5	304.6	304.7	304.8	304.8	304.8
137.5°	322.0	322.5	323.0	323.5	324.0	324.3	324.5	324.7	324.8	325.1	325.1
140°	334.8	335.2	335.6	336.0	336.4	336.8	337.0	337.3	337.5	337.8	337.9
142.5°	347.5	347.8	348.2	348.5	348.9	349.2	349.5	349.8	350.2	350.5	350.6
145°	366.2	366.6	366.9	367.2	367.5	367.8	368.0	368.3	368.5	368.8	368.8
147.5°	383.5	383.7	383.8	384.0	384.3	384.4	384.6	384.8	385.0	385.2	385.4
150°	395.0	394.9	394.8	394.8	394.7	394.8	395.2	395.5	395.8	396.2	396.2
152.5°	404.5	404.6	404.7	404.8	405.0	405.0	405.2	405.4	405.4	405.6	405.8
155°	419.1	419.1	419.1	419.1	419.1	419.1	419.1	419.2	419.3	419.4	419.7
157.5°	432.0	431.9	431.7	431.5	431.3	431.3	431.4	431.5	431.5	431.6	431.9
160°	439.8	439.5	439.2	439.0	438.7	438.6	438.7	438.8	438.9	439.0	439.4
162.5°	446.5	446.4	446.2	446.0	445.8	445.7	445.7	445.7	445.8	445.8	446.2
165°	455.6	455.4	455.3	455.1	454.9	454.9	455.0	455.1	455.2	455.3	455.6
167.5°	463.3	463.0	462.7	462.4	462.0	461.9	461.9	461.9	461.9	461.9	462.4
170°	467.4	467.1	466.8	466.4	466.1	465.9	465.9	465.9	465.9	465.9	466.4
172.5°	470.4	470.1	469.8	469.4	469.1	469.0	469.0	469.0	469.0	469.0	469.4
175°	473.8	473.4	473.0	472.7	472.4	472.2	472.2	472.2	472.2	472.2	472.7
177.5°	475.4	475.2	474.9	474.7	474.3	474.2	474.2	474.1	474.0	473.9	474.3
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8



TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	817.4	818.5	819.6	820.1	820.0	819.9	819.8	819.7
5°	812.4	813.8	815.1	815.7	815.4	815.1	814.9	814.6
7.5°	802.3	803.2	804.2	804.5	804.2	803.9	803.6	803.3
10°	793.7	794.1	794.6	794.6	794.1	793.7	793.3	792.9
12.5°	781.6	782.0	782.2	782.0	781.4	780.8	780.2	779.5
15°	761.7	761.5	761.4	760.7	759.5	758.2	757.0	755.7
17.5°	736.8	736.1	735.4	734.5	733.5	732.5	731.5	730.4
20°	718.4	717.7	717.1	716.1	714.9	713.6	712.4	711.1
22.5°	700.3	698.9	697.6	696.3	695.4	694.3	693.3	692.3
25°	670.4	668.6	666.8	665.1	663.7	662.1	660.6	659.1
27.5°	638.1	635.6	633.1	631.1	629.7	628.2	626.7	625.3
30°	615.0	611.8	608.6	606.4	605.2	604.0	602.8	601.5
32.5°	592.5	589.1	585.5	583.0	581.4	579.8	578.3	576.7
35°	557.6	553.6	549.6	546.7	544.7	542.7	540.9	538.9
37.5°	521.1	516.2	511.4	508.1	506.2	504.4	502.6	500.7
40°	496.8	491.6	486.4	483.0	481.4	479.6	478.0	476.4
42.5°	473.0	468.0	463.0	459.3	456.9	454.4	452.0	449.6
45°	435.0	429.5	424.0	420.2	418.2	416.0	414.0	412.0
47.5°	397.4	391.7	386.0	382.0	379.8	377.5	375.2	372.9
50°	371.9	366.1	360.3	356.4	354.3	352.3	350.2	348.1
52.5°	347.7	341.4	335.3	331.1	329.1	327.0	324.9	322.9
55°	311.0	304.8	298.6	294.4	292.2	290.0	287.8	285.6
57.5°	274.2	268.2	262.1	258.0	256.1	254.1	252.3	250.3
60°	249.9	243.9	237.8	233.7	231.7	229.6	227.6	225.5
62.5°	226.0	220.4	214.7	210.9	208.9	206.8	204.7	202.7
65°	190.9	185.4	179.9	176.1	174.1	172.0	169.9	167.9
67.5°	157.4	152.4	147.3	144.0	142.4	140.7	139.0	137.4
70°	135.2	130.9	126.6	123.7	122.1	120.4	118.7	117.1
72.5°	114.5	110.6	106.6	104.1	103.1	101.9	100.9	99.7
75°	85.6	82.6	79.6	77.5	76.6	75.7	74.7	73.7
77.5°	60.9	58.8	56.7	55.3	54.5	53.8	53.2	52.4
80°	45.8	44.6	43.4	42.6	42.3	42.1	41.7	41.5
82.5°	34.2	33.7	33.1	32.8	32.6	32.4	32.3	32.1
85°	19.6	19.4	19.2	19.2	19.0	18.8	18.8	18.6
87.5°	8.8	8.9	9.0	9.0	8.9	8.8	8.8	8.7
90°	6.8	7.2	7.6	7.9	8.2	8.4	8.6	8.9
92.5°	15.2	15.8	16.4	16.7	16.9	17.0	17.3	17.4
95°	29.6	30.2	30.7	31.1	31.3	31.5	31.6	31.8
97.5°	46.4	47.0	47.5	47.8	47.9	48.0	48.1	48.2
100°	58.0	58.8	59.5	59.9	60.1	60.3	60.4	60.6
102.5°	70.0	70.8	71.6	72.1	72.3	72.6	72.8	73.1
105°	89.3	89.8	90.3	90.7	90.9	91.2	91.4	91.6
107.5°	110.1	110.4	110.6	110.8	110.8	110.7	110.7	110.7
110°	124.7	124.9	125.1	125.2	125.1	125.1	125.0	124.9





TEST NUMBER: P333663-930

CATALOG NUMBER: S125RDIW-S610D470U930-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	139.2	139.3	139.4	139.4	139.3	139.1	138.9	138.8
115°	161.3	161.3	161.2	161.1	161.0	160.9	160.9	160.8
117.5°	183.5	183.5	183.6	183.5	183.2	182.9	182.5	182.1
120°	198.4	198.4	198.4	198.3	198.0	197.6	197.3	197.0
122.5°	213.1	213.0	213.0	212.8	212.5	212.3	212.0	211.7
125°	234.7	234.6	234.4	234.2	234.2	234.1	234.0	233.9
127.5°	256.2	256.1	256.0	255.8	255.7	255.5	255.4	255.2
130°	270.4	270.3	270.2	270.0	269.9	269.7	269.5	269.4
132.5°	283.9	283.8	283.7	283.6	283.4	283.2	282.9	282.7
135°	304.8	304.8	304.8	304.7	304.4	304.0	303.7	303.4
137.5°	325.2	325.3	325.5	325.3	324.9	324.5	324.0	323.6
140°	338.1	338.3	338.4	338.3	337.9	337.5	337.0	336.6
142.5°	350.7	350.7	350.8	350.7	350.3	349.8	349.4	349.0
145°	368.8	368.8	368.8	368.7	368.4	368.2	367.9	367.7
147.5°	385.6	385.8	386.0	385.8	385.2	384.7	384.1	383.6
150°	396.2	396.2	396.2	396.1	395.9	395.7	395.6	395.4
152.5°	406.0	406.2	406.3	406.3	406.0	405.8	405.4	405.1
155°	420.0	420.4	420.7	420.7	420.3	419.9	419.5	419.1
157.5°	432.3	432.6	432.9	432.8	432.3	431.7	431.2	430.6
160°	439.7	440.0	440.3	440.3	439.9	439.4	439.0	438.6
162.5°	446.6	446.9	447.4	447.4	446.9	446.4	445.9	445.4
165°	455.9	456.2	456.6	456.5	456.0	455.5	455.0	454.5
167.5°	462.8	463.3	463.8	463.8	463.3	462.8	462.3	461.8
170°	466.9	467.4	468.0	467.9	467.3	466.8	466.2	465.6
172.5°	469.9	470.4	470.9	470.9	470.3	469.9	469.4	468.9
175°	473.2	473.8	474.3	474.2	473.6	473.0	472.5	471.9
177.5°	474.7	475.2	475.6	475.5	475.1	474.6	474.1	473.7
180°	474.8	474.8	474.8	474.8	474.8	474.8	474.8	474.8

(END OF REPORT)