

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333666-930

Luminaire Tested: **S125RDIW-S610D770U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333666-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U930-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4441.8 lumens
Efficiency: N/A
Efficacy: 118.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	92	89	85	88	85	81	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	80	74	69	65	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	55	50	46	45	41	39	35	33	31	27
4	74	63	55	49	67	58	51	46	49	44	40	40	36	33	32	29	27	23
5	68	56	48	42	62	52	45	40	43	38	34	36	32	29	29	26	24	20
6	62	50	42	37	57	47	40	34	39	34	30	32	28	25	26	23	21	18
7	58	46	38	32	53	42	35	30	36	30	26	29	25	22	24	21	19	16
8	53	41	34	29	49	38	31	27	32	27	23	27	23	20	22	19	17	14
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	20	17	15	13
10	46	35	27	23	43	32	26	21	27	22	19	23	19	16	19	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5297	5297	5297
5°	5309	5249	5281
10°	5269	5200	5200
15°	5207	5094	5053
20°	5126	4947	4887
25°	5032	4802	4697
30°	4915	4633	4486
35°	4796	4459	4249
40°	4684	4278	4016
45°	4549	4074	3763
50°	4413	3852	3497
55°	4255	3640	3216
60°	4097	3384	2913
65°	3909	3085	2566
70°	3697	2713	2211
75°	3401	2286	1839
80°	2998	1796	1543
85°	2527	1467	1378



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	1.7
10°-20°	215.5	4.9
20°-30°	312.5	7.0
30°-40°	356.2	8.0
40°-50°	347.2	7.8
50°-60°	292.3	6.6
60°-70°	204.9	4.6
70°-80°	105.3	2.4
80°-90°	28.3	0.6
90°-100°	29.6	0.7
100°-110°	182.5	4.1
110°-120°	331.0	7.5
120°-130°	424.8	9.6
130°-140°	456.9	10.3
140°-150°	428.9	9.7
150°-160°	346.9	7.8
160°-170°	224.4	5.1
170°-180°	77.4	1.7
0°-30°	605.2	13.6
0°-40°	961.4	21.6
0°-60°	1600.8	36.0
0°-90°	1939.3	43.7
90°-120°	543.2	12.2
90°-150°	1853.8	41.7
90°-180°	2503.0	56.4
0°-180°	4441.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	820	820	820	820	820	
5°	819	816	810	815	815	78
15°	779	774	762	761	756	219
25°	706	696	674	666	659	325
35°	608	593	566	548	539	381
45°	498	479	446	422	412	384
55°	378	357	323	296	286	338
65°	256	234	202	178	168	253
75°	136	117	92	79	74	144
85°	34	23	20	19	19	38
90°	1	5	10	13	14	3
95°	34	32	10	12	13	44
105°	178	180	180	180	179	188
115°	334	336	337	335	331	330
125°	474	478	478	476	474	423
135°	591	595	594	592	589	456
145°	686	687	687	687	684	429
155°	755	752	753	754	750	348
165°	797	793	794	797	793	225
175°	815	812	812	816	811	78
180°	815	815	815	815	815	



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	821.7	821.3	821.0	820.7	820.4	819.6	818.5	817.4	816.3	815.2	816.3
5°	818.9	818.4	817.8	817.3	816.7	815.7	814.2	812.7	811.1	809.6	811.0
7.5°	810.9	810.3	809.8	809.3	808.8	807.6	805.8	804.0	802.2	800.3	801.3
10°	803.4	803.0	802.6	802.2	801.8	800.6	798.7	796.8	794.8	792.9	793.3
12.5°	795.0	794.5	793.9	793.4	792.9	791.3	788.8	786.2	783.6	781.0	781.3
15°	778.7	777.8	777.0	776.2	775.3	773.5	770.6	767.7	764.8	761.9	761.8
17.5°	760.2	759.0	757.7	756.4	755.1	752.7	749.0	745.4	741.8	738.2	737.4
20°	745.8	744.4	743.1	741.7	740.3	737.4	733.0	728.6	724.2	719.8	719.1
22.5°	729.9	728.6	727.2	725.9	724.5	721.5	716.8	712.2	707.6	703.0	701.6
25°	706.2	704.1	702.1	700.0	697.9	694.3	689.3	684.1	679.1	673.9	672.2
27.5°	678.9	676.5	673.9	671.4	668.9	665.0	659.5	654.0	648.6	643.1	640.6
30°	659.1	656.5	653.9	651.3	648.7	644.4	638.6	632.9	627.1	621.3	618.2
32.5°	639.8	636.7	633.7	630.6	627.5	623.1	617.2	611.3	605.4	599.5	596.0
35°	608.3	605.0	601.7	598.4	595.1	590.4	584.2	578.0	571.8	565.6	561.6
37.5°	577.5	573.4	569.4	565.4	561.4	556.2	549.8	543.4	537.0	530.6	525.9
40°	555.6	551.5	547.4	543.2	539.2	533.8	527.2	520.6	514.0	507.4	502.1
42.5°	532.9	528.6	524.4	520.2	515.9	510.4	503.5	496.7	489.9	483.1	478.0
45°	498.1	494.1	490.1	486.1	482.1	476.3	468.7	461.1	453.6	446.0	440.5
47.5°	462.0	457.8	453.6	449.4	445.2	439.2	431.6	424.0	416.4	408.7	403.1
50°	439.2	434.6	430.1	425.6	421.0	414.8	407.0	399.2	391.3	383.4	377.6
52.5°	414.4	409.8	405.1	400.5	395.8	389.8	382.4	375.0	367.5	360.1	353.9
55°	377.9	373.5	369.1	364.7	360.3	354.2	346.5	338.8	331.1	323.3	317.2
57.5°	341.0	336.2	331.5	326.9	322.1	316.0	308.6	301.2	293.8	286.3	280.2
60°	317.2	312.3	307.5	302.7	297.9	291.8	284.3	276.9	269.5	262.0	256.0
62.5°	291.9	287.3	282.7	278.1	273.5	267.4	259.9	252.3	244.8	237.3	231.6
65°	255.8	251.2	246.5	241.8	237.1	231.1	223.8	216.5	209.2	201.9	196.4
67.5°	220.0	215.3	210.7	206.0	201.3	195.5	188.5	181.5	174.5	167.5	162.5
70°	195.8	191.1	186.4	181.7	177.0	171.2	164.4	157.5	150.6	143.7	139.4
72.5°	171.9	167.4	162.8	158.2	153.7	148.1	141.7	135.3	128.8	122.4	118.5
75°	136.3	132.2	128.0	123.9	119.8	114.8	109.0	103.2	97.4	91.6	88.6
77.5°	100.9	97.5	94.2	90.9	87.6	83.6	79.0	74.4	69.8	65.1	63.0
80°	80.6	77.2	73.9	70.6	67.3	63.8	59.8	56.0	52.2	48.3	47.0
82.5°	60.7	57.7	54.8	51.8	48.8	46.0	43.4	40.7	38.1	35.5	34.9
85°	34.1	31.6	29.1	26.7	24.1	22.6	21.9	21.2	20.5	19.8	19.6
87.5°	11.5	10.9	10.4	9.9	9.3	9.0	9.1	9.2	9.3	9.4	9.5
90°	0.6	1.7	2.8	3.8	4.9	5.9	6.8	7.8	8.7	9.7	10.4
92.5°	9.3	8.6	7.8	7.0	6.3	6.4	7.2	8.0	8.8	9.7	10.4
95°	34.4	34.0	33.6	33.3	32.9	30.1	24.9	19.9	14.8	9.7	10.4
97.5°	71.9	72.6	73.4	74.0	74.8	70.1	60.0	49.9	39.8	29.8	25.9
100°	100.9	101.3	101.7	102.1	102.5	103.0	103.5	104.0	104.6	105.1	85.1
102.5°	130.4	130.9	131.4	131.9	132.4	132.8	133.1	133.5	133.8	134.1	130.4
105°	177.6	178.1	178.7	179.2	179.8	180.0	180.0	180.0	180.0	180.0	180.0
107.5°	226.7	226.7	226.7	226.7	226.7	226.8	227.1	227.3	227.6	227.9	227.9
110°	258.5	258.5	258.5	258.5	258.5	258.7	258.9	259.3	259.5	259.8	259.3



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	288.5	288.9	289.2	289.5	289.8	290.1	290.2	290.4	290.6	290.7	290.2
115°	333.5	334.1	334.8	335.5	336.1	336.6	336.7	336.8	337.0	337.1	336.6
117.5°	380.0	379.9	379.9	379.9	379.8	380.1	380.7	381.2	381.6	382.1	381.5
120°	409.0	408.9	408.7	408.5	408.5	408.5	409.0	409.4	409.8	410.2	409.9
122.5°	434.6	435.1	435.6	436.1	436.7	437.0	437.2	437.3	437.6	437.7	437.5
125°	474.3	475.2	476.1	477.0	478.0	478.4	478.4	478.4	478.4	478.4	477.9
127.5°	512.0	512.7	513.4	514.0	514.7	515.0	514.9	514.9	514.8	514.7	514.4
130°	535.2	535.9	536.5	537.3	537.9	538.3	538.4	538.6	538.7	538.8	538.4
132.5°	558.4	559.2	560.0	560.8	561.6	561.8	561.5	561.2	560.9	560.6	560.5
135°	591.4	592.2	593.0	593.9	594.7	594.9	594.7	594.4	594.1	593.9	593.5
137.5°	621.7	622.5	623.1	623.9	624.5	624.8	624.5	624.3	624.0	623.8	623.9
140°	641.6	641.8	642.1	642.4	642.6	642.7	642.5	642.5	642.3	642.1	642.5
142.5°	659.4	659.6	659.7	659.9	660.1	660.2	660.5	660.6	660.8	661.0	661.0
145°	685.7	685.9	686.2	686.5	686.7	686.9	686.9	686.9	686.9	686.9	687.0
147.5°	708.7	708.6	708.5	708.5	708.4	708.5	708.7	708.7	708.9	709.1	709.2
150°	723.1	722.8	722.6	722.3	722.0	722.0	722.3	722.6	722.8	723.1	723.4
152.5°	737.1	736.5	736.0	735.4	734.7	734.6	734.9	735.2	735.4	735.6	736.0
155°	755.1	754.3	753.5	752.7	752.0	751.6	752.0	752.2	752.4	752.7	753.1
157.5°	769.0	768.6	768.1	767.6	767.1	766.9	766.9	767.0	767.0	767.0	767.4
160°	778.7	777.9	777.1	776.2	775.5	775.1	775.3	775.4	775.5	775.7	776.2
162.5°	786.4	785.6	784.8	784.0	783.2	782.9	783.0	783.2	783.3	783.4	784.2
165°	796.8	796.0	795.2	794.4	793.6	793.3	793.4	793.5	793.7	793.8	794.6
167.5°	804.5	803.7	802.9	802.1	801.2	800.9	801.0	801.1	801.3	801.4	802.3
170°	808.9	808.0	807.0	806.1	805.1	804.7	804.9	805.0	805.1	805.3	806.3
172.5°	811.8	810.9	809.9	808.9	808.0	807.7	808.0	808.2	808.5	808.7	809.6
175°	815.0	814.2	813.3	812.5	811.7	811.4	811.5	811.6	811.8	812.0	813.0
177.5°	816.4	815.7	815.1	814.5	813.8	813.5	813.7	813.8	813.8	814.0	814.7
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	817.4	818.5	819.6	820.1	820.0	819.9	819.8	819.7
5°	812.4	813.8	815.1	815.7	815.4	815.1	814.9	814.6
7.5°	802.3	803.2	804.2	804.5	804.2	803.9	803.6	803.3
10°	793.7	794.1	794.6	794.6	794.1	793.7	793.3	792.9
12.5°	781.6	782.0	782.2	782.0	781.4	780.8	780.2	779.5
15°	761.7	761.5	761.4	760.7	759.5	758.2	757.0	755.7
17.5°	736.8	736.1	735.4	734.5	733.5	732.5	731.5	730.4
20°	718.4	717.7	717.1	716.1	714.9	713.6	712.4	711.1
22.5°	700.3	698.9	697.6	696.3	695.4	694.3	693.3	692.3
25°	670.4	668.6	666.8	665.1	663.7	662.1	660.6	659.1
27.5°	638.1	635.6	633.1	631.1	629.7	628.2	626.7	625.3
30°	615.0	611.8	608.6	606.4	605.2	604.0	602.8	601.5
32.5°	592.5	589.1	585.5	583.0	581.4	579.8	578.3	576.7
35°	557.6	553.6	549.6	546.7	544.7	542.7	540.9	538.9
37.5°	521.1	516.2	511.4	508.1	506.2	504.4	502.6	500.7
40°	496.8	491.6	486.4	483.0	481.4	479.6	478.0	476.4
42.5°	473.0	468.0	463.0	459.3	456.9	454.4	452.0	449.6
45°	435.0	429.5	424.0	420.2	418.2	416.0	414.0	412.0
47.5°	397.4	391.7	386.0	382.0	379.8	377.5	375.2	372.9
50°	371.9	366.1	360.3	356.4	354.3	352.3	350.2	348.1
52.5°	347.7	341.4	335.3	331.1	329.1	327.0	324.9	322.9
55°	311.0	304.8	298.6	294.4	292.2	290.0	287.8	285.6
57.5°	274.2	268.2	262.1	258.0	256.1	254.1	252.3	250.3
60°	249.9	243.9	237.8	233.7	231.7	229.6	227.6	225.5
62.5°	226.0	220.4	214.7	210.9	208.9	206.8	204.7	202.7
65°	190.9	185.4	179.9	176.1	174.1	172.0	169.9	167.9
67.5°	157.4	152.4	147.3	144.0	142.4	140.7	139.0	137.4
70°	135.2	130.9	126.6	123.7	122.1	120.4	118.7	117.1
72.5°	114.5	110.6	106.6	104.1	103.1	101.9	100.9	99.7
75°	85.6	82.6	79.6	77.5	76.6	75.7	74.7	73.7
77.5°	60.9	58.8	56.7	55.3	54.5	53.8	53.2	52.4
80°	45.8	44.6	43.4	42.6	42.3	42.1	41.7	41.5
82.5°	34.2	33.7	33.1	32.8	32.6	32.4	32.3	32.1
85°	19.6	19.4	19.2	19.2	19.0	18.8	18.8	18.6
87.5°	9.6	9.8	9.9	9.9	9.9	9.9	9.9	9.9
90°	11.0	11.7	12.3	12.9	13.3	13.7	14.1	14.5
92.5°	11.0	11.7	12.3	12.8	13.0	13.1	13.4	13.5
95°	11.0	11.7	12.3	12.7	12.7	12.7	12.7	12.7
97.5°	22.2	18.3	14.6	12.7	12.7	12.7	12.7	12.7
100°	65.1	45.1	25.1	14.8	14.3	13.8	13.2	12.7
102.5°	126.5	122.8	119.0	112.5	103.4	94.2	85.1	76.0
105°	180.0	180.0	180.0	179.9	179.9	179.7	179.5	179.4
107.5°	228.0	228.0	228.0	227.8	227.4	227.0	226.6	226.2
110°	258.9	258.5	258.1	258.0	258.1	258.3	258.4	258.5



TEST NUMBER: P333666-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	289.7	289.2	288.6	288.3	288.1	288.0	287.7	287.6
115°	336.0	335.5	334.9	334.3	333.5	332.6	331.8	331.0
117.5°	380.7	380.1	379.4	378.9	378.5	378.1	377.8	377.5
120°	409.7	409.4	409.1	408.6	408.0	407.3	406.7	405.9
122.5°	437.2	436.9	436.7	436.1	435.4	434.6	433.8	433.0
125°	477.4	476.9	476.3	475.8	475.4	475.0	474.7	474.3
127.5°	514.1	513.8	513.6	512.9	511.8	510.9	509.9	508.9
130°	538.1	537.7	537.3	536.7	536.1	535.4	534.7	534.0
132.5°	560.4	560.4	560.3	559.9	559.2	558.6	557.9	557.3
135°	593.3	593.0	592.8	592.2	591.4	590.6	589.8	589.0
137.5°	623.9	623.9	624.0	623.7	623.0	622.3	621.6	620.9
140°	642.7	642.9	643.3	642.9	642.1	641.4	640.6	639.8
142.5°	661.1	661.2	661.2	660.9	660.1	659.3	658.4	657.6
145°	687.1	687.3	687.4	687.1	686.2	685.4	684.7	683.9
147.5°	709.4	709.6	709.7	709.3	708.4	707.4	706.5	705.5
150°	723.7	723.9	724.2	723.8	722.7	721.6	720.6	719.5
152.5°	736.2	736.5	736.8	736.4	735.4	734.5	733.5	732.5
155°	753.5	753.9	754.3	754.0	752.9	751.9	750.8	749.7
157.5°	767.8	768.3	768.7	768.3	767.3	766.2	765.2	764.1
160°	776.7	777.3	777.8	777.6	776.5	775.4	774.4	773.2
162.5°	784.9	785.6	786.4	786.2	785.1	783.8	782.7	781.5
165°	795.4	796.2	797.0	796.9	795.8	794.8	793.7	792.6
167.5°	803.3	804.3	805.3	805.2	804.0	802.7	801.5	800.3
170°	807.4	808.5	809.6	809.5	808.3	807.1	805.8	804.7
172.5°	810.6	811.5	812.5	812.4	811.2	810.0	808.8	807.6
175°	814.1	815.1	816.2	816.1	815.0	813.8	812.5	811.3
177.5°	815.5	816.2	817.0	816.9	816.0	815.2	814.3	813.5
180°	815.0	815.0	815.0	815.0	815.0	815.0	815.0	815.0

(END OF REPORT)