

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333667-930

Luminaire Tested: **S125RDIW-S610D770U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333667-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D770U930-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4109.5 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	97	93	89	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	70	81	75	70	66	63	60	56	52	50	47	42	40	39	34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	38	35	33	29
4	74	64	56	50	68	59	52	47	50	45	41	41	38	35	34	31	29	25
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	30	27	25	22
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	21	18	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5297	5297	5297
5°	5309	5249	5281
10°	5269	5200	5200
15°	5207	5094	5053
20°	5126	4947	4887
25°	5032	4802	4697
30°	4915	4633	4486
35°	4796	4459	4249
40°	4684	4278	4016
45°	4549	4074	3763
50°	4413	3852	3497
55°	4255	3640	3216
60°	4097	3384	2913
65°	3909	3085	2566
70°	3697	2713	2211
75°	3401	2286	1839
80°	2998	1796	1543
85°	2527	1467	1378



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	1.9
10°-20°	215.5	5.2
20°-30°	312.5	7.6
30°-40°	356.2	8.7
40°-50°	347.2	8.4
50°-60°	292.3	7.1
60°-70°	204.9	5.0
70°-80°	105.3	2.6
80°-90°	28.3	0.7
90°-100°	52.1	1.3
100°-110°	153.8	3.7
110°-120°	260.5	6.3
120°-130°	342.9	8.3
130°-140°	384.2	9.3
140°-150°	376.6	9.2
150°-160°	316.3	7.7
160°-170°	210.2	5.1
170°-180°	73.6	1.8
0°-30°	605.2	14.7
0°-40°	961.4	23.4
0°-60°	1600.8	39.0
0°-90°	1939.3	47.2
90°-120°	466.4	11.4
90°-150°	1570.1	38.2
90°-180°	2170.0	52.8
0°-180°	4109.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	820	820	820	820	820	
5°	819	816	810	815	815	78
15°	779	774	762	761	756	219
25°	706	696	674	666	659	325
35°	608	593	566	548	539	381
45°	498	479	446	422	412	384
55°	378	357	323	296	286	338
65°	256	234	202	178	168	253
75°	136	117	92	79	74	144
85°	34	23	20	19	19	38
90°	1	5	10	13	14	4
95°	39	41	47	51	52	42
105°	138	141	145	148	150	147
115°	261	263	264	264	263	258
125°	381	384	385	384	383	341
135°	495	499	499	499	497	381
145°	600	602	604	604	602	375
155°	686	686	687	689	686	316
165°	746	745	746	748	744	210
175°	776	774	774	777	773	74
180°	778	778	778	778	778	



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	821.7	821.3	821.0	820.7	820.4	819.6	818.5	817.4	816.3	815.2	816.3
5°	818.9	818.4	817.8	817.3	816.7	815.7	814.2	812.7	811.1	809.6	811.0
7.5°	810.9	810.3	809.8	809.3	808.8	807.6	805.8	804.0	802.2	800.3	801.3
10°	803.4	803.0	802.6	802.2	801.8	800.6	798.7	796.8	794.8	792.9	793.3
12.5°	795.0	794.5	793.9	793.4	792.9	791.3	788.8	786.2	783.6	781.0	781.3
15°	778.7	777.8	777.0	776.2	775.3	773.5	770.6	767.7	764.8	761.9	761.8
17.5°	760.2	759.0	757.7	756.4	755.1	752.7	749.0	745.4	741.8	738.2	737.4
20°	745.8	744.4	743.1	741.7	740.3	737.4	733.0	728.6	724.2	719.8	719.1
22.5°	729.9	728.6	727.2	725.9	724.5	721.5	716.8	712.2	707.6	703.0	701.6
25°	706.2	704.1	702.1	700.0	697.9	694.3	689.3	684.1	679.1	673.9	672.2
27.5°	678.9	676.5	673.9	671.4	668.9	665.0	659.5	654.0	648.6	643.1	640.6
30°	659.1	656.5	653.9	651.3	648.7	644.4	638.6	632.9	627.1	621.3	618.2
32.5°	639.8	636.7	633.7	630.6	627.5	623.1	617.2	611.3	605.4	599.5	596.0
35°	608.3	605.0	601.7	598.4	595.1	590.4	584.2	578.0	571.8	565.6	561.6
37.5°	577.5	573.4	569.4	565.4	561.4	556.2	549.8	543.4	537.0	530.6	525.9
40°	555.6	551.5	547.4	543.2	539.2	533.8	527.2	520.6	514.0	507.4	502.1
42.5°	532.9	528.6	524.4	520.2	515.9	510.4	503.5	496.7	489.9	483.1	478.0
45°	498.1	494.1	490.1	486.1	482.1	476.3	468.7	461.1	453.6	446.0	440.5
47.5°	462.0	457.8	453.6	449.4	445.2	439.2	431.6	424.0	416.4	408.7	403.1
50°	439.2	434.6	430.1	425.6	421.0	414.8	407.0	399.2	391.3	383.4	377.6
52.5°	414.4	409.8	405.1	400.5	395.8	389.8	382.4	375.0	367.5	360.1	353.9
55°	377.9	373.5	369.1	364.7	360.3	354.2	346.5	338.8	331.1	323.3	317.2
57.5°	341.0	336.2	331.5	326.9	322.1	316.0	308.6	301.2	293.8	286.3	280.2
60°	317.2	312.3	307.5	302.7	297.9	291.8	284.3	276.9	269.5	262.0	256.0
62.5°	291.9	287.3	282.7	278.1	273.5	267.4	259.9	252.3	244.8	237.3	231.6
65°	255.8	251.2	246.5	241.8	237.1	231.1	223.8	216.5	209.2	201.9	196.4
67.5°	220.0	215.3	210.7	206.0	201.3	195.5	188.5	181.5	174.5	167.5	162.5
70°	195.8	191.1	186.4	181.7	177.0	171.2	164.4	157.5	150.6	143.7	139.4
72.5°	171.9	167.4	162.8	158.2	153.7	148.1	141.7	135.3	128.8	122.4	118.5
75°	136.3	132.2	128.0	123.9	119.8	114.8	109.0	103.2	97.4	91.6	88.6
77.5°	100.9	97.5	94.2	90.9	87.6	83.6	79.0	74.4	69.8	65.1	63.0
80°	80.6	77.2	73.9	70.6	67.3	63.8	59.8	56.0	52.2	48.3	47.0
82.5°	60.7	57.7	54.8	51.8	48.8	46.0	43.4	40.7	38.1	35.5	34.9
85°	34.1	31.6	29.1	26.7	24.1	22.6	21.9	21.2	20.5	19.8	19.6
87.5°	11.5	10.9	10.4	9.9	9.3	9.0	9.1	9.2	9.3	9.4	9.5
90°	0.6	1.7	2.8	3.8	4.9	6.0	6.8	7.8	8.7	9.7	10.4
92.5°	14.7	15.4	16.1	16.9	17.7	18.6	19.8	21.0	22.1	23.2	24.1
95°	39.4	39.6	39.9	40.1	40.4	41.3	42.6	43.9	45.2	46.6	47.5
97.5°	65.4	65.5	65.6	65.7	65.8	66.8	68.6	70.5	72.3	74.2	75.1
100°	84.7	84.7	84.7	84.7	84.7	85.6	87.3	89.1	90.8	92.6	93.8
102.5°	105.6	106.1	106.6	107.1	107.7	108.4	109.3	110.2	111.0	111.9	113.3
105°	138.0	138.7	139.3	140.0	140.7	141.5	142.3	143.0	143.8	144.6	145.4
107.5°	173.8	174.5	175.2	175.9	176.5	177.2	177.8	178.4	179.0	179.6	180.0
110°	198.5	199.2	199.8	200.6	201.2	201.7	202.1	202.5	202.9	203.3	203.7



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	223.7	224.0	224.4	224.8	225.1	225.5	226.0	226.6	227.1	227.6	227.8
115°	260.9	261.4	262.0	262.4	263.0	263.4	263.7	263.9	264.2	264.5	264.3
117.5°	298.2	298.4	298.6	298.9	299.1	299.4	299.6	299.9	300.1	300.4	300.4
120°	321.4	322.0	322.7	323.4	324.1	324.5	324.6	324.7	324.9	325.0	325.0
122.5°	346.6	346.8	347.1	347.3	347.6	347.8	348.1	348.5	348.9	349.2	349.1
125°	380.7	381.5	382.3	383.1	383.9	384.4	384.5	384.7	384.8	384.9	384.7
127.5°	417.0	417.4	417.9	418.4	418.8	419.1	419.3	419.5	419.6	419.8	419.6
130°	438.8	439.4	440.2	440.8	441.5	442.0	442.2	442.5	442.8	443.0	442.9
132.5°	460.6	461.7	462.8	463.9	465.0	465.5	465.5	465.4	465.4	465.3	465.2
135°	495.0	495.9	496.7	497.5	498.3	498.8	498.9	499.0	499.2	499.3	499.3
137.5°	527.5	528.3	529.0	529.9	530.7	531.2	531.5	531.7	532.1	532.4	532.6
140°	548.4	549.0	549.7	550.3	551.1	551.5	552.0	552.4	552.8	553.2	553.4
142.5°	569.2	569.7	570.3	570.9	571.4	571.9	572.5	573.0	573.5	574.0	574.1
145°	599.8	600.3	600.9	601.4	601.9	602.4	602.8	603.2	603.6	604.1	604.1
147.5°	628.1	628.4	628.7	629.0	629.3	629.6	629.9	630.2	630.6	630.9	631.2
150°	647.0	646.9	646.7	646.6	646.5	646.7	647.2	647.8	648.2	648.8	648.8
152.5°	662.5	662.7	662.8	663.1	663.2	663.4	663.7	663.9	664.1	664.3	664.6
155°	686.3	686.3	686.3	686.3	686.3	686.4	686.6	686.6	686.8	687.0	687.5
157.5°	707.7	707.4	707.0	706.8	706.5	706.4	706.5	706.6	706.8	706.9	707.4
160°	720.2	719.8	719.4	719.0	718.6	718.4	718.6	718.8	718.8	719.0	719.6
162.5°	731.4	731.1	730.8	730.5	730.2	730.0	730.1	730.1	730.1	730.2	730.8
165°	746.2	746.0	745.8	745.4	745.2	745.1	745.3	745.3	745.5	745.7	746.2
167.5°	758.9	758.3	757.7	757.2	756.7	756.4	756.4	756.4	756.4	756.4	757.2
170°	765.6	765.1	764.5	764.0	763.4	763.2	763.2	763.2	763.2	763.2	764.0
172.5°	770.5	769.9	769.4	768.8	768.3	768.0	768.0	768.0	768.0	768.0	768.8
175°	775.9	775.3	774.9	774.3	773.7	773.5	773.5	773.5	773.5	773.5	774.3
177.5°	778.7	778.3	777.8	777.4	777.0	776.7	776.6	776.5	776.4	776.2	776.9
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	820.2	820.2	820.2	820.2	820.2	820.2	820.2	820.2
2.5°	817.4	818.5	819.6	820.1	820.0	819.9	819.8	819.7
5°	812.4	813.8	815.1	815.7	815.4	815.1	814.9	814.6
7.5°	802.3	803.2	804.2	804.5	804.2	803.9	803.6	803.3
10°	793.7	794.1	794.6	794.6	794.1	793.7	793.3	792.9
12.5°	781.6	782.0	782.2	782.0	781.4	780.8	780.2	779.5
15°	761.7	761.5	761.4	760.7	759.5	758.2	757.0	755.7
17.5°	736.8	736.1	735.4	734.5	733.5	732.5	731.5	730.4
20°	718.4	717.7	717.1	716.1	714.9	713.6	712.4	711.1
22.5°	700.3	698.9	697.6	696.3	695.4	694.3	693.3	692.3
25°	670.4	668.6	666.8	665.1	663.7	662.1	660.6	659.1
27.5°	638.1	635.6	633.1	631.1	629.7	628.2	626.7	625.3
30°	615.0	611.8	608.6	606.4	605.2	604.0	602.8	601.5
32.5°	592.5	589.1	585.5	583.0	581.4	579.8	578.3	576.7
35°	557.6	553.6	549.6	546.7	544.7	542.7	540.9	538.9
37.5°	521.1	516.2	511.4	508.1	506.2	504.4	502.6	500.7
40°	496.8	491.6	486.4	483.0	481.4	479.6	478.0	476.4
42.5°	473.0	468.0	463.0	459.3	456.9	454.4	452.0	449.6
45°	435.0	429.5	424.0	420.2	418.2	416.0	414.0	412.0
47.5°	397.4	391.7	386.0	382.0	379.8	377.5	375.2	372.9
50°	371.9	366.1	360.3	356.4	354.3	352.3	350.2	348.1
52.5°	347.7	341.4	335.3	331.1	329.1	327.0	324.9	322.9
55°	311.0	304.8	298.6	294.4	292.2	290.0	287.8	285.6
57.5°	274.2	268.2	262.1	258.0	256.1	254.1	252.3	250.3
60°	249.9	243.9	237.8	233.7	231.7	229.6	227.6	225.5
62.5°	226.0	220.4	214.7	210.9	208.9	206.8	204.7	202.7
65°	190.9	185.4	179.9	176.1	174.1	172.0	169.9	167.9
67.5°	157.4	152.4	147.3	144.0	142.4	140.7	139.0	137.4
70°	135.2	130.9	126.6	123.7	122.1	120.4	118.7	117.1
72.5°	114.5	110.6	106.6	104.1	103.1	101.9	100.9	99.7
75°	85.6	82.6	79.6	77.5	76.6	75.7	74.7	73.7
77.5°	60.9	58.8	56.7	55.3	54.5	53.8	53.2	52.4
80°	45.8	44.6	43.4	42.6	42.3	42.1	41.7	41.5
82.5°	34.2	33.7	33.1	32.8	32.6	32.4	32.3	32.1
85°	19.6	19.4	19.2	19.2	19.0	18.8	18.8	18.6
87.5°	9.6	9.8	9.9	9.9	9.9	9.9	9.9	9.9
90°	11.0	11.7	12.4	12.9	13.3	13.7	14.1	14.5
92.5°	25.0	25.9	26.8	27.4	27.7	28.0	28.3	28.5
95°	48.5	49.4	50.4	51.0	51.3	51.5	51.8	52.0
97.5°	76.0	76.9	77.8	78.3	78.4	78.6	78.8	78.9
100°	95.0	96.2	97.4	98.2	98.5	98.7	99.0	99.2
102.5°	114.6	115.9	117.2	118.1	118.5	118.9	119.2	119.6
105°	146.3	147.1	147.9	148.5	148.9	149.3	149.7	150.1
107.5°	180.4	180.8	181.2	181.4	181.4	181.4	181.3	181.3
110°	204.2	204.6	205.0	205.1	205.0	204.8	204.7	204.6



TEST NUMBER: P333667-930

CATALOG NUMBER: S125RDIW-S610D770U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	228.0	228.1	228.3	228.3	228.0	227.8	227.6	227.3
115°	264.2	264.1	263.9	263.8	263.7	263.6	263.4	263.3
117.5°	300.5	300.6	300.8	300.5	300.0	299.5	298.9	298.4
120°	325.0	325.0	325.0	324.7	324.2	323.7	323.1	322.6
122.5°	349.0	348.9	348.8	348.5	348.1	347.6	347.2	346.8
125°	384.4	384.1	383.8	383.7	383.5	383.4	383.3	383.1
127.5°	419.6	419.4	419.2	419.1	418.8	418.5	418.2	418.0
130°	442.8	442.6	442.5	442.3	442.1	441.7	441.5	441.2
132.5°	465.0	464.9	464.8	464.5	464.1	463.7	463.4	463.0
135°	499.3	499.3	499.3	499.0	498.5	498.0	497.4	496.9
137.5°	532.7	532.9	533.0	532.7	532.1	531.4	530.8	530.0
140°	553.8	554.0	554.2	554.1	553.4	552.7	552.0	551.4
142.5°	574.3	574.5	574.6	574.4	573.7	573.1	572.3	571.7
145°	604.1	604.1	604.1	603.8	603.4	603.0	602.6	602.2
147.5°	631.5	631.9	632.2	631.9	631.0	630.1	629.2	628.3
150°	648.8	648.8	648.8	648.7	648.4	648.2	647.8	647.6
152.5°	665.0	665.3	665.6	665.5	665.0	664.6	664.1	663.6
155°	688.0	688.5	689.1	689.0	688.4	687.7	687.0	686.3
157.5°	708.0	708.5	709.1	708.9	708.0	707.1	706.2	705.3
160°	720.1	720.6	721.1	721.1	720.4	719.7	719.1	718.4
162.5°	731.5	732.1	732.7	732.7	731.9	731.1	730.3	729.5
165°	746.7	747.3	747.8	747.6	746.9	746.1	745.3	744.4
167.5°	758.1	758.9	759.6	759.6	758.8	758.0	757.2	756.3
170°	764.8	765.6	766.5	766.4	765.4	764.5	763.5	762.6
172.5°	769.6	770.5	771.3	771.3	770.5	769.6	768.7	767.9
175°	775.1	775.9	776.7	776.7	775.7	774.8	773.8	772.9
177.5°	777.6	778.2	778.9	778.8	778.0	777.3	776.6	775.8
180°	777.7	777.7	777.7	777.7	777.7	777.7	777.7	777.7

(END OF REPORT)