

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333467-927

Luminaire Tested: **S125DIW-S1270D770U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333467-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U927-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6215.7 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66
1	102	97	94	90	96	92	88	85	81	79	77	72	70	68	63	62	61	56
2	93	85	79	74	87	81	75	71	72	68	64	64	60	57	56	54	51	48
3	85	75	68	62	80	71	65	59	64	58	54	56	52	49	50	47	44	41
4	78	67	59	53	73	63	56	51	57	51	46	50	46	42	45	41	38	35
5	72	60	51	45	67	57	49	44	51	45	40	45	40	37	40	36	33	30
6	66	54	45	40	62	51	44	38	46	40	35	41	36	32	37	33	29	27
7	61	49	40	35	57	46	39	34	42	36	31	37	32	29	33	29	26	24
8	57	44	36	31	53	42	35	30	38	32	28	34	29	26	31	27	23	21
9	53	40	33	28	50	39	32	27	35	29	25	32	27	23	28	24	21	19
10	49	37	30	25	47	35	29	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9396	9396	9396	9396
5°	10881	9428	8255	9428
10°	12660	9379	7233	9379
15°	14014	9310	6672	9310
20°	15687	9201	6222	9201
25°	18377	9079	6002	9079
30°	19848	8957	5812	8957
35°	16320	8729	5687	8729
40°	11600	8413	5550	8413
45°	8912	7986	5471	7986
50°	7607	7458	5460	7458
55°	6773	6939	5507	6939
60°	6110	6373	5647	6373
65°	5644	5804	5793	5804
70°	5130	5212	5876	5212
75°	4531	4591	5827	4591
80°	3812	3745	5326	3745
85°	3016	2697	4305	2697



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.1	2.3
10°-20°	417.0	6.7
20°-30°	677.1	10.9
30°-40°	826.0	13.3
40°-50°	751.4	12.1
50°-60°	598.5	9.6
60°-70°	416.9	6.7
70°-80°	222.3	3.6
80°-90°	57.8	0.9
90°-100°	50.6	0.8
100°-110°	149.5	2.4
110°-120°	253.2	4.1
120°-130°	333.2	5.4
130°-140°	373.3	6.0
140°-150°	365.9	5.9
150°-160°	307.3	4.9
160°-170°	204.3	3.3
170°-180°	71.5	1.2
0°-30°	1234.2	19.9
0°-40°	2060.2	33.1
0°-60°	3410.1	54.9
0°-90°	4107.1	66.1
90°-120°	453.2	7.3
90°-150°	1525.6	24.5
90°-180°	2109.0	33.9
0°-180°	6215.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1455	1455	1455	1455	1455	
5°	1678	1454	1273	1454	1678	169
15°	2096	1392	998	1392	2096	600
25°	2579	1274	842	1274	2579	1178
35°	2070	1107	721	1107	2070	1267
45°	976	874	599	874	976	781
55°	602	616	489	616	602	542
65°	369	380	379	380	369	367
75°	182	184	234	184	182	196
85°	41	36	58	36	41	47
90°	14	1	14	1	14	10
95°	50	38	50	38	50	51
105°	146	134	146	134	146	155
115°	256	254	256	254	256	253
125°	372	370	372	370	372	332
135°	483	481	483	481	483	372
145°	585	583	585	583	585	365
155°	667	667	667	667	667	307
165°	723	725	723	725	723	204
175°	751	754	751	754	751	71
180°	756	756	756	756	756	



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1538.9	1536.9	1534.9	1531.0	1533.9	1525.5	1521.5	1514.7	1506.3	1503.3	1499.8
5°	1678.4	1681.5	1684.6	1671.7	1672.9	1664.2	1644.5	1628.4	1615.4	1598.8	1587.1
7.5°	1846.4	1839.1	1838.5	1830.1	1815.7	1804.0	1783.3	1756.8	1731.3	1702.2	1678.1
10°	1930.4	1931.0	1925.5	1915.6	1900.1	1889.0	1861.9	1835.9	1804.4	1767.4	1740.8
12.5°	1993.6	1996.2	1989.2	1975.9	1968.3	1943.4	1922.1	1891.3	1853.8	1824.2	1783.8
15°	2095.9	2089.1	2084.2	2067.4	2054.5	2028.5	1994.6	1962.5	1921.8	1884.0	1846.4
17.5°	2194.4	2199.9	2190.6	2175.4	2135.2	2104.9	2059.4	2015.3	1964.6	1914.1	1869.2
20°	2282.4	2287.3	2273.1	2246.5	2198.4	2168.1	2108.2	2051.4	1992.7	1927.9	1878.5
22.5°	2392.1	2388.1	2368.9	2328.5	2286.8	2230.9	2166.1	2096.8	2023.4	1950.1	1884.4
25°	2578.8	2552.8	2541.1	2491.1	2436.1	2354.0	2265.1	2163.8	2072.4	1975.5	1891.5
27.5°	2682.3	2674.1	2661.0	2626.2	2568.4	2480.6	2375.8	2252.3	2123.4	2001.1	1891.1
30°	2661.5	2662.8	2664.0	2652.9	2615.9	2549.7	2445.4	2312.6	2159.5	2021.8	1894.6
32.5°	2477.8	2500.2	2521.8	2547.2	2557.6	2544.8	2479.5	2359.6	2201.9	2045.5	1892.6
35°	2070.0	2076.7	2146.5	2215.7	2309.5	2382.4	2431.2	2378.1	2245.3	2065.6	1890.2
37.5°	1614.0	1647.3	1695.6	1773.8	1909.2	2030.5	2186.5	2258.3	2215.4	2072.2	1885.9
40°	1375.9	1406.8	1438.2	1517.9	1632.1	1779.1	1956.3	2107.6	2142.8	2051.4	1871.1
42.5°	1192.1	1216.6	1251.5	1311.4	1406.8	1537.0	1706.4	1904.1	2025.7	1991.2	1840.0
45°	975.7	991.1	1018.3	1065.9	1135.0	1236.9	1386.3	1602.5	1790.8	1853.2	1766.1
47.5°	835.1	835.0	856.1	889.0	938.9	1025.5	1136.0	1305.4	1506.5	1655.3	1648.5
50°	757.1	754.0	770.6	799.1	838.6	896.0	1001.6	1136.9	1330.2	1498.7	1545.6
52.5°	689.9	690.2	700.5	721.5	754.6	803.7	882.6	1004.5	1169.6	1342.6	1431.1
55°	601.5	599.0	610.7	625.0	649.0	681.1	737.9	831.2	965.2	1135.6	1250.5
57.5°	520.5	527.3	532.0	541.9	561.8	583.3	631.2	699.7	806.0	952.2	1073.6
60°	473.0	479.8	483.5	493.4	509.5	528.0	565.1	620.6	710.2	836.1	956.6
62.5°	430.6	435.9	437.0	446.0	459.1	477.1	506.3	552.9	623.7	733.9	851.8
65°	369.3	369.3	371.8	381.0	387.2	403.2	425.5	459.5	516.3	602.1	702.7
67.5°	310.2	313.2	312.6	316.6	322.3	334.9	350.8	378.8	420.9	483.5	564.0
70°	271.7	274.2	273.5	276.6	282.8	290.9	303.8	330.3	360.6	414.4	483.5
72.5°	237.1	238.1	236.5	240.6	244.3	251.4	265.8	280.0	308.2	353.6	410.4
75°	181.6	182.8	184.0	186.5	190.2	193.9	201.3	215.6	234.0	268.0	304.4
77.5°	136.1	133.7	136.7	136.3	138.5	141.3	147.8	155.3	170.6	192.0	220.2
80°	102.5	103.1	103.1	103.8	106.9	108.7	114.2	119.8	131.5	147.6	167.4
82.5°	74.9	76.4	75.5	76.6	79.1	80.5	83.6	88.2	95.0	107.6	121.9
85°	40.7	37.7	38.9	40.2	40.2	40.7	43.3	45.1	48.8	53.7	59.3
87.5°	14.7	15.6	16.0	15.9	16.3	16.2	18.1	18.0	19.3	20.7	22.4
90°	14.1	13.7	13.3	12.9	12.5	12.0	11.4	10.7	10.1	9.4	8.5
92.5°	27.7	27.5	27.2	26.9	26.6	26.1	25.2	24.3	23.4	22.6	21.5
95°	50.5	50.3	50.1	49.8	49.5	49.0	48.0	47.1	46.2	45.3	44.0
97.5°	76.7	76.5	76.4	76.2	76.0	75.6	74.7	73.8	73.0	72.1	70.3
100°	96.4	96.2	95.9	95.7	95.4	94.7	93.5	92.3	91.2	90.0	88.2
102.5°	116.2	115.8	115.5	115.1	114.7	113.9	112.6	111.4	110.1	108.8	107.9
105°	145.8	145.4	145.0	144.7	144.3	143.7	142.9	142.1	141.3	140.5	139.7
107.5°	176.2	176.2	176.3	176.3	176.3	176.1	175.7	175.3	174.9	174.5	174.0
110°	198.8	198.9	199.0	199.2	199.3	199.2	198.8	198.4	198.0	197.6	197.2



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.9	221.1	221.3	221.6	221.8	221.8	221.7	221.5	221.3	221.1	220.6
115°	255.8	256.0	256.1	256.2	256.4	256.4	256.6	256.7	256.8	257.0	256.7
117.5°	289.9	290.4	291.0	291.5	292.0	292.2	292.1	292.0	291.9	291.8	291.6
120°	313.5	313.9	314.5	315.1	315.5	315.8	315.8	315.8	315.8	315.8	315.7
122.5°	337.0	337.4	337.8	338.2	338.7	338.9	339.0	339.1	339.2	339.3	339.0
125°	372.2	372.4	372.5	372.6	372.8	373.0	373.2	373.5	373.8	374.0	373.9
127.5°	406.2	406.4	406.6	406.9	407.2	407.3	407.5	407.7	407.7	407.9	407.7
130°	428.7	429.0	429.2	429.5	429.8	429.9	430.1	430.2	430.3	430.5	430.2
132.5°	449.9	450.3	450.6	451.0	451.3	451.6	451.7	451.9	452.0	452.1	452.2
135°	482.8	483.3	483.9	484.3	484.9	485.1	485.1	485.1	485.1	485.1	485.1
137.5°	515.0	515.7	516.3	517.0	517.6	517.9	517.8	517.6	517.5	517.3	517.0
140°	535.8	536.4	537.0	537.7	538.4	538.5	538.3	538.1	537.7	537.5	537.1
142.5°	555.5	556.1	556.8	557.5	558.1	558.3	558.2	558.0	557.9	557.7	557.2
145°	585.1	585.5	585.9	586.3	586.7	586.9	586.9	586.9	586.9	586.9	586.5
147.5°	610.5	611.3	612.2	613.1	613.9	614.3	613.9	613.6	613.3	613.0	612.7
150°	629.2	629.5	629.8	630.0	630.3	630.4	630.4	630.4	630.4	630.4	629.9
152.5°	644.8	645.2	645.7	646.2	646.7	646.7	646.4	646.1	645.8	645.5	645.2
155°	666.9	667.5	668.2	668.8	669.5	669.6	669.0	668.5	668.0	667.5	667.3
157.5°	685.3	686.2	687.1	687.9	688.8	689.0	688.4	687.9	687.4	686.9	686.7
160°	698.1	698.7	699.3	700.0	700.7	700.7	700.2	699.7	699.2	698.6	698.5
162.5°	708.8	709.6	710.3	711.1	711.9	711.9	711.3	710.7	710.1	709.5	709.4
165°	723.3	724.1	724.9	725.7	726.4	726.6	726.1	725.6	725.0	724.5	724.4
167.5°	734.8	735.7	736.5	737.3	738.1	738.1	737.4	736.6	735.8	735.0	735.0
170°	741.0	741.9	742.8	743.7	744.7	744.7	743.9	743.1	742.4	741.6	741.6
172.5°	746.2	746.9	747.7	748.6	749.4	749.4	748.6	747.8	747.0	746.2	746.2
175°	751.0	751.9	752.8	753.7	754.6	754.7	753.9	753.1	752.3	751.5	751.5
177.5°	753.8	754.6	755.3	756.0	756.7	756.8	756.1	755.5	754.9	754.2	754.4
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1496.9	1493.4	1489.5	1482.6	1474.2	1469.7	1462.8	1458.3	1449.5	1442.0	1434.2
5°	1572.8	1556.8	1542.0	1522.8	1501.8	1488.2	1472.2	1454.3	1435.8	1416.6	1395.6
7.5°	1651.5	1623.1	1592.2	1559.0	1526.5	1496.6	1468.1	1440.0	1413.9	1382.3	1355.5
10°	1704.4	1668.6	1630.2	1585.2	1541.3	1503.1	1464.1	1430.2	1395.6	1358.5	1325.8
12.5°	1757.2	1709.5	1655.4	1605.9	1553.2	1507.0	1461.2	1417.8	1374.4	1333.3	1295.2
15°	1794.5	1752.5	1702.5	1632.1	1572.8	1509.3	1448.7	1392.5	1340.1	1294.3	1246.2
17.5°	1819.1	1765.0	1711.3	1643.7	1566.1	1494.9	1426.3	1362.0	1302.8	1244.9	1198.5
20°	1823.5	1768.0	1711.7	1645.7	1566.1	1484.5	1415.9	1338.8	1275.2	1215.3	1158.5
22.5°	1822.1	1759.0	1698.0	1629.9	1552.2	1477.1	1394.2	1315.6	1246.5	1187.6	1128.3
25°	1808.1	1740.8	1664.2	1595.7	1519.1	1439.5	1355.5	1274.0	1203.6	1136.2	1077.6
27.5°	1796.5	1709.2	1622.5	1542.5	1468.6	1395.6	1315.2	1231.7	1153.7	1085.4	1030.2
30°	1782.2	1686.5	1588.9	1505.5	1429.6	1358.5	1282.6	1201.1	1119.6	1052.9	993.6
32.5°	1769.3	1657.8	1554.8	1464.0	1383.6	1314.5	1244.5	1167.0	1087.0	1019.3	960.0
35°	1744.5	1615.4	1497.5	1395.0	1309.2	1238.1	1179.5	1107.2	1033.7	968.3	911.5
37.5°	1713.0	1559.9	1433.3	1325.8	1231.7	1156.9	1102.2	1046.8	976.3	913.2	861.8
40°	1688.3	1520.4	1386.3	1276.4	1178.8	1101.1	1050.4	997.9	939.3	880.6	826.2
42.5°	1657.2	1484.8	1338.9	1220.6	1124.0	1048.2	995.1	950.5	898.7	844.1	793.6
45°	1600.0	1420.3	1262.2	1135.0	1037.4	962.7	907.8	874.4	835.5	783.6	741.0
47.5°	1515.9	1342.8	1179.3	1048.1	947.4	878.1	826.6	794.6	767.2	728.6	690.0
50°	1441.3	1285.1	1119.6	989.3	888.6	818.8	771.3	742.3	718.8	689.1	656.4
52.5°	1357.8	1212.4	1060.8	932.0	832.3	763.5	716.9	691.4	671.8	650.6	618.4
55°	1225.2	1101.7	960.8	838.6	746.6	679.3	638.5	616.3	600.2	584.2	564.4
57.5°	1079.0	982.5	857.8	746.0	661.2	600.0	562.0	540.3	527.8	519.6	507.9
60°	976.3	893.6	786.1	684.2	601.5	547.2	510.1	493.4	482.9	476.1	467.5
62.5°	881.0	813.0	713.5	620.5	548.1	496.7	463.7	447.4	437.4	434.1	427.0
65°	740.4	687.9	605.8	528.6	466.8	423.0	395.2	379.8	373.6	369.9	370.5
67.5°	602.0	570.0	504.0	438.2	388.9	352.1	329.9	318.1	315.0	310.0	309.9
70°	517.5	493.4	437.8	380.4	336.5	308.2	288.4	276.0	272.9	270.5	269.9
72.5°	442.9	421.8	373.6	327.6	288.1	263.2	246.9	239.5	234.4	232.9	232.8
75°	332.9	321.2	282.8	246.4	219.2	201.9	190.8	184.0	180.3	179.7	180.3
77.5°	236.6	226.4	202.1	176.3	159.1	146.0	136.6	134.3	130.1	130.2	129.5
80°	177.8	171.0	155.6	135.2	121.0	110.0	105.0	100.7	99.4	97.6	99.4
82.5°	129.0	121.7	111.1	98.2	86.4	79.8	74.9	73.5	72.7	71.9	72.2
85°	63.6	64.2	58.1	48.2	43.3	39.5	36.4	36.4	35.8	35.2	35.8
87.5°	23.3	22.1	19.9	18.2	15.5	13.9	13.2	13.5	12.2	11.9	12.6
90°	7.6	6.7	5.8	4.8	3.7	2.7	1.7	0.6	1.7	2.7	3.7
92.5°	20.4	19.3	18.1	17.2	16.4	15.7	15.0	14.3	15.0	15.7	16.4
95°	42.7	41.4	40.1	39.3	39.0	38.7	38.5	38.3	38.5	38.7	39.0
97.5°	68.5	66.7	64.9	63.9	63.8	63.7	63.6	63.5	63.6	63.7	63.8
100°	86.6	84.8	83.2	82.3	82.3	82.3	82.3	82.3	82.3	82.3	82.3
102.5°	107.1	106.2	105.4	104.6	104.1	103.6	103.1	102.6	103.1	103.6	104.1
105°	138.9	138.2	137.4	136.7	136.0	135.4	134.8	134.1	134.8	135.4	136.0
107.5°	173.3	172.8	172.1	171.5	170.9	170.2	169.5	168.9	169.5	170.2	170.9
110°	196.8	196.4	196.0	195.5	194.9	194.2	193.5	192.9	193.5	194.2	194.9



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	220.1	219.6	219.1	218.7	218.4	218.0	217.7	217.4	217.7	218.0	218.4
115°	256.4	256.2	256.0	255.6	255.0	254.5	254.0	253.5	254.0	254.5	255.0
117.5°	291.4	291.1	290.9	290.7	290.4	290.2	289.9	289.7	289.9	290.2	290.4
120°	315.5	315.4	315.3	314.9	314.3	313.5	312.9	312.3	312.9	313.5	314.3
122.5°	338.7	338.3	337.9	337.7	337.5	337.2	337.0	336.8	337.0	337.2	337.5
125°	373.8	373.6	373.5	373.0	372.2	371.5	370.7	369.9	370.7	371.5	372.2
127.5°	407.6	407.4	407.3	406.9	406.5	406.1	405.6	405.2	405.6	406.1	406.5
130°	429.9	429.7	429.4	429.0	428.3	427.7	427.0	426.4	427.0	427.7	428.3
132.5°	452.2	452.3	452.3	451.8	450.8	449.6	448.6	447.5	448.6	449.6	450.8
135°	484.9	484.7	484.7	484.2	483.4	482.6	481.8	481.0	481.8	482.6	483.4
137.5°	516.7	516.4	516.1	515.6	514.8	514.0	513.3	512.5	513.3	514.0	514.8
140°	536.7	536.3	535.9	535.4	534.7	534.1	533.5	532.8	533.5	534.1	534.7
142.5°	556.7	556.3	555.7	555.2	554.7	554.1	553.6	553.0	553.6	554.1	554.7
145°	586.1	585.7	585.3	584.9	584.3	583.8	583.3	582.8	583.3	583.8	584.3
147.5°	612.4	612.0	611.7	611.5	611.2	610.9	610.6	610.3	610.6	610.9	611.2
150°	629.4	628.8	628.4	628.1	628.3	628.4	628.5	628.7	628.5	628.4	628.3
152.5°	645.1	644.8	644.6	644.4	644.3	644.0	643.9	643.7	643.9	644.0	644.3
155°	667.2	667.1	666.9	666.9	666.9	666.9	666.9	666.9	666.9	666.9	666.9
157.5°	686.6	686.5	686.3	686.4	686.7	687.0	687.3	687.6	687.3	687.0	686.7
160°	698.4	698.2	698.1	698.2	698.6	699.0	699.4	699.8	699.4	699.0	698.6
162.5°	709.4	709.4	709.3	709.5	709.8	710.0	710.3	710.7	710.3	710.0	709.8
165°	724.2	724.1	724.0	724.1	724.3	724.6	724.8	725.1	724.8	724.6	724.3
167.5°	735.0	735.0	735.0	735.2	735.8	736.3	736.8	737.4	736.8	736.3	735.8
170°	741.6	741.6	741.6	741.8	742.4	742.8	743.4	743.9	743.4	742.8	742.4
172.5°	746.2	746.2	746.2	746.6	747.0	747.6	748.1	748.6	748.1	747.6	747.0
175°	751.5	751.5	751.5	751.8	752.3	752.9	753.4	753.9	753.4	752.9	752.3
177.5°	754.5	754.6	754.7	754.9	755.3	755.7	756.2	756.6	756.2	755.7	755.3
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1429.7	1424.3	1419.8	1409.9	1404.5	1397.1	1391.2	1397.6	1390.7	1393.6	1389.2
5°	1385.1	1367.8	1355.5	1337.5	1322.2	1307.9	1297.4	1295.5	1290.6	1288.2	1280.7
7.5°	1331.5	1309.9	1288.6	1265.2	1245.4	1225.3	1212.4	1201.8	1194.8	1185.5	1179.2
10°	1299.9	1270.9	1246.2	1217.7	1193.0	1171.5	1154.1	1145.5	1137.5	1125.8	1121.4
12.5°	1260.8	1230.8	1200.7	1170.4	1146.6	1122.5	1107.7	1094.6	1089.1	1075.9	1074.5
15°	1214.0	1168.9	1139.3	1108.4	1075.7	1056.0	1043.6	1029.4	1023.3	1014.0	1007.2
17.5°	1158.2	1117.9	1080.9	1048.9	1020.9	1004.2	988.9	979.1	968.5	962.5	951.3
20°	1117.7	1079.4	1042.4	1008.4	986.8	967.7	955.3	946.0	934.9	931.8	920.8
22.5°	1083.6	1041.4	1005.8	977.3	953.7	932.1	918.8	912.4	904.8	895.3	893.0
25°	1028.2	984.4	954.1	925.7	904.7	884.9	875.7	867.6	860.2	853.4	851.0
27.5°	980.2	941.1	905.1	879.5	861.2	843.2	835.0	825.3	819.8	814.4	807.7
30°	946.7	906.5	875.0	850.3	830.6	814.5	805.9	799.1	794.2	789.2	785.5
32.5°	912.1	874.9	844.4	820.2	800.4	788.3	780.7	775.9	770.4	764.5	759.8
35°	866.4	825.6	796.0	775.0	759.5	750.3	741.6	737.3	731.2	731.2	726.2
37.5°	814.9	779.7	753.5	734.4	720.5	712.3	702.9	699.9	695.9	693.3	691.7
40°	784.3	751.5	726.8	707.7	692.8	686.0	678.7	673.8	671.2	668.1	666.9
42.5°	752.7	721.4	697.7	680.0	667.2	661.4	654.4	651.0	646.0	642.0	641.3
45°	704.6	674.3	652.8	638.5	627.4	620.6	616.3	608.9	606.4	601.5	600.9
47.5°	659.0	630.0	608.8	597.1	587.4	581.9	575.0	567.6	564.8	562.3	562.1
50°	625.0	598.4	578.6	567.5	558.3	550.2	543.4	538.4	536.6	536.6	537.9
52.5°	590.3	567.8	551.0	537.3	528.6	520.1	513.8	510.8	507.9	511.0	513.2
55°	539.7	516.9	504.5	491.5	482.9	473.0	469.9	468.7	466.8	471.8	474.3
57.5°	486.1	470.1	455.6	442.8	435.0	429.3	425.1	424.4	427.9	430.2	438.2
60°	452.0	433.5	420.6	410.7	401.4	397.7	396.5	395.2	397.7	404.5	414.9
62.5°	414.5	399.4	385.5	378.0	371.2	365.1	364.8	365.6	370.5	378.3	388.8
65°	359.4	346.4	337.2	328.5	323.0	319.2	320.5	323.0	328.5	339.1	350.8
67.5°	303.5	294.5	286.3	279.2	273.9	273.9	275.2	278.8	285.4	297.5	308.2
70°	267.4	257.5	250.7	247.6	243.3	240.8	244.5	250.7	256.3	267.4	276.6
72.5°	231.3	222.9	217.6	215.6	213.7	211.7	212.9	219.6	227.1	238.2	249.0
75°	177.8	174.8	171.0	168.6	166.8	167.9	169.2	175.4	181.6	193.3	205.7
77.5°	129.8	126.6	124.4	123.7	122.8	123.3	126.8	131.4	137.4	146.0	155.3
80°	98.2	97.0	95.7	95.1	95.1	95.7	100.7	103.8	109.3	117.3	124.8
82.5°	71.5	70.7	70.5	70.4	70.9	71.0	74.0	78.0	82.6	88.6	95.1
85°	37.7	36.4	38.3	38.9	37.7	39.5	40.7	43.3	45.1	48.2	51.3
87.5°	13.3	14.5	14.2	14.9	15.1	16.2	15.8	18.0	19.1	20.2	19.8
90°	4.8	5.8	6.7	7.6	8.5	9.4	10.1	10.7	11.4	12.0	12.5
92.5°	17.2	18.1	19.3	20.4	21.5	22.6	23.4	24.3	25.2	26.1	26.6
95°	39.3	40.1	41.4	42.7	44.0	45.3	46.2	47.1	48.0	49.0	49.5
97.5°	63.9	64.9	66.7	68.5	70.3	72.1	73.0	73.8	74.7	75.6	76.0
100°	82.3	83.2	84.8	86.6	88.2	90.0	91.2	92.3	93.5	94.7	95.4
102.5°	104.6	105.4	106.2	107.1	107.9	108.8	110.1	111.4	112.6	113.9	114.7
105°	136.7	137.4	138.2	138.9	139.7	140.5	141.3	142.1	142.9	143.7	144.3
107.5°	171.5	172.1	172.8	173.3	174.0	174.5	174.9	175.3	175.7	176.1	176.3
110°	195.5	196.0	196.4	196.8	197.2	197.6	198.0	198.4	198.8	199.2	199.3



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	218.7	219.1	219.6	220.1	220.6	221.1	221.3	221.5	221.7	221.8	221.8
115°	255.6	256.0	256.2	256.4	256.7	257.0	256.8	256.7	256.6	256.4	256.4
117.5°	290.7	290.9	291.1	291.4	291.6	291.8	291.9	292.0	292.1	292.2	292.0
120°	314.9	315.3	315.4	315.5	315.7	315.8	315.8	315.8	315.8	315.8	315.5
122.5°	337.7	337.9	338.3	338.7	339.0	339.3	339.2	339.1	339.0	338.9	338.7
125°	373.0	373.5	373.6	373.8	373.9	374.0	373.8	373.5	373.2	373.0	372.8
127.5°	406.9	407.3	407.4	407.6	407.7	407.9	407.7	407.7	407.5	407.3	407.2
130°	429.0	429.4	429.7	429.9	430.2	430.5	430.3	430.2	430.1	429.9	429.8
132.5°	451.8	452.3	452.3	452.2	452.2	452.1	452.0	451.9	451.7	451.6	451.3
135°	484.2	484.7	484.7	484.9	485.1	485.1	485.1	485.1	485.1	485.1	484.9
137.5°	515.6	516.1	516.4	516.7	517.0	517.3	517.5	517.6	517.8	517.9	517.6
140°	535.4	535.9	536.3	536.7	537.1	537.5	537.7	538.1	538.3	538.5	538.4
142.5°	555.2	555.7	556.3	556.7	557.2	557.7	557.9	558.0	558.2	558.3	558.1
145°	584.9	585.3	585.7	586.1	586.5	586.9	586.9	586.9	586.9	586.9	586.7
147.5°	611.5	611.7	612.0	612.4	612.7	613.0	613.3	613.6	613.9	614.3	613.9
150°	628.1	628.4	628.8	629.4	629.9	630.4	630.4	630.4	630.4	630.4	630.3
152.5°	644.4	644.6	644.8	645.1	645.2	645.5	645.8	646.1	646.4	646.7	646.7
155°	666.9	666.9	667.1	667.2	667.3	667.5	668.0	668.5	669.0	669.6	669.5
157.5°	686.4	686.3	686.5	686.6	686.7	686.9	687.4	687.9	688.4	689.0	688.8
160°	698.2	698.1	698.2	698.4	698.5	698.6	699.2	699.7	700.2	700.7	700.7
162.5°	709.5	709.3	709.4	709.4	709.4	709.5	710.1	710.7	711.3	711.9	711.9
165°	724.1	724.0	724.1	724.2	724.4	724.5	725.0	725.6	726.1	726.6	726.4
167.5°	735.2	735.0	735.0	735.0	735.0	735.0	735.8	736.6	737.4	738.1	738.1
170°	741.8	741.6	741.6	741.6	741.6	741.6	742.4	743.1	743.9	744.7	744.7
172.5°	746.6	746.2	746.2	746.2	746.2	746.2	747.0	747.8	748.6	749.4	749.4
175°	751.8	751.5	751.5	751.5	751.5	751.5	752.3	753.1	753.9	754.7	754.6
177.5°	754.9	754.7	754.6	754.5	754.4	754.2	754.9	755.5	756.1	756.8	756.7
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1386.2	1389.6	1386.7	1390.7	1386.7	1389.6	1386.2	1389.2	1393.6	1390.7	1397.6
5°	1277.6	1272.1	1275.8	1273.4	1275.8	1272.1	1277.6	1280.7	1288.2	1290.6	1295.5
7.5°	1177.3	1172.0	1166.0	1163.2	1166.0	1172.0	1177.3	1179.2	1185.5	1194.8	1201.8
10°	1114.6	1107.9	1107.2	1102.9	1107.2	1107.9	1114.6	1121.4	1125.8	1137.5	1145.5
12.5°	1068.7	1062.4	1055.3	1053.5	1055.3	1062.4	1068.7	1074.5	1075.9	1089.1	1094.6
15°	1003.5	998.5	994.2	997.9	994.2	998.5	1003.5	1007.2	1014.0	1023.3	1029.4
17.5°	949.3	945.2	944.4	939.8	944.4	945.2	949.3	951.3	962.5	968.5	979.1
20°	915.2	912.1	913.3	905.3	913.3	912.1	915.2	920.8	931.8	934.9	946.0
22.5°	888.0	881.9	881.2	879.6	881.2	881.9	888.0	893.0	895.3	904.8	912.4
25°	845.4	842.3	839.2	842.3	839.2	842.3	845.4	851.0	853.4	860.2	867.6
27.5°	808.2	804.5	803.7	804.0	803.7	804.5	808.2	807.7	814.4	819.8	825.3
30°	785.5	779.3	779.9	779.3	779.9	779.3	785.5	785.5	789.2	794.2	799.1
32.5°	760.8	756.6	755.7	754.6	755.7	756.6	760.8	759.8	764.5	770.4	775.9
35°	724.4	724.4	721.3	721.3	721.3	724.4	724.4	726.2	731.2	731.2	737.3
37.5°	690.1	689.5	687.7	687.9	687.7	689.5	690.1	691.7	693.3	695.9	699.9
40°	664.5	663.8	661.9	658.3	661.9	663.8	664.5	666.9	668.1	671.2	673.8
42.5°	639.8	637.6	636.8	635.6	636.8	637.6	639.8	641.3	642.0	646.0	651.0
45°	600.9	600.9	599.6	599.0	599.6	600.9	600.9	600.9	601.5	606.4	608.9
47.5°	563.1	564.2	566.5	566.2	566.5	564.2	563.1	562.1	562.3	564.8	567.6
50°	540.3	541.0	542.8	543.4	542.8	541.0	540.3	537.9	536.6	536.6	538.4
52.5°	515.2	518.7	521.1	520.7	521.1	518.7	515.2	513.2	511.0	507.9	510.8
55°	479.8	484.1	488.5	489.1	488.5	484.1	479.8	474.3	471.8	466.8	468.7
57.5°	444.9	450.9	455.5	456.9	455.5	450.9	444.9	438.2	430.2	427.9	424.4
60°	421.1	429.2	434.7	437.2	434.7	429.2	421.1	414.9	404.5	397.7	395.2
62.5°	398.4	407.4	413.0	413.5	413.0	407.4	398.4	388.8	378.3	370.5	365.6
65°	361.2	370.5	375.4	379.1	375.4	370.5	361.2	350.8	339.1	328.5	323.0
67.5°	321.2	330.5	336.0	338.9	336.0	330.5	321.2	308.2	297.5	285.4	278.8
70°	292.1	301.3	308.8	311.2	308.8	301.3	292.1	276.6	267.4	256.3	250.7
72.5°	263.4	271.7	277.7	280.6	277.7	271.7	263.4	249.0	238.2	227.1	219.6
75°	213.7	224.7	230.4	233.5	230.4	224.7	213.7	205.7	193.3	181.6	175.4
77.5°	164.8	174.9	178.2	179.8	178.2	174.9	164.8	155.3	146.0	137.4	131.4
80°	132.1	138.3	142.7	143.2	142.7	138.3	132.1	124.8	117.3	109.3	103.8
82.5°	101.6	106.7	108.1	109.6	108.1	106.7	101.6	95.1	88.6	82.6	78.0
85°	55.6	58.1	58.7	58.1	58.7	58.1	55.6	51.3	48.2	45.1	43.3
87.5°	20.8	20.4	20.5	21.6	20.5	20.4	20.8	19.8	20.2	19.1	18.0
90°	12.9	13.3	13.7	14.1	13.7	13.3	12.9	12.5	12.0	11.4	10.7
92.5°	26.9	27.2	27.5	27.7	27.5	27.2	26.9	26.6	26.1	25.2	24.3
95°	49.8	50.1	50.3	50.5	50.3	50.1	49.8	49.5	49.0	48.0	47.1
97.5°	76.2	76.4	76.5	76.7	76.5	76.4	76.2	76.0	75.6	74.7	73.8
100°	95.7	95.9	96.2	96.4	96.2	95.9	95.7	95.4	94.7	93.5	92.3
102.5°	115.1	115.5	115.8	116.2	115.8	115.5	115.1	114.7	113.9	112.6	111.4
105°	144.7	145.0	145.4	145.8	145.4	145.0	144.7	144.3	143.7	142.9	142.1
107.5°	176.3	176.3	176.2	176.2	176.2	176.3	176.3	176.3	176.1	175.7	175.3
110°	199.2	199.0	198.9	198.8	198.9	199.0	199.2	199.3	199.2	198.8	198.4



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	221.6	221.3	221.1	220.9	221.1	221.3	221.6	221.8	221.8	221.7	221.5
115°	256.2	256.1	256.0	255.8	256.0	256.1	256.2	256.4	256.4	256.6	256.7
117.5°	291.5	291.0	290.4	289.9	290.4	291.0	291.5	292.0	292.2	292.1	292.0
120°	315.1	314.5	313.9	313.5	313.9	314.5	315.1	315.5	315.8	315.8	315.8
122.5°	338.2	337.8	337.4	337.0	337.4	337.8	338.2	338.7	338.9	339.0	339.1
125°	372.6	372.5	372.4	372.2	372.4	372.5	372.6	372.8	373.0	373.2	373.5
127.5°	406.9	406.6	406.4	406.2	406.4	406.6	406.9	407.2	407.3	407.5	407.7
130°	429.5	429.2	429.0	428.7	429.0	429.2	429.5	429.8	429.9	430.1	430.2
132.5°	451.0	450.6	450.3	449.9	450.3	450.6	451.0	451.3	451.6	451.7	451.9
135°	484.3	483.9	483.3	482.8	483.3	483.9	484.3	484.9	485.1	485.1	485.1
137.5°	517.0	516.3	515.7	515.0	515.7	516.3	517.0	517.6	517.9	517.8	517.6
140°	537.7	537.0	536.4	535.8	536.4	537.0	537.7	538.4	538.5	538.3	538.1
142.5°	557.5	556.8	556.1	555.5	556.1	556.8	557.5	558.1	558.3	558.2	558.0
145°	586.3	585.9	585.5	585.1	585.5	585.9	586.3	586.7	586.9	586.9	586.9
147.5°	613.1	612.2	611.3	610.5	611.3	612.2	613.1	613.9	614.3	613.9	613.6
150°	630.0	629.8	629.5	629.2	629.5	629.8	630.0	630.3	630.4	630.4	630.4
152.5°	646.2	645.7	645.2	644.8	645.2	645.7	646.2	646.7	646.7	646.4	646.1
155°	668.8	668.2	667.5	666.9	667.5	668.2	668.8	669.5	669.6	669.0	668.5
157.5°	687.9	687.1	686.2	685.3	686.2	687.1	687.9	688.8	689.0	688.4	687.9
160°	700.0	699.3	698.7	698.1	698.7	699.3	700.0	700.7	700.7	700.2	699.7
162.5°	711.1	710.3	709.6	708.8	709.6	710.3	711.1	711.9	711.9	711.3	710.7
165°	725.7	724.9	724.1	723.3	724.1	724.9	725.7	726.4	726.6	726.1	725.6
167.5°	737.3	736.5	735.7	734.8	735.7	736.5	737.3	738.1	738.1	737.4	736.6
170°	743.7	742.8	741.9	741.0	741.9	742.8	743.7	744.7	744.7	743.9	743.1
172.5°	748.6	747.7	746.9	746.2	746.9	747.7	748.6	749.4	749.4	748.6	747.8
175°	753.7	752.8	751.9	751.0	751.9	752.8	753.7	754.6	754.7	753.9	753.1
177.5°	756.0	755.3	754.6	753.8	754.6	755.3	756.0	756.7	756.8	756.1	755.5
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1391.2	1397.1	1404.5	1409.9	1419.8	1424.3	1429.7	1434.2	1442.0	1449.5	1458.3
5°	1297.4	1307.9	1322.2	1337.5	1355.5	1367.8	1385.1	1395.6	1416.6	1435.8	1454.3
7.5°	1212.4	1225.3	1245.4	1265.2	1288.6	1309.9	1331.5	1355.5	1382.3	1413.9	1440.0
10°	1154.1	1171.5	1193.0	1217.7	1246.2	1270.9	1299.9	1325.8	1358.5	1395.6	1430.2
12.5°	1107.7	1122.5	1146.6	1170.4	1200.7	1230.8	1260.8	1295.2	1333.3	1374.4	1417.8
15°	1043.6	1056.0	1075.7	1108.4	1139.3	1168.9	1214.0	1246.2	1294.3	1340.1	1392.5
17.5°	988.9	1004.2	1020.9	1048.9	1080.9	1117.9	1158.2	1198.5	1244.9	1302.8	1362.0
20°	955.3	967.7	986.8	1008.4	1042.4	1079.4	1117.7	1158.5	1215.3	1275.2	1338.8
22.5°	918.8	932.1	953.7	977.3	1005.8	1041.4	1083.6	1128.3	1187.6	1246.5	1315.6
25°	875.7	884.9	904.7	925.7	954.1	984.4	1028.2	1077.6	1136.2	1203.6	1274.0
27.5°	835.0	843.2	861.2	879.5	905.1	941.1	980.2	1030.2	1085.4	1153.7	1231.7
30°	805.9	814.5	830.6	850.3	875.0	906.5	946.7	993.6	1052.9	1119.6	1201.1
32.5°	780.7	788.3	800.4	820.2	844.4	874.9	912.1	960.0	1019.3	1087.0	1167.0
35°	741.6	750.3	759.5	775.0	796.0	825.6	866.4	911.5	968.3	1033.7	1107.2
37.5°	702.9	712.3	720.5	734.4	753.5	779.7	814.9	861.8	913.2	976.3	1046.8
40°	678.7	686.0	692.8	707.7	726.8	751.5	784.3	826.2	880.6	939.3	997.9
42.5°	654.4	661.4	667.2	680.0	697.7	721.4	752.7	793.6	844.1	898.7	950.5
45°	616.3	620.6	627.4	638.5	652.8	674.3	704.6	741.0	783.6	835.5	874.4
47.5°	575.0	581.9	587.4	597.1	608.8	630.0	659.0	690.0	728.6	767.2	794.6
50°	543.4	550.2	558.3	567.5	578.6	598.4	625.0	656.4	689.1	718.8	742.3
52.5°	513.8	520.1	528.6	537.3	551.0	567.8	590.3	618.4	650.6	671.8	691.4
55°	469.9	473.0	482.9	491.5	504.5	516.9	539.7	564.4	584.2	600.2	616.3
57.5°	425.1	429.3	435.0	442.8	455.6	470.1	486.1	507.9	519.6	527.8	540.3
60°	396.5	397.7	401.4	410.7	420.6	433.5	452.0	467.5	476.1	482.9	493.4
62.5°	364.8	365.1	371.2	378.0	385.5	399.4	414.5	427.0	434.1	437.4	447.4
65°	320.5	319.2	323.0	328.5	337.2	346.4	359.4	370.5	369.9	373.6	379.8
67.5°	275.2	273.9	273.9	279.2	286.3	294.5	303.5	309.9	310.0	315.0	318.1
70°	244.5	240.8	243.3	247.6	250.7	257.5	267.4	269.9	270.5	272.9	276.0
72.5°	212.9	211.7	213.7	215.6	217.6	222.9	231.3	232.8	232.9	234.4	239.5
75°	169.2	167.9	166.8	168.6	171.0	174.8	177.8	180.3	179.7	180.3	184.0
77.5°	126.8	123.3	122.8	123.7	124.4	126.6	129.8	129.5	130.2	130.1	134.3
80°	100.7	95.7	95.1	95.1	95.7	97.0	98.2	99.4	97.6	99.4	100.7
82.5°	74.0	71.0	70.9	70.4	70.5	70.7	71.5	72.2	71.9	72.7	73.5
85°	40.7	39.5	37.7	38.9	38.3	36.4	37.7	35.8	35.2	35.8	36.4
87.5°	15.8	16.2	15.1	14.9	14.2	14.5	13.3	12.6	11.9	12.2	13.5
90°	10.1	9.4	8.5	7.6	6.7	5.8	4.8	3.7	2.7	1.7	0.6
92.5°	23.4	22.6	21.5	20.4	19.3	18.1	17.2	16.4	15.7	15.0	14.3
95°	46.2	45.3	44.0	42.7	41.4	40.1	39.3	39.0	38.7	38.5	38.3
97.5°	73.0	72.1	70.3	68.5	66.7	64.9	63.9	63.8	63.7	63.6	63.5
100°	91.2	90.0	88.2	86.6	84.8	83.2	82.3	82.3	82.3	82.3	82.3
102.5°	110.1	108.8	107.9	107.1	106.2	105.4	104.6	104.1	103.6	103.1	102.6
105°	141.3	140.5	139.7	138.9	138.2	137.4	136.7	136.0	135.4	134.8	134.1
107.5°	174.9	174.5	174.0	173.3	172.8	172.1	171.5	170.9	170.2	169.5	168.9
110°	198.0	197.6	197.2	196.8	196.4	196.0	195.5	194.9	194.2	193.5	192.9



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	221.3	221.1	220.6	220.1	219.6	219.1	218.7	218.4	218.0	217.7	217.4
115°	256.8	257.0	256.7	256.4	256.2	256.0	255.6	255.0	254.5	254.0	253.5
117.5°	291.9	291.8	291.6	291.4	291.1	290.9	290.7	290.4	290.2	289.9	289.7
120°	315.8	315.8	315.7	315.5	315.4	315.3	314.9	314.3	313.5	312.9	312.3
122.5°	339.2	339.3	339.0	338.7	338.3	337.9	337.7	337.5	337.2	337.0	336.8
125°	373.8	374.0	373.9	373.8	373.6	373.5	373.0	372.2	371.5	370.7	369.9
127.5°	407.7	407.9	407.7	407.6	407.4	407.3	406.9	406.5	406.1	405.6	405.2
130°	430.3	430.5	430.2	429.9	429.7	429.4	429.0	428.3	427.7	427.0	426.4
132.5°	452.0	452.1	452.2	452.2	452.3	452.3	451.8	450.8	449.6	448.6	447.5
135°	485.1	485.1	485.1	484.9	484.7	484.7	484.2	483.4	482.6	481.8	481.0
137.5°	517.5	517.3	517.0	516.7	516.4	516.1	515.6	514.8	514.0	513.3	512.5
140°	537.7	537.5	537.1	536.7	536.3	535.9	535.4	534.7	534.1	533.5	532.8
142.5°	557.9	557.7	557.2	556.7	556.3	555.7	555.2	554.7	554.1	553.6	553.0
145°	586.9	586.9	586.5	586.1	585.7	585.3	584.9	584.3	583.8	583.3	582.8
147.5°	613.3	613.0	612.7	612.4	612.0	611.7	611.5	611.2	610.9	610.6	610.3
150°	630.4	630.4	629.9	629.4	628.8	628.4	628.1	628.3	628.4	628.5	628.7
152.5°	645.8	645.5	645.2	645.1	644.8	644.6	644.4	644.3	644.0	643.9	643.7
155°	668.0	667.5	667.3	667.2	667.1	666.9	666.9	666.9	666.9	666.9	666.9
157.5°	687.4	686.9	686.7	686.6	686.5	686.3	686.4	686.7	687.0	687.3	687.6
160°	699.2	698.6	698.5	698.4	698.2	698.1	698.2	698.6	699.0	699.4	699.8
162.5°	710.1	709.5	709.4	709.4	709.4	709.3	709.5	709.8	710.0	710.3	710.7
165°	725.0	724.5	724.4	724.2	724.1	724.0	724.1	724.3	724.6	724.8	725.1
167.5°	735.8	735.0	735.0	735.0	735.0	735.0	735.2	735.8	736.3	736.8	737.4
170°	742.4	741.6	741.6	741.6	741.6	741.6	741.8	742.4	742.8	743.4	743.9
172.5°	747.0	746.2	746.2	746.2	746.2	746.2	746.6	747.0	747.6	748.1	748.6
175°	752.3	751.5	751.5	751.5	751.5	751.5	751.8	752.3	752.9	753.4	753.9
177.5°	754.9	754.2	754.4	754.5	754.6	754.7	754.9	755.3	755.7	756.2	756.6
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1462.8	1469.7	1474.2	1482.6	1489.5	1493.4	1496.9	1499.8	1503.3	1506.3	1514.7
5°	1472.2	1488.2	1501.8	1522.8	1542.0	1556.8	1572.8	1587.1	1598.8	1615.4	1628.4
7.5°	1468.1	1496.6	1526.5	1559.0	1592.2	1623.1	1651.5	1678.1	1702.2	1731.3	1756.8
10°	1464.1	1503.1	1541.3	1585.2	1630.2	1668.6	1704.4	1740.8	1767.4	1804.4	1835.9
12.5°	1461.2	1507.0	1553.2	1605.9	1655.4	1709.5	1757.2	1783.8	1824.2	1853.8	1891.3
15°	1448.7	1509.3	1572.8	1632.1	1702.5	1752.5	1794.5	1846.4	1884.0	1921.8	1962.5
17.5°	1426.3	1494.9	1566.1	1643.7	1711.3	1765.0	1819.1	1869.2	1914.1	1964.6	2015.3
20°	1415.9	1484.5	1566.1	1645.7	1711.7	1768.0	1823.5	1878.5	1927.9	1992.7	2051.4
22.5°	1394.2	1477.1	1552.2	1629.9	1698.0	1759.0	1822.1	1884.4	1950.1	2023.4	2096.8
25°	1355.5	1439.5	1519.1	1595.7	1664.2	1740.8	1808.1	1891.5	1975.5	2072.4	2163.8
27.5°	1315.2	1395.6	1468.6	1542.5	1622.5	1709.2	1796.5	1891.1	2001.1	2123.4	2252.3
30°	1282.6	1358.5	1429.6	1505.5	1588.9	1686.5	1782.2	1894.6	2021.8	2159.5	2312.6
32.5°	1244.5	1314.5	1383.6	1464.0	1554.8	1657.8	1769.3	1892.6	2045.5	2201.9	2359.6
35°	1179.5	1238.1	1309.2	1395.0	1497.5	1615.4	1744.5	1890.2	2065.6	2245.3	2378.1
37.5°	1102.2	1156.9	1231.7	1325.8	1433.3	1559.9	1713.0	1885.9	2072.2	2215.4	2258.3
40°	1050.4	1101.1	1178.8	1276.4	1386.3	1520.4	1688.3	1871.1	2051.4	2142.8	2107.6
42.5°	995.1	1048.2	1124.0	1220.6	1338.9	1484.8	1657.2	1840.0	1991.2	2025.7	1904.1
45°	907.8	962.7	1037.4	1135.0	1262.2	1420.3	1600.0	1766.1	1853.2	1790.8	1602.5
47.5°	826.6	878.1	947.4	1048.1	1179.3	1342.8	1515.9	1648.5	1655.3	1506.5	1305.4
50°	771.3	818.8	888.6	989.3	1119.6	1285.1	1441.3	1545.6	1498.7	1330.2	1136.9
52.5°	716.9	763.5	832.3	932.0	1060.8	1212.4	1357.8	1431.1	1342.6	1169.6	1004.5
55°	638.5	679.3	746.6	838.6	960.8	1101.7	1225.2	1250.5	1135.6	965.2	831.2
57.5°	562.0	600.0	661.2	746.0	857.8	982.5	1079.0	1073.6	952.2	806.0	699.7
60°	510.1	547.2	601.5	684.2	786.1	893.6	976.3	956.6	836.1	710.2	620.6
62.5°	463.7	496.7	548.1	620.5	713.5	813.0	881.0	851.8	733.9	623.7	552.9
65°	395.2	423.0	466.8	528.6	605.8	687.9	740.4	702.7	602.1	516.3	459.5
67.5°	329.9	352.1	388.9	438.2	504.0	570.0	602.0	564.0	483.5	420.9	378.8
70°	288.4	308.2	336.5	380.4	437.8	493.4	517.5	483.5	414.4	360.6	330.3
72.5°	246.9	263.2	288.1	327.6	373.6	421.8	442.9	410.4	353.6	308.2	280.0
75°	190.8	201.9	219.2	246.4	282.8	321.2	332.9	304.4	268.0	234.0	215.6
77.5°	136.6	146.0	159.1	176.3	202.1	226.4	236.6	220.2	192.0	170.6	155.3
80°	105.0	110.0	121.0	135.2	155.6	171.0	177.8	167.4	147.6	131.5	119.8
82.5°	74.9	79.8	86.4	98.2	111.1	121.7	129.0	121.9	107.6	95.0	88.2
85°	36.4	39.5	43.3	48.2	58.1	64.2	63.6	59.3	53.7	48.8	45.1
87.5°	13.2	13.9	15.5	18.2	19.9	22.1	23.3	22.4	20.7	19.3	18.0
90°	1.7	2.7	3.7	4.8	5.8	6.7	7.6	8.5	9.4	10.1	10.7
92.5°	15.0	15.7	16.4	17.2	18.1	19.3	20.4	21.5	22.6	23.4	24.3
95°	38.5	38.7	39.0	39.3	40.1	41.4	42.7	44.0	45.3	46.2	47.1
97.5°	63.6	63.7	63.8	63.9	64.9	66.7	68.5	70.3	72.1	73.0	73.8
100°	82.3	82.3	82.3	82.3	83.2	84.8	86.6	88.2	90.0	91.2	92.3
102.5°	103.1	103.6	104.1	104.6	105.4	106.2	107.1	107.9	108.8	110.1	111.4
105°	134.8	135.4	136.0	136.7	137.4	138.2	138.9	139.7	140.5	141.3	142.1
107.5°	169.5	170.2	170.9	171.5	172.1	172.8	173.3	174.0	174.5	174.9	175.3
110°	193.5	194.2	194.9	195.5	196.0	196.4	196.8	197.2	197.6	198.0	198.4



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	217.7	218.0	218.4	218.7	219.1	219.6	220.1	220.6	221.1	221.3	221.5
115°	254.0	254.5	255.0	255.6	256.0	256.2	256.4	256.7	257.0	256.8	256.7
117.5°	289.9	290.2	290.4	290.7	290.9	291.1	291.4	291.6	291.8	291.9	292.0
120°	312.9	313.5	314.3	314.9	315.3	315.4	315.5	315.7	315.8	315.8	315.8
122.5°	337.0	337.2	337.5	337.7	337.9	338.3	338.7	339.0	339.3	339.2	339.1
125°	370.7	371.5	372.2	373.0	373.5	373.6	373.8	373.9	374.0	373.8	373.5
127.5°	405.6	406.1	406.5	406.9	407.3	407.4	407.6	407.7	407.9	407.7	407.7
130°	427.0	427.7	428.3	429.0	429.4	429.7	429.9	430.2	430.5	430.3	430.2
132.5°	448.6	449.6	450.8	451.8	452.3	452.3	452.2	452.2	452.1	452.0	451.9
135°	481.8	482.6	483.4	484.2	484.7	484.7	484.9	485.1	485.1	485.1	485.1
137.5°	513.3	514.0	514.8	515.6	516.1	516.4	516.7	517.0	517.3	517.5	517.6
140°	533.5	534.1	534.7	535.4	535.9	536.3	536.7	537.1	537.5	537.7	538.1
142.5°	553.6	554.1	554.7	555.2	555.7	556.3	556.7	557.2	557.7	557.9	558.0
145°	583.3	583.8	584.3	584.9	585.3	585.7	586.1	586.5	586.9	586.9	586.9
147.5°	610.6	610.9	611.2	611.5	611.7	612.0	612.4	612.7	613.0	613.3	613.6
150°	628.5	628.4	628.3	628.1	628.4	628.8	629.4	629.9	630.4	630.4	630.4
152.5°	643.9	644.0	644.3	644.4	644.6	644.8	645.1	645.2	645.5	645.8	646.1
155°	666.9	666.9	666.9	666.9	666.9	667.1	667.2	667.3	667.5	668.0	668.5
157.5°	687.3	687.0	686.7	686.4	686.3	686.5	686.6	686.7	686.9	687.4	687.9
160°	699.4	699.0	698.6	698.2	698.1	698.2	698.4	698.5	698.6	699.2	699.7
162.5°	710.3	710.0	709.8	709.5	709.3	709.4	709.4	709.4	709.5	710.1	710.7
165°	724.8	724.6	724.3	724.1	724.0	724.1	724.2	724.4	724.5	725.0	725.6
167.5°	736.8	736.3	735.8	735.2	735.0	735.0	735.0	735.0	735.0	735.8	736.6
170°	743.4	742.8	742.4	741.8	741.6	741.6	741.6	741.6	741.6	742.4	743.1
172.5°	748.1	747.6	747.0	746.6	746.2	746.2	746.2	746.2	746.2	747.0	747.8
175°	753.4	752.9	752.3	751.8	751.5	751.5	751.5	751.5	751.5	752.3	753.1
177.5°	756.2	755.7	755.3	754.9	754.7	754.6	754.5	754.4	754.2	754.9	755.5
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7	755.7



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9	1454.9
2.5°	1521.5	1525.5	1533.9	1531.0	1534.9	1536.9	1538.9
5°	1644.5	1664.2	1672.9	1671.7	1684.6	1681.5	1678.4
7.5°	1783.3	1804.0	1815.7	1830.1	1838.5	1839.1	1846.4
10°	1861.9	1889.0	1900.1	1915.6	1925.5	1931.0	1930.4
12.5°	1922.1	1943.4	1968.3	1975.9	1989.2	1996.2	1993.6
15°	1994.6	2028.5	2054.5	2067.4	2084.2	2089.1	2095.9
17.5°	2059.4	2104.9	2135.2	2175.4	2190.6	2199.9	2194.4
20°	2108.2	2168.1	2198.4	2246.5	2273.1	2287.3	2282.4
22.5°	2166.1	2230.9	2286.8	2328.5	2368.9	2388.1	2392.1
25°	2265.1	2354.0	2436.1	2491.1	2541.1	2552.8	2578.8
27.5°	2375.8	2480.6	2568.4	2626.2	2661.0	2674.1	2682.3
30°	2445.4	2549.7	2615.9	2652.9	2664.0	2662.8	2661.5
32.5°	2479.5	2544.8	2557.6	2547.2	2521.8	2500.2	2477.8
35°	2431.2	2382.4	2309.5	2215.7	2146.5	2076.7	2070.0
37.5°	2186.5	2030.5	1909.2	1773.8	1695.6	1647.3	1614.0
40°	1956.3	1779.1	1632.1	1517.9	1438.2	1406.8	1375.9
42.5°	1706.4	1537.0	1406.8	1311.4	1251.5	1216.6	1192.1
45°	1386.3	1236.9	1135.0	1065.9	1018.3	991.1	975.7
47.5°	1136.0	1025.5	938.9	889.0	856.1	835.0	835.1
50°	1001.6	896.0	838.6	799.1	770.6	754.0	757.1
52.5°	882.6	803.7	754.6	721.5	700.5	690.2	689.9
55°	737.9	681.1	649.0	625.0	610.7	599.0	601.5
57.5°	631.2	583.3	561.8	541.9	532.0	527.3	520.5
60°	565.1	528.0	509.5	493.4	483.5	479.8	473.0
62.5°	506.3	477.1	459.1	446.0	437.0	435.9	430.6
65°	425.5	403.2	387.2	381.0	371.8	369.3	369.3
67.5°	350.8	334.9	322.3	316.6	312.6	313.2	310.2
70°	303.8	290.9	282.8	276.6	273.5	274.2	271.7
72.5°	265.8	251.4	244.3	240.6	236.5	238.1	237.1
75°	201.3	193.9	190.2	186.5	184.0	182.8	181.6
77.5°	147.8	141.3	138.5	136.3	136.7	133.7	136.1
80°	114.2	108.7	106.9	103.8	103.1	103.1	102.5
82.5°	83.6	80.5	79.1	76.6	75.5	76.4	74.9
85°	43.3	40.7	40.2	40.2	38.9	37.7	40.7
87.5°	18.1	16.2	16.3	15.9	16.0	15.6	14.7
90°	11.4	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	25.2	26.1	26.6	26.9	27.2	27.5	27.7
95°	48.0	49.0	49.5	49.8	50.1	50.3	50.5
97.5°	74.7	75.6	76.0	76.2	76.4	76.5	76.7
100°	93.5	94.7	95.4	95.7	95.9	96.2	96.4
102.5°	112.6	113.9	114.7	115.1	115.5	115.8	116.2
105°	142.9	143.7	144.3	144.7	145.0	145.4	145.8
107.5°	175.7	176.1	176.3	176.3	176.3	176.2	176.2
110°	198.8	199.2	199.3	199.2	199.0	198.9	198.8



TEST NUMBER: P333467-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.7	221.8	221.8	221.6	221.3	221.1	220.9
115°	256.6	256.4	256.4	256.2	256.1	256.0	255.8
117.5°	292.1	292.2	292.0	291.5	291.0	290.4	289.9
120°	315.8	315.8	315.5	315.1	314.5	313.9	313.5
122.5°	339.0	338.9	338.7	338.2	337.8	337.4	337.0
125°	373.2	373.0	372.8	372.6	372.5	372.4	372.2
127.5°	407.5	407.3	407.2	406.9	406.6	406.4	406.2
130°	430.1	429.9	429.8	429.5	429.2	429.0	428.7
132.5°	451.7	451.6	451.3	451.0	450.6	450.3	449.9
135°	485.1	485.1	484.9	484.3	483.9	483.3	482.8
137.5°	517.8	517.9	517.6	517.0	516.3	515.7	515.0
140°	538.3	538.5	538.4	537.7	537.0	536.4	535.8
142.5°	558.2	558.3	558.1	557.5	556.8	556.1	555.5
145°	586.9	586.9	586.7	586.3	585.9	585.5	585.1
147.5°	613.9	614.3	613.9	613.1	612.2	611.3	610.5
150°	630.4	630.4	630.3	630.0	629.8	629.5	629.2
152.5°	646.4	646.7	646.7	646.2	645.7	645.2	644.8
155°	669.0	669.6	669.5	668.8	668.2	667.5	666.9
157.5°	688.4	689.0	688.8	687.9	687.1	686.2	685.3
160°	700.2	700.7	700.7	700.0	699.3	698.7	698.1
162.5°	711.3	711.9	711.9	711.1	710.3	709.6	708.8
165°	726.1	726.6	726.4	725.7	724.9	724.1	723.3
167.5°	737.4	738.1	738.1	737.3	736.5	735.7	734.8
170°	743.9	744.7	744.7	743.7	742.8	741.9	741.0
172.5°	748.6	749.4	749.4	748.6	747.7	746.9	746.2
175°	753.9	754.7	754.6	753.7	752.8	751.9	751.0
177.5°	756.1	756.8	756.7	756.0	755.3	754.6	753.8
180°	755.7	755.7	755.7	755.7	755.7	755.7	755.7

(END OF REPORT)