

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333452

Luminaire Tested: **S125DIW-S1090D1340U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333452  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S1090D1340U835-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1340 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9807.4 lumens  
Efficiency: N/A  
Efficacy: 140.5 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 69.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45					45			
1	97	92	88	85	88	85	81	78	71	68	66	58	56	55	46	45	44	38					38			
2	88	81	74	69	80	74	69	64	62	58	55	51	48	45	40	38	37	32					32			
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27					27			
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23					23			
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20					20			
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18					18			
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16					16			
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14					14			
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13					13			
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11					11			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.9	1.6
10°-20°	454.5	4.6
20°-30°	671.0	6.8
30°-40°	783.0	8.0
40°-50°	786.4	8.0
50°-60°	690.3	7.0
60°-70°	514.4	5.2
70°-80°	294.1	3.0
80°-90°	89.2	0.9
90°-100°	63.5	0.6
100°-110°	391.2	4.0
110°-120°	709.5	7.2
120°-130°	910.5	9.3
130°-140°	979.3	10.0
140°-150°	919.2	9.4
150°-160°	743.6	7.6
160°-170°	480.9	4.9
170°-180°	165.9	1.7
0°-30°	1286.4	13.1
0°-40°	2069.4	21.1
0°-60°	3546.2	36.2
0°-90°	4443.9	45.3
90°-120°	1164.1	11.9
90°-150°	3973.2	40.5
90°-180°	5364.0	54.7
0°-180°	9807.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	1	12	21	27	31	7
95°	74	67	21	27	27	94
105°	381	386	386	386	384	404
115°	715	721	722	717	710	708
125°	1016	1025	1025	1020	1016	907
135°	1268	1275	1273	1270	1262	977
145°	1470	1472	1472	1473	1466	919
155°	1618	1611	1613	1616	1607	745
165°	1708	1700	1701	1708	1699	482
175°	1747	1739	1740	1749	1739	166
180°	1747	1747	1747	1747	1747	



TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.4	29.9	30.3	30.8	31.3	31.6	31.7	31.9	32.1	32.2	32.5
90°	1.3	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.7	22.2
92.5°	19.9	18.3	16.7	15.1	13.5	13.6	15.4	17.1	18.9	20.7	22.2
95°	73.8	72.9	72.1	71.2	70.3	64.4	53.5	42.6	31.6	20.7	22.2
97.5°	154.1	155.6	157.2	158.7	160.3	150.2	128.6	107.0	85.3	63.7	55.6
100°	216.2	217.1	217.9	218.8	219.7	220.7	221.8	223.0	224.1	225.3	182.4
102.5°	279.4	280.5	281.6	282.7	283.8	284.7	285.4	286.1	286.7	287.4	279.3
105°	380.7	381.8	383.0	384.1	385.3	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	485.8	485.8	485.8	485.8	485.8	486.1	486.7	487.2	487.8	488.4	488.4
110°	554.2	554.2	554.2	554.2	554.2	554.4	555.0	555.6	556.2	556.7	555.9



TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	618.4	619.1	619.8	620.4	621.1	621.7	622.0	622.3	622.7	623.0	621.9
115°	714.7	716.1	717.6	719.0	720.5	721.3	721.6	721.9	722.2	722.5	721.3
117.5°	814.4	814.3	814.3	814.2	814.2	814.7	815.8	816.9	818.0	819.1	817.6
120°	876.5	876.3	876.0	875.7	875.4	875.7	876.5	877.4	878.3	879.1	878.6
122.5°	931.4	932.5	933.6	934.7	935.8	936.6	937.0	937.4	937.8	938.2	937.6
125°	1016.4	1018.4	1020.4	1022.4	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3
127.5°	1097.4	1098.9	1100.3	1101.7	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5
130°	1147.1	1148.6	1150.0	1151.5	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1
132.5°	1196.9	1198.5	1200.2	1201.9	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4
135°	1267.6	1269.3	1271.0	1272.7	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2
137.5°	1332.6	1334.0	1335.5	1337.0	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1
140°	1375.0	1375.6	1376.2	1376.7	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9
142.5°	1413.3	1413.7	1414.0	1414.4	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8
145°	1469.5	1470.1	1470.7	1471.3	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4
147.5°	1518.7	1518.6	1518.5	1518.4	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1
150°	1549.8	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4
152.5°	1579.8	1578.6	1577.3	1576.1	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3
155°	1618.4	1616.7	1615.0	1613.3	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1
157.5°	1648.2	1647.2	1646.1	1645.1	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7
160°	1668.9	1667.2	1665.5	1663.7	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6
162.5°	1685.5	1683.8	1682.0	1680.3	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6
165°	1707.8	1706.0	1704.3	1702.6	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0
167.5°	1724.3	1722.6	1720.8	1719.0	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7
170°	1733.7	1731.7	1729.6	1727.6	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2
172.5°	1739.9	1737.9	1735.9	1733.8	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2
175°	1746.6	1744.9	1743.2	1741.4	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4
177.5°	1749.7	1748.3	1747.0	1745.6	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	32.8	33.1	33.4	33.4	33.1	32.7	32.4	32.1
90°	23.6	25.0	26.5	27.6	28.5	29.3	30.2	31.1
92.5°	23.6	25.0	26.5	27.4	27.8	28.2	28.6	29.0
95°	23.6	25.0	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	47.5	39.4	31.2	27.2	27.2	27.2	27.2	27.2
100°	139.5	96.7	53.8	31.8	30.6	29.5	28.3	27.2
102.5°	271.2	263.1	255.0	241.1	221.6	202.0	182.4	162.9
105°	385.8	385.8	385.8	385.7	385.4	385.1	384.8	384.5
107.5°	488.5	488.6	488.6	488.2	487.3	486.5	485.6	484.8
110°	555.0	554.2	553.3	553.0	553.3	553.6	553.9	554.2





TEST NUMBER: P333452

CATALOG NUMBER: S125DIW-S1090D1340U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	620.8	619.8	618.7	617.9	617.5	617.1	616.7	616.3
115°	720.2	719.0	717.9	716.4	714.7	713.0	711.2	709.5
117.5°	816.1	814.6	813.1	811.9	811.2	810.5	809.7	809.0
120°	878.0	877.4	876.8	875.8	874.4	872.9	871.5	870.1
122.5°	937.0	936.4	935.9	934.7	933.1	931.4	929.7	928.1
125°	1023.1	1022.0	1020.8	1019.8	1019.0	1018.1	1017.2	1016.4
127.5°	1101.9	1101.2	1100.6	1099.2	1097.1	1095.0	1092.8	1090.7
130°	1153.2	1152.3	1151.5	1150.3	1148.9	1147.4	1146.0	1144.6
132.5°	1201.2	1201.0	1200.8	1200.0	1198.6	1197.2	1195.7	1194.3
135°	1271.6	1271.0	1270.4	1269.3	1267.6	1265.8	1264.1	1262.4
137.5°	1337.2	1337.3	1337.4	1336.7	1335.2	1333.7	1332.2	1330.7
140°	1377.5	1378.0	1378.6	1378.0	1376.3	1374.6	1372.9	1371.1
142.5°	1416.9	1417.1	1417.2	1416.4	1414.6	1412.9	1411.2	1409.5
145°	1472.7	1473.0	1473.3	1472.6	1470.8	1469.1	1467.4	1465.7
147.5°	1520.5	1520.8	1521.2	1520.3	1518.2	1516.1	1514.1	1512.0
150°	1551.0	1551.5	1552.1	1551.2	1548.9	1546.6	1544.3	1542.0
152.5°	1577.9	1578.5	1579.0	1578.3	1576.2	1574.2	1572.1	1570.0
155°	1615.0	1615.8	1616.7	1616.0	1613.7	1611.4	1609.1	1606.8
157.5°	1645.7	1646.6	1647.5	1646.8	1644.5	1642.2	1639.9	1637.6
160°	1664.8	1665.9	1667.1	1666.5	1664.2	1661.9	1659.6	1657.3
162.5°	1682.2	1683.9	1685.5	1685.0	1682.5	1679.9	1677.4	1674.9
165°	1704.7	1706.5	1708.2	1707.9	1705.6	1703.3	1701.0	1698.7
167.5°	1721.8	1723.8	1725.9	1725.6	1723.0	1720.5	1717.9	1715.3
170°	1730.5	1732.8	1735.1	1735.0	1732.4	1729.8	1727.2	1724.6
172.5°	1737.3	1739.4	1741.4	1741.2	1738.6	1736.0	1733.4	1730.8
175°	1744.7	1747.0	1749.3	1749.2	1746.6	1744.0	1741.4	1738.8
177.5°	1747.8	1749.4	1751.0	1750.9	1749.0	1747.2	1745.3	1743.5
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6

(END OF REPORT)