

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333470-927

Luminaire Tested: **S125DIW-S1270D770U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333470-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6495.7 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	53	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	66	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	25	22	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10083	10083	10083
5°	10105	10009	10073
10°	10044	9938	9996
15°	9934	9819	9860
20°	9779	9652	9669
25°	9612	9453	9443
30°	9405	9238	9192
35°	9183	9008	8881
40°	8955	8757	8632
45°	8709	8528	8359
50°	8439	8252	8004
55°	8178	7942	7719
60°	7865	7626	7355
65°	7494	7248	7002
70°	7138	6811	6577
75°	6503	6288	6071
80°	5787	5694	5560
85°	5039	5128	4846



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.2	2.3
10°-20°	415.8	6.4
20°-30°	613.9	9.5
30°-40°	716.4	11.0
40°-50°	719.5	11.1
50°-60°	631.6	9.7
60°-70°	470.6	7.2
70°-80°	269.1	4.1
80°-90°	79.9	1.2
90°-100°	28.8	0.4
100°-110°	177.3	2.7
110°-120°	321.6	5.0
120°-130°	412.8	6.4
130°-140°	444.0	6.8
140°-150°	416.7	6.4
150°-160°	337.1	5.2
160°-170°	218.0	3.4
170°-180°	75.2	1.2
0°-30°	1177.0	18.1
0°-40°	1893.4	29.1
0°-60°	3244.5	49.9
0°-90°	4064.1	62.6
90°-120°	527.8	8.1
90°-150°	1801.3	27.7
90°-180°	2432.0	37.4
0°-180°	6495.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1561	1561	1561	1561	1561	
5°	1559	1556	1544	1554	1554	148
15°	1486	1482	1468	1474	1475	419
25°	1349	1342	1326	1329	1325	620
35°	1165	1159	1142	1136	1126	728
45°	954	948	934	920	915	734
55°	726	722	705	694	686	648
65°	490	487	474	464	458	486
75°	261	258	252	248	243	278
85°	68	69	69	68	65	76
90°	1	5	9	12	14	5
95°	33	31	9	12	12	43
105°	172	175	175	175	174	183
115°	324	327	328	325	322	321
125°	461	465	465	463	461	411
135°	575	578	577	576	572	443
145°	666	667	667	668	664	416
155°	734	730	731	733	728	338
165°	774	771	771	774	770	219
175°	792	789	789	793	788	75
180°	792	792	792	792	792	



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2
2.5°	1565.1	1564.5	1563.8	1563.1	1562.5	1561.1	1558.9	1556.6	1554.5	1552.3	1554.5
5°	1558.7	1558.1	1557.6	1557.0	1556.5	1554.9	1552.1	1549.4	1546.7	1543.9	1546.3
7.5°	1544.4	1543.8	1543.3	1542.7	1542.1	1540.4	1537.4	1534.4	1531.4	1528.4	1530.7
10°	1531.5	1531.0	1530.4	1529.9	1529.3	1527.6	1524.6	1521.5	1518.5	1515.4	1517.7
12.5°	1515.7	1514.7	1513.8	1512.8	1511.8	1509.9	1507.0	1504.3	1501.5	1498.7	1500.5
15°	1485.8	1485.0	1484.2	1483.4	1482.6	1480.6	1477.6	1474.6	1471.6	1468.5	1469.9
17.5°	1451.5	1450.3	1449.1	1447.9	1446.7	1444.5	1441.4	1438.2	1435.1	1431.9	1433.7
20°	1422.8	1422.3	1421.7	1421.2	1420.6	1418.6	1415.0	1411.4	1407.9	1404.3	1406.2
22.5°	1394.2	1393.2	1392.2	1391.2	1390.2	1388.1	1384.7	1381.4	1378.0	1374.7	1375.9
25°	1348.8	1347.3	1346.0	1344.7	1343.2	1340.8	1337.2	1333.6	1330.1	1326.5	1327.1
27.5°	1295.6	1294.8	1294.0	1293.2	1292.4	1290.1	1286.4	1282.7	1279.1	1275.3	1275.5
30°	1261.1	1260.2	1259.4	1258.5	1257.7	1255.3	1251.2	1247.1	1242.9	1238.8	1238.3
32.5°	1223.5	1222.3	1221.0	1219.7	1218.5	1216.0	1212.3	1208.6	1204.9	1201.3	1200.3
35°	1164.7	1163.6	1162.5	1161.4	1160.3	1157.9	1154.0	1150.2	1146.3	1142.5	1141.1
37.5°	1103.7	1102.3	1101.0	1099.5	1098.2	1095.7	1092.1	1088.5	1084.8	1081.2	1079.2
40°	1062.2	1060.8	1059.5	1058.0	1056.7	1054.1	1050.3	1046.4	1042.6	1038.7	1036.3
42.5°	1017.7	1016.6	1015.4	1014.2	1013.1	1010.6	1006.8	1002.9	999.1	995.2	993.0
45°	953.5	952.4	951.3	950.2	949.1	946.9	943.6	940.3	937.1	933.7	930.4
47.5°	884.3	884.4	884.5	884.5	884.6	882.6	878.7	874.7	870.8	866.8	863.5
50°	839.9	839.1	838.2	837.4	836.5	834.5	831.2	827.9	824.7	821.3	817.8
52.5°	794.4	793.8	793.2	792.6	792.0	790.0	786.4	782.9	779.4	775.9	772.8
55°	726.3	725.4	724.6	723.7	722.9	720.6	716.8	713.0	709.1	705.3	702.7
57.5°	654.3	653.9	653.5	653.1	652.6	650.8	647.5	644.3	641.0	637.8	634.6
60°	608.9	607.8	606.7	605.6	604.5	602.5	599.4	596.4	593.4	590.4	587.6
62.5°	561.5	560.6	559.8	558.8	557.9	556.3	553.7	551.0	548.5	545.9	543.0
65°	490.4	489.8	489.3	488.7	488.1	486.3	483.3	480.3	477.3	474.3	471.8
67.5°	421.4	420.3	419.1	418.0	416.8	415.1	412.9	410.6	408.4	406.1	404.0
70°	378.0	376.6	375.2	373.8	372.5	370.5	368.0	365.6	363.1	360.7	359.0
72.5°	330.5	329.5	328.7	327.7	326.8	325.5	323.9	322.3	320.8	319.2	317.3
75°	260.6	260.1	259.5	259.0	258.4	257.5	256.1	254.7	253.3	252.0	251.1
77.5°	196.1	195.9	195.7	195.5	195.3	194.8	194.0	193.2	192.4	191.7	191.2
80°	155.6	155.6	155.6	155.6	155.6	155.3	154.8	154.2	153.7	153.1	152.9
82.5°	120.0	119.6	119.1	118.7	118.3	118.0	117.9	117.8	117.7	117.6	117.1
85°	68.0	68.2	68.4	68.8	69.0	69.2	69.2	69.2	69.2	69.2	68.9
87.5°	26.8	27.0	27.3	27.4	27.6	27.7	27.6	27.6	27.6	27.6	27.7
90°	0.6	1.7	2.7	3.7	4.8	5.7	6.7	7.6	8.5	9.4	10.1
92.5°	9.0	8.3	7.6	6.8	6.1	6.2	7.0	7.8	8.6	9.4	10.1
95°	33.4	33.0	32.6	32.3	31.9	29.2	24.2	19.3	14.3	9.4	10.1
97.5°	69.9	70.6	71.3	71.9	72.6	68.1	58.3	48.5	38.7	28.9	25.2
100°	98.0	98.4	98.8	99.2	99.6	100.1	100.6	101.1	101.6	102.1	82.7
102.5°	126.7	127.1	127.7	128.2	128.7	129.0	129.4	129.7	130.0	130.3	126.7
105°	172.5	173.1	173.6	174.1	174.7	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	220.2	220.2	220.2	220.2	220.2	220.4	220.6	220.9	221.2	221.4	221.4
110°	251.2	251.2	251.2	251.2	251.2	251.4	251.6	251.9	252.2	252.4	252.0



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	280.4	280.7	281.0	281.3	281.6	281.9	282.0	282.2	282.3	282.5	281.9
115°	324.0	324.6	325.3	326.0	326.6	327.0	327.2	327.3	327.4	327.6	327.0
117.5°	369.2	369.2	369.2	369.2	369.1	369.3	369.9	370.3	370.8	371.3	370.7
120°	397.4	397.3	397.1	397.0	396.9	397.0	397.4	397.8	398.2	398.5	398.3
122.5°	422.2	422.8	423.3	423.7	424.3	424.6	424.8	424.9	425.2	425.3	425.1
125°	460.8	461.7	462.6	463.5	464.5	464.9	464.9	464.9	464.9	464.9	464.4
127.5°	497.5	498.2	498.8	499.5	500.1	500.4	500.3	500.3	500.2	500.1	499.8
130°	520.1	520.7	521.3	522.0	522.7	523.1	523.2	523.3	523.5	523.6	523.2
132.5°	542.6	543.4	544.2	544.9	545.7	545.9	545.6	545.3	545.0	544.7	544.6
135°	574.6	575.4	576.2	577.0	577.8	578.1	577.8	577.5	577.3	577.0	576.7
137.5°	604.1	604.8	605.5	606.2	606.8	607.0	606.8	606.6	606.3	606.1	606.2
140°	623.4	623.6	623.9	624.2	624.4	624.5	624.3	624.2	624.1	623.9	624.2
142.5°	640.7	640.9	641.0	641.2	641.4	641.5	641.7	641.9	642.1	642.3	642.3
145°	666.2	666.5	666.8	667.0	667.3	667.4	667.4	667.4	667.4	667.4	667.5
147.5°	688.6	688.5	688.4	688.4	688.3	688.4	688.6	688.6	688.8	689.0	689.1
150°	702.6	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.9
152.5°	716.2	715.7	715.1	714.5	713.9	713.8	714.1	714.3	714.5	714.8	715.1
155°	733.7	732.9	732.1	731.3	730.6	730.3	730.6	730.9	731.1	731.3	731.7
157.5°	747.2	746.8	746.3	745.8	745.4	745.1	745.1	745.2	745.2	745.2	745.7
160°	756.6	755.8	755.0	754.2	753.5	753.1	753.3	753.4	753.5	753.7	754.2
162.5°	764.1	763.3	762.6	761.8	761.0	760.7	760.8	761.0	761.0	761.2	761.9
165°	774.2	773.4	772.7	771.9	771.1	770.8	770.9	771.0	771.2	771.3	772.1
167.5°	781.7	780.9	780.1	779.3	778.5	778.2	778.3	778.4	778.6	778.7	779.6
170°	786.0	785.1	784.1	783.2	782.3	781.9	782.0	782.2	782.3	782.4	783.5
172.5°	788.8	787.9	787.0	786.0	785.1	784.8	785.1	785.3	785.5	785.8	786.6
175°	791.9	791.1	790.3	789.5	788.7	788.4	788.5	788.6	788.8	788.9	790.0
177.5°	793.2	792.6	792.0	791.4	790.8	790.4	790.6	790.7	790.8	790.9	791.6
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2	1561.2
2.5°	1556.6	1558.9	1561.1	1562.0	1561.9	1561.6	1561.4	1561.2
5°	1548.8	1551.3	1553.8	1554.9	1554.6	1554.3	1554.0	1553.8
7.5°	1533.1	1535.6	1537.9	1539.1	1538.8	1538.5	1538.3	1537.9
10°	1519.9	1522.1	1524.2	1525.2	1525.0	1524.6	1524.4	1524.2
12.5°	1502.2	1504.0	1505.7	1506.6	1506.5	1506.4	1506.4	1506.3
15°	1471.3	1472.7	1474.0	1474.7	1474.7	1474.7	1474.7	1474.7
17.5°	1435.4	1437.1	1438.8	1438.9	1437.6	1436.2	1434.8	1433.5
20°	1408.2	1410.1	1412.0	1412.3	1410.9	1409.5	1408.2	1406.8
22.5°	1377.2	1378.5	1379.7	1379.9	1379.0	1378.0	1377.1	1376.2
25°	1327.6	1328.2	1328.7	1328.6	1327.8	1326.9	1326.1	1325.2
27.5°	1275.6	1275.7	1275.8	1275.4	1274.6	1273.8	1273.0	1272.2
30°	1237.7	1237.2	1236.6	1236.0	1235.1	1234.3	1233.4	1232.6
32.5°	1199.3	1198.3	1197.3	1196.0	1194.6	1193.1	1191.6	1190.2
35°	1139.7	1138.4	1137.0	1135.2	1133.0	1130.8	1128.6	1126.4
37.5°	1077.1	1075.1	1073.1	1071.4	1070.2	1068.9	1067.6	1066.4
40°	1033.8	1031.3	1028.8	1027.2	1026.4	1025.6	1024.7	1023.9
42.5°	990.8	988.5	986.3	984.5	983.3	982.0	980.7	979.5
45°	927.2	923.8	920.6	918.5	917.7	916.9	916.0	915.2
47.5°	860.1	856.7	853.4	850.8	848.8	846.9	845.0	843.1
50°	814.2	810.6	807.1	804.3	802.4	800.5	798.6	796.6
52.5°	769.6	766.5	763.3	760.7	758.6	756.5	754.3	752.2
55°	700.3	697.8	695.4	693.2	691.3	689.4	687.4	685.5
57.5°	631.4	628.3	625.1	623.0	621.9	620.9	619.8	618.8
60°	584.9	582.2	579.4	577.1	575.1	573.2	571.3	569.4
62.5°	540.0	537.0	534.1	531.9	530.4	528.9	527.4	525.9
65°	469.4	466.8	464.4	462.6	461.5	460.4	459.3	458.2
67.5°	402.0	399.8	397.8	396.4	395.7	395.1	394.4	393.7
70°	357.4	355.7	354.0	352.7	351.6	350.5	349.4	348.3
72.5°	315.4	313.5	311.7	310.2	309.1	308.0	306.9	305.8
75°	250.3	249.5	248.7	247.7	246.6	245.5	244.4	243.3
77.5°	190.7	190.2	189.7	189.1	188.3	187.5	186.8	186.0
80°	152.6	152.3	152.0	151.6	151.1	150.5	150.0	149.5
82.5°	116.6	116.1	115.6	115.3	115.2	115.1	114.9	114.9
85°	68.6	68.4	68.0	67.7	67.1	66.5	66.0	65.4
87.5°	27.8	28.0	28.1	28.0	27.6	27.3	26.9	26.5
90°	10.7	11.3	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	10.7	11.3	12.0	12.4	12.6	12.8	13.0	13.2
95°	10.7	11.3	12.0	12.4	12.4	12.4	12.4	12.4
97.5°	21.5	17.8	14.2	12.4	12.4	12.4	12.4	12.4
100°	63.3	43.8	24.4	14.4	13.9	13.4	12.8	12.4
102.5°	122.9	119.3	115.6	109.3	100.4	91.6	82.7	73.8
105°	174.9	174.9	174.9	174.8	174.8	174.6	174.4	174.4
107.5°	221.5	221.5	221.5	221.3	220.9	220.5	220.1	219.8
110°	251.6	251.2	250.8	250.7	250.8	251.0	251.1	251.2



TEST NUMBER: P333470-927

CATALOG NUMBER: S125DIW-S1270D770U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	281.5	281.0	280.4	280.1	280.0	279.8	279.6	279.4
115°	326.5	326.0	325.4	324.8	324.0	323.2	322.4	321.6
117.5°	369.9	369.3	368.6	368.1	367.7	367.4	367.1	366.8
120°	398.1	397.8	397.5	397.0	396.4	395.8	395.1	394.4
122.5°	424.8	424.5	424.3	423.7	423.0	422.2	421.5	420.7
125°	463.8	463.3	462.8	462.3	461.9	461.5	461.2	460.8
127.5°	499.6	499.2	499.0	498.4	497.3	496.4	495.4	494.5
130°	522.8	522.4	522.0	521.5	520.9	520.2	519.5	518.9
132.5°	544.5	544.5	544.4	544.1	543.4	542.7	542.1	541.5
135°	576.5	576.2	576.0	575.4	574.6	573.9	573.1	572.3
137.5°	606.3	606.3	606.3	606.0	605.3	604.7	604.0	603.3
140°	624.5	624.7	625.0	624.7	623.9	623.2	622.4	621.6
142.5°	642.4	642.5	642.5	642.1	641.4	640.6	639.8	639.0
145°	667.7	667.8	667.9	667.6	666.8	666.0	665.3	664.5
147.5°	689.3	689.4	689.6	689.2	688.3	687.4	686.4	685.5
150°	703.1	703.4	703.7	703.3	702.2	701.2	700.1	699.1
152.5°	715.3	715.6	715.9	715.5	714.5	713.7	712.7	711.8
155°	732.1	732.5	732.9	732.6	731.6	730.6	729.5	728.4
157.5°	746.1	746.5	746.9	746.6	745.5	744.5	743.5	742.4
160°	754.7	755.3	755.7	755.5	754.5	753.4	752.4	751.3
162.5°	762.6	763.3	764.1	763.9	762.8	761.6	760.5	759.3
165°	772.9	773.6	774.4	774.3	773.2	772.2	771.2	770.1
167.5°	780.5	781.5	782.4	782.4	781.2	780.0	778.8	777.6
170°	784.5	785.6	786.6	786.6	785.4	784.2	783.0	781.9
172.5°	787.6	788.5	789.5	789.3	788.2	787.0	785.8	784.7
175°	791.0	792.0	793.1	793.0	791.9	790.7	789.5	788.3
177.5°	792.3	793.1	793.8	793.8	792.9	792.1	791.2	790.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9

(END OF REPORT)