

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333458

Luminaire Tested: **S125DIW-S1090D1560U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333458
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D1560U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10680.5 lumens
Efficiency: N/A
Efficacy: 139.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	42
1	96	92	88	84	87	84	80	77	69	67	64	55	54	52	43	42	41	35
2	87	80	74	69	79	73	68	63	60	56	53	48	46	44	38	36	34	29
3	80	70	63	57	72	64	58	53	53	49	45	43	40	37	33	31	29	25
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18
6	61	49	41	36	56	45	38	33	38	33	28	31	27	24	24	21	19	16
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	40	33	28	48	37	30	26	31	26	22	26	22	19	20	17	15	13
9	49	37	29	24	45	34	27	23	29	23	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	1.5
10°-20°	454.5	4.3
20°-30°	671.0	6.3
30°-40°	783.0	7.3
40°-50°	786.4	7.4
50°-60°	690.3	6.5
60°-70°	514.4	4.8
70°-80°	294.1	2.8
80°-90°	89.8	0.8
90°-100°	73.8	0.7
100°-110°	454.8	4.3
110°-120°	824.9	7.7
120°-130°	1058.6	9.9
130°-140°	1138.6	10.7
140°-150°	1068.8	10.0
150°-160°	864.5	8.1
160°-170°	559.1	5.2
170°-180°	192.9	1.8
0°-30°	1286.4	12.0
0°-40°	2069.4	19.4
0°-60°	3546.2	33.2
0°-90°	4444.5	41.6
90°-120°	1353.5	12.7
90°-150°	4619.5	43.3
90°-180°	6236.0	58.4
0°-180°	10680.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	2	13	24	31	36	8
95°	86	78	24	31	32	109
105°	443	448	449	448	447	469
115°	831	838	840	834	825	823
125°	1182	1192	1192	1186	1182	1055
135°	1474	1482	1480	1476	1468	1136
145°	1709	1711	1712	1712	1704	1068
155°	1882	1873	1876	1879	1868	867
165°	1986	1977	1978	1986	1975	561
175°	2031	2022	2023	2034	2022	193
180°	2031	2031	2031	2031	2031	



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.5	30.0	30.5	31.1	31.6	32.0	32.2	32.4	32.7	32.9	33.2
90°	1.5	4.2	6.9	9.5	12.2	14.7	17.1	19.4	21.7	24.1	25.8
92.5°	23.2	21.3	19.4	17.6	15.7	15.8	17.9	19.9	22.0	24.1	25.8
95°	85.8	84.8	83.8	82.8	81.8	74.9	62.2	49.5	36.8	24.1	25.8
97.5°	179.1	180.9	182.7	184.6	186.4	174.7	149.5	124.4	99.2	74.1	64.6
100°	251.4	252.4	253.4	254.4	255.4	256.6	257.9	259.3	260.6	261.9	212.1
102.5°	324.9	326.1	327.4	328.7	329.9	331.0	331.8	332.6	333.4	334.2	324.8
105°	442.6	443.9	445.3	446.6	447.9	448.6	448.6	448.6	448.6	448.6	448.6
107.5°	564.8	564.8	564.8	564.8	564.8	565.1	565.8	566.5	567.2	567.8	567.9
110°	644.3	644.3	644.3	644.3	644.3	644.6	645.3	646.0	646.6	647.3	646.3



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	719.0	719.8	720.6	721.4	722.2	722.8	723.2	723.6	724.0	724.4	723.1
115°	831.0	832.6	834.3	836.0	837.6	838.6	839.0	839.3	839.7	840.0	838.6
117.5°	946.9	946.8	946.7	946.7	946.6	947.2	948.5	949.7	951.0	952.3	950.5
120°	1019.1	1018.8	1018.5	1018.1	1017.8	1018.1	1019.1	1020.1	1021.1	1022.1	1021.5
122.5°	1083.0	1084.2	1085.5	1086.8	1088.0	1088.9	1089.4	1089.8	1090.3	1090.8	1090.1
125°	1181.7	1184.0	1186.4	1188.7	1191.1	1192.2	1192.2	1192.2	1192.2	1192.2	1190.9
127.5°	1275.9	1277.6	1279.3	1281.0	1282.6	1283.4	1283.2	1283.0	1282.8	1282.6	1281.8
130°	1333.7	1335.4	1337.1	1338.8	1340.4	1341.4	1341.8	1342.1	1342.4	1342.8	1341.8
132.5°	1391.5	1393.5	1395.4	1397.4	1399.3	1399.9	1399.2	1398.4	1397.7	1397.0	1396.8
135°	1473.7	1475.7	1477.8	1479.8	1481.8	1482.4	1481.8	1481.1	1480.4	1479.8	1479.1
137.5°	1549.3	1551.0	1552.8	1554.5	1556.3	1556.8	1556.2	1555.6	1555.0	1554.4	1554.6
140°	1598.7	1599.4	1600.0	1600.7	1601.4	1601.5	1601.2	1600.9	1600.5	1600.2	1600.9
142.5°	1643.2	1643.6	1644.0	1644.4	1644.8	1645.3	1645.8	1646.2	1646.7	1647.2	1647.3
145°	1708.6	1709.2	1709.9	1710.6	1711.3	1711.6	1711.6	1711.6	1711.6	1711.6	1711.9
147.5°	1765.8	1765.6	1765.5	1765.4	1765.2	1765.4	1765.8	1766.2	1766.6	1767.0	1767.4
150°	1801.9	1801.2	1800.6	1799.9	1799.2	1799.2	1799.9	1800.6	1801.2	1801.9	1802.6
152.5°	1836.8	1835.4	1833.9	1832.4	1830.9	1830.5	1831.2	1831.9	1832.6	1833.2	1833.9
155°	1881.7	1879.7	1877.7	1875.7	1873.7	1873.0	1873.7	1874.3	1875.0	1875.7	1876.7
157.5°	1916.3	1915.1	1913.9	1912.7	1911.5	1910.9	1911.0	1911.1	1911.1	1911.2	1912.3
160°	1940.4	1938.4	1936.4	1934.4	1932.4	1931.5	1931.9	1932.2	1932.5	1932.9	1934.2
162.5°	1959.7	1957.7	1955.7	1953.6	1951.6	1950.8	1951.1	1951.5	1951.8	1952.1	1954.0
165°	1985.6	1983.6	1981.5	1979.5	1977.5	1976.7	1977.0	1977.4	1977.7	1978.0	1980.0
167.5°	2004.8	2002.8	2000.7	1998.6	1996.5	1995.7	1996.0	1996.3	1996.7	1997.0	1999.4
170°	2015.7	2013.3	2011.0	2008.6	2006.3	2005.3	2005.6	2006.0	2006.3	2006.6	2009.3
172.5°	2022.9	2020.6	2018.2	2015.9	2013.5	2012.7	2013.3	2013.9	2014.5	2015.1	2017.5
175°	2030.7	2028.7	2026.7	2024.7	2022.7	2021.9	2022.2	2022.5	2022.9	2023.2	2025.9
177.5°	2034.3	2032.7	2031.1	2029.5	2027.9	2027.2	2027.5	2027.8	2028.0	2028.3	2030.2
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	33.6	33.9	34.2	34.3	34.0	33.7	33.4	33.1
90°	27.4	29.1	30.8	32.1	33.1	34.1	35.1	36.1
92.5°	27.4	29.1	30.8	31.8	32.3	32.8	33.3	33.7
95°	27.4	29.1	30.8	31.6	31.6	31.6	31.6	31.6
97.5°	55.2	45.8	36.3	31.6	31.6	31.6	31.6	31.6
100°	162.2	112.4	62.6	37.0	35.6	34.3	33.0	31.6
102.5°	315.3	305.9	296.5	280.4	257.6	234.9	212.1	189.4
105°	448.6	448.6	448.6	448.4	448.1	447.8	447.4	447.1
107.5°	568.0	568.0	568.1	567.6	566.6	565.6	564.6	563.6
110°	645.3	644.3	643.3	643.0	643.3	643.6	644.0	644.3



TEST NUMBER: P333458

CATALOG NUMBER: S125DIW-S1090D1560U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	721.8	720.6	719.3	718.4	718.0	717.5	717.0	716.5
115°	837.3	836.0	834.6	833.0	831.0	828.9	826.9	824.9
117.5°	948.8	947.1	945.3	944.0	943.2	942.3	941.4	940.5
120°	1020.8	1020.1	1019.5	1018.3	1016.6	1014.9	1013.3	1011.6
122.5°	1089.4	1088.8	1088.1	1086.8	1084.9	1082.9	1081.0	1079.0
125°	1189.6	1188.2	1186.9	1185.7	1184.7	1183.7	1182.7	1181.7
127.5°	1281.1	1280.4	1279.6	1278.0	1275.5	1273.1	1270.6	1268.1
130°	1340.8	1339.8	1338.8	1337.4	1335.8	1334.1	1332.4	1330.7
132.5°	1396.6	1396.4	1396.2	1395.2	1393.6	1391.9	1390.2	1388.5
135°	1478.4	1477.8	1477.1	1475.7	1473.7	1471.7	1469.7	1467.7
137.5°	1554.7	1554.8	1555.0	1554.2	1552.4	1550.7	1548.9	1547.2
140°	1601.5	1602.2	1602.9	1602.2	1600.2	1598.2	1596.2	1594.2
142.5°	1647.4	1647.6	1647.7	1646.8	1644.7	1642.7	1640.7	1638.7
145°	1712.3	1712.6	1712.9	1712.1	1710.1	1708.1	1706.1	1704.1
147.5°	1767.8	1768.2	1768.6	1767.6	1765.2	1762.8	1760.4	1758.0
150°	1803.2	1803.9	1804.6	1803.6	1800.9	1798.2	1795.6	1792.9
152.5°	1834.6	1835.2	1835.9	1835.0	1832.6	1830.2	1827.8	1825.4
155°	1877.7	1878.7	1879.7	1878.8	1876.2	1873.5	1870.8	1868.1
157.5°	1913.3	1914.4	1915.5	1914.7	1912.0	1909.3	1906.6	1904.0
160°	1935.5	1936.9	1938.2	1937.6	1934.9	1932.2	1929.5	1926.9
162.5°	1955.9	1957.8	1959.6	1959.1	1956.2	1953.2	1950.3	1947.3
165°	1982.0	1984.1	1986.1	1985.7	1983.1	1980.4	1977.7	1975.0
167.5°	2001.8	2004.2	2006.6	2006.3	2003.3	2000.3	1997.3	1994.3
170°	2012.0	2014.7	2017.3	2017.2	2014.2	2011.2	2008.1	2005.1
172.5°	2019.9	2022.3	2024.7	2024.4	2021.4	2018.4	2015.4	2012.4
175°	2028.5	2031.2	2033.9	2033.7	2030.7	2027.7	2024.7	2021.7
177.5°	2032.1	2033.9	2035.8	2035.7	2033.5	2031.4	2029.2	2027.1
180°	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7	2030.7

(END OF REPORT)