

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333441

Luminaire Tested: **S125DIW-S1090D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333441
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1090D770U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7104.1 lumens
Efficiency: N/A
Efficacy: 132.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68	63
1	101	96	92	88	94	90	87	84	79	77	74	69	67	65	60	58	57	53
2	92	84	78	72	85	79	73	69	69	65	61	61	57	54	52	50	48	44
3	83	74	66	60	78	69	63	57	61	56	52	54	49	46	46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44	48	43	39	42	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	34	31	28
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24	22
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	29	24	21	19
9	52	39	32	26	49	37	30	25	33	28	23	30	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	28	23	19	24	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11021	11021	11021
5°	11045	10940	11010
10°	10978	10863	10925
15°	10858	10732	10777
20°	10689	10549	10568
25°	10505	10332	10322
30°	10279	10097	10047
35°	10037	9845	9707
40°	9788	9571	9435
45°	9519	9322	9136
50°	9224	9020	8748
55°	8938	8679	8436
60°	8596	8335	8038
65°	8189	7922	7653
70°	7801	7444	7189
75°	7107	6872	6635
80°	6326	6226	6073
85°	5498	5602	5298



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	2.3
10°-20°	454.5	6.4
20°-30°	671.0	9.4
30°-40°	783.0	11.0
40°-50°	786.4	11.1
50°-60°	690.3	9.7
60°-70°	514.4	7.2
70°-80°	294.1	4.1
80°-90°	87.6	1.2
90°-100°	63.9	0.9
100°-110°	188.7	2.7
110°-120°	319.6	4.5
120°-130°	420.6	5.9
130°-140°	471.2	6.6
140°-150°	461.9	6.5
150°-160°	387.9	5.5
160°-170°	257.9	3.6
170°-180°	90.2	1.3
0°-30°	1286.4	18.1
0°-40°	2069.4	29.1
0°-60°	3546.2	49.9
0°-90°	4442.3	62.5
90°-120°	572.1	8.1
90°-150°	1925.8	27.1
90°-180°	2662.0	37.5
0°-180°	7104.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1706	1706	1706	1706	1706	
5°	1704	1700	1688	1699	1698	162
15°	1624	1619	1605	1612	1612	458
25°	1474	1467	1450	1452	1448	678
35°	1273	1267	1249	1242	1231	796
45°	1042	1036	1021	1005	1000	803
55°	794	789	771	759	749	708
65°	536	533	518	507	501	532
75°	285	282	275	271	266	304
85°	74	76	76	74	72	83
90°	1	7	12	16	18	7
95°	48	50	57	62	64	52
105°	169	173	177	182	184	181
115°	320	323	324	324	323	316
125°	467	471	472	471	470	418
135°	607	612	612	612	610	468
145°	736	739	741	741	739	460
155°	842	842	843	845	842	388
165°	915	914	915	917	913	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1710.7	1710.0	1709.2	1708.5	1707.8	1706.2	1703.8	1701.4	1699.0	1696.6	1699.0
5°	1703.7	1703.1	1702.5	1701.9	1701.3	1699.5	1696.5	1693.5	1690.5	1687.5	1690.2
7.5°	1688.0	1687.4	1686.8	1686.2	1685.6	1683.6	1680.3	1677.0	1673.7	1670.4	1673.1
10°	1674.0	1673.4	1672.8	1672.2	1671.6	1669.6	1666.3	1663.0	1659.7	1656.4	1658.8
12.5°	1656.7	1655.6	1654.5	1653.4	1652.4	1650.3	1647.2	1644.2	1641.1	1638.0	1640.0
15°	1624.0	1623.1	1622.2	1621.3	1620.4	1618.3	1615.0	1611.7	1608.4	1605.1	1606.6
17.5°	1586.5	1585.2	1583.8	1582.5	1581.2	1578.8	1575.4	1572.0	1568.6	1565.1	1567.0
20°	1555.2	1554.6	1554.0	1553.4	1552.8	1550.5	1546.6	1542.7	1538.8	1534.9	1537.0
22.5°	1523.8	1522.8	1521.7	1520.6	1519.5	1517.1	1513.5	1509.8	1506.2	1502.5	1503.9
25°	1474.2	1472.7	1471.2	1469.7	1468.2	1465.5	1461.6	1457.7	1453.8	1449.9	1450.5
27.5°	1416.1	1415.2	1414.3	1413.4	1412.5	1410.1	1406.0	1402.0	1398.0	1394.0	1394.1
30°	1378.3	1377.4	1376.5	1375.6	1374.7	1372.0	1367.5	1363.0	1358.5	1354.0	1353.4
32.5°	1337.3	1335.9	1334.5	1333.1	1331.8	1329.1	1325.0	1321.0	1317.0	1313.0	1311.9
35°	1273.0	1271.8	1270.6	1269.4	1268.2	1265.5	1261.3	1257.1	1252.9	1248.7	1247.2
37.5°	1206.3	1204.8	1203.3	1201.8	1200.3	1197.6	1193.6	1189.7	1185.7	1181.8	1179.5
40°	1161.0	1159.5	1158.0	1156.5	1155.0	1152.1	1147.9	1143.7	1139.5	1135.3	1132.6
42.5°	1112.4	1111.1	1109.9	1108.6	1107.3	1104.6	1100.4	1096.2	1092.0	1087.8	1085.3
45°	1042.2	1041.0	1039.8	1038.6	1037.4	1035.0	1031.4	1027.8	1024.2	1020.6	1017.0
47.5°	966.6	966.6	966.7	966.8	966.8	964.7	960.4	956.0	951.7	947.4	943.7
50°	918.0	917.1	916.2	915.3	914.4	912.1	908.5	904.9	901.3	897.7	893.8
52.5°	868.3	867.6	867.0	866.3	865.7	863.4	859.6	855.7	851.9	848.0	844.6
55°	793.8	792.9	792.0	791.1	790.2	787.6	783.4	779.2	775.0	770.8	768.1
57.5°	715.2	714.7	714.3	713.8	713.3	711.3	707.7	704.2	700.7	697.1	693.6
60°	665.5	664.3	663.1	661.9	660.7	658.5	655.2	651.9	648.6	645.3	642.3
62.5°	613.7	612.7	611.8	610.8	609.9	608.0	605.1	602.3	599.5	596.7	593.4
65°	535.9	535.3	534.7	534.1	533.5	531.6	528.3	525.0	521.7	518.4	515.7
67.5°	460.6	459.3	458.1	456.8	455.6	453.7	451.2	448.8	446.3	443.9	441.6
70°	413.1	411.6	410.1	408.6	407.1	405.0	402.3	399.6	396.9	394.2	392.4
72.5°	361.3	360.2	359.2	358.2	357.2	355.8	354.1	352.3	350.6	348.8	346.8
75°	284.8	284.2	283.6	283.0	282.4	281.4	279.9	278.4	276.9	275.4	274.5
77.5°	214.4	214.1	213.9	213.7	213.4	212.9	212.0	211.2	210.4	209.5	209.0
80°	170.1	170.1	170.1	170.1	170.1	169.8	169.2	168.6	168.0	167.4	167.1
82.5°	131.2	130.7	130.3	129.8	129.3	129.0	128.9	128.8	128.6	128.5	128.0
85°	74.2	74.5	74.8	75.1	75.4	75.6	75.6	75.6	75.6	75.6	75.3
87.5°	29.3	29.6	29.8	30.1	30.4	30.5	30.5	30.5	30.5	30.5	30.6
90°	0.7	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7
92.5°	18.0	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6
95°	48.3	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3
97.5°	80.2	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1
100°	103.9	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1
102.5°	129.5	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0
105°	169.3	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4
107.5°	213.2	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8
110°	243.5	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.4	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4
115°	320.0	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2
117.5°	365.7	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5
120°	394.2	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6
122.5°	425.1	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2
125°	466.9	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8
127.5°	511.5	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7
130°	538.2	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2
132.5°	564.9	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6
135°	607.2	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4
137.5°	647.0	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2
140°	672.6	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8
142.5°	698.1	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2
145°	735.7	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9
147.5°	770.4	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2
150°	793.6	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8
152.5°	812.6	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2
155°	841.8	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2
157.5°	868.0	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7
160°	883.4	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6
162.5°	897.1	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4
165°	915.3	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2
167.5°	930.8	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8
170°	939.1	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1
172.5°	945.0	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0
175°	951.7	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7
177.5°	955.1	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4	1706.4
2.5°	1701.4	1703.8	1706.2	1707.3	1707.1	1706.8	1706.6	1706.4
5°	1692.9	1695.6	1698.3	1699.5	1699.2	1698.9	1698.6	1698.3
7.5°	1675.7	1678.4	1681.0	1682.2	1681.9	1681.6	1681.3	1681.0
10°	1661.2	1663.6	1666.0	1667.1	1666.8	1666.5	1666.2	1665.9
12.5°	1641.9	1643.8	1645.7	1646.7	1646.6	1646.5	1646.5	1646.4
15°	1608.1	1609.6	1611.1	1611.9	1611.9	1611.9	1611.9	1611.9
17.5°	1568.9	1570.7	1572.6	1572.8	1571.3	1569.8	1568.3	1566.8
20°	1539.1	1541.2	1543.3	1543.6	1542.1	1540.6	1539.1	1537.6
22.5°	1505.3	1506.7	1508.0	1508.2	1507.2	1506.2	1505.2	1504.1
25°	1451.1	1451.7	1452.3	1452.1	1451.2	1450.3	1449.4	1448.5
27.5°	1394.2	1394.3	1394.5	1394.1	1393.2	1392.3	1391.4	1390.5
30°	1352.8	1352.2	1351.6	1350.9	1350.0	1349.1	1348.2	1347.3
32.5°	1310.8	1309.7	1308.7	1307.3	1305.7	1304.1	1302.4	1300.8
35°	1245.7	1244.2	1242.7	1240.8	1238.4	1236.0	1233.6	1231.2
37.5°	1177.3	1175.1	1172.9	1171.1	1169.7	1168.3	1166.9	1165.6
40°	1129.9	1127.2	1124.5	1122.7	1121.8	1120.9	1120.0	1119.1
42.5°	1082.9	1080.4	1078.0	1076.0	1074.7	1073.3	1071.9	1070.5
45°	1013.4	1009.8	1006.2	1003.9	1003.0	1002.1	1001.2	1000.3
47.5°	940.1	936.4	932.8	929.9	927.8	925.7	923.6	921.5
50°	889.9	886.0	882.1	879.1	877.0	874.9	872.8	870.7
52.5°	841.2	837.8	834.4	831.5	829.1	826.8	824.5	822.1
55°	765.4	762.7	760.0	757.6	755.5	753.4	751.3	749.2
57.5°	690.2	686.7	683.2	680.9	679.8	678.6	677.5	676.3
60°	639.3	636.3	633.3	630.7	628.6	626.5	624.4	622.3
62.5°	590.2	587.0	583.7	581.3	579.7	578.1	576.4	574.8
65°	513.0	510.3	507.6	505.6	504.4	503.2	502.0	500.8
67.5°	439.3	437.0	434.7	433.2	432.5	431.8	431.1	430.4
70°	390.6	388.8	387.0	385.5	384.3	383.1	381.9	380.7
72.5°	344.8	342.7	340.7	339.1	337.9	336.7	335.5	334.3
75°	273.6	272.7	271.8	270.7	269.5	268.3	267.1	265.9
77.5°	208.4	207.9	207.4	206.7	205.8	205.0	204.1	203.3
80°	166.8	166.5	166.2	165.7	165.1	164.5	163.9	163.3
82.5°	127.4	126.9	126.4	126.0	125.9	125.8	125.7	125.5
85°	75.0	74.7	74.4	73.9	73.3	72.7	72.1	71.5
87.5°	30.8	30.9	31.1	31.0	30.6	30.2	29.9	29.5
90°	13.5	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	30.7	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	59.5	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	93.2	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	116.5	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	140.6	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	179.4	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.3	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.4	250.9	251.4	251.6	251.4	251.2	251.1	250.9



TEST NUMBER: P333441

CATALOG NUMBER: S125DIW-S1090D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.6	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	324.1	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.6	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	428.1	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.5	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.6	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	543.1	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.4	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.4	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.2	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.4	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	774.6	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	815.6	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	843.9	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	868.4	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.2	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.2	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	915.9	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	929.8	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	938.1	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	944.0	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	950.7	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	953.7	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)