

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333369-927

Luminaire Tested: **S125DIW-S375D1560U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333369-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S375D1560U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5491.5 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	89	89	89	89	68	68	68	48	48	48	30	30	30	22
1	91	87	84	80	81	78	74	72	59	57	55	42	41	40	27	26	26	18
2	83	76	70	65	74	68	63	59	52	48	46	37	35	33	23	22	21	15
3	76	67	60	54	67	59	54	49	46	42	38	33	30	28	21	19	18	13
4	69	59	51	46	61	53	46	41	40	36	32	29	26	24	19	17	16	11
5	63	52	45	39	56	47	40	35	36	31	28	26	23	21	17	15	14	10
6	58	47	39	34	51	42	35	30	32	28	24	23	20	18	15	13	12	9
7	54	42	34	29	47	38	31	26	29	24	21	21	18	16	14	12	11	8
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	13	11	9	7
9	46	35	27	23	41	31	25	20	24	20	16	18	15	12	12	10	8	6
10	43	31	25	20	38	28	22	18	22	18	15	16	13	11	11	9	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2989	2989	2989
5°	2995	2967	2986
10°	2977	2946	2963
15°	2945	2910	2923
20°	2899	2861	2866
25°	2849	2802	2799
30°	2788	2738	2725
35°	2722	2670	2633
40°	2655	2596	2559
45°	2582	2528	2478
50°	2502	2446	2372
55°	2423	2354	2288
60°	2331	2260	2180
65°	2222	2149	2077
70°	2115	2019	1949
75°	1926	1864	1799
80°	1715	1689	1648
85°	1489	1519	1438



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.6	0.8
10°-20°	123.3	2.2
20°-30°	182.0	3.3
30°-40°	212.4	3.9
40°-50°	213.3	3.9
50°-60°	187.2	3.4
60°-70°	139.5	2.5
70°-80°	79.8	1.5
80°-90°	26.6	0.5
90°-100°	102.8	1.9
100°-110°	303.6	5.5
110°-120°	514.3	9.4
120°-130°	676.9	12.3
130°-140°	758.4	13.8
140°-150°	743.3	13.5
150°-160°	624.3	11.4
160°-170°	415.0	7.6
170°-180°	145.2	2.6
0°-30°	348.9	6.4
0°-40°	561.2	10.2
0°-60°	961.7	17.5
0°-90°	1207.5	22.0
90°-120°	920.8	16.8
90°-150°	3099.4	56.4
90°-180°	4284.0	78.0
0°-180°	5491.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	463	463	463	463	463	
5°	462	461	458	461	461	44
15°	440	439	435	437	437	124
25°	400	398	393	394	393	184
35°	345	344	339	337	334	216
45°	283	281	277	273	271	218
55°	215	214	209	206	203	192
65°	145	144	141	137	136	144
75°	77	76	75	74	72	82
85°	20	20	20	20	19	23
90°	1	11	19	25	29	5
95°	78	81	92	100	103	83
105°	272	278	286	292	296	291
115°	515	520	522	521	520	509
125°	752	758	760	758	756	673
135°	977	984	986	985	981	753
145°	1184	1189	1192	1192	1189	740
155°	1355	1355	1356	1360	1355	624
165°	1473	1471	1472	1476	1470	415
175°	1532	1527	1527	1533	1526	145
180°	1535	1535	1535	1535	1535	



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	463.9	463.7	463.6	463.3	463.2	462.7	462.1	461.4	460.8	460.1	460.8
5°	462.0	461.8	461.7	461.5	461.4	460.9	460.1	459.3	458.4	457.6	458.4
7.5°	457.8	457.6	457.5	457.3	457.2	456.6	455.7	454.8	453.9	453.0	453.8
10°	454.0	453.8	453.7	453.5	453.4	452.8	451.9	451.0	450.1	449.2	449.9
12.5°	449.3	449.0	448.7	448.5	448.1	447.6	446.7	445.9	445.0	444.3	444.7
15°	440.5	440.2	440.0	439.7	439.4	438.9	438.0	437.1	436.2	435.3	435.7
17.5°	430.2	429.9	429.5	429.2	428.8	428.2	427.2	426.4	425.4	424.5	425.0
20°	421.8	421.6	421.4	421.3	421.1	420.5	419.5	418.4	417.3	416.3	416.8
22.5°	413.3	413.0	412.6	412.4	412.1	411.5	410.4	409.5	408.4	407.5	407.9
25°	399.8	399.4	398.9	398.5	398.2	397.4	396.4	395.3	394.3	393.2	393.4
27.5°	384.0	383.8	383.6	383.3	383.1	382.4	381.4	380.2	379.1	378.0	378.1
30°	373.8	373.6	373.3	373.0	372.8	372.1	370.9	369.6	368.4	367.2	367.0
32.5°	362.7	362.3	361.9	361.6	361.2	360.4	359.3	358.2	357.2	356.1	355.8
35°	345.2	344.9	344.6	344.3	344.0	343.2	342.1	341.0	339.8	338.7	338.3
37.5°	327.2	326.8	326.4	325.9	325.5	324.8	323.7	322.7	321.5	320.5	319.9
40°	314.9	314.4	314.0	313.6	313.2	312.4	311.3	310.2	309.0	307.9	307.2
42.5°	301.7	301.3	301.0	300.6	300.3	299.6	298.4	297.3	296.1	295.0	294.4
45°	282.7	282.3	282.0	281.7	281.3	280.7	279.7	278.8	277.7	276.8	275.8
47.5°	262.1	262.1	262.1	262.2	262.2	261.7	260.5	259.3	258.1	256.9	256.0
50°	249.0	248.7	248.5	248.2	248.0	247.4	246.4	245.4	244.5	243.4	242.4
52.5°	235.5	235.3	235.1	235.0	234.8	234.2	233.1	232.1	231.0	230.0	229.1
55°	215.2	215.0	214.8	214.5	214.3	213.6	212.5	211.4	210.2	209.1	208.3
57.5°	194.0	193.8	193.7	193.6	193.5	192.9	191.9	191.0	190.0	189.1	188.1
60°	180.5	180.1	179.8	179.5	179.2	178.6	177.7	176.8	175.9	175.0	174.2
62.5°	166.4	166.2	165.9	165.6	165.4	164.9	164.1	163.3	162.6	161.8	161.0
65°	145.4	145.2	145.0	144.9	144.7	144.2	143.3	142.4	141.5	140.6	139.8
67.5°	124.9	124.6	124.2	123.9	123.6	123.0	122.4	121.7	121.0	120.4	119.8
70°	112.0	111.6	111.2	110.8	110.4	109.8	109.1	108.4	107.7	106.9	106.4
72.5°	98.0	97.7	97.4	97.1	96.9	96.5	96.0	95.5	95.1	94.6	94.0
75°	77.2	77.1	76.9	76.8	76.6	76.3	75.9	75.5	75.1	74.7	74.5
77.5°	58.1	58.1	58.0	57.9	57.9	57.8	57.5	57.3	57.0	56.8	56.6
80°	46.1	46.1	46.1	46.1	46.1	46.0	45.9	45.7	45.6	45.4	45.3
82.5°	35.6	35.5	35.3	35.2	35.1	35.0	34.9	34.9	34.9	34.9	34.7
85°	20.1	20.2	20.3	20.4	20.4	20.5	20.5	20.5	20.5	20.5	20.4
87.5°	8.2	8.6	9.0	9.4	9.8	10.2	10.5	10.9	11.2	11.4	11.7
90°	1.2	3.3	5.5	7.6	9.7	11.6	13.5	15.4	17.3	19.1	20.4
92.5°	28.9	30.4	31.9	33.4	34.9	36.8	39.1	41.3	43.6	45.9	47.6
95°	77.6	78.2	78.7	79.2	79.8	81.4	84.1	86.7	89.4	92.0	93.9
97.5°	129.0	129.2	129.4	129.7	129.9	131.8	135.5	139.2	142.8	146.5	148.2
100°	167.2	167.2	167.2	167.2	167.2	169.0	172.5	175.9	179.4	182.8	185.2
102.5°	208.3	209.5	210.5	211.5	212.6	214.0	215.8	217.5	219.3	221.0	223.6
105°	272.4	273.7	275.0	276.4	277.7	279.2	280.7	282.3	283.9	285.6	287.2
107.5°	343.1	344.4	345.8	347.1	348.4	349.7	350.9	352.1	353.4	354.6	355.4
110°	391.9	393.2	394.5	395.9	397.2	398.2	399.0	399.8	400.6	401.4	402.2



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	441.6	442.3	443.0	443.6	444.3	445.2	446.2	447.2	448.2	449.2	449.6
115°	514.9	516.0	517.1	518.1	519.2	520.0	520.5	521.0	521.6	522.1	521.8
117.5°	588.5	589.0	589.5	589.9	590.4	590.9	591.4	591.8	592.3	592.9	593.0
120°	634.4	635.7	637.1	638.4	639.7	640.5	640.8	641.0	641.3	641.6	641.6
122.5°	684.1	684.6	685.1	685.6	686.0	686.6	687.3	688.0	688.6	689.4	689.1
125°	751.5	753.0	754.7	756.3	757.9	758.8	759.1	759.3	759.6	759.9	759.3
127.5°	823.2	824.1	825.0	825.9	826.8	827.4	827.8	828.1	828.4	828.7	828.4
130°	866.2	867.5	868.9	870.1	871.5	872.4	873.0	873.5	874.0	874.6	874.3
132.5°	909.2	911.4	913.5	915.8	917.9	918.9	918.9	918.7	918.6	918.5	918.2
135°	977.3	978.9	980.5	982.1	983.7	984.6	984.8	985.2	985.4	985.6	985.6
137.5°	1041.3	1042.9	1044.4	1045.9	1047.5	1048.5	1049.2	1049.7	1050.3	1050.9	1051.2
140°	1082.4	1083.8	1085.1	1086.4	1087.7	1088.8	1089.6	1090.4	1091.2	1092.0	1092.5
142.5°	1123.6	1124.7	1125.8	1126.9	1128.0	1129.0	1130.0	1131.1	1132.1	1133.1	1133.4
145°	1184.0	1185.0	1186.1	1187.2	1188.3	1189.1	1189.9	1190.7	1191.5	1192.3	1192.3
147.5°	1239.9	1240.5	1241.0	1241.7	1242.2	1242.9	1243.5	1244.1	1244.8	1245.4	1246.0
150°	1277.2	1276.9	1276.7	1276.4	1276.1	1276.5	1277.6	1278.7	1279.7	1280.8	1280.8
152.5°	1307.7	1308.1	1308.5	1308.8	1309.2	1309.6	1310.1	1310.5	1310.9	1311.4	1312.0
155°	1354.9	1354.9	1354.9	1354.9	1354.9	1354.9	1355.3	1355.5	1355.7	1356.1	1357.1
157.5°	1396.9	1396.3	1395.7	1395.1	1394.6	1394.4	1394.6	1395.0	1395.2	1395.4	1396.5
160°	1421.7	1420.9	1420.1	1419.4	1418.6	1418.3	1418.6	1418.8	1419.1	1419.4	1420.4
162.5°	1443.8	1443.1	1442.6	1442.0	1441.4	1441.1	1441.1	1441.2	1441.3	1441.3	1442.6
165°	1473.1	1472.6	1472.0	1471.6	1471.0	1470.8	1471.2	1471.4	1471.6	1472.0	1473.0
167.5°	1497.9	1496.9	1495.9	1494.8	1493.7	1493.2	1493.2	1493.2	1493.2	1493.2	1494.8
170°	1511.3	1510.3	1509.2	1508.2	1507.1	1506.6	1506.6	1506.6	1506.6	1506.6	1508.2
172.5°	1520.9	1519.9	1518.8	1517.7	1516.6	1516.2	1516.2	1516.2	1516.2	1516.2	1517.7
175°	1531.7	1530.6	1529.5	1528.4	1527.4	1526.9	1526.9	1526.9	1526.9	1526.9	1528.4
177.5°	1537.2	1536.3	1535.5	1534.6	1533.7	1533.2	1533.0	1532.8	1532.6	1532.4	1533.7
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	462.8	462.8	462.8	462.8	462.8	462.8	462.8	462.8
2.5°	461.4	462.1	462.7	463.0	463.0	462.9	462.9	462.8
5°	459.1	459.9	460.6	460.9	460.8	460.7	460.7	460.6
7.5°	454.5	455.2	455.9	456.2	456.1	456.1	456.0	455.9
10°	450.5	451.1	451.9	452.1	452.0	451.9	451.9	451.8
12.5°	445.3	445.8	446.3	446.6	446.6	446.6	446.6	446.5
15°	436.1	436.5	437.0	437.1	437.1	437.1	437.1	437.1
17.5°	425.5	426.0	426.5	426.5	426.1	425.7	425.3	424.9
20°	417.4	418.0	418.5	418.7	418.2	417.8	417.4	417.0
22.5°	408.2	408.6	409.0	409.0	408.8	408.4	408.2	407.9
25°	393.6	393.7	393.9	393.8	393.6	393.3	393.1	392.8
27.5°	378.1	378.1	378.2	378.1	377.8	377.6	377.3	377.1
30°	366.9	366.7	366.5	366.4	366.1	365.9	365.6	365.4
32.5°	355.5	355.2	354.9	354.6	354.1	353.6	353.2	352.8
35°	337.9	337.5	337.0	336.5	335.9	335.2	334.5	333.9
37.5°	319.3	318.7	318.1	317.6	317.2	316.9	316.5	316.1
40°	306.4	305.7	305.0	304.5	304.3	304.0	303.7	303.5
42.5°	293.7	293.0	292.3	291.8	291.4	291.0	290.7	290.3
45°	274.8	273.9	272.9	272.3	272.0	271.8	271.6	271.3
47.5°	254.9	254.0	252.9	252.2	251.6	251.0	250.5	249.9
50°	241.4	240.3	239.2	238.4	237.8	237.3	236.7	236.1
52.5°	228.1	227.2	226.2	225.5	224.9	224.3	223.6	223.0
55°	207.6	206.8	206.1	205.5	204.9	204.3	203.7	203.2
57.5°	187.2	186.2	185.3	184.7	184.3	184.0	183.7	183.4
60°	173.4	172.5	171.7	171.0	170.5	169.9	169.4	168.8
62.5°	160.1	159.1	158.3	157.6	157.2	156.8	156.3	155.9
65°	139.1	138.4	137.7	137.1	136.8	136.5	136.2	135.9
67.5°	119.1	118.5	117.9	117.5	117.3	117.1	116.9	116.7
70°	105.9	105.4	105.0	104.6	104.3	103.9	103.5	103.2
72.5°	93.5	92.9	92.4	92.0	91.7	91.3	90.9	90.6
75°	74.2	74.0	73.7	73.4	73.1	72.8	72.5	72.1
77.5°	56.6	56.4	56.2	56.1	55.8	55.6	55.4	55.1
80°	45.2	45.2	45.1	44.9	44.8	44.6	44.4	44.3
82.5°	34.5	34.4	34.3	34.1	34.1	34.1	34.1	34.1
85°	20.4	20.3	20.2	20.0	19.9	19.7	19.6	19.4
87.5°	12.0	12.2	12.5	12.7	12.7	12.7	12.8	12.8
90°	21.8	23.1	24.4	25.5	26.3	27.1	27.9	28.7
92.5°	49.4	51.1	52.9	54.0	54.7	55.2	55.8	56.4
95°	95.7	97.6	99.4	100.6	101.2	101.7	102.2	102.7
97.5°	150.0	151.7	153.4	154.6	154.9	155.2	155.5	155.8
100°	187.6	190.0	192.3	193.8	194.3	194.9	195.4	195.9
102.5°	226.2	228.9	231.4	233.1	233.9	234.6	235.4	236.1
105°	288.8	290.3	291.9	293.1	293.9	294.7	295.5	296.3
107.5°	356.2	357.0	357.7	358.1	358.1	358.1	358.0	357.9
110°	403.1	403.9	404.6	404.9	404.6	404.3	404.1	403.9



TEST NUMBER: P333369-927

CATALOG NUMBER: S125DIW-S375D1560U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	450.0	450.4	450.7	450.7	450.2	449.7	449.2	448.8
115°	521.6	521.3	521.0	520.8	520.5	520.2	520.0	519.8
117.5°	593.3	593.5	593.7	593.3	592.2	591.1	590.1	589.0
120°	641.6	641.6	641.6	641.0	640.0	638.9	637.9	636.8
122.5°	689.0	688.7	688.5	688.0	687.1	686.3	685.4	684.6
125°	758.8	758.3	757.7	757.3	757.1	756.8	756.5	756.3
127.5°	828.1	827.9	827.6	827.2	826.6	826.2	825.6	825.1
130°	874.0	873.8	873.5	873.1	872.6	872.0	871.5	871.0
132.5°	918.0	917.7	917.4	917.0	916.2	915.4	914.7	913.9
135°	985.6	985.6	985.6	985.2	984.0	983.0	981.9	980.9
137.5°	1051.5	1051.9	1052.2	1051.7	1050.4	1049.0	1047.7	1046.3
140°	1093.1	1093.6	1094.1	1093.7	1092.4	1091.1	1089.7	1088.4
142.5°	1133.7	1134.0	1134.4	1133.9	1132.5	1131.2	1129.9	1128.5
145°	1192.3	1192.3	1192.3	1191.9	1191.1	1190.3	1189.5	1188.7
147.5°	1246.7	1247.3	1247.9	1247.4	1245.5	1243.7	1242.0	1240.2
150°	1280.8	1280.8	1280.8	1280.5	1279.9	1279.5	1278.9	1278.3
152.5°	1312.6	1313.3	1313.9	1313.8	1312.8	1311.9	1310.9	1310.0
155°	1358.1	1359.2	1360.3	1360.2	1358.8	1357.5	1356.1	1354.9
157.5°	1397.6	1398.7	1399.7	1399.4	1397.6	1395.8	1394.1	1392.3
160°	1421.5	1422.5	1423.6	1423.5	1422.1	1420.8	1419.5	1418.2
162.5°	1443.9	1445.2	1446.4	1446.3	1444.8	1443.2	1441.7	1440.1
165°	1474.0	1475.1	1476.2	1475.9	1474.3	1472.7	1471.2	1469.5
167.5°	1496.4	1497.9	1499.5	1499.5	1497.9	1496.3	1494.6	1492.9
170°	1509.7	1511.3	1512.9	1512.8	1510.9	1509.1	1507.2	1505.4
172.5°	1519.3	1520.9	1522.5	1522.5	1520.8	1519.2	1517.5	1515.9
175°	1530.1	1531.7	1533.3	1533.1	1531.3	1529.4	1527.6	1525.7
177.5°	1534.9	1536.2	1537.5	1537.4	1535.9	1534.4	1532.9	1531.4
180°	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2	1535.2

(END OF REPORT)