

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333473

Luminaire Tested: **S125DIW-S1270D1050U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333473
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1050U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8818.5 lumens
Efficiency: N/A
Efficacy: 130.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333473
CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	88	93	90	86	83	78	75	73	67	65	64	57	56	55	50
2	91	84	78	73	85	79	73	69	68	64	61	59	56	54	51	48	47	42
3	83	74	67	61	78	69	63	58	61	56	51	53	49	46	45	42	40	36
4	76	66	58	52	71	62	55	49	54	48	44	47	43	39	40	37	34	31
5	70	59	50	44	65	55	48	42	48	43	38	42	38	34	36	33	30	27
6	65	53	44	39	60	50	42	37	44	38	33	38	34	30	33	29	27	24
7	60	48	40	34	56	45	38	32	40	34	29	35	30	27	30	26	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	19
9	52	40	32	27	48	37	30	26	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	28	23	31	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	2.0
10°-20°	526.4	6.0
20°-30°	854.8	9.7
30°-40°	1042.7	11.8
40°-50°	948.5	10.8
50°-60°	755.5	8.6
60°-70°	526.2	6.0
70°-80°	280.6	3.2
80°-90°	73.7	0.8
90°-100°	87.2	1.0
100°-110°	257.5	2.9
110°-120°	436.2	4.9
120°-130°	574.0	6.5
130°-140°	643.2	7.3
140°-150°	630.4	7.1
150°-160°	529.5	6.0
160°-170°	352.0	4.0
170°-180°	123.2	1.4
0°-30°	1558.0	17.7
0°-40°	2600.7	29.5
0°-60°	4304.7	48.8
0°-90°	5185.3	58.8
90°-120°	780.9	8.9
90°-150°	2628.6	29.8
90°-180°	3633.0	41.2
0°-180°	8818.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	24	1	24	1	24	16
95°	87	66	87	66	87	89
105°	251	231	251	231	251	266
115°	441	437	441	437	441	436
125°	641	637	641	637	641	573
135°	832	829	832	829	832	642
145°	1008	1004	1008	1004	1008	629
155°	1149	1149	1149	1149	1149	529
165°	1246	1249	1246	1249	1246	351
175°	1294	1299	1294	1299	1294	123
180°	1302	1302	1302	1302	1302	



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	19.8	20.9	21.4	21.3	21.8	21.6	23.9	23.6	25.3	26.9	29.1
90°	24.3	23.6	23.0	22.3	21.6	20.7	19.6	18.5	17.3	16.2	14.6
92.5°	47.8	47.3	46.8	46.3	45.8	44.9	43.4	41.9	40.4	38.9	37.0
95°	87.1	86.7	86.2	85.8	85.3	84.3	82.7	81.2	79.6	78.0	75.8
97.5°	132.1	131.9	131.6	131.3	131.0	130.2	128.7	127.2	125.7	124.2	121.1
100°	166.2	165.7	165.3	164.8	164.4	163.1	161.1	159.1	157.1	155.0	152.1
102.5°	200.2	199.6	199.0	198.3	197.7	196.3	194.1	191.9	189.7	187.5	186.0
105°	251.3	250.6	249.9	249.3	248.6	247.6	246.2	244.9	243.5	242.2	240.8
107.5°	303.6	303.6	303.7	303.7	303.8	303.4	302.8	302.1	301.4	300.7	299.7
110°	342.5	342.7	342.9	343.2	343.4	343.2	342.5	341.8	341.1	340.5	339.8



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	380.6	381.0	381.4	381.8	382.2	382.2	381.9	381.6	381.3	381.0	380.1
115°	440.8	441.0	441.2	441.4	441.7	441.9	442.1	442.3	442.6	442.8	442.3
117.5°	499.5	500.4	501.3	502.2	503.1	503.5	503.3	503.1	503.0	502.8	502.4
120°	540.1	541.0	541.9	542.8	543.7	544.1	544.1	544.1	544.1	544.1	543.9
122.5°	580.6	581.3	582.0	582.8	583.5	583.9	584.1	584.3	584.5	584.7	584.1
125°	641.4	641.6	641.8	642.1	642.3	642.6	643.1	643.5	644.0	644.4	644.2
127.5°	699.8	700.2	700.7	701.1	701.6	701.9	702.1	702.3	702.6	702.8	702.5
130°	738.7	739.1	739.6	740.0	740.5	740.8	741.0	741.3	741.5	741.7	741.3
132.5°	775.1	775.8	776.4	777.0	777.7	778.1	778.3	778.5	778.8	779.0	779.1
135°	831.9	832.8	833.7	834.6	835.5	835.9	835.9	835.9	835.9	835.9	835.7
137.5°	887.4	888.5	889.7	890.8	891.9	892.3	892.1	891.8	891.5	891.3	890.8
140°	923.1	924.2	925.3	926.5	927.6	927.9	927.5	927.0	926.6	926.1	925.4
142.5°	957.1	958.3	959.4	960.5	961.6	962.1	961.8	961.5	961.2	961.0	960.1
145°	1008.2	1008.9	1009.5	1010.2	1010.9	1011.2	1011.2	1011.2	1011.2	1011.2	1010.6
147.5°	1051.8	1053.3	1054.8	1056.4	1057.9	1058.4	1057.8	1057.3	1056.8	1056.2	1055.7
150°	1084.2	1084.6	1085.1	1085.5	1086.0	1086.2	1086.2	1086.2	1086.2	1086.2	1085.3
152.5°	1110.9	1111.7	1112.6	1113.4	1114.2	1114.3	1113.8	1113.2	1112.7	1112.2	1111.8
155°	1149.0	1150.2	1151.3	1152.4	1153.5	1153.7	1152.8	1151.9	1151.0	1150.1	1149.8
157.5°	1180.9	1182.3	1183.8	1185.3	1186.8	1187.1	1186.2	1185.3	1184.4	1183.5	1183.3
160°	1202.7	1203.9	1205.0	1206.1	1207.2	1207.4	1206.5	1205.6	1204.7	1203.8	1203.5
162.5°	1221.4	1222.7	1224.0	1225.3	1226.6	1226.7	1225.6	1224.6	1223.5	1222.4	1222.4
165°	1246.3	1247.7	1249.0	1250.4	1251.7	1251.9	1251.0	1250.1	1249.2	1248.3	1248.1
167.5°	1266.2	1267.6	1269.0	1270.4	1271.8	1271.8	1270.4	1269.1	1267.7	1266.4	1266.4
170°	1276.7	1278.3	1279.9	1281.4	1283.0	1283.1	1281.8	1280.4	1279.1	1277.7	1277.7
172.5°	1285.6	1287.0	1288.4	1289.8	1291.2	1291.2	1289.9	1288.5	1287.2	1285.8	1285.8
175°	1293.9	1295.5	1297.1	1298.7	1300.2	1300.4	1299.0	1297.6	1296.3	1294.9	1294.9
177.5°	1298.8	1300.1	1301.3	1302.6	1303.8	1303.9	1302.9	1301.8	1300.7	1299.6	1299.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	30.1	28.5	25.7	23.5	20.0	17.8	16.8	17.0	15.5	15.3	16.3
90°	13.1	11.5	9.9	8.2	6.4	4.6	2.8	1.0	2.8	4.6	6.4
92.5°	35.0	33.1	31.2	29.6	28.3	27.0	25.8	24.5	25.8	27.0	28.3
95°	73.5	71.3	69.0	67.7	67.2	66.8	66.3	65.9	66.3	66.8	67.2
97.5°	118.0	114.9	111.8	110.2	110.0	109.8	109.6	109.4	109.6	109.8	110.0
100°	149.2	146.2	143.3	141.9	141.9	141.9	141.9	141.9	141.9	141.9	141.9
102.5°	184.5	183.0	181.5	180.3	179.4	178.5	177.6	176.7	177.6	178.5	179.4
105°	239.5	238.1	236.8	235.5	234.4	233.3	232.1	231.0	232.1	233.3	234.4
107.5°	298.7	297.6	296.6	295.5	294.4	293.3	292.1	291.0	292.1	293.3	294.4
110°	339.1	338.4	337.8	336.9	335.7	334.6	333.5	332.3	333.5	334.6	335.7



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	379.3	378.4	377.6	376.8	376.3	375.7	375.1	374.5	375.1	375.7	376.3
115°	441.9	441.4	441.0	440.3	439.4	438.5	437.6	436.7	437.6	438.5	439.4
117.5°	502.0	501.6	501.2	500.8	500.3	499.9	499.5	499.1	499.5	499.9	500.3
120°	543.7	543.4	543.2	542.5	541.4	540.3	539.2	538.0	539.2	540.3	541.4
122.5°	583.5	582.9	582.3	581.8	581.4	581.0	580.6	580.2	580.6	581.0	581.4
125°	644.0	643.8	643.5	642.7	641.4	640.0	638.7	637.3	638.7	640.0	641.4
127.5°	702.3	702.0	701.7	701.2	700.4	699.7	698.9	698.1	698.9	699.7	700.4
130°	740.8	740.4	739.9	739.1	738.0	736.9	735.7	734.6	735.7	736.9	738.0
132.5°	779.2	779.3	779.4	778.5	776.6	774.8	772.9	771.1	772.9	774.8	776.6
135°	835.5	835.3	835.0	834.3	832.9	831.5	830.2	828.8	830.2	831.5	832.9
137.5°	890.3	889.8	889.3	888.4	887.1	885.8	884.5	883.2	884.5	885.8	887.1
140°	924.8	924.1	923.4	922.5	921.4	920.3	919.1	918.0	919.1	920.3	921.4
142.5°	959.3	958.4	957.6	956.7	955.7	954.8	953.8	952.9	953.8	954.8	955.7
145°	1009.9	1009.2	1008.5	1007.7	1006.8	1005.9	1005.0	1004.1	1005.0	1005.9	1006.8
147.5°	1055.1	1054.6	1054.1	1053.5	1053.0	1052.6	1052.1	1051.6	1052.1	1052.6	1053.0
150°	1084.4	1083.5	1082.6	1082.3	1082.5	1082.7	1083.0	1083.2	1083.0	1082.7	1082.5
152.5°	1111.4	1111.1	1110.7	1110.4	1110.1	1109.7	1109.4	1109.1	1109.4	1109.7	1110.1
155°	1149.6	1149.4	1149.1	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0	1149.0
157.5°	1183.0	1182.8	1182.6	1182.7	1183.2	1183.7	1184.2	1184.7	1184.2	1183.7	1183.2
160°	1203.3	1203.1	1202.9	1203.1	1203.8	1204.4	1205.1	1205.8	1205.1	1204.4	1203.8
162.5°	1222.3	1222.3	1222.2	1222.4	1222.9	1223.4	1223.9	1224.4	1223.9	1223.4	1222.9
165°	1247.9	1247.7	1247.4	1247.5	1248.0	1248.4	1248.9	1249.4	1248.9	1248.4	1248.0
167.5°	1266.4	1266.4	1266.4	1266.8	1267.7	1268.6	1269.5	1270.4	1269.5	1268.6	1267.7
170°	1277.7	1277.7	1277.7	1278.2	1279.1	1280.0	1280.9	1281.8	1280.9	1280.0	1279.1
172.5°	1285.8	1285.8	1285.8	1286.3	1287.2	1288.1	1289.0	1289.9	1289.0	1288.1	1287.2
175°	1294.9	1294.9	1294.9	1295.4	1296.3	1297.2	1298.1	1299.0	1298.1	1297.2	1296.3
177.5°	1300.0	1300.1	1300.3	1300.8	1301.5	1302.2	1302.9	1303.7	1302.9	1302.2	1301.5
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	17.2	18.8	18.5	19.4	19.8	21.3	20.9	23.6	25.1	26.6	26.1
90°	8.2	9.9	11.5	13.1	14.6	16.2	17.3	18.5	19.6	20.7	21.6
92.5°	29.6	31.2	33.1	35.0	37.0	38.9	40.4	41.9	43.4	44.9	45.8
95°	67.7	69.0	71.3	73.5	75.8	78.0	79.6	81.2	82.7	84.3	85.3
97.5°	110.2	111.8	114.9	118.0	121.1	124.2	125.7	127.2	128.7	130.2	131.0
100°	141.9	143.3	146.2	149.2	152.1	155.0	157.1	159.1	161.1	163.1	164.4
102.5°	180.3	181.5	183.0	184.5	186.0	187.5	189.7	191.9	194.1	196.3	197.7
105°	235.5	236.8	238.1	239.5	240.8	242.2	243.5	244.9	246.2	247.6	248.6
107.5°	295.5	296.6	297.6	298.7	299.7	300.7	301.4	302.1	302.8	303.4	303.8
110°	336.9	337.8	338.4	339.1	339.8	340.5	341.1	341.8	342.5	343.2	343.4



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	376.8	377.6	378.4	379.3	380.1	381.0	381.3	381.6	381.9	382.2	382.2
115°	440.3	441.0	441.4	441.9	442.3	442.8	442.6	442.3	442.1	441.9	441.7
117.5°	500.8	501.2	501.6	502.0	502.4	502.8	503.0	503.1	503.3	503.5	503.1
120°	542.5	543.2	543.4	543.7	543.9	544.1	544.1	544.1	544.1	544.1	543.7
122.5°	581.8	582.3	582.9	583.5	584.1	584.7	584.5	584.3	584.1	583.9	583.5
125°	642.7	643.5	643.8	644.0	644.2	644.4	644.0	643.5	643.1	642.6	642.3
127.5°	701.2	701.7	702.0	702.3	702.5	702.8	702.6	702.3	702.1	701.9	701.6
130°	739.1	739.9	740.4	740.8	741.3	741.7	741.5	741.3	741.0	740.8	740.5
132.5°	778.5	779.4	779.3	779.2	779.1	779.0	778.8	778.5	778.3	778.1	777.7
135°	834.3	835.0	835.3	835.5	835.7	835.9	835.9	835.9	835.9	835.9	835.5
137.5°	888.4	889.3	889.8	890.3	890.8	891.3	891.5	891.8	892.1	892.3	891.9
140°	922.5	923.4	924.1	924.8	925.4	926.1	926.6	927.0	927.5	927.9	927.6
142.5°	956.7	957.6	958.4	959.3	960.1	961.0	961.2	961.5	961.8	962.1	961.6
145°	1007.7	1008.5	1009.2	1009.9	1010.6	1011.2	1011.2	1011.2	1011.2	1011.2	1010.9
147.5°	1053.5	1054.1	1054.6	1055.1	1055.7	1056.2	1056.8	1057.3	1057.8	1058.4	1057.9
150°	1082.3	1082.6	1083.5	1084.4	1085.3	1086.2	1086.2	1086.2	1086.2	1086.2	1086.0
152.5°	1110.4	1110.7	1111.1	1111.4	1111.8	1112.2	1112.7	1113.2	1113.8	1114.3	1114.2
155°	1149.0	1149.1	1149.4	1149.6	1149.8	1150.1	1151.0	1151.9	1152.8	1153.7	1153.5
157.5°	1182.7	1182.6	1182.8	1183.0	1183.3	1183.5	1184.4	1185.3	1186.2	1187.1	1186.8
160°	1203.1	1202.9	1203.1	1203.3	1203.5	1203.8	1204.7	1205.6	1206.5	1207.4	1207.2
162.5°	1222.4	1222.2	1222.3	1222.3	1222.4	1222.4	1223.5	1224.6	1225.6	1226.7	1226.6
165°	1247.5	1247.4	1247.7	1247.9	1248.1	1248.3	1249.2	1250.1	1251.0	1251.9	1251.7
167.5°	1266.8	1266.4	1266.4	1266.4	1266.4	1266.4	1267.7	1269.1	1270.4	1271.8	1271.8
170°	1278.2	1277.7	1277.7	1277.7	1277.7	1277.7	1279.1	1280.4	1281.8	1283.1	1283.0
172.5°	1286.3	1285.8	1285.8	1285.8	1285.8	1285.8	1287.2	1288.5	1289.9	1291.2	1291.2
175°	1295.4	1294.9	1294.9	1294.9	1294.9	1294.9	1296.3	1297.6	1299.0	1300.4	1300.2
177.5°	1300.8	1300.3	1300.1	1300.0	1299.8	1299.6	1300.7	1301.8	1302.9	1303.9	1303.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	27.5	27.0	27.2	28.6	27.2	27.0	27.5	26.1	26.6	25.1	23.6
90°	22.3	23.0	23.6	24.3	23.6	23.0	22.3	21.6	20.7	19.6	18.5
92.5°	46.3	46.8	47.3	47.8	47.3	46.8	46.3	45.8	44.9	43.4	41.9
95°	85.8	86.2	86.7	87.1	86.7	86.2	85.8	85.3	84.3	82.7	81.2
97.5°	131.3	131.6	131.9	132.1	131.9	131.6	131.3	131.0	130.2	128.7	127.2
100°	164.8	165.3	165.7	166.2	165.7	165.3	164.8	164.4	163.1	161.1	159.1
102.5°	198.3	199.0	199.6	200.2	199.6	199.0	198.3	197.7	196.3	194.1	191.9
105°	249.3	249.9	250.6	251.3	250.6	249.9	249.3	248.6	247.6	246.2	244.9
107.5°	303.7	303.7	303.6	303.6	303.6	303.7	303.7	303.8	303.4	302.8	302.1
110°	343.2	342.9	342.7	342.5	342.7	342.9	343.2	343.4	343.2	342.5	341.8



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	381.8	381.4	381.0	380.6	381.0	381.4	381.8	382.2	382.2	381.9	381.6
115°	441.4	441.2	441.0	440.8	441.0	441.2	441.4	441.7	441.9	442.1	442.3
117.5°	502.2	501.3	500.4	499.5	500.4	501.3	502.2	503.1	503.5	503.3	503.1
120°	542.8	541.9	541.0	540.1	541.0	541.9	542.8	543.7	544.1	544.1	544.1
122.5°	582.8	582.0	581.3	580.6	581.3	582.0	582.8	583.5	583.9	584.1	584.3
125°	642.1	641.8	641.6	641.4	641.6	641.8	642.1	642.3	642.6	643.1	643.5
127.5°	701.1	700.7	700.2	699.8	700.2	700.7	701.1	701.6	701.9	702.1	702.3
130°	740.0	739.6	739.1	738.7	739.1	739.6	740.0	740.5	740.8	741.0	741.3
132.5°	777.0	776.4	775.8	775.1	775.8	776.4	777.0	777.7	778.1	778.3	778.5
135°	834.6	833.7	832.8	831.9	832.8	833.7	834.6	835.5	835.9	835.9	835.9
137.5°	890.8	889.7	888.5	887.4	888.5	889.7	890.8	891.9	892.3	892.1	891.8
140°	926.5	925.3	924.2	923.1	924.2	925.3	926.5	927.6	927.9	927.5	927.0
142.5°	960.5	959.4	958.3	957.1	958.3	959.4	960.5	961.6	962.1	961.8	961.5
145°	1010.2	1009.5	1008.9	1008.2	1008.9	1009.5	1010.2	1010.9	1011.2	1011.2	1011.2
147.5°	1056.4	1054.8	1053.3	1051.8	1053.3	1054.8	1056.4	1057.9	1058.4	1057.8	1057.3
150°	1085.5	1085.1	1084.6	1084.2	1084.6	1085.1	1085.5	1086.0	1086.2	1086.2	1086.2
152.5°	1113.4	1112.6	1111.7	1110.9	1111.7	1112.6	1113.4	1114.2	1114.3	1113.8	1113.2
155°	1152.4	1151.3	1150.2	1149.0	1150.2	1151.3	1152.4	1153.5	1153.7	1152.8	1151.9
157.5°	1185.3	1183.8	1182.3	1180.9	1182.3	1183.8	1185.3	1186.8	1187.1	1186.2	1185.3
160°	1206.1	1205.0	1203.9	1202.7	1203.9	1205.0	1206.1	1207.2	1207.4	1206.5	1205.6
162.5°	1225.3	1224.0	1222.7	1221.4	1222.7	1224.0	1225.3	1226.6	1226.7	1225.6	1224.6
165°	1250.4	1249.0	1247.7	1246.3	1247.7	1249.0	1250.4	1251.7	1251.9	1251.0	1250.1
167.5°	1270.4	1269.0	1267.6	1266.2	1267.6	1269.0	1270.4	1271.8	1271.8	1270.4	1269.1
170°	1281.4	1279.9	1278.3	1276.7	1278.3	1279.9	1281.4	1283.0	1283.1	1281.8	1280.4
172.5°	1289.8	1288.4	1287.0	1285.6	1287.0	1288.4	1289.8	1291.2	1291.2	1289.9	1288.5
175°	1298.7	1297.1	1295.5	1293.9	1295.5	1297.1	1298.7	1300.2	1300.4	1299.0	1297.6
177.5°	1302.6	1301.3	1300.1	1298.8	1300.1	1301.3	1302.6	1303.8	1303.9	1302.9	1301.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	20.9	21.3	19.8	19.4	18.5	18.8	17.2	16.3	15.3	15.5	17.0
90°	17.3	16.2	14.6	13.1	11.5	9.9	8.2	6.4	4.6	2.8	1.0
92.5°	40.4	38.9	37.0	35.0	33.1	31.2	29.6	28.3	27.0	25.8	24.5
95°	79.6	78.0	75.8	73.5	71.3	69.0	67.7	67.2	66.8	66.3	65.9
97.5°	125.7	124.2	121.1	118.0	114.9	111.8	110.2	110.0	109.8	109.6	109.4
100°	157.1	155.0	152.1	149.2	146.2	143.3	141.9	141.9	141.9	141.9	141.9
102.5°	189.7	187.5	186.0	184.5	183.0	181.5	180.3	179.4	178.5	177.6	176.7
105°	243.5	242.2	240.8	239.5	238.1	236.8	235.5	234.4	233.3	232.1	231.0
107.5°	301.4	300.7	299.7	298.7	297.6	296.6	295.5	294.4	293.3	292.1	291.0
110°	341.1	340.5	339.8	339.1	338.4	337.8	336.9	335.7	334.6	333.5	332.3



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	381.3	381.0	380.1	379.3	378.4	377.6	376.8	376.3	375.7	375.1	374.5
115°	442.6	442.8	442.3	441.9	441.4	441.0	440.3	439.4	438.5	437.6	436.7
117.5°	503.0	502.8	502.4	502.0	501.6	501.2	500.8	500.3	499.9	499.5	499.1
120°	544.1	544.1	543.9	543.7	543.4	543.2	542.5	541.4	540.3	539.2	538.0
122.5°	584.5	584.7	584.1	583.5	582.9	582.3	581.8	581.4	581.0	580.6	580.2
125°	644.0	644.4	644.2	644.0	643.8	643.5	642.7	641.4	640.0	638.7	637.3
127.5°	702.6	702.8	702.5	702.3	702.0	701.7	701.2	700.4	699.7	698.9	698.1
130°	741.5	741.7	741.3	740.8	740.4	739.9	739.1	738.0	736.9	735.7	734.6
132.5°	778.8	779.0	779.1	779.2	779.3	779.4	778.5	776.6	774.8	772.9	771.1
135°	835.9	835.9	835.7	835.5	835.3	835.0	834.3	832.9	831.5	830.2	828.8
137.5°	891.5	891.3	890.8	890.3	889.8	889.3	888.4	887.1	885.8	884.5	883.2
140°	926.6	926.1	925.4	924.8	924.1	923.4	922.5	921.4	920.3	919.1	918.0
142.5°	961.2	961.0	960.1	959.3	958.4	957.6	956.7	955.7	954.8	953.8	952.9
145°	1011.2	1011.2	1010.6	1009.9	1009.2	1008.5	1007.7	1006.8	1005.9	1005.0	1004.1
147.5°	1056.8	1056.2	1055.7	1055.1	1054.6	1054.1	1053.5	1053.0	1052.6	1052.1	1051.6
150°	1086.2	1086.2	1085.3	1084.4	1083.5	1082.6	1082.3	1082.5	1082.7	1083.0	1083.2
152.5°	1112.7	1112.2	1111.8	1111.4	1111.1	1110.7	1110.4	1110.1	1109.7	1109.4	1109.1
155°	1151.0	1150.1	1149.8	1149.6	1149.4	1149.1	1149.0	1149.0	1149.0	1149.0	1149.0
157.5°	1184.4	1183.5	1183.3	1183.0	1182.8	1182.6	1182.7	1183.2	1183.7	1184.2	1184.7
160°	1204.7	1203.8	1203.5	1203.3	1203.1	1202.9	1203.1	1203.8	1204.4	1205.1	1205.8
162.5°	1223.5	1222.4	1222.4	1222.3	1222.3	1222.2	1222.4	1222.9	1223.4	1223.9	1224.4
165°	1249.2	1248.3	1248.1	1247.9	1247.7	1247.4	1247.5	1248.0	1248.4	1248.9	1249.4
167.5°	1267.7	1266.4	1266.4	1266.4	1266.4	1266.4	1266.8	1267.7	1268.6	1269.5	1270.4
170°	1279.1	1277.7	1277.7	1277.7	1277.7	1277.7	1278.2	1279.1	1280.0	1280.9	1281.8
172.5°	1287.2	1285.8	1285.8	1285.8	1285.8	1285.8	1286.3	1287.2	1288.1	1289.0	1289.9
175°	1296.3	1294.9	1294.9	1294.9	1294.9	1294.9	1295.4	1296.3	1297.2	1298.1	1299.0
177.5°	1300.7	1299.6	1299.8	1300.0	1300.1	1300.3	1300.8	1301.5	1302.2	1302.9	1303.7
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.8	17.8	20.0	23.5	25.7	28.5	30.1	29.1	26.9	25.3	23.6
90°	2.8	4.6	6.4	8.2	9.9	11.5	13.1	14.6	16.2	17.3	18.5
92.5°	25.8	27.0	28.3	29.6	31.2	33.1	35.0	37.0	38.9	40.4	41.9
95°	66.3	66.8	67.2	67.7	69.0	71.3	73.5	75.8	78.0	79.6	81.2
97.5°	109.6	109.8	110.0	110.2	111.8	114.9	118.0	121.1	124.2	125.7	127.2
100°	141.9	141.9	141.9	141.9	143.3	146.2	149.2	152.1	155.0	157.1	159.1
102.5°	177.6	178.5	179.4	180.3	181.5	183.0	184.5	186.0	187.5	189.7	191.9
105°	232.1	233.3	234.4	235.5	236.8	238.1	239.5	240.8	242.2	243.5	244.9
107.5°	292.1	293.3	294.4	295.5	296.6	297.6	298.7	299.7	300.7	301.4	302.1
110°	333.5	334.6	335.7	336.9	337.8	338.4	339.1	339.8	340.5	341.1	341.8



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	375.1	375.7	376.3	376.8	377.6	378.4	379.3	380.1	381.0	381.3	381.6
115°	437.6	438.5	439.4	440.3	441.0	441.4	441.9	442.3	442.8	442.6	442.3
117.5°	499.5	499.9	500.3	500.8	501.2	501.6	502.0	502.4	502.8	503.0	503.1
120°	539.2	540.3	541.4	542.5	543.2	543.4	543.7	543.9	544.1	544.1	544.1
122.5°	580.6	581.0	581.4	581.8	582.3	582.9	583.5	584.1	584.7	584.5	584.3
125°	638.7	640.0	641.4	642.7	643.5	643.8	644.0	644.2	644.4	644.0	643.5
127.5°	698.9	699.7	700.4	701.2	701.7	702.0	702.3	702.5	702.8	702.6	702.3
130°	735.7	736.9	738.0	739.1	739.9	740.4	740.8	741.3	741.7	741.5	741.3
132.5°	772.9	774.8	776.6	778.5	779.4	779.3	779.2	779.1	779.0	778.8	778.5
135°	830.2	831.5	832.9	834.3	835.0	835.3	835.5	835.7	835.9	835.9	835.9
137.5°	884.5	885.8	887.1	888.4	889.3	889.8	890.3	890.8	891.3	891.5	891.8
140°	919.1	920.3	921.4	922.5	923.4	924.1	924.8	925.4	926.1	926.6	927.0
142.5°	953.8	954.8	955.7	956.7	957.6	958.4	959.3	960.1	961.0	961.2	961.5
145°	1005.0	1005.9	1006.8	1007.7	1008.5	1009.2	1009.9	1010.6	1011.2	1011.2	1011.2
147.5°	1052.1	1052.6	1053.0	1053.5	1054.1	1054.6	1055.1	1055.7	1056.2	1056.8	1057.3
150°	1083.0	1082.7	1082.5	1082.3	1082.6	1083.5	1084.4	1085.3	1086.2	1086.2	1086.2
152.5°	1109.4	1109.7	1110.1	1110.4	1110.7	1111.1	1111.4	1111.8	1112.2	1112.7	1113.2
155°	1149.0	1149.0	1149.0	1149.0	1149.1	1149.4	1149.6	1149.8	1150.1	1151.0	1151.9
157.5°	1184.2	1183.7	1183.2	1182.7	1182.6	1182.8	1183.0	1183.3	1183.5	1184.4	1185.3
160°	1205.1	1204.4	1203.8	1203.1	1202.9	1203.1	1203.3	1203.5	1203.8	1204.7	1205.6
162.5°	1223.9	1223.4	1222.9	1222.4	1222.2	1222.3	1222.3	1222.4	1222.4	1223.5	1224.6
165°	1248.9	1248.4	1248.0	1247.5	1247.4	1247.7	1247.9	1248.1	1248.3	1249.2	1250.1
167.5°	1269.5	1268.6	1267.7	1266.8	1266.4	1266.4	1266.4	1266.4	1266.4	1267.7	1269.1
170°	1280.9	1280.0	1279.1	1278.2	1277.7	1277.7	1277.7	1277.7	1277.7	1279.1	1280.4
172.5°	1289.0	1288.1	1287.2	1286.3	1285.8	1285.8	1285.8	1285.8	1285.8	1287.2	1288.5
175°	1298.1	1297.2	1296.3	1295.4	1294.9	1294.9	1294.9	1294.9	1294.9	1296.3	1297.6
177.5°	1302.9	1302.2	1301.5	1300.8	1300.3	1300.1	1300.0	1299.8	1299.6	1300.7	1301.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	23.9	21.6	21.8	21.3	21.4	20.9	19.8
90°	19.6	20.7	21.6	22.3	23.0	23.6	24.3
92.5°	43.4	44.9	45.8	46.3	46.8	47.3	47.8
95°	82.7	84.3	85.3	85.8	86.2	86.7	87.1
97.5°	128.7	130.2	131.0	131.3	131.6	131.9	132.1
100°	161.1	163.1	164.4	164.8	165.3	165.7	166.2
102.5°	194.1	196.3	197.7	198.3	199.0	199.6	200.2
105°	246.2	247.6	248.6	249.3	249.9	250.6	251.3
107.5°	302.8	303.4	303.8	303.7	303.7	303.6	303.6
110°	342.5	343.2	343.4	343.2	342.9	342.7	342.5



TEST NUMBER: P333473

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	381.9	382.2	382.2	381.8	381.4	381.0	380.6
115°	442.1	441.9	441.7	441.4	441.2	441.0	440.8
117.5°	503.3	503.5	503.1	502.2	501.3	500.4	499.5
120°	544.1	544.1	543.7	542.8	541.9	541.0	540.1
122.5°	584.1	583.9	583.5	582.8	582.0	581.3	580.6
125°	643.1	642.6	642.3	642.1	641.8	641.6	641.4
127.5°	702.1	701.9	701.6	701.1	700.7	700.2	699.8
130°	741.0	740.8	740.5	740.0	739.6	739.1	738.7
132.5°	778.3	778.1	777.7	777.0	776.4	775.8	775.1
135°	835.9	835.9	835.5	834.6	833.7	832.8	831.9
137.5°	892.1	892.3	891.9	890.8	889.7	888.5	887.4
140°	927.5	927.9	927.6	926.5	925.3	924.2	923.1
142.5°	961.8	962.1	961.6	960.5	959.4	958.3	957.1
145°	1011.2	1011.2	1010.9	1010.2	1009.5	1008.9	1008.2
147.5°	1057.8	1058.4	1057.9	1056.4	1054.8	1053.3	1051.8
150°	1086.2	1086.2	1086.0	1085.5	1085.1	1084.6	1084.2
152.5°	1113.8	1114.3	1114.2	1113.4	1112.6	1111.7	1110.9
155°	1152.8	1153.7	1153.5	1152.4	1151.3	1150.2	1149.0
157.5°	1186.2	1187.1	1186.8	1185.3	1183.8	1182.3	1180.9
160°	1206.5	1207.4	1207.2	1206.1	1205.0	1203.9	1202.7
162.5°	1225.6	1226.7	1226.6	1225.3	1224.0	1222.7	1221.4
165°	1251.0	1251.9	1251.7	1250.4	1249.0	1247.7	1246.3
167.5°	1270.4	1271.8	1271.8	1270.4	1269.0	1267.6	1266.2
170°	1281.8	1283.1	1283.0	1281.4	1279.9	1278.3	1276.7
172.5°	1289.9	1291.2	1291.2	1289.8	1288.4	1287.0	1285.6
175°	1299.0	1300.4	1300.2	1298.7	1297.1	1295.5	1293.9
177.5°	1302.9	1303.9	1303.8	1302.6	1301.3	1300.1	1298.8
180°	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0	1302.0

(END OF REPORT)