

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333476

Luminaire Tested: **S125DIW-S1270D1050U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333476
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D1050U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9320.7 lumens
Efficiency: N/A
Efficacy: 138.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55
1	99	94	90	87	92	88	84	81	75	73	71	64	62	61	54	52	51	46
2	90	82	76	71	83	77	71	67	66	62	58	56	53	51	47	45	43	39
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37	33
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32	28
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27	24
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24	21
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21	19
8	55	42	34	29	51	39	32	27	35	29	25	30	25	22	26	22	19	17
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17	15
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.0
10°-20°	524.9	5.6
20°-30°	775.0	8.3
30°-40°	904.3	9.7
40°-50°	908.3	9.7
50°-60°	797.3	8.6
60°-70°	594.1	6.4
70°-80°	339.7	3.6
80°-90°	101.7	1.1
90°-100°	49.6	0.5
100°-110°	305.6	3.3
110°-120°	554.2	5.9
120°-130°	711.2	7.6
130°-140°	765.0	8.2
140°-150°	718.0	7.7
150°-160°	580.8	6.2
160°-170°	375.7	4.0
170°-180°	129.6	1.4
0°-30°	1485.7	15.9
0°-40°	2390.0	25.6
0°-60°	4095.6	43.9
0°-90°	5131.0	55.0
90°-120°	909.3	9.8
90°-150°	3103.6	33.3
90°-180°	4190.0	45.0
0°-180°	9320.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	1	9	16	21	24	7
95°	58	53	16	21	21	73
105°	297	301	301	301	300	315
115°	558	563	564	560	554	553
125°	794	801	801	797	794	709
135°	990	996	994	992	986	763
145°	1148	1150	1150	1151	1145	718
155°	1264	1259	1260	1263	1255	582
165°	1334	1328	1329	1334	1327	377
175°	1364	1359	1359	1366	1358	130
180°	1364	1364	1364	1364	1364	



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.9	34.2	34.6	35.0	35.3	35.5	35.6	35.6	35.6	35.7	35.9
90°	1.0	2.8	4.6	6.4	8.2	9.9	11.5	13.0	14.6	16.2	17.3
92.5°	15.6	14.3	13.1	11.8	10.5	10.6	12.0	13.4	14.8	16.2	17.3
95°	57.6	57.0	56.3	55.6	55.0	50.3	41.8	33.3	24.7	16.2	17.3
97.5°	120.4	121.6	122.8	124.0	125.2	117.4	100.5	83.6	66.7	49.8	43.4
100°	168.9	169.6	170.2	170.9	171.6	172.4	173.3	174.2	175.1	176.0	142.5
102.5°	218.3	219.1	220.0	220.8	221.7	222.4	222.9	223.4	224.0	224.5	218.2
105°	297.3	298.2	299.1	300.0	300.9	301.4	301.4	301.4	301.4	301.4	301.4
107.5°	379.5	379.5	379.5	379.5	379.5	379.7	380.1	380.6	381.0	381.5	381.5
110°	432.9	432.9	432.9	432.9	432.9	433.1	433.5	434.0	434.4	434.9	434.2



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	483.0	483.6	484.1	484.6	485.2	485.6	485.9	486.1	486.4	486.7	485.8
115°	558.3	559.4	560.5	561.6	562.8	563.4	563.7	563.9	564.1	564.3	563.4
117.5°	636.2	636.1	636.1	636.0	636.0	636.4	637.2	638.1	638.9	639.8	638.6
120°	684.7	684.5	684.2	684.0	683.8	684.0	684.7	685.4	686.0	686.7	686.3
122.5°	727.6	728.4	729.3	730.1	731.0	731.6	731.9	732.2	732.5	732.8	732.4
125°	793.9	795.5	797.1	798.6	800.2	801.0	801.0	801.0	801.0	801.0	800.1
127.5°	857.2	858.4	859.5	860.6	861.7	862.2	862.1	862.0	861.8	861.7	861.2
130°	896.1	897.2	898.3	899.4	900.6	901.2	901.5	901.7	901.9	902.1	901.5
132.5°	934.9	936.2	937.5	938.8	940.1	940.5	940.0	939.5	939.0	938.6	938.4
135°	990.1	991.5	992.8	994.2	995.5	996.0	995.5	995.1	994.6	994.2	993.7
137.5°	1040.9	1042.1	1043.2	1044.4	1045.6	1046.0	1045.6	1045.2	1044.7	1044.3	1044.4
140°	1074.1	1074.5	1075.0	1075.4	1075.9	1076.0	1075.8	1075.5	1075.3	1075.1	1075.5
142.5°	1104.0	1104.3	1104.6	1104.8	1105.1	1105.4	1105.7	1106.0	1106.3	1106.6	1106.7
145°	1147.9	1148.4	1148.8	1149.3	1149.7	1149.9	1149.9	1149.9	1149.9	1149.9	1150.2
147.5°	1186.3	1186.3	1186.2	1186.1	1186.0	1186.1	1186.3	1186.6	1186.9	1187.1	1187.4
150°	1210.6	1210.2	1209.7	1209.3	1208.8	1208.8	1209.3	1209.7	1210.2	1210.6	1211.1
152.5°	1234.1	1233.1	1232.1	1231.1	1230.1	1229.9	1230.3	1230.8	1231.2	1231.6	1232.1
155°	1264.2	1262.9	1261.5	1260.2	1258.8	1258.4	1258.8	1259.3	1259.7	1260.2	1260.8
157.5°	1287.5	1286.7	1285.9	1285.1	1284.2	1283.9	1283.9	1283.9	1284.0	1284.0	1284.8
160°	1303.7	1302.3	1301.0	1299.6	1298.3	1297.7	1297.9	1298.2	1298.4	1298.6	1299.5
162.5°	1316.6	1315.3	1313.9	1312.6	1311.2	1310.6	1310.9	1311.1	1311.3	1311.5	1312.8
165°	1334.0	1332.7	1331.3	1330.0	1328.6	1328.0	1328.3	1328.5	1328.7	1328.9	1330.3
167.5°	1346.9	1345.6	1344.2	1342.8	1341.4	1340.8	1341.0	1341.2	1341.5	1341.7	1343.3
170°	1354.2	1352.7	1351.1	1349.5	1347.9	1347.3	1347.5	1347.7	1347.9	1348.2	1350.0
172.5°	1359.1	1357.5	1355.9	1354.4	1352.8	1352.2	1352.6	1353.0	1353.4	1353.8	1355.4
175°	1364.3	1363.0	1361.6	1360.3	1358.9	1358.4	1358.6	1358.8	1359.1	1359.3	1361.1
177.5°	1366.8	1365.7	1364.6	1363.5	1362.5	1362.0	1362.2	1362.4	1362.5	1362.7	1364.0
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	36.1	36.3	36.6	36.5	36.0	35.6	35.2	34.8
90°	18.4	19.6	20.7	21.6	22.3	22.9	23.6	24.3
92.5°	18.4	19.6	20.7	21.4	21.7	22.0	22.3	22.7
95°	18.4	19.6	20.7	21.2	21.2	21.2	21.2	21.2
97.5°	37.1	30.7	24.4	21.2	21.2	21.2	21.2	21.2
100°	109.0	75.5	42.0	24.8	23.9	23.0	22.1	21.2
102.5°	211.8	205.5	199.2	188.4	173.1	157.8	142.5	127.2
105°	301.4	301.4	301.4	301.3	301.1	300.8	300.6	300.4
107.5°	381.6	381.6	381.7	381.4	380.7	380.0	379.3	378.7
110°	433.5	432.9	432.2	432.0	432.2	432.4	432.6	432.9



TEST NUMBER: P333476

CATALOG NUMBER: S125DIW-S1270D1050U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	485.0	484.1	483.3	482.7	482.4	482.0	481.7	481.4
115°	562.5	561.6	560.7	559.6	558.3	556.9	555.6	554.2
117.5°	637.5	636.3	635.1	634.2	633.7	633.1	632.5	631.9
120°	685.8	685.4	684.9	684.1	683.0	681.9	680.8	679.6
122.5°	731.9	731.5	731.0	730.2	728.9	727.6	726.3	725.0
125°	799.2	798.3	797.4	796.6	796.0	795.3	794.6	793.9
127.5°	860.7	860.2	859.7	858.6	857.0	855.3	853.6	852.0
130°	900.8	900.1	899.4	898.5	897.4	896.3	895.2	894.1
132.5°	938.3	938.1	938.0	937.4	936.3	935.1	934.0	932.9
135°	993.3	992.8	992.4	991.5	990.1	988.8	987.4	986.1
137.5°	1044.5	1044.6	1044.7	1044.2	1043.0	1041.8	1040.7	1039.5
140°	1076.0	1076.4	1076.9	1076.4	1075.1	1073.7	1072.4	1071.0
142.5°	1106.8	1106.9	1107.0	1106.4	1105.0	1103.7	1102.3	1101.0
145°	1150.4	1150.6	1150.8	1150.3	1148.9	1147.6	1146.2	1144.9
147.5°	1187.7	1188.0	1188.2	1187.6	1185.9	1184.3	1182.7	1181.1
150°	1211.5	1212.0	1212.4	1211.7	1209.9	1208.1	1206.3	1204.5
152.5°	1232.5	1233.0	1233.4	1232.9	1231.2	1229.6	1228.0	1226.4
155°	1261.5	1262.2	1262.9	1262.3	1260.5	1258.7	1256.9	1255.1
157.5°	1285.5	1286.2	1286.9	1286.4	1284.6	1282.8	1281.0	1279.2
160°	1300.4	1301.3	1302.2	1301.7	1300.0	1298.2	1296.4	1294.6
162.5°	1314.1	1315.3	1316.6	1316.2	1314.2	1312.3	1310.3	1308.3
165°	1331.6	1333.0	1334.3	1334.1	1332.3	1330.5	1328.7	1326.9
167.5°	1344.9	1346.5	1348.2	1348.0	1345.9	1343.9	1341.9	1339.9
170°	1351.8	1353.6	1355.4	1355.2	1353.2	1351.2	1349.2	1347.1
172.5°	1357.1	1358.7	1360.3	1360.1	1358.1	1356.0	1354.0	1352.0
175°	1362.9	1364.7	1366.5	1366.4	1364.3	1362.3	1360.3	1358.3
177.5°	1365.2	1366.5	1367.8	1367.7	1366.2	1364.8	1363.4	1361.9
180°	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3	1364.3

(END OF REPORT)