

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333346-927

Luminaire Tested: **S125DIW-S375D770U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333346-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S375D770U927-4F0-1E-UDD-A  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3650.2 lumens  
Efficiency: N/A  
Efficacy: 120.1 lumens/watt  
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 30.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	36	35	28
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29	24
3	78	69	62	57	70	63	57	52	50	46	43	39	36	34	29	27	25	20
4	72	61	54	48	64	56	49	44	45	40	36	35	32	29	26	23	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	15
6	60	49	41	35	54	44	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	23	20	17	17	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	14	12	10
10	45	33	26	21	40	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2785	2785	2785	2785
5°	3225	2795	2447	2795
10°	3752	2781	2144	2781
15°	4153	2760	1978	2760
20°	4649	2728	1844	2728
25°	5447	2691	1779	2691
30°	5883	2655	1723	2655
35°	4837	2588	1686	2588
40°	3438	2494	1645	2494
45°	2641	2367	1621	2367
50°	2255	2210	1619	2210
55°	2008	2057	1633	2057
60°	1811	1888	1674	1888
65°	1673	1721	1718	1721
70°	1522	1545	1743	1545
75°	1342	1362	1727	1362
80°	1131	1112	1581	1112
85°	897	800	1275	800



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	41.5	1.1
10°-20°	123.6	3.4
20°-30°	200.7	5.5
30°-40°	244.8	6.7
40°-50°	222.7	6.1
50°-60°	177.4	4.9
60°-70°	123.6	3.4
70°-80°	65.9	1.8
80°-90°	18.3	0.5
90°-100°	28.8	0.8
100°-110°	177.3	4.9
110°-120°	321.6	8.8
120°-130°	412.8	11.3
130°-140°	444.0	12.2
140°-150°	416.7	11.4
150°-160°	337.1	9.2
160°-170°	218.0	6.0
170°-180°	75.2	2.1
0°-30°	365.9	10.0
0°-40°	610.7	16.7
0°-60°	1010.8	27.7
0°-90°	1218.6	33.4
90°-120°	527.8	14.5
90°-150°	1801.3	49.3
90°-180°	2432.0	66.6
0°-180°	3650.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	431	431	431	431	431	
5°	498	431	378	431	498	50
15°	621	413	296	413	621	178
25°	764	378	250	378	764	349
35°	614	328	214	328	614	375
45°	289	259	178	259	289	231
55°	178	183	145	183	178	161
65°	110	113	112	113	110	109
75°	54	55	69	55	54	58
85°	12	11	17	11	12	14
90°	14	1	14	1	14	7
95°	12	33	12	33	12	10
105°	174	172	174	172	174	158
115°	322	324	322	324	322	319
125°	461	461	461	461	461	410
135°	572	575	572	575	572	442
145°	664	666	664	666	664	415
155°	728	734	728	734	728	336
165°	770	774	770	774	770	217
175°	788	792	788	792	788	75
180°	792	792	792	792	792	



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	456.1	455.6	455.0	453.8	454.7	452.2	451.1	449.0	446.5	445.6	444.6
5°	497.5	498.4	499.4	495.5	495.9	493.3	487.4	482.7	478.9	473.9	470.4
7.5°	547.3	545.2	544.9	542.5	538.2	534.7	528.6	520.8	513.2	504.5	497.4
10°	572.2	572.4	570.8	567.8	563.2	559.9	551.9	544.2	534.9	523.9	516.0
12.5°	591.0	591.8	589.6	585.7	583.4	576.1	569.7	560.6	549.5	540.7	528.8
15°	621.2	619.2	617.8	612.8	609.0	601.3	591.3	581.7	569.7	558.5	547.3
17.5°	650.5	652.1	649.4	644.8	632.9	623.9	610.5	597.4	582.3	567.4	554.1
20°	676.5	678.0	673.8	665.9	651.6	642.7	625.0	608.1	590.7	571.5	556.8
22.5°	709.1	707.9	702.2	690.2	677.9	661.3	642.1	621.5	599.8	578.1	558.6
25°	764.4	756.7	753.2	738.4	722.2	697.8	671.5	641.4	614.3	585.6	560.7
27.5°	795.1	792.7	788.8	778.5	761.4	735.3	704.3	667.7	629.5	593.2	560.5
30°	788.9	789.3	789.6	786.4	775.4	755.8	724.8	685.6	640.1	599.3	561.6
32.5°	734.4	741.1	747.5	755.0	758.1	754.3	735.0	699.4	652.7	606.3	561.0
35°	613.5	615.6	636.3	656.8	684.6	706.2	720.6	704.9	665.6	612.3	560.3
37.5°	478.4	488.3	502.6	525.8	565.9	601.9	648.2	669.4	656.7	614.3	559.0
40°	407.8	417.0	426.4	450.0	483.8	527.4	579.9	624.7	635.2	608.1	554.6
42.5°	353.4	360.6	371.0	388.7	417.0	455.6	505.8	564.4	600.5	590.3	545.4
45°	289.2	293.8	301.8	315.9	336.4	366.6	410.9	475.0	530.8	549.3	523.6
47.5°	247.6	247.6	253.8	263.5	278.3	304.0	336.8	386.9	446.6	490.7	488.6
50°	224.4	223.5	228.5	236.9	248.6	265.6	296.9	337.0	394.3	444.3	458.2
52.5°	204.5	204.6	207.6	213.9	223.7	238.2	261.6	297.8	346.7	398.0	424.2
55°	178.3	177.5	181.0	185.2	192.4	201.9	218.7	246.4	286.1	336.6	370.7
57.5°	154.2	156.3	157.6	160.6	166.5	172.9	187.1	207.4	238.9	282.3	318.2
60°	140.2	142.2	143.3	146.2	151.0	156.5	167.5	183.9	210.5	247.9	283.5
62.5°	127.6	129.2	129.6	132.2	136.1	141.4	150.0	163.9	184.9	217.5	252.5
65°	109.5	109.5	110.2	113.0	114.8	119.5	126.1	136.2	153.0	178.5	208.3
67.5°	92.0	92.8	92.7	93.9	95.5	99.3	103.9	112.3	124.8	143.3	167.2
70°	80.6	81.3	81.1	82.0	83.8	86.2	90.1	97.9	106.9	122.8	143.3
72.5°	70.3	70.6	70.1	71.3	72.4	74.5	78.8	83.0	91.3	104.8	121.7
75°	53.8	54.2	54.6	55.3	56.4	57.5	59.7	63.8	69.4	79.5	90.2
77.5°	40.3	39.6	40.6	40.4	41.0	41.9	43.8	46.0	50.5	57.0	65.3
80°	30.4	30.6	30.6	30.7	31.7	32.2	33.8	35.5	39.0	43.7	49.6
82.5°	22.2	22.7	22.3	22.7	23.4	23.8	24.8	26.1	28.1	31.9	36.1
85°	12.1	11.2	11.6	11.9	11.9	12.1	12.8	13.4	14.5	15.9	17.6
87.5°	6.3	6.6	6.7	6.6	6.6	6.5	7.0	6.8	7.1	7.4	7.8
90°	14.1	13.7	13.3	12.9	12.5	12.0	11.3	10.7	10.1	9.4	8.5
92.5°	13.2	13.0	12.8	12.6	12.4	12.0	11.3	10.7	10.1	9.4	8.6
95°	12.4	12.4	12.4	12.4	12.4	12.0	11.3	10.7	10.1	9.4	14.3
97.5°	12.4	12.4	12.4	12.4	12.4	14.2	17.8	21.5	25.2	28.9	38.7
100°	12.4	12.8	13.4	13.9	14.4	24.4	43.8	63.3	82.7	102.1	101.6
102.5°	73.8	82.7	91.6	100.4	109.3	115.6	119.3	122.9	126.7	130.3	130.0
105°	174.4	174.4	174.6	174.8	174.8	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	219.8	220.1	220.5	220.9	221.3	221.5	221.5	221.5	221.4	221.4	221.2
110°	251.2	251.1	251.0	250.8	250.7	250.8	251.2	251.6	252.0	252.4	252.2



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	279.4	279.6	279.8	280.0	280.1	280.4	281.0	281.5	281.9	282.5	282.3
115°	321.6	322.4	323.2	324.0	324.8	325.4	326.0	326.5	327.0	327.6	327.4
117.5°	366.8	367.1	367.4	367.7	368.1	368.6	369.3	369.9	370.7	371.3	370.8
120°	394.4	395.1	395.8	396.4	397.0	397.5	397.8	398.1	398.3	398.5	398.2
122.5°	420.7	421.5	422.2	423.0	423.7	424.3	424.5	424.8	425.1	425.3	425.2
125°	460.8	461.2	461.5	461.9	462.3	462.8	463.3	463.8	464.4	464.9	464.9
127.5°	494.5	495.4	496.4	497.3	498.4	499.0	499.2	499.6	499.8	500.1	500.2
130°	518.9	519.5	520.2	520.9	521.5	522.0	522.4	522.8	523.2	523.6	523.5
132.5°	541.5	542.1	542.7	543.4	544.1	544.4	544.5	544.5	544.6	544.7	545.0
135°	572.3	573.1	573.9	574.6	575.4	576.0	576.2	576.5	576.7	577.0	577.3
137.5°	603.3	604.0	604.7	605.3	606.0	606.3	606.3	606.3	606.2	606.1	606.3
140°	621.6	622.4	623.2	623.9	624.7	625.0	624.7	624.5	624.2	623.9	624.1
142.5°	639.0	639.8	640.6	641.4	642.1	642.5	642.5	642.4	642.3	642.3	642.1
145°	664.5	665.3	666.0	666.8	667.6	667.9	667.8	667.7	667.5	667.4	667.4
147.5°	685.5	686.4	687.4	688.3	689.2	689.6	689.4	689.3	689.1	689.0	688.8
150°	699.1	700.1	701.2	702.2	703.3	703.7	703.4	703.1	702.9	702.6	702.3
152.5°	711.8	712.7	713.7	714.5	715.5	715.9	715.6	715.3	715.1	714.8	714.5
155°	728.4	729.5	730.6	731.6	732.6	732.9	732.5	732.1	731.7	731.3	731.1
157.5°	742.4	743.5	744.5	745.5	746.6	746.9	746.5	746.1	745.7	745.2	745.2
160°	751.3	752.4	753.4	754.5	755.5	755.7	755.3	754.7	754.2	753.7	753.5
162.5°	759.3	760.5	761.6	762.8	763.9	764.1	763.3	762.6	761.9	761.2	761.0
165°	770.1	771.2	772.2	773.2	774.3	774.4	773.6	772.9	772.1	771.3	771.2
167.5°	777.6	778.8	780.0	781.2	782.4	782.4	781.5	780.5	779.6	778.7	778.6
170°	781.9	783.0	784.2	785.4	786.6	786.6	785.6	784.5	783.5	782.4	782.3
172.5°	784.7	785.8	787.0	788.2	789.3	789.5	788.5	787.6	786.6	785.8	785.5
175°	788.3	789.5	790.7	791.9	793.0	793.1	792.0	791.0	790.0	788.9	788.8
177.5°	790.4	791.2	792.1	792.9	793.8	793.8	793.1	792.3	791.6	790.9	790.8
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	443.7	442.7	441.5	439.4	437.0	435.6	433.6	432.3	429.7	427.5	425.1
5°	466.2	461.4	457.1	451.4	445.2	441.2	436.4	431.1	425.6	419.9	413.7
7.5°	489.6	481.1	472.0	462.2	452.5	443.6	435.1	426.9	419.1	409.7	401.8
10°	505.2	494.6	483.2	469.9	456.9	445.5	434.0	424.0	413.7	402.7	393.0
12.5°	520.9	506.8	490.7	476.0	460.4	446.7	433.2	420.3	407.4	395.2	383.9
15°	532.0	519.5	504.7	483.8	466.2	447.3	429.4	412.8	397.2	383.7	369.4
17.5°	539.2	523.2	507.2	487.3	464.2	443.1	422.8	403.7	386.2	369.0	355.3
20°	540.5	524.0	507.4	487.8	464.2	440.1	419.7	396.9	378.0	360.2	343.4
22.5°	540.1	521.4	503.3	483.2	460.1	437.8	413.3	390.0	369.5	352.0	334.5
25°	536.0	516.0	493.3	473.0	450.3	426.7	401.8	377.6	356.8	336.8	319.4
27.5°	532.5	506.7	480.9	457.2	435.3	413.7	389.8	365.1	342.0	321.8	305.4
30°	528.3	499.9	471.0	446.2	423.7	402.7	380.2	356.0	331.8	312.1	294.5
32.5°	524.5	491.4	460.9	434.0	410.1	389.7	368.9	345.9	322.2	302.1	284.6
35°	517.1	478.9	443.9	413.5	388.1	367.0	349.6	328.2	306.4	287.0	270.2
37.5°	507.8	462.4	424.8	393.0	365.1	342.9	326.8	310.3	289.4	270.7	255.5
40°	500.4	450.7	410.9	378.3	349.4	326.4	311.3	295.8	278.5	261.0	244.9
42.5°	491.2	440.1	396.9	361.8	333.2	310.7	294.9	281.8	266.4	250.2	235.3
45°	474.3	421.0	374.1	336.4	307.5	285.3	269.1	259.2	247.6	232.3	219.7
47.5°	449.3	398.1	349.6	310.7	280.8	260.3	245.0	235.5	227.4	216.0	204.5
50°	427.2	381.0	331.8	293.3	263.4	242.7	228.6	220.0	213.1	204.3	194.6
52.5°	402.5	359.4	314.4	276.2	246.7	226.3	212.5	204.9	199.2	192.9	183.3
55°	363.1	326.5	284.8	248.6	221.3	201.4	189.3	182.7	177.9	173.2	167.3
57.5°	319.9	291.2	254.3	221.1	196.0	177.8	166.6	160.2	156.5	154.0	150.6
60°	289.4	264.9	233.1	202.8	178.3	162.2	151.2	146.2	143.1	141.2	138.6
62.5°	261.1	241.0	211.5	183.9	162.5	147.3	137.4	132.6	129.7	128.7	126.6
65°	219.5	203.9	179.6	156.7	138.4	125.4	117.2	112.6	110.7	109.6	109.8
67.5°	178.4	169.0	149.4	129.9	115.3	104.4	97.8	94.3	93.3	91.9	91.9
70°	153.4	146.2	129.8	112.7	99.7	91.3	85.5	81.8	80.9	80.2	80.0
72.5°	131.3	125.0	110.7	97.1	85.4	78.0	73.2	71.0	69.5	69.1	69.0
75°	98.6	95.2	83.8	73.0	65.0	59.9	56.6	54.6	53.5	53.2	53.5
77.5°	70.1	67.1	59.9	52.2	47.1	43.3	40.5	39.8	38.6	38.6	38.4
80°	52.7	50.7	46.1	40.1	35.9	32.6	31.1	29.9	29.5	28.9	29.5
82.5°	38.2	36.0	33.0	29.1	25.6	23.7	22.2	21.8	21.5	21.3	21.4
85°	18.9	19.0	17.2	14.3	12.8	11.7	10.8	10.8	10.6	10.5	10.6
87.5°	7.9	7.4	6.7	6.1	5.1	4.5	4.1	4.0	3.8	3.9	4.3
90°	7.6	6.7	5.7	4.8	3.7	2.7	1.7	0.6	1.7	2.7	3.7
92.5°	7.8	7.0	6.2	6.1	6.8	7.6	8.3	9.0	8.3	7.6	6.8
95°	19.3	24.2	29.2	31.9	32.3	32.6	33.0	33.4	33.0	32.6	32.3
97.5°	48.5	58.3	68.1	72.6	71.9	71.3	70.6	69.9	70.6	71.3	71.9
100°	101.1	100.6	100.1	99.6	99.2	98.8	98.4	98.0	98.4	98.8	99.2
102.5°	129.7	129.4	129.0	128.7	128.2	127.7	127.1	126.7	127.1	127.7	128.2
105°	174.9	174.9	174.9	174.7	174.1	173.6	173.1	172.5	173.1	173.6	174.1
107.5°	220.9	220.6	220.4	220.2	220.2	220.2	220.2	220.2	220.2	220.2	220.2
110°	251.9	251.6	251.4	251.2	251.2	251.2	251.2	251.2	251.2	251.2	251.2





TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	282.2	282.0	281.9	281.6	281.3	281.0	280.7	280.4	280.7	281.0	281.3
115°	327.3	327.2	327.0	326.6	326.0	325.3	324.6	324.0	324.6	325.3	326.0
117.5°	370.3	369.9	369.3	369.1	369.2	369.2	369.2	369.2	369.2	369.2	369.2
120°	397.8	397.4	397.0	396.9	397.0	397.1	397.3	397.4	397.3	397.1	397.0
122.5°	424.9	424.8	424.6	424.3	423.7	423.3	422.8	422.2	422.8	423.3	423.7
125°	464.9	464.9	464.9	464.5	463.5	462.6	461.7	460.8	461.7	462.6	463.5
127.5°	500.3	500.3	500.4	500.1	499.5	498.8	498.2	497.5	498.2	498.8	499.5
130°	523.3	523.2	523.1	522.7	522.0	521.3	520.7	520.1	520.7	521.3	522.0
132.5°	545.3	545.6	545.9	545.7	544.9	544.2	543.4	542.6	543.4	544.2	544.9
135°	577.5	577.8	578.1	577.8	577.0	576.2	575.4	574.6	575.4	576.2	577.0
137.5°	606.6	606.8	607.0	606.8	606.2	605.5	604.8	604.1	604.8	605.5	606.2
140°	624.2	624.3	624.5	624.4	624.2	623.9	623.6	623.4	623.6	623.9	624.2
142.5°	641.9	641.7	641.5	641.4	641.2	641.0	640.9	640.7	640.9	641.0	641.2
145°	667.4	667.4	667.4	667.3	667.0	666.8	666.5	666.2	666.5	666.8	667.0
147.5°	688.6	688.6	688.4	688.3	688.4	688.4	688.5	688.6	688.5	688.4	688.4
150°	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.3	702.1	701.8
152.5°	714.3	714.1	713.8	713.9	714.5	715.1	715.7	716.2	715.7	715.1	714.5
155°	730.9	730.6	730.3	730.6	731.3	732.1	732.9	733.7	732.9	732.1	731.3
157.5°	745.2	745.1	745.1	745.4	745.8	746.3	746.8	747.2	746.8	746.3	745.8
160°	753.4	753.3	753.1	753.5	754.2	755.0	755.8	756.6	755.8	755.0	754.2
162.5°	761.0	760.8	760.7	761.0	761.8	762.6	763.3	764.1	763.3	762.6	761.8
165°	771.0	770.9	770.8	771.1	771.9	772.7	773.4	774.2	773.4	772.7	771.9
167.5°	778.4	778.3	778.2	778.5	779.3	780.1	780.9	781.7	780.9	780.1	779.3
170°	782.2	782.0	781.9	782.3	783.2	784.1	785.1	786.0	785.1	784.1	783.2
172.5°	785.3	785.1	784.8	785.1	786.0	787.0	787.9	788.8	787.9	787.0	786.0
175°	788.6	788.5	788.4	788.7	789.5	790.3	791.1	791.9	791.1	790.3	789.5
177.5°	790.7	790.6	790.4	790.8	791.4	792.0	792.6	793.2	792.6	792.0	791.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	423.8	422.2	420.9	418.0	416.3	414.2	412.4	414.3	412.3	413.1	411.8
5°	410.6	405.4	401.8	396.5	391.9	387.7	384.6	384.0	382.5	381.8	379.6
7.5°	394.7	388.2	382.0	375.0	369.2	363.2	359.4	356.2	354.2	351.4	349.5
10°	385.3	376.7	369.4	361.0	353.6	347.2	342.1	339.5	337.2	333.7	332.4
12.5°	373.8	364.9	355.9	346.9	339.8	332.7	328.4	324.5	322.8	318.9	318.5
15°	359.9	346.5	337.7	328.6	318.9	313.0	309.3	305.1	303.3	300.6	298.6
17.5°	343.3	331.4	320.4	310.9	302.6	297.7	293.1	290.3	287.1	285.3	282.0
20°	331.3	320.0	309.0	298.9	292.5	286.8	283.2	280.4	277.1	276.2	272.9
22.5°	321.2	308.7	298.2	289.7	282.7	276.3	272.4	270.5	268.2	265.4	264.7
25°	304.8	291.8	282.8	274.4	268.2	262.3	259.6	257.2	255.0	252.9	252.2
27.5°	290.6	278.9	268.3	260.7	255.2	249.9	247.6	244.6	243.0	241.4	239.4
30°	280.6	268.7	259.4	252.1	246.2	241.5	238.8	236.9	235.4	233.9	232.8
32.5°	270.4	259.4	250.3	243.1	237.3	233.7	231.4	230.0	228.4	226.6	225.2
35°	256.8	244.7	235.9	229.7	225.1	222.4	219.8	218.6	216.7	216.7	215.2
37.5°	241.5	231.1	223.3	217.7	213.6	211.1	208.3	207.5	206.3	205.5	205.0
40°	232.5	222.8	215.5	209.8	205.4	203.4	201.1	199.7	199.0	198.0	197.7
42.5°	223.1	213.8	206.8	201.6	197.7	196.1	194.0	193.0	191.5	190.3	190.0
45°	208.8	199.9	193.5	189.3	186.0	183.9	182.7	180.5	179.7	178.3	178.1
47.5°	195.4	186.7	180.5	177.0	174.1	172.5	170.5	168.3	167.4	166.7	166.6
50°	185.2	177.4	171.5	168.3	165.5	163.1	161.1	159.6	159.1	159.1	159.5
52.5°	175.0	168.3	163.3	159.3	156.7	154.2	152.3	151.4	150.6	151.5	152.1
55°	160.0	153.2	149.6	145.7	143.1	140.2	139.3	138.9	138.4	139.8	140.6
57.5°	144.1	139.3	135.1	131.3	129.0	127.2	126.0	125.8	126.8	127.5	129.9
60°	134.0	128.5	124.7	121.8	119.0	117.9	117.5	117.2	117.9	119.9	123.0
62.5°	122.9	118.4	114.2	112.1	110.0	108.2	108.1	108.4	109.8	112.2	115.3
65°	106.5	102.7	100.0	97.4	95.7	94.7	95.0	95.7	97.4	100.5	103.9
67.5°	89.9	87.3	84.8	82.8	81.2	81.2	81.6	82.7	84.6	88.2	91.3
70°	79.3	76.4	74.3	73.4	72.1	71.4	72.5	74.3	76.0	79.3	82.0
72.5°	68.6	66.1	64.5	63.8	63.3	62.7	63.1	65.1	67.3	70.6	73.8
75°	52.7	51.8	50.7	50.0	49.4	49.8	50.1	52.0	53.8	57.3	60.9
77.5°	38.5	37.5	36.8	36.7	36.4	36.6	37.6	39.0	40.7	43.3	46.0
80°	29.1	28.8	28.4	28.2	28.2	28.4	29.9	30.7	32.4	34.8	37.0
82.5°	21.2	21.0	20.9	20.8	21.0	21.1	21.9	23.1	24.5	26.3	28.2
85°	11.2	10.8	11.3	11.6	11.2	11.7	12.1	12.8	13.4	14.3	15.2
87.5°	4.6	5.1	5.1	5.5	5.6	6.1	6.1	6.8	7.3	7.7	7.6
90°	4.8	5.7	6.7	7.6	8.5	9.4	10.1	10.7	11.3	12.0	12.5
92.5°	6.1	6.2	7.0	7.8	8.6	9.4	10.1	10.7	11.3	12.0	12.4
95°	31.9	29.2	24.2	19.3	14.3	9.4	10.1	10.7	11.3	12.0	12.4
97.5°	72.6	68.1	58.3	48.5	38.7	28.9	25.2	21.5	17.8	14.2	12.4
100°	99.6	100.1	100.6	101.1	101.6	102.1	82.7	63.3	43.8	24.4	14.4
102.5°	128.7	129.0	129.4	129.7	130.0	130.3	126.7	122.9	119.3	115.6	109.3
105°	174.7	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.9	174.8
107.5°	220.2	220.4	220.6	220.9	221.2	221.4	221.4	221.5	221.5	221.5	221.3
110°	251.2	251.4	251.6	251.9	252.2	252.4	252.0	251.6	251.2	250.8	250.7



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	281.6	281.9	282.0	282.2	282.3	282.5	281.9	281.5	281.0	280.4	280.1
115°	326.6	327.0	327.2	327.3	327.4	327.6	327.0	326.5	326.0	325.4	324.8
117.5°	369.1	369.3	369.9	370.3	370.8	371.3	370.7	369.9	369.3	368.6	368.1
120°	396.9	397.0	397.4	397.8	398.2	398.5	398.3	398.1	397.8	397.5	397.0
122.5°	424.3	424.6	424.8	424.9	425.2	425.3	425.1	424.8	424.5	424.3	423.7
125°	464.5	464.9	464.9	464.9	464.9	464.9	464.4	463.8	463.3	462.8	462.3
127.5°	500.1	500.4	500.3	500.3	500.2	500.1	499.8	499.6	499.2	499.0	498.4
130°	522.7	523.1	523.2	523.3	523.5	523.6	523.2	522.8	522.4	522.0	521.5
132.5°	545.7	545.9	545.6	545.3	545.0	544.7	544.6	544.5	544.5	544.4	544.1
135°	577.8	578.1	577.8	577.5	577.3	577.0	576.7	576.5	576.2	576.0	575.4
137.5°	606.8	607.0	606.8	606.6	606.3	606.1	606.2	606.3	606.3	606.3	606.0
140°	624.4	624.5	624.3	624.2	624.1	623.9	624.2	624.5	624.7	625.0	624.7
142.5°	641.4	641.5	641.7	641.9	642.1	642.3	642.3	642.4	642.5	642.5	642.1
145°	667.3	667.4	667.4	667.4	667.4	667.4	667.5	667.7	667.8	667.9	667.6
147.5°	688.3	688.4	688.6	688.6	688.8	689.0	689.1	689.3	689.4	689.6	689.2
150°	701.6	701.6	701.8	702.1	702.3	702.6	702.9	703.1	703.4	703.7	703.3
152.5°	713.9	713.8	714.1	714.3	714.5	714.8	715.1	715.3	715.6	715.9	715.5
155°	730.6	730.3	730.6	730.9	731.1	731.3	731.7	732.1	732.5	732.9	732.6
157.5°	745.4	745.1	745.1	745.2	745.2	745.2	745.7	746.1	746.5	746.9	746.6
160°	753.5	753.1	753.3	753.4	753.5	753.7	754.2	754.7	755.3	755.7	755.5
162.5°	761.0	760.7	760.8	761.0	761.0	761.2	761.9	762.6	763.3	764.1	763.9
165°	771.1	770.8	770.9	771.0	771.2	771.3	772.1	772.9	773.6	774.4	774.3
167.5°	778.5	778.2	778.3	778.4	778.6	778.7	779.6	780.5	781.5	782.4	782.4
170°	782.3	781.9	782.0	782.2	782.3	782.4	783.5	784.5	785.6	786.6	786.6
172.5°	785.1	784.8	785.1	785.3	785.5	785.8	786.6	787.6	788.5	789.5	789.3
175°	788.7	788.4	788.5	788.6	788.8	788.9	790.0	791.0	792.0	793.1	793.0
177.5°	790.8	790.4	790.6	790.7	790.8	790.9	791.6	792.3	793.1	793.8	793.8
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	410.9	411.9	411.1	412.3	411.1	411.9	410.9	411.8	413.1	412.3	414.3
5°	378.7	377.1	378.2	377.5	378.2	377.1	378.7	379.6	381.8	382.5	384.0
7.5°	349.0	347.5	345.6	344.8	345.6	347.5	349.0	349.5	351.4	354.2	356.2
10°	330.4	328.4	328.2	326.9	328.2	328.4	330.4	332.4	333.7	337.2	339.5
12.5°	316.8	314.9	312.8	312.3	312.8	314.9	316.8	318.5	318.9	322.8	324.5
15°	297.5	296.0	294.7	295.8	294.7	296.0	297.5	298.6	300.6	303.3	305.1
17.5°	281.4	280.2	280.0	278.6	280.0	280.2	281.4	282.0	285.3	287.1	290.3
20°	271.2	270.4	270.8	268.3	270.8	270.4	271.2	272.9	276.2	277.1	280.4
22.5°	263.2	261.4	261.2	260.7	261.2	261.4	263.2	264.7	265.4	268.2	270.5
25°	250.6	249.7	248.7	249.7	248.7	249.7	250.6	252.2	252.9	255.0	257.2
27.5°	239.6	238.4	238.2	238.4	238.2	238.4	239.6	239.4	241.4	243.0	244.6
30°	232.8	231.0	231.2	231.0	231.2	231.0	232.8	232.8	233.9	235.4	236.9
32.5°	225.5	224.3	224.0	223.7	224.0	224.3	225.5	225.2	226.6	228.4	230.0
35°	214.7	214.7	213.8	213.8	213.8	214.7	214.7	215.2	216.7	216.7	218.6
37.5°	204.5	204.4	203.8	203.9	203.8	204.4	204.5	205.0	205.5	206.3	207.5
40°	196.9	196.8	196.2	195.1	196.2	196.8	196.9	197.7	198.0	199.0	199.7
42.5°	189.6	189.0	188.8	188.4	188.8	189.0	189.6	190.0	190.3	191.5	193.0
45°	178.1	178.1	177.8	177.5	177.8	178.1	178.1	178.1	178.3	179.7	180.5
47.5°	166.9	167.2	167.9	167.8	167.9	167.2	166.9	166.6	166.7	167.4	168.3
50°	160.2	160.3	160.9	161.1	160.9	160.3	160.2	159.5	159.1	159.1	159.6
52.5°	152.7	153.8	154.5	154.3	154.5	153.8	152.7	152.1	151.5	150.6	151.4
55°	142.2	143.5	144.8	145.0	144.8	143.5	142.2	140.6	139.8	138.4	138.9
57.5°	131.9	133.6	135.0	135.5	135.0	133.6	131.9	129.9	127.5	126.8	125.8
60°	124.8	127.2	128.9	129.6	128.9	127.2	124.8	123.0	119.9	117.9	117.2
62.5°	118.1	120.8	122.4	122.6	122.4	120.8	118.1	115.3	112.2	109.8	108.4
65°	107.1	109.8	111.3	112.4	111.3	109.8	107.1	103.9	100.5	97.4	95.7
67.5°	95.2	98.0	99.6	100.4	99.6	98.0	95.2	91.3	88.2	84.6	82.7
70°	86.6	89.4	91.5	92.3	91.5	89.4	86.6	82.0	79.3	76.0	74.3
72.5°	78.1	80.6	82.3	83.2	82.3	80.6	78.1	73.8	70.6	67.3	65.1
75°	63.3	66.6	68.3	69.2	68.3	66.6	63.3	60.9	57.3	53.8	52.0
77.5°	48.8	51.8	52.8	53.3	52.8	51.8	48.8	46.0	43.3	40.7	39.0
80°	39.1	41.0	42.3	42.5	42.3	41.0	39.1	37.0	34.8	32.4	30.7
82.5°	30.1	31.6	32.0	32.5	32.0	31.6	30.1	28.2	26.3	24.5	23.1
85°	16.5	17.2	17.4	17.2	17.4	17.2	16.5	15.2	14.3	13.4	12.8
87.5°	8.0	7.9	8.0	8.4	8.0	7.9	8.0	7.6	7.7	7.3	6.8
90°	12.9	13.3	13.7	14.1	13.7	13.3	12.9	12.5	12.0	11.3	10.7
92.5°	12.6	12.8	13.0	13.2	13.0	12.8	12.6	12.4	12.0	11.3	10.7
95°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.0	11.3	10.7
97.5°	12.4	12.4	12.4	12.4	12.4	12.4	12.4	12.4	14.2	17.8	21.5
100°	13.9	13.4	12.8	12.4	12.8	13.4	13.9	14.4	24.4	43.8	63.3
102.5°	100.4	91.6	82.7	73.8	82.7	91.6	100.4	109.3	115.6	119.3	122.9
105°	174.8	174.6	174.4	174.4	174.4	174.6	174.8	174.8	174.9	174.9	174.9
107.5°	220.9	220.5	220.1	219.8	220.1	220.5	220.9	221.3	221.5	221.5	221.5
110°	250.8	251.0	251.1	251.2	251.1	251.0	250.8	250.7	250.8	251.2	251.6



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	280.0	279.8	279.6	279.4	279.6	279.8	280.0	280.1	280.4	281.0	281.5
115°	324.0	323.2	322.4	321.6	322.4	323.2	324.0	324.8	325.4	326.0	326.5
117.5°	367.7	367.4	367.1	366.8	367.1	367.4	367.7	368.1	368.6	369.3	369.9
120°	396.4	395.8	395.1	394.4	395.1	395.8	396.4	397.0	397.5	397.8	398.1
122.5°	423.0	422.2	421.5	420.7	421.5	422.2	423.0	423.7	424.3	424.5	424.8
125°	461.9	461.5	461.2	460.8	461.2	461.5	461.9	462.3	462.8	463.3	463.8
127.5°	497.3	496.4	495.4	494.5	495.4	496.4	497.3	498.4	499.0	499.2	499.6
130°	520.9	520.2	519.5	518.9	519.5	520.2	520.9	521.5	522.0	522.4	522.8
132.5°	543.4	542.7	542.1	541.5	542.1	542.7	543.4	544.1	544.4	544.5	544.5
135°	574.6	573.9	573.1	572.3	573.1	573.9	574.6	575.4	576.0	576.2	576.5
137.5°	605.3	604.7	604.0	603.3	604.0	604.7	605.3	606.0	606.3	606.3	606.3
140°	623.9	623.2	622.4	621.6	622.4	623.2	623.9	624.7	625.0	624.7	624.5
142.5°	641.4	640.6	639.8	639.0	639.8	640.6	641.4	642.1	642.5	642.5	642.4
145°	666.8	666.0	665.3	664.5	665.3	666.0	666.8	667.6	667.9	667.8	667.7
147.5°	688.3	687.4	686.4	685.5	686.4	687.4	688.3	689.2	689.6	689.4	689.3
150°	702.2	701.2	700.1	699.1	700.1	701.2	702.2	703.3	703.7	703.4	703.1
152.5°	714.5	713.7	712.7	711.8	712.7	713.7	714.5	715.5	715.9	715.6	715.3
155°	731.6	730.6	729.5	728.4	729.5	730.6	731.6	732.6	732.9	732.5	732.1
157.5°	745.5	744.5	743.5	742.4	743.5	744.5	745.5	746.6	746.9	746.5	746.1
160°	754.5	753.4	752.4	751.3	752.4	753.4	754.5	755.5	755.7	755.3	754.7
162.5°	762.8	761.6	760.5	759.3	760.5	761.6	762.8	763.9	764.1	763.3	762.6
165°	773.2	772.2	771.2	770.1	771.2	772.2	773.2	774.3	774.4	773.6	772.9
167.5°	781.2	780.0	778.8	777.6	778.8	780.0	781.2	782.4	782.4	781.5	780.5
170°	785.4	784.2	783.0	781.9	783.0	784.2	785.4	786.6	786.6	785.6	784.5
172.5°	788.2	787.0	785.8	784.7	785.8	787.0	788.2	789.3	789.5	788.5	787.6
175°	791.9	790.7	789.5	788.3	789.5	790.7	791.9	793.0	793.1	792.0	791.0
177.5°	792.9	792.1	791.2	790.4	791.2	792.1	792.9	793.8	793.8	793.1	792.3
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	412.4	414.2	416.3	418.0	420.9	422.2	423.8	425.1	427.5	429.7	432.3
5°	384.6	387.7	391.9	396.5	401.8	405.4	410.6	413.7	419.9	425.6	431.1
7.5°	359.4	363.2	369.2	375.0	382.0	388.2	394.7	401.8	409.7	419.1	426.9
10°	342.1	347.2	353.6	361.0	369.4	376.7	385.3	393.0	402.7	413.7	424.0
12.5°	328.4	332.7	339.8	346.9	355.9	364.9	373.8	383.9	395.2	407.4	420.3
15°	309.3	313.0	318.9	328.6	337.7	346.5	359.9	369.4	383.7	397.2	412.8
17.5°	293.1	297.7	302.6	310.9	320.4	331.4	343.3	355.3	369.0	386.2	403.7
20°	283.2	286.8	292.5	298.9	309.0	320.0	331.3	343.4	360.2	378.0	396.9
22.5°	272.4	276.3	282.7	289.7	298.2	308.7	321.2	334.5	352.0	369.5	390.0
25°	259.6	262.3	268.2	274.4	282.8	291.8	304.8	319.4	336.8	356.8	377.6
27.5°	247.6	249.9	255.2	260.7	268.3	278.9	290.6	305.4	321.8	342.0	365.1
30°	238.8	241.5	246.2	252.1	259.4	268.7	280.6	294.5	312.1	331.8	356.0
32.5°	231.4	233.7	237.3	243.1	250.3	259.4	270.4	284.6	302.1	322.2	345.9
35°	219.8	222.4	225.1	229.7	235.9	244.7	256.8	270.2	287.0	306.4	328.2
37.5°	208.3	211.1	213.6	217.7	223.3	231.1	241.5	255.5	270.7	289.4	310.3
40°	201.1	203.4	205.4	209.8	215.5	222.8	232.5	244.9	261.0	278.5	295.8
42.5°	194.0	196.1	197.7	201.6	206.8	213.8	223.1	235.3	250.2	266.4	281.8
45°	182.7	183.9	186.0	189.3	193.5	199.9	208.8	219.7	232.3	247.6	259.2
47.5°	170.5	172.5	174.1	177.0	180.5	186.7	195.4	204.5	216.0	227.4	235.5
50°	161.1	163.1	165.5	168.3	171.5	177.4	185.2	194.6	204.3	213.1	220.0
52.5°	152.3	154.2	156.7	159.3	163.3	168.3	175.0	183.3	192.9	199.2	204.9
55°	139.3	140.2	143.1	145.7	149.6	153.2	160.0	167.3	173.2	177.9	182.7
57.5°	126.0	127.2	129.0	131.3	135.1	139.3	144.1	150.6	154.0	156.5	160.2
60°	117.5	117.9	119.0	121.8	124.7	128.5	134.0	138.6	141.2	143.1	146.2
62.5°	108.1	108.2	110.0	112.1	114.2	118.4	122.9	126.6	128.7	129.7	132.6
65°	95.0	94.7	95.7	97.4	100.0	102.7	106.5	109.8	109.6	110.7	112.6
67.5°	81.6	81.2	81.2	82.8	84.8	87.3	89.9	91.9	91.9	93.3	94.3
70°	72.5	71.4	72.1	73.4	74.3	76.4	79.3	80.0	80.2	80.9	81.8
72.5°	63.1	62.7	63.3	63.8	64.5	66.1	68.6	69.0	69.1	69.5	71.0
75°	50.1	49.8	49.4	50.0	50.7	51.8	52.7	53.5	53.2	53.5	54.6
77.5°	37.6	36.6	36.4	36.7	36.8	37.5	38.5	38.4	38.6	38.6	39.8
80°	29.9	28.4	28.2	28.2	28.4	28.8	29.1	29.5	28.9	29.5	29.9
82.5°	21.9	21.1	21.0	20.8	20.9	21.0	21.2	21.4	21.3	21.5	21.8
85°	12.1	11.7	11.2	11.6	11.3	10.8	11.2	10.6	10.5	10.6	10.8
87.5°	6.1	6.1	5.6	5.5	5.1	5.1	4.6	4.3	3.9	3.8	4.0
90°	10.1	9.4	8.5	7.6	6.7	5.7	4.8	3.7	2.7	1.7	0.6
92.5°	10.1	9.4	8.6	7.8	7.0	6.2	6.1	6.8	7.6	8.3	9.0
95°	10.1	9.4	14.3	19.3	24.2	29.2	31.9	32.3	32.6	33.0	33.4
97.5°	25.2	28.9	38.7	48.5	58.3	68.1	72.6	71.9	71.3	70.6	69.9
100°	82.7	102.1	101.6	101.1	100.6	100.1	99.6	99.2	98.8	98.4	98.0
102.5°	126.7	130.3	130.0	129.7	129.4	129.0	128.7	128.2	127.7	127.1	126.7
105°	174.9	174.9	174.9	174.9	174.9	174.9	174.7	174.1	173.6	173.1	172.5
107.5°	221.4	221.4	221.2	220.9	220.6	220.4	220.2	220.2	220.2	220.2	220.2
110°	252.0	252.4	252.2	251.9	251.6	251.4	251.2	251.2	251.2	251.2	251.2



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	281.9	282.5	282.3	282.2	282.0	281.9	281.6	281.3	281.0	280.7	280.4
115°	327.0	327.6	327.4	327.3	327.2	327.0	326.6	326.0	325.3	324.6	324.0
117.5°	370.7	371.3	370.8	370.3	369.9	369.3	369.1	369.2	369.2	369.2	369.2
120°	398.3	398.5	398.2	397.8	397.4	397.0	396.9	397.0	397.1	397.3	397.4
122.5°	425.1	425.3	425.2	424.9	424.8	424.6	424.3	423.7	423.3	422.8	422.2
125°	464.4	464.9	464.9	464.9	464.9	464.9	464.5	463.5	462.6	461.7	460.8
127.5°	499.8	500.1	500.2	500.3	500.3	500.4	500.1	499.5	498.8	498.2	497.5
130°	523.2	523.6	523.5	523.3	523.2	523.1	522.7	522.0	521.3	520.7	520.1
132.5°	544.6	544.7	545.0	545.3	545.6	545.9	545.7	544.9	544.2	543.4	542.6
135°	576.7	577.0	577.3	577.5	577.8	578.1	577.8	577.0	576.2	575.4	574.6
137.5°	606.2	606.1	606.3	606.6	606.8	607.0	606.8	606.2	605.5	604.8	604.1
140°	624.2	623.9	624.1	624.2	624.3	624.5	624.4	624.2	623.9	623.6	623.4
142.5°	642.3	642.3	642.1	641.9	641.7	641.5	641.4	641.2	641.0	640.9	640.7
145°	667.5	667.4	667.4	667.4	667.4	667.4	667.3	667.0	666.8	666.5	666.2
147.5°	689.1	689.0	688.8	688.6	688.6	688.4	688.3	688.4	688.4	688.5	688.6
150°	702.9	702.6	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6
152.5°	715.1	714.8	714.5	714.3	714.1	713.8	713.9	714.5	715.1	715.7	716.2
155°	731.7	731.3	731.1	730.9	730.6	730.3	730.6	731.3	732.1	732.9	733.7
157.5°	745.7	745.2	745.2	745.2	745.1	745.1	745.4	745.8	746.3	746.8	747.2
160°	754.2	753.7	753.5	753.4	753.3	753.1	753.5	754.2	755.0	755.8	756.6
162.5°	761.9	761.2	761.0	761.0	760.8	760.7	761.0	761.8	762.6	763.3	764.1
165°	772.1	771.3	771.2	771.0	770.9	770.8	771.1	771.9	772.7	773.4	774.2
167.5°	779.6	778.7	778.6	778.4	778.3	778.2	778.5	779.3	780.1	780.9	781.7
170°	783.5	782.4	782.3	782.2	782.0	781.9	782.3	783.2	784.1	785.1	786.0
172.5°	786.6	785.8	785.5	785.3	785.1	784.8	785.1	786.0	787.0	787.9	788.8
175°	790.0	788.9	788.8	788.6	788.5	788.4	788.7	789.5	790.3	791.1	791.9
177.5°	791.6	790.9	790.8	790.7	790.6	790.4	790.8	791.4	792.0	792.6	793.2
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	433.6	435.6	437.0	439.4	441.5	442.7	443.7	444.6	445.6	446.5	449.0
5°	436.4	441.2	445.2	451.4	457.1	461.4	466.2	470.4	473.9	478.9	482.7
7.5°	435.1	443.6	452.5	462.2	472.0	481.1	489.6	497.4	504.5	513.2	520.8
10°	434.0	445.5	456.9	469.9	483.2	494.6	505.2	516.0	523.9	534.9	544.2
12.5°	433.2	446.7	460.4	476.0	490.7	506.8	520.9	528.8	540.7	549.5	560.6
15°	429.4	447.3	466.2	483.8	504.7	519.5	532.0	547.3	558.5	569.7	581.7
17.5°	422.8	443.1	464.2	487.3	507.2	523.2	539.2	554.1	567.4	582.3	597.4
20°	419.7	440.1	464.2	487.8	507.4	524.0	540.5	556.8	571.5	590.7	608.1
22.5°	413.3	437.8	460.1	483.2	503.3	521.4	540.1	558.6	578.1	599.8	621.5
25°	401.8	426.7	450.3	473.0	493.3	516.0	536.0	560.7	585.6	614.3	641.4
27.5°	389.8	413.7	435.3	457.2	480.9	506.7	532.5	560.5	593.2	629.5	667.7
30°	380.2	402.7	423.7	446.2	471.0	499.9	528.3	561.6	599.3	640.1	685.6
32.5°	368.9	389.7	410.1	434.0	460.9	491.4	524.5	561.0	606.3	652.7	699.4
35°	349.6	367.0	388.1	413.5	443.9	478.9	517.1	560.3	612.3	665.6	704.9
37.5°	326.8	342.9	365.1	393.0	424.8	462.4	507.8	559.0	614.3	656.7	669.4
40°	311.3	326.4	349.4	378.3	410.9	450.7	500.4	554.6	608.1	635.2	624.7
42.5°	294.9	310.7	333.2	361.8	396.9	440.1	491.2	545.4	590.3	600.5	564.4
45°	269.1	285.3	307.5	336.4	374.1	421.0	474.3	523.6	549.3	530.8	475.0
47.5°	245.0	260.3	280.8	310.7	349.6	398.1	449.3	488.6	490.7	446.6	386.9
50°	228.6	242.7	263.4	293.3	331.8	381.0	427.2	458.2	444.3	394.3	337.0
52.5°	212.5	226.3	246.7	276.2	314.4	359.4	402.5	424.2	398.0	346.7	297.8
55°	189.3	201.4	221.3	248.6	284.8	326.5	363.1	370.7	336.6	286.1	246.4
57.5°	166.6	177.8	196.0	221.1	254.3	291.2	319.9	318.2	282.3	238.9	207.4
60°	151.2	162.2	178.3	202.8	233.1	264.9	289.4	283.5	247.9	210.5	183.9
62.5°	137.4	147.3	162.5	183.9	211.5	241.0	261.1	252.5	217.5	184.9	163.9
65°	117.2	125.4	138.4	156.7	179.6	203.9	219.5	208.3	178.5	153.0	136.2
67.5°	97.8	104.4	115.3	129.9	149.4	169.0	178.4	167.2	143.3	124.8	112.3
70°	85.5	91.3	99.7	112.7	129.8	146.2	153.4	143.3	122.8	106.9	97.9
72.5°	73.2	78.0	85.4	97.1	110.7	125.0	131.3	121.7	104.8	91.3	83.0
75°	56.6	59.9	65.0	73.0	83.8	95.2	98.6	90.2	79.5	69.4	63.8
77.5°	40.5	43.3	47.1	52.2	59.9	67.1	70.1	65.3	57.0	50.5	46.0
80°	31.1	32.6	35.9	40.1	46.1	50.7	52.7	49.6	43.7	39.0	35.5
82.5°	22.2	23.7	25.6	29.1	33.0	36.0	38.2	36.1	31.9	28.1	26.1
85°	10.8	11.7	12.8	14.3	17.2	19.0	18.9	17.6	15.9	14.5	13.4
87.5°	4.1	4.5	5.1	6.1	6.7	7.4	7.9	7.8	7.4	7.1	6.8
90°	1.7	2.7	3.7	4.8	5.7	6.7	7.6	8.5	9.4	10.1	10.7
92.5°	8.3	7.6	6.8	6.1	6.2	7.0	7.8	8.6	9.4	10.1	10.7
95°	33.0	32.6	32.3	31.9	29.2	24.2	19.3	14.3	9.4	10.1	10.7
97.5°	70.6	71.3	71.9	72.6	68.1	58.3	48.5	38.7	28.9	25.2	21.5
100°	98.4	98.8	99.2	99.6	100.1	100.6	101.1	101.6	102.1	82.7	63.3
102.5°	127.1	127.7	128.2	128.7	129.0	129.4	129.7	130.0	130.3	126.7	122.9
105°	173.1	173.6	174.1	174.7	174.9	174.9	174.9	174.9	174.9	174.9	174.9
107.5°	220.2	220.2	220.2	220.2	220.4	220.6	220.9	221.2	221.4	221.4	221.5
110°	251.2	251.2	251.2	251.2	251.4	251.6	251.9	252.2	252.4	252.0	251.6





TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	280.7	281.0	281.3	281.6	281.9	282.0	282.2	282.3	282.5	281.9	281.5
115°	324.6	325.3	326.0	326.6	327.0	327.2	327.3	327.4	327.6	327.0	326.5
117.5°	369.2	369.2	369.2	369.1	369.3	369.9	370.3	370.8	371.3	370.7	369.9
120°	397.3	397.1	397.0	396.9	397.0	397.4	397.8	398.2	398.5	398.3	398.1
122.5°	422.8	423.3	423.7	424.3	424.6	424.8	424.9	425.2	425.3	425.1	424.8
125°	461.7	462.6	463.5	464.5	464.9	464.9	464.9	464.9	464.9	464.4	463.8
127.5°	498.2	498.8	499.5	500.1	500.4	500.3	500.3	500.2	500.1	499.8	499.6
130°	520.7	521.3	522.0	522.7	523.1	523.2	523.3	523.5	523.6	523.2	522.8
132.5°	543.4	544.2	544.9	545.7	545.9	545.6	545.3	545.0	544.7	544.6	544.5
135°	575.4	576.2	577.0	577.8	578.1	577.8	577.5	577.3	577.0	576.7	576.5
137.5°	604.8	605.5	606.2	606.8	607.0	606.8	606.6	606.3	606.1	606.2	606.3
140°	623.6	623.9	624.2	624.4	624.5	624.3	624.2	624.1	623.9	624.2	624.5
142.5°	640.9	641.0	641.2	641.4	641.5	641.7	641.9	642.1	642.3	642.3	642.4
145°	666.5	666.8	667.0	667.3	667.4	667.4	667.4	667.4	667.4	667.5	667.7
147.5°	688.5	688.4	688.4	688.3	688.4	688.6	688.6	688.8	689.0	689.1	689.3
150°	702.3	702.1	701.8	701.6	701.6	701.8	702.1	702.3	702.6	702.9	703.1
152.5°	715.7	715.1	714.5	713.9	713.8	714.1	714.3	714.5	714.8	715.1	715.3
155°	732.9	732.1	731.3	730.6	730.3	730.6	730.9	731.1	731.3	731.7	732.1
157.5°	746.8	746.3	745.8	745.4	745.1	745.1	745.2	745.2	745.2	745.7	746.1
160°	755.8	755.0	754.2	753.5	753.1	753.3	753.4	753.5	753.7	754.2	754.7
162.5°	763.3	762.6	761.8	761.0	760.7	760.8	761.0	761.0	761.2	761.9	762.6
165°	773.4	772.7	771.9	771.1	770.8	770.9	771.0	771.2	771.3	772.1	772.9
167.5°	780.9	780.1	779.3	778.5	778.2	778.3	778.4	778.6	778.7	779.6	780.5
170°	785.1	784.1	783.2	782.3	781.9	782.0	782.2	782.3	782.4	783.5	784.5
172.5°	787.9	787.0	786.0	785.1	784.8	785.1	785.3	785.5	785.8	786.6	787.6
175°	791.1	790.3	789.5	788.7	788.4	788.5	788.6	788.8	788.9	790.0	791.0
177.5°	792.6	792.0	791.4	790.8	790.4	790.6	790.7	790.8	790.9	791.6	792.3
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9	791.9



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	431.3	431.3	431.3	431.3	431.3	431.3	431.3
2.5°	451.1	452.2	454.7	453.8	455.0	455.6	456.1
5°	487.4	493.3	495.9	495.5	499.4	498.4	497.5
7.5°	528.6	534.7	538.2	542.5	544.9	545.2	547.3
10°	551.9	559.9	563.2	567.8	570.8	572.4	572.2
12.5°	569.7	576.1	583.4	585.7	589.6	591.8	591.0
15°	591.3	601.3	609.0	612.8	617.8	619.2	621.2
17.5°	610.5	623.9	632.9	644.8	649.4	652.1	650.5
20°	625.0	642.7	651.6	665.9	673.8	678.0	676.5
22.5°	642.1	661.3	677.9	690.2	702.2	707.9	709.1
25°	671.5	697.8	722.2	738.4	753.2	756.7	764.4
27.5°	704.3	735.3	761.4	778.5	788.8	792.7	795.1
30°	724.8	755.8	775.4	786.4	789.6	789.3	788.9
32.5°	735.0	754.3	758.1	755.0	747.5	741.1	734.4
35°	720.6	706.2	684.6	656.8	636.3	615.6	613.5
37.5°	648.2	601.9	565.9	525.8	502.6	488.3	478.4
40°	579.9	527.4	483.8	450.0	426.4	417.0	407.8
42.5°	505.8	455.6	417.0	388.7	371.0	360.6	353.4
45°	410.9	366.6	336.4	315.9	301.8	293.8	289.2
47.5°	336.8	304.0	278.3	263.5	253.8	247.6	247.6
50°	296.9	265.6	248.6	236.9	228.5	223.5	224.4
52.5°	261.6	238.2	223.7	213.9	207.6	204.6	204.5
55°	218.7	201.9	192.4	185.2	181.0	177.5	178.3
57.5°	187.1	172.9	166.5	160.6	157.6	156.3	154.2
60°	167.5	156.5	151.0	146.2	143.3	142.2	140.2
62.5°	150.0	141.4	136.1	132.2	129.6	129.2	127.6
65°	126.1	119.5	114.8	113.0	110.2	109.5	109.5
67.5°	103.9	99.3	95.5	93.9	92.7	92.8	92.0
70°	90.1	86.2	83.8	82.0	81.1	81.3	80.6
72.5°	78.8	74.5	72.4	71.3	70.1	70.6	70.3
75°	59.7	57.5	56.4	55.3	54.6	54.2	53.8
77.5°	43.8	41.9	41.0	40.4	40.6	39.6	40.3
80°	33.8	32.2	31.7	30.7	30.6	30.6	30.4
82.5°	24.8	23.8	23.4	22.7	22.3	22.7	22.2
85°	12.8	12.1	11.9	11.9	11.6	11.2	12.1
87.5°	7.0	6.5	6.6	6.6	6.7	6.6	6.3
90°	11.3	12.0	12.5	12.9	13.3	13.7	14.1
92.5°	11.3	12.0	12.4	12.6	12.8	13.0	13.2
95°	11.3	12.0	12.4	12.4	12.4	12.4	12.4
97.5°	17.8	14.2	12.4	12.4	12.4	12.4	12.4
100°	43.8	24.4	14.4	13.9	13.4	12.8	12.4
102.5°	119.3	115.6	109.3	100.4	91.6	82.7	73.8
105°	174.9	174.9	174.8	174.8	174.6	174.4	174.4
107.5°	221.5	221.5	221.3	220.9	220.5	220.1	219.8
110°	251.2	250.8	250.7	250.8	251.0	251.1	251.2



TEST NUMBER: P333346-927

CATALOG NUMBER: S125DIW-S375D770U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	281.0	280.4	280.1	280.0	279.8	279.6	279.4
115°	326.0	325.4	324.8	324.0	323.2	322.4	321.6
117.5°	369.3	368.6	368.1	367.7	367.4	367.1	366.8
120°	397.8	397.5	397.0	396.4	395.8	395.1	394.4
122.5°	424.5	424.3	423.7	423.0	422.2	421.5	420.7
125°	463.3	462.8	462.3	461.9	461.5	461.2	460.8
127.5°	499.2	499.0	498.4	497.3	496.4	495.4	494.5
130°	522.4	522.0	521.5	520.9	520.2	519.5	518.9
132.5°	544.5	544.4	544.1	543.4	542.7	542.1	541.5
135°	576.2	576.0	575.4	574.6	573.9	573.1	572.3
137.5°	606.3	606.3	606.0	605.3	604.7	604.0	603.3
140°	624.7	625.0	624.7	623.9	623.2	622.4	621.6
142.5°	642.5	642.5	642.1	641.4	640.6	639.8	639.0
145°	667.8	667.9	667.6	666.8	666.0	665.3	664.5
147.5°	689.4	689.6	689.2	688.3	687.4	686.4	685.5
150°	703.4	703.7	703.3	702.2	701.2	700.1	699.1
152.5°	715.6	715.9	715.5	714.5	713.7	712.7	711.8
155°	732.5	732.9	732.6	731.6	730.6	729.5	728.4
157.5°	746.5	746.9	746.6	745.5	744.5	743.5	742.4
160°	755.3	755.7	755.5	754.5	753.4	752.4	751.3
162.5°	763.3	764.1	763.9	762.8	761.6	760.5	759.3
165°	773.6	774.4	774.3	773.2	772.2	771.2	770.1
167.5°	781.5	782.4	782.4	781.2	780.0	778.8	777.6
170°	785.6	786.6	786.6	785.4	784.2	783.0	781.9
172.5°	788.5	789.5	789.3	788.2	787.0	785.8	784.7
175°	792.0	793.1	793.0	791.9	790.7	789.5	788.3
177.5°	793.1	793.8	793.8	792.9	792.1	791.2	790.4
180°	791.9	791.9	791.9	791.9	791.9	791.9	791.9

(END OF REPORT)