

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333464

Luminaire Tested: **S125DIW-S1270D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333464
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D470U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7003.5 lumens
Efficiency: N/A
Efficacy: 133.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	62
2	94	86	79	74	89	82	76	71	74	69	65	67	63	60	60	57	55	51
3	85	76	68	62	81	72	65	59	65	60	55	59	55	51	53	50	47	44
4	78	67	59	52	74	64	56	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	49	44	52	46	41	47	42	38	43	39	35	32
6	66	54	45	39	63	51	44	38	47	40	36	43	37	33	39	34	31	28
7	62	49	40	35	58	47	39	34	43	36	31	39	34	29	36	31	28	25
8	57	44	36	31	54	43	35	30	39	33	28	36	30	26	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	37	30	25	47	36	29	24	33	27	23	31	25	22	28	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12727	12727	12727
5°	12756	12635	12716
10°	12679	12545	12618
15°	12541	12395	12447
20°	12344	12183	12205
25°	12133	11932	11921
30°	11872	11662	11604
35°	11591	11371	11211
40°	11304	11054	10897
45°	10993	10766	10552
50°	10652	10417	10104
55°	10323	10025	9743
60°	9928	9627	9285
65°	9459	9149	8839
70°	9009	8597	8303
75°	8210	7938	7663
80°	7305	7189	7018
85°	6358	6469	6121



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.8	2.7
10°-20°	524.9	7.5
20°-30°	775.0	11.1
30°-40°	904.3	12.9
40°-50°	908.3	13.0
50°-60°	797.3	11.4
60°-70°	594.1	8.5
70°-80°	339.7	4.9
80°-90°	100.1	1.4
90°-100°	22.2	0.3
100°-110°	136.7	2.0
110°-120°	247.9	3.5
120°-130°	318.1	4.5
130°-140°	342.2	4.9
140°-150°	321.2	4.6
150°-160°	259.8	3.7
160°-170°	168.0	2.4
170°-180°	58.0	0.8
0°-30°	1485.7	21.2
0°-40°	2390.0	34.1
0°-60°	4095.6	58.5
0°-90°	5129.4	73.2
90°-120°	406.7	5.8
90°-150°	1388.2	19.8
90°-180°	1874.0	26.8
0°-180°	7003.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1971	1971	1971	1971	1971	
5°	1968	1964	1949	1962	1961	187
15°	1876	1870	1854	1861	1862	528
25°	1703	1694	1674	1677	1673	783
35°	1470	1463	1442	1434	1422	919
45°	1204	1197	1179	1161	1155	927
55°	917	911	890	876	865	818
65°	619	615	599	585	578	614
75°	329	326	318	313	307	351
85°	86	87	87	86	83	96
90°	0	4	7	9	11	6
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	251	248	247
125°	355	358	358	356	355	317
135°	443	445	445	444	441	341
145°	514	514	514	515	512	321
155°	566	563	564	565	561	260
165°	597	594	594	597	594	168
175°	610	608	608	611	608	58
180°	610	610	610	610	610	



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1975.7	1974.9	1974.1	1973.2	1972.4	1970.6	1967.8	1965.0	1962.3	1959.5	1962.3
5°	1967.6	1966.9	1966.2	1965.5	1964.8	1962.8	1959.3	1955.8	1952.4	1948.9	1952.0
7.5°	1949.5	1948.8	1948.1	1947.4	1946.7	1944.5	1940.7	1936.9	1933.1	1929.3	1932.3
10°	1933.3	1932.6	1931.9	1931.2	1930.5	1928.3	1924.5	1920.7	1916.8	1913.0	1915.8
12.5°	1913.3	1912.1	1910.9	1909.6	1908.4	1906.0	1902.4	1898.9	1895.4	1891.8	1894.1
15°	1875.6	1874.6	1873.5	1872.5	1871.5	1869.0	1865.2	1861.4	1857.6	1853.8	1855.5
17.5°	1832.3	1830.8	1829.2	1827.7	1826.2	1823.4	1819.5	1815.5	1811.6	1807.6	1809.8
20°	1796.1	1795.4	1794.7	1794.0	1793.3	1790.7	1786.2	1781.7	1777.2	1772.7	1775.1
22.5°	1759.9	1758.7	1757.4	1756.2	1754.9	1752.2	1748.0	1743.8	1739.5	1735.3	1736.9
25°	1702.6	1700.8	1699.1	1697.4	1695.6	1692.5	1688.0	1683.5	1679.0	1674.5	1675.2
27.5°	1635.5	1634.5	1633.4	1632.4	1631.4	1628.5	1623.9	1619.2	1614.6	1609.9	1610.1
30°	1591.9	1590.8	1589.8	1588.7	1587.7	1584.6	1579.4	1574.2	1569.0	1563.8	1563.1
32.5°	1544.5	1542.9	1541.3	1539.7	1538.1	1535.0	1530.3	1525.7	1521.0	1516.4	1515.2
35°	1470.2	1468.9	1467.5	1466.1	1464.7	1461.6	1456.7	1451.9	1447.0	1442.2	1440.5
37.5°	1393.2	1391.5	1389.8	1388.0	1386.3	1383.1	1378.6	1374.0	1369.4	1364.9	1362.3
40°	1340.8	1339.1	1337.4	1335.6	1333.9	1330.6	1325.8	1320.9	1316.1	1311.2	1308.1
42.5°	1284.7	1283.3	1281.8	1280.3	1278.9	1275.7	1270.9	1266.0	1261.2	1256.3	1253.5
45°	1203.6	1202.3	1200.9	1199.5	1198.1	1195.3	1191.2	1187.0	1182.9	1178.7	1174.5
47.5°	1116.3	1116.4	1116.5	1116.5	1116.6	1114.1	1109.2	1104.2	1099.2	1094.2	1090.0
50°	1060.2	1059.2	1058.1	1057.1	1056.0	1053.4	1049.3	1045.1	1041.0	1036.8	1032.3
52.5°	1002.8	1002.1	1001.3	1000.5	999.8	997.2	992.7	988.3	983.9	979.4	975.5
55°	916.8	915.7	914.7	913.6	912.6	909.7	904.8	900.0	895.1	890.3	887.1
57.5°	826.0	825.5	824.9	824.4	823.8	821.5	817.4	813.3	809.2	805.1	801.1
60°	768.6	767.3	765.9	764.5	763.1	760.5	756.7	752.9	749.1	745.3	741.8
62.5°	708.8	707.7	706.6	705.4	704.3	702.2	698.9	695.6	692.4	689.1	685.4
65°	619.0	618.3	617.6	616.9	616.2	613.9	610.1	606.3	602.5	598.7	595.6
67.5°	532.0	530.5	529.1	527.6	526.2	524.0	521.2	518.3	515.5	512.6	510.0
70°	477.1	475.4	473.6	471.9	470.2	467.7	464.6	461.5	458.4	455.3	453.2
72.5°	417.2	416.0	414.9	413.7	412.5	410.9	408.9	406.9	404.9	402.9	400.5
75°	329.0	328.3	327.6	326.9	326.2	325.0	323.3	321.5	319.8	318.1	317.0
77.5°	247.6	247.3	247.0	246.8	246.5	245.9	244.9	243.9	242.9	242.0	241.4
80°	196.4	196.4	196.4	196.4	196.4	196.1	195.4	194.7	194.0	193.3	193.0
82.5°	151.5	151.0	150.4	149.9	149.3	149.0	148.8	148.7	148.6	148.4	147.8
85°	85.8	86.1	86.4	86.8	87.1	87.3	87.3	87.3	87.3	87.3	87.0
87.5°	33.8	33.9	34.1	34.2	34.4	34.4	34.3	34.2	34.0	33.9	34.0
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.2	7.7
92.5°	7.0	6.4	5.8	5.3	4.7	4.7	5.4	6.0	6.6	7.2	7.7
95°	25.8	25.5	25.2	24.9	24.6	22.5	18.7	14.9	11.1	7.2	7.7
97.5°	53.8	54.4	54.9	55.5	56.0	52.5	44.9	37.4	29.8	22.3	19.4
100°	75.5	75.9	76.2	76.5	76.8	77.1	77.5	77.9	78.3	78.7	63.7
102.5°	97.6	98.0	98.4	98.8	99.2	99.5	99.7	99.9	100.2	100.4	97.6
105°	133.0	133.4	133.8	134.2	134.6	134.8	134.8	134.8	134.8	134.8	134.8
107.5°	169.7	169.7	169.7	169.7	169.7	169.8	170.0	170.2	170.4	170.6	170.7
110°	193.6	193.6	193.6	193.6	193.6	193.7	193.9	194.1	194.3	194.5	194.2



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	216.1	216.3	216.5	216.8	217.0	217.2	217.3	217.5	217.6	217.7	217.3
115°	249.7	250.2	250.7	251.2	251.7	252.0	252.1	252.2	252.3	252.4	252.0
117.5°	284.6	284.5	284.5	284.5	284.5	284.7	285.0	285.4	285.8	286.2	285.7
120°	306.3	306.2	306.1	306.0	305.9	306.0	306.3	306.6	306.9	307.2	307.0
122.5°	325.5	325.8	326.2	326.6	327.0	327.2	327.4	327.5	327.7	327.8	327.6
125°	355.1	355.8	356.5	357.2	357.9	358.3	358.3	358.3	358.3	358.3	357.9
127.5°	383.4	384.0	384.5	385.0	385.5	385.7	385.6	385.6	385.5	385.4	385.2
130°	400.8	401.3	401.8	402.3	402.8	403.1	403.2	403.3	403.4	403.5	403.2
132.5°	418.2	418.8	419.4	419.9	420.5	420.7	420.5	420.3	420.0	419.8	419.8
135°	442.9	443.5	444.1	444.7	445.3	445.5	445.3	445.1	444.9	444.7	444.5
137.5°	465.6	466.1	466.6	467.2	467.7	467.9	467.7	467.5	467.3	467.1	467.2
140°	480.4	480.6	480.8	481.0	481.2	481.3	481.2	481.1	481.0	480.9	481.1
142.5°	493.8	494.0	494.1	494.2	494.3	494.4	494.6	494.7	494.9	495.0	495.0
145°	513.5	513.7	513.9	514.1	514.3	514.4	514.4	514.4	514.4	514.4	514.5
147.5°	530.7	530.6	530.6	530.5	530.5	530.5	530.7	530.8	530.9	531.0	531.1
150°	541.5	541.3	541.1	540.9	540.7	540.7	540.9	541.1	541.3	541.5	541.7
152.5°	552.0	551.6	551.1	550.7	550.2	550.1	550.3	550.5	550.7	550.9	551.1
155°	565.5	564.9	564.3	563.7	563.1	562.9	563.1	563.3	563.5	563.7	564.0
157.5°	575.9	575.5	575.2	574.8	574.4	574.3	574.3	574.3	574.3	574.4	574.7
160°	583.1	582.5	581.9	581.3	580.7	580.5	580.6	580.7	580.8	580.9	581.3
162.5°	588.9	588.3	587.7	587.1	586.5	586.3	586.4	586.5	586.6	586.7	587.2
165°	596.7	596.1	595.5	594.9	594.3	594.0	594.1	594.2	594.3	594.4	595.0
167.5°	602.5	601.9	601.3	600.6	600.0	599.7	599.8	599.9	600.0	600.1	600.9
170°	605.8	605.1	604.3	603.6	602.9	602.6	602.7	602.8	602.9	603.0	603.8
172.5°	607.9	607.2	606.5	605.8	605.1	604.9	605.0	605.2	605.4	605.6	606.3
175°	610.3	609.7	609.1	608.5	607.9	607.6	607.7	607.8	607.9	608.0	608.8
177.5°	611.4	610.9	610.4	609.9	609.4	609.2	609.3	609.4	609.5	609.6	610.1
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7	1970.7
2.5°	1965.0	1967.8	1970.6	1971.8	1971.6	1971.3	1971.0	1970.7
5°	1955.1	1958.3	1961.4	1962.8	1962.4	1962.1	1961.7	1961.4
7.5°	1935.3	1938.4	1941.4	1942.8	1942.5	1942.1	1941.8	1941.4
10°	1918.6	1921.4	1924.1	1925.3	1925.0	1924.6	1924.3	1924.0
12.5°	1896.3	1898.5	1900.7	1901.8	1901.7	1901.6	1901.6	1901.5
15°	1857.3	1859.0	1860.7	1861.6	1861.6	1861.6	1861.6	1861.6
17.5°	1811.9	1814.1	1816.2	1816.4	1814.7	1813.0	1811.2	1809.5
20°	1777.6	1780.0	1782.4	1782.8	1781.0	1779.3	1777.6	1775.8
22.5°	1738.5	1740.1	1741.7	1741.9	1740.7	1739.5	1738.3	1737.2
25°	1675.9	1676.6	1677.3	1677.1	1676.1	1675.0	1674.0	1672.9
27.5°	1610.2	1610.4	1610.5	1610.0	1609.0	1608.0	1606.9	1605.9
30°	1562.4	1561.7	1561.0	1560.2	1559.1	1558.1	1557.0	1556.0
32.5°	1513.9	1512.7	1511.4	1509.8	1508.0	1506.1	1504.2	1502.4
35°	1438.7	1437.0	1435.3	1433.0	1430.2	1427.5	1424.7	1421.9
37.5°	1359.7	1357.2	1354.6	1352.5	1350.9	1349.3	1347.7	1346.1
40°	1305.0	1301.9	1298.7	1296.7	1295.6	1294.6	1293.5	1292.5
42.5°	1250.7	1247.8	1245.0	1242.8	1241.2	1239.6	1238.0	1236.4
45°	1170.4	1166.2	1162.1	1159.5	1158.4	1157.4	1156.3	1155.3
47.5°	1085.7	1081.5	1077.3	1074.0	1071.5	1069.1	1066.7	1064.3
50°	1027.8	1023.3	1018.8	1015.3	1012.9	1010.5	1008.1	1005.6
52.5°	971.5	967.6	963.6	960.3	957.6	954.9	952.2	949.5
55°	884.0	880.9	877.8	875.0	872.6	870.2	867.7	865.3
57.5°	797.1	793.1	789.1	786.4	785.1	783.8	782.4	781.1
60°	738.3	734.9	731.4	728.5	726.0	723.6	721.2	718.8
62.5°	681.6	677.9	674.2	671.4	669.5	667.6	665.7	663.9
65°	592.5	589.3	586.2	584.0	582.6	581.2	579.8	578.4
67.5°	507.4	504.7	502.1	500.4	499.5	498.7	497.9	497.0
70°	451.1	449.0	446.9	445.2	443.8	442.4	441.1	439.7
72.5°	398.2	395.8	393.5	391.6	390.2	388.8	387.4	386.0
75°	316.0	314.9	313.9	312.7	311.3	309.9	308.5	307.1
77.5°	240.7	240.1	239.5	238.7	237.7	236.7	235.8	234.8
80°	192.6	192.3	191.9	191.4	190.7	190.0	189.3	188.7
82.5°	147.2	146.6	145.9	145.6	145.4	145.3	145.1	145.0
85°	86.6	86.3	85.9	85.4	84.7	84.0	83.3	82.6
87.5°	34.1	34.2	34.3	34.1	33.6	33.1	32.6	32.1
90°	8.2	8.7	9.2	9.7	10.0	10.3	10.6	10.9
92.5°	8.2	8.7	9.2	9.6	9.7	9.9	10.0	10.1
95°	8.2	8.7	9.2	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.8	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.8	33.8	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.8	91.9	89.1	84.3	77.4	70.6	63.7	56.9
105°	134.8	134.8	134.8	134.8	134.7	134.6	134.5	134.4
107.5°	170.7	170.7	170.7	170.6	170.3	170.0	169.7	169.4
110°	193.9	193.6	193.3	193.2	193.3	193.4	193.5	193.6



TEST NUMBER: P333464

CATALOG NUMBER: S125DIW-S1270D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.9	216.5	216.2	215.9	215.8	215.6	215.5	215.3
115°	251.6	251.2	250.8	250.3	249.7	249.1	248.5	247.9
117.5°	285.1	284.6	284.1	283.7	283.4	283.2	282.9	282.7
120°	306.8	306.6	306.4	306.0	305.5	305.0	304.5	304.0
122.5°	327.4	327.2	327.0	326.6	326.0	325.4	324.9	324.3
125°	357.5	357.1	356.7	356.3	356.0	355.7	355.4	355.1
127.5°	385.0	384.8	384.6	384.1	383.3	382.6	381.8	381.1
130°	402.9	402.6	402.3	401.9	401.4	400.9	400.4	399.9
132.5°	419.7	419.6	419.6	419.3	418.8	418.3	417.8	417.3
135°	444.3	444.1	443.9	443.5	442.9	442.3	441.7	441.1
137.5°	467.2	467.3	467.3	467.1	466.5	466.0	465.5	465.0
140°	481.3	481.5	481.7	481.5	480.9	480.3	479.7	479.1
142.5°	495.1	495.1	495.2	494.9	494.3	493.7	493.1	492.5
145°	514.6	514.7	514.8	514.5	513.9	513.3	512.7	512.1
147.5°	531.3	531.4	531.5	531.2	530.5	529.8	529.0	528.3
150°	541.9	542.1	542.3	542.0	541.2	540.4	539.6	538.8
152.5°	551.3	551.5	551.7	551.5	550.7	550.0	549.3	548.6
155°	564.3	564.6	564.9	564.6	563.8	563.0	562.2	561.4
157.5°	575.0	575.3	575.6	575.4	574.6	573.8	573.0	572.2
160°	581.7	582.1	582.5	582.3	581.5	580.7	579.9	579.1
162.5°	587.8	588.4	588.9	588.8	587.9	587.0	586.1	585.2
165°	595.7	596.3	596.9	596.8	596.0	595.1	594.3	593.5
167.5°	601.6	602.3	603.0	603.0	602.0	601.1	600.2	599.3
170°	604.6	605.5	606.3	606.2	605.3	604.4	603.5	602.6
172.5°	607.0	607.7	608.5	608.4	607.5	606.6	605.7	604.8
175°	609.6	610.4	611.2	611.2	610.3	609.4	608.5	607.6
177.5°	610.7	611.2	611.8	611.8	611.1	610.5	609.8	609.2
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3

(END OF REPORT)