

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333466

Luminaire Tested: **S125DIW-S1270D770U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333466
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S1270D770U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8254.0 lumens
Efficiency: N/A
Efficacy: 138.0 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	63
1	101	97	93	89	95	91	87	84	80	77	75	70	68	66	60	59	58	54
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	54	51	49	45
3	84	75	67	61	79	70	64	59	62	57	53	55	51	47	48	45	42	39
4	77	66	58	52	72	63	55	50	55	50	45	49	44	41	43	39	36	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	29
6	65	53	45	39	61	50	43	38	45	39	34	40	35	31	35	31	28	25
7	61	48	40	34	57	46	38	33	41	35	30	36	31	28	32	28	25	23
8	56	44	36	31	53	42	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18
10	49	37	29	25	46	35	28	24	31	26	22	28	23	20	25	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11861	11861	11861	11861
5°	13736	11902	10421	11902
10°	15980	11840	9130	11840
15°	17690	11753	8423	11753
20°	19801	11615	7854	11615
25°	23197	11460	7577	11460
30°	25055	11307	7337	11307
35°	20601	11020	7179	11020
40°	14643	10620	7006	10620
45°	11249	10082	6906	10082
50°	9602	9414	6893	9414
55°	8550	8760	6952	8760
60°	7713	8045	7129	8045
65°	7124	7326	7314	7326
70°	6477	6579	7419	6579
75°	5719	5797	7354	5797
80°	4813	4727	6724	4727
85°	3809	3409	5432	3409



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.8	2.1
10°-20°	526.4	6.4
20°-30°	854.8	10.4
30°-40°	1042.7	12.6
40°-50°	948.5	11.5
50°-60°	755.5	9.2
60°-70°	526.2	6.4
70°-80°	280.6	3.4
80°-90°	72.9	0.9
90°-100°	36.3	0.4
100°-110°	223.9	2.7
110°-120°	406.0	4.9
120°-130°	521.1	6.3
130°-140°	560.5	6.8
140°-150°	526.1	6.4
150°-160°	425.5	5.2
160°-170°	275.2	3.3
170°-180°	94.9	1.2
0°-30°	1558.0	18.9
0°-40°	2600.7	31.5
0°-60°	4304.7	52.2
0°-90°	5184.5	62.8
90°-120°	666.2	8.1
90°-150°	2273.8	27.5
90°-180°	3069.0	37.2
0°-180°	8254.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1837	1837	1837	1837	1837	
5°	2119	1836	1607	1836	2119	214
15°	2646	1758	1260	1758	2646	757
25°	3255	1608	1063	1608	3255	1487
35°	2613	1398	910	1398	2613	1599
45°	1232	1104	756	1104	1232	986
55°	759	778	617	778	759	684
65°	466	479	479	479	466	463
75°	229	232	295	232	229	247
85°	51	46	73	46	51	60
90°	18	1	18	1	18	10
95°	16	42	16	42	16	13
105°	220	218	220	218	220	199
115°	406	409	406	409	406	403
125°	582	582	582	582	582	517
135°	722	725	722	725	722	558
145°	839	841	839	841	839	524
155°	920	926	920	926	920	424
165°	972	977	972	977	972	274
175°	995	1000	995	1000	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1942.6	1940.1	1937.6	1932.6	1936.3	1925.7	1920.7	1912.0	1901.4	1897.7	1893.3
5°	2118.7	2122.6	2126.5	2110.2	2111.7	2100.8	2075.9	2055.6	2039.2	2018.2	2003.4
7.5°	2330.8	2321.6	2320.8	2310.2	2292.0	2277.3	2251.1	2217.7	2185.5	2148.7	2118.3
10°	2436.8	2437.6	2430.6	2418.1	2398.6	2384.6	2350.3	2317.5	2277.8	2231.0	2197.5
12.5°	2516.6	2519.9	2511.0	2494.2	2484.6	2453.2	2426.3	2387.4	2340.1	2302.7	2251.7
15°	2645.7	2637.1	2630.9	2609.8	2593.5	2560.7	2517.9	2477.3	2425.9	2378.3	2330.8
17.5°	2770.1	2777.0	2765.3	2746.1	2695.3	2657.1	2599.6	2544.0	2480.0	2416.2	2359.5
20°	2881.1	2887.4	2869.4	2835.9	2775.1	2736.9	2661.3	2589.6	2515.5	2433.7	2371.3
22.5°	3019.6	3014.6	2990.4	2939.4	2886.7	2816.1	2734.3	2646.9	2554.2	2461.7	2378.8
25°	3255.3	3222.5	3207.7	3144.6	3075.2	2971.5	2859.3	2731.4	2616.1	2493.7	2387.7
27.5°	3385.9	3375.6	3359.1	3315.2	3242.2	3131.3	2999.0	2843.2	2680.5	2526.0	2387.2
30°	3359.7	3361.3	3362.9	3348.8	3302.1	3218.6	3086.9	2919.3	2726.0	2552.2	2391.6
32.5°	3127.8	3156.1	3183.3	3215.4	3228.5	3212.4	3129.9	2978.6	2779.6	2582.1	2389.1
35°	2613.0	2621.5	2709.6	2796.9	2915.4	3007.4	3069.0	3001.9	2834.3	2607.5	2386.1
37.5°	2037.4	2079.5	2140.4	2239.1	2410.1	2563.2	2760.1	2850.7	2796.6	2615.8	2380.7
40°	1736.8	1775.8	1815.5	1916.1	2060.3	2245.8	2469.5	2660.5	2704.9	2589.6	2362.0
42.5°	1504.8	1535.7	1579.8	1655.4	1775.9	1940.2	2154.0	2403.6	2557.1	2513.5	2322.7
45°	1231.6	1251.1	1285.4	1345.5	1432.8	1561.4	1750.0	2022.9	2260.6	2339.3	2229.4
47.5°	1054.2	1054.1	1080.7	1122.2	1185.2	1294.5	1434.0	1647.8	1901.7	2089.6	2080.9
50°	955.7	951.8	972.8	1008.7	1058.6	1131.1	1264.4	1435.1	1679.1	1891.9	1951.1
52.5°	870.9	871.3	884.3	910.8	952.6	1014.5	1114.1	1268.0	1476.4	1694.8	1806.5
55°	759.3	756.1	770.9	788.9	819.3	859.8	931.5	1049.2	1218.4	1433.5	1578.5
57.5°	657.0	665.6	671.5	684.0	709.2	736.3	796.8	883.2	1017.4	1202.0	1355.3
60°	597.1	605.7	610.4	622.8	643.1	666.5	713.3	783.4	896.5	1055.5	1207.5
62.5°	543.5	550.2	551.7	563.0	579.5	602.3	639.1	698.0	787.3	926.4	1075.3
65°	466.2	466.2	469.3	481.0	488.8	509.0	537.1	580.0	651.7	760.0	887.1
67.5°	391.6	395.4	394.6	399.7	406.9	422.7	442.8	478.2	531.3	610.4	712.0
70°	343.0	346.1	345.3	349.2	357.0	367.2	383.5	417.0	455.2	523.1	610.4
72.5°	299.3	300.6	298.6	303.7	308.4	317.3	335.5	353.4	389.1	446.4	518.1
75°	229.2	230.7	232.3	235.4	240.1	244.8	254.1	272.1	295.4	338.3	384.3
77.5°	171.8	168.8	172.6	172.1	174.8	178.4	186.6	196.1	215.3	242.4	278.0
80°	129.4	130.2	130.2	131.0	134.9	137.2	144.2	151.2	166.0	186.3	211.3
82.5°	94.5	96.5	95.3	96.7	99.9	101.6	105.5	111.3	119.9	135.8	153.9
85°	51.4	47.6	49.1	50.7	50.7	51.4	54.6	56.9	61.6	67.8	74.8
87.5°	18.5	19.7	20.2	20.1	20.6	20.5	22.8	22.7	24.4	26.1	28.3
90°	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5	12.7	11.9	10.7
92.5°	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5	12.7	11.9	10.8
95°	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5	12.7	11.9	18.1
97.5°	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2	31.8	36.5	48.8
100°	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9	104.4	128.9	128.3
102.5°	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2	159.9	164.5	164.1
105°	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6	279.5	279.5	279.2
110°	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6	318.1	318.6	318.3



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3	355.9	356.6	356.4
115°	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1	412.8	413.5	413.3
117.5°	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0	467.9	468.7	468.1
120°	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5	502.8	503.1	502.6
122.5°	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2	536.6	536.9	536.7
125°	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5	586.2	586.8	586.8
127.5°	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6	630.9	631.3	631.4
130°	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0	660.4	660.9	660.8
132.5°	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4	687.5	687.6	688.0
135°	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7	728.0	728.4	728.7
137.5°	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3	765.2	765.1	765.4
140°	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3	788.0	787.6	787.8
142.5°	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9	810.8	810.8	810.5
145°	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8	842.6	842.5	842.5
147.5°	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1	869.9	869.7	869.5
150°	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6	887.3	886.9	886.6
152.5°	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0	902.7	902.3	902.0
155°	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2	923.7	923.2	922.9
157.5°	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8	941.3	940.7	940.7
160°	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7	952.1	951.4	951.2
162.5°	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7	961.8	960.9	960.7
165°	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6	974.6	973.6	973.5
167.5°	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3	984.1	983.0	982.8
170°	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3	989.0	987.7	987.5
172.5°	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2	993.0	991.9	991.6
175°	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5	997.2	995.9	995.7
177.5°	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2	999.3	998.4	998.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1889.6	1885.2	1880.2	1871.5	1860.9	1855.3	1846.5	1840.9	1829.7	1820.3	1810.4
5°	1985.4	1965.2	1946.5	1922.3	1895.8	1878.6	1858.4	1835.8	1812.4	1788.2	1761.7
7.5°	2084.8	2048.9	2009.9	1968.0	1927.0	1889.2	1853.2	1817.8	1784.8	1744.9	1711.1
10°	2151.5	2106.3	2057.9	2001.0	1945.7	1897.4	1848.2	1805.4	1761.7	1714.9	1673.6
12.5°	2218.2	2158.0	2089.7	2027.2	1960.7	1902.3	1844.5	1789.8	1734.9	1683.1	1635.0
15°	2265.3	2212.3	2149.1	2060.3	1985.4	1905.2	1828.8	1757.8	1691.6	1633.9	1573.1
17.5°	2296.3	2228.0	2160.2	2074.9	1976.9	1887.1	1800.5	1719.3	1644.6	1571.5	1512.9
20°	2301.9	2231.8	2160.8	2077.4	1976.9	1874.0	1787.4	1690.0	1609.7	1534.1	1462.4
22.5°	2300.1	2220.5	2143.4	2057.5	1959.4	1864.6	1760.0	1660.7	1573.5	1499.2	1424.3
25°	2282.4	2197.5	2100.8	2014.3	1917.6	1817.1	1711.1	1608.2	1519.3	1434.3	1360.3
27.5°	2267.8	2157.6	2048.1	1947.2	1853.9	1761.7	1660.2	1554.8	1456.3	1370.2	1300.4
30°	2249.7	2128.9	2005.7	1900.5	1804.6	1714.9	1619.1	1516.2	1413.3	1329.1	1254.3
32.5°	2233.5	2092.7	1962.7	1848.1	1746.6	1659.4	1571.0	1473.1	1372.1	1286.7	1211.8
35°	2202.2	2039.2	1890.3	1760.9	1652.6	1562.9	1488.9	1397.7	1304.9	1222.3	1150.6
37.5°	2162.4	1969.1	1809.3	1673.6	1554.8	1460.4	1391.4	1321.4	1232.4	1152.8	1087.9
40°	2131.2	1919.2	1750.0	1611.3	1488.1	1389.9	1326.0	1259.7	1185.7	1111.6	1043.0
42.5°	2091.9	1874.3	1690.2	1540.8	1418.9	1323.2	1256.1	1199.8	1134.5	1065.5	1001.8
45°	2019.7	1792.9	1593.3	1432.8	1309.6	1215.3	1145.9	1103.8	1054.7	989.2	935.4
47.5°	1913.6	1695.1	1488.7	1323.0	1195.9	1108.5	1043.5	1003.1	968.5	919.8	871.0
50°	1819.4	1622.2	1413.3	1248.8	1121.7	1033.6	973.6	937.0	907.4	869.9	828.6
52.5°	1714.0	1530.5	1339.1	1176.5	1050.6	963.8	905.0	872.8	848.1	821.3	780.6
55°	1546.6	1390.7	1212.9	1058.6	942.4	857.5	806.0	778.0	757.7	737.4	712.5
57.5°	1362.1	1240.2	1082.8	941.7	834.7	757.4	709.4	682.1	666.3	655.9	641.2
60°	1232.4	1128.0	992.3	863.7	759.3	690.7	643.9	622.8	609.6	601.0	590.1
62.5°	1112.1	1026.3	900.7	783.3	691.9	627.0	585.3	564.8	552.2	548.0	539.0
65°	934.6	868.4	764.7	667.3	589.3	534.0	498.9	479.4	471.6	466.9	467.7
67.5°	759.9	719.5	636.2	553.1	490.9	444.5	416.4	401.5	397.6	391.3	391.2
70°	653.2	622.8	552.7	480.2	424.8	389.0	364.0	348.4	344.5	341.4	340.7
72.5°	559.1	532.4	471.6	413.5	363.7	332.2	311.7	302.3	295.9	294.0	293.9
75°	420.2	405.4	357.0	311.0	276.7	254.9	240.9	232.3	227.6	226.8	227.6
77.5°	298.7	285.8	255.1	222.5	200.8	184.3	172.4	169.5	164.2	164.3	163.5
80°	224.5	215.9	196.4	170.7	152.8	138.8	132.5	127.1	125.5	123.2	125.5
82.5°	162.8	153.6	140.3	123.9	109.1	100.7	94.5	92.8	91.8	90.7	91.2
85°	80.3	81.1	73.3	60.8	54.6	49.9	46.0	46.0	45.2	44.4	45.2
87.5°	29.3	27.9	25.1	23.0	19.6	17.5	16.6	17.0	15.4	15.0	15.9
90°	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4	10.5	9.6	8.6
95°	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2	41.7	41.2	40.8
97.5°	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2	89.1	90.0	90.8
100°	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7	124.2	124.7	125.2
102.5°	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9	160.5	161.2	161.8
105°	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8	218.5	219.2	219.8
107.5°	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0
110°	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9	354.3	354.7	355.1
115°	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0	409.8	410.7	411.5
117.5°	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1	466.0	466.0	466.0
120°	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6	501.5	501.3	501.1
122.5°	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0	533.7	534.3	534.9
125°	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7	582.8	584.0	585.1
127.5°	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0	628.9	629.7	630.5
130°	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5	657.3	658.1	659.0
132.5°	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9	685.9	686.9	687.8
135°	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4	726.4	727.4	728.4
137.5°	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6	763.5	764.3	765.2
140°	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9	787.2	787.6	787.9
142.5°	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8	809.0	809.2	809.4
145°	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0	841.3	841.7	842.0
147.5°	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2	869.1	869.0	869.0
150°	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	886.6	886.3	885.9
152.5°	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1	903.4	902.7	902.0
155°	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2	925.2	924.2	923.2
157.5°	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2	942.7	942.1	941.5
160°	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1	954.1	953.1	952.1
162.5°	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6	963.6	962.6	961.6
165°	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3	976.3	975.4	974.4
167.5°	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8	985.8	984.8	983.8
170°	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2	991.0	989.8	988.7
172.5°	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7	994.6	993.4	992.2
175°	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6	998.6	997.6	996.6
177.5°	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3	1000.5	999.8	999.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1804.7	1797.9	1792.3	1779.8	1772.9	1763.6	1756.1	1764.2	1755.5	1759.2	1753.6
5°	1748.5	1726.6	1711.1	1688.4	1669.0	1651.0	1637.8	1635.4	1629.2	1626.1	1616.7
7.5°	1680.8	1653.5	1626.7	1597.1	1572.1	1546.7	1530.5	1517.1	1508.2	1496.5	1488.6
10°	1640.9	1604.3	1573.1	1537.2	1506.0	1478.8	1456.9	1446.0	1435.9	1421.1	1415.6
12.5°	1591.6	1553.7	1515.7	1477.4	1447.4	1417.0	1398.3	1381.8	1374.8	1358.1	1356.4
15°	1532.5	1475.6	1438.2	1399.2	1357.9	1333.0	1317.4	1299.5	1291.7	1280.0	1271.4
17.5°	1462.1	1411.2	1364.5	1324.1	1288.7	1267.7	1248.3	1236.0	1222.6	1215.0	1200.9
20°	1410.9	1362.6	1315.8	1273.0	1245.7	1221.5	1205.9	1194.2	1180.2	1176.3	1162.3
22.5°	1367.9	1314.6	1269.7	1233.7	1203.9	1176.6	1159.8	1151.8	1142.2	1130.2	1127.3
25°	1297.9	1242.6	1204.4	1168.5	1142.0	1117.1	1105.4	1095.2	1085.9	1077.3	1074.2
27.5°	1237.4	1188.0	1142.6	1110.2	1087.1	1064.4	1054.1	1041.8	1034.9	1028.0	1019.6
30°	1195.0	1144.3	1104.6	1073.4	1048.5	1028.2	1017.3	1008.7	1002.5	996.2	991.6
32.5°	1151.4	1104.4	1065.9	1035.4	1010.4	995.1	985.5	979.4	972.5	965.0	959.1
35°	1093.7	1042.2	1004.8	978.3	958.8	947.1	936.2	930.7	923.0	923.0	916.7
37.5°	1028.7	984.2	951.2	927.0	909.5	899.1	887.3	883.5	878.5	875.2	873.1
40°	990.0	948.7	917.5	893.3	874.6	866.0	856.7	850.5	847.3	843.4	841.9
42.5°	950.1	910.6	880.7	858.4	842.2	834.9	826.1	821.8	815.5	810.4	809.5
45°	889.4	851.2	824.0	806.0	792.0	783.4	778.0	768.6	765.5	759.3	758.5
47.5°	831.9	795.3	768.5	753.8	741.5	734.5	725.9	716.5	713.0	709.8	709.5
50°	788.9	755.4	730.4	716.4	704.7	694.6	686.0	679.7	677.4	677.4	679.0
52.5°	745.2	716.7	695.5	678.3	667.3	656.5	648.6	644.8	641.2	645.0	647.8
55°	681.3	652.5	636.9	620.5	609.6	597.1	593.2	591.7	589.3	595.6	598.7
57.5°	613.6	593.4	575.1	558.9	549.1	541.9	536.6	535.7	540.1	543.0	553.1
60°	570.6	547.2	530.9	518.4	506.7	502.0	500.5	498.9	502.0	510.6	523.8
62.5°	523.2	504.2	486.6	477.2	468.6	460.9	460.5	461.5	467.7	477.5	490.8
65°	453.7	437.3	425.6	414.7	407.7	403.0	404.6	407.7	414.7	428.0	442.8
67.5°	383.1	371.8	361.4	352.5	345.8	345.8	347.4	352.0	360.3	375.6	389.1
70°	337.5	325.1	316.5	312.6	307.1	304.0	308.7	316.5	323.5	337.5	349.2
72.5°	292.0	281.4	274.7	272.1	269.7	267.2	268.8	277.2	286.7	300.7	314.3
75°	224.5	220.6	215.9	212.8	210.5	212.0	213.6	221.4	229.2	244.0	259.6
77.5°	163.9	159.8	157.0	156.2	155.0	155.7	160.1	165.9	173.5	184.3	196.1
80°	123.9	122.4	120.8	120.0	120.0	120.8	127.1	131.0	138.0	148.1	157.5
82.5°	90.3	89.3	89.0	88.9	89.5	89.6	93.4	98.5	104.3	111.9	120.0
85°	47.6	46.0	48.3	49.1	47.6	49.9	51.4	54.6	56.9	60.8	64.7
87.5°	16.8	18.3	17.9	18.7	19.0	20.5	20.0	22.7	24.1	25.5	25.0
90°	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5	14.3	15.1	15.8
92.5°	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5	14.3	15.1	15.7
95°	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5	14.3	15.1	15.6
97.5°	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2	22.5	17.9	15.6
100°	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9	55.3	30.8	18.2
102.5°	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2	150.6	145.9	138.0
105°	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.7
107.5°	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6	279.6	279.6	279.4
110°	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6	317.1	316.6	316.5



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3	354.7	354.0	353.6
115°	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1	411.5	410.8	410.0
117.5°	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0	466.2	465.3	464.7
120°	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5	502.1	501.8	501.2
122.5°	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2	535.9	535.6	534.9
125°	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5	584.9	584.2	583.6
127.5°	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6	630.2	629.9	629.1
130°	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0	659.5	659.0	658.3
132.5°	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4	687.3	687.2	686.8
135°	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7	727.4	727.1	726.4
137.5°	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3	765.3	765.4	765.0
140°	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3	788.6	789.0	788.6
142.5°	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9	811.0	811.0	810.6
145°	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8	843.0	843.1	842.7
147.5°	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1	870.3	870.5	870.0
150°	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6	887.9	888.3	887.8
152.5°	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0	903.3	903.7	903.2
155°	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2	924.7	925.2	924.8
157.5°	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8	942.3	942.8	942.4
160°	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7	953.4	954.0	953.7
162.5°	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7	963.6	964.6	964.3
165°	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6	976.6	977.6	977.4
167.5°	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3	986.5	987.7	987.6
170°	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3	991.7	993.0	992.9
172.5°	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2	995.4	996.6	996.4
175°	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5	999.8	1001.1	1001.0
177.5°	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2	1001.1	1002.1	1002.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1749.9	1754.2	1750.5	1755.5	1750.5	1754.2	1749.9	1753.6	1759.2	1755.5	1764.2
5°	1612.8	1605.8	1610.5	1607.4	1610.5	1605.8	1612.8	1616.7	1626.1	1629.2	1635.4
7.5°	1486.2	1479.5	1471.9	1468.3	1471.9	1479.5	1486.2	1488.6	1496.5	1508.2	1517.1
10°	1407.0	1398.5	1397.7	1392.2	1397.7	1398.5	1407.0	1415.6	1421.1	1435.9	1446.0
12.5°	1349.0	1341.1	1332.2	1329.9	1332.2	1341.1	1349.0	1356.4	1358.1	1374.8	1381.8
15°	1266.7	1260.5	1255.0	1259.7	1255.0	1260.5	1266.7	1271.4	1280.0	1291.7	1299.5
17.5°	1198.3	1193.1	1192.2	1186.4	1192.2	1193.1	1198.3	1200.9	1215.0	1222.6	1236.0
20°	1155.3	1151.4	1152.9	1142.8	1152.9	1151.4	1155.3	1162.3	1176.3	1180.2	1194.2
22.5°	1121.0	1113.3	1112.4	1110.4	1112.4	1113.3	1121.0	1127.3	1130.2	1142.2	1151.8
25°	1067.2	1063.3	1059.4	1063.3	1059.4	1063.3	1067.2	1074.2	1077.3	1085.9	1095.2
27.5°	1020.2	1015.6	1014.5	1014.9	1014.5	1015.6	1020.2	1019.6	1028.0	1034.9	1041.8
30°	991.6	983.8	984.5	983.8	984.5	983.8	991.6	991.6	996.2	1002.5	1008.7
32.5°	960.4	955.1	954.0	952.6	954.0	955.1	960.4	959.1	965.0	972.5	979.4
35°	914.4	914.4	910.5	910.5	910.5	914.4	914.4	916.7	923.0	923.0	930.7
37.5°	871.2	870.4	868.1	868.4	868.1	870.4	871.2	873.1	875.2	878.5	883.5
40°	838.8	838.0	835.6	831.0	835.6	838.0	838.8	841.9	843.4	847.3	850.5
42.5°	807.6	804.9	803.8	802.3	803.8	804.9	807.6	809.5	810.4	815.5	821.8
45°	758.5	758.5	756.9	756.1	756.9	758.5	758.5	758.5	759.3	765.5	768.6
47.5°	710.8	712.2	715.1	714.7	715.1	712.2	710.8	709.5	709.8	713.0	716.5
50°	682.1	682.9	685.2	686.0	685.2	682.9	682.1	679.0	677.4	677.4	679.7
52.5°	650.3	654.8	657.8	657.3	657.8	654.8	650.3	647.8	645.0	641.2	644.8
55°	605.7	611.1	616.6	617.4	616.6	611.1	605.7	598.7	595.6	589.3	591.7
57.5°	561.6	569.2	575.0	576.8	575.0	569.2	561.6	553.1	543.0	540.1	535.7
60°	531.6	541.8	548.8	551.9	548.8	541.8	531.6	523.8	510.6	502.0	498.9
62.5°	502.9	514.3	521.3	522.0	521.3	514.3	502.9	490.8	477.5	467.7	461.5
65°	456.0	467.7	473.9	478.6	473.9	467.7	456.0	442.8	428.0	414.7	407.7
67.5°	405.5	417.2	424.1	427.8	424.1	417.2	405.5	389.1	375.6	360.3	352.0
70°	368.7	380.4	389.8	392.9	389.8	380.4	368.7	349.2	337.5	323.5	316.5
72.5°	332.5	343.0	350.5	354.2	350.5	343.0	332.5	314.3	300.7	286.7	277.2
75°	269.7	283.7	290.8	294.7	290.8	283.7	269.7	259.6	244.0	229.2	221.4
77.5°	208.0	220.8	225.0	227.0	225.0	220.8	208.0	196.1	184.3	173.5	165.9
80°	166.8	174.6	180.1	180.8	180.1	174.6	166.8	157.5	148.1	138.0	131.0
82.5°	128.2	134.7	136.4	138.4	136.4	134.7	128.2	120.0	111.9	104.3	98.5
85°	70.2	73.3	74.1	73.3	74.1	73.3	70.2	64.7	60.8	56.9	54.6
87.5°	26.3	25.8	25.9	27.3	25.9	25.8	26.3	25.0	25.5	24.1	22.7
90°	16.3	16.8	17.3	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5
92.5°	15.9	16.1	16.4	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5
95°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5
97.5°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2
100°	17.5	16.9	16.2	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9
102.5°	126.8	115.6	104.4	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2
105°	220.6	220.4	220.2	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8
107.5°	278.9	278.4	277.9	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6
110°	316.6	316.8	317.0	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	353.4	353.2	352.9	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3
115°	409.0	408.0	407.0	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1
117.5°	464.2	463.8	463.4	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0
120°	500.4	499.6	498.8	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5
122.5°	534.0	533.0	532.1	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2
125°	583.1	582.6	582.2	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5
127.5°	627.8	626.6	625.4	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6
130°	657.5	656.7	655.8	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0
132.5°	685.9	685.1	684.3	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4
135°	725.4	724.4	723.4	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7
137.5°	764.1	763.3	762.4	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3
140°	787.6	786.7	785.7	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3
142.5°	809.6	808.6	807.6	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9
145°	841.7	840.7	839.8	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8
147.5°	868.9	867.7	866.5	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1
150°	886.4	885.1	883.8	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6
152.5°	902.0	900.9	899.7	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0
155°	923.5	922.2	920.9	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2
157.5°	941.1	939.8	938.5	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8
160°	952.4	951.1	949.8	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7
162.5°	962.9	961.4	960.0	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7
165°	976.1	974.8	973.5	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6
167.5°	986.1	984.6	983.1	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3
170°	991.4	989.9	988.4	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3
172.5°	995.0	993.5	992.0	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2
175°	999.6	998.1	996.6	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5
177.5°	1000.9	999.9	998.8	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1756.1	1763.6	1772.9	1779.8	1792.3	1797.9	1804.7	1810.4	1820.3	1829.7	1840.9
5°	1637.8	1651.0	1669.0	1688.4	1711.1	1726.6	1748.5	1761.7	1788.2	1812.4	1835.8
7.5°	1530.5	1546.7	1572.1	1597.1	1626.7	1653.5	1680.8	1711.1	1744.9	1784.8	1817.8
10°	1456.9	1478.8	1506.0	1537.2	1573.1	1604.3	1640.9	1673.6	1714.9	1761.7	1805.4
12.5°	1398.3	1417.0	1447.4	1477.4	1515.7	1553.7	1591.6	1635.0	1683.1	1734.9	1789.8
15°	1317.4	1333.0	1357.9	1399.2	1438.2	1475.6	1532.5	1573.1	1633.9	1691.6	1757.8
17.5°	1248.3	1267.7	1288.7	1324.1	1364.5	1411.2	1462.1	1512.9	1571.5	1644.6	1719.3
20°	1205.9	1221.5	1245.7	1273.0	1315.8	1362.6	1410.9	1462.4	1534.1	1609.7	1690.0
22.5°	1159.8	1176.6	1203.9	1233.7	1269.7	1314.6	1367.9	1424.3	1499.2	1573.5	1660.7
25°	1105.4	1117.1	1142.0	1168.5	1204.4	1242.6	1297.9	1360.3	1434.3	1519.3	1608.2
27.5°	1054.1	1064.4	1087.1	1110.2	1142.6	1188.0	1237.4	1300.4	1370.2	1456.3	1554.8
30°	1017.3	1028.2	1048.5	1073.4	1104.6	1144.3	1195.0	1254.3	1329.1	1413.3	1516.2
32.5°	985.5	995.1	1010.4	1035.4	1065.9	1104.4	1151.4	1211.8	1286.7	1372.1	1473.1
35°	936.2	947.1	958.8	978.3	1004.8	1042.2	1093.7	1150.6	1222.3	1304.9	1397.7
37.5°	887.3	899.1	909.5	927.0	951.2	984.2	1028.7	1087.9	1152.8	1232.4	1321.4
40°	856.7	866.0	874.6	893.3	917.5	948.7	990.0	1043.0	1111.6	1185.7	1259.7
42.5°	826.1	834.9	842.2	858.4	880.7	910.6	950.1	1001.8	1065.5	1134.5	1199.8
45°	778.0	783.4	792.0	806.0	824.0	851.2	889.4	935.4	989.2	1054.7	1103.8
47.5°	725.9	734.5	741.5	753.8	768.5	795.3	831.9	871.0	919.8	968.5	1003.1
50°	686.0	694.6	704.7	716.4	730.4	755.4	788.9	828.6	869.9	907.4	937.0
52.5°	648.6	656.5	667.3	678.3	695.5	716.7	745.2	780.6	821.3	848.1	872.8
55°	593.2	597.1	609.6	620.5	636.9	652.5	681.3	712.5	737.4	757.7	778.0
57.5°	536.6	541.9	549.1	558.9	575.1	593.4	613.6	641.2	655.9	666.3	682.1
60°	500.5	502.0	506.7	518.4	530.9	547.2	570.6	590.1	601.0	609.6	622.8
62.5°	460.5	460.9	468.6	477.2	486.6	504.2	523.2	539.0	548.0	552.2	564.8
65°	404.6	403.0	407.7	414.7	425.6	437.3	453.7	467.7	466.9	471.6	479.4
67.5°	347.4	345.8	345.8	352.5	361.4	371.8	383.1	391.2	391.3	397.6	401.5
70°	308.7	304.0	307.1	312.6	316.5	325.1	337.5	340.7	341.4	344.5	348.4
72.5°	268.8	267.2	269.7	272.1	274.7	281.4	292.0	293.9	294.0	295.9	302.3
75°	213.6	212.0	210.5	212.8	215.9	220.6	224.5	227.6	226.8	227.6	232.3
77.5°	160.1	155.7	155.0	156.2	157.0	159.8	163.9	163.5	164.3	164.2	169.5
80°	127.1	120.8	120.0	120.0	120.8	122.4	123.9	125.5	123.2	125.5	127.1
82.5°	93.4	89.6	89.5	88.9	89.0	89.3	90.3	91.2	90.7	91.8	92.8
85°	51.4	49.9	47.6	49.1	48.3	46.0	47.6	45.2	44.4	45.2	46.0
87.5°	20.0	20.5	19.0	18.7	17.9	18.3	16.8	15.9	15.0	15.4	17.0
90°	12.7	11.9	10.7	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7
92.5°	12.7	11.9	10.8	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4
95°	12.7	11.9	18.1	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2
97.5°	31.8	36.5	48.8	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2
100°	104.4	128.9	128.3	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7
102.5°	159.9	164.5	164.1	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9
105°	220.8	220.8	220.8	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8
107.5°	279.5	279.5	279.2	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0
110°	318.1	318.6	318.3	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	355.9	356.6	356.4	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9
115°	412.8	413.5	413.3	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0
117.5°	467.9	468.7	468.1	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1
120°	502.8	503.1	502.6	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6
122.5°	536.6	536.9	536.7	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0
125°	586.2	586.8	586.8	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7
127.5°	630.9	631.3	631.4	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0
130°	660.4	660.9	660.8	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5
132.5°	687.5	687.6	688.0	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9
135°	728.0	728.4	728.7	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4
137.5°	765.2	765.1	765.4	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6
140°	788.0	787.6	787.8	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9
142.5°	810.8	810.8	810.5	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8
145°	842.6	842.5	842.5	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0
147.5°	869.9	869.7	869.5	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2
150°	887.3	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9
152.5°	902.7	902.3	902.0	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1
155°	923.7	923.2	922.9	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2
157.5°	941.3	940.7	940.7	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2
160°	952.1	951.4	951.2	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1
162.5°	961.8	960.9	960.7	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6
165°	974.6	973.6	973.5	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3
167.5°	984.1	983.0	982.8	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8
170°	989.0	987.7	987.5	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2
172.5°	993.0	991.9	991.6	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7
175°	997.2	995.9	995.7	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6
177.5°	999.3	998.4	998.2	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1846.5	1855.3	1860.9	1871.5	1880.2	1885.2	1889.6	1893.3	1897.7	1901.4	1912.0
5°	1858.4	1878.6	1895.8	1922.3	1946.5	1965.2	1985.4	2003.4	2018.2	2039.2	2055.6
7.5°	1853.2	1889.2	1927.0	1968.0	2009.9	2048.9	2084.8	2118.3	2148.7	2185.5	2217.7
10°	1848.2	1897.4	1945.7	2001.0	2057.9	2106.3	2151.5	2197.5	2231.0	2277.8	2317.5
12.5°	1844.5	1902.3	1960.7	2027.2	2089.7	2158.0	2218.2	2251.7	2302.7	2340.1	2387.4
15°	1828.8	1905.2	1985.4	2060.3	2149.1	2212.3	2265.3	2330.8	2378.3	2425.9	2477.3
17.5°	1800.5	1887.1	1976.9	2074.9	2160.2	2228.0	2296.3	2359.5	2416.2	2480.0	2544.0
20°	1787.4	1874.0	1976.9	2077.4	2160.8	2231.8	2301.9	2371.3	2433.7	2515.5	2589.6
22.5°	1760.0	1864.6	1959.4	2057.5	2143.4	2220.5	2300.1	2378.8	2461.7	2554.2	2646.9
25°	1711.1	1817.1	1917.6	2014.3	2100.8	2197.5	2282.4	2387.7	2493.7	2616.1	2731.4
27.5°	1660.2	1761.7	1853.9	1947.2	2048.1	2157.6	2267.8	2387.2	2526.0	2680.5	2843.2
30°	1619.1	1714.9	1804.6	1900.5	2005.7	2128.9	2249.7	2391.6	2552.2	2726.0	2919.3
32.5°	1571.0	1659.4	1746.6	1848.1	1962.7	2092.7	2233.5	2389.1	2582.1	2779.6	2978.6
35°	1488.9	1562.9	1652.6	1760.9	1890.3	2039.2	2202.2	2386.1	2607.5	2834.3	3001.9
37.5°	1391.4	1460.4	1554.8	1673.6	1809.3	1969.1	2162.4	2380.7	2615.8	2796.6	2850.7
40°	1326.0	1389.9	1488.1	1611.3	1750.0	1919.2	2131.2	2362.0	2589.6	2704.9	2660.5
42.5°	1256.1	1323.2	1418.9	1540.8	1690.2	1874.3	2091.9	2322.7	2513.5	2557.1	2403.6
45°	1145.9	1215.3	1309.6	1432.8	1593.3	1792.9	2019.7	2229.4	2339.3	2260.6	2022.9
47.5°	1043.5	1108.5	1195.9	1323.0	1488.7	1695.1	1913.6	2080.9	2089.6	1901.7	1647.8
50°	973.6	1033.6	1121.7	1248.8	1413.3	1622.2	1819.4	1951.1	1891.9	1679.1	1435.1
52.5°	905.0	963.8	1050.6	1176.5	1339.1	1530.5	1714.0	1806.5	1694.8	1476.4	1268.0
55°	806.0	857.5	942.4	1058.6	1212.9	1390.7	1546.6	1578.5	1433.5	1218.4	1049.2
57.5°	709.4	757.4	834.7	941.7	1082.8	1240.2	1362.1	1355.3	1202.0	1017.4	883.2
60°	643.9	690.7	759.3	863.7	992.3	1128.0	1232.4	1207.5	1055.5	896.5	783.4
62.5°	585.3	627.0	691.9	783.3	900.7	1026.3	1112.1	1075.3	926.4	787.3	698.0
65°	498.9	534.0	589.3	667.3	764.7	868.4	934.6	887.1	760.0	651.7	580.0
67.5°	416.4	444.5	490.9	553.1	636.2	719.5	759.9	712.0	610.4	531.3	478.2
70°	364.0	389.0	424.8	480.2	552.7	622.8	653.2	610.4	523.1	455.2	417.0
72.5°	311.7	332.2	363.7	413.5	471.6	532.4	559.1	518.1	446.4	389.1	353.4
75°	240.9	254.9	276.7	311.0	357.0	405.4	420.2	384.3	338.3	295.4	272.1
77.5°	172.4	184.3	200.8	222.5	255.1	285.8	298.7	278.0	242.4	215.3	196.1
80°	132.5	138.8	152.8	170.7	196.4	215.9	224.5	211.3	186.3	166.0	151.2
82.5°	94.5	100.7	109.1	123.9	140.3	153.6	162.8	153.9	135.8	119.9	111.3
85°	46.0	49.9	54.6	60.8	73.3	81.1	80.3	74.8	67.8	61.6	56.9
87.5°	16.6	17.5	19.6	23.0	25.1	27.9	29.3	28.3	26.1	24.4	22.7
90°	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5
92.5°	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5
95°	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5
97.5°	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2
100°	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9
102.5°	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2
105°	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6
110°	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3
115°	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1
117.5°	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0
120°	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5
122.5°	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2
125°	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5
127.5°	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6
130°	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0
132.5°	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4
135°	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7
137.5°	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3
140°	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3
142.5°	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9
145°	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8
147.5°	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1
150°	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6
152.5°	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0
155°	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2
157.5°	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8
160°	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7
162.5°	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7
165°	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6
167.5°	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3
170°	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3
172.5°	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2
175°	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5
177.5°	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6	1836.6
2.5°	1920.7	1925.7	1936.3	1932.6	1937.6	1940.1	1942.6
5°	2075.9	2100.8	2111.7	2110.2	2126.5	2122.6	2118.7
7.5°	2251.1	2277.3	2292.0	2310.2	2320.8	2321.6	2330.8
10°	2350.3	2384.6	2398.6	2418.1	2430.6	2437.6	2436.8
12.5°	2426.3	2453.2	2484.6	2494.2	2511.0	2519.9	2516.6
15°	2517.9	2560.7	2593.5	2609.8	2630.9	2637.1	2645.7
17.5°	2599.6	2657.1	2695.3	2746.1	2765.3	2777.0	2770.1
20°	2661.3	2736.9	2775.1	2835.9	2869.4	2887.4	2881.1
22.5°	2734.3	2816.1	2886.7	2939.4	2990.4	3014.6	3019.6
25°	2859.3	2971.5	3075.2	3144.6	3207.7	3222.5	3255.3
27.5°	2999.0	3131.3	3242.2	3315.2	3359.1	3375.6	3385.9
30°	3086.9	3218.6	3302.1	3348.8	3362.9	3361.3	3359.7
32.5°	3129.9	3212.4	3228.5	3215.4	3183.3	3156.1	3127.8
35°	3069.0	3007.4	2915.4	2796.9	2709.6	2621.5	2613.0
37.5°	2760.1	2563.2	2410.1	2239.1	2140.4	2079.5	2037.4
40°	2469.5	2245.8	2060.3	1916.1	1815.5	1775.8	1736.8
42.5°	2154.0	1940.2	1775.9	1655.4	1579.8	1535.7	1504.8
45°	1750.0	1561.4	1432.8	1345.5	1285.4	1251.1	1231.6
47.5°	1434.0	1294.5	1185.2	1122.2	1080.7	1054.1	1054.2
50°	1264.4	1131.1	1058.6	1008.7	972.8	951.8	955.7
52.5°	1114.1	1014.5	952.6	910.8	884.3	871.3	870.9
55°	931.5	859.8	819.3	788.9	770.9	756.1	759.3
57.5°	796.8	736.3	709.2	684.0	671.5	665.6	657.0
60°	713.3	666.5	643.1	622.8	610.4	605.7	597.1
62.5°	639.1	602.3	579.5	563.0	551.7	550.2	543.5
65°	537.1	509.0	488.8	481.0	469.3	466.2	466.2
67.5°	442.8	422.7	406.9	399.7	394.6	395.4	391.6
70°	383.5	367.2	357.0	349.2	345.3	346.1	343.0
72.5°	335.5	317.3	308.4	303.7	298.6	300.6	299.3
75°	254.1	244.8	240.1	235.4	232.3	230.7	229.2
77.5°	186.6	178.4	174.8	172.1	172.6	168.8	171.8
80°	144.2	137.2	134.9	131.0	130.2	130.2	129.4
82.5°	105.5	101.6	99.9	96.7	95.3	96.5	94.5
85°	54.6	51.4	50.7	50.7	49.1	47.6	51.4
87.5°	22.8	20.5	20.6	20.1	20.2	19.7	18.5
90°	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.1	316.6	316.5	316.6	316.8	317.0	317.1



TEST NUMBER: P333466

CATALOG NUMBER: S125DIW-S1270D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)