

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333417-927

Luminaire Tested: **S125DIW-S850D1050U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333417-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1050U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1050 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5586.6 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29
4	74	63	55	49	68	58	51	46	50	44	40	41	37	34	34	31	28	25
5	68	56	48	42	62	52	45	40	44	39	34	37	33	30	30	27	25	21
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22	19
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19	17
8	54	41	34	28	49	38	31	27	33	27	23	28	24	20	23	20	17	15
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	13
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.1	1.8
10°-20°	277.0	5.0
20°-30°	409.0	7.3
30°-40°	477.2	8.5
40°-50°	479.3	8.6
50°-60°	420.7	7.5
60°-70°	313.5	5.6
70°-80°	179.3	3.2
80°-90°	54.4	1.0
90°-100°	69.1	1.2
100°-110°	204.0	3.7
110°-120°	345.5	6.2
120°-130°	454.7	8.1
130°-140°	509.6	9.1
140°-150°	499.4	8.9
150°-160°	419.5	7.5
160°-170°	278.8	5.0
170°-180°	97.6	1.7
0°-30°	784.0	14.0
0°-40°	1261.2	22.6
0°-60°	2161.2	38.7
0°-90°	2708.4	48.5
90°-120°	618.6	11.1
90°-150°	2082.3	37.3
90°-180°	2878.0	51.5
0°-180°	5586.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	7	13	17	19	5
95°	52	54	62	67	69	56
105°	183	187	192	196	199	195
115°	346	349	351	350	349	342
125°	505	509	510	509	508	452
135°	657	661	662	662	659	506
145°	795	799	801	801	799	497
155°	910	910	911	914	910	419
165°	990	988	989	992	987	279
175°	1029	1026	1026	1030	1025	98
180°	1031	1031	1031	1031	1031	



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	17.9	18.2	18.5	18.8	19.1	19.3	19.4	19.5	19.6	19.6	19.9
90°	0.8	2.2	3.6	5.1	6.5	7.8	9.1	10.4	11.6	12.8	13.7
92.5°	19.4	20.4	21.4	22.4	23.4	24.7	26.2	27.7	29.3	30.8	32.0
95°	52.2	52.5	52.9	53.2	53.6	54.7	56.5	58.2	60.0	61.8	63.1
97.5°	86.7	86.8	87.0	87.1	87.3	88.6	91.0	93.5	95.9	98.4	99.6
100°	112.4	112.4	112.4	112.4	112.4	113.5	115.8	118.2	120.5	122.8	124.5
102.5°	140.0	140.7	141.4	142.1	142.8	143.8	145.0	146.2	147.3	148.5	150.3
105°	183.0	183.9	184.8	185.7	186.6	187.6	188.6	189.7	190.8	191.9	192.9
107.5°	230.5	231.4	232.3	233.2	234.1	235.0	235.8	236.6	237.4	238.2	238.8
110°	263.2	264.2	265.1	265.9	266.9	267.6	268.1	268.6	269.2	269.7	270.2



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	296.7	297.1	297.6	298.1	298.5	299.1	299.8	300.5	301.1	301.8	302.1
115°	345.9	346.7	347.4	348.1	348.8	349.4	349.7	350.1	350.4	350.8	350.6
117.5°	395.4	395.7	396.0	396.3	396.7	397.0	397.4	397.7	398.0	398.3	398.5
120°	426.2	427.1	428.0	428.9	429.8	430.3	430.5	430.7	430.9	431.0	431.0
122.5°	459.6	459.9	460.3	460.6	460.9	461.3	461.8	462.2	462.7	463.2	463.0
125°	504.9	506.0	507.0	508.1	509.1	509.8	510.0	510.2	510.3	510.5	510.2
127.5°	553.0	553.7	554.3	554.8	555.5	555.9	556.1	556.3	556.5	556.7	556.6
130°	581.9	582.8	583.8	584.6	585.5	586.1	586.5	586.8	587.2	587.6	587.4
132.5°	610.9	612.3	613.8	615.2	616.7	617.4	617.3	617.3	617.2	617.1	617.0
135°	656.6	657.7	658.7	659.8	660.9	661.5	661.7	661.9	662.0	662.2	662.2
137.5°	699.7	700.7	701.7	702.7	703.8	704.5	704.9	705.3	705.7	706.1	706.2
140°	727.2	728.1	729.0	729.9	730.8	731.5	732.1	732.6	733.1	733.6	734.0
142.5°	754.9	755.6	756.4	757.1	757.9	758.6	759.2	759.9	760.6	761.3	761.4
145°	795.4	796.1	796.9	797.6	798.3	798.9	799.5	800.0	800.6	801.1	801.1
147.5°	833.1	833.5	833.9	834.2	834.6	835.0	835.4	835.8	836.3	836.7	837.2
150°	858.1	857.9	857.7	857.5	857.4	857.6	858.3	859.0	859.8	860.5	860.5
152.5°	878.6	878.8	879.1	879.4	879.6	879.9	880.2	880.4	880.7	881.1	881.5
155°	910.2	910.2	910.2	910.2	910.2	910.3	910.5	910.7	910.9	911.1	911.8
157.5°	938.5	938.1	937.7	937.3	936.9	936.8	937.0	937.2	937.4	937.5	938.3
160°	955.2	954.7	954.1	953.6	953.1	952.9	953.1	953.2	953.4	953.6	954.3
162.5°	969.9	969.6	969.2	968.8	968.4	968.2	968.3	968.3	968.4	968.4	969.2
165°	989.8	989.4	989.0	988.6	988.2	988.2	988.4	988.6	988.7	988.9	989.6
167.5°	1006.4	1005.7	1005.0	1004.2	1003.5	1003.2	1003.2	1003.2	1003.2	1003.2	1004.2
170°	1015.4	1014.7	1014.0	1013.3	1012.6	1012.2	1012.2	1012.2	1012.2	1012.2	1013.3
172.5°	1021.8	1021.1	1020.4	1019.7	1019.0	1018.6	1018.6	1018.6	1018.6	1018.6	1019.7
175°	1029.0	1028.3	1027.6	1026.9	1026.2	1025.8	1025.8	1025.8	1025.8	1025.8	1026.9
177.5°	1032.8	1032.1	1031.6	1031.0	1030.5	1030.1	1029.9	1029.8	1029.7	1029.5	1030.4
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	20.0	20.2	20.4	20.4	20.2	20.0	19.8	19.6
90°	14.7	15.5	16.4	17.1	17.7	18.2	18.7	19.3
92.5°	33.2	34.4	35.6	36.3	36.7	37.1	37.5	37.9
95°	64.3	65.5	66.8	67.6	68.0	68.3	68.7	69.0
97.5°	100.8	102.0	103.1	103.8	104.0	104.3	104.5	104.6
100°	126.0	127.6	129.2	130.2	130.6	130.9	131.3	131.7
102.5°	152.0	153.8	155.5	156.6	157.1	157.6	158.1	158.6
105°	194.0	195.0	196.1	196.9	197.5	198.0	198.5	199.1
107.5°	239.3	239.9	240.3	240.7	240.6	240.6	240.5	240.5
110°	270.8	271.3	271.9	272.0	271.9	271.6	271.5	271.3



TEST NUMBER: P333417-927

CATALOG NUMBER: S125DIW-S850D1050U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	302.3	302.5	302.8	302.8	302.5	302.1	301.8	301.5
115°	350.4	350.2	350.1	349.9	349.7	349.5	349.4	349.2
117.5°	398.5	398.7	398.9	398.5	397.8	397.1	396.4	395.7
120°	431.0	431.0	431.0	430.7	430.0	429.3	428.6	427.9
122.5°	462.9	462.7	462.6	462.2	461.7	461.1	460.5	459.9
125°	509.8	509.5	509.1	508.8	508.7	508.4	508.3	508.1
127.5°	556.3	556.2	556.0	555.8	555.4	555.1	554.7	554.4
130°	587.2	587.0	586.8	586.6	586.2	585.9	585.5	585.2
132.5°	616.7	616.6	616.4	616.1	615.5	615.1	614.6	614.0
135°	662.2	662.2	662.2	661.9	661.2	660.4	659.7	659.0
137.5°	706.5	706.7	706.9	706.5	705.7	704.8	703.9	703.0
140°	734.4	734.7	735.1	734.8	734.0	733.0	732.1	731.3
142.5°	761.7	761.9	762.2	761.8	760.9	760.0	759.1	758.2
145°	801.1	801.1	801.1	800.8	800.3	799.7	799.2	798.7
147.5°	837.6	838.0	838.4	838.0	836.9	835.6	834.4	833.2
150°	860.5	860.5	860.5	860.3	859.9	859.6	859.2	858.9
152.5°	881.9	882.3	882.7	882.6	882.0	881.4	880.7	880.0
155°	912.5	913.2	913.9	913.8	912.9	912.0	911.2	910.2
157.5°	939.0	939.7	940.4	940.2	939.0	937.8	936.6	935.5
160°	955.1	955.8	956.5	956.3	955.5	954.6	953.7	952.8
162.5°	970.1	970.9	971.8	971.7	970.7	969.6	968.6	967.6
165°	990.3	991.0	991.7	991.6	990.5	989.4	988.4	987.3
167.5°	1005.4	1006.4	1007.5	1007.5	1006.4	1005.3	1004.2	1003.1
170°	1014.3	1015.4	1016.4	1016.4	1015.1	1013.9	1012.6	1011.4
172.5°	1020.7	1021.8	1022.9	1022.9	1021.8	1020.6	1019.5	1018.4
175°	1027.9	1029.0	1030.2	1030.0	1028.8	1027.5	1026.3	1025.0
177.5°	1031.3	1032.1	1032.9	1032.8	1031.9	1030.9	1029.9	1028.9
180°	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4	1031.4

(END OF REPORT)