

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333418-927

Luminaire Tested: **S125DIW-S850D1340U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333418-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1340U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6986.5 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 61.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	91	88	84	87	83	80	77	68	66	64	54	53	51	41	40	39	33
2	87	80	74	69	79	73	68	64	60	56	53	48	45	43	36	35	33	28
3	80	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	29	24
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	27	25	21
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	24	22	18
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	24	21	19	16
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	16	14	11
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	6259	6259	6259	6259
5°	7248	6280	5499	6280
10°	8433	6248	4818	6248
15°	9335	6202	4444	6202
20°	10449	6129	4144	6129
25°	12241	6047	3998	6047
30°	13221	5967	3871	5967
35°	10871	5815	3788	5815
40°	7727	5604	3697	5604
45°	5936	5320	3644	5320
50°	5067	4967	3636	4967
55°	4512	4622	3668	4622
60°	4070	4246	3761	4246
65°	3759	3865	3859	3865
70°	3418	3473	3914	3473
75°	3019	3059	3880	3059
80°	2540	2492	3552	2492
85°	2016	1793	2868	1793



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.3	1.3
10°-20°	277.8	4.0
20°-30°	451.1	6.5
30°-40°	550.2	7.9
40°-50°	500.5	7.2
50°-60°	398.7	5.7
60°-70°	277.7	4.0
70°-80°	148.1	2.1
80°-90°	40.3	0.6
90°-100°	50.3	0.7
100°-110°	309.9	4.4
110°-120°	562.0	8.0
120°-130°	721.3	10.3
130°-140°	775.8	11.1
140°-150°	728.2	10.4
150°-160°	589.1	8.4
160°-170°	381.0	5.5
170°-180°	131.4	1.9
0°-30°	822.1	11.8
0°-40°	1372.3	19.6
0°-60°	2271.6	32.5
0°-90°	2737.6	39.2
90°-120°	922.2	13.2
90°-150°	3147.5	45.1
90°-180°	4249.0	60.8
0°-180°	6986.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	969	969	969	969	969	
5°	1118	969	848	969	1118	113
15°	1396	928	665	928	1396	400
25°	1718	849	561	849	1718	785
35°	1379	738	480	738	1379	844
45°	650	582	399	582	650	520
55°	401	410	326	410	401	361
65°	246	253	252	253	246	244
75°	121	123	156	123	121	130
85°	27	24	39	24	27	32
90°	25	1	25	1	25	12
95°	22	58	22	58	22	18
105°	305	302	305	302	305	275
115°	562	566	562	566	562	558
125°	805	805	805	805	805	716
135°	1000	1004	1000	1004	1000	772
145°	1161	1164	1161	1164	1161	725
155°	1273	1282	1273	1282	1273	587
165°	1346	1353	1346	1353	1346	380
175°	1377	1384	1377	1384	1377	131
180°	1384	1384	1384	1384	1384	



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1025.1	1023.7	1022.5	1019.8	1021.8	1016.2	1013.5	1008.9	1003.4	1001.4	999.1
5°	1118.0	1120.1	1122.1	1113.5	1114.4	1108.6	1095.4	1084.7	1076.1	1065.0	1057.2
7.5°	1229.9	1225.0	1224.6	1219.1	1209.4	1201.7	1187.9	1170.3	1153.3	1133.9	1117.8
10°	1285.9	1286.3	1282.5	1276.0	1265.7	1258.3	1240.2	1222.9	1202.0	1177.3	1159.6
12.5°	1328.0	1329.7	1325.0	1316.1	1311.1	1294.5	1280.3	1259.8	1234.9	1215.1	1188.2
15°	1396.1	1391.5	1388.3	1377.2	1368.6	1351.3	1328.6	1307.3	1280.1	1255.0	1229.9
17.5°	1461.7	1465.4	1459.2	1449.1	1422.3	1402.1	1371.7	1342.4	1308.7	1275.0	1245.1
20°	1520.4	1523.6	1514.2	1496.5	1464.4	1444.2	1404.3	1366.5	1327.4	1284.2	1251.3
22.5°	1593.4	1590.8	1578.0	1551.1	1523.3	1486.1	1442.8	1396.8	1347.8	1299.0	1255.3
25°	1717.8	1700.5	1692.7	1659.4	1622.8	1568.0	1508.8	1441.4	1380.5	1315.9	1260.0
27.5°	1786.7	1781.3	1772.6	1749.4	1710.9	1652.4	1582.5	1500.3	1414.4	1332.9	1259.7
30°	1772.9	1773.7	1774.6	1767.1	1742.5	1698.4	1629.0	1540.5	1438.4	1346.7	1262.0
32.5°	1650.5	1665.5	1679.7	1696.7	1703.6	1695.2	1651.6	1571.8	1466.8	1362.6	1260.7
35°	1378.8	1383.4	1429.8	1475.9	1538.4	1587.0	1619.5	1584.1	1495.6	1375.9	1259.1
37.5°	1075.1	1097.3	1129.5	1181.5	1271.8	1352.6	1456.5	1504.3	1475.8	1380.3	1256.2
40°	916.5	937.1	958.0	1011.1	1087.2	1185.1	1303.1	1403.9	1427.4	1366.5	1246.3
42.5°	794.1	810.3	833.6	873.5	937.2	1023.8	1136.6	1268.4	1349.4	1326.4	1225.7
45°	649.9	660.2	678.3	710.0	756.1	823.9	923.4	1067.5	1192.9	1234.5	1176.5
47.5°	556.3	556.2	570.3	592.2	625.4	683.1	756.7	869.5	1003.5	1102.6	1098.0
50°	504.3	502.2	513.3	532.3	558.6	596.8	667.2	757.2	886.1	998.3	1029.6
52.5°	459.5	459.8	466.6	480.6	502.6	535.4	587.9	669.1	779.1	894.4	953.2
55°	400.7	399.0	406.8	416.3	432.3	453.7	491.5	553.7	642.9	756.5	833.0
57.5°	346.7	351.2	354.3	360.9	374.2	388.6	420.5	466.0	536.9	634.3	715.2
60°	315.1	319.6	322.1	328.7	339.4	351.7	376.4	413.4	473.0	557.0	637.2
62.5°	286.8	290.3	291.1	297.1	305.8	317.8	337.2	368.3	415.4	488.9	567.4
65°	246.0	246.0	247.6	253.8	257.9	268.6	283.4	306.0	343.9	401.1	468.1
67.5°	206.7	208.7	208.2	211.0	214.8	223.0	233.6	252.3	280.4	322.1	375.7
70°	181.0	182.6	182.2	184.3	188.4	193.8	202.4	220.1	240.2	276.0	322.1
72.5°	158.0	158.6	157.6	160.3	162.7	167.4	177.1	186.5	205.3	235.5	273.4
75°	121.0	121.8	122.6	124.2	126.7	129.1	134.1	143.5	155.9	178.6	202.8
77.5°	90.6	89.1	91.1	90.9	92.2	94.1	98.5	103.5	113.6	127.9	146.7
80°	68.3	68.7	68.7	69.1	71.1	72.4	76.1	79.8	87.6	98.3	111.5
82.5°	49.8	50.9	50.3	51.0	52.8	53.6	55.7	58.7	63.3	71.7	81.2
85°	27.2	25.1	25.9	26.8	26.8	27.2	28.8	30.0	32.5	35.8	39.5
87.5°	12.8	13.3	13.5	13.4	13.6	13.4	14.5	14.3	15.1	15.8	16.8
90°	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7	17.6	16.4	14.8
92.5°	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7	17.6	16.4	15.0
95°	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7	17.6	16.4	25.0
97.5°	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6	44.0	50.5	67.6
100°	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5	144.5	178.5	177.5
102.5°	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8	221.3	227.7	227.1
105°	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0	386.9	386.9	386.4
110°	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7	440.4	441.0	440.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8	492.7	493.5	493.3
115°	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5	571.4	572.4	572.1
117.5°	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5	647.7	648.9	648.0
120°	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5	696.0	696.4	695.8
122.5°	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3	742.8	743.2	742.9
125°	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5	811.4	812.3	812.3
127.5°	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9	873.4	873.9	874.0
130°	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5	914.3	914.9	914.7
132.5°	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6	951.7	951.8	952.4
135°	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3	1007.8	1008.2	1008.7
137.5°	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3	1059.2	1059.1	1059.5
140°	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2	1090.8	1090.3	1090.5
142.5°	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4	1122.4	1122.3	1122.0
145°	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6	1166.4	1166.2	1166.2
147.5°	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5	1204.2	1204.0	1203.6
150°	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7	1228.2	1227.7	1227.2
152.5°	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0	1249.5	1249.0	1248.6
155°	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4	1278.7	1278.0	1277.6
157.5°	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7	1302.9	1302.2	1302.2
160°	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8	1317.9	1317.0	1316.8
162.5°	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6	1331.3	1330.1	1329.8
165°	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4	1349.1	1347.7	1347.5
167.5°	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0	1362.3	1360.7	1360.4
170°	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9	1369.0	1367.2	1367.0
172.5°	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3	1374.6	1372.9	1372.5
175°	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1	1380.3	1378.5	1378.3
177.5°	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6	1383.3	1382.0	1381.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	997.1	994.8	992.1	987.5	982.0	979.0	974.4	971.5	965.5	960.6	955.3
5°	1047.7	1037.0	1027.1	1014.4	1000.4	991.3	980.6	968.7	956.4	943.6	929.6
7.5°	1100.1	1081.2	1060.6	1038.5	1016.8	997.0	977.9	959.3	941.8	920.8	902.9
10°	1135.3	1111.4	1085.9	1055.9	1026.7	1001.2	975.3	952.7	929.6	905.0	883.1
12.5°	1170.5	1138.8	1102.7	1069.8	1034.6	1003.9	973.4	944.4	915.5	888.2	862.8
15°	1195.4	1167.4	1134.1	1087.2	1047.7	1005.4	965.0	927.6	892.6	862.2	830.1
17.5°	1211.7	1175.7	1140.0	1095.0	1043.1	995.8	950.1	907.3	867.8	829.3	798.4
20°	1214.7	1177.7	1140.3	1096.2	1043.1	988.9	943.3	891.8	849.5	809.5	771.7
22.5°	1213.7	1171.8	1131.0	1085.7	1034.0	984.0	928.8	876.3	830.4	791.1	751.6
25°	1204.4	1159.6	1108.6	1063.0	1011.9	958.9	902.9	848.6	801.7	756.9	717.8
27.5°	1196.7	1138.5	1080.8	1027.5	978.3	929.6	876.1	820.5	768.5	723.0	686.2
30°	1187.2	1123.4	1058.4	1002.8	952.3	905.0	854.4	800.1	745.8	701.3	661.9
32.5°	1178.6	1104.3	1035.7	975.3	921.6	875.7	829.0	777.4	724.1	679.0	639.4
35°	1162.1	1076.1	997.5	929.2	872.0	824.7	785.7	737.5	688.6	645.0	607.1
37.5°	1141.1	1039.0	954.7	883.1	820.5	770.6	734.3	697.3	650.3	608.3	574.1
40°	1124.6	1012.7	923.4	850.2	785.3	733.4	699.7	664.7	625.7	586.6	550.4
42.5°	1103.9	989.0	891.9	813.1	748.7	698.2	662.8	633.1	598.7	562.2	528.6
45°	1065.8	946.1	840.8	756.1	691.0	641.3	604.7	582.5	556.6	522.0	493.6
47.5°	1009.8	894.5	785.6	698.2	631.1	584.9	550.6	529.3	511.0	485.4	459.6
50°	960.0	856.0	745.8	658.9	591.9	545.4	513.8	494.4	478.8	459.1	437.3
52.5°	904.4	807.6	706.6	620.8	554.4	508.6	477.6	460.6	447.6	433.4	411.9
55°	816.1	733.9	640.1	558.6	497.3	452.5	425.3	410.5	399.8	389.1	376.0
57.5°	718.7	654.4	571.3	496.9	440.5	399.7	374.3	359.9	351.6	346.1	338.3
60°	650.3	595.2	523.6	455.7	400.7	364.5	339.8	328.7	321.7	317.1	311.4
62.5°	586.8	541.6	475.2	413.3	365.1	330.9	308.9	298.1	291.4	289.1	284.4
65°	493.2	458.3	403.5	352.1	311.0	281.8	263.2	252.9	248.8	246.4	246.8
67.5°	401.0	379.7	335.7	291.9	259.0	234.6	219.8	211.8	209.8	206.5	206.4
70°	344.7	328.7	291.7	253.4	224.2	205.3	192.1	183.9	181.8	180.1	179.7
72.5°	295.0	281.0	248.8	218.2	191.9	175.3	164.5	159.5	156.1	155.2	155.1
75°	221.7	213.9	188.4	164.1	146.0	134.5	127.1	122.6	120.1	119.7	120.1
77.5°	157.6	150.8	134.6	117.4	106.0	97.3	91.0	89.4	86.7	86.7	86.3
80°	118.4	113.9	103.7	90.1	80.6	73.2	69.9	67.0	66.2	65.0	66.2
82.5°	85.9	81.0	74.1	65.4	57.6	53.2	49.8	49.0	48.5	47.8	48.2
85°	42.4	42.8	38.7	32.1	28.8	26.3	24.2	24.2	23.8	23.4	23.8
87.5°	17.1	16.2	14.5	13.2	11.2	9.8	9.1	9.1	8.5	8.5	9.2
90°	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0	2.9	4.7	6.5
92.5°	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8	14.5	13.2	12.0
95°	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5	57.8	57.1	56.4
97.5°	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1	123.3	124.5	125.7
100°	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3	172.0	172.6	173.3
102.5°	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3	222.2	223.1	223.9
105°	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6	302.5	303.4	304.3
107.5°	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8
110°	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9	490.4	491.0	491.5
115°	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2	567.3	568.5	569.6
117.5°	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2	645.1	645.1	645.0
120°	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3	694.2	694.0	693.7
122.5°	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8	738.7	739.6	740.5
125°	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2	806.8	808.3	809.9
127.5°	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3	870.5	871.6	872.7
130°	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7	909.9	911.0	912.2
132.5°	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2	949.4	950.8	952.1
135°	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2	1005.5	1006.9	1008.2
137.5°	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7	1056.8	1058.0	1059.1
140°	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3	1089.7	1090.2	1090.6
142.5°	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6	1119.9	1120.1	1120.5
145°	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1	1164.6	1165.1	1165.5
147.5°	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1	1203.0	1202.9	1202.8
150°	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1227.2	1226.9	1226.4
152.5°	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5	1250.5	1249.5	1248.6
155°	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1	1280.7	1279.4	1278.0
157.5°	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7	1304.9	1304.0	1303.2
160°	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1	1320.7	1319.4	1318.0
162.5°	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2	1333.9	1332.5	1331.1
165°	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9	1351.5	1350.1	1348.8
167.5°	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0	1364.6	1363.2	1361.8
170°	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4	1371.8	1370.2	1368.6
172.5°	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3	1376.7	1375.1	1373.5
175°	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6	1382.3	1380.9	1379.5
177.5°	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1	1385.0	1383.9	1382.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	952.4	948.7	945.8	939.2	935.6	930.7	926.7	931.0	926.4	928.4	925.3
5°	922.7	911.2	902.9	891.0	880.7	871.2	864.3	863.0	859.7	858.1	853.1
7.5°	886.9	872.5	858.4	842.8	829.6	816.2	807.6	800.6	795.9	789.7	785.5
10°	865.9	846.5	830.1	811.2	794.7	780.3	768.8	763.0	757.7	749.9	747.0
12.5°	839.9	819.9	799.8	779.6	763.8	747.7	737.8	729.1	725.5	716.6	715.7
15°	808.7	778.7	758.9	738.4	716.5	703.4	695.1	685.7	681.6	675.4	670.9
17.5°	771.5	744.7	720.0	698.7	680.0	668.9	658.7	652.2	645.2	641.1	633.7
20°	744.6	719.1	694.3	671.7	657.4	644.6	636.4	630.2	622.8	620.8	613.3
22.5°	721.8	693.7	670.0	651.0	635.3	620.9	612.0	607.8	602.7	596.4	594.8
25°	684.9	655.7	635.6	616.6	602.6	589.5	583.3	578.0	573.0	568.5	566.8
27.5°	653.0	626.9	602.9	585.8	573.7	561.7	556.2	549.7	546.1	542.5	538.1
30°	630.6	603.9	582.9	566.4	553.3	542.6	536.8	532.3	529.0	525.7	523.2
32.5°	607.5	582.8	562.4	546.4	533.2	525.1	520.0	516.8	513.2	509.2	506.1
35°	577.1	549.9	530.2	516.3	506.0	499.8	494.0	491.2	487.0	487.0	483.7
37.5°	542.8	519.4	501.9	489.2	480.0	474.4	468.2	466.2	463.6	461.8	460.7
40°	522.4	500.6	484.2	471.4	461.5	457.0	452.1	448.8	447.1	445.0	444.3
42.5°	501.4	480.5	464.8	453.0	444.4	440.5	435.9	433.6	430.3	427.6	427.1
45°	469.4	449.2	434.8	425.3	418.0	413.4	410.5	405.6	403.9	400.7	400.2
47.5°	438.9	419.6	405.5	397.8	391.3	387.5	383.0	378.1	376.2	374.5	374.4
50°	416.3	398.6	385.4	378.0	371.9	366.5	361.9	358.7	357.4	357.4	358.3
52.5°	393.2	378.2	367.0	358.0	352.1	346.4	342.2	340.2	338.3	340.3	341.8
55°	359.5	344.3	336.0	327.4	321.7	315.1	313.1	312.2	311.0	314.3	315.9
57.5°	323.8	313.1	303.5	294.9	289.8	286.0	283.2	282.7	284.9	286.5	291.9
60°	301.1	288.8	280.1	273.5	267.4	264.9	264.1	263.2	264.9	269.4	276.4
62.5°	276.1	266.1	256.7	251.8	247.3	243.2	243.0	243.5	246.8	252.0	259.0
65°	239.4	230.8	224.6	218.8	215.2	212.7	213.5	215.2	218.8	225.9	233.6
67.5°	202.2	196.2	190.7	186.0	182.4	182.4	183.3	185.8	190.1	198.2	205.3
70°	178.1	171.5	167.0	164.9	162.1	160.4	162.9	167.0	170.7	178.1	184.3
72.5°	154.1	148.5	145.0	143.5	142.4	141.0	141.8	146.2	151.3	158.7	165.9
75°	118.4	116.4	113.9	112.3	111.1	111.9	112.7	116.8	121.0	128.7	137.0
77.5°	86.4	84.3	82.9	82.5	81.8	82.1	84.5	87.5	91.6	97.3	103.5
80°	65.4	64.6	63.8	63.4	63.4	63.8	67.0	69.1	72.8	78.2	83.1
82.5°	47.6	47.1	47.0	46.9	47.2	47.3	49.3	52.0	55.1	59.1	63.4
85°	25.1	24.2	25.5	25.9	25.1	26.3	27.2	28.8	30.0	32.1	34.1
87.5°	9.9	10.9	10.9	11.6	11.9	12.8	12.8	14.3	15.1	16.0	15.9
90°	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7	19.8	21.0	21.9
92.5°	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7	19.8	21.0	21.7
95°	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7	19.8	21.0	21.5
97.5°	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6	31.2	24.7	21.5
100°	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5	76.6	42.6	25.2
102.5°	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8	208.4	202.0	191.0
105°	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.5
107.5°	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0	387.1	387.1	386.7
110°	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7	439.0	438.3	438.1



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8	491.0	490.1	489.5
115°	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5	569.6	568.7	567.5
117.5°	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5	645.3	644.1	643.2
120°	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5	695.1	694.6	693.8
122.5°	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3	741.8	741.4	740.5
125°	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5	809.6	808.7	807.9
127.5°	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9	872.4	871.9	870.8
130°	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5	912.8	912.2	911.2
132.5°	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6	951.4	951.3	950.6
135°	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3	1006.9	1006.4	1005.5
137.5°	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3	1059.4	1059.5	1058.9
140°	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2	1091.6	1092.1	1091.6
142.5°	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4	1122.6	1122.7	1122.0
145°	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6	1166.9	1167.1	1166.6
147.5°	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5	1204.8	1205.1	1204.4
150°	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7	1229.1	1229.5	1228.8
152.5°	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0	1250.5	1250.9	1250.3
155°	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4	1280.0	1280.7	1280.2
157.5°	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7	1304.4	1305.1	1304.6
160°	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8	1319.7	1320.6	1320.2
162.5°	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6	1334.0	1335.2	1334.8
165°	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4	1351.9	1353.2	1353.0
167.5°	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0	1365.6	1367.2	1367.0
170°	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9	1372.7	1374.5	1374.4
172.5°	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3	1377.9	1379.5	1379.3
175°	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1	1383.9	1385.8	1385.7
177.5°	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6	1385.8	1387.1	1387.0
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	923.4	925.7	923.7	926.4	923.7	925.7	923.4	925.3	928.4	926.4	931.0
5°	851.0	847.4	849.9	848.2	849.9	847.4	851.0	853.1	858.1	859.7	863.0
7.5°	784.3	780.7	776.7	774.8	776.7	780.7	784.3	785.5	789.7	795.9	800.6
10°	742.5	737.9	737.5	734.7	737.5	737.9	742.5	747.0	749.9	757.7	763.0
12.5°	711.9	707.7	703.0	701.8	703.0	707.7	711.9	715.7	716.6	725.5	729.1
15°	668.4	665.1	662.3	664.7	662.3	665.1	668.4	670.9	675.4	681.6	685.7
17.5°	632.3	629.6	629.1	626.1	629.1	629.6	632.3	633.7	641.1	645.2	652.2
20°	609.6	607.5	608.4	603.0	608.4	607.5	609.6	613.3	620.8	622.8	630.2
22.5°	591.5	587.5	587.0	585.9	587.0	587.5	591.5	594.8	596.4	602.7	607.8
25°	563.2	561.1	559.0	561.1	559.0	561.1	563.2	566.8	568.5	573.0	578.0
27.5°	538.4	535.9	535.4	535.6	535.4	535.9	538.4	538.1	542.5	546.1	549.7
30°	523.2	519.1	519.5	519.1	519.5	519.1	523.2	523.2	525.7	529.0	532.3
32.5°	506.8	504.0	503.4	502.6	503.4	504.0	506.8	506.1	509.2	513.2	516.8
35°	482.5	482.5	480.5	480.5	480.5	482.5	482.5	483.7	487.0	487.0	491.2
37.5°	459.7	459.3	458.0	458.3	458.0	459.3	459.7	460.7	461.8	463.6	466.2
40°	442.6	442.2	440.9	438.5	440.9	442.2	442.6	444.3	445.0	447.1	448.8
42.5°	426.1	424.8	424.2	423.3	424.2	424.8	426.1	427.1	427.6	430.3	433.6
45°	400.2	400.2	399.4	399.0	399.4	400.2	400.2	400.2	400.7	403.9	405.6
47.5°	375.1	375.8	377.4	377.2	377.4	375.8	375.1	374.4	374.5	376.2	378.1
50°	359.9	360.4	361.6	361.9	361.6	360.4	359.9	358.3	357.4	357.4	358.7
52.5°	343.2	345.5	347.1	346.8	347.1	345.5	343.2	341.8	340.3	338.3	340.2
55°	319.6	322.5	325.3	325.8	325.3	322.5	319.6	315.9	314.3	311.0	312.2
57.5°	296.4	300.4	303.4	304.4	303.4	300.4	296.4	291.9	286.5	284.9	282.7
60°	280.5	285.9	289.6	291.2	289.6	285.9	280.5	276.4	269.4	264.9	263.2
62.5°	265.4	271.4	275.1	275.4	275.1	271.4	265.4	259.0	252.0	246.8	243.5
65°	240.7	246.8	250.1	252.5	250.1	246.8	240.7	233.6	225.9	218.8	215.2
67.5°	214.0	220.1	223.8	225.8	223.8	220.1	214.0	205.3	198.2	190.1	185.8
70°	194.6	200.7	205.7	207.3	205.7	200.7	194.6	184.3	178.1	170.7	167.0
72.5°	175.5	181.0	185.0	186.9	185.0	181.0	175.5	165.9	158.7	151.3	146.2
75°	142.4	149.7	153.4	155.5	153.4	149.7	142.4	137.0	128.7	121.0	116.8
77.5°	109.7	116.5	118.7	119.8	118.7	116.5	109.7	103.5	97.3	91.6	87.5
80°	88.0	92.1	95.0	95.5	95.0	92.1	88.0	83.1	78.2	72.8	69.1
82.5°	67.7	71.1	72.0	73.0	72.0	71.1	67.7	63.4	59.1	55.1	52.0
85°	37.0	38.7	39.1	38.7	39.1	38.7	37.0	34.1	32.1	30.0	28.8
87.5°	16.7	16.5	16.6	17.4	16.6	16.5	16.7	15.9	16.0	15.1	14.3
90°	22.6	23.2	23.9	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7
92.5°	22.0	22.3	22.7	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7
95°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7
97.5°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6
100°	24.2	23.4	22.4	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5
102.5°	175.5	160.0	144.5	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8
105°	305.3	305.1	304.8	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6
107.5°	386.0	385.4	384.7	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0
110°	438.3	438.6	438.8	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.2	488.9	488.5	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8
115°	566.2	564.8	563.4	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5
117.5°	642.6	642.1	641.4	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5
120°	692.7	691.5	690.4	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5
122.5°	739.2	737.8	736.5	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3
125°	807.2	806.5	805.8	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5
127.5°	869.1	867.4	865.7	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9
130°	910.1	908.9	907.8	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5
132.5°	949.5	948.4	947.2	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6
135°	1004.2	1002.7	1001.4	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3
137.5°	1057.7	1056.5	1055.3	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3
140°	1090.3	1088.9	1087.6	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2
142.5°	1120.6	1119.3	1117.9	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4
145°	1165.1	1163.8	1162.4	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6
147.5°	1202.7	1201.0	1199.4	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5
150°	1227.0	1225.2	1223.4	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7
152.5°	1248.6	1247.1	1245.4	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0
155°	1278.3	1276.5	1274.7	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4
157.5°	1302.7	1300.9	1299.1	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7
160°	1318.3	1316.5	1314.7	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8
162.5°	1332.8	1330.8	1328.8	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6
165°	1351.1	1349.3	1347.5	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4
167.5°	1364.9	1362.9	1360.9	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0
170°	1372.4	1370.3	1368.3	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9
172.5°	1377.3	1375.2	1373.2	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3
175°	1383.6	1381.6	1379.5	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1
177.5°	1385.5	1384.1	1382.6	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	926.7	930.7	935.6	939.2	945.8	948.7	952.4	955.3	960.6	965.5	971.5
5°	864.3	871.2	880.7	891.0	902.9	911.2	922.7	929.6	943.6	956.4	968.7
7.5°	807.6	816.2	829.6	842.8	858.4	872.5	886.9	902.9	920.8	941.8	959.3
10°	768.8	780.3	794.7	811.2	830.1	846.5	865.9	883.1	905.0	929.6	952.7
12.5°	737.8	747.7	763.8	779.6	799.8	819.9	839.9	862.8	888.2	915.5	944.4
15°	695.1	703.4	716.5	738.4	758.9	778.7	808.7	830.1	862.2	892.6	927.6
17.5°	658.7	668.9	680.0	698.7	720.0	744.7	771.5	798.4	829.3	867.8	907.3
20°	636.4	644.6	657.4	671.7	694.3	719.1	744.6	771.7	809.5	849.5	891.8
22.5°	612.0	620.9	635.3	651.0	670.0	693.7	721.8	751.6	791.1	830.4	876.3
25°	583.3	589.5	602.6	616.6	635.6	655.7	684.9	717.8	756.9	801.7	848.6
27.5°	556.2	561.7	573.7	585.8	602.9	626.9	653.0	686.2	723.0	768.5	820.5
30°	536.8	542.6	553.3	566.4	582.9	603.9	630.6	661.9	701.3	745.8	800.1
32.5°	520.0	525.1	533.2	546.4	562.4	582.8	607.5	639.4	679.0	724.1	777.4
35°	494.0	499.8	506.0	516.3	530.2	549.9	577.1	607.1	645.0	688.6	737.5
37.5°	468.2	474.4	480.0	489.2	501.9	519.4	542.8	574.1	608.3	650.3	697.3
40°	452.1	457.0	461.5	471.4	484.2	500.6	522.4	550.4	586.6	625.7	664.7
42.5°	435.9	440.5	444.4	453.0	464.8	480.5	501.4	528.6	562.2	598.7	633.1
45°	410.5	413.4	418.0	425.3	434.8	449.2	469.4	493.6	522.0	556.6	582.5
47.5°	383.0	387.5	391.3	397.8	405.5	419.6	438.9	459.6	485.4	511.0	529.3
50°	361.9	366.5	371.9	378.0	385.4	398.6	416.3	437.3	459.1	478.8	494.4
52.5°	342.2	346.4	352.1	358.0	367.0	378.2	393.2	411.9	433.4	447.6	460.6
55°	313.1	315.1	321.7	327.4	336.0	344.3	359.5	376.0	389.1	399.8	410.5
57.5°	283.2	286.0	289.8	294.9	303.5	313.1	323.8	338.3	346.1	351.6	359.9
60°	264.1	264.9	267.4	273.5	280.1	288.8	301.1	311.4	317.1	321.7	328.7
62.5°	243.0	243.2	247.3	251.8	256.7	266.1	276.1	284.4	289.1	291.4	298.1
65°	213.5	212.7	215.2	218.8	224.6	230.8	239.4	246.8	246.4	248.8	252.9
67.5°	183.3	182.4	182.4	186.0	190.7	196.2	202.2	206.4	206.5	209.8	211.8
70°	162.9	160.4	162.1	164.9	167.0	171.5	178.1	179.7	180.1	181.8	183.9
72.5°	141.8	141.0	142.4	143.5	145.0	148.5	154.1	155.1	155.2	156.1	159.5
75°	112.7	111.9	111.1	112.3	113.9	116.4	118.4	120.1	119.7	120.1	122.6
77.5°	84.5	82.1	81.8	82.5	82.9	84.3	86.4	86.3	86.7	86.7	89.4
80°	67.0	63.8	63.4	63.4	63.8	64.6	65.4	66.2	65.0	66.2	67.0
82.5°	49.3	47.3	47.2	46.9	47.0	47.1	47.6	48.2	47.8	48.5	49.0
85°	27.2	26.3	25.1	25.9	25.5	24.2	25.1	23.8	23.4	23.8	24.2
87.5°	12.8	12.8	11.9	11.6	10.9	10.9	9.9	9.2	8.5	8.5	9.1
90°	17.6	16.4	14.8	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0
92.5°	17.6	16.4	15.0	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8
95°	17.6	16.4	25.0	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5
97.5°	44.0	50.5	67.6	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1
100°	144.5	178.5	177.5	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3
102.5°	221.3	227.7	227.1	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3
105°	305.6	305.6	305.6	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6
107.5°	386.9	386.9	386.4	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8
110°	440.4	441.0	440.6	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.7	493.5	493.3	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9
115°	571.4	572.4	572.1	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2
117.5°	647.7	648.9	648.0	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2
120°	696.0	696.4	695.8	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3
122.5°	742.8	743.2	742.9	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8
125°	811.4	812.3	812.3	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2
127.5°	873.4	873.9	874.0	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3
130°	914.3	914.9	914.7	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7
132.5°	951.7	951.8	952.4	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2
135°	1007.8	1008.2	1008.7	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2
137.5°	1059.2	1059.1	1059.5	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7
140°	1090.8	1090.3	1090.5	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3
142.5°	1122.4	1122.3	1122.0	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6
145°	1166.4	1166.2	1166.2	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1
147.5°	1204.2	1204.0	1203.6	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1
150°	1228.2	1227.7	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7
152.5°	1249.5	1249.0	1248.6	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5
155°	1278.7	1278.0	1277.6	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1
157.5°	1302.9	1302.2	1302.2	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7
160°	1317.9	1317.0	1316.8	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1
162.5°	1331.3	1330.1	1329.8	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2
165°	1349.1	1347.7	1347.5	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9
167.5°	1362.3	1360.7	1360.4	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0
170°	1369.0	1367.2	1367.0	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4
172.5°	1374.6	1372.9	1372.5	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3
175°	1380.3	1378.5	1378.3	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6
177.5°	1383.3	1382.0	1381.8	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	974.4	979.0	982.0	987.5	992.1	994.8	997.1	999.1	1001.4	1003.4	1008.9
5°	980.6	991.3	1000.4	1014.4	1027.1	1037.0	1047.7	1057.2	1065.0	1076.1	1084.7
7.5°	977.9	997.0	1016.8	1038.5	1060.6	1081.2	1100.1	1117.8	1133.9	1153.3	1170.3
10°	975.3	1001.2	1026.7	1055.9	1085.9	1111.4	1135.3	1159.6	1177.3	1202.0	1222.9
12.5°	973.4	1003.9	1034.6	1069.8	1102.7	1138.8	1170.5	1188.2	1215.1	1234.9	1259.8
15°	965.0	1005.4	1047.7	1087.2	1134.1	1167.4	1195.4	1229.9	1255.0	1280.1	1307.3
17.5°	950.1	995.8	1043.1	1095.0	1140.0	1175.7	1211.7	1245.1	1275.0	1308.7	1342.4
20°	943.3	988.9	1043.1	1096.2	1140.3	1177.7	1214.7	1251.3	1284.2	1327.4	1366.5
22.5°	928.8	984.0	1034.0	1085.7	1131.0	1171.8	1213.7	1255.3	1299.0	1347.8	1396.8
25°	902.9	958.9	1011.9	1063.0	1108.6	1159.6	1204.4	1260.0	1315.9	1380.5	1441.4
27.5°	876.1	929.6	978.3	1027.5	1080.8	1138.5	1196.7	1259.7	1332.9	1414.4	1500.3
30°	854.4	905.0	952.3	1002.8	1058.4	1123.4	1187.2	1262.0	1346.7	1438.4	1540.5
32.5°	829.0	875.7	921.6	975.3	1035.7	1104.3	1178.6	1260.7	1362.6	1466.8	1571.8
35°	785.7	824.7	872.0	929.2	997.5	1076.1	1162.1	1259.1	1375.9	1495.6	1584.1
37.5°	734.3	770.6	820.5	883.1	954.7	1039.0	1141.1	1256.2	1380.3	1475.8	1504.3
40°	699.7	733.4	785.3	850.2	923.4	1012.7	1124.6	1246.3	1366.5	1427.4	1403.9
42.5°	662.8	698.2	748.7	813.1	891.9	989.0	1103.9	1225.7	1326.4	1349.4	1268.4
45°	604.7	641.3	691.0	756.1	840.8	946.1	1065.8	1176.5	1234.5	1192.9	1067.5
47.5°	550.6	584.9	631.1	698.2	785.6	894.5	1009.8	1098.0	1102.6	1003.5	869.5
50°	513.8	545.4	591.9	658.9	745.8	856.0	960.0	1029.6	998.3	886.1	757.2
52.5°	477.6	508.6	554.4	620.8	706.6	807.6	904.4	953.2	894.4	779.1	669.1
55°	425.3	452.5	497.3	558.6	640.1	733.9	816.1	833.0	756.5	642.9	553.7
57.5°	374.3	399.7	440.5	496.9	571.3	654.4	718.7	715.2	634.3	536.9	466.0
60°	339.8	364.5	400.7	455.7	523.6	595.2	650.3	637.2	557.0	473.0	413.4
62.5°	308.9	330.9	365.1	413.3	475.2	541.6	586.8	567.4	488.9	415.4	368.3
65°	263.2	281.8	311.0	352.1	403.5	458.3	493.2	468.1	401.1	343.9	306.0
67.5°	219.8	234.6	259.0	291.9	335.7	379.7	401.0	375.7	322.1	280.4	252.3
70°	192.1	205.3	224.2	253.4	291.7	328.7	344.7	322.1	276.0	240.2	220.1
72.5°	164.5	175.3	191.9	218.2	248.8	281.0	295.0	273.4	235.5	205.3	186.5
75°	127.1	134.5	146.0	164.1	188.4	213.9	221.7	202.8	178.6	155.9	143.5
77.5°	91.0	97.3	106.0	117.4	134.6	150.8	157.6	146.7	127.9	113.6	103.5
80°	69.9	73.2	80.6	90.1	103.7	113.9	118.4	111.5	98.3	87.6	79.8
82.5°	49.8	53.2	57.6	65.4	74.1	81.0	85.9	81.2	71.7	63.3	58.7
85°	24.2	26.3	28.8	32.1	38.7	42.8	42.4	39.5	35.8	32.5	30.0
87.5°	9.1	9.8	11.2	13.2	14.5	16.2	17.1	16.8	15.8	15.1	14.3
90°	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7
92.5°	14.5	13.2	12.0	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7
95°	57.8	57.1	56.4	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7
97.5°	123.3	124.5	125.7	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6
100°	172.0	172.6	173.3	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5
102.5°	222.2	223.1	223.9	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8
105°	302.5	303.4	304.3	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.8	384.8	384.8	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0
110°	439.0	439.0	439.0	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	490.4	491.0	491.5	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8
115°	567.3	568.5	569.6	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5
117.5°	645.1	645.1	645.0	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5
120°	694.2	694.0	693.7	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5
122.5°	738.7	739.6	740.5	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3
125°	806.8	808.3	809.9	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5
127.5°	870.5	871.6	872.7	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9
130°	909.9	911.0	912.2	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5
132.5°	949.4	950.8	952.1	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6
135°	1005.5	1006.9	1008.2	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3
137.5°	1056.8	1058.0	1059.1	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3
140°	1089.7	1090.2	1090.6	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2
142.5°	1119.9	1120.1	1120.5	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4
145°	1164.6	1165.1	1165.5	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6
147.5°	1203.0	1202.9	1202.8	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5
150°	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7
152.5°	1250.5	1249.5	1248.6	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0
155°	1280.7	1279.4	1278.0	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4
157.5°	1304.9	1304.0	1303.2	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7
160°	1320.7	1319.4	1318.0	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8
162.5°	1333.9	1332.5	1331.1	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6
165°	1351.5	1350.1	1348.8	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4
167.5°	1364.6	1363.2	1361.8	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0
170°	1371.8	1370.2	1368.6	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9
172.5°	1376.7	1375.1	1373.5	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3
175°	1382.3	1380.9	1379.5	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1
177.5°	1385.0	1383.9	1382.8	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	969.2	969.2	969.2	969.2	969.2	969.2	969.2
2.5°	1013.5	1016.2	1021.8	1019.8	1022.5	1023.7	1025.1
5°	1095.4	1108.6	1114.4	1113.5	1122.1	1120.1	1118.0
7.5°	1187.9	1201.7	1209.4	1219.1	1224.6	1225.0	1229.9
10°	1240.2	1258.3	1265.7	1276.0	1282.5	1286.3	1285.9
12.5°	1280.3	1294.5	1311.1	1316.1	1325.0	1329.7	1328.0
15°	1328.6	1351.3	1368.6	1377.2	1388.3	1391.5	1396.1
17.5°	1371.7	1402.1	1422.3	1449.1	1459.2	1465.4	1461.7
20°	1404.3	1444.2	1464.4	1496.5	1514.2	1523.6	1520.4
22.5°	1442.8	1486.1	1523.3	1551.1	1578.0	1590.8	1593.4
25°	1508.8	1568.0	1622.8	1659.4	1692.7	1700.5	1717.8
27.5°	1582.5	1652.4	1710.9	1749.4	1772.6	1781.3	1786.7
30°	1629.0	1698.4	1742.5	1767.1	1774.6	1773.7	1772.9
32.5°	1651.6	1695.2	1703.6	1696.7	1679.7	1665.5	1650.5
35°	1619.5	1587.0	1538.4	1475.9	1429.8	1383.4	1378.8
37.5°	1456.5	1352.6	1271.8	1181.5	1129.5	1097.3	1075.1
40°	1303.1	1185.1	1087.2	1011.1	958.0	937.1	916.5
42.5°	1136.6	1023.8	937.2	873.5	833.6	810.3	794.1
45°	923.4	823.9	756.1	710.0	678.3	660.2	649.9
47.5°	756.7	683.1	625.4	592.2	570.3	556.2	556.3
50°	667.2	596.8	558.6	532.3	513.3	502.2	504.3
52.5°	587.9	535.4	502.6	480.6	466.6	459.8	459.5
55°	491.5	453.7	432.3	416.3	406.8	399.0	400.7
57.5°	420.5	388.6	374.2	360.9	354.3	351.2	346.7
60°	376.4	351.7	339.4	328.7	322.1	319.6	315.1
62.5°	337.2	317.8	305.8	297.1	291.1	290.3	286.8
65°	283.4	268.6	257.9	253.8	247.6	246.0	246.0
67.5°	233.6	223.0	214.8	211.0	208.2	208.7	206.7
70°	202.4	193.8	188.4	184.3	182.2	182.6	181.0
72.5°	177.1	167.4	162.7	160.3	157.6	158.6	158.0
75°	134.1	129.1	126.7	124.2	122.6	121.8	121.0
77.5°	98.5	94.1	92.2	90.9	91.1	89.1	90.6
80°	76.1	72.4	71.1	69.1	68.7	68.7	68.3
82.5°	55.7	53.6	52.8	51.0	50.3	50.9	49.8
85°	28.8	27.2	26.8	26.8	25.9	25.1	27.2
87.5°	14.5	13.4	13.6	13.4	13.5	13.3	12.8
90°	19.8	21.0	21.9	22.6	23.2	23.9	24.6
92.5°	19.8	21.0	21.7	22.0	22.3	22.7	23.0
95°	19.8	21.0	21.5	21.5	21.5	21.5	21.5
97.5°	31.2	24.7	21.5	21.5	21.5	21.5	21.5
100°	76.6	42.6	25.2	24.2	23.4	22.4	21.5
102.5°	208.4	202.0	191.0	175.5	160.0	144.5	129.0
105°	305.6	305.6	305.5	305.3	305.1	304.8	304.6
107.5°	387.1	387.1	386.7	386.0	385.4	384.7	384.0
110°	439.0	438.3	438.1	438.3	438.6	438.8	439.0



TEST NUMBER: P333418-927

CATALOG NUMBER: S125DIW-S850D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.0	490.1	489.5	489.2	488.9	488.5	488.2
115°	569.6	568.7	567.5	566.2	564.8	563.4	562.1
117.5°	645.3	644.1	643.2	642.6	642.1	641.4	640.9
120°	695.1	694.6	693.8	692.7	691.5	690.4	689.3
122.5°	741.8	741.4	740.5	739.2	737.8	736.5	735.2
125°	809.6	808.7	807.9	807.2	806.5	805.8	805.2
127.5°	872.4	871.9	870.8	869.1	867.4	865.7	864.0
130°	912.8	912.2	911.2	910.1	908.9	907.8	906.7
132.5°	951.4	951.3	950.6	949.5	948.4	947.2	946.1
135°	1006.9	1006.4	1005.5	1004.2	1002.7	1001.4	1000.1
137.5°	1059.4	1059.5	1058.9	1057.7	1056.5	1055.3	1054.2
140°	1091.6	1092.1	1091.6	1090.3	1088.9	1087.6	1086.2
142.5°	1122.6	1122.7	1122.0	1120.6	1119.3	1117.9	1116.6
145°	1166.9	1167.1	1166.6	1165.1	1163.8	1162.4	1161.1
147.5°	1204.8	1205.1	1204.4	1202.7	1201.0	1199.4	1197.8
150°	1229.1	1229.5	1228.8	1227.0	1225.2	1223.4	1221.5
152.5°	1250.5	1250.9	1250.3	1248.6	1247.1	1245.4	1243.7
155°	1280.0	1280.7	1280.2	1278.3	1276.5	1274.7	1272.9
157.5°	1304.4	1305.1	1304.6	1302.7	1300.9	1299.1	1297.3
160°	1319.7	1320.6	1320.2	1318.3	1316.5	1314.7	1312.9
162.5°	1334.0	1335.2	1334.8	1332.8	1330.8	1328.8	1326.8
165°	1351.9	1353.2	1353.0	1351.1	1349.3	1347.5	1345.7
167.5°	1365.6	1367.2	1367.0	1364.9	1362.9	1360.9	1358.8
170°	1372.7	1374.5	1374.4	1372.4	1370.3	1368.3	1366.2
172.5°	1377.9	1379.5	1379.3	1377.3	1375.2	1373.2	1371.1
175°	1383.9	1385.8	1385.7	1383.6	1381.6	1379.5	1377.4
177.5°	1385.8	1387.1	1387.0	1385.5	1384.1	1382.6	1381.2
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6

(END OF REPORT)