

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333428-927

Luminaire Tested: **S125DIW-S850D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333428-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D1560U927-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7649.5 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 68.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	94	90	86	83	85	82	78	76	66	64	62	51	50	48	38	37	36	30
2	86	79	73	68	77	71	66	62	58	54	51	45	42	40	33	32	30	25
3	78	69	62	56	71	63	57	52	51	46	43	40	37	34	29	27	26	21
4	72	61	53	47	64	56	49	44	45	40	36	35	32	29	26	24	22	18
5	66	54	46	41	59	49	43	37	40	35	31	32	28	25	24	21	19	16
6	60	49	41	35	54	44	37	32	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	28	33	28	24	26	22	19	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	13	11
9	48	36	29	24	43	33	27	22	27	22	19	22	18	15	16	14	12	10
10	45	33	26	21	41	30	24	20	25	20	17	20	16	14	15	13	11	9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6716	6716	6716
5°	6731	6667	6710
10°	6690	6620	6658
15°	6618	6540	6568
20°	6514	6429	6441
25°	6402	6297	6291
30°	6264	6154	6123
35°	6117	6000	5916
40°	5966	5833	5751
45°	5802	5681	5569
50°	5621	5497	5332
55°	5447	5290	5141
60°	5239	5079	4899
65°	4991	4828	4664
70°	4755	4538	4381
75°	4332	4190	4045
80°	3857	3794	3704
85°	3349	3416	3231



TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.1	1.3
10°-20°	277.0	3.6
20°-30°	409.0	5.3
30°-40°	477.2	6.2
40°-50°	479.3	6.3
50°-60°	420.7	5.5
60°-70°	313.5	4.1
70°-80°	179.3	2.3
80°-90°	55.5	0.7
90°-100°	58.5	0.8
100°-110°	360.3	4.7
110°-120°	653.4	8.5
120°-130°	838.6	11.0
130°-140°	902.0	11.8
140°-150°	846.7	11.1
150°-160°	684.9	9.0
160°-170°	442.9	5.8
170°-180°	152.8	2.0
0°-30°	784.0	10.2
0°-40°	1261.2	16.5
0°-60°	2161.2	28.3
0°-90°	2709.4	35.4
90°-120°	1072.2	14.0
90°-150°	3659.5	47.8
90°-180°	4940.0	64.6
0°-180°	7649.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1040	1040	1040	1040	1040	
5°	1038	1036	1028	1035	1035	98
15°	990	987	978	982	982	279
25°	898	894	884	885	883	413
35°	776	772	761	757	750	485
45°	635	631	622	612	610	489
55°	484	481	470	462	457	432
65°	327	325	316	309	305	324
75°	174	172	168	165	162	185
85°	45	46	46	45	44	51
90°	1	11	19	25	29	5
95°	68	62	19	25	25	87
105°	351	355	355	355	354	372
115°	658	664	665	661	654	652
125°	936	944	944	940	936	836
135°	1167	1174	1172	1170	1163	900
145°	1354	1356	1356	1357	1350	846
155°	1491	1484	1486	1489	1480	686
165°	1573	1566	1567	1573	1565	444
175°	1609	1602	1603	1611	1602	153
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1042.6	1042.1	1041.7	1041.2	1040.8	1039.8	1038.4	1037.0	1035.5	1034.0	1035.5
5°	1038.3	1037.9	1037.5	1037.2	1036.8	1035.7	1033.9	1032.1	1030.2	1028.4	1030.1
7.5°	1028.7	1028.4	1028.0	1027.6	1027.3	1026.1	1024.1	1022.1	1020.1	1018.0	1019.6
10°	1020.2	1019.9	1019.5	1019.1	1018.7	1017.6	1015.5	1013.5	1011.5	1009.5	1011.0
12.5°	1009.6	1009.0	1008.4	1007.7	1007.0	1005.8	1003.9	1002.0	1000.1	998.3	999.5
15°	989.8	989.2	988.6	988.1	987.5	986.3	984.3	982.2	980.2	978.2	979.1
17.5°	966.9	966.1	965.3	964.5	963.7	962.2	960.1	958.1	955.9	953.9	955.0
20°	947.8	947.5	947.1	946.7	946.3	944.9	942.5	940.2	937.8	935.4	936.8
22.5°	928.7	928.0	927.4	926.7	926.1	924.6	922.4	920.1	917.9	915.7	916.6
25°	898.4	897.5	896.6	895.6	894.8	893.1	890.7	888.4	886.0	883.6	884.0
27.5°	863.0	862.5	862.0	861.4	860.9	859.4	856.9	854.4	852.0	849.5	849.6
30°	840.0	839.5	838.9	838.4	837.8	836.1	833.5	830.7	827.9	825.2	824.8
32.5°	815.0	814.1	813.3	812.5	811.7	810.0	807.6	805.1	802.6	800.2	799.5
35°	775.9	775.1	774.4	773.6	772.9	771.3	768.7	766.1	763.6	761.0	760.1
37.5°	735.2	734.3	733.3	732.5	731.5	729.8	727.5	725.0	722.6	720.3	718.8
40°	707.6	706.6	705.8	704.8	703.9	702.2	699.6	697.0	694.5	691.9	690.3
42.5°	677.9	677.2	676.4	675.7	674.9	673.2	670.7	668.0	665.5	663.0	661.5
45°	635.2	634.4	633.7	633.0	632.2	630.7	628.6	626.4	624.2	622.0	619.8
47.5°	589.1	589.1	589.1	589.1	589.2	588.0	585.3	582.7	580.0	577.4	575.1
50°	559.4	558.9	558.3	557.8	557.3	555.9	553.7	551.5	549.3	547.1	544.7
52.5°	529.2	528.8	528.4	528.0	527.6	526.2	523.9	521.5	519.2	516.8	514.8
55°	483.8	483.2	482.7	482.1	481.6	480.0	477.4	474.9	472.3	469.8	468.1
57.5°	435.9	435.6	435.3	435.0	434.7	433.5	431.3	429.2	427.0	424.8	422.7
60°	405.6	404.9	404.2	403.4	402.7	401.3	399.3	397.3	395.3	393.2	391.4
62.5°	374.0	373.4	372.9	372.2	371.7	370.5	368.8	367.1	365.4	363.6	361.7
65°	326.6	326.2	325.9	325.5	325.2	324.0	321.9	320.0	317.9	315.9	314.3
67.5°	280.7	280.0	279.2	278.4	277.7	276.5	275.0	273.5	272.0	270.5	269.1
70°	251.8	250.8	249.9	249.0	248.1	246.8	245.2	243.5	241.9	240.3	239.2
72.5°	220.1	219.5	218.9	218.3	217.7	216.8	215.8	214.7	213.7	212.6	211.4
75°	173.6	173.3	172.9	172.5	172.1	171.5	170.6	169.7	168.7	167.9	167.3
77.5°	130.6	130.5	130.4	130.2	130.1	129.8	129.2	128.7	128.2	127.7	127.4
80°	103.7	103.7	103.7	103.7	103.7	103.5	103.1	102.7	102.3	102.0	101.9
82.5°	79.9	79.7	79.4	79.1	78.8	78.6	78.5	78.5	78.4	78.3	78.0
85°	45.2	45.5	45.6	45.8	45.9	46.1	46.1	46.1	46.1	46.1	45.9
87.5°	18.0	18.5	18.9	19.3	19.7	20.0	20.3	20.5	20.7	20.9	21.2
90°	1.2	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4
92.5°	18.4	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4
95°	68.0	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4
97.5°	141.9	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2
100°	199.2	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0
102.5°	257.4	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3
105°	350.6	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9
110°	510.4	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0



TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.6	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8
115°	658.3	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3
117.5°	750.1	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0
120°	807.3	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2
122.5°	857.9	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6
125°	936.1	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4
127.5°	1010.7	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4
130°	1056.5	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0
132.5°	1102.3	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5
135°	1167.4	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7
137.5°	1227.3	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5
140°	1266.5	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2
142.5°	1301.7	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0
145°	1353.5	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1
147.5°	1398.8	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1
150°	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0
152.5°	1455.1	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8
155°	1490.6	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7
157.5°	1518.1	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9
160°	1537.2	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2
162.5°	1552.4	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9
165°	1573.0	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5
167.5°	1588.2	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9
170°	1596.8	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7
172.5°	1602.5	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2
175°	1608.7	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9
177.5°	1611.5	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9	1039.9
2.5°	1037.0	1038.4	1039.8	1040.5	1040.4	1040.2	1040.1	1039.9
5°	1031.7	1033.3	1035.0	1035.7	1035.5	1035.4	1035.1	1035.0
7.5°	1021.3	1022.9	1024.5	1025.2	1025.0	1024.8	1024.6	1024.5
10°	1012.4	1013.9	1015.3	1016.0	1015.8	1015.6	1015.4	1015.3
12.5°	1000.6	1001.8	1003.0	1003.5	1003.5	1003.5	1003.5	1003.4
15°	980.1	981.0	981.9	982.3	982.3	982.3	982.3	982.3
17.5°	956.2	957.3	958.4	958.5	957.6	956.7	955.8	954.9
20°	938.0	939.3	940.6	940.7	939.8	938.9	938.0	937.1
22.5°	917.3	918.2	919.1	919.2	918.5	917.9	917.3	916.7
25°	884.3	884.7	885.1	884.9	884.5	883.9	883.4	882.8
27.5°	849.7	849.8	849.9	849.6	849.1	848.5	848.0	847.4
30°	824.5	824.1	823.7	823.3	822.8	822.2	821.7	821.1
32.5°	798.8	798.2	797.6	796.7	795.7	794.7	793.8	792.8
35°	759.2	758.3	757.4	756.2	754.7	753.3	751.8	750.4
37.5°	717.5	716.1	714.8	713.7	712.9	712.0	711.2	710.3
40°	688.6	687.0	685.3	684.2	683.7	683.2	682.6	682.1
42.5°	660.0	658.5	657.0	655.8	655.0	654.1	653.2	652.4
45°	617.6	615.4	613.2	611.8	611.3	610.8	610.2	609.7
47.5°	572.9	570.7	568.5	566.7	565.5	564.2	562.8	561.6
50°	542.3	540.0	537.6	535.8	534.5	533.2	532.0	530.7
52.5°	512.7	510.6	508.5	506.8	505.3	503.9	502.5	501.1
55°	466.5	464.9	463.2	461.8	460.4	459.1	457.9	456.6
57.5°	420.6	418.5	416.4	414.9	414.2	413.6	412.9	412.2
60°	389.6	387.8	386.0	384.4	383.1	381.8	380.6	379.3
62.5°	359.7	357.7	355.8	354.3	353.3	352.3	351.3	350.3
65°	312.7	311.0	309.3	308.2	307.4	306.7	305.9	305.2
67.5°	267.8	266.3	265.0	264.0	263.6	263.2	262.7	262.3
70°	238.1	236.9	235.8	235.0	234.2	233.5	232.7	232.0
72.5°	210.1	208.9	207.6	206.6	205.9	205.2	204.5	203.7
75°	166.8	166.2	165.6	165.0	164.3	163.5	162.8	162.1
77.5°	127.1	126.7	126.4	126.0	125.4	124.9	124.5	123.9
80°	101.6	101.5	101.3	101.0	100.7	100.3	99.9	99.6
82.5°	77.6	77.3	77.0	76.8	76.8	76.7	76.6	76.5
85°	45.7	45.6	45.3	45.1	44.7	44.4	44.0	43.6
87.5°	21.5	21.7	22.0	22.0	21.9	21.8	21.6	21.5
90°	21.7	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	21.7	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	21.7	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	43.7	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	128.5	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	249.8	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	511.2	510.4	509.6	509.4	509.6	509.8	510.2	510.4





TEST NUMBER: P333428-927

CATALOG NUMBER: S125DIW-S850D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.8	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	663.3	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	751.6	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.7	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	863.0	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	942.4	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.9	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1062.2	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.4	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1171.2	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.6	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1268.7	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.0	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.5	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.4	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1428.5	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.3	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1487.5	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1515.7	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1533.3	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1549.4	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1570.1	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1585.8	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1593.9	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1600.1	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1606.9	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1609.8	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)