

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333375

Luminaire Tested: **S125DIW-S610D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333375
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D470U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4125.5 lumens
Efficiency: N/A
Efficacy: 136.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333375
CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	93	90	86	83	78	76	73	68	66	64	58	57	55	51
2	91	83	77	72	85	78	73	68	68	64	61	59	56	53	51	49	47	43
3	83	73	66	60	77	69	62	57	60	55	51	53	49	45	45	42	40	36
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34	31
5	70	58	50	44	65	55	47	41	48	42	37	42	37	34	36	33	30	27
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26	24
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23	21
8	55	43	35	29	52	40	33	28	36	30	26	32	27	23	28	24	21	19
9	52	39	31	26	48	37	30	25	33	27	23	29	24	21	26	22	19	17
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	2.2
10°-20°	255.8	6.2
20°-30°	377.7	9.2
30°-40°	440.7	10.7
40°-50°	442.6	10.7
50°-60°	388.5	9.4
60°-70°	289.5	7.0
70°-80°	165.5	4.0
80°-90°	49.4	1.2
90°-100°	39.0	0.9
100°-110°	115.2	2.8
110°-120°	195.1	4.7
120°-130°	256.8	6.2
130°-140°	287.7	7.0
140°-150°	282.0	6.8
150°-160°	236.9	5.7
160°-170°	157.4	3.8
170°-180°	55.1	1.3
0°-30°	724.0	17.5
0°-40°	1164.7	28.2
0°-60°	1995.9	48.4
0°-90°	2500.3	60.6
90°-120°	349.3	8.5
90°-150°	1175.8	28.5
90°-180°	1625.0	39.4
0°-180°	4125.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	0	4	7	10	11	4
95°	30	31	35	38	39	31
105°	103	106	108	111	112	110
115°	195	197	198	198	197	193
125°	285	288	288	287	287	255
135°	371	373	374	374	372	286
145°	449	451	452	452	451	281
155°	514	514	514	516	514	237
165°	559	558	558	560	558	158
175°	581	579	579	582	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.5	16.7	16.8	17.0	17.1	17.2	17.2	17.2	17.2	17.3	17.4
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8
92.5°	11.0	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1
95°	29.5	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6
97.5°	48.9	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2
100°	63.5	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3
102.5°	79.0	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8
105°	103.3	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9
107.5°	130.2	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8
110°	148.7	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6



TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.5	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6
115°	195.3	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0
117.5°	223.3	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0
120°	240.7	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4
122.5°	259.5	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4
125°	285.1	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1
127.5°	312.3	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3
130°	328.6	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7
132.5°	344.9	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3
135°	370.7	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9
137.5°	395.0	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8
140°	410.6	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5
142.5°	426.2	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0
145°	449.2	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3
147.5°	470.4	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7
150°	484.5	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9
152.5°	496.1	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7
155°	514.0	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8
157.5°	529.9	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8
160°	539.4	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9
162.5°	547.7	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3
165°	558.8	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8
167.5°	568.3	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1
170°	573.3	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1
172.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8
175°	581.1	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8
177.5°	583.1	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	17.5	17.6	17.7	17.6	17.4	17.2	17.0	16.8
90°	8.3	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	18.7	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	36.3	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	56.9	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	71.2	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	85.8	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	109.5	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.1	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	152.9	153.2	153.5	153.6	153.5	153.4	153.3	153.2



TEST NUMBER: P333375

CATALOG NUMBER: S125DIW-S610D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.9	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.4	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.9	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.2	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.6	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.2	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	398.9	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.7	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.1	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	472.9	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.0	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.2	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.2	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.3	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	547.8	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.2	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	567.7	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	572.7	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	576.4	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	580.4	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.3	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)