

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333381

Luminaire Tested: **S125DIW-S610D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333381
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S610D770U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5163.0 lumens
Efficiency: N/A
Efficacy: 137.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55
1	97	93	89	86	89	86	82	79	72	70	68	60	58	56	48	47	46
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39
3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	34	31	28
5	68	56	48	42	62	52	45	39	44	39	34	37	33	30	30	27	25
6	62	50	42	36	57	47	40	34	40	34	30	33	29	26	27	24	22
7	58	45	38	32	53	42	35	30	36	31	26	30	26	23	25	22	19
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17
9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	19	17	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6203	6203	6203
5°	6217	6157	6196
10°	6178	6114	6149
15°	6111	6040	6066
20°	6016	5937	5948
25°	5912	5815	5810
30°	5785	5683	5655
35°	5649	5541	5463
40°	5509	5387	5311
45°	5358	5246	5142
50°	5191	5077	4924
55°	5031	4884	4748
60°	4839	4691	4525
65°	4609	4459	4308
70°	4390	4190	4047
75°	4000	3868	3735
80°	3559	3503	3418
85°	3097	3149	2986



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	1.8
10°-20°	255.8	5.0
20°-30°	377.7	7.3
30°-40°	440.7	8.5
40°-50°	442.6	8.6
50°-60°	388.5	7.5
60°-70°	289.5	5.6
70°-80°	165.5	3.2
80°-90°	50.2	1.0
90°-100°	63.9	1.2
100°-110°	188.7	3.7
110°-120°	319.6	6.2
120°-130°	420.6	8.1
130°-140°	471.2	9.1
140°-150°	461.9	8.9
150°-160°	387.9	7.5
160°-170°	257.9	5.0
170°-180°	90.2	1.7
0°-30°	724.0	14.0
0°-40°	1164.7	22.6
0°-60°	1995.9	38.7
0°-90°	2501.1	48.4
90°-120°	572.1	11.1
90°-150°	1925.8	37.3
90°-180°	2662.0	51.6
0°-180°	5163.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	960	960	960	960	960	
5°	959	957	950	956	956	91
15°	914	911	903	907	907	257
25°	830	826	816	817	815	382
35°	716	713	703	699	693	448
45°	587	583	574	566	563	452
55°	447	444	434	427	422	399
65°	302	300	292	285	282	299
75°	160	159	155	153	150	171
85°	42	42	42	42	40	47
90°	1	7	12	16	18	5
95°	48	50	57	62	64	52
105°	169	173	177	182	184	181
115°	320	323	324	324	323	316
125°	467	471	472	471	470	418
135°	607	612	612	612	610	468
145°	736	739	741	741	739	460
155°	842	842	843	845	842	388
165°	915	914	915	917	913	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	962.8	962.4	962.0	961.6	961.2	960.3	959.0	957.6	956.3	954.9	956.3
5°	958.9	958.5	958.2	957.8	957.5	956.5	954.8	953.1	951.4	949.7	951.3
7.5°	950.0	949.7	949.4	949.0	948.7	947.6	945.7	943.9	942.0	940.2	941.6
10°	942.1	941.8	941.5	941.1	940.8	939.7	937.8	936.0	934.1	932.3	933.6
12.5°	932.4	931.8	931.2	930.6	930.0	928.8	927.1	925.4	923.6	921.9	923.0
15°	914.0	913.5	913.0	912.5	912.0	910.8	909.0	907.1	905.2	903.4	904.2
17.5°	892.9	892.2	891.4	890.7	889.9	888.6	886.7	884.7	882.8	880.9	881.9
20°	875.3	874.9	874.6	874.3	873.9	872.7	870.5	868.3	866.1	863.9	865.1
22.5°	857.6	857.0	856.4	855.8	855.2	853.9	851.8	849.8	847.7	845.6	846.4
25°	829.7	828.8	828.0	827.2	826.3	824.8	822.6	820.4	818.2	816.0	816.4
27.5°	797.0	796.5	796.0	795.5	795.0	793.6	791.3	789.1	786.8	784.6	784.6
30°	775.7	775.2	774.7	774.2	773.7	772.2	769.7	767.1	764.6	762.1	761.7
32.5°	752.6	751.9	751.1	750.3	749.5	748.0	745.8	743.5	741.2	739.0	738.4
35°	716.5	715.8	715.1	714.5	713.8	712.3	709.9	707.5	705.2	702.8	702.0
37.5°	678.9	678.1	677.3	676.4	675.6	674.0	671.8	669.6	667.3	665.1	663.9
40°	653.4	652.6	651.7	650.9	650.0	648.4	646.1	643.7	641.3	639.0	637.5
42.5°	626.1	625.4	624.6	623.9	623.2	621.7	619.3	617.0	614.6	612.2	610.9
45°	586.6	585.9	585.2	584.5	583.9	582.5	580.5	578.5	576.4	574.4	572.4
47.5°	544.0	544.0	544.1	544.1	544.1	542.9	540.5	538.1	535.7	533.2	531.2
50°	516.7	516.1	515.6	515.1	514.6	513.4	511.3	509.3	507.3	505.3	503.1
52.5°	488.7	488.3	488.0	487.6	487.2	485.9	483.8	481.6	479.5	477.3	475.4
55°	446.8	446.2	445.7	445.2	444.7	443.3	440.9	438.6	436.2	433.8	432.3
57.5°	402.5	402.3	402.0	401.7	401.5	400.3	398.3	396.3	394.3	392.4	390.4
60°	374.6	373.9	373.2	372.5	371.9	370.6	368.8	366.9	365.0	363.2	361.5
62.5°	345.4	344.9	344.3	343.8	343.2	342.2	340.6	339.0	337.4	335.8	334.0
65°	301.6	301.3	301.0	300.6	300.3	299.2	297.3	295.5	293.6	291.8	290.2
67.5°	259.2	258.5	257.8	257.1	256.4	255.4	254.0	252.6	251.2	249.8	248.5
70°	232.5	231.7	230.8	230.0	229.1	227.9	226.4	224.9	223.4	221.9	220.8
72.5°	203.3	202.7	202.2	201.6	201.0	200.2	199.3	198.3	197.3	196.3	195.2
75°	160.3	160.0	159.6	159.3	159.0	158.4	157.5	156.7	155.8	155.0	154.5
77.5°	120.7	120.5	120.4	120.2	120.1	119.8	119.3	118.9	118.4	117.9	117.6
80°	95.7	95.7	95.7	95.7	95.7	95.6	95.2	94.9	94.6	94.2	94.0
82.5°	73.9	73.6	73.3	73.0	72.8	72.6	72.5	72.5	72.4	72.3	72.0
85°	41.8	42.0	42.1	42.3	42.5	42.5	42.5	42.5	42.5	42.5	42.4
87.5°	16.6	16.8	17.1	17.4	17.6	17.8	17.9	18.0	18.1	18.2	18.3
90°	0.7	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7
92.5°	18.0	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6
95°	48.3	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3
97.5°	80.2	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1
100°	103.9	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1
102.5°	129.5	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0
105°	169.3	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4
107.5°	213.2	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8
110°	243.5	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.4	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4
115°	320.0	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2
117.5°	365.7	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5
120°	394.2	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6
122.5°	425.1	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2
125°	466.9	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8
127.5°	511.5	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7
130°	538.2	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2
132.5°	564.9	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6
135°	607.2	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4
137.5°	647.0	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2
140°	672.6	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8
142.5°	698.1	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2
145°	735.7	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9
147.5°	770.4	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2
150°	793.6	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8
152.5°	812.6	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2
155°	841.8	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2
157.5°	868.0	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7
160°	883.4	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6
162.5°	897.1	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4
165°	915.3	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2
167.5°	930.8	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8
170°	939.1	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1
172.5°	945.0	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0
175°	951.7	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7
177.5°	955.1	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	960.4	960.4	960.4	960.4	960.4	960.4	960.4	960.4
2.5°	957.6	959.0	960.3	960.9	960.8	960.6	960.5	960.4
5°	952.8	954.3	955.8	956.5	956.3	956.2	956.0	955.8
7.5°	943.1	944.6	946.1	946.8	946.6	946.4	946.3	946.1
10°	935.0	936.3	937.7	938.3	938.1	937.9	937.7	937.6
12.5°	924.1	925.2	926.2	926.8	926.7	926.7	926.7	926.6
15°	905.1	905.9	906.8	907.2	907.2	907.2	907.2	907.2
17.5°	883.0	884.0	885.1	885.2	884.3	883.5	882.7	881.8
20°	866.2	867.4	868.6	868.8	867.9	867.1	866.2	865.4
22.5°	847.2	848.0	848.8	848.9	848.3	847.7	847.1	846.6
25°	816.7	817.0	817.4	817.3	816.8	816.3	815.8	815.3
27.5°	784.7	784.8	784.8	784.6	784.1	783.6	783.1	782.6
30°	761.4	761.1	760.7	760.3	759.8	759.3	758.8	758.3
32.5°	737.8	737.1	736.5	735.8	734.9	734.0	733.0	732.1
35°	701.1	700.3	699.4	698.3	697.0	695.6	694.3	692.9
37.5°	662.6	661.4	660.1	659.1	658.3	657.6	656.8	656.0
40°	635.9	634.4	632.9	631.9	631.4	630.9	630.4	629.9
42.5°	609.5	608.1	606.7	605.6	604.8	604.1	603.3	602.5
45°	570.3	568.3	566.3	565.0	564.5	564.0	563.5	563.0
47.5°	529.1	527.0	525.0	523.4	522.2	521.0	519.8	518.6
50°	500.9	498.7	496.5	494.8	493.6	492.4	491.2	490.1
52.5°	473.4	471.5	469.6	468.0	466.7	465.3	464.0	462.7
55°	430.8	429.3	427.8	426.4	425.2	424.0	422.9	421.7
57.5°	388.4	386.5	384.5	383.2	382.6	381.9	381.3	380.7
60°	359.8	358.1	356.4	355.0	353.8	352.6	351.4	350.3
62.5°	332.2	330.4	328.5	327.2	326.3	325.3	324.4	323.5
65°	288.7	287.2	285.7	284.6	283.9	283.2	282.6	281.9
67.5°	247.3	246.0	244.7	243.8	243.4	243.0	242.6	242.2
70°	219.8	218.8	217.8	217.0	216.3	215.6	214.9	214.3
72.5°	194.0	192.9	191.7	190.8	190.1	189.5	188.8	188.1
75°	154.0	153.5	153.0	152.4	151.7	151.0	150.4	149.7
77.5°	117.3	117.0	116.7	116.3	115.8	115.4	114.9	114.4
80°	93.9	93.7	93.5	93.3	92.9	92.6	92.3	91.9
82.5°	71.7	71.4	71.1	70.9	70.9	70.8	70.7	70.7
85°	42.2	42.0	41.9	41.6	41.3	40.9	40.6	40.3
87.5°	18.5	18.7	18.8	18.8	18.7	18.5	18.3	18.2
90°	13.5	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	30.7	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	59.5	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	93.2	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	116.5	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	140.6	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	179.4	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.3	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.4	250.9	251.4	251.6	251.4	251.2	251.1	250.9



TEST NUMBER: P333381

CATALOG NUMBER: S125DIW-S610D770U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.6	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	324.1	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.6	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	428.1	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.5	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.6	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	543.1	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.4	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.4	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.2	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.4	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	774.6	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	815.6	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	843.9	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	868.4	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.2	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.2	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	915.9	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	929.8	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	938.1	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	944.0	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	950.7	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	953.7	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)