

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333732-927

Luminaire Tested: **S125RDIW-S1270D1340U927-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333732-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1340U927-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8149.1 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48
1	98	94	90	87	90	86	83	80	73	70	68	60	59	57	49	48	47	41
2	89	82	76	71	82	76	71	66	64	60	57	53	51	48	43	41	40	35
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	39	36	34	30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30	26
5	69	57	49	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	63	52	44	38	58	48	41	36	41	36	31	35	30	27	28	25	23	20
7	59	47	39	33	54	43	36	31	37	32	28	31	27	24	26	23	21	18
8	54	42	35	29	50	39	33	28	34	29	25	29	25	22	24	21	18	16
9	51	39	31	26	47	36	29	25	31	26	22	26	22	19	22	19	17	14
10	47	35	28	24	44	33	27	22	29	23	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	9715	9715	9715	9715
5°	11177	9728	8591	9728
10°	12821	9678	7581	9678
15°	13848	9579	6738	9579
20°	15270	9465	6222	9465
25°	17672	9311	5773	9311
30°	19231	9150	5480	9150
35°	16222	8964	5210	8964
40°	11328	8627	4977	8627
45°	8404	8173	4748	8173
50°	6701	7700	4554	7700
55°	5687	7113	4380	7113
60°	4914	6589	4100	6589
65°	4378	6021	3529	6021
70°	3846	5516	3218	5516
75°	3329	4776	3019	4776
80°	2525	4020	2525	4020
85°	2104	3157	2379	3157



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.3	1.8
10°-20°	422.7	5.2
20°-30°	670.3	8.2
30°-40°	808.3	9.9
40°-50°	721.8	8.9
50°-60°	553.6	6.8
60°-70°	359.7	4.4
70°-80°	174.9	2.1
80°-90°	44.6	0.5
90°-100°	50.3	0.6
100°-110°	309.9	3.8
110°-120°	562.0	6.9
120°-130°	721.3	8.9
130°-140°	775.8	9.5
140°-150°	728.2	8.9
150°-160°	589.1	7.2
160°-170°	381.0	4.7
170°-180°	131.4	1.6
0°-30°	1237.3	15.2
0°-40°	2045.6	25.1
0°-60°	3320.9	40.8
0°-90°	3900.2	47.9
90°-120°	922.2	11.3
90°-150°	3147.5	38.6
90°-180°	4249.0	52.1
0°-180°	8149.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1504	1504	1504	1504	1504	
5°	1724	1501	1325	1501	1724	172
15°	2071	1433	1008	1433	2071	593
25°	2480	1307	810	1307	2480	1139
35°	2058	1137	661	1137	2058	1243
45°	920	895	520	895	920	734
55°	505	632	389	632	505	458
65°	286	394	231	394	286	285
75°	133	191	121	191	133	142
85°	28	43	32	43	28	33
90°	25	1	25	1	25	12
95°	22	58	22	58	22	18
105°	305	302	305	302	305	275
115°	562	566	562	566	562	558
125°	805	805	805	805	805	716
135°	1000	1004	1000	1004	1000	772
145°	1161	1164	1161	1164	1161	725
155°	1273	1282	1273	1282	1273	587
165°	1346	1353	1346	1353	1346	380
175°	1377	1384	1377	1384	1377	131
180°	1384	1384	1384	1384	1384	



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1582.3	1581.4	1583.3	1577.9	1578.3	1569.9	1569.9	1563.5	1555.1	1548.7	1545.8
5°	1724.1	1725.4	1722.8	1713.6	1707.5	1698.2	1687.7	1669.1	1653.7	1638.9	1627.1
7.5°	1870.1	1871.0	1862.8	1860.0	1844.4	1833.0	1809.7	1784.5	1762.1	1733.8	1712.0
10°	1955.0	1954.5	1945.8	1939.0	1925.4	1908.1	1885.3	1855.6	1827.9	1797.0	1767.4
12.5°	2004.5	2002.9	2000.1	1991.9	1979.3	1964.0	1944.6	1915.4	1881.2	1847.4	1812.8
15°	2071.2	2066.8	2058.8	2048.3	2030.4	2012.5	1990.8	1964.9	1932.2	1893.9	1861.8
17.5°	2153.6	2153.8	2141.4	2126.9	2102.5	2070.9	2037.6	1995.7	1951.2	1909.1	1874.9
20°	2221.8	2219.9	2207.7	2179.2	2151.4	2111.9	2073.6	2022.4	1968.0	1913.0	1870.4
22.5°	2319.7	2314.8	2302.0	2264.7	2221.6	2170.7	2112.1	2049.5	1983.9	1921.4	1865.5
25°	2479.9	2476.2	2450.9	2407.7	2347.2	2268.7	2192.2	2106.3	2011.9	1929.8	1861.8
27.5°	2589.6	2585.5	2566.7	2530.9	2475.0	2392.5	2288.9	2174.1	2056.2	1943.2	1845.2
30°	2578.7	2588.0	2585.5	2568.9	2526.9	2452.8	2357.1	2228.0	2087.8	1955.0	1838.3
32.5°	2423.6	2431.9	2453.6	2486.3	2488.8	2459.2	2387.7	2268.5	2123.4	1972.4	1832.9
35°	2057.5	2068.7	2110.7	2176.8	2263.2	2335.4	2350.2	2286.1	2155.8	1993.4	1824.8
37.5°	1581.8	1642.6	1677.9	1747.5	1878.1	2011.0	2138.8	2185.9	2130.4	1984.7	1811.6
40°	1343.7	1358.5	1421.5	1499.9	1609.9	1748.2	1930.4	2061.9	2066.2	1964.9	1790.8
42.5°	1150.1	1168.9	1212.0	1274.7	1368.8	1507.1	1695.2	1868.8	1949.2	1910.6	1763.6
45°	920.1	934.3	965.8	1014.0	1086.2	1200.5	1362.2	1562.9	1722.3	1784.6	1690.8
47.5°	755.8	763.5	790.9	827.6	881.1	964.3	1089.6	1263.8	1454.8	1588.9	1575.7
50°	666.9	675.6	696.6	724.4	769.4	839.8	939.8	1085.0	1282.0	1445.6	1478.4
52.5°	597.8	604.9	618.0	644.3	681.5	735.6	816.3	947.6	1124.9	1298.9	1374.6
55°	505.1	510.1	520.5	535.4	565.1	604.0	673.7	764.5	907.8	1083.2	1194.3
57.5°	428.8	431.3	437.9	451.6	472.1	500.6	551.0	627.9	730.6	888.6	1011.2
60°	380.4	382.9	391.5	400.8	416.8	442.8	482.3	536.0	634.8	765.1	889.2
62.5°	341.8	343.3	347.1	356.3	370.4	390.4	421.5	465.3	543.9	658.4	775.6
65°	286.5	287.2	288.4	295.8	304.4	319.2	339.6	370.5	429.8	516.3	620.0
67.5°	233.5	234.2	238.6	241.2	250.3	258.0	270.0	293.6	335.3	393.6	474.3
70°	203.7	203.2	207.5	210.6	213.7	222.9	230.9	250.1	276.0	320.5	387.8
72.5°	176.1	174.5	176.3	177.4	181.6	187.8	195.9	207.6	227.6	258.3	309.7
75°	133.4	134.0	134.0	135.2	138.3	140.8	143.2	149.4	160.6	180.9	208.7
77.5°	93.6	92.6	95.2	95.6	97.4	100.1	102.3	104.7	109.3	117.7	132.1
80°	67.9	67.9	68.5	70.4	69.8	71.0	74.1	76.6	82.1	87.1	92.0
82.5°	52.1	51.7	52.2	52.6	52.5	53.7	54.8	55.3	57.4	59.9	63.4
85°	28.4	28.4	29.0	29.0	29.6	29.6	30.3	30.3	30.3	30.9	31.5
87.5°	15.8	15.1	14.5	14.4	14.7	15.5	14.8	14.1	13.9	13.6	13.9
90°	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7	17.6	16.4	14.8
92.5°	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7	17.6	16.4	15.0
95°	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7	17.6	16.4	25.0
97.5°	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6	44.0	50.5	67.6
100°	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5	144.5	178.5	177.5
102.5°	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8	221.3	227.7	227.1
105°	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0	386.9	386.9	386.4
110°	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7	440.4	441.0	440.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8	492.7	493.5	493.3
115°	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5	571.4	572.4	572.1
117.5°	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5	647.7	648.9	648.0
120°	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5	696.0	696.4	695.8
122.5°	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3	742.8	743.2	742.9
125°	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5	811.4	812.3	812.3
127.5°	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9	873.4	873.9	874.0
130°	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5	914.3	914.9	914.7
132.5°	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6	951.7	951.8	952.4
135°	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3	1007.8	1008.2	1008.7
137.5°	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3	1059.2	1059.1	1059.5
140°	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2	1090.8	1090.3	1090.5
142.5°	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4	1122.4	1122.3	1122.0
145°	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6	1166.4	1166.2	1166.2
147.5°	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5	1204.2	1204.0	1203.6
150°	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7	1228.2	1227.7	1227.2
152.5°	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0	1249.5	1249.0	1248.6
155°	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4	1278.7	1278.0	1277.6
157.5°	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7	1302.9	1302.2	1302.2
160°	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8	1317.9	1317.0	1316.8
162.5°	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6	1331.3	1330.1	1329.8
165°	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4	1349.1	1347.7	1347.5
167.5°	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0	1362.3	1360.7	1360.4
170°	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9	1369.0	1367.2	1367.0
172.5°	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3	1374.6	1372.9	1372.5
175°	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1	1380.3	1378.5	1378.3
177.5°	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6	1383.3	1382.0	1381.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1545.8	1542.3	1535.9	1529.9	1522.6	1516.2	1511.6	1506.3	1499.4	1491.0	1484.0
5°	1614.2	1600.6	1582.7	1567.3	1547.5	1532.1	1516.0	1500.6	1485.1	1465.4	1448.1
7.5°	1690.0	1662.0	1634.7	1600.4	1569.2	1541.4	1514.7	1487.7	1461.3	1433.2	1406.2
10°	1736.5	1702.5	1664.9	1621.6	1582.1	1544.4	1509.8	1475.8	1440.0	1408.6	1374.6
12.5°	1780.0	1736.1	1693.0	1638.4	1590.9	1544.9	1500.9	1458.6	1420.3	1379.4	1343.0
15°	1819.2	1776.0	1727.8	1661.1	1595.1	1539.4	1487.6	1432.7	1385.1	1339.4	1298.6
17.5°	1834.4	1789.1	1733.1	1669.0	1596.8	1526.9	1460.1	1399.8	1343.9	1290.6	1244.8
20°	1828.4	1784.6	1727.2	1666.0	1588.9	1516.0	1443.8	1377.1	1314.7	1258.5	1209.7
22.5°	1814.2	1768.8	1713.3	1648.8	1575.5	1498.3	1421.0	1349.9	1284.5	1226.4	1173.1
25°	1792.6	1730.9	1674.1	1611.1	1541.3	1464.7	1385.1	1306.6	1236.9	1177.6	1119.6
27.5°	1770.3	1693.2	1621.0	1558.4	1484.6	1416.3	1339.5	1259.1	1185.7	1125.4	1065.8
30°	1750.0	1663.6	1583.9	1512.9	1443.1	1378.3	1305.4	1227.0	1151.7	1089.3	1028.8
32.5°	1724.8	1632.9	1545.4	1463.5	1396.2	1331.9	1265.9	1191.0	1117.6	1053.2	991.7
35°	1693.2	1575.9	1480.8	1393.8	1319.0	1256.6	1197.4	1136.9	1063.3	996.6	936.8
37.5°	1651.7	1518.6	1408.6	1313.7	1234.9	1172.3	1125.5	1070.2	1003.1	939.2	883.7
40°	1626.5	1477.1	1356.7	1262.8	1180.0	1114.0	1070.2	1023.3	962.1	902.2	846.6
42.5°	1592.9	1439.1	1304.3	1206.5	1123.2	1059.6	1015.3	974.3	923.1	866.6	807.1
45°	1527.1	1365.3	1223.9	1119.0	1035.0	972.6	931.2	894.8	855.9	804.0	752.1
47.5°	1441.4	1288.4	1140.4	1025.8	943.6	885.7	845.5	816.7	788.9	744.8	694.4
50°	1372.8	1225.2	1080.6	969.5	881.8	826.9	789.2	766.4	741.0	700.8	658.9
52.5°	1291.7	1159.9	1018.4	904.8	822.0	770.6	734.4	711.5	690.6	657.9	617.9
55°	1164.0	1048.5	918.9	815.7	739.8	687.9	653.3	631.7	619.4	591.6	560.1
57.5°	1016.7	933.9	819.6	720.2	653.0	601.7	576.4	558.0	544.1	524.4	502.2
60°	913.9	855.9	753.4	658.9	597.1	548.3	525.5	510.1	497.1	480.5	463.1
62.5°	809.7	767.5	678.3	597.1	540.3	499.5	478.1	464.1	449.2	437.9	421.1
65°	670.0	632.3	570.6	507.0	454.5	421.8	406.3	394.0	384.7	372.3	360.6
67.5°	521.2	505.9	463.3	419.4	381.8	352.6	339.3	330.7	319.5	312.1	304.0
70°	429.8	422.4	392.1	363.1	327.9	308.2	295.8	292.1	278.5	271.1	265.5
72.5°	348.8	345.3	327.9	307.8	283.0	265.6	254.3	250.1	241.5	235.5	232.0
75°	239.0	240.2	237.1	224.2	214.9	203.7	193.9	191.4	185.3	180.3	177.2
77.5°	151.1	157.5	157.7	157.1	153.4	146.6	142.5	140.7	134.6	132.8	132.1
80°	103.8	110.5	116.7	116.1	114.9	113.0	110.0	108.1	105.0	103.1	101.9
82.5°	69.2	75.5	80.6	84.0	83.7	81.9	79.8	78.9	78.3	76.9	76.7
85°	32.7	34.0	35.8	40.2	43.3	43.8	43.3	42.6	40.7	41.4	42.0
87.5°	14.0	13.7	13.9	13.5	12.7	14.7	15.9	16.0	15.4	14.7	14.2
90°	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0	2.9	4.7	6.5
92.5°	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8	14.5	13.2	12.0
95°	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5	57.8	57.1	56.4
97.5°	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1	123.3	124.5	125.7
100°	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3	172.0	172.6	173.3
102.5°	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3	222.2	223.1	223.9
105°	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6	302.5	303.4	304.3
107.5°	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8	384.8	384.8	384.8
110°	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9	490.4	491.0	491.5
115°	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2	567.3	568.5	569.6
117.5°	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2	645.1	645.1	645.0
120°	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3	694.2	694.0	693.7
122.5°	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8	738.7	739.6	740.5
125°	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2	806.8	808.3	809.9
127.5°	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3	870.5	871.6	872.7
130°	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7	909.9	911.0	912.2
132.5°	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2	949.4	950.8	952.1
135°	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2	1005.5	1006.9	1008.2
137.5°	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7	1056.8	1058.0	1059.1
140°	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3	1089.7	1090.2	1090.6
142.5°	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6	1119.9	1120.1	1120.5
145°	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1	1164.6	1165.1	1165.5
147.5°	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1	1203.0	1202.9	1202.8
150°	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1227.2	1226.9	1226.4
152.5°	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5	1250.5	1249.5	1248.6
155°	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1	1280.7	1279.4	1278.0
157.5°	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7	1304.9	1304.0	1303.2
160°	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1	1320.7	1319.4	1318.0
162.5°	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2	1333.9	1332.5	1331.1
165°	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9	1351.5	1350.1	1348.8
167.5°	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0	1364.6	1363.2	1361.8
170°	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4	1371.8	1370.2	1368.6
172.5°	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3	1376.7	1375.1	1373.5
175°	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6	1382.3	1380.9	1379.5
177.5°	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1	1385.0	1383.9	1382.8
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1479.1	1472.2	1467.2	1457.3	1450.4	1447.5	1442.0	1440.5	1446.0	1442.0	1441.5
5°	1435.1	1417.2	1403.0	1388.8	1373.3	1363.5	1348.7	1346.2	1342.5	1336.9	1335.7
7.5°	1382.4	1359.1	1340.8	1317.3	1296.9	1280.5	1261.9	1253.2	1248.4	1241.2	1231.6
10°	1346.8	1319.0	1294.3	1270.8	1245.5	1225.2	1206.7	1192.4	1183.1	1174.5	1170.8
12.5°	1311.7	1283.4	1251.8	1223.4	1195.2	1172.3	1151.8	1142.6	1132.3	1122.1	1113.5
15°	1257.3	1219.6	1185.0	1152.3	1128.2	1103.5	1083.7	1070.2	1054.7	1050.4	1033.7
17.5°	1199.4	1162.5	1122.0	1087.6	1059.6	1032.5	1010.7	995.3	983.7	967.8	960.1
20°	1163.4	1119.6	1080.1	1048.5	1017.6	985.6	963.3	950.4	939.2	926.3	920.1
22.5°	1124.9	1082.0	1041.5	1004.6	973.2	941.6	925.7	912.4	899.7	887.7	879.6
25°	1068.3	1025.1	982.5	944.2	911.5	888.6	870.1	854.6	847.9	836.1	827.4
27.5°	1012.3	966.4	922.2	884.0	858.3	835.8	820.5	808.3	796.1	785.8	778.3
30°	976.3	929.4	881.2	851.0	823.8	802.2	785.4	773.7	764.5	755.2	749.6
32.5°	940.2	891.8	849.1	816.3	790.7	772.0	754.9	743.6	733.9	723.6	717.1
35°	882.4	833.1	798.4	766.4	741.0	723.7	712.0	695.9	687.9	680.5	673.7
37.5°	828.7	782.8	745.4	717.2	695.2	678.0	662.8	654.2	644.3	637.6	632.0
40°	789.2	747.2	713.2	683.6	667.6	648.4	634.2	623.1	615.7	607.0	600.9
42.5°	753.6	714.6	681.6	655.0	634.9	618.8	605.1	593.9	584.6	578.4	573.1
45°	703.4	664.5	632.3	607.6	589.1	573.7	559.4	553.9	541.5	534.2	531.7
47.5°	651.3	616.6	585.5	562.8	543.8	529.2	515.9	504.5	497.7	490.4	486.5
50°	616.3	583.0	553.9	531.7	513.2	497.1	484.7	477.4	468.1	461.3	456.4
52.5°	581.2	550.3	521.3	500.0	484.0	467.9	454.2	446.7	437.9	433.6	430.2
55°	531.1	498.4	473.6	452.7	435.9	421.1	408.2	400.8	395.2	390.9	389.7
57.5°	474.3	448.3	425.3	406.5	389.1	375.2	363.8	356.8	351.9	351.3	347.5
60°	437.2	413.8	392.8	372.3	357.5	344.6	334.7	326.7	321.7	321.1	319.9
62.5°	400.1	377.6	358.1	340.2	326.9	314.4	305.1	296.0	293.1	290.0	287.2
65°	345.2	324.8	308.8	294.5	280.4	269.8	260.6	255.0	248.3	244.5	237.7
67.5°	291.2	275.4	260.0	248.0	236.9	226.9	219.2	211.0	206.4	203.4	198.4
70°	255.6	243.3	227.8	214.9	206.3	198.2	192.0	182.8	179.7	177.2	174.8
72.5°	222.0	211.2	198.2	187.7	179.1	171.5	164.4	160.0	157.0	154.5	153.0
75°	174.8	164.3	153.1	145.8	139.6	133.4	129.7	126.6	125.3	124.8	122.2
77.5°	128.3	122.8	113.8	108.0	103.9	101.4	98.1	96.5	96.3	93.6	92.8
80°	98.2	95.1	87.7	85.2	82.1	79.7	77.8	74.7	71.6	70.4	68.5
82.5°	73.0	69.9	66.9	63.0	60.4	58.9	57.0	55.9	56.3	54.6	53.7
85°	38.9	35.8	34.6	34.0	32.7	34.0	33.4	32.7	32.1	31.5	32.1
87.5°	14.0	14.3	14.2	15.5	14.3	15.1	15.4	15.1	15.3	15.5	15.2
90°	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7	19.8	21.0	21.9
92.5°	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7	19.8	21.0	21.7
95°	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7	19.8	21.0	21.5
97.5°	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6	31.2	24.7	21.5
100°	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5	76.6	42.6	25.2
102.5°	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8	208.4	202.0	191.0
105°	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.6	305.5
107.5°	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0	387.1	387.1	386.7
110°	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7	439.0	438.3	438.1



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8	491.0	490.1	489.5
115°	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5	569.6	568.7	567.5
117.5°	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5	645.3	644.1	643.2
120°	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5	695.1	694.6	693.8
122.5°	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3	741.8	741.4	740.5
125°	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5	809.6	808.7	807.9
127.5°	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9	872.4	871.9	870.8
130°	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5	912.8	912.2	911.2
132.5°	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6	951.4	951.3	950.6
135°	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3	1006.9	1006.4	1005.5
137.5°	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3	1059.4	1059.5	1058.9
140°	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2	1091.6	1092.1	1091.6
142.5°	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4	1122.6	1122.7	1122.0
145°	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6	1166.9	1167.1	1166.6
147.5°	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5	1204.8	1205.1	1204.4
150°	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7	1229.1	1229.5	1228.8
152.5°	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0	1250.5	1250.9	1250.3
155°	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4	1280.0	1280.7	1280.2
157.5°	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7	1304.4	1305.1	1304.6
160°	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8	1319.7	1320.6	1320.2
162.5°	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6	1334.0	1335.2	1334.8
165°	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4	1351.9	1353.2	1353.0
167.5°	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0	1365.6	1367.2	1367.0
170°	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9	1372.7	1374.5	1374.4
172.5°	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3	1377.9	1379.5	1379.3
175°	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1	1383.9	1385.8	1385.7
177.5°	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6	1385.8	1387.1	1387.0
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1441.1	1435.6	1434.1	1436.1	1434.1	1435.6	1441.1	1441.5	1442.0	1446.0	1440.5
5°	1329.5	1323.3	1326.4	1325.2	1326.4	1323.3	1329.5	1335.7	1336.9	1342.5	1346.2
7.5°	1231.4	1223.8	1215.6	1218.2	1215.6	1223.8	1231.4	1231.6	1241.2	1248.4	1253.2
10°	1162.8	1156.6	1152.9	1156.0	1152.9	1156.6	1162.8	1170.8	1174.5	1183.1	1192.4
12.5°	1105.0	1101.3	1098.0	1096.7	1098.0	1101.3	1105.0	1113.5	1122.1	1132.3	1142.6
15°	1026.3	1018.9	1015.8	1007.8	1015.8	1018.9	1026.3	1033.7	1050.4	1054.7	1070.2
17.5°	953.8	951.3	943.3	939.8	943.3	951.3	953.8	960.1	967.8	983.7	995.3
20°	910.9	908.4	900.3	905.3	900.3	908.4	910.9	920.1	926.3	939.2	950.4
22.5°	875.3	869.8	867.2	865.8	867.2	869.8	875.3	879.6	887.7	899.7	912.4
25°	825.0	817.0	813.9	810.2	813.9	817.0	825.0	827.4	836.1	847.9	854.6
27.5°	774.8	770.6	766.4	765.5	766.4	770.6	774.8	778.3	785.8	796.1	808.3
30°	742.3	737.9	734.8	734.8	734.8	737.9	742.3	749.6	755.2	764.5	773.7
32.5°	713.1	709.8	706.7	706.2	706.7	709.8	713.1	717.1	723.6	733.9	743.6
35°	670.7	665.7	664.5	660.8	664.5	665.7	670.7	673.7	680.5	687.9	695.9
37.5°	626.5	622.4	622.3	621.9	622.3	622.4	626.5	632.0	637.6	644.3	654.2
40°	598.3	595.2	594.7	590.3	594.7	595.2	598.3	600.9	607.0	615.7	623.1
42.5°	568.2	566.6	564.5	562.7	564.5	566.6	568.2	573.1	578.4	584.6	593.9
45°	527.4	523.0	523.0	519.9	523.0	523.0	527.4	531.7	534.2	541.5	553.9
47.5°	485.1	481.8	482.1	479.0	482.1	481.8	485.1	486.5	490.4	497.7	504.5
50°	456.9	455.1	454.5	453.3	454.5	455.1	456.9	456.4	461.3	468.1	477.4
52.5°	428.8	427.9	430.3	427.5	430.3	427.9	428.8	430.2	433.6	437.9	446.7
55°	390.9	389.0	392.8	389.0	392.8	389.0	390.9	389.7	390.9	395.2	400.8
57.5°	347.3	345.5	348.9	347.1	348.9	345.5	347.3	347.5	351.3	351.9	356.8
60°	318.6	315.0	316.8	317.4	316.8	315.0	318.6	319.9	321.1	321.7	326.7
62.5°	284.6	282.3	283.7	280.8	283.7	282.3	284.6	287.2	290.0	293.1	296.0
65°	236.5	234.6	232.2	230.9	232.2	234.6	236.5	237.7	244.5	248.3	255.0
67.5°	198.7	194.2	194.2	195.1	194.2	194.2	198.7	198.4	203.4	206.4	211.0
70°	171.0	171.0	170.4	170.4	170.4	171.0	171.0	174.8	177.2	179.7	182.8
72.5°	151.8	151.3	150.2	149.7	150.2	151.3	151.8	153.0	154.5	157.0	160.0
75°	122.2	122.9	121.7	121.0	121.7	122.9	122.2	122.2	124.8	125.3	126.6
77.5°	90.3	87.7	89.0	87.7	89.0	87.7	90.3	92.8	93.6	96.3	96.5
80°	68.5	67.9	69.8	67.9	69.8	67.9	68.5	68.5	70.4	71.6	74.7
82.5°	54.2	53.6	54.5	53.1	54.5	53.6	54.2	53.7	54.6	56.3	55.9
85°	32.7	32.1	31.5	32.1	31.5	32.1	32.7	32.1	31.5	32.1	32.7
87.5°	15.8	15.5	15.7	15.8	15.7	15.5	15.8	15.2	15.5	15.3	15.1
90°	22.6	23.2	23.9	24.6	23.9	23.2	22.6	21.9	21.0	19.8	18.7
92.5°	22.0	22.3	22.7	23.0	22.7	22.3	22.0	21.7	21.0	19.8	18.7
95°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.0	19.8	18.7
97.5°	21.5	21.5	21.5	21.5	21.5	21.5	21.5	21.5	24.7	31.2	37.6
100°	24.2	23.4	22.4	21.5	22.4	23.4	24.2	25.2	42.6	76.6	110.5
102.5°	175.5	160.0	144.5	129.0	144.5	160.0	175.5	191.0	202.0	208.4	214.8
105°	305.3	305.1	304.8	304.6	304.8	305.1	305.3	305.5	305.6	305.6	305.6
107.5°	386.0	385.4	384.7	384.0	384.7	385.4	386.0	386.7	387.1	387.1	387.0
110°	438.3	438.6	438.8	439.0	438.8	438.6	438.3	438.1	438.3	439.0	439.7



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	489.2	488.9	488.5	488.2	488.5	488.9	489.2	489.5	490.1	491.0	491.8
115°	566.2	564.8	563.4	562.1	563.4	564.8	566.2	567.5	568.7	569.6	570.5
117.5°	642.6	642.1	641.4	640.9	641.4	642.1	642.6	643.2	644.1	645.3	646.5
120°	692.7	691.5	690.4	689.3	690.4	691.5	692.7	693.8	694.6	695.1	695.5
122.5°	739.2	737.8	736.5	735.2	736.5	737.8	739.2	740.5	741.4	741.8	742.3
125°	807.2	806.5	805.8	805.2	805.8	806.5	807.2	807.9	808.7	809.6	810.5
127.5°	869.1	867.4	865.7	864.0	865.7	867.4	869.1	870.8	871.9	872.4	872.9
130°	910.1	908.9	907.8	906.7	907.8	908.9	910.1	911.2	912.2	912.8	913.5
132.5°	949.5	948.4	947.2	946.1	947.2	948.4	949.5	950.6	951.3	951.4	951.6
135°	1004.2	1002.7	1001.4	1000.1	1001.4	1002.7	1004.2	1005.5	1006.4	1006.9	1007.3
137.5°	1057.7	1056.5	1055.3	1054.2	1055.3	1056.5	1057.7	1058.9	1059.5	1059.4	1059.3
140°	1090.3	1088.9	1087.6	1086.2	1087.6	1088.9	1090.3	1091.6	1092.1	1091.6	1091.2
142.5°	1120.6	1119.3	1117.9	1116.6	1117.9	1119.3	1120.6	1122.0	1122.7	1122.6	1122.4
145°	1165.1	1163.8	1162.4	1161.1	1162.4	1163.8	1165.1	1166.6	1167.1	1166.9	1166.6
147.5°	1202.7	1201.0	1199.4	1197.8	1199.4	1201.0	1202.7	1204.4	1205.1	1204.8	1204.5
150°	1227.0	1225.2	1223.4	1221.5	1223.4	1225.2	1227.0	1228.8	1229.5	1229.1	1228.7
152.5°	1248.6	1247.1	1245.4	1243.7	1245.4	1247.1	1248.6	1250.3	1250.9	1250.5	1250.0
155°	1278.3	1276.5	1274.7	1272.9	1274.7	1276.5	1278.3	1280.2	1280.7	1280.0	1279.4
157.5°	1302.7	1300.9	1299.1	1297.3	1299.1	1300.9	1302.7	1304.6	1305.1	1304.4	1303.7
160°	1318.3	1316.5	1314.7	1312.9	1314.7	1316.5	1318.3	1320.2	1320.6	1319.7	1318.8
162.5°	1332.8	1330.8	1328.8	1326.8	1328.8	1330.8	1332.8	1334.8	1335.2	1334.0	1332.6
165°	1351.1	1349.3	1347.5	1345.7	1347.5	1349.3	1351.1	1353.0	1353.2	1351.9	1350.4
167.5°	1364.9	1362.9	1360.9	1358.8	1360.9	1362.9	1364.9	1367.0	1367.2	1365.6	1364.0
170°	1372.4	1370.3	1368.3	1366.2	1368.3	1370.3	1372.4	1374.4	1374.5	1372.7	1370.9
172.5°	1377.3	1375.2	1373.2	1371.1	1373.2	1375.2	1377.3	1379.3	1379.5	1377.9	1376.3
175°	1383.6	1381.6	1379.5	1377.4	1379.5	1381.6	1383.6	1385.7	1385.8	1383.9	1382.1
177.5°	1385.5	1384.1	1382.6	1381.2	1382.6	1384.1	1385.5	1387.0	1387.1	1385.8	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1442.0	1447.5	1450.4	1457.3	1467.2	1472.2	1479.1	1484.0	1491.0	1499.4	1506.3
5°	1348.7	1363.5	1373.3	1388.8	1403.0	1417.2	1435.1	1448.1	1465.4	1485.1	1500.6
7.5°	1261.9	1280.5	1296.9	1317.3	1340.8	1359.1	1382.4	1406.2	1433.2	1461.3	1487.7
10°	1206.7	1225.2	1245.5	1270.8	1294.3	1319.0	1346.8	1374.6	1408.6	1440.0	1475.8
12.5°	1151.8	1172.3	1195.2	1223.4	1251.8	1283.4	1311.7	1343.0	1379.4	1420.3	1458.6
15°	1083.7	1103.5	1128.2	1152.3	1185.0	1219.6	1257.3	1298.6	1339.4	1385.1	1432.7
17.5°	1010.7	1032.5	1059.6	1087.6	1122.0	1162.5	1199.4	1244.8	1290.6	1343.9	1399.8
20°	963.3	985.6	1017.6	1048.5	1080.1	1119.6	1163.4	1209.7	1258.5	1314.7	1377.1
22.5°	925.7	941.6	973.2	1004.6	1041.5	1082.0	1124.9	1173.1	1226.4	1284.5	1349.9
25°	870.1	888.6	911.5	944.2	982.5	1025.1	1068.3	1119.6	1177.6	1236.9	1306.6
27.5°	820.5	835.8	858.3	884.0	922.2	966.4	1012.3	1065.8	1125.4	1185.7	1259.1
30°	785.4	802.2	823.8	851.0	881.2	929.4	976.3	1028.8	1089.3	1151.7	1227.0
32.5°	754.9	772.0	790.7	816.3	849.1	891.8	940.2	991.7	1053.2	1117.6	1191.0
35°	712.0	723.7	741.0	766.4	798.4	833.1	882.4	936.8	996.6	1063.3	1136.9
37.5°	662.8	678.0	695.2	717.2	745.4	782.8	828.7	883.7	939.2	1003.1	1070.2
40°	634.2	648.4	667.6	683.6	713.2	747.2	789.2	846.6	902.2	962.1	1023.3
42.5°	605.1	618.8	634.9	655.0	681.6	714.6	753.6	807.1	866.6	923.1	974.3
45°	559.4	573.7	589.1	607.6	632.3	664.5	703.4	752.1	804.0	855.9	894.8
47.5°	515.9	529.2	543.8	562.8	585.5	616.6	651.3	694.4	744.8	788.9	816.7
50°	484.7	497.1	513.2	531.7	553.9	583.0	616.3	658.9	700.8	741.0	766.4
52.5°	454.2	467.9	484.0	500.0	521.3	550.3	581.2	617.9	657.9	690.6	711.5
55°	408.2	421.1	435.9	452.7	473.6	498.4	531.1	560.1	591.6	619.4	631.7
57.5°	363.8	375.2	389.1	406.5	425.3	448.3	474.3	502.2	524.4	544.1	558.0
60°	334.7	344.6	357.5	372.3	392.8	413.8	437.2	463.1	480.5	497.1	510.1
62.5°	305.1	314.4	326.9	340.2	358.1	377.6	400.1	421.1	437.9	449.2	464.1
65°	260.6	269.8	280.4	294.5	308.8	324.8	345.2	360.6	372.3	384.7	394.0
67.5°	219.2	226.9	236.9	248.0	260.0	275.4	291.2	304.0	312.1	319.5	330.7
70°	192.0	198.2	206.3	214.9	227.8	243.3	255.6	265.5	271.1	278.5	292.1
72.5°	164.4	171.5	179.1	187.7	198.2	211.2	222.0	232.0	235.5	241.5	250.1
75°	129.7	133.4	139.6	145.8	153.1	164.3	174.8	177.2	180.3	185.3	191.4
77.5°	98.1	101.4	103.9	108.0	113.8	122.8	128.3	132.1	132.8	134.6	140.7
80°	77.8	79.7	82.1	85.2	87.7	95.1	98.2	101.9	103.1	105.0	108.1
82.5°	57.0	58.9	60.4	63.0	66.9	69.9	73.0	76.7	76.9	78.3	78.9
85°	33.4	34.0	32.7	34.0	34.6	35.8	38.9	42.0	41.4	40.7	42.6
87.5°	15.4	15.1	14.3	15.5	14.2	14.3	14.0	14.2	14.7	15.4	16.0
90°	17.6	16.4	14.8	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0
92.5°	17.6	16.4	15.0	13.5	12.2	10.8	10.7	12.0	13.2	14.5	15.8
95°	17.6	16.4	25.0	33.7	42.4	51.0	55.7	56.4	57.1	57.8	58.5
97.5°	44.0	50.5	67.6	84.8	101.9	119.0	127.0	125.7	124.5	123.3	122.1
100°	144.5	178.5	177.5	176.7	175.7	174.8	174.0	173.3	172.6	172.0	171.3
102.5°	221.3	227.7	227.1	226.6	226.1	225.5	224.8	223.9	223.1	222.2	221.3
105°	305.6	305.6	305.6	305.6	305.6	305.6	305.2	304.3	303.4	302.5	301.6
107.5°	386.9	386.9	386.4	386.0	385.6	385.1	384.8	384.8	384.8	384.8	384.8
110°	440.4	441.0	440.6	440.1	439.7	439.2	439.0	439.0	439.0	439.0	439.0



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	492.7	493.5	493.3	493.0	492.7	492.5	492.0	491.5	491.0	490.4	489.9
115°	571.4	572.4	572.1	571.9	571.6	571.4	570.8	569.6	568.5	567.3	566.2
117.5°	647.7	648.9	648.0	647.1	646.3	645.4	645.0	645.0	645.1	645.1	645.2
120°	696.0	696.4	695.8	695.1	694.3	693.7	693.5	693.7	694.0	694.2	694.3
122.5°	742.8	743.2	742.9	742.6	742.3	742.0	741.3	740.5	739.6	738.7	737.8
125°	811.4	812.3	812.3	812.3	812.3	812.3	811.5	809.9	808.3	806.8	805.2
127.5°	873.4	873.9	874.0	874.2	874.3	874.4	873.9	872.7	871.6	870.5	869.3
130°	914.3	914.9	914.7	914.4	914.3	914.0	913.3	912.2	911.0	909.9	908.7
132.5°	951.7	951.8	952.4	952.8	953.3	953.9	953.4	952.1	950.8	949.4	948.2
135°	1007.8	1008.2	1008.7	1009.2	1009.6	1010.0	1009.6	1008.2	1006.9	1005.5	1004.2
137.5°	1059.2	1059.1	1059.5	1059.9	1060.3	1060.7	1060.3	1059.1	1058.0	1056.8	1055.7
140°	1090.8	1090.3	1090.5	1090.8	1091.0	1091.2	1091.1	1090.6	1090.2	1089.7	1089.3
142.5°	1122.4	1122.3	1122.0	1121.7	1121.3	1121.0	1120.7	1120.5	1120.1	1119.9	1119.6
145°	1166.4	1166.2	1166.2	1166.2	1166.2	1166.2	1165.9	1165.5	1165.1	1164.6	1164.1
147.5°	1204.2	1204.0	1203.6	1203.4	1203.1	1202.8	1202.8	1202.8	1202.9	1203.0	1203.1
150°	1228.2	1227.7	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7
152.5°	1249.5	1249.0	1248.6	1248.2	1247.7	1247.2	1247.5	1248.6	1249.5	1250.5	1251.5
155°	1278.7	1278.0	1277.6	1277.1	1276.6	1276.2	1276.6	1278.0	1279.4	1280.7	1282.1
157.5°	1302.9	1302.2	1302.2	1302.1	1302.0	1302.0	1302.4	1303.2	1304.0	1304.9	1305.7
160°	1317.9	1317.0	1316.8	1316.5	1316.3	1316.1	1316.6	1318.0	1319.4	1320.7	1322.1
162.5°	1331.3	1330.1	1329.8	1329.7	1329.4	1329.2	1329.8	1331.1	1332.5	1333.9	1335.2
165°	1349.1	1347.7	1347.5	1347.3	1347.0	1346.8	1347.4	1348.8	1350.1	1351.5	1352.9
167.5°	1362.3	1360.7	1360.4	1360.2	1359.9	1359.8	1360.3	1361.8	1363.2	1364.6	1366.0
170°	1369.0	1367.2	1367.0	1366.8	1366.5	1366.3	1367.0	1368.6	1370.2	1371.8	1373.4
172.5°	1374.6	1372.9	1372.5	1372.1	1371.7	1371.3	1371.9	1373.5	1375.1	1376.7	1378.3
175°	1380.3	1378.5	1378.3	1378.1	1377.8	1377.6	1378.2	1379.5	1380.9	1382.3	1383.6
177.5°	1383.3	1382.0	1381.8	1381.6	1381.5	1381.2	1381.7	1382.8	1383.9	1385.0	1386.1
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1511.6	1516.2	1522.6	1529.9	1535.9	1542.3	1545.8	1545.8	1548.7	1555.1	1563.5
5°	1516.0	1532.1	1547.5	1567.3	1582.7	1600.6	1614.2	1627.1	1638.9	1653.7	1669.1
7.5°	1514.7	1541.4	1569.2	1600.4	1634.7	1662.0	1690.0	1712.0	1733.8	1762.1	1784.5
10°	1509.8	1544.4	1582.1	1621.6	1664.9	1702.5	1736.5	1767.4	1797.0	1827.9	1855.6
12.5°	1500.9	1544.9	1590.9	1638.4	1693.0	1736.1	1780.0	1812.8	1847.4	1881.2	1915.4
15°	1487.6	1539.4	1595.1	1661.1	1727.8	1776.0	1819.2	1861.8	1893.9	1932.2	1964.9
17.5°	1460.1	1526.9	1596.8	1669.0	1733.1	1789.1	1834.4	1874.9	1909.1	1951.2	1995.7
20°	1443.8	1516.0	1588.9	1666.0	1727.2	1784.6	1828.4	1870.4	1913.0	1968.0	2022.4
22.5°	1421.0	1498.3	1575.5	1648.8	1713.3	1768.8	1814.2	1865.5	1921.4	1983.9	2049.5
25°	1385.1	1464.7	1541.3	1611.1	1674.1	1730.9	1792.6	1861.8	1929.8	2011.9	2106.3
27.5°	1339.5	1416.3	1484.6	1558.4	1621.0	1693.2	1770.3	1845.2	1943.2	2056.2	2174.1
30°	1305.4	1378.3	1443.1	1512.9	1583.9	1663.6	1750.0	1838.3	1955.0	2087.8	2228.0
32.5°	1265.9	1331.9	1396.2	1463.5	1545.4	1632.9	1724.8	1832.9	1972.4	2123.4	2268.5
35°	1197.4	1256.6	1319.0	1393.8	1480.8	1575.9	1693.2	1824.8	1993.4	2155.8	2286.1
37.5°	1125.5	1172.3	1234.9	1313.7	1408.6	1518.6	1651.7	1811.6	1984.7	2130.4	2185.9
40°	1070.2	1114.0	1180.0	1262.8	1356.7	1477.1	1626.5	1790.8	1964.9	2066.2	2061.9
42.5°	1015.3	1059.6	1123.2	1206.5	1304.3	1439.1	1592.9	1763.6	1910.6	1949.2	1868.8
45°	931.2	972.6	1035.0	1119.0	1223.9	1365.3	1527.1	1690.8	1784.6	1722.3	1562.9
47.5°	845.5	885.7	943.6	1025.8	1140.4	1288.4	1441.4	1575.7	1588.9	1454.8	1263.8
50°	789.2	826.9	881.8	969.5	1080.6	1225.2	1372.8	1478.4	1445.6	1282.0	1085.0
52.5°	734.4	770.6	822.0	904.8	1018.4	1159.9	1291.7	1374.6	1298.9	1124.9	947.6
55°	653.3	687.9	739.8	815.7	918.9	1048.5	1164.0	1194.3	1083.2	907.8	764.5
57.5°	576.4	601.7	653.0	720.2	819.6	933.9	1016.7	1011.2	888.6	730.6	627.9
60°	525.5	548.3	597.1	658.9	753.4	855.9	913.9	889.2	765.1	634.8	536.0
62.5°	478.1	499.5	540.3	597.1	678.3	767.5	809.7	775.6	658.4	543.9	465.3
65°	406.3	421.8	454.5	507.0	570.6	632.3	670.0	620.0	516.3	429.8	370.5
67.5°	339.3	352.6	381.8	419.4	463.3	505.9	521.2	474.3	393.6	335.3	293.6
70°	295.8	308.2	327.9	363.1	392.1	422.4	429.8	387.8	320.5	276.0	250.1
72.5°	254.3	265.6	283.0	307.8	327.9	345.3	348.8	309.7	258.3	227.6	207.6
75°	193.9	203.7	214.9	224.2	237.1	240.2	239.0	208.7	180.9	160.6	149.4
77.5°	142.5	146.6	153.4	157.1	157.7	157.5	151.1	132.1	117.7	109.3	104.7
80°	110.0	113.0	114.9	116.1	116.7	110.5	103.8	92.0	87.1	82.1	76.6
82.5°	79.8	81.9	83.7	84.0	80.6	75.5	69.2	63.4	59.9	57.4	55.3
85°	43.3	43.8	43.3	40.2	35.8	34.0	32.7	31.5	30.9	30.3	30.3
87.5°	15.9	14.7	12.7	13.5	13.9	13.7	14.0	13.9	13.6	13.9	14.1
90°	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.4	17.6	18.7
92.5°	14.5	13.2	12.0	10.7	10.8	12.2	13.5	15.0	16.4	17.6	18.7
95°	57.8	57.1	56.4	55.7	51.0	42.4	33.7	25.0	16.4	17.6	18.7
97.5°	123.3	124.5	125.7	127.0	119.0	101.9	84.8	67.6	50.5	44.0	37.6
100°	172.0	172.6	173.3	174.0	174.8	175.7	176.7	177.5	178.5	144.5	110.5
102.5°	222.2	223.1	223.9	224.8	225.5	226.1	226.6	227.1	227.7	221.3	214.8
105°	302.5	303.4	304.3	305.2	305.6	305.6	305.6	305.6	305.6	305.6	305.6
107.5°	384.8	384.8	384.8	384.8	385.1	385.6	386.0	386.4	386.9	386.9	387.0
110°	439.0	439.0	439.0	439.0	439.2	439.7	440.1	440.6	441.0	440.4	439.7



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	490.4	491.0	491.5	492.0	492.5	492.7	493.0	493.3	493.5	492.7	491.8
115°	567.3	568.5	569.6	570.8	571.4	571.6	571.9	572.1	572.4	571.4	570.5
117.5°	645.1	645.1	645.0	645.0	645.4	646.3	647.1	648.0	648.9	647.7	646.5
120°	694.2	694.0	693.7	693.5	693.7	694.3	695.1	695.8	696.4	696.0	695.5
122.5°	738.7	739.6	740.5	741.3	742.0	742.3	742.6	742.9	743.2	742.8	742.3
125°	806.8	808.3	809.9	811.5	812.3	812.3	812.3	812.3	812.3	811.4	810.5
127.5°	870.5	871.6	872.7	873.9	874.4	874.3	874.2	874.0	873.9	873.4	872.9
130°	909.9	911.0	912.2	913.3	914.0	914.3	914.4	914.7	914.9	914.3	913.5
132.5°	949.4	950.8	952.1	953.4	953.9	953.3	952.8	952.4	951.8	951.7	951.6
135°	1005.5	1006.9	1008.2	1009.6	1010.0	1009.6	1009.2	1008.7	1008.2	1007.8	1007.3
137.5°	1056.8	1058.0	1059.1	1060.3	1060.7	1060.3	1059.9	1059.5	1059.1	1059.2	1059.3
140°	1089.7	1090.2	1090.6	1091.1	1091.2	1091.0	1090.8	1090.5	1090.3	1090.8	1091.2
142.5°	1119.9	1120.1	1120.5	1120.7	1121.0	1121.3	1121.7	1122.0	1122.3	1122.4	1122.4
145°	1164.6	1165.1	1165.5	1165.9	1166.2	1166.2	1166.2	1166.2	1166.2	1166.4	1166.6
147.5°	1203.0	1202.9	1202.8	1202.8	1202.8	1203.1	1203.4	1203.6	1204.0	1204.2	1204.5
150°	1227.2	1226.9	1226.4	1225.9	1225.9	1226.4	1226.9	1227.2	1227.7	1228.2	1228.7
152.5°	1250.5	1249.5	1248.6	1247.5	1247.2	1247.7	1248.2	1248.6	1249.0	1249.5	1250.0
155°	1280.7	1279.4	1278.0	1276.6	1276.2	1276.6	1277.1	1277.6	1278.0	1278.7	1279.4
157.5°	1304.9	1304.0	1303.2	1302.4	1302.0	1302.0	1302.1	1302.2	1302.2	1302.9	1303.7
160°	1320.7	1319.4	1318.0	1316.6	1316.1	1316.3	1316.5	1316.8	1317.0	1317.9	1318.8
162.5°	1333.9	1332.5	1331.1	1329.8	1329.2	1329.4	1329.7	1329.8	1330.1	1331.3	1332.6
165°	1351.5	1350.1	1348.8	1347.4	1346.8	1347.0	1347.3	1347.5	1347.7	1349.1	1350.4
167.5°	1364.6	1363.2	1361.8	1360.3	1359.8	1359.9	1360.2	1360.4	1360.7	1362.3	1364.0
170°	1371.8	1370.2	1368.6	1367.0	1366.3	1366.5	1366.8	1367.0	1367.2	1369.0	1370.9
172.5°	1376.7	1375.1	1373.5	1371.9	1371.3	1371.7	1372.1	1372.5	1372.9	1374.6	1376.3
175°	1382.3	1380.9	1379.5	1378.2	1377.6	1377.8	1378.1	1378.3	1378.5	1380.3	1382.1
177.5°	1385.0	1383.9	1382.8	1381.7	1381.2	1381.5	1381.6	1381.8	1382.0	1383.3	1384.6
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3	1504.3
2.5°	1569.9	1569.9	1578.3	1577.9	1583.3	1581.4	1582.3
5°	1687.7	1698.2	1707.5	1713.6	1722.8	1725.4	1724.1
7.5°	1809.7	1833.0	1844.4	1860.0	1862.8	1871.0	1870.1
10°	1885.3	1908.1	1925.4	1939.0	1945.8	1954.5	1955.0
12.5°	1944.6	1964.0	1979.3	1991.9	2000.1	2002.9	2004.5
15°	1990.8	2012.5	2030.4	2048.3	2058.8	2066.8	2071.2
17.5°	2037.6	2070.9	2102.5	2126.9	2141.4	2153.8	2153.6
20°	2073.6	2111.9	2151.4	2179.2	2207.7	2219.9	2221.8
22.5°	2112.1	2170.7	2221.6	2264.7	2302.0	2314.8	2319.7
25°	2192.2	2268.7	2347.2	2407.7	2450.9	2476.2	2479.9
27.5°	2288.9	2392.5	2475.0	2530.9	2566.7	2585.5	2589.6
30°	2357.1	2452.8	2526.9	2568.9	2585.5	2588.0	2578.7
32.5°	2387.7	2459.2	2488.8	2486.3	2453.6	2431.9	2423.6
35°	2350.2	2335.4	2263.2	2176.8	2110.7	2068.7	2057.5
37.5°	2138.8	2011.0	1878.1	1747.5	1677.9	1642.6	1581.8
40°	1930.4	1748.2	1609.9	1499.9	1421.5	1358.5	1343.7
42.5°	1695.2	1507.1	1368.8	1274.7	1212.0	1168.9	1150.1
45°	1362.2	1200.5	1086.2	1014.0	965.8	934.3	920.1
47.5°	1089.6	964.3	881.1	827.6	790.9	763.5	755.8
50°	939.8	839.8	769.4	724.4	696.6	675.6	666.9
52.5°	816.3	735.6	681.5	644.3	618.0	604.9	597.8
55°	673.7	604.0	565.1	535.4	520.5	510.1	505.1
57.5°	551.0	500.6	472.1	451.6	437.9	431.3	428.8
60°	482.3	442.8	416.8	400.8	391.5	382.9	380.4
62.5°	421.5	390.4	370.4	356.3	347.1	343.3	341.8
65°	339.6	319.2	304.4	295.8	288.4	287.2	286.5
67.5°	270.0	258.0	250.3	241.2	238.6	234.2	233.5
70°	230.9	222.9	213.7	210.6	207.5	203.2	203.7
72.5°	195.9	187.8	181.6	177.4	176.3	174.5	176.1
75°	143.2	140.8	138.3	135.2	134.0	134.0	133.4
77.5°	102.3	100.1	97.4	95.6	95.2	92.6	93.6
80°	74.1	71.0	69.8	70.4	68.5	67.9	67.9
82.5°	54.8	53.7	52.5	52.6	52.2	51.7	52.1
85°	30.3	29.6	29.6	29.0	29.0	28.4	28.4
87.5°	14.8	15.5	14.7	14.4	14.5	15.1	15.8
90°	19.8	21.0	21.9	22.6	23.2	23.9	24.6
92.5°	19.8	21.0	21.7	22.0	22.3	22.7	23.0
95°	19.8	21.0	21.5	21.5	21.5	21.5	21.5
97.5°	31.2	24.7	21.5	21.5	21.5	21.5	21.5
100°	76.6	42.6	25.2	24.2	23.4	22.4	21.5
102.5°	208.4	202.0	191.0	175.5	160.0	144.5	129.0
105°	305.6	305.6	305.5	305.3	305.1	304.8	304.6
107.5°	387.1	387.1	386.7	386.0	385.4	384.7	384.0
110°	439.0	438.3	438.1	438.3	438.6	438.8	439.0



TEST NUMBER: P333732-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	491.0	490.1	489.5	489.2	488.9	488.5	488.2
115°	569.6	568.7	567.5	566.2	564.8	563.4	562.1
117.5°	645.3	644.1	643.2	642.6	642.1	641.4	640.9
120°	695.1	694.6	693.8	692.7	691.5	690.4	689.3
122.5°	741.8	741.4	740.5	739.2	737.8	736.5	735.2
125°	809.6	808.7	807.9	807.2	806.5	805.8	805.2
127.5°	872.4	871.9	870.8	869.1	867.4	865.7	864.0
130°	912.8	912.2	911.2	910.1	908.9	907.8	906.7
132.5°	951.4	951.3	950.6	949.5	948.4	947.2	946.1
135°	1006.9	1006.4	1005.5	1004.2	1002.7	1001.4	1000.1
137.5°	1059.4	1059.5	1058.9	1057.7	1056.5	1055.3	1054.2
140°	1091.6	1092.1	1091.6	1090.3	1088.9	1087.6	1086.2
142.5°	1122.6	1122.7	1122.0	1120.6	1119.3	1117.9	1116.6
145°	1166.9	1167.1	1166.6	1165.1	1163.8	1162.4	1161.1
147.5°	1204.8	1205.1	1204.4	1202.7	1201.0	1199.4	1197.8
150°	1229.1	1229.5	1228.8	1227.0	1225.2	1223.4	1221.5
152.5°	1250.5	1250.9	1250.3	1248.6	1247.1	1245.4	1243.7
155°	1280.0	1280.7	1280.2	1278.3	1276.5	1274.7	1272.9
157.5°	1304.4	1305.1	1304.6	1302.7	1300.9	1299.1	1297.3
160°	1319.7	1320.6	1320.2	1318.3	1316.5	1314.7	1312.9
162.5°	1334.0	1335.2	1334.8	1332.8	1330.8	1328.8	1326.8
165°	1351.9	1353.2	1353.0	1351.1	1349.3	1347.5	1345.7
167.5°	1365.6	1367.2	1367.0	1364.9	1362.9	1360.9	1358.8
170°	1372.7	1374.5	1374.4	1372.4	1370.3	1368.3	1366.2
172.5°	1377.9	1379.5	1379.3	1377.3	1375.2	1373.2	1371.1
175°	1383.9	1385.8	1385.7	1383.6	1381.6	1379.5	1377.4
177.5°	1385.8	1387.1	1387.0	1385.5	1384.1	1382.6	1381.2
180°	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6	1383.6

(END OF REPORT)