

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333735-927

Luminaire Tested: **S125RDIW-S1270D1340U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333735-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1270 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7550.8 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 76.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57	57	57	51
1	98	94	90	87	91	87	84	81	74	72	69		62	60	59		51	50	49	44
2	90	82	76	71	83	76	71	67	65	61	58		55	52	49		45	43	41	37
3	82	73	65	60	75	67	61	56	58	53	49		49	45	42		40	38	35	31
4	75	64	57	51	69	60	53	48	51	46	42		43	39	36		36	33	31	27
5	69	57	49	43	64	53	46	41	46	40	36		39	35	31		32	29	27	24
6	64	52	44	38	59	48	41	36	41	36	32		35	31	28		30	26	24	21
7	59	47	39	33	54	44	36	31	38	32	28		32	28	25		27	24	21	19
8	55	42	35	29	50	40	33	28	34	29	25		29	25	22		25	22	19	17
9	51	39	31	26	47	36	30	25	32	26	22		27	23	20		23	20	17	15
10	48	36	28	24	44	33	27	22	29	24	20		25	21	18		21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10561	10561	10561
5°	10585	10466	10529
10°	10506	10368	10368
15°	10380	10158	10075
20°	10221	9864	9745
25°	10033	9576	9365
30°	9801	9238	8944
35°	9563	8891	8472
40°	9340	8528	8008
45°	9070	8122	7501
50°	8799	7681	6974
55°	8483	7260	6411
60°	8169	6748	5807
65°	7795	6154	5115
70°	7370	5410	4409
75°	6780	4561	3666
80°	5973	3582	3080
85°	5039	2927	2749



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.8	2.0
10°-20°	429.7	5.7
20°-30°	623.1	8.3
30°-40°	710.2	9.4
40°-50°	692.3	9.2
50°-60°	582.7	7.7
60°-70°	408.5	5.4
70°-80°	210.0	2.8
80°-90°	55.9	0.7
90°-100°	88.4	1.2
100°-110°	261.2	3.5
110°-120°	442.4	5.9
120°-130°	582.2	7.7
130°-140°	652.3	8.6
140°-150°	639.3	8.5
150°-160°	537.0	7.1
160°-170°	357.0	4.7
170°-180°	124.9	1.7
0°-30°	1206.6	16.0
0°-40°	1916.8	25.4
0°-60°	3191.8	42.3
0°-90°	3866.1	51.2
90°-120°	792.0	10.5
90°-150°	2665.8	35.3
90°-180°	3685.0	48.8
0°-180°	7550.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1635	1635	1635	1635	1635	
5°	1633	1627	1614	1626	1624	155
15°	1552	1544	1519	1517	1507	437
25°	1408	1388	1344	1328	1314	648
35°	1213	1182	1128	1093	1074	759
45°	993	955	889	842	821	766
55°	753	712	645	591	569	674
65°	510	467	403	355	335	505
75°	272	234	183	157	147	288
85°	68	47	40	38	37	76
90°	1	9	16	21	25	7
95°	67	69	79	86	88	71
105°	234	239	246	252	255	250
115°	443	447	449	448	447	438
125°	646	652	654	652	650	579
135°	841	846	848	848	844	648
145°	1018	1022	1026	1025	1022	636
155°	1165	1165	1166	1170	1165	536
165°	1267	1265	1266	1270	1264	357
175°	1317	1314	1313	1319	1312	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1638.2	1637.6	1636.9	1636.3	1635.6	1634.2	1632.0	1629.8	1627.6	1625.4	1627.6
5°	1632.8	1631.7	1630.6	1629.5	1628.4	1626.4	1623.3	1620.3	1617.3	1614.3	1617.0
7.5°	1616.8	1615.7	1614.7	1613.6	1612.6	1610.3	1606.6	1603.0	1599.4	1595.8	1597.7
10°	1602.0	1601.1	1600.3	1599.5	1598.6	1596.3	1592.4	1588.6	1584.8	1581.0	1581.8
12.5°	1585.2	1584.1	1583.0	1582.0	1581.0	1577.9	1572.7	1567.6	1562.3	1557.2	1557.8
15°	1552.5	1550.9	1549.3	1547.6	1545.9	1542.2	1536.4	1530.7	1525.0	1519.2	1518.9
17.5°	1515.7	1513.2	1510.7	1508.2	1505.6	1500.7	1493.5	1486.2	1479.0	1471.7	1470.4
20°	1487.1	1484.3	1481.5	1478.8	1476.1	1470.3	1461.6	1452.8	1444.0	1435.2	1433.8
22.5°	1455.5	1452.7	1449.9	1447.2	1444.5	1438.5	1429.3	1420.1	1410.8	1401.6	1398.9
25°	1408.0	1403.9	1399.8	1395.7	1391.5	1384.4	1374.3	1364.1	1353.9	1343.8	1340.2
27.5°	1353.7	1348.7	1343.7	1338.7	1333.7	1325.8	1314.9	1304.0	1293.2	1282.3	1277.3
30°	1314.2	1308.9	1303.7	1298.5	1293.3	1284.9	1273.4	1261.9	1250.3	1238.8	1232.5
32.5°	1275.7	1269.6	1263.5	1257.4	1251.3	1242.3	1230.6	1218.9	1207.0	1195.3	1188.4
35°	1212.9	1206.3	1199.7	1193.1	1186.5	1177.0	1164.7	1152.4	1140.0	1127.7	1119.7
37.5°	1151.4	1143.4	1135.4	1127.4	1119.3	1108.9	1096.2	1083.5	1070.7	1058.0	1048.5
40°	1107.9	1099.6	1091.4	1083.2	1075.0	1064.2	1051.1	1037.9	1024.7	1011.5	1001.2
42.5°	1062.5	1054.0	1045.5	1037.0	1028.6	1017.6	1004.0	990.4	976.8	963.1	953.2
45°	993.0	985.1	977.1	969.2	961.2	949.7	934.5	919.5	904.4	889.3	878.3
47.5°	921.1	912.8	904.4	896.0	887.6	875.8	860.5	845.3	830.1	814.9	803.6
50°	875.7	866.6	857.5	848.5	839.5	827.1	811.4	795.8	780.1	764.5	753.0
52.5°	826.2	817.0	807.7	798.4	789.2	777.1	762.4	747.7	732.8	718.1	705.7
55°	753.4	744.7	735.9	727.1	718.3	706.2	690.9	675.5	660.1	644.8	632.4
57.5°	679.8	670.4	661.0	651.6	642.2	630.2	615.4	600.5	585.7	570.8	558.8
60°	632.4	622.7	613.1	603.6	594.0	581.7	566.9	552.1	537.3	522.4	510.4
62.5°	582.0	572.8	563.6	554.4	545.3	533.2	518.2	503.1	488.1	473.0	461.8
65°	510.1	500.7	491.5	482.1	472.8	460.8	446.3	431.7	417.2	402.7	391.7
67.5°	438.7	429.4	420.0	410.7	401.4	389.8	375.8	361.9	347.9	334.0	323.9
70°	390.3	381.0	371.6	362.3	353.0	341.4	327.7	314.0	300.2	286.5	278.1
72.5°	342.9	333.7	324.6	315.5	306.4	295.4	282.6	269.7	256.9	244.1	236.2
75°	271.7	263.5	255.2	247.0	238.8	228.9	217.4	205.9	194.3	182.8	176.7
77.5°	201.1	194.5	187.9	181.3	174.8	166.8	157.6	148.4	139.2	129.9	125.7
80°	160.6	154.0	147.4	140.8	134.2	127.1	119.4	111.7	104.0	96.3	93.9
82.5°	121.0	115.1	109.2	103.2	97.4	91.7	86.4	81.2	75.9	70.7	69.5
85°	68.0	63.0	58.1	53.1	48.2	45.0	43.6	42.3	40.9	39.5	39.2
87.5°	22.9	21.8	20.6	19.4	18.2	17.7	17.8	17.9	18.0	18.1	18.3
90°	1.0	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.5	17.6
92.5°	24.9	26.1	27.4	28.7	29.9	31.6	33.6	35.6	37.5	39.5	41.0
95°	66.8	67.3	67.7	68.1	68.6	70.0	72.2	74.5	76.8	79.1	80.7
97.5°	111.0	111.1	111.4	111.5	111.7	113.4	116.5	119.7	122.9	126.0	127.5
100°	143.9	143.9	143.9	143.9	143.9	145.4	148.3	151.3	154.2	157.2	159.3
102.5°	179.2	180.1	181.0	182.0	182.8	184.1	185.6	187.1	188.6	190.1	192.3
105°	234.3	235.4	236.5	237.7	238.8	240.1	241.5	242.9	244.2	245.6	247.0
107.5°	295.1	296.3	297.4	298.6	299.7	300.8	301.8	302.9	304.0	305.0	305.7
110°	337.1	338.2	339.4	340.5	341.6	342.5	343.3	343.9	344.6	345.2	345.9



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	379.8	380.4	381.0	381.6	382.1	382.9	383.7	384.6	385.5	386.3	386.7
115°	442.9	443.8	444.7	445.6	446.6	447.3	447.7	448.1	448.6	449.1	448.9
117.5°	506.2	506.6	507.0	507.4	507.9	508.3	508.7	509.1	509.5	509.9	510.1
120°	545.7	546.8	548.0	549.1	550.2	550.9	551.1	551.4	551.6	551.8	551.8
122.5°	588.4	588.8	589.2	589.6	590.0	590.6	591.1	591.8	592.3	592.9	592.7
125°	646.3	647.7	649.1	650.5	651.8	652.6	652.8	653.1	653.3	653.6	653.1
127.5°	708.0	708.8	709.6	710.3	711.1	711.6	711.9	712.2	712.5	712.7	712.5
130°	745.0	746.2	747.3	748.5	749.6	750.4	750.8	751.3	751.7	752.2	751.9
132.5°	782.0	783.9	785.8	787.6	789.5	790.4	790.3	790.2	790.1	790.0	789.8
135°	840.6	841.9	843.3	844.7	846.1	846.8	847.1	847.3	847.6	847.8	847.8
137.5°	895.6	897.0	898.3	899.6	900.9	901.8	902.4	902.9	903.4	903.9	904.1
140°	931.0	932.2	933.3	934.5	935.6	936.4	937.2	937.9	938.5	939.2	939.7
142.5°	966.4	967.3	968.3	969.2	970.2	971.1	971.9	972.8	973.7	974.5	974.9
145°	1018.4	1019.2	1020.2	1021.0	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6
147.5°	1066.4	1066.9	1067.5	1067.9	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7
150°	1098.5	1098.3	1098.0	1097.8	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6
152.5°	1124.8	1125.1	1125.5	1125.8	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5
155°	1165.3	1165.3	1165.3	1165.3	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2
157.5°	1201.4	1200.9	1200.5	1199.9	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1
160°	1222.8	1222.2	1221.5	1220.8	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7
162.5°	1241.7	1241.3	1240.7	1240.2	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8
165°	1267.0	1266.5	1266.1	1265.7	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9
167.5°	1288.4	1287.5	1286.6	1285.6	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6
170°	1299.9	1299.0	1298.1	1297.2	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2
172.5°	1308.1	1307.2	1306.3	1305.4	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4
175°	1317.4	1316.4	1315.6	1314.6	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6
177.5°	1322.1	1321.4	1320.6	1319.9	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3	1635.3
2.5°	1629.8	1632.0	1634.2	1635.1	1635.0	1634.7	1634.5	1634.3
5°	1619.8	1622.5	1625.2	1626.4	1625.8	1625.2	1624.7	1624.1
7.5°	1599.6	1601.6	1603.5	1604.1	1603.5	1602.9	1602.3	1601.7
10°	1582.5	1583.4	1584.2	1584.2	1583.4	1582.5	1581.8	1581.0
12.5°	1558.5	1559.0	1559.6	1559.3	1558.1	1556.8	1555.5	1554.3
15°	1518.6	1518.4	1518.1	1516.7	1514.3	1511.8	1509.3	1506.8
17.5°	1469.0	1467.6	1466.3	1464.6	1462.5	1460.5	1458.5	1456.4
20°	1432.4	1431.1	1429.7	1427.8	1425.3	1422.8	1420.4	1417.9
22.5°	1396.2	1393.5	1390.8	1388.5	1386.5	1384.4	1382.4	1380.4
25°	1336.6	1333.1	1329.5	1326.2	1323.2	1320.2	1317.2	1314.2
27.5°	1272.3	1267.3	1262.3	1258.4	1255.5	1252.5	1249.6	1246.7
30°	1226.2	1219.9	1213.5	1209.2	1206.7	1204.2	1201.7	1199.3
32.5°	1181.4	1174.4	1167.4	1162.4	1159.3	1156.1	1153.0	1149.9
35°	1111.7	1103.7	1095.8	1089.9	1086.1	1082.2	1078.4	1074.5
37.5°	1038.9	1029.4	1019.8	1013.1	1009.4	1005.7	1002.0	998.2
40°	990.7	980.2	969.9	963.0	959.6	956.4	953.1	949.8
42.5°	943.2	933.2	923.2	915.8	910.9	906.1	901.3	896.4
45°	867.3	856.3	845.3	837.8	833.7	829.6	825.5	821.3
47.5°	792.3	781.0	769.7	761.8	757.2	752.7	748.1	743.5
50°	741.5	729.9	718.4	710.6	706.5	702.3	698.2	694.1
52.5°	693.2	680.9	668.4	660.2	656.1	652.0	647.8	643.7
55°	620.0	607.7	595.3	586.9	582.6	578.1	573.8	569.4
57.5°	546.7	534.6	522.5	514.6	510.6	506.8	502.9	499.0
60°	498.3	486.2	474.1	466.0	461.9	457.8	453.7	449.6
62.5°	450.7	439.4	428.3	420.6	416.5	412.3	408.2	404.1
65°	380.7	369.7	358.7	351.2	347.1	342.9	338.8	334.7
67.5°	313.9	303.8	293.8	287.1	283.8	280.5	277.3	273.9
70°	269.5	261.0	252.5	246.6	243.3	240.0	236.7	233.5
72.5°	228.4	220.5	212.6	207.6	205.4	203.3	201.1	198.8
75°	170.7	164.7	158.7	154.6	152.7	150.8	148.9	146.9
77.5°	121.4	117.2	113.0	110.2	108.8	107.3	105.9	104.5
80°	91.4	89.0	86.4	84.9	84.4	83.8	83.3	82.8
82.5°	68.4	67.2	66.1	65.3	65.0	64.6	64.3	64.0
85°	39.0	38.7	38.4	38.2	37.9	37.6	37.3	37.1
87.5°	18.5	18.8	19.0	19.1	19.0	18.9	18.9	18.8
90°	18.7	19.9	21.0	21.9	22.6	23.3	24.0	24.6
92.5°	42.5	44.0	45.5	46.5	47.0	47.5	48.0	48.5
95°	82.3	83.9	85.6	86.5	87.0	87.5	87.9	88.4
97.5°	129.0	130.5	132.0	132.9	133.2	133.5	133.7	134.0
100°	161.4	163.3	165.4	166.7	167.2	167.6	168.1	168.5
102.5°	194.6	196.8	199.1	200.5	201.1	201.8	202.4	203.0
105°	248.3	249.7	251.0	252.1	252.8	253.5	254.1	254.8
107.5°	306.3	307.0	307.8	308.1	308.0	307.9	307.9	307.8
110°	346.7	347.3	348.0	348.2	348.0	347.8	347.5	347.3



TEST NUMBER: P333735-927

CATALOG NUMBER: S125RDIW-S1270D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.0	387.3	387.6	387.6	387.2	386.8	386.3	386.0
115°	448.6	448.4	448.1	447.9	447.7	447.4	447.3	447.0
117.5°	510.2	510.4	510.6	510.2	509.4	508.4	507.6	506.6
120°	551.8	551.8	551.8	551.4	550.4	549.5	548.6	547.7
122.5°	592.6	592.4	592.2	591.8	591.0	590.3	589.5	588.8
125°	652.6	652.2	651.7	651.4	651.2	650.9	650.7	650.5
127.5°	712.3	712.0	711.9	711.5	711.1	710.6	710.1	709.6
130°	751.7	751.5	751.3	750.9	750.5	750.0	749.6	749.1
132.5°	789.6	789.3	789.1	788.7	788.1	787.3	786.7	786.1
135°	847.8	847.8	847.8	847.3	846.4	845.5	844.5	843.7
137.5°	904.4	904.7	905.0	904.5	903.4	902.2	901.1	900.0
140°	940.2	940.6	941.0	940.7	939.5	938.4	937.3	936.1
142.5°	975.1	975.4	975.7	975.3	974.1	973.0	971.8	970.7
145°	1025.6	1025.6	1025.6	1025.2	1024.5	1023.8	1023.1	1022.5
147.5°	1072.2	1072.8	1073.3	1072.9	1071.3	1069.8	1068.2	1066.7
150°	1101.6	1101.6	1101.6	1101.4	1100.9	1100.4	1099.9	1099.5
152.5°	1128.9	1129.5	1130.0	1130.0	1129.1	1128.3	1127.4	1126.6
155°	1168.2	1169.0	1170.0	1169.8	1168.7	1167.6	1166.4	1165.3
157.5°	1202.1	1202.9	1203.9	1203.6	1202.1	1200.6	1199.0	1197.5
160°	1222.6	1223.5	1224.4	1224.3	1223.2	1222.0	1220.9	1219.7
162.5°	1241.9	1242.9	1244.0	1244.0	1242.6	1241.3	1240.0	1238.7
165°	1267.8	1268.8	1269.6	1269.4	1268.0	1266.7	1265.3	1263.9
167.5°	1287.1	1288.4	1289.8	1289.8	1288.3	1286.9	1285.5	1284.0
170°	1298.5	1299.9	1301.2	1301.2	1299.6	1298.0	1296.3	1294.7
172.5°	1306.8	1308.1	1309.5	1309.5	1308.1	1306.6	1305.2	1303.8
175°	1316.0	1317.4	1318.7	1318.6	1317.0	1315.4	1313.8	1312.2
177.5°	1320.2	1321.3	1322.4	1322.3	1321.0	1319.7	1318.4	1317.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)