

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333425

Luminaire Tested: **S125DIW-S850D1560U835-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333425
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D1560U835-4F0-1E-UDD-A1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1560 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8864.2 lumens
Efficiency: N/A
Efficacy: 130.2 lumens/watt
Spacing Criteria (0/90/45): 1.43 / 1.23 / 1.52
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39				
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	41	40	39	33				
2	87	80	74	69	79	73	68	63	60	56	53	47	45	43	36	35	33	28				
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28	24				
4	73	62	55	49	66	57	50	45	47	42	38	38	34	31	29	26	25	21				
5	67	55	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21	18				
6	61	50	42	36	56	46	39	34	38	32	29	30	27	24	24	21	19	16				
7	57	45	37	32	51	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13				
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	14	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	18	15	17	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	7901	7901	7901	7901
5°	9149	7927	6941	7927
10°	10645	7887	6082	7887
15°	11784	7829	5610	7829
20°	13190	7737	5232	7737
25°	15452	7633	5047	7633
30°	16690	7532	4887	7532
35°	13722	7340	4782	7340
40°	9754	7074	4666	7074
45°	7493	6716	4601	6716
50°	6396	6271	4591	6271
55°	5695	5835	4631	5835
60°	5137	5359	4748	5359
65°	4745	4879	4872	4879
70°	4315	4383	4942	4383
75°	3810	3860	4898	3860
80°	3206	3146	4482	3146
85°	2542	2267	3616	2267



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.8	1.3
10°-20°	350.7	4.0
20°-30°	569.4	6.4
30°-40°	694.5	7.8
40°-50°	631.8	7.1
50°-60°	503.3	5.7
60°-70°	350.5	4.0
70°-80°	186.9	2.1
80°-90°	51.4	0.6
90°-100°	129.8	1.5
100°-110°	383.3	4.3
110°-120°	649.2	7.3
120°-130°	854.4	9.6
130°-140°	957.4	10.8
140°-150°	938.3	10.6
150°-160°	788.1	8.9
160°-170°	523.9	5.9
170°-180°	183.3	2.1
0°-30°	1037.8	11.7
0°-40°	1732.4	19.5
0°-60°	2867.5	32.3
0°-90°	3456.3	39.0
90°-120°	1162.3	13.1
90°-150°	3912.5	44.1
90°-180°	5408.0	61.0
0°-180°	8864.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1223	1223	1223	1223	1223	
5°	1411	1223	1071	1223	1411	142
15°	1762	1171	839	1171	1762	504
25°	2168	1071	708	1071	2168	990
35°	1740	931	606	931	1740	1065
45°	820	735	504	735	820	657
55°	506	518	411	518	506	455
65°	310	319	319	319	310	308
75°	153	155	196	155	153	164
85°	34	31	49	31	34	40
90°	36	2	36	2	36	22
95°	130	98	130	98	130	132
105°	374	344	374	344	374	396
115°	656	650	656	650	656	649
125°	955	949	955	949	955	852
135°	1238	1234	1238	1234	1238	955
145°	1501	1495	1501	1495	1501	937
155°	1710	1710	1710	1710	1710	787
165°	1855	1860	1855	1860	1855	523
175°	1926	1934	1926	1934	1926	183
180°	1938	1938	1938	1938	1938	



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1294.0	1292.3	1290.7	1287.3	1289.8	1282.8	1279.4	1273.6	1266.6	1264.1	1261.2
5°	1411.3	1413.9	1416.5	1405.6	1406.7	1399.4	1382.8	1369.3	1358.4	1344.4	1334.5
7.5°	1552.6	1546.4	1545.9	1538.9	1526.7	1517.0	1499.5	1477.3	1455.8	1431.3	1411.0
10°	1623.2	1623.7	1619.0	1610.7	1597.8	1588.4	1565.6	1543.7	1517.3	1486.1	1463.8
12.5°	1676.4	1678.5	1672.6	1661.4	1655.1	1634.1	1616.2	1590.3	1558.8	1533.9	1499.9
15°	1762.4	1756.6	1752.5	1738.5	1727.6	1705.8	1677.2	1650.2	1615.9	1584.2	1552.6
17.5°	1845.2	1849.8	1842.0	1829.2	1795.4	1769.9	1731.6	1694.6	1652.0	1609.5	1571.7
20°	1919.2	1923.3	1911.4	1889.1	1848.6	1823.1	1772.7	1725.0	1675.6	1621.1	1579.6
22.5°	2011.4	2008.1	1992.0	1958.0	1922.9	1875.9	1821.3	1763.2	1701.4	1639.8	1584.6
25°	2168.4	2146.6	2136.7	2094.7	2048.5	1979.4	1904.6	1819.5	1742.6	1661.1	1590.5
27.5°	2255.4	2248.6	2237.6	2208.3	2159.7	2085.9	1997.7	1893.9	1785.5	1682.6	1590.2
30°	2238.0	2239.0	2240.1	2230.7	2199.6	2144.0	2056.3	1944.6	1815.8	1700.0	1593.1
32.5°	2083.5	2102.4	2120.4	2141.8	2150.5	2139.9	2084.9	1984.1	1851.6	1720.0	1591.4
35°	1740.5	1746.3	1804.9	1863.1	1942.0	2003.3	2044.3	1999.7	1888.0	1736.9	1589.4
37.5°	1357.1	1385.2	1425.8	1491.5	1605.4	1707.4	1838.6	1898.9	1862.9	1742.4	1585.8
40°	1156.9	1182.9	1209.3	1276.3	1372.4	1496.0	1645.0	1772.2	1801.8	1725.0	1573.3
42.5°	1002.4	1022.9	1052.3	1102.7	1183.0	1292.4	1434.8	1601.1	1703.4	1674.3	1547.2
45°	820.4	833.4	856.3	896.2	954.4	1040.1	1165.7	1347.5	1505.8	1558.3	1485.1
47.5°	702.2	702.1	719.9	747.5	789.5	862.3	955.2	1097.6	1266.8	1391.9	1386.1
50°	636.6	634.0	648.0	671.9	705.1	753.4	842.2	955.9	1118.5	1260.2	1299.7
52.5°	580.1	580.4	589.0	606.7	634.5	675.8	742.1	844.6	983.5	1129.0	1203.3
55°	505.8	503.7	513.5	525.5	545.7	572.7	620.5	698.9	811.6	954.9	1051.5
57.5°	437.6	443.3	447.3	455.6	472.4	490.5	530.8	588.3	677.7	800.7	902.8
60°	397.7	403.5	406.6	414.9	428.4	444.0	475.1	521.9	597.1	703.1	804.3
62.5°	362.0	366.5	367.5	375.0	386.0	401.2	425.7	464.9	524.4	617.1	716.3
65°	310.5	310.5	312.6	320.4	325.6	339.1	357.8	386.3	434.1	506.3	590.9
67.5°	260.9	263.4	262.8	266.3	271.1	281.5	294.9	318.5	353.9	406.6	474.3
70°	228.5	230.5	230.0	232.6	237.8	244.6	255.5	277.8	303.2	348.4	406.6
72.5°	199.4	200.2	198.9	202.3	205.4	211.3	223.5	235.4	259.2	297.3	345.1
75°	152.7	153.7	154.7	156.8	159.9	163.0	169.3	181.2	196.8	225.4	256.0
77.5°	114.4	112.5	115.0	114.7	116.4	118.8	124.3	130.6	143.4	161.5	185.2
80°	86.2	86.7	86.7	87.2	89.8	91.4	96.1	100.7	110.6	124.1	140.7
82.5°	62.9	64.3	63.5	64.4	66.6	67.7	70.3	74.1	79.9	90.5	102.5
85°	34.3	31.7	32.7	33.8	33.8	34.3	36.3	37.9	41.0	45.2	49.8
87.5°	17.2	17.8	18.1	17.9	18.1	17.8	19.1	18.8	19.7	20.6	21.8
90°	36.2	35.2	34.2	33.2	32.2	30.8	29.2	27.5	25.8	24.1	21.8
92.5°	71.2	70.4	69.7	69.0	68.2	66.8	64.5	62.3	60.1	57.9	55.0
95°	129.7	129.0	128.4	127.7	127.0	125.5	123.2	120.8	118.5	116.1	112.8
97.5°	196.7	196.3	195.9	195.5	195.1	193.7	191.5	189.3	187.1	184.9	180.3
100°	247.3	246.7	246.0	245.3	244.7	242.8	239.8	236.8	233.8	230.7	226.4
102.5°	298.0	297.1	296.1	295.2	294.3	292.1	288.9	285.6	282.3	279.0	276.8
105°	374.0	373.0	372.0	371.0	370.0	368.5	366.5	364.5	362.5	360.5	358.4
107.5°	451.8	451.9	452.0	452.0	452.1	451.6	450.6	449.6	448.6	447.6	446.1
110°	509.8	510.1	510.4	510.8	511.1	510.8	509.8	508.8	507.7	506.7	505.7



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	566.5	567.1	567.7	568.3	568.9	568.9	568.5	568.0	567.5	567.1	565.8
115°	656.1	656.4	656.7	657.1	657.4	657.7	658.1	658.4	658.7	659.1	658.4
117.5°	743.5	744.9	746.2	747.5	748.9	749.4	749.2	748.9	748.6	748.4	747.7
120°	803.9	805.2	806.5	807.9	809.2	809.9	809.9	809.9	809.9	809.9	809.5
122.5°	864.2	865.2	866.3	867.4	868.5	869.1	869.4	869.7	869.9	870.2	869.3
125°	954.7	955.0	955.3	955.7	956.0	956.5	957.2	957.9	958.5	959.2	958.9
127.5°	1041.5	1042.2	1042.9	1043.5	1044.2	1044.7	1045.1	1045.4	1045.7	1046.1	1045.7
130°	1099.5	1100.1	1100.8	1101.5	1102.1	1102.6	1103.0	1103.3	1103.6	1104.0	1103.3
132.5°	1153.7	1154.7	1155.6	1156.6	1157.5	1158.1	1158.5	1158.8	1159.1	1159.5	1159.6
135°	1238.2	1239.5	1240.9	1242.2	1243.6	1244.2	1244.2	1244.2	1244.2	1244.2	1243.9
137.5°	1320.8	1322.5	1324.2	1325.9	1327.6	1328.2	1327.8	1327.4	1327.0	1326.6	1325.8
140°	1373.9	1375.6	1377.3	1379.0	1380.6	1381.1	1380.5	1379.8	1379.1	1378.5	1377.5
142.5°	1424.6	1426.3	1428.0	1429.6	1431.3	1432.0	1431.5	1431.1	1430.7	1430.3	1429.1
145°	1500.6	1501.6	1502.6	1503.6	1504.6	1505.1	1505.1	1505.1	1505.1	1505.1	1504.1
147.5°	1565.5	1567.8	1570.0	1572.3	1574.6	1575.3	1574.5	1573.7	1572.9	1572.1	1571.3
150°	1613.7	1614.4	1615.1	1615.7	1616.4	1616.8	1616.8	1616.8	1616.8	1616.8	1615.4
152.5°	1653.6	1654.8	1656.0	1657.2	1658.4	1658.6	1657.8	1657.0	1656.2	1655.4	1654.8
155°	1710.3	1711.9	1713.6	1715.3	1717.0	1717.1	1715.8	1714.4	1713.1	1711.8	1711.4
157.5°	1757.6	1759.8	1762.0	1764.2	1766.5	1766.9	1765.6	1764.2	1762.9	1761.5	1761.2
160°	1790.2	1791.9	1793.5	1795.2	1796.9	1797.1	1795.7	1794.4	1793.0	1791.7	1791.4
162.5°	1817.9	1819.9	1821.8	1823.8	1825.7	1825.9	1824.3	1822.7	1821.1	1819.4	1819.4
165°	1855.0	1857.1	1859.1	1861.1	1863.1	1863.4	1862.1	1860.7	1859.4	1858.1	1857.7
167.5°	1884.6	1886.7	1888.8	1890.8	1892.9	1892.9	1890.9	1888.9	1886.9	1884.9	1884.9
170°	1900.3	1902.6	1905.0	1907.3	1909.7	1909.8	1907.8	1905.8	1903.8	1901.8	1901.8
172.5°	1913.6	1915.6	1917.7	1919.8	1921.9	1921.9	1919.9	1917.9	1915.9	1913.9	1913.9
175°	1925.9	1928.3	1930.6	1933.0	1935.3	1935.5	1933.5	1931.5	1929.4	1927.4	1927.4
177.5°	1933.2	1935.0	1936.9	1938.8	1940.7	1940.8	1939.2	1937.6	1936.0	1934.4	1934.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1258.7	1255.8	1252.4	1246.6	1239.6	1235.8	1230.0	1226.3	1218.8	1212.6	1205.9
5°	1322.5	1309.0	1296.6	1280.5	1262.8	1251.4	1237.9	1222.8	1207.3	1191.2	1173.5
7.5°	1388.7	1364.8	1338.8	1310.9	1283.6	1258.5	1234.5	1210.9	1188.9	1162.3	1139.8
10°	1433.1	1403.0	1370.8	1332.9	1296.1	1263.9	1231.2	1202.6	1173.5	1142.4	1114.8
12.5°	1477.6	1437.5	1392.0	1350.4	1306.0	1267.2	1228.7	1192.2	1155.7	1121.2	1089.1
15°	1509.0	1473.6	1431.6	1372.4	1322.5	1269.1	1218.2	1170.9	1126.8	1088.4	1047.9
17.5°	1529.6	1484.1	1439.0	1382.2	1316.8	1257.0	1199.4	1145.3	1095.5	1046.8	1007.8
20°	1533.4	1486.6	1439.4	1383.8	1316.8	1248.3	1190.7	1125.7	1072.3	1021.9	974.1
22.5°	1532.1	1479.2	1427.7	1370.5	1305.2	1242.1	1172.4	1106.2	1048.2	998.6	948.8
25°	1520.4	1463.8	1399.4	1341.8	1277.4	1210.4	1139.8	1071.2	1012.0	955.4	906.1
27.5°	1510.6	1437.2	1364.3	1297.1	1234.9	1173.5	1105.9	1035.7	970.1	912.7	866.2
30°	1498.6	1418.1	1336.0	1265.9	1202.1	1142.4	1078.5	1010.0	941.4	885.3	835.5
32.5°	1487.8	1394.0	1307.4	1231.1	1163.4	1105.4	1046.5	981.3	914.0	857.1	807.2
35°	1466.9	1358.4	1259.2	1173.0	1100.8	1041.1	991.8	931.0	869.2	814.2	766.4
37.5°	1440.4	1311.6	1205.2	1114.8	1035.7	972.8	926.9	880.2	820.9	767.9	724.7
40°	1419.6	1278.4	1165.7	1073.3	991.3	925.8	883.3	839.1	789.8	740.5	694.8
42.5°	1393.5	1248.5	1125.9	1026.4	945.1	881.4	836.7	799.2	755.7	709.7	667.3
45°	1345.4	1194.3	1061.4	954.4	872.3	809.5	763.3	735.3	702.6	658.9	623.1
47.5°	1274.7	1129.2	991.7	881.3	796.6	738.4	695.1	668.2	645.1	612.7	580.2
50°	1211.9	1080.6	941.4	831.8	747.2	688.5	648.6	624.1	604.4	579.5	552.0
52.5°	1141.7	1019.5	892.0	783.7	699.9	642.0	602.9	581.4	565.0	547.1	520.0
55°	1030.2	926.4	808.0	705.1	627.8	571.2	536.9	518.2	504.7	491.2	474.6
57.5°	907.3	826.1	721.2	627.3	556.0	504.5	472.5	454.3	443.9	436.9	427.1
60°	820.9	751.4	661.0	575.3	505.8	460.1	428.9	414.9	406.1	400.3	393.1
62.5°	740.8	683.7	599.9	521.7	460.9	417.7	389.9	376.3	367.8	365.0	359.0
65°	622.6	578.5	509.4	444.5	392.6	355.7	332.3	319.3	314.1	311.0	311.6
67.5°	506.2	479.3	423.8	368.5	327.0	296.1	277.4	267.4	264.8	260.7	260.6
70°	435.1	414.9	368.2	319.9	283.0	259.1	242.5	232.1	229.5	227.4	226.9
72.5°	372.4	354.7	314.1	275.4	242.3	221.3	207.6	201.4	197.1	195.9	195.8
75°	279.9	270.0	237.8	207.2	184.3	169.8	160.5	154.7	151.6	151.1	151.6
77.5°	199.0	190.4	169.9	148.2	133.8	122.8	114.9	112.9	109.4	109.5	108.9
80°	149.5	143.8	130.9	113.7	101.8	92.4	88.3	84.6	83.6	82.0	83.6
82.5°	108.4	102.3	93.5	82.6	72.7	67.1	62.9	61.8	61.2	60.4	60.8
85°	53.5	54.0	48.8	40.5	36.3	33.2	30.6	30.6	30.1	29.6	30.1
87.5°	22.2	20.9	18.7	17.0	14.4	12.6	11.6	11.5	10.8	10.9	11.9
90°	19.4	17.1	14.7	12.2	9.6	6.9	4.2	1.5	4.2	6.9	9.6
92.5°	52.1	49.3	46.4	44.0	42.1	40.3	38.4	36.5	38.4	40.3	42.1
95°	109.4	106.1	102.7	100.7	100.0	99.4	98.7	98.0	98.7	99.4	100.0
97.5°	175.7	171.0	166.4	164.0	163.7	163.4	163.1	162.9	163.1	163.4	163.7
100°	222.0	217.7	213.3	211.1	211.1	211.1	211.1	211.1	211.1	211.1	211.1
102.5°	274.6	272.4	270.2	268.4	267.0	265.7	264.4	263.0	264.4	265.7	267.0
105°	356.4	354.4	352.4	350.6	348.9	347.2	345.5	343.9	345.5	347.2	348.9
107.5°	444.5	443.0	441.5	439.8	438.2	436.5	434.8	433.1	434.8	436.5	438.2
110°	504.7	503.7	502.7	501.4	499.7	498.0	496.4	494.7	496.4	498.0	499.7



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	564.5	563.2	562.0	560.9	560.0	559.2	558.3	557.4	558.3	559.2	560.0
115°	657.7	657.1	656.4	655.4	654.0	652.7	651.4	650.0	651.4	652.7	654.0
117.5°	747.1	746.5	745.9	745.3	744.7	744.1	743.5	742.9	743.5	744.1	744.7
120°	809.2	808.9	808.5	807.5	805.9	804.2	802.5	800.8	802.5	804.2	805.9
122.5°	868.5	867.6	866.7	866.0	865.4	864.8	864.2	863.6	864.2	864.8	865.4
125°	958.5	958.2	957.9	956.7	954.7	952.7	950.6	948.6	950.6	952.7	954.7
127.5°	1045.3	1044.9	1044.5	1043.7	1042.5	1041.4	1040.3	1039.1	1040.3	1041.4	1042.5
130°	1102.6	1102.0	1101.3	1100.1	1098.4	1096.8	1095.1	1093.4	1095.1	1096.8	1098.4
132.5°	1159.7	1159.9	1160.0	1158.7	1156.0	1153.2	1150.5	1147.7	1150.5	1153.2	1156.0
135°	1243.6	1243.2	1242.9	1241.7	1239.7	1237.7	1235.7	1233.7	1235.7	1237.7	1239.7
137.5°	1325.1	1324.4	1323.6	1322.3	1320.3	1318.4	1316.5	1314.5	1316.5	1318.4	1320.3
140°	1376.5	1375.4	1374.4	1373.1	1371.4	1369.7	1368.1	1366.4	1368.1	1369.7	1371.4
142.5°	1427.8	1426.5	1425.2	1423.9	1422.5	1421.1	1419.7	1418.3	1419.7	1421.1	1422.5
145°	1503.1	1502.1	1501.1	1500.0	1498.6	1497.3	1495.9	1494.6	1495.9	1497.3	1498.6
147.5°	1570.5	1569.7	1568.9	1568.1	1567.4	1566.6	1565.9	1565.2	1565.9	1566.6	1567.4
150°	1614.1	1612.7	1611.4	1610.9	1611.2	1611.6	1611.9	1612.2	1611.9	1611.6	1611.2
152.5°	1654.3	1653.8	1653.2	1652.7	1652.2	1651.8	1651.3	1650.8	1651.3	1651.8	1652.2
155°	1711.1	1710.8	1710.4	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3	1710.3
157.5°	1760.9	1760.5	1760.2	1760.4	1761.1	1761.9	1762.6	1763.3	1762.6	1761.9	1761.1
160°	1791.0	1790.7	1790.4	1790.7	1791.7	1792.7	1793.7	1794.7	1793.7	1792.7	1791.7
162.5°	1819.3	1819.2	1819.2	1819.5	1820.3	1821.0	1821.7	1822.5	1821.7	1821.0	1820.3
165°	1857.4	1857.1	1856.7	1856.9	1857.6	1858.2	1858.9	1859.6	1858.9	1858.2	1857.6
167.5°	1884.9	1884.9	1884.9	1885.6	1886.9	1888.3	1889.6	1890.9	1889.6	1888.3	1886.9
170°	1901.8	1901.8	1901.8	1902.5	1903.8	1905.1	1906.5	1907.8	1906.5	1905.1	1903.8
172.5°	1913.9	1913.9	1913.9	1914.5	1915.9	1917.2	1918.6	1919.9	1918.6	1917.2	1915.9
175°	1927.4	1927.4	1927.4	1928.1	1929.4	1930.8	1932.1	1933.5	1932.1	1930.8	1929.4
177.5°	1934.9	1935.2	1935.4	1936.1	1937.2	1938.3	1939.3	1940.4	1939.3	1938.3	1937.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1202.2	1197.6	1193.9	1185.6	1181.0	1174.8	1169.8	1175.2	1169.4	1171.9	1168.1
5°	1164.7	1150.2	1139.8	1124.7	1111.7	1099.8	1091.0	1089.4	1085.2	1083.2	1076.9
7.5°	1119.6	1101.4	1083.6	1063.9	1047.2	1030.3	1019.5	1010.6	1004.7	996.9	991.6
10°	1093.0	1068.6	1047.9	1024.0	1003.2	985.0	970.5	963.2	956.5	946.6	943.0
12.5°	1060.2	1035.0	1009.6	984.1	964.2	943.9	931.4	920.4	915.8	904.6	903.5
15°	1020.9	983.0	958.0	932.1	904.5	887.9	877.5	865.6	860.4	852.6	846.9
17.5°	973.9	940.1	908.9	882.0	858.4	844.4	831.5	823.3	814.4	809.3	800.0
20°	939.9	907.7	876.5	847.9	829.8	813.7	803.3	795.5	786.2	783.6	774.2
22.5°	911.2	875.7	845.8	821.8	801.9	783.8	772.5	767.3	760.8	752.8	750.9
25°	864.6	827.7	802.3	778.4	760.7	744.1	736.3	729.6	723.3	717.6	715.5
27.5°	824.3	791.3	761.1	739.5	724.2	709.0	702.1	693.9	689.4	684.8	679.2
30°	796.0	762.3	735.8	715.0	698.4	684.9	677.6	671.9	667.8	663.6	660.5
32.5°	766.9	735.7	710.0	689.7	673.1	662.9	656.4	652.4	647.8	642.8	638.9
35°	728.5	694.2	669.3	651.7	638.7	630.9	623.6	620.0	614.8	614.8	610.6
37.5°	685.2	655.6	633.6	617.5	605.9	598.9	591.0	588.5	585.2	583.0	581.6
40°	659.5	631.9	611.2	595.1	582.6	576.9	570.7	566.5	564.4	561.8	560.8
42.5°	632.9	606.6	586.7	571.8	561.0	556.1	550.3	547.4	543.2	539.8	539.2
45°	592.5	567.0	548.9	536.9	527.6	521.9	518.2	512.0	509.9	505.8	505.2
47.5°	554.1	529.7	511.9	502.1	493.9	489.2	483.5	477.3	474.9	472.8	472.6
50°	525.5	503.2	486.5	477.2	469.4	462.7	456.9	452.8	451.2	451.2	452.3
52.5°	496.4	477.4	463.3	451.9	444.5	437.3	432.0	429.5	427.1	429.6	431.5
55°	453.8	434.6	424.2	413.3	406.1	397.7	395.2	394.1	392.6	396.7	398.8
57.5°	408.8	395.3	383.1	372.3	365.8	361.0	357.5	356.8	359.7	361.7	368.5
60°	380.1	364.5	353.6	345.3	337.5	334.4	333.4	332.3	334.4	340.1	348.9
62.5°	348.5	335.9	324.1	317.9	312.2	307.0	306.8	307.4	311.6	318.1	326.9
65°	302.2	291.3	283.5	276.2	271.6	268.5	269.5	271.6	276.2	285.1	294.9
67.5°	255.2	247.7	240.7	234.8	230.3	230.3	231.4	234.5	240.0	250.2	259.2
70°	224.8	216.5	210.8	208.2	204.6	202.5	205.6	210.8	215.5	224.8	232.6
72.5°	194.5	187.5	183.0	181.2	179.7	178.0	179.0	184.6	191.0	200.3	209.4
75°	149.5	146.9	143.8	141.8	140.2	141.2	142.3	147.5	152.7	162.5	172.9
77.5°	109.1	106.4	104.6	104.1	103.2	103.7	106.7	110.5	115.6	122.8	130.6
80°	82.6	81.5	80.5	80.0	80.0	80.5	84.6	87.2	91.9	98.7	104.9
82.5°	60.1	59.5	59.3	59.2	59.6	59.7	62.2	65.6	69.5	74.6	80.0
85°	31.7	30.6	32.2	32.7	31.7	33.2	34.3	36.3	37.9	40.5	43.1
87.5°	12.8	14.2	14.2	15.1	15.6	16.9	16.8	18.8	20.0	21.1	21.0
90°	12.2	14.7	17.1	19.4	21.8	24.1	25.8	27.5	29.2	30.8	32.2
92.5°	44.0	46.4	49.3	52.1	55.0	57.9	60.1	62.3	64.5	66.8	68.2
95°	100.7	102.7	106.1	109.4	112.8	116.1	118.5	120.8	123.2	125.5	127.0
97.5°	164.0	166.4	171.0	175.7	180.3	184.9	187.1	189.3	191.5	193.7	195.1
100°	211.1	213.3	217.7	222.0	226.4	230.7	233.8	236.8	239.8	242.8	244.7
102.5°	268.4	270.2	272.4	274.6	276.8	279.0	282.3	285.6	288.9	292.1	294.3
105°	350.6	352.4	354.4	356.4	358.4	360.5	362.5	364.5	366.5	368.5	370.0
107.5°	439.8	441.5	443.0	444.5	446.1	447.6	448.6	449.6	450.6	451.6	452.1
110°	501.4	502.7	503.7	504.7	505.7	506.7	507.7	508.8	509.8	510.8	511.1



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	560.9	562.0	563.2	564.5	565.8	567.1	567.5	568.0	568.5	568.9	568.9
115°	655.4	656.4	657.1	657.7	658.4	659.1	658.7	658.4	658.1	657.7	657.4
117.5°	745.3	745.9	746.5	747.1	747.7	748.4	748.6	748.9	749.2	749.4	748.9
120°	807.5	808.5	808.9	809.2	809.5	809.9	809.9	809.9	809.9	809.9	809.2
122.5°	866.0	866.7	867.6	868.5	869.3	870.2	869.9	869.7	869.4	869.1	868.5
125°	956.7	957.9	958.2	958.5	958.9	959.2	958.5	957.9	957.2	956.5	956.0
127.5°	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7	1045.4	1045.1	1044.7	1044.2
130°	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6	1103.3	1103.0	1102.6	1102.1
132.5°	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1	1158.8	1158.5	1158.1	1157.5
135°	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2	1244.2	1244.2	1244.2	1243.6
137.5°	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0	1327.4	1327.8	1328.2	1327.6
140°	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1	1379.8	1380.5	1381.1	1380.6
142.5°	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7	1431.1	1431.5	1432.0	1431.3
145°	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1	1505.1	1505.1	1505.1	1504.6
147.5°	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9	1573.7	1574.5	1575.3	1574.6
150°	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8	1616.8	1616.8	1616.8	1616.4
152.5°	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2	1657.0	1657.8	1658.6	1658.4
155°	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1	1714.4	1715.8	1717.1	1717.0
157.5°	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9	1764.2	1765.6	1766.9	1766.5
160°	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0	1794.4	1795.7	1797.1	1796.9
162.5°	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1	1822.7	1824.3	1825.9	1825.7
165°	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4	1860.7	1862.1	1863.4	1863.1
167.5°	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9	1888.9	1890.9	1892.9	1892.9
170°	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8	1905.8	1907.8	1909.8	1909.7
172.5°	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9	1917.9	1919.9	1921.9	1921.9
175°	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4	1931.5	1933.5	1935.5	1935.3
177.5°	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0	1937.6	1939.2	1940.8	1940.7
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1165.6	1168.5	1166.0	1169.4	1166.0	1168.5	1165.6	1168.1	1171.9	1169.4	1175.2
5°	1074.3	1069.7	1072.8	1070.7	1072.8	1069.7	1074.3	1076.9	1083.2	1085.2	1089.4
7.5°	990.0	985.5	980.5	978.1	980.5	985.5	990.0	991.6	996.9	1004.7	1010.6
10°	937.3	931.5	931.0	927.4	931.0	931.5	937.3	943.0	946.6	956.5	963.2
12.5°	898.6	893.3	887.4	885.9	887.4	893.3	898.6	903.5	904.6	915.8	920.4
15°	843.8	839.6	836.0	839.1	836.0	839.6	843.8	846.9	852.6	860.4	865.6
17.5°	798.2	794.8	794.1	790.3	794.1	794.8	798.2	800.0	809.3	814.4	823.3
20°	769.5	766.9	768.0	761.2	768.0	766.9	769.5	774.2	783.6	786.2	795.5
22.5°	746.7	741.6	741.0	739.6	741.0	741.6	746.7	750.9	752.8	760.8	767.3
25°	710.9	708.3	705.7	708.3	705.7	708.3	710.9	715.5	717.6	723.3	729.6
27.5°	679.6	676.5	675.8	676.1	675.8	676.5	679.6	679.2	684.8	689.4	693.9
30°	660.5	655.3	655.8	655.3	655.8	655.3	660.5	660.5	663.6	667.8	671.9
32.5°	639.7	636.2	635.5	634.5	635.5	636.2	639.7	638.9	642.8	647.8	652.4
35°	609.1	609.1	606.5	606.5	606.5	609.1	609.1	610.6	614.8	614.8	620.0
37.5°	580.3	579.8	578.2	578.5	578.2	579.8	580.3	581.6	583.0	585.2	588.5
40°	558.7	558.2	556.6	553.5	556.6	558.2	558.7	560.8	561.8	564.4	566.5
42.5°	537.9	536.2	535.5	534.4	535.5	536.2	537.9	539.2	539.8	543.2	547.4
45°	505.2	505.2	504.2	503.7	504.2	505.2	505.2	505.2	505.8	509.9	512.0
47.5°	473.5	474.4	476.4	476.1	476.4	474.4	473.5	472.6	472.8	474.9	477.3
50°	454.3	454.9	456.4	456.9	456.4	454.9	454.3	452.3	451.2	451.2	452.8
52.5°	433.2	436.2	438.1	437.8	438.1	436.2	433.2	431.5	429.6	427.1	429.5
55°	403.5	407.1	410.7	411.3	410.7	407.1	403.5	398.8	396.7	392.6	394.1
57.5°	374.1	379.2	383.0	384.2	383.0	379.2	374.1	368.5	361.7	359.7	356.8
60°	354.1	360.9	365.6	367.6	365.6	360.9	354.1	348.9	340.1	334.4	332.3
62.5°	335.0	342.6	347.3	347.7	347.3	342.6	335.0	326.9	318.1	311.6	307.4
65°	303.8	311.6	315.7	318.8	315.7	311.6	303.8	294.9	285.1	276.2	271.6
67.5°	270.1	277.9	282.5	285.0	282.5	277.9	270.1	259.2	250.2	240.0	234.5
70°	245.6	253.4	259.6	261.7	259.6	253.4	245.6	232.6	224.8	215.5	210.8
72.5°	221.5	228.5	233.5	235.9	233.5	228.5	221.5	209.4	200.3	191.0	184.6
75°	179.7	189.0	193.7	196.3	193.7	189.0	179.7	172.9	162.5	152.7	147.5
77.5°	138.5	147.1	149.9	151.2	149.9	147.1	138.5	130.6	122.8	115.6	110.5
80°	111.1	116.3	119.9	120.5	119.9	116.3	111.1	104.9	98.7	91.9	87.2
82.5°	85.4	89.7	90.9	92.2	90.9	89.7	85.4	80.0	74.6	69.5	65.6
85°	46.7	48.8	49.3	48.8	49.3	48.8	46.7	43.1	40.5	37.9	36.3
87.5°	22.0	21.8	22.0	23.0	22.0	21.8	22.0	21.0	21.1	20.0	18.8
90°	33.2	34.2	35.2	36.2	35.2	34.2	33.2	32.2	30.8	29.2	27.5
92.5°	69.0	69.7	70.4	71.2	70.4	69.7	69.0	68.2	66.8	64.5	62.3
95°	127.7	128.4	129.0	129.7	129.0	128.4	127.7	127.0	125.5	123.2	120.8
97.5°	195.5	195.9	196.3	196.7	196.3	195.9	195.5	195.1	193.7	191.5	189.3
100°	245.3	246.0	246.7	247.3	246.7	246.0	245.3	244.7	242.8	239.8	236.8
102.5°	295.2	296.1	297.1	298.0	297.1	296.1	295.2	294.3	292.1	288.9	285.6
105°	371.0	372.0	373.0	374.0	373.0	372.0	371.0	370.0	368.5	366.5	364.5
107.5°	452.0	452.0	451.9	451.8	451.9	452.0	452.0	452.1	451.6	450.6	449.6
110°	510.8	510.4	510.1	509.8	510.1	510.4	510.8	511.1	510.8	509.8	508.8



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	568.3	567.7	567.1	566.5	567.1	567.7	568.3	568.9	568.9	568.5	568.0
115°	657.1	656.7	656.4	656.1	656.4	656.7	657.1	657.4	657.7	658.1	658.4
117.5°	747.5	746.2	744.9	743.5	744.9	746.2	747.5	748.9	749.4	749.2	748.9
120°	807.9	806.5	805.2	803.9	805.2	806.5	807.9	809.2	809.9	809.9	809.9
122.5°	867.4	866.3	865.2	864.2	865.2	866.3	867.4	868.5	869.1	869.4	869.7
125°	955.7	955.3	955.0	954.7	955.0	955.3	955.7	956.0	956.5	957.2	957.9
127.5°	1043.5	1042.9	1042.2	1041.5	1042.2	1042.9	1043.5	1044.2	1044.7	1045.1	1045.4
130°	1101.5	1100.8	1100.1	1099.5	1100.1	1100.8	1101.5	1102.1	1102.6	1103.0	1103.3
132.5°	1156.6	1155.6	1154.7	1153.7	1154.7	1155.6	1156.6	1157.5	1158.1	1158.5	1158.8
135°	1242.2	1240.9	1239.5	1238.2	1239.5	1240.9	1242.2	1243.6	1244.2	1244.2	1244.2
137.5°	1325.9	1324.2	1322.5	1320.8	1322.5	1324.2	1325.9	1327.6	1328.2	1327.8	1327.4
140°	1379.0	1377.3	1375.6	1373.9	1375.6	1377.3	1379.0	1380.6	1381.1	1380.5	1379.8
142.5°	1429.6	1428.0	1426.3	1424.6	1426.3	1428.0	1429.6	1431.3	1432.0	1431.5	1431.1
145°	1503.6	1502.6	1501.6	1500.6	1501.6	1502.6	1503.6	1504.6	1505.1	1505.1	1505.1
147.5°	1572.3	1570.0	1567.8	1565.5	1567.8	1570.0	1572.3	1574.6	1575.3	1574.5	1573.7
150°	1615.7	1615.1	1614.4	1613.7	1614.4	1615.1	1615.7	1616.4	1616.8	1616.8	1616.8
152.5°	1657.2	1656.0	1654.8	1653.6	1654.8	1656.0	1657.2	1658.4	1658.6	1657.8	1657.0
155°	1715.3	1713.6	1711.9	1710.3	1711.9	1713.6	1715.3	1717.0	1717.1	1715.8	1714.4
157.5°	1764.2	1762.0	1759.8	1757.6	1759.8	1762.0	1764.2	1766.5	1766.9	1765.6	1764.2
160°	1795.2	1793.5	1791.9	1790.2	1791.9	1793.5	1795.2	1796.9	1797.1	1795.7	1794.4
162.5°	1823.8	1821.8	1819.9	1817.9	1819.9	1821.8	1823.8	1825.7	1825.9	1824.3	1822.7
165°	1861.1	1859.1	1857.1	1855.0	1857.1	1859.1	1861.1	1863.1	1863.4	1862.1	1860.7
167.5°	1890.8	1888.8	1886.7	1884.6	1886.7	1888.8	1890.8	1892.9	1892.9	1890.9	1888.9
170°	1907.3	1905.0	1902.6	1900.3	1902.6	1905.0	1907.3	1909.7	1909.8	1907.8	1905.8
172.5°	1919.8	1917.7	1915.6	1913.6	1915.6	1917.7	1919.8	1921.9	1921.9	1919.9	1917.9
175°	1933.0	1930.6	1928.3	1925.9	1928.3	1930.6	1933.0	1935.3	1935.5	1933.5	1931.5
177.5°	1938.8	1936.9	1935.0	1933.2	1935.0	1936.9	1938.8	1940.7	1940.8	1939.2	1937.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1169.8	1174.8	1181.0	1185.6	1193.9	1197.6	1202.2	1205.9	1212.6	1218.8	1226.3
5°	1091.0	1099.8	1111.7	1124.7	1139.8	1150.2	1164.7	1173.5	1191.2	1207.3	1222.8
7.5°	1019.5	1030.3	1047.2	1063.9	1083.6	1101.4	1119.6	1139.8	1162.3	1188.9	1210.9
10°	970.5	985.0	1003.2	1024.0	1047.9	1068.6	1093.0	1114.8	1142.4	1173.5	1202.6
12.5°	931.4	943.9	964.2	984.1	1009.6	1035.0	1060.2	1089.1	1121.2	1155.7	1192.2
15°	877.5	887.9	904.5	932.1	958.0	983.0	1020.9	1047.9	1088.4	1126.8	1170.9
17.5°	831.5	844.4	858.4	882.0	908.9	940.1	973.9	1007.8	1046.8	1095.5	1145.3
20°	803.3	813.7	829.8	847.9	876.5	907.7	939.9	974.1	1021.9	1072.3	1125.7
22.5°	772.5	783.8	801.9	821.8	845.8	875.7	911.2	948.8	998.6	1048.2	1106.2
25°	736.3	744.1	760.7	778.4	802.3	827.7	864.6	906.1	955.4	1012.0	1071.2
27.5°	702.1	709.0	724.2	739.5	761.1	791.3	824.3	866.2	912.7	970.1	1035.7
30°	677.6	684.9	698.4	715.0	735.8	762.3	796.0	835.5	885.3	941.4	1010.0
32.5°	656.4	662.9	673.1	689.7	710.0	735.7	766.9	807.2	857.1	914.0	981.3
35°	623.6	630.9	638.7	651.7	669.3	694.2	728.5	766.4	814.2	869.2	931.0
37.5°	591.0	598.9	605.9	617.5	633.6	655.6	685.2	724.7	767.9	820.9	880.2
40°	570.7	576.9	582.6	595.1	611.2	631.9	659.5	694.8	740.5	789.8	839.1
42.5°	550.3	556.1	561.0	571.8	586.7	606.6	632.9	667.3	709.7	755.7	799.2
45°	518.2	521.9	527.6	536.9	548.9	567.0	592.5	623.1	658.9	702.6	735.3
47.5°	483.5	489.2	493.9	502.1	511.9	529.7	554.1	580.2	612.7	645.1	668.2
50°	456.9	462.7	469.4	477.2	486.5	503.2	525.5	552.0	579.5	604.4	624.1
52.5°	432.0	437.3	444.5	451.9	463.3	477.4	496.4	520.0	547.1	565.0	581.4
55°	395.2	397.7	406.1	413.3	424.2	434.6	453.8	474.6	491.2	504.7	518.2
57.5°	357.5	361.0	365.8	372.3	383.1	395.3	408.8	427.1	436.9	443.9	454.3
60°	333.4	334.4	337.5	345.3	353.6	364.5	380.1	393.1	400.3	406.1	414.9
62.5°	306.8	307.0	312.2	317.9	324.1	335.9	348.5	359.0	365.0	367.8	376.3
65°	269.5	268.5	271.6	276.2	283.5	291.3	302.2	311.6	311.0	314.1	319.3
67.5°	231.4	230.3	230.3	234.8	240.7	247.7	255.2	260.6	260.7	264.8	267.4
70°	205.6	202.5	204.6	208.2	210.8	216.5	224.8	226.9	227.4	229.5	232.1
72.5°	179.0	178.0	179.7	181.2	183.0	187.5	194.5	195.8	195.9	197.1	201.4
75°	142.3	141.2	140.2	141.8	143.8	146.9	149.5	151.6	151.1	151.6	154.7
77.5°	106.7	103.7	103.2	104.1	104.6	106.4	109.1	108.9	109.5	109.4	112.9
80°	84.6	80.5	80.0	80.0	80.5	81.5	82.6	83.6	82.0	83.6	84.6
82.5°	62.2	59.7	59.6	59.2	59.3	59.5	60.1	60.8	60.4	61.2	61.8
85°	34.3	33.2	31.7	32.7	32.2	30.6	31.7	30.1	29.6	30.1	30.6
87.5°	16.8	16.9	15.6	15.1	14.2	14.2	12.8	11.9	10.9	10.8	11.5
90°	25.8	24.1	21.8	19.4	17.1	14.7	12.2	9.6	6.9	4.2	1.5
92.5°	60.1	57.9	55.0	52.1	49.3	46.4	44.0	42.1	40.3	38.4	36.5
95°	118.5	116.1	112.8	109.4	106.1	102.7	100.7	100.0	99.4	98.7	98.0
97.5°	187.1	184.9	180.3	175.7	171.0	166.4	164.0	163.7	163.4	163.1	162.9
100°	233.8	230.7	226.4	222.0	217.7	213.3	211.1	211.1	211.1	211.1	211.1
102.5°	282.3	279.0	276.8	274.6	272.4	270.2	268.4	267.0	265.7	264.4	263.0
105°	362.5	360.5	358.4	356.4	354.4	352.4	350.6	348.9	347.2	345.5	343.9
107.5°	448.6	447.6	446.1	444.5	443.0	441.5	439.8	438.2	436.5	434.8	433.1
110°	507.7	506.7	505.7	504.7	503.7	502.7	501.4	499.7	498.0	496.4	494.7



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	567.5	567.1	565.8	564.5	563.2	562.0	560.9	560.0	559.2	558.3	557.4
115°	658.7	659.1	658.4	657.7	657.1	656.4	655.4	654.0	652.7	651.4	650.0
117.5°	748.6	748.4	747.7	747.1	746.5	745.9	745.3	744.7	744.1	743.5	742.9
120°	809.9	809.9	809.5	809.2	808.9	808.5	807.5	805.9	804.2	802.5	800.8
122.5°	869.9	870.2	869.3	868.5	867.6	866.7	866.0	865.4	864.8	864.2	863.6
125°	958.5	959.2	958.9	958.5	958.2	957.9	956.7	954.7	952.7	950.6	948.6
127.5°	1045.7	1046.1	1045.7	1045.3	1044.9	1044.5	1043.7	1042.5	1041.4	1040.3	1039.1
130°	1103.6	1104.0	1103.3	1102.6	1102.0	1101.3	1100.1	1098.4	1096.8	1095.1	1093.4
132.5°	1159.1	1159.5	1159.6	1159.7	1159.9	1160.0	1158.7	1156.0	1153.2	1150.5	1147.7
135°	1244.2	1244.2	1243.9	1243.6	1243.2	1242.9	1241.7	1239.7	1237.7	1235.7	1233.7
137.5°	1327.0	1326.6	1325.8	1325.1	1324.4	1323.6	1322.3	1320.3	1318.4	1316.5	1314.5
140°	1379.1	1378.5	1377.5	1376.5	1375.4	1374.4	1373.1	1371.4	1369.7	1368.1	1366.4
142.5°	1430.7	1430.3	1429.1	1427.8	1426.5	1425.2	1423.9	1422.5	1421.1	1419.7	1418.3
145°	1505.1	1505.1	1504.1	1503.1	1502.1	1501.1	1500.0	1498.6	1497.3	1495.9	1494.6
147.5°	1572.9	1572.1	1571.3	1570.5	1569.7	1568.9	1568.1	1567.4	1566.6	1565.9	1565.2
150°	1616.8	1616.8	1615.4	1614.1	1612.7	1611.4	1610.9	1611.2	1611.6	1611.9	1612.2
152.5°	1656.2	1655.4	1654.8	1654.3	1653.8	1653.2	1652.7	1652.2	1651.8	1651.3	1650.8
155°	1713.1	1711.8	1711.4	1711.1	1710.8	1710.4	1710.3	1710.3	1710.3	1710.3	1710.3
157.5°	1762.9	1761.5	1761.2	1760.9	1760.5	1760.2	1760.4	1761.1	1761.9	1762.6	1763.3
160°	1793.0	1791.7	1791.4	1791.0	1790.7	1790.4	1790.7	1791.7	1792.7	1793.7	1794.7
162.5°	1821.1	1819.4	1819.4	1819.3	1819.2	1819.2	1819.5	1820.3	1821.0	1821.7	1822.5
165°	1859.4	1858.1	1857.7	1857.4	1857.1	1856.7	1856.9	1857.6	1858.2	1858.9	1859.6
167.5°	1886.9	1884.9	1884.9	1884.9	1884.9	1884.9	1885.6	1886.9	1888.3	1889.6	1890.9
170°	1903.8	1901.8	1901.8	1901.8	1901.8	1901.8	1902.5	1903.8	1905.1	1906.5	1907.8
172.5°	1915.9	1913.9	1913.9	1913.9	1913.9	1913.9	1914.5	1915.9	1917.2	1918.6	1919.9
175°	1929.4	1927.4	1927.4	1927.4	1927.4	1927.4	1928.1	1929.4	1930.8	1932.1	1933.5
177.5°	1936.0	1934.4	1934.6	1934.9	1935.2	1935.4	1936.1	1937.2	1938.3	1939.3	1940.4
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1230.0	1235.8	1239.6	1246.6	1252.4	1255.8	1258.7	1261.2	1264.1	1266.6	1273.6
5°	1237.9	1251.4	1262.8	1280.5	1296.6	1309.0	1322.5	1334.5	1344.4	1358.4	1369.3
7.5°	1234.5	1258.5	1283.6	1310.9	1338.8	1364.8	1388.7	1411.0	1431.3	1455.8	1477.3
10°	1231.2	1263.9	1296.1	1332.9	1370.8	1403.0	1433.1	1463.8	1486.1	1517.3	1543.7
12.5°	1228.7	1267.2	1306.0	1350.4	1392.0	1437.5	1477.6	1499.9	1533.9	1558.8	1590.3
15°	1218.2	1269.1	1322.5	1372.4	1431.6	1473.6	1509.0	1552.6	1584.2	1615.9	1650.2
17.5°	1199.4	1257.0	1316.8	1382.2	1439.0	1484.1	1529.6	1571.7	1609.5	1652.0	1694.6
20°	1190.7	1248.3	1316.8	1383.8	1439.4	1486.6	1533.4	1579.6	1621.1	1675.6	1725.0
22.5°	1172.4	1242.1	1305.2	1370.5	1427.7	1479.2	1532.1	1584.6	1639.8	1701.4	1763.2
25°	1139.8	1210.4	1277.4	1341.8	1399.4	1463.8	1520.4	1590.5	1661.1	1742.6	1819.5
27.5°	1105.9	1173.5	1234.9	1297.1	1364.3	1437.2	1510.6	1590.2	1682.6	1785.5	1893.9
30°	1078.5	1142.4	1202.1	1265.9	1336.0	1418.1	1498.6	1593.1	1700.0	1815.8	1944.6
32.5°	1046.5	1105.4	1163.4	1231.1	1307.4	1394.0	1487.8	1591.4	1720.0	1851.6	1984.1
35°	991.8	1041.1	1100.8	1173.0	1259.2	1358.4	1466.9	1589.4	1736.9	1888.0	1999.7
37.5°	926.9	972.8	1035.7	1114.8	1205.2	1311.6	1440.4	1585.8	1742.4	1862.9	1898.9
40°	883.3	925.8	991.3	1073.3	1165.7	1278.4	1419.6	1573.3	1725.0	1801.8	1772.2
42.5°	836.7	881.4	945.1	1026.4	1125.9	1248.5	1393.5	1547.2	1674.3	1703.4	1601.1
45°	763.3	809.5	872.3	954.4	1061.4	1194.3	1345.4	1485.1	1558.3	1505.8	1347.5
47.5°	695.1	738.4	796.6	881.3	991.7	1129.2	1274.7	1386.1	1391.9	1266.8	1097.6
50°	648.6	688.5	747.2	831.8	941.4	1080.6	1211.9	1299.7	1260.2	1118.5	955.9
52.5°	602.9	642.0	699.9	783.7	892.0	1019.5	1141.7	1203.3	1129.0	983.5	844.6
55°	536.9	571.2	627.8	705.1	808.0	926.4	1030.2	1051.5	954.9	811.6	698.9
57.5°	472.5	504.5	556.0	627.3	721.2	826.1	907.3	902.8	800.7	677.7	588.3
60°	428.9	460.1	505.8	575.3	661.0	751.4	820.9	804.3	703.1	597.1	521.9
62.5°	389.9	417.7	460.9	521.7	599.9	683.7	740.8	716.3	617.1	524.4	464.9
65°	332.3	355.7	392.6	444.5	509.4	578.5	622.6	590.9	506.3	434.1	386.3
67.5°	277.4	296.1	327.0	368.5	423.8	479.3	506.2	474.3	406.6	353.9	318.5
70°	242.5	259.1	283.0	319.9	368.2	414.9	435.1	406.6	348.4	303.2	277.8
72.5°	207.6	221.3	242.3	275.4	314.1	354.7	372.4	345.1	297.3	259.2	235.4
75°	160.5	169.8	184.3	207.2	237.8	270.0	279.9	256.0	225.4	196.8	181.2
77.5°	114.9	122.8	133.8	148.2	169.9	190.4	199.0	185.2	161.5	143.4	130.6
80°	88.3	92.4	101.8	113.7	130.9	143.8	149.5	140.7	124.1	110.6	100.7
82.5°	62.9	67.1	72.7	82.6	93.5	102.3	108.4	102.5	90.5	79.9	74.1
85°	30.6	33.2	36.3	40.5	48.8	54.0	53.5	49.8	45.2	41.0	37.9
87.5°	11.6	12.6	14.4	17.0	18.7	20.9	22.2	21.8	20.6	19.7	18.8
90°	4.2	6.9	9.6	12.2	14.7	17.1	19.4	21.8	24.1	25.8	27.5
92.5°	38.4	40.3	42.1	44.0	46.4	49.3	52.1	55.0	57.9	60.1	62.3
95°	98.7	99.4	100.0	100.7	102.7	106.1	109.4	112.8	116.1	118.5	120.8
97.5°	163.1	163.4	163.7	164.0	166.4	171.0	175.7	180.3	184.9	187.1	189.3
100°	211.1	211.1	211.1	211.1	213.3	217.7	222.0	226.4	230.7	233.8	236.8
102.5°	264.4	265.7	267.0	268.4	270.2	272.4	274.6	276.8	279.0	282.3	285.6
105°	345.5	347.2	348.9	350.6	352.4	354.4	356.4	358.4	360.5	362.5	364.5
107.5°	434.8	436.5	438.2	439.8	441.5	443.0	444.5	446.1	447.6	448.6	449.6
110°	496.4	498.0	499.7	501.4	502.7	503.7	504.7	505.7	506.7	507.7	508.8



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	558.3	559.2	560.0	560.9	562.0	563.2	564.5	565.8	567.1	567.5	568.0
115°	651.4	652.7	654.0	655.4	656.4	657.1	657.7	658.4	659.1	658.7	658.4
117.5°	743.5	744.1	744.7	745.3	745.9	746.5	747.1	747.7	748.4	748.6	748.9
120°	802.5	804.2	805.9	807.5	808.5	808.9	809.2	809.5	809.9	809.9	809.9
122.5°	864.2	864.8	865.4	866.0	866.7	867.6	868.5	869.3	870.2	869.9	869.7
125°	950.6	952.7	954.7	956.7	957.9	958.2	958.5	958.9	959.2	958.5	957.9
127.5°	1040.3	1041.4	1042.5	1043.7	1044.5	1044.9	1045.3	1045.7	1046.1	1045.7	1045.4
130°	1095.1	1096.8	1098.4	1100.1	1101.3	1102.0	1102.6	1103.3	1104.0	1103.6	1103.3
132.5°	1150.5	1153.2	1156.0	1158.7	1160.0	1159.9	1159.7	1159.6	1159.5	1159.1	1158.8
135°	1235.7	1237.7	1239.7	1241.7	1242.9	1243.2	1243.6	1243.9	1244.2	1244.2	1244.2
137.5°	1316.5	1318.4	1320.3	1322.3	1323.6	1324.4	1325.1	1325.8	1326.6	1327.0	1327.4
140°	1368.1	1369.7	1371.4	1373.1	1374.4	1375.4	1376.5	1377.5	1378.5	1379.1	1379.8
142.5°	1419.7	1421.1	1422.5	1423.9	1425.2	1426.5	1427.8	1429.1	1430.3	1430.7	1431.1
145°	1495.9	1497.3	1498.6	1500.0	1501.1	1502.1	1503.1	1504.1	1505.1	1505.1	1505.1
147.5°	1565.9	1566.6	1567.4	1568.1	1568.9	1569.7	1570.5	1571.3	1572.1	1572.9	1573.7
150°	1611.9	1611.6	1611.2	1610.9	1611.4	1612.7	1614.1	1615.4	1616.8	1616.8	1616.8
152.5°	1651.3	1651.8	1652.2	1652.7	1653.2	1653.8	1654.3	1654.8	1655.4	1656.2	1657.0
155°	1710.3	1710.3	1710.3	1710.3	1710.4	1710.8	1711.1	1711.4	1711.8	1713.1	1714.4
157.5°	1762.6	1761.9	1761.1	1760.4	1760.2	1760.5	1760.9	1761.2	1761.5	1762.9	1764.2
160°	1793.7	1792.7	1791.7	1790.7	1790.4	1790.7	1791.0	1791.4	1791.7	1793.0	1794.4
162.5°	1821.7	1821.0	1820.3	1819.5	1819.2	1819.2	1819.3	1819.4	1819.4	1821.1	1822.7
165°	1858.9	1858.2	1857.6	1856.9	1856.7	1857.1	1857.4	1857.7	1858.1	1859.4	1860.7
167.5°	1889.6	1888.3	1886.9	1885.6	1884.9	1884.9	1884.9	1884.9	1884.9	1886.9	1888.9
170°	1906.5	1905.1	1903.8	1902.5	1901.8	1901.8	1901.8	1901.8	1901.8	1903.8	1905.8
172.5°	1918.6	1917.2	1915.9	1914.5	1913.9	1913.9	1913.9	1913.9	1913.9	1915.9	1917.9
175°	1932.1	1930.8	1929.4	1928.1	1927.4	1927.4	1927.4	1927.4	1927.4	1929.4	1931.5
177.5°	1939.3	1938.3	1937.2	1936.1	1935.4	1935.2	1934.9	1934.6	1934.4	1936.0	1937.6
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4	1223.4
2.5°	1279.4	1282.8	1289.8	1287.3	1290.7	1292.3	1294.0
5°	1382.8	1399.4	1406.7	1405.6	1416.5	1413.9	1411.3
7.5°	1499.5	1517.0	1526.7	1538.9	1545.9	1546.4	1552.6
10°	1565.6	1588.4	1597.8	1610.7	1619.0	1623.7	1623.2
12.5°	1616.2	1634.1	1655.1	1661.4	1672.6	1678.5	1676.4
15°	1677.2	1705.8	1727.6	1738.5	1752.5	1756.6	1762.4
17.5°	1731.6	1769.9	1795.4	1829.2	1842.0	1849.8	1845.2
20°	1772.7	1823.1	1848.6	1889.1	1911.4	1923.3	1919.2
22.5°	1821.3	1875.9	1922.9	1958.0	1992.0	2008.1	2011.4
25°	1904.6	1979.4	2048.5	2094.7	2136.7	2146.6	2168.4
27.5°	1997.7	2085.9	2159.7	2208.3	2237.6	2248.6	2255.4
30°	2056.3	2144.0	2199.6	2230.7	2240.1	2239.0	2238.0
32.5°	2084.9	2139.9	2150.5	2141.8	2120.4	2102.4	2083.5
35°	2044.3	2003.3	1942.0	1863.1	1804.9	1746.3	1740.5
37.5°	1838.6	1707.4	1605.4	1491.5	1425.8	1385.2	1357.1
40°	1645.0	1496.0	1372.4	1276.3	1209.3	1182.9	1156.9
42.5°	1434.8	1292.4	1183.0	1102.7	1052.3	1022.9	1002.4
45°	1165.7	1040.1	954.4	896.2	856.3	833.4	820.4
47.5°	955.2	862.3	789.5	747.5	719.9	702.1	702.2
50°	842.2	753.4	705.1	671.9	648.0	634.0	636.6
52.5°	742.1	675.8	634.5	606.7	589.0	580.4	580.1
55°	620.5	572.7	545.7	525.5	513.5	503.7	505.8
57.5°	530.8	490.5	472.4	455.6	447.3	443.3	437.6
60°	475.1	444.0	428.4	414.9	406.6	403.5	397.7
62.5°	425.7	401.2	386.0	375.0	367.5	366.5	362.0
65°	357.8	339.1	325.6	320.4	312.6	310.5	310.5
67.5°	294.9	281.5	271.1	266.3	262.8	263.4	260.9
70°	255.5	244.6	237.8	232.6	230.0	230.5	228.5
72.5°	223.5	211.3	205.4	202.3	198.9	200.2	199.4
75°	169.3	163.0	159.9	156.8	154.7	153.7	152.7
77.5°	124.3	118.8	116.4	114.7	115.0	112.5	114.4
80°	96.1	91.4	89.8	87.2	86.7	86.7	86.2
82.5°	70.3	67.7	66.6	64.4	63.5	64.3	62.9
85°	36.3	34.3	33.8	33.8	32.7	31.7	34.3
87.5°	19.1	17.8	18.1	17.9	18.1	17.8	17.2
90°	29.2	30.8	32.2	33.2	34.2	35.2	36.2
92.5°	64.5	66.8	68.2	69.0	69.7	70.4	71.2
95°	123.2	125.5	127.0	127.7	128.4	129.0	129.7
97.5°	191.5	193.7	195.1	195.5	195.9	196.3	196.7
100°	239.8	242.8	244.7	245.3	246.0	246.7	247.3
102.5°	288.9	292.1	294.3	295.2	296.1	297.1	298.0
105°	366.5	368.5	370.0	371.0	372.0	373.0	374.0
107.5°	450.6	451.6	452.1	452.0	452.0	451.9	451.8
110°	509.8	510.8	511.1	510.8	510.4	510.1	509.8



TEST NUMBER: P333425

CATALOG NUMBER: S125DIW-S850D1560U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	568.5	568.9	568.9	568.3	567.7	567.1	566.5
115°	658.1	657.7	657.4	657.1	656.7	656.4	656.1
117.5°	749.2	749.4	748.9	747.5	746.2	744.9	743.5
120°	809.9	809.9	809.2	807.9	806.5	805.2	803.9
122.5°	869.4	869.1	868.5	867.4	866.3	865.2	864.2
125°	957.2	956.5	956.0	955.7	955.3	955.0	954.7
127.5°	1045.1	1044.7	1044.2	1043.5	1042.9	1042.2	1041.5
130°	1103.0	1102.6	1102.1	1101.5	1100.8	1100.1	1099.5
132.5°	1158.5	1158.1	1157.5	1156.6	1155.6	1154.7	1153.7
135°	1244.2	1244.2	1243.6	1242.2	1240.9	1239.5	1238.2
137.5°	1327.8	1328.2	1327.6	1325.9	1324.2	1322.5	1320.8
140°	1380.5	1381.1	1380.6	1379.0	1377.3	1375.6	1373.9
142.5°	1431.5	1432.0	1431.3	1429.6	1428.0	1426.3	1424.6
145°	1505.1	1505.1	1504.6	1503.6	1502.6	1501.6	1500.6
147.5°	1574.5	1575.3	1574.6	1572.3	1570.0	1567.8	1565.5
150°	1616.8	1616.8	1616.4	1615.7	1615.1	1614.4	1613.7
152.5°	1657.8	1658.6	1658.4	1657.2	1656.0	1654.8	1653.6
155°	1715.8	1717.1	1717.0	1715.3	1713.6	1711.9	1710.3
157.5°	1765.6	1766.9	1766.5	1764.2	1762.0	1759.8	1757.6
160°	1795.7	1797.1	1796.9	1795.2	1793.5	1791.9	1790.2
162.5°	1824.3	1825.9	1825.7	1823.8	1821.8	1819.9	1817.9
165°	1862.1	1863.4	1863.1	1861.1	1859.1	1857.1	1855.0
167.5°	1890.9	1892.9	1892.9	1890.8	1888.8	1886.7	1884.6
170°	1907.8	1909.8	1909.7	1907.3	1905.0	1902.6	1900.3
172.5°	1919.9	1921.9	1921.9	1919.8	1917.7	1915.6	1913.6
175°	1933.5	1935.5	1935.3	1933.0	1930.6	1928.3	1925.9
177.5°	1939.2	1940.8	1940.7	1938.8	1936.9	1935.0	1933.2
180°	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0	1938.0

(END OF REPORT)