

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333650-927

Luminaire Tested: **S125RDIW-S375D1050U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333650-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S375D1050U927-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1050 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4466.4 lumens
Efficiency: N/A
Efficacy: 117.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	66	75	69	64	60	54	50	48	40	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21
4	70	60	52	47	62	54	47	42	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	17	15	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	18	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	1.0
10°-20°	127.4	2.9
20°-30°	184.7	4.1
30°-40°	210.5	4.7
40°-50°	205.2	4.6
50°-60°	172.7	3.9
60°-70°	121.1	2.7
70°-80°	62.2	1.4
80°-90°	18.0	0.4
90°-100°	39.3	0.9
100°-110°	242.1	5.4
110°-120°	439.0	9.8
120°-130°	563.4	12.6
130°-140°	606.0	13.6
140°-150°	568.8	12.7
150°-160°	460.1	10.3
160°-170°	297.6	6.7
170°-180°	102.6	2.3
0°-30°	357.7	8.0
0°-40°	568.2	12.7
0°-60°	946.1	21.2
0°-90°	1147.4	25.7
90°-120°	720.3	16.1
90°-150°	2458.6	55.0
90°-180°	3319.0	74.3
0°-180°	4466.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	7	13	17	19	3
95°	46	42	13	17	17	58
105°	236	239	239	239	238	250
115°	442	446	447	444	439	438
125°	629	634	634	631	629	562
135°	784	789	788	786	781	604
145°	909	911	911	911	907	568
155°	1002	997	998	1000	994	461
165°	1057	1052	1053	1057	1051	298
175°	1081	1076	1077	1082	1076	103
180°	1081	1081	1081	1081	1081	



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	6.9	6.7	6.6	6.4	6.2	6.3	6.4	6.6	6.7	7.0	7.1
90°	0.8	2.2	3.6	5.1	6.5	7.8	9.1	10.3	11.6	12.8	13.7
92.5°	12.4	11.3	10.4	9.3	8.3	8.4	9.5	10.6	11.7	12.8	13.7
95°	45.6	45.2	44.6	44.0	43.6	39.8	33.1	26.4	19.6	12.8	13.7
97.5°	95.4	96.3	97.3	98.2	99.2	93.0	79.6	66.2	52.8	39.5	34.4
100°	133.8	134.4	134.8	135.4	135.9	136.6	137.3	138.0	138.7	139.4	112.9
102.5°	172.9	173.6	174.3	174.9	175.6	176.2	176.6	177.0	177.4	177.8	172.9
105°	235.5	236.2	236.9	237.7	238.4	238.8	238.8	238.8	238.8	238.8	238.8
107.5°	300.6	300.6	300.6	300.6	300.6	300.8	301.1	301.5	301.8	302.2	302.2
110°	342.9	342.9	342.9	342.9	342.9	343.1	343.4	343.8	344.1	344.5	344.0



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	382.6	383.1	383.5	383.9	384.4	384.7	384.9	385.1	385.3	385.6	384.8
115°	442.3	443.1	444.0	444.9	445.8	446.3	446.6	446.7	446.9	447.0	446.3
117.5°	504.0	503.9	503.9	503.8	503.8	504.1	504.8	505.5	506.1	506.8	505.9
120°	542.4	542.2	542.0	541.9	541.7	541.9	542.4	543.0	543.4	544.0	543.7
122.5°	576.4	577.0	577.7	578.4	579.1	579.6	579.8	580.0	580.3	580.5	580.2
125°	628.9	630.2	631.4	632.6	633.9	634.5	634.5	634.5	634.5	634.5	633.8
127.5°	679.1	680.0	680.9	681.8	682.6	683.0	682.9	682.9	682.7	682.6	682.2
130°	709.9	710.7	711.6	712.5	713.4	713.9	714.2	714.3	714.5	714.6	714.2
132.5°	740.6	741.6	742.7	743.7	744.7	745.0	744.7	744.3	743.9	743.5	743.4
135°	784.3	785.4	786.5	787.6	788.6	789.0	788.6	788.3	787.9	787.6	787.2
137.5°	824.6	825.5	826.4	827.4	828.3	828.6	828.3	828.0	827.6	827.3	827.4
140°	850.9	851.2	851.6	851.9	852.3	852.4	852.2	852.0	851.8	851.7	852.0
142.5°	874.6	874.8	875.0	875.2	875.4	875.7	875.9	876.2	876.4	876.6	876.7
145°	909.3	909.7	910.1	910.5	910.8	910.9	910.9	910.9	910.9	910.9	911.2
147.5°	939.8	939.8	939.7	939.6	939.5	939.6	939.8	940.0	940.2	940.4	940.6
150°	959.0	958.7	958.3	958.0	957.6	957.6	958.0	958.3	958.7	959.0	959.4
152.5°	977.6	976.8	976.0	975.3	974.5	974.3	974.6	975.0	975.3	975.7	976.0
155°	1001.5	1000.4	999.3	998.3	997.2	996.9	997.2	997.6	997.9	998.3	998.8
157.5°	1019.9	1019.3	1018.7	1018.0	1017.3	1017.1	1017.1	1017.1	1017.2	1017.2	1017.8
160°	1032.8	1031.7	1030.6	1029.5	1028.5	1028.0	1028.2	1028.4	1028.6	1028.7	1029.4
162.5°	1043.0	1042.0	1040.8	1039.8	1038.7	1038.2	1038.5	1038.6	1038.8	1038.9	1040.0
165°	1056.8	1055.7	1054.6	1053.6	1052.5	1052.0	1052.3	1052.4	1052.6	1052.7	1053.8
167.5°	1067.0	1066.0	1064.9	1063.7	1062.6	1062.2	1062.3	1062.5	1062.7	1062.9	1064.1
170°	1072.8	1071.6	1070.3	1069.1	1067.8	1067.3	1067.5	1067.6	1067.8	1068.0	1069.4
172.5°	1076.7	1075.4	1074.1	1072.9	1071.7	1071.2	1071.5	1071.8	1072.1	1072.5	1073.7
175°	1080.8	1079.7	1078.6	1077.6	1076.5	1076.1	1076.3	1076.4	1076.7	1076.8	1078.2
177.5°	1082.8	1081.9	1081.0	1080.1	1079.3	1079.0	1079.1	1079.3	1079.3	1079.5	1080.5
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	7.3	7.5	7.7	7.8	7.8	7.8	7.9	7.9
90°	14.6	15.5	16.4	17.1	17.7	18.1	18.7	19.3
92.5°	14.6	15.5	16.4	17.0	17.2	17.4	17.7	18.0
95°	14.6	15.5	16.4	16.8	16.8	16.8	16.8	16.8
97.5°	29.4	24.3	19.3	16.8	16.8	16.8	16.8	16.8
100°	86.3	59.8	33.3	19.6	18.9	18.2	17.5	16.8
102.5°	167.8	162.8	157.8	149.2	137.1	125.0	112.9	100.8
105°	238.8	238.8	238.8	238.7	238.5	238.3	238.1	238.0
107.5°	302.3	302.3	302.4	302.1	301.6	301.0	300.5	300.0
110°	343.4	342.9	342.4	342.2	342.4	342.5	342.7	342.9



TEST NUMBER: P333650-927

CATALOG NUMBER: S125RDIW-S375D1050U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	384.2	383.5	382.9	382.4	382.1	381.8	381.6	381.4
115°	445.6	444.9	444.2	443.3	442.3	441.2	440.1	439.0
117.5°	505.0	504.1	503.1	502.4	502.0	501.5	501.1	500.6
120°	543.3	543.0	542.6	541.9	541.1	540.2	539.3	538.4
122.5°	579.8	579.5	579.1	578.5	577.4	576.4	575.4	574.3
125°	633.1	632.4	631.7	631.1	630.6	630.0	629.5	628.9
127.5°	681.8	681.4	681.0	680.2	678.9	677.6	676.2	674.9
130°	713.6	713.0	712.5	711.8	710.9	710.0	709.2	708.3
132.5°	743.3	743.1	743.1	742.6	741.7	740.8	739.9	739.0
135°	786.9	786.5	786.2	785.4	784.3	783.3	782.2	781.2
137.5°	827.4	827.5	827.6	827.2	826.2	825.3	824.4	823.5
140°	852.4	852.7	853.1	852.7	851.7	850.6	849.5	848.4
142.5°	876.8	876.9	876.9	876.5	875.4	874.3	873.2	872.2
145°	911.3	911.5	911.6	911.2	910.1	909.1	908.0	907.0
147.5°	940.9	941.1	941.3	940.8	939.4	938.2	936.9	935.6
150°	959.7	960.1	960.4	959.9	958.5	957.0	955.6	954.2
152.5°	976.4	976.8	977.1	976.7	975.3	974.1	972.8	971.5
155°	999.3	999.9	1000.4	1000.0	998.5	997.1	995.7	994.3
157.5°	1018.4	1018.9	1019.5	1019.1	1017.6	1016.2	1014.8	1013.4
160°	1030.2	1030.9	1031.6	1031.2	1029.8	1028.4	1027.0	1025.6
162.5°	1041.0	1042.0	1043.0	1042.7	1041.1	1039.6	1038.0	1036.4
165°	1054.9	1056.0	1057.0	1056.9	1055.4	1054.0	1052.6	1051.1
167.5°	1065.4	1066.7	1068.0	1067.9	1066.2	1064.6	1063.0	1061.4
170°	1070.9	1072.3	1073.7	1073.6	1072.0	1070.4	1068.8	1067.1
172.5°	1075.1	1076.3	1077.6	1077.4	1075.9	1074.2	1072.6	1071.0
175°	1079.7	1081.1	1082.5	1082.4	1080.8	1079.2	1077.6	1076.0
177.5°	1081.5	1082.5	1083.5	1083.5	1082.3	1081.2	1080.1	1078.9
180°	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8	1080.8

(END OF REPORT)