

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333404

Luminaire Tested: **S125DIW-S850D470U835-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333404
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U835-4F0-1E-UDD-F
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5291.3 lumens
Efficiency: N/A
Efficacy: 140.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	70	70	70	65
1	101	97	92	89	95	91	87	84	80	78	75	70	68	67	61	60	59	54
2	92	84	78	73	86	79	74	69	70	66	62	62	58	56	54	51	49	45
3	84	74	67	60	78	70	63	58	62	57	52	55	50	47	48	45	42	38
4	77	66	57	51	72	62	55	49	55	49	45	49	44	40	43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	38	44	39	35	38	35	31	29
6	65	53	44	38	61	50	42	37	44	38	34	40	35	31	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	18
10	49	36	29	24	46	35	28	23	31	25	21	28	23	20	25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	2.3
10°-20°	349.6	6.6
20°-30°	516.2	9.8
30°-40°	602.4	11.4
40°-50°	605.0	11.4
50°-60°	531.1	10.0
60°-70°	395.7	7.5
70°-80°	226.3	4.3
80°-90°	67.1	1.3
90°-100°	22.2	0.4
100°-110°	136.7	2.6
110°-120°	247.9	4.7
120°-130°	318.1	6.0
130°-140°	342.2	6.5
140°-150°	321.2	6.1
150°-160°	259.8	4.9
160°-170°	168.0	3.2
170°-180°	58.0	1.1
0°-30°	989.7	18.7
0°-40°	1592.1	30.1
0°-60°	2728.2	51.6
0°-90°	3417.3	64.6
90°-120°	406.7	7.7
90°-150°	1388.2	26.2
90°-180°	1874.0	35.4
0°-180°	5291.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	0	4	7	9	11	4
95°	26	24	7	9	10	33
105°	133	135	135	135	134	141
115°	250	252	252	251	248	247
125°	355	358	358	356	355	317
135°	443	445	445	444	441	341
145°	514	514	514	515	512	321
155°	566	563	564	565	561	260
165°	597	594	594	597	594	168
175°	610	608	608	611	608	58
180°	610	610	610	610	610	



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.5	22.7	22.8	23.0	23.2	23.2	23.2	23.1	23.1	23.0	23.2
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.2	7.7
92.5°	7.0	6.4	5.8	5.3	4.7	4.7	5.4	6.0	6.6	7.2	7.7
95°	25.8	25.5	25.2	24.9	24.6	22.5	18.7	14.9	11.1	7.2	7.7
97.5°	53.8	54.4	54.9	55.5	56.0	52.5	44.9	37.4	29.8	22.3	19.4
100°	75.5	75.9	76.2	76.5	76.8	77.1	77.5	77.9	78.3	78.7	63.7
102.5°	97.6	98.0	98.4	98.8	99.2	99.5	99.7	99.9	100.2	100.4	97.6
105°	133.0	133.4	133.8	134.2	134.6	134.8	134.8	134.8	134.8	134.8	134.8
107.5°	169.7	169.7	169.7	169.7	169.7	169.8	170.0	170.2	170.4	170.6	170.7
110°	193.6	193.6	193.6	193.6	193.6	193.7	193.9	194.1	194.3	194.5	194.2



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	216.1	216.3	216.5	216.8	217.0	217.2	217.3	217.5	217.6	217.7	217.3
115°	249.7	250.2	250.7	251.2	251.7	252.0	252.1	252.2	252.3	252.4	252.0
117.5°	284.6	284.5	284.5	284.5	284.5	284.7	285.0	285.4	285.8	286.2	285.7
120°	306.3	306.2	306.1	306.0	305.9	306.0	306.3	306.6	306.9	307.2	307.0
122.5°	325.5	325.8	326.2	326.6	327.0	327.2	327.4	327.5	327.7	327.8	327.6
125°	355.1	355.8	356.5	357.2	357.9	358.3	358.3	358.3	358.3	358.3	357.9
127.5°	383.4	384.0	384.5	385.0	385.5	385.7	385.6	385.6	385.5	385.4	385.2
130°	400.8	401.3	401.8	402.3	402.8	403.1	403.2	403.3	403.4	403.5	403.2
132.5°	418.2	418.8	419.4	419.9	420.5	420.7	420.5	420.3	420.0	419.8	419.8
135°	442.9	443.5	444.1	444.7	445.3	445.5	445.3	445.1	444.9	444.7	444.5
137.5°	465.6	466.1	466.6	467.2	467.7	467.9	467.7	467.5	467.3	467.1	467.2
140°	480.4	480.6	480.8	481.0	481.2	481.3	481.2	481.1	481.0	480.9	481.1
142.5°	493.8	494.0	494.1	494.2	494.3	494.4	494.6	494.7	494.9	495.0	495.0
145°	513.5	513.7	513.9	514.1	514.3	514.4	514.4	514.4	514.4	514.4	514.5
147.5°	530.7	530.6	530.6	530.5	530.5	530.5	530.7	530.8	530.9	531.0	531.1
150°	541.5	541.3	541.1	540.9	540.7	540.7	540.9	541.1	541.3	541.5	541.7
152.5°	552.0	551.6	551.1	550.7	550.2	550.1	550.3	550.5	550.7	550.9	551.1
155°	565.5	564.9	564.3	563.7	563.1	562.9	563.1	563.3	563.5	563.7	564.0
157.5°	575.9	575.5	575.2	574.8	574.4	574.3	574.3	574.3	574.3	574.4	574.7
160°	583.1	582.5	581.9	581.3	580.7	580.5	580.6	580.7	580.8	580.9	581.3
162.5°	588.9	588.3	587.7	587.1	586.5	586.3	586.4	586.5	586.6	586.7	587.2
165°	596.7	596.1	595.5	594.9	594.3	594.0	594.1	594.2	594.3	594.4	595.0
167.5°	602.5	601.9	601.3	600.6	600.0	599.7	599.8	599.9	600.0	600.1	600.9
170°	605.8	605.1	604.3	603.6	602.9	602.6	602.7	602.8	602.9	603.0	603.8
172.5°	607.9	607.2	606.5	605.8	605.1	604.9	605.0	605.2	605.4	605.6	606.3
175°	610.3	609.7	609.1	608.5	607.9	607.6	607.7	607.8	607.9	608.0	608.8
177.5°	611.4	610.9	610.4	609.9	609.4	609.2	609.3	609.4	609.5	609.6	610.1
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	23.3	23.4	23.5	23.3	23.0	22.7	22.4	22.1
90°	8.2	8.7	9.2	9.7	10.0	10.3	10.6	10.9
92.5°	8.2	8.7	9.2	9.6	9.7	9.9	10.0	10.1
95°	8.2	8.7	9.2	9.5	9.5	9.5	9.5	9.5
97.5°	16.6	13.8	10.9	9.5	9.5	9.5	9.5	9.5
100°	48.8	33.8	18.8	11.1	10.7	10.3	9.9	9.5
102.5°	94.8	91.9	89.1	84.3	77.4	70.6	63.7	56.9
105°	134.8	134.8	134.8	134.8	134.7	134.6	134.5	134.4
107.5°	170.7	170.7	170.7	170.6	170.3	170.0	169.7	169.4
110°	193.9	193.6	193.3	193.2	193.3	193.4	193.5	193.6



TEST NUMBER: P333404

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	216.9	216.5	216.2	215.9	215.8	215.6	215.5	215.3
115°	251.6	251.2	250.8	250.3	249.7	249.1	248.5	247.9
117.5°	285.1	284.6	284.1	283.7	283.4	283.2	282.9	282.7
120°	306.8	306.6	306.4	306.0	305.5	305.0	304.5	304.0
122.5°	327.4	327.2	327.0	326.6	326.0	325.4	324.9	324.3
125°	357.5	357.1	356.7	356.3	356.0	355.7	355.4	355.1
127.5°	385.0	384.8	384.6	384.1	383.3	382.6	381.8	381.1
130°	402.9	402.6	402.3	401.9	401.4	400.9	400.4	399.9
132.5°	419.7	419.6	419.6	419.3	418.8	418.3	417.8	417.3
135°	444.3	444.1	443.9	443.5	442.9	442.3	441.7	441.1
137.5°	467.2	467.3	467.3	467.1	466.5	466.0	465.5	465.0
140°	481.3	481.5	481.7	481.5	480.9	480.3	479.7	479.1
142.5°	495.1	495.1	495.2	494.9	494.3	493.7	493.1	492.5
145°	514.6	514.7	514.8	514.5	513.9	513.3	512.7	512.1
147.5°	531.3	531.4	531.5	531.2	530.5	529.8	529.0	528.3
150°	541.9	542.1	542.3	542.0	541.2	540.4	539.6	538.8
152.5°	551.3	551.5	551.7	551.5	550.7	550.0	549.3	548.6
155°	564.3	564.6	564.9	564.6	563.8	563.0	562.2	561.4
157.5°	575.0	575.3	575.6	575.4	574.6	573.8	573.0	572.2
160°	581.7	582.1	582.5	582.3	581.5	580.7	579.9	579.1
162.5°	587.8	588.4	588.9	588.8	587.9	587.0	586.1	585.2
165°	595.7	596.3	596.9	596.8	596.0	595.1	594.3	593.5
167.5°	601.6	602.3	603.0	603.0	602.0	601.1	600.2	599.3
170°	604.6	605.5	606.3	606.2	605.3	604.4	603.5	602.6
172.5°	607.0	607.7	608.5	608.4	607.5	606.6	605.7	604.8
175°	609.6	610.4	611.2	611.2	610.3	609.4	608.5	607.6
177.5°	610.7	611.2	611.8	611.8	611.1	610.5	609.8	609.2
180°	610.3	610.3	610.3	610.3	610.3	610.3	610.3	610.3

(END OF REPORT)