

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333405

Luminaire Tested: **S125DIW-S850D470U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333405
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125DIW-S850D470U835-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 470 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5042.5 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333405
CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	97	93	90	96	92	88	85	82	79	77	72	70	69	64	62	61	57
2	93	85	78	73	87	80	75	70	72	67	63	64	60	57	56	54	51	48
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	50	47	44	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	45	41	38	35
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	123.8	2.5
10°-20°	349.6	6.9
20°-30°	516.2	10.2
30°-40°	602.4	11.9
40°-50°	605.0	12.0
50°-60°	531.1	10.5
60°-70°	395.7	7.8
70°-80°	226.3	4.5
80°-90°	67.1	1.3
90°-100°	39.0	0.8
100°-110°	115.2	2.3
110°-120°	195.1	3.9
120°-130°	256.8	5.1
130°-140°	287.7	5.7
140°-150°	282.0	5.6
150°-160°	236.9	4.7
160°-170°	157.4	3.1
170°-180°	55.1	1.1
0°-30°	989.7	19.6
0°-40°	1592.1	31.6
0°-60°	2728.2	54.1
0°-90°	3417.3	67.8
90°-120°	349.3	6.9
90°-150°	1175.8	23.3
90°-180°	1625.0	32.2
0°-180°	5042.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	0	4	7	10	11	5
95°	30	31	35	38	39	31
105°	103	106	108	111	112	110
115°	195	197	198	198	197	193
125°	285	288	288	287	287	255
135°	371	373	374	374	372	286
145°	449	451	452	452	451	281
155°	514	514	514	516	514	237
165°	559	558	558	560	558	158
175°	581	579	579	582	579	55
180°	582	582	582	582	582	



TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.5	22.7	22.8	23.0	23.2	23.2	23.2	23.1	23.1	23.1	23.2
90°	0.5	1.3	2.1	2.9	3.7	4.4	5.1	5.8	6.5	7.3	7.8
92.5°	11.0	11.5	12.1	12.7	13.2	13.9	14.8	15.7	16.5	17.4	18.1
95°	29.5	29.7	29.9	30.1	30.3	30.9	31.9	32.9	33.9	34.9	35.6
97.5°	48.9	49.0	49.1	49.2	49.3	50.0	51.4	52.8	54.2	55.6	56.2
100°	63.5	63.5	63.5	63.5	63.5	64.1	65.4	66.7	68.0	69.3	70.3
102.5°	79.0	79.4	79.9	80.3	80.7	81.2	81.9	82.5	83.2	83.8	84.8
105°	103.3	103.8	104.3	104.8	105.4	105.9	106.5	107.1	107.7	108.3	108.9
107.5°	130.2	130.7	131.2	131.7	132.2	132.7	133.1	133.6	134.1	134.5	134.8
110°	148.7	149.2	149.7	150.2	150.7	151.1	151.4	151.7	152.0	152.3	152.6



TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	167.5	167.8	168.0	168.3	168.6	168.9	169.3	169.7	170.0	170.4	170.6
115°	195.3	195.7	196.2	196.6	197.0	197.3	197.5	197.7	197.9	198.1	198.0
117.5°	223.3	223.4	223.6	223.8	224.0	224.2	224.4	224.5	224.7	224.9	225.0
120°	240.7	241.2	241.7	242.2	242.7	243.0	243.1	243.2	243.3	243.4	243.4
122.5°	259.5	259.7	259.9	260.1	260.2	260.5	260.7	261.0	261.3	261.5	261.4
125°	285.1	285.7	286.3	286.9	287.5	287.9	288.0	288.1	288.2	288.3	288.1
127.5°	312.3	312.6	313.0	313.3	313.7	313.9	314.0	314.1	314.2	314.4	314.3
130°	328.6	329.1	329.6	330.1	330.6	331.0	331.2	331.4	331.6	331.8	331.7
132.5°	344.9	345.7	346.6	347.4	348.2	348.6	348.6	348.5	348.5	348.4	348.3
135°	370.7	371.4	372.0	372.6	373.2	373.5	373.6	373.7	373.8	373.9	373.9
137.5°	395.0	395.6	396.2	396.8	397.4	397.8	398.0	398.2	398.4	398.7	398.8
140°	410.6	411.1	411.6	412.1	412.6	413.1	413.4	413.7	414.0	414.3	414.5
142.5°	426.2	426.6	427.1	427.5	427.9	428.3	428.7	429.1	429.5	429.9	430.0
145°	449.2	449.6	450.0	450.4	450.8	451.1	451.4	451.7	452.0	452.3	452.3
147.5°	470.4	470.6	470.8	471.0	471.3	471.5	471.7	472.0	472.2	472.5	472.7
150°	484.5	484.4	484.3	484.2	484.1	484.3	484.7	485.1	485.5	485.9	485.9
152.5°	496.1	496.3	496.4	496.5	496.7	496.8	497.0	497.2	497.3	497.5	497.7
155°	514.0	514.0	514.0	514.0	514.0	514.0	514.1	514.2	514.3	514.4	514.8
157.5°	529.9	529.7	529.5	529.3	529.0	529.0	529.1	529.2	529.3	529.4	529.8
160°	539.4	539.1	538.7	538.4	538.1	538.0	538.1	538.2	538.3	538.4	538.9
162.5°	547.7	547.5	547.3	547.0	546.8	546.7	546.7	546.7	546.8	546.8	547.3
165°	558.8	558.6	558.4	558.2	558.0	558.0	558.1	558.2	558.3	558.4	558.8
167.5°	568.3	567.9	567.5	567.1	566.7	566.5	566.5	566.5	566.5	566.5	567.1
170°	573.3	572.9	572.5	572.1	571.7	571.5	571.5	571.5	571.5	571.5	572.1
172.5°	577.0	576.6	576.2	575.8	575.4	575.2	575.2	575.2	575.2	575.2	575.8
175°	581.1	580.6	580.2	579.8	579.4	579.2	579.2	579.2	579.2	579.2	579.8
177.5°	583.1	582.8	582.5	582.2	581.8	581.6	581.6	581.5	581.4	581.3	581.8
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4



TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	23.3	23.4	23.5	23.4	23.0	22.7	22.4	22.1
90°	8.3	8.8	9.3	9.7	10.0	10.3	10.6	10.9
92.5°	18.7	19.4	20.1	20.5	20.7	20.9	21.2	21.4
95°	36.3	37.0	37.7	38.2	38.4	38.6	38.8	39.0
97.5°	56.9	57.6	58.2	58.6	58.7	58.9	59.0	59.1
100°	71.2	72.1	73.0	73.5	73.7	73.9	74.1	74.3
102.5°	85.8	86.8	87.8	88.4	88.7	89.0	89.3	89.6
105°	109.5	110.1	110.7	111.2	111.5	111.8	112.1	112.4
107.5°	135.1	135.4	135.7	135.9	135.9	135.8	135.8	135.8
110°	152.9	153.2	153.5	153.6	153.5	153.4	153.3	153.2



TEST NUMBER: P333405

CATALOG NUMBER: S125DIW-S850D470U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	170.7	170.8	171.0	171.0	170.8	170.6	170.4	170.2
115°	197.9	197.8	197.7	197.6	197.5	197.4	197.3	197.2
117.5°	225.1	225.1	225.2	225.1	224.7	224.3	223.8	223.4
120°	243.4	243.4	243.4	243.2	242.8	242.4	242.0	241.6
122.5°	261.4	261.3	261.2	261.0	260.7	260.4	260.0	259.7
125°	287.9	287.7	287.5	287.3	287.2	287.1	287.0	286.9
127.5°	314.2	314.1	314.0	313.8	313.6	313.4	313.2	313.0
130°	331.6	331.5	331.4	331.2	331.0	330.8	330.6	330.4
132.5°	348.2	348.1	348.0	347.9	347.6	347.3	347.0	346.7
135°	373.9	373.9	373.9	373.7	373.3	372.9	372.5	372.1
137.5°	398.9	399.0	399.2	399.0	398.5	398.0	397.4	396.9
140°	414.7	414.9	415.1	414.9	414.4	413.9	413.4	412.9
142.5°	430.1	430.2	430.3	430.1	429.6	429.1	428.6	428.1
145°	452.3	452.3	452.3	452.2	451.9	451.6	451.3	451.0
147.5°	472.9	473.2	473.4	473.2	472.5	471.8	471.1	470.5
150°	485.9	485.9	485.9	485.8	485.6	485.4	485.2	485.0
152.5°	498.0	498.2	498.4	498.4	498.0	497.7	497.3	496.9
155°	515.2	515.6	516.0	516.0	515.5	515.0	514.5	514.0
157.5°	530.2	530.6	531.0	530.9	530.2	529.5	528.9	528.2
160°	539.3	539.7	540.1	540.0	539.5	539.0	538.5	538.0
162.5°	547.8	548.2	548.7	548.7	548.1	547.5	546.9	546.3
165°	559.2	559.6	560.0	559.9	559.3	558.7	558.1	557.5
167.5°	567.7	568.3	568.9	568.9	568.2	567.6	567.0	566.4
170°	572.7	573.3	574.0	573.9	573.2	572.5	571.8	571.1
172.5°	576.4	577.0	577.6	577.6	576.9	576.3	575.7	575.1
175°	580.4	581.1	581.7	581.6	580.9	580.2	579.5	578.8
177.5°	582.3	582.8	583.3	583.2	582.7	582.1	581.5	581.0
180°	582.4	582.4	582.4	582.4	582.4	582.4	582.4	582.4

(END OF REPORT)