

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333653-927

Luminaire Tested: **S125RDIW-S375D1340U927-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333653-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1340U927-4F0-1E-UDD-A1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4842.8 lumens  
Efficiency: N/A  
Efficacy: 103.9 lumens/watt  
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47  
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - · - · 90°-270°    - · - · 135°-315°



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32	24
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27	21
2	84	77	71	66	74	69	64	60	53	50	47	39	37	35	25	24	23	17
3	77	68	61	55	68	61	55	50	47	43	40	34	32	30	23	21	20	15
4	70	60	53	47	62	54	47	42	42	37	34	31	28	26	20	19	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	17	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	17	15	13	10
7	55	43	35	30	48	39	32	27	30	26	22	22	19	17	15	13	12	9
8	50	39	31	26	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	23	42	32	26	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	2880	2880	2880	2880
5°	3313	2884	2547	2884
10°	3801	2868	2247	2868
15°	4105	2840	1997	2840
20°	4526	2805	1844	2805
25°	5238	2760	1712	2760
30°	5700	2712	1625	2712
35°	4809	2657	1544	2657
40°	3358	2557	1475	2557
45°	2491	2422	1408	2422
50°	1986	2283	1350	2283
55°	1686	2109	1298	2109
60°	1456	1953	1215	1953
65°	1297	1785	1045	1785
70°	1141	1635	954	1635
75°	986	1415	896	1415
80°	748	1190	748	1190
85°	622	934	704	934



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.8	0.9
10°-20°	125.3	2.6
20°-30°	198.7	4.1
30°-40°	239.6	4.9
40°-50°	214.0	4.4
50°-60°	164.1	3.4
60°-70°	106.6	2.2
70°-80°	51.8	1.1
80°-90°	15.3	0.3
90°-100°	88.4	1.8
100°-110°	261.2	5.4
110°-120°	442.4	9.1
120°-130°	582.2	12.0
130°-140°	652.3	13.5
140°-150°	639.3	13.2
150°-160°	537.0	11.1
160°-170°	357.0	7.4
170°-180°	124.9	2.6
0°-30°	366.8	7.6
0°-40°	606.3	12.5
0°-60°	984.4	20.3
0°-90°	1158.1	23.9
90°-120°	792.0	16.4
90°-150°	2665.8	55.0
90°-180°	3685.0	76.1
0°-180°	4842.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	446	446	446	446	446	
5°	511	445	393	445	511	51
15°	614	425	299	425	614	176
25°	735	387	240	387	735	338
35°	610	337	196	337	610	368
45°	273	265	154	265	273	218
55°	150	187	115	187	150	136
65°	85	117	68	117	85	84
75°	40	57	36	57	40	42
85°	8	13	10	13	8	10
90°	25	1	25	1	25	15
95°	88	67	88	67	88	90
105°	255	234	255	234	255	270
115°	447	443	447	443	447	442
125°	650	646	650	646	650	581
135°	844	841	844	841	844	651
145°	1022	1018	1022	1018	1022	638
155°	1165	1165	1165	1165	1165	536
165°	1264	1267	1264	1267	1264	356
175°	1312	1317	1312	1317	1312	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	469.1	468.7	469.4	467.7	467.9	465.4	465.4	463.5	461.0	459.1	458.2
5°	511.0	511.4	510.7	507.9	506.1	503.4	500.3	494.8	490.2	485.8	482.4
7.5°	554.4	554.6	552.2	551.4	546.7	543.4	536.5	528.9	522.4	513.9	507.5
10°	579.6	579.3	576.8	574.7	570.8	565.6	558.8	550.1	541.9	532.7	523.9
12.5°	594.1	593.7	592.9	590.4	586.7	582.2	576.4	567.8	557.6	547.6	537.3
15°	613.9	612.7	610.3	607.1	601.8	596.5	590.2	582.5	572.7	561.4	551.9
17.5°	638.4	638.4	634.8	630.4	623.2	613.9	604.0	591.6	578.4	565.9	555.8
20°	658.6	658.1	654.4	645.9	637.7	626.0	614.7	599.4	583.4	567.0	554.4
22.5°	687.6	686.2	682.4	671.3	658.5	643.4	626.1	607.5	588.0	569.6	552.9
25°	735.1	734.0	726.5	713.7	695.8	672.5	649.8	624.4	596.4	572.0	551.9
27.5°	767.6	766.4	760.8	750.2	733.6	709.2	678.5	644.4	609.5	576.0	547.0
30°	764.4	767.1	766.4	761.4	749.0	727.1	698.7	660.4	618.9	579.6	544.9
32.5°	718.4	720.9	727.3	737.0	737.8	729.0	707.7	672.4	629.4	584.6	543.3
35°	609.9	613.2	625.7	645.2	670.9	692.3	696.6	677.6	639.0	590.9	540.9
37.5°	468.9	486.9	497.4	518.0	556.7	596.1	634.0	647.9	631.5	588.3	537.0
40°	398.3	402.7	421.4	444.7	477.2	518.2	572.2	611.2	612.4	582.5	530.8
42.5°	340.9	346.5	359.3	377.9	405.8	446.7	502.5	554.0	577.7	566.3	522.8
45°	272.7	276.9	286.3	300.6	321.9	355.8	403.8	463.3	510.5	529.0	501.2
47.5°	224.0	226.3	234.4	245.3	261.2	285.8	323.0	374.6	431.3	471.0	467.1
50°	197.7	200.3	206.4	214.7	228.1	248.9	278.6	321.6	380.0	428.5	438.2
52.5°	177.2	179.4	183.2	191.0	202.0	218.0	242.0	280.9	333.4	385.0	407.5
55°	149.7	151.2	154.3	158.7	167.5	179.0	199.7	226.6	269.1	321.1	354.0
57.5°	127.1	127.9	129.8	133.9	140.0	148.4	163.3	186.1	216.6	263.4	299.8
60°	112.7	113.5	116.1	118.8	123.6	131.3	143.0	158.9	188.1	226.8	263.6
62.5°	101.3	101.8	102.9	105.6	109.8	115.7	124.9	137.9	161.2	195.2	229.9
65°	84.9	85.1	85.5	87.7	90.2	94.7	100.7	109.8	127.4	153.0	183.8
67.5°	69.2	69.5	70.7	71.5	74.1	76.4	80.0	87.0	99.4	116.7	140.6
70°	60.4	60.2	61.5	62.4	63.3	66.1	68.4	74.1	81.8	95.0	114.9
72.5°	52.2	51.7	52.3	52.6	53.8	55.7	58.1	61.6	67.5	76.5	91.8
75°	39.5	39.7	39.7	40.1	41.0	41.7	42.5	44.3	47.6	53.6	61.9
77.5°	27.7	27.5	28.2	28.4	28.9	29.7	30.3	31.1	32.4	34.9	39.1
80°	20.1	20.1	20.3	20.8	20.7	21.1	21.9	22.7	24.3	25.8	27.3
82.5°	15.4	15.3	15.4	15.6	15.5	15.9	16.2	16.4	17.0	17.7	18.8
85°	8.4	8.4	8.6	8.6	8.8	8.8	9.0	9.0	9.0	9.2	9.3
87.5°	8.2	7.8	7.6	7.4	7.4	7.6	7.2	6.8	6.6	6.3	6.2
90°	24.6	24.0	23.3	22.6	21.9	21.0	19.9	18.7	17.6	16.5	14.8
92.5°	48.5	48.0	47.5	47.0	46.5	45.5	44.0	42.5	41.0	39.5	37.5
95°	88.4	87.9	87.5	87.0	86.5	85.6	83.9	82.3	80.7	79.1	76.8
97.5°	134.0	133.7	133.5	133.2	132.9	132.0	130.5	129.0	127.5	126.0	122.9
100°	168.5	168.1	167.6	167.2	166.7	165.4	163.3	161.4	159.3	157.2	154.2
102.5°	203.0	202.4	201.8	201.1	200.5	199.1	196.8	194.6	192.3	190.1	188.6
105°	254.8	254.1	253.5	252.8	252.1	251.0	249.7	248.3	247.0	245.6	244.2
107.5°	307.8	307.9	307.9	308.0	308.1	307.8	307.0	306.3	305.7	305.0	304.0
110°	347.3	347.5	347.8	348.0	348.2	348.0	347.3	346.7	345.9	345.2	344.6



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	386.0	386.3	386.8	387.2	387.6	387.6	387.3	387.0	386.7	386.3	385.5
115°	447.0	447.3	447.4	447.7	447.9	448.1	448.4	448.6	448.9	449.1	448.6
117.5°	506.6	507.6	508.4	509.4	510.2	510.6	510.4	510.2	510.1	509.9	509.5
120°	547.7	548.6	549.5	550.4	551.4	551.8	551.8	551.8	551.8	551.8	551.6
122.5°	588.8	589.5	590.3	591.0	591.8	592.2	592.4	592.6	592.7	592.9	592.3
125°	650.5	650.7	650.9	651.2	651.4	651.7	652.2	652.6	653.1	653.6	653.3
127.5°	709.6	710.1	710.6	711.1	711.5	711.9	712.0	712.3	712.5	712.7	712.5
130°	749.1	749.6	750.0	750.5	750.9	751.3	751.5	751.7	751.9	752.2	751.7
132.5°	786.1	786.7	787.3	788.1	788.7	789.1	789.3	789.6	789.8	790.0	790.1
135°	843.7	844.5	845.5	846.4	847.3	847.8	847.8	847.8	847.8	847.8	847.6
137.5°	900.0	901.1	902.2	903.4	904.5	905.0	904.7	904.4	904.1	903.9	903.4
140°	936.1	937.3	938.4	939.5	940.7	941.0	940.6	940.2	939.7	939.2	938.5
142.5°	970.7	971.8	973.0	974.1	975.3	975.7	975.4	975.1	974.9	974.5	973.7
145°	1022.5	1023.1	1023.8	1024.5	1025.2	1025.6	1025.6	1025.6	1025.6	1025.6	1024.8
147.5°	1066.7	1068.2	1069.8	1071.3	1072.9	1073.3	1072.8	1072.2	1071.7	1071.2	1070.6
150°	1099.5	1099.9	1100.4	1100.9	1101.4	1101.6	1101.6	1101.6	1101.6	1101.6	1100.7
152.5°	1126.6	1127.4	1128.3	1129.1	1130.0	1130.0	1129.5	1128.9	1128.5	1127.9	1127.5
155°	1165.3	1166.4	1167.6	1168.7	1169.8	1170.0	1169.0	1168.2	1167.2	1166.3	1166.1
157.5°	1197.5	1199.0	1200.6	1202.1	1203.6	1203.9	1202.9	1202.1	1201.1	1200.2	1200.0
160°	1219.7	1220.9	1222.0	1223.2	1224.3	1224.4	1223.5	1222.6	1221.7	1220.8	1220.5
162.5°	1238.7	1240.0	1241.3	1242.6	1244.0	1244.0	1242.9	1241.9	1240.8	1239.7	1239.6
165°	1263.9	1265.3	1266.7	1268.0	1269.4	1269.6	1268.8	1267.8	1266.9	1266.0	1265.7
167.5°	1284.0	1285.5	1286.9	1288.3	1289.8	1289.8	1288.4	1287.1	1285.6	1284.3	1284.3
170°	1294.7	1296.3	1298.0	1299.6	1301.2	1301.2	1299.9	1298.5	1297.2	1295.8	1295.8
172.5°	1303.8	1305.2	1306.6	1308.1	1309.5	1309.5	1308.1	1306.8	1305.4	1304.0	1304.0
175°	1312.2	1313.8	1315.4	1317.0	1318.6	1318.7	1317.4	1316.0	1314.6	1313.3	1313.3
177.5°	1317.2	1318.4	1319.7	1321.0	1322.3	1322.4	1321.3	1320.2	1319.1	1318.0	1318.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	458.2	457.2	455.3	453.5	451.3	449.4	448.1	446.5	444.4	442.0	439.9
5°	478.5	474.4	469.1	464.5	458.7	454.2	449.4	444.8	440.2	434.4	429.2
7.5°	501.0	492.7	484.6	474.4	465.2	456.9	449.0	441.0	433.2	424.8	416.8
10°	514.8	504.6	493.5	480.7	469.0	457.8	447.6	437.4	426.8	417.6	407.5
12.5°	527.6	514.6	501.8	485.7	471.6	458.0	444.9	432.4	421.0	408.9	398.1
15°	539.2	526.4	512.1	492.4	472.8	456.3	440.9	424.7	410.6	397.0	384.9
17.5°	543.8	530.3	513.7	494.7	473.3	452.6	432.8	414.9	398.3	382.5	369.0
20°	542.0	529.0	512.0	493.8	471.0	449.4	427.9	408.2	389.7	373.0	358.6
22.5°	537.7	524.3	507.9	488.7	467.0	444.1	421.2	400.1	380.8	363.5	347.8
25°	531.4	513.1	496.2	477.5	456.9	434.2	410.6	387.3	366.6	349.0	331.8
27.5°	524.7	501.9	480.5	461.9	440.1	419.9	397.0	373.2	351.5	333.6	315.9
30°	518.7	493.1	469.5	448.5	427.8	408.5	387.0	363.7	341.4	322.9	305.0
32.5°	511.3	484.0	458.1	433.8	413.8	394.8	375.3	353.0	331.3	312.2	294.0
35°	501.9	467.1	438.9	413.1	391.0	372.5	354.9	337.0	315.2	295.4	277.7
37.5°	489.6	450.1	417.6	389.4	366.1	347.5	333.6	317.2	297.3	278.5	262.0
40°	482.1	437.8	402.2	374.3	349.8	330.2	317.2	303.3	285.2	267.4	251.0
42.5°	472.2	426.6	386.7	357.7	333.0	314.1	301.0	288.8	273.6	256.9	239.2
45°	452.7	404.7	362.8	331.7	306.8	288.3	276.0	265.2	253.7	238.3	222.9
47.5°	427.3	381.9	338.0	304.0	279.7	262.5	250.6	242.1	233.9	220.8	205.9
50°	406.9	363.1	320.4	287.4	261.4	245.1	233.9	227.2	219.7	207.8	195.3
52.5°	382.9	343.8	301.9	268.2	243.7	228.4	217.7	210.9	204.7	195.0	183.2
55°	345.1	310.8	272.4	241.8	219.3	203.9	193.7	187.3	183.6	175.4	166.0
57.5°	301.3	276.9	243.0	213.5	193.5	178.4	170.9	165.4	161.3	155.4	148.9
60°	270.9	253.7	223.3	195.3	177.0	162.6	155.7	151.2	147.3	142.4	137.3
62.5°	240.0	227.5	201.1	177.0	160.2	148.1	141.7	137.6	133.2	129.8	124.8
65°	198.6	187.4	169.1	150.3	134.8	125.0	120.4	116.8	114.1	110.4	106.9
67.5°	154.5	150.0	137.3	124.3	113.1	104.5	100.5	98.0	94.7	92.5	90.2
70°	127.4	125.2	116.2	107.7	97.2	91.3	87.7	86.6	82.5	80.3	78.7
72.5°	103.4	102.3	97.2	91.3	83.9	78.7	75.4	74.1	71.5	69.8	68.8
75°	70.8	71.2	70.3	66.5	63.7	60.4	57.5	56.7	54.9	53.5	52.5
77.5°	44.8	46.7	46.7	46.6	45.5	43.5	42.2	41.7	39.9	39.4	39.1
80°	30.7	32.8	34.6	34.4	34.1	33.5	32.6	32.0	31.1	30.6	30.2
82.5°	20.5	22.3	23.9	24.9	24.8	24.2	23.7	23.4	23.2	22.8	22.7
85°	9.7	10.1	10.6	11.9	12.8	13.0	12.8	12.6	12.1	12.3	12.4
87.5°	6.0	5.7	5.5	5.1	4.7	5.1	5.1	4.9	5.0	5.1	5.1
90°	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0	2.9	4.7	6.5
92.5°	35.6	33.6	31.6	29.9	28.7	27.4	26.1	24.9	26.1	27.4	28.7
95°	74.5	72.2	70.0	68.6	68.1	67.7	67.3	66.8	67.3	67.7	68.1
97.5°	119.7	116.5	113.4	111.7	111.5	111.4	111.1	111.0	111.1	111.4	111.5
100°	151.3	148.3	145.4	143.9	143.9	143.9	143.9	143.9	143.9	143.9	143.9
102.5°	187.1	185.6	184.1	182.8	182.0	181.0	180.1	179.2	180.1	181.0	182.0
105°	242.9	241.5	240.1	238.8	237.7	236.5	235.4	234.3	235.4	236.5	237.7
107.5°	302.9	301.8	300.8	299.7	298.6	297.4	296.3	295.1	296.3	297.4	298.6
110°	343.9	343.3	342.5	341.6	340.5	339.4	338.2	337.1	338.2	339.4	340.5





TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	384.6	383.7	382.9	382.1	381.6	381.0	380.4	379.8	380.4	381.0	381.6
115°	448.1	447.7	447.3	446.6	445.6	444.7	443.8	442.9	443.8	444.7	445.6
117.5°	509.1	508.7	508.3	507.9	507.4	507.0	506.6	506.2	506.6	507.0	507.4
120°	551.4	551.1	550.9	550.2	549.1	548.0	546.8	545.7	546.8	548.0	549.1
122.5°	591.8	591.1	590.6	590.0	589.6	589.2	588.8	588.4	588.8	589.2	589.6
125°	653.1	652.8	652.6	651.8	650.5	649.1	647.7	646.3	647.7	649.1	650.5
127.5°	712.2	711.9	711.6	711.1	710.3	709.6	708.8	708.0	708.8	709.6	710.3
130°	751.3	750.8	750.4	749.6	748.5	747.3	746.2	745.0	746.2	747.3	748.5
132.5°	790.2	790.3	790.4	789.5	787.6	785.8	783.9	782.0	783.9	785.8	787.6
135°	847.3	847.1	846.8	846.1	844.7	843.3	841.9	840.6	841.9	843.3	844.7
137.5°	902.9	902.4	901.8	900.9	899.6	898.3	897.0	895.6	897.0	898.3	899.6
140°	937.9	937.2	936.4	935.6	934.5	933.3	932.2	931.0	932.2	933.3	934.5
142.5°	972.8	971.9	971.1	970.2	969.2	968.3	967.3	966.4	967.3	968.3	969.2
145°	1024.1	1023.5	1022.8	1022.0	1021.0	1020.2	1019.2	1018.4	1019.2	1020.2	1021.0
147.5°	1070.1	1069.5	1069.0	1068.4	1067.9	1067.5	1066.9	1066.4	1066.9	1067.5	1067.9
150°	1099.8	1098.8	1097.9	1097.6	1097.8	1098.0	1098.3	1098.5	1098.3	1098.0	1097.8
152.5°	1127.1	1126.8	1126.4	1126.1	1125.8	1125.5	1125.1	1124.8	1125.1	1125.5	1125.8
155°	1165.9	1165.6	1165.4	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3	1165.3
157.5°	1199.8	1199.5	1199.3	1199.4	1199.9	1200.5	1200.9	1201.4	1200.9	1200.5	1199.9
160°	1220.4	1220.1	1219.9	1220.1	1220.8	1221.5	1222.2	1222.8	1222.2	1221.5	1220.8
162.5°	1239.6	1239.5	1239.5	1239.8	1240.2	1240.7	1241.3	1241.7	1241.3	1240.7	1240.2
165°	1265.5	1265.3	1265.1	1265.2	1265.7	1266.1	1266.5	1267.0	1266.5	1266.1	1265.7
167.5°	1284.3	1284.3	1284.3	1284.8	1285.6	1286.6	1287.5	1288.4	1287.5	1286.6	1285.6
170°	1295.8	1295.8	1295.8	1296.2	1297.2	1298.1	1299.0	1299.9	1299.0	1298.1	1297.2
172.5°	1304.0	1304.0	1304.0	1304.5	1305.4	1306.3	1307.2	1308.1	1307.2	1306.3	1305.4
175°	1313.3	1313.3	1313.3	1313.8	1314.6	1315.6	1316.4	1317.4	1316.4	1315.6	1314.6
177.5°	1318.3	1318.5	1318.7	1319.1	1319.9	1320.6	1321.4	1322.1	1321.4	1320.6	1319.9
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	438.4	436.4	434.9	432.0	429.9	429.0	427.5	427.0	428.6	427.5	427.3
5°	425.4	420.1	415.9	411.7	407.1	404.2	399.7	399.0	397.9	396.3	395.9
7.5°	409.8	402.8	397.4	390.5	384.4	379.5	374.1	371.5	370.0	367.9	365.0
10°	399.3	391.0	383.7	376.7	369.2	363.1	357.7	353.5	350.7	348.2	347.1
12.5°	388.8	380.4	371.1	362.7	354.3	347.5	341.4	338.7	335.6	332.6	330.1
15°	372.6	361.6	351.3	341.6	334.5	327.1	321.2	317.2	312.7	311.3	306.4
17.5°	355.5	344.6	332.6	322.4	314.1	306.0	299.6	295.0	291.6	286.8	284.6
20°	344.8	331.8	320.1	310.8	301.7	292.2	285.6	281.7	278.5	274.6	272.7
22.5°	333.4	320.8	308.7	297.8	288.5	279.1	274.4	270.5	266.7	263.2	260.7
25°	316.6	303.9	291.2	279.9	270.2	263.4	257.9	253.3	251.4	247.9	245.3
27.5°	300.1	286.5	273.4	262.1	254.4	247.7	243.2	239.6	236.0	233.0	230.7
30°	289.4	275.5	261.2	252.2	244.2	237.8	232.8	229.3	226.6	223.9	222.2
32.5°	278.7	264.4	251.7	242.0	234.4	228.9	223.8	220.4	217.5	214.5	212.5
35°	261.6	246.9	236.7	227.2	219.7	214.5	211.0	206.3	203.9	201.7	199.7
37.5°	245.7	232.0	220.9	212.6	206.0	201.0	196.5	193.9	191.0	189.0	187.4
40°	233.9	221.5	211.4	202.6	197.9	192.2	188.0	184.7	182.5	179.9	178.1
42.5°	223.4	211.8	202.0	194.2	188.2	183.4	179.4	176.0	173.3	171.4	169.9
45°	208.5	196.9	187.4	180.1	174.6	170.1	165.8	164.2	160.5	158.4	157.6
47.5°	193.1	182.8	173.6	166.8	161.2	156.9	152.9	149.6	147.5	145.4	144.2
50°	182.7	172.8	164.2	157.6	152.1	147.3	143.7	141.5	138.7	136.7	135.3
52.5°	172.3	163.1	154.6	148.2	143.5	138.7	134.6	132.5	129.8	128.6	127.5
55°	157.4	147.7	140.4	134.2	129.2	124.8	121.0	118.8	117.2	115.9	115.5
57.5°	140.6	132.9	126.1	120.5	115.3	111.2	107.8	105.8	104.3	104.1	103.0
60°	129.6	122.6	116.5	110.4	106.0	102.1	99.2	96.8	95.4	95.2	94.8
62.5°	118.6	111.9	106.2	100.8	96.9	93.2	90.4	87.8	86.9	86.0	85.2
65°	102.3	96.3	91.5	87.3	83.1	80.0	77.2	75.6	73.6	72.5	70.5
67.5°	86.3	81.7	77.1	73.5	70.2	67.3	65.0	62.5	61.2	60.3	58.9
70°	75.8	72.1	67.6	63.7	61.2	58.8	57.0	54.2	53.2	52.5	51.8
72.5°	65.8	62.6	58.8	55.6	53.1	50.9	48.7	47.5	46.5	45.8	45.4
75°	51.8	48.7	45.4	43.2	41.4	39.5	38.4	37.5	37.2	37.0	36.3
77.5°	38.0	36.4	33.7	32.0	30.8	30.0	29.1	28.6	28.5	27.7	27.5
80°	29.1	28.2	26.0	25.3	24.3	23.6	23.1	22.2	21.2	20.8	20.3
82.5°	21.6	20.8	19.8	18.7	17.9	17.4	17.0	16.6	16.7	16.2	15.9
85°	11.6	10.6	10.2	10.1	9.7	10.1	9.9	9.7	9.5	9.3	9.5
87.5°	5.3	5.7	5.9	6.4	6.3	6.8	7.1	7.1	7.4	7.6	7.6
90°	8.3	10.1	11.6	13.2	14.8	16.5	17.6	18.7	19.9	21.0	21.9
92.5°	29.9	31.6	33.6	35.6	37.5	39.5	41.0	42.5	44.0	45.5	46.5
95°	68.6	70.0	72.2	74.5	76.8	79.1	80.7	82.3	83.9	85.6	86.5
97.5°	111.7	113.4	116.5	119.7	122.9	126.0	127.5	129.0	130.5	132.0	132.9
100°	143.9	145.4	148.3	151.3	154.2	157.2	159.3	161.4	163.3	165.4	166.7
102.5°	182.8	184.1	185.6	187.1	188.6	190.1	192.3	194.6	196.8	199.1	200.5
105°	238.8	240.1	241.5	242.9	244.2	245.6	247.0	248.3	249.7	251.0	252.1
107.5°	299.7	300.8	301.8	302.9	304.0	305.0	305.7	306.3	307.0	307.8	308.1
110°	341.6	342.5	343.3	343.9	344.6	345.2	345.9	346.7	347.3	348.0	348.2



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	382.1	382.9	383.7	384.6	385.5	386.3	386.7	387.0	387.3	387.6	387.6
115°	446.6	447.3	447.7	448.1	448.6	449.1	448.9	448.6	448.4	448.1	447.9
117.5°	507.9	508.3	508.7	509.1	509.5	509.9	510.1	510.2	510.4	510.6	510.2
120°	550.2	550.9	551.1	551.4	551.6	551.8	551.8	551.8	551.8	551.8	551.4
122.5°	590.0	590.6	591.1	591.8	592.3	592.9	592.7	592.6	592.4	592.2	591.8
125°	651.8	652.6	652.8	653.1	653.3	653.6	653.1	652.6	652.2	651.7	651.4
127.5°	711.1	711.6	711.9	712.2	712.5	712.7	712.5	712.3	712.0	711.9	711.5
130°	749.6	750.4	750.8	751.3	751.7	752.2	751.9	751.7	751.5	751.3	750.9
132.5°	789.5	790.4	790.3	790.2	790.1	790.0	789.8	789.6	789.3	789.1	788.7
135°	846.1	846.8	847.1	847.3	847.6	847.8	847.8	847.8	847.8	847.8	847.3
137.5°	900.9	901.8	902.4	902.9	903.4	903.9	904.1	904.4	904.7	905.0	904.5
140°	935.6	936.4	937.2	937.9	938.5	939.2	939.7	940.2	940.6	941.0	940.7
142.5°	970.2	971.1	971.9	972.8	973.7	974.5	974.9	975.1	975.4	975.7	975.3
145°	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6	1025.6	1025.6	1025.6	1025.2
147.5°	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7	1072.2	1072.8	1073.3	1072.9
150°	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6	1101.6	1101.6	1101.6	1101.4
152.5°	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5	1128.9	1129.5	1130.0	1130.0
155°	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2	1168.2	1169.0	1170.0	1169.8
157.5°	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1	1202.1	1202.9	1203.9	1203.6
160°	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7	1222.6	1223.5	1224.4	1224.3
162.5°	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8	1241.9	1242.9	1244.0	1244.0
165°	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9	1267.8	1268.8	1269.6	1269.4
167.5°	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6	1287.1	1288.4	1289.8	1289.8
170°	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2	1298.5	1299.9	1301.2	1301.2
172.5°	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4	1306.8	1308.1	1309.5	1309.5
175°	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6	1316.0	1317.4	1318.7	1318.6
177.5°	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1	1320.2	1321.3	1322.4	1322.3
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.1	425.6	425.1	425.7	425.1	425.6	427.1	427.3	427.5	428.6	427.0
5°	394.1	392.3	393.2	392.8	393.2	392.3	394.1	395.9	396.3	397.9	399.0
7.5°	365.0	362.7	360.4	361.1	360.4	362.7	365.0	365.0	367.9	370.0	371.5
10°	344.7	342.9	341.7	342.7	341.7	342.9	344.7	347.1	348.2	350.7	353.5
12.5°	327.6	326.5	325.5	325.1	325.5	326.5	327.6	330.1	332.6	335.6	338.7
15°	304.2	302.1	301.1	298.7	301.1	302.1	304.2	306.4	311.3	312.7	317.2
17.5°	282.7	282.0	279.6	278.6	279.6	282.0	282.7	284.6	286.8	291.6	295.0
20°	270.0	269.3	266.9	268.3	266.9	269.3	270.0	272.7	274.6	278.5	281.7
22.5°	259.4	257.9	257.1	256.7	257.1	257.9	259.4	260.7	263.2	266.7	270.5
25°	244.5	242.2	241.2	240.2	241.2	242.2	244.5	245.3	247.9	251.4	253.3
27.5°	229.7	228.4	227.2	226.9	227.2	228.4	229.7	230.7	233.0	236.0	239.6
30°	220.0	218.7	217.9	217.9	217.9	218.7	220.0	222.2	223.9	226.6	229.3
32.5°	211.4	210.4	209.5	209.3	209.5	210.4	211.4	212.5	214.5	217.5	220.4
35°	198.8	197.3	196.9	195.8	196.9	197.3	198.8	199.7	201.7	203.9	206.3
37.5°	185.7	184.5	184.5	184.3	184.5	184.5	185.7	187.4	189.0	191.0	193.9
40°	177.4	176.4	176.3	175.0	176.3	176.4	177.4	178.1	179.9	182.5	184.7
42.5°	168.4	167.9	167.3	166.8	167.3	167.9	168.4	169.9	171.4	173.3	176.0
45°	156.3	155.0	155.0	154.2	155.0	155.0	156.3	157.6	158.4	160.5	164.2
47.5°	143.8	142.8	142.9	142.0	142.9	142.8	143.8	144.2	145.4	147.5	149.6
50°	135.5	134.9	134.8	134.4	134.8	134.9	135.5	135.3	136.7	138.7	141.5
52.5°	127.1	126.8	127.5	126.7	127.5	126.8	127.1	127.5	128.6	129.8	132.5
55°	115.9	115.3	116.5	115.3	116.5	115.3	115.9	115.5	115.9	117.2	118.8
57.5°	103.0	102.4	103.5	102.9	103.5	102.4	103.0	103.0	104.1	104.3	105.8
60°	94.4	93.3	93.9	94.1	93.9	93.3	94.4	94.8	95.2	95.4	96.8
62.5°	84.4	83.7	84.1	83.3	84.1	83.7	84.4	85.2	86.0	86.9	87.8
65°	70.1	69.6	68.8	68.4	68.8	69.6	70.1	70.5	72.5	73.6	75.6
67.5°	58.9	57.6	57.5	57.8	57.5	57.6	58.9	58.9	60.3	61.2	62.5
70°	50.7	50.7	50.5	50.5	50.5	50.7	50.7	51.8	52.5	53.2	54.2
72.5°	45.0	44.8	44.5	44.4	44.5	44.8	45.0	45.4	45.8	46.5	47.5
75°	36.3	36.4	36.0	35.9	36.0	36.4	36.3	36.3	37.0	37.2	37.5
77.5°	26.8	26.0	26.4	26.0	26.4	26.0	26.8	27.5	27.7	28.5	28.6
80°	20.3	20.1	20.7	20.1	20.7	20.1	20.3	20.3	20.8	21.2	22.2
82.5°	16.1	15.9	16.2	15.8	16.2	15.9	16.1	15.9	16.2	16.7	16.6
85°	9.7	9.5	9.3	9.5	9.3	9.5	9.7	9.5	9.3	9.5	9.7
87.5°	7.9	7.8	8.0	8.2	8.0	7.8	7.9	7.6	7.6	7.4	7.1
90°	22.6	23.3	24.0	24.6	24.0	23.3	22.6	21.9	21.0	19.9	18.7
92.5°	47.0	47.5	48.0	48.5	48.0	47.5	47.0	46.5	45.5	44.0	42.5
95°	87.0	87.5	87.9	88.4	87.9	87.5	87.0	86.5	85.6	83.9	82.3
97.5°	133.2	133.5	133.7	134.0	133.7	133.5	133.2	132.9	132.0	130.5	129.0
100°	167.2	167.6	168.1	168.5	168.1	167.6	167.2	166.7	165.4	163.3	161.4
102.5°	201.1	201.8	202.4	203.0	202.4	201.8	201.1	200.5	199.1	196.8	194.6
105°	252.8	253.5	254.1	254.8	254.1	253.5	252.8	252.1	251.0	249.7	248.3
107.5°	308.0	307.9	307.9	307.8	307.9	307.9	308.0	308.1	307.8	307.0	306.3
110°	348.0	347.8	347.5	347.3	347.5	347.8	348.0	348.2	348.0	347.3	346.7



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	387.2	386.8	386.3	386.0	386.3	386.8	387.2	387.6	387.6	387.3	387.0
115°	447.7	447.4	447.3	447.0	447.3	447.4	447.7	447.9	448.1	448.4	448.6
117.5°	509.4	508.4	507.6	506.6	507.6	508.4	509.4	510.2	510.6	510.4	510.2
120°	550.4	549.5	548.6	547.7	548.6	549.5	550.4	551.4	551.8	551.8	551.8
122.5°	591.0	590.3	589.5	588.8	589.5	590.3	591.0	591.8	592.2	592.4	592.6
125°	651.2	650.9	650.7	650.5	650.7	650.9	651.2	651.4	651.7	652.2	652.6
127.5°	711.1	710.6	710.1	709.6	710.1	710.6	711.1	711.5	711.9	712.0	712.3
130°	750.5	750.0	749.6	749.1	749.6	750.0	750.5	750.9	751.3	751.5	751.7
132.5°	788.1	787.3	786.7	786.1	786.7	787.3	788.1	788.7	789.1	789.3	789.6
135°	846.4	845.5	844.5	843.7	844.5	845.5	846.4	847.3	847.8	847.8	847.8
137.5°	903.4	902.2	901.1	900.0	901.1	902.2	903.4	904.5	905.0	904.7	904.4
140°	939.5	938.4	937.3	936.1	937.3	938.4	939.5	940.7	941.0	940.6	940.2
142.5°	974.1	973.0	971.8	970.7	971.8	973.0	974.1	975.3	975.7	975.4	975.1
145°	1024.5	1023.8	1023.1	1022.5	1023.1	1023.8	1024.5	1025.2	1025.6	1025.6	1025.6
147.5°	1071.3	1069.8	1068.2	1066.7	1068.2	1069.8	1071.3	1072.9	1073.3	1072.8	1072.2
150°	1100.9	1100.4	1099.9	1099.5	1099.9	1100.4	1100.9	1101.4	1101.6	1101.6	1101.6
152.5°	1129.1	1128.3	1127.4	1126.6	1127.4	1128.3	1129.1	1130.0	1130.0	1129.5	1128.9
155°	1168.7	1167.6	1166.4	1165.3	1166.4	1167.6	1168.7	1169.8	1170.0	1169.0	1168.2
157.5°	1202.1	1200.6	1199.0	1197.5	1199.0	1200.6	1202.1	1203.6	1203.9	1202.9	1202.1
160°	1223.2	1222.0	1220.9	1219.7	1220.9	1222.0	1223.2	1224.3	1224.4	1223.5	1222.6
162.5°	1242.6	1241.3	1240.0	1238.7	1240.0	1241.3	1242.6	1244.0	1244.0	1242.9	1241.9
165°	1268.0	1266.7	1265.3	1263.9	1265.3	1266.7	1268.0	1269.4	1269.6	1268.8	1267.8
167.5°	1288.3	1286.9	1285.5	1284.0	1285.5	1286.9	1288.3	1289.8	1289.8	1288.4	1287.1
170°	1299.6	1298.0	1296.3	1294.7	1296.3	1298.0	1299.6	1301.2	1301.2	1299.9	1298.5
172.5°	1308.1	1306.6	1305.2	1303.8	1305.2	1306.6	1308.1	1309.5	1309.5	1308.1	1306.8
175°	1317.0	1315.4	1313.8	1312.2	1313.8	1315.4	1317.0	1318.6	1318.7	1317.4	1316.0
177.5°	1321.0	1319.7	1318.4	1317.2	1318.4	1319.7	1321.0	1322.3	1322.4	1321.3	1320.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	427.5	429.0	429.9	432.0	434.9	436.4	438.4	439.9	442.0	444.4	446.5
5°	399.7	404.2	407.1	411.7	415.9	420.1	425.4	429.2	434.4	440.2	444.8
7.5°	374.1	379.5	384.4	390.5	397.4	402.8	409.8	416.8	424.8	433.2	441.0
10°	357.7	363.1	369.2	376.7	383.7	391.0	399.3	407.5	417.6	426.8	437.4
12.5°	341.4	347.5	354.3	362.7	371.1	380.4	388.8	398.1	408.9	421.0	432.4
15°	321.2	327.1	334.5	341.6	351.3	361.6	372.6	384.9	397.0	410.6	424.7
17.5°	299.6	306.0	314.1	322.4	332.6	344.6	355.5	369.0	382.5	398.3	414.9
20°	285.6	292.2	301.7	310.8	320.1	331.8	344.8	358.6	373.0	389.7	408.2
22.5°	274.4	279.1	288.5	297.8	308.7	320.8	333.4	347.8	363.5	380.8	400.1
25°	257.9	263.4	270.2	279.9	291.2	303.9	316.6	331.8	349.0	366.6	387.3
27.5°	243.2	247.7	254.4	262.1	273.4	286.5	300.1	315.9	333.6	351.5	373.2
30°	232.8	237.8	244.2	252.2	261.2	275.5	289.4	305.0	322.9	341.4	363.7
32.5°	223.8	228.9	234.4	242.0	251.7	264.4	278.7	294.0	312.2	331.3	353.0
35°	211.0	214.5	219.7	227.2	236.7	246.9	261.6	277.7	295.4	315.2	337.0
37.5°	196.5	201.0	206.0	212.6	220.9	232.0	245.7	262.0	278.5	297.3	317.2
40°	188.0	192.2	197.9	202.6	211.4	221.5	233.9	251.0	267.4	285.2	303.3
42.5°	179.4	183.4	188.2	194.2	202.0	211.8	223.4	239.2	256.9	273.6	288.8
45°	165.8	170.1	174.6	180.1	187.4	196.9	208.5	222.9	238.3	253.7	265.2
47.5°	152.9	156.9	161.2	166.8	173.6	182.8	193.1	205.9	220.8	233.9	242.1
50°	143.7	147.3	152.1	157.6	164.2	172.8	182.7	195.3	207.8	219.7	227.2
52.5°	134.6	138.7	143.5	148.2	154.6	163.1	172.3	183.2	195.0	204.7	210.9
55°	121.0	124.8	129.2	134.2	140.4	147.7	157.4	166.0	175.4	183.6	187.3
57.5°	107.8	111.2	115.3	120.5	126.1	132.9	140.6	148.9	155.4	161.3	165.4
60°	99.2	102.1	106.0	110.4	116.5	122.6	129.6	137.3	142.4	147.3	151.2
62.5°	90.4	93.2	96.9	100.8	106.2	111.9	118.6	124.8	129.8	133.2	137.6
65°	77.2	80.0	83.1	87.3	91.5	96.3	102.3	106.9	110.4	114.1	116.8
67.5°	65.0	67.3	70.2	73.5	77.1	81.7	86.3	90.2	92.5	94.7	98.0
70°	57.0	58.8	61.2	63.7	67.6	72.1	75.8	78.7	80.3	82.5	86.6
72.5°	48.7	50.9	53.1	55.6	58.8	62.6	65.8	68.8	69.8	71.5	74.1
75°	38.4	39.5	41.4	43.2	45.4	48.7	51.8	52.5	53.5	54.9	56.7
77.5°	29.1	30.0	30.8	32.0	33.7	36.4	38.0	39.1	39.4	39.9	41.7
80°	23.1	23.6	24.3	25.3	26.0	28.2	29.1	30.2	30.6	31.1	32.0
82.5°	17.0	17.4	17.9	18.7	19.8	20.8	21.6	22.7	22.8	23.2	23.4
85°	9.9	10.1	9.7	10.1	10.2	10.6	11.6	12.4	12.3	12.1	12.6
87.5°	7.1	6.8	6.3	6.4	5.9	5.7	5.3	5.1	5.1	5.0	4.9
90°	17.6	16.5	14.8	13.2	11.6	10.1	8.3	6.5	4.7	2.9	1.0
92.5°	41.0	39.5	37.5	35.6	33.6	31.6	29.9	28.7	27.4	26.1	24.9
95°	80.7	79.1	76.8	74.5	72.2	70.0	68.6	68.1	67.7	67.3	66.8
97.5°	127.5	126.0	122.9	119.7	116.5	113.4	111.7	111.5	111.4	111.1	111.0
100°	159.3	157.2	154.2	151.3	148.3	145.4	143.9	143.9	143.9	143.9	143.9
102.5°	192.3	190.1	188.6	187.1	185.6	184.1	182.8	182.0	181.0	180.1	179.2
105°	247.0	245.6	244.2	242.9	241.5	240.1	238.8	237.7	236.5	235.4	234.3
107.5°	305.7	305.0	304.0	302.9	301.8	300.8	299.7	298.6	297.4	296.3	295.1
110°	345.9	345.2	344.6	343.9	343.3	342.5	341.6	340.5	339.4	338.2	337.1



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	386.7	386.3	385.5	384.6	383.7	382.9	382.1	381.6	381.0	380.4	379.8
115°	448.9	449.1	448.6	448.1	447.7	447.3	446.6	445.6	444.7	443.8	442.9
117.5°	510.1	509.9	509.5	509.1	508.7	508.3	507.9	507.4	507.0	506.6	506.2
120°	551.8	551.8	551.6	551.4	551.1	550.9	550.2	549.1	548.0	546.8	545.7
122.5°	592.7	592.9	592.3	591.8	591.1	590.6	590.0	589.6	589.2	588.8	588.4
125°	653.1	653.6	653.3	653.1	652.8	652.6	651.8	650.5	649.1	647.7	646.3
127.5°	712.5	712.7	712.5	712.2	711.9	711.6	711.1	710.3	709.6	708.8	708.0
130°	751.9	752.2	751.7	751.3	750.8	750.4	749.6	748.5	747.3	746.2	745.0
132.5°	789.8	790.0	790.1	790.2	790.3	790.4	789.5	787.6	785.8	783.9	782.0
135°	847.8	847.8	847.6	847.3	847.1	846.8	846.1	844.7	843.3	841.9	840.6
137.5°	904.1	903.9	903.4	902.9	902.4	901.8	900.9	899.6	898.3	897.0	895.6
140°	939.7	939.2	938.5	937.9	937.2	936.4	935.6	934.5	933.3	932.2	931.0
142.5°	974.9	974.5	973.7	972.8	971.9	971.1	970.2	969.2	968.3	967.3	966.4
145°	1025.6	1025.6	1024.8	1024.1	1023.5	1022.8	1022.0	1021.0	1020.2	1019.2	1018.4
147.5°	1071.7	1071.2	1070.6	1070.1	1069.5	1069.0	1068.4	1067.9	1067.5	1066.9	1066.4
150°	1101.6	1101.6	1100.7	1099.8	1098.8	1097.9	1097.6	1097.8	1098.0	1098.3	1098.5
152.5°	1128.5	1127.9	1127.5	1127.1	1126.8	1126.4	1126.1	1125.8	1125.5	1125.1	1124.8
155°	1167.2	1166.3	1166.1	1165.9	1165.6	1165.4	1165.3	1165.3	1165.3	1165.3	1165.3
157.5°	1201.1	1200.2	1200.0	1199.8	1199.5	1199.3	1199.4	1199.9	1200.5	1200.9	1201.4
160°	1221.7	1220.8	1220.5	1220.4	1220.1	1219.9	1220.1	1220.8	1221.5	1222.2	1222.8
162.5°	1240.8	1239.7	1239.6	1239.6	1239.5	1239.5	1239.8	1240.2	1240.7	1241.3	1241.7
165°	1266.9	1266.0	1265.7	1265.5	1265.3	1265.1	1265.2	1265.7	1266.1	1266.5	1267.0
167.5°	1285.6	1284.3	1284.3	1284.3	1284.3	1284.3	1284.8	1285.6	1286.6	1287.5	1288.4
170°	1297.2	1295.8	1295.8	1295.8	1295.8	1295.8	1296.2	1297.2	1298.1	1299.0	1299.9
172.5°	1305.4	1304.0	1304.0	1304.0	1304.0	1304.0	1304.5	1305.4	1306.3	1307.2	1308.1
175°	1314.6	1313.3	1313.3	1313.3	1313.3	1313.3	1313.8	1314.6	1315.6	1316.4	1317.4
177.5°	1319.1	1318.0	1318.2	1318.3	1318.5	1318.7	1319.1	1319.9	1320.6	1321.4	1322.1
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	448.1	449.4	451.3	453.5	455.3	457.2	458.2	458.2	459.1	461.0	463.5
5°	449.4	454.2	458.7	464.5	469.1	474.4	478.5	482.4	485.8	490.2	494.8
7.5°	449.0	456.9	465.2	474.4	484.6	492.7	501.0	507.5	513.9	522.4	528.9
10°	447.6	457.8	469.0	480.7	493.5	504.6	514.8	523.9	532.7	541.9	550.1
12.5°	444.9	458.0	471.6	485.7	501.8	514.6	527.6	537.3	547.6	557.6	567.8
15°	440.9	456.3	472.8	492.4	512.1	526.4	539.2	551.9	561.4	572.7	582.5
17.5°	432.8	452.6	473.3	494.7	513.7	530.3	543.8	555.8	565.9	578.4	591.6
20°	427.9	449.4	471.0	493.8	512.0	529.0	542.0	554.4	567.0	583.4	599.4
22.5°	421.2	444.1	467.0	488.7	507.9	524.3	537.7	552.9	569.6	588.0	607.5
25°	410.6	434.2	456.9	477.5	496.2	513.1	531.4	551.9	572.0	596.4	624.4
27.5°	397.0	419.9	440.1	461.9	480.5	501.9	524.7	547.0	576.0	609.5	644.4
30°	387.0	408.5	427.8	448.5	469.5	493.1	518.7	544.9	579.6	618.9	660.4
32.5°	375.3	394.8	413.8	433.8	458.1	484.0	511.3	543.3	584.6	629.4	672.4
35°	354.9	372.5	391.0	413.1	438.9	467.1	501.9	540.9	590.9	639.0	677.6
37.5°	333.6	347.5	366.1	389.4	417.6	450.1	489.6	537.0	588.3	631.5	647.9
40°	317.2	330.2	349.8	374.3	402.2	437.8	482.1	530.8	582.5	612.4	611.2
42.5°	301.0	314.1	333.0	357.7	386.7	426.6	472.2	522.8	566.3	577.7	554.0
45°	276.0	288.3	306.8	331.7	362.8	404.7	452.7	501.2	529.0	510.5	463.3
47.5°	250.6	262.5	279.7	304.0	338.0	381.9	427.3	467.1	471.0	431.3	374.6
50°	233.9	245.1	261.4	287.4	320.4	363.1	406.9	438.2	428.5	380.0	321.6
52.5°	217.7	228.4	243.7	268.2	301.9	343.8	382.9	407.5	385.0	333.4	280.9
55°	193.7	203.9	219.3	241.8	272.4	310.8	345.1	354.0	321.1	269.1	226.6
57.5°	170.9	178.4	193.5	213.5	243.0	276.9	301.3	299.8	263.4	216.6	186.1
60°	155.7	162.6	177.0	195.3	223.3	253.7	270.9	263.6	226.8	188.1	158.9
62.5°	141.7	148.1	160.2	177.0	201.1	227.5	240.0	229.9	195.2	161.2	137.9
65°	120.4	125.0	134.8	150.3	169.1	187.4	198.6	183.8	153.0	127.4	109.8
67.5°	100.5	104.5	113.1	124.3	137.3	150.0	154.5	140.6	116.7	99.4	87.0
70°	87.7	91.3	97.2	107.7	116.2	125.2	127.4	114.9	95.0	81.8	74.1
72.5°	75.4	78.7	83.9	91.3	97.2	102.3	103.4	91.8	76.5	67.5	61.6
75°	57.5	60.4	63.7	66.5	70.3	71.2	70.8	61.9	53.6	47.6	44.3
77.5°	42.2	43.5	45.5	46.6	46.7	46.7	44.8	39.1	34.9	32.4	31.1
80°	32.6	33.5	34.1	34.4	34.6	32.8	30.7	27.3	25.8	24.3	22.7
82.5°	23.7	24.2	24.8	24.9	23.9	22.3	20.5	18.8	17.7	17.0	16.4
85°	12.8	13.0	12.8	11.9	10.6	10.1	9.7	9.3	9.2	9.0	9.0
87.5°	5.1	5.1	4.7	5.1	5.5	5.7	6.0	6.2	6.3	6.6	6.8
90°	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.5	17.6	18.7
92.5°	26.1	27.4	28.7	29.9	31.6	33.6	35.6	37.5	39.5	41.0	42.5
95°	67.3	67.7	68.1	68.6	70.0	72.2	74.5	76.8	79.1	80.7	82.3
97.5°	111.1	111.4	111.5	111.7	113.4	116.5	119.7	122.9	126.0	127.5	129.0
100°	143.9	143.9	143.9	143.9	145.4	148.3	151.3	154.2	157.2	159.3	161.4
102.5°	180.1	181.0	182.0	182.8	184.1	185.6	187.1	188.6	190.1	192.3	194.6
105°	235.4	236.5	237.7	238.8	240.1	241.5	242.9	244.2	245.6	247.0	248.3
107.5°	296.3	297.4	298.6	299.7	300.8	301.8	302.9	304.0	305.0	305.7	306.3
110°	338.2	339.4	340.5	341.6	342.5	343.3	343.9	344.6	345.2	345.9	346.7





TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	380.4	381.0	381.6	382.1	382.9	383.7	384.6	385.5	386.3	386.7	387.0
115°	443.8	444.7	445.6	446.6	447.3	447.7	448.1	448.6	449.1	448.9	448.6
117.5°	506.6	507.0	507.4	507.9	508.3	508.7	509.1	509.5	509.9	510.1	510.2
120°	546.8	548.0	549.1	550.2	550.9	551.1	551.4	551.6	551.8	551.8	551.8
122.5°	588.8	589.2	589.6	590.0	590.6	591.1	591.8	592.3	592.9	592.7	592.6
125°	647.7	649.1	650.5	651.8	652.6	652.8	653.1	653.3	653.6	653.1	652.6
127.5°	708.8	709.6	710.3	711.1	711.6	711.9	712.2	712.5	712.7	712.5	712.3
130°	746.2	747.3	748.5	749.6	750.4	750.8	751.3	751.7	752.2	751.9	751.7
132.5°	783.9	785.8	787.6	789.5	790.4	790.3	790.2	790.1	790.0	789.8	789.6
135°	841.9	843.3	844.7	846.1	846.8	847.1	847.3	847.6	847.8	847.8	847.8
137.5°	897.0	898.3	899.6	900.9	901.8	902.4	902.9	903.4	903.9	904.1	904.4
140°	932.2	933.3	934.5	935.6	936.4	937.2	937.9	938.5	939.2	939.7	940.2
142.5°	967.3	968.3	969.2	970.2	971.1	971.9	972.8	973.7	974.5	974.9	975.1
145°	1019.2	1020.2	1021.0	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6	1025.6
147.5°	1066.9	1067.5	1067.9	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7	1072.2
150°	1098.3	1098.0	1097.8	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6	1101.6
152.5°	1125.1	1125.5	1125.8	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5	1128.9
155°	1165.3	1165.3	1165.3	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2	1168.2
157.5°	1200.9	1200.5	1199.9	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1	1202.1
160°	1222.2	1221.5	1220.8	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7	1222.6
162.5°	1241.3	1240.7	1240.2	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8	1241.9
165°	1266.5	1266.1	1265.7	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9	1267.8
167.5°	1287.5	1286.6	1285.6	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6	1287.1
170°	1299.0	1298.1	1297.2	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2	1298.5
172.5°	1307.2	1306.3	1305.4	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4	1306.8
175°	1316.4	1315.6	1314.6	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6	1316.0
177.5°	1321.4	1320.6	1319.9	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1	1320.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	445.9	445.9	445.9	445.9	445.9	445.9	445.9
2.5°	465.4	465.4	467.9	467.7	469.4	468.7	469.1
5°	500.3	503.4	506.1	507.9	510.7	511.4	511.0
7.5°	536.5	543.4	546.7	551.4	552.2	554.6	554.4
10°	558.8	565.6	570.8	574.7	576.8	579.3	579.6
12.5°	576.4	582.2	586.7	590.4	592.9	593.7	594.1
15°	590.2	596.5	601.8	607.1	610.3	612.7	613.9
17.5°	604.0	613.9	623.2	630.4	634.8	638.4	638.4
20°	614.7	626.0	637.7	645.9	654.4	658.1	658.6
22.5°	626.1	643.4	658.5	671.3	682.4	686.2	687.6
25°	649.8	672.5	695.8	713.7	726.5	734.0	735.1
27.5°	678.5	709.2	733.6	750.2	760.8	766.4	767.6
30°	698.7	727.1	749.0	761.4	766.4	767.1	764.4
32.5°	707.7	729.0	737.8	737.0	727.3	720.9	718.4
35°	696.6	692.3	670.9	645.2	625.7	613.2	609.9
37.5°	634.0	596.1	556.7	518.0	497.4	486.9	468.9
40°	572.2	518.2	477.2	444.7	421.4	402.7	398.3
42.5°	502.5	446.7	405.8	377.9	359.3	346.5	340.9
45°	403.8	355.8	321.9	300.6	286.3	276.9	272.7
47.5°	323.0	285.8	261.2	245.3	234.4	226.3	224.0
50°	278.6	248.9	228.1	214.7	206.4	200.3	197.7
52.5°	242.0	218.0	202.0	191.0	183.2	179.4	177.2
55°	199.7	179.0	167.5	158.7	154.3	151.2	149.7
57.5°	163.3	148.4	140.0	133.9	129.8	127.9	127.1
60°	143.0	131.3	123.6	118.8	116.1	113.5	112.7
62.5°	124.9	115.7	109.8	105.6	102.9	101.8	101.3
65°	100.7	94.7	90.2	87.7	85.5	85.1	84.9
67.5°	80.0	76.4	74.1	71.5	70.7	69.5	69.2
70°	68.4	66.1	63.3	62.4	61.5	60.2	60.4
72.5°	58.1	55.7	53.8	52.6	52.3	51.7	52.2
75°	42.5	41.7	41.0	40.1	39.7	39.7	39.5
77.5°	30.3	29.7	28.9	28.4	28.2	27.5	27.7
80°	21.9	21.1	20.7	20.8	20.3	20.1	20.1
82.5°	16.2	15.9	15.5	15.6	15.4	15.3	15.4
85°	9.0	8.8	8.8	8.6	8.6	8.4	8.4
87.5°	7.2	7.6	7.4	7.4	7.6	7.8	8.2
90°	19.9	21.0	21.9	22.6	23.3	24.0	24.6
92.5°	44.0	45.5	46.5	47.0	47.5	48.0	48.5
95°	83.9	85.6	86.5	87.0	87.5	87.9	88.4
97.5°	130.5	132.0	132.9	133.2	133.5	133.7	134.0
100°	163.3	165.4	166.7	167.2	167.6	168.1	168.5
102.5°	196.8	199.1	200.5	201.1	201.8	202.4	203.0
105°	249.7	251.0	252.1	252.8	253.5	254.1	254.8
107.5°	307.0	307.8	308.1	308.0	307.9	307.9	307.8
110°	347.3	348.0	348.2	348.0	347.8	347.5	347.3



TEST NUMBER: P333653-927

CATALOG NUMBER: S125RDIW-S375D1340U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.3	387.6	387.6	387.2	386.8	386.3	386.0
115°	448.4	448.1	447.9	447.7	447.4	447.3	447.0
117.5°	510.4	510.6	510.2	509.4	508.4	507.6	506.6
120°	551.8	551.8	551.4	550.4	549.5	548.6	547.7
122.5°	592.4	592.2	591.8	591.0	590.3	589.5	588.8
125°	652.2	651.7	651.4	651.2	650.9	650.7	650.5
127.5°	712.0	711.9	711.5	711.1	710.6	710.1	709.6
130°	751.5	751.3	750.9	750.5	750.0	749.6	749.1
132.5°	789.3	789.1	788.7	788.1	787.3	786.7	786.1
135°	847.8	847.8	847.3	846.4	845.5	844.5	843.7
137.5°	904.7	905.0	904.5	903.4	902.2	901.1	900.0
140°	940.6	941.0	940.7	939.5	938.4	937.3	936.1
142.5°	975.4	975.7	975.3	974.1	973.0	971.8	970.7
145°	1025.6	1025.6	1025.2	1024.5	1023.8	1023.1	1022.5
147.5°	1072.8	1073.3	1072.9	1071.3	1069.8	1068.2	1066.7
150°	1101.6	1101.6	1101.4	1100.9	1100.4	1099.9	1099.5
152.5°	1129.5	1130.0	1130.0	1129.1	1128.3	1127.4	1126.6
155°	1169.0	1170.0	1169.8	1168.7	1167.6	1166.4	1165.3
157.5°	1202.9	1203.9	1203.6	1202.1	1200.6	1199.0	1197.5
160°	1223.5	1224.4	1224.3	1223.2	1222.0	1220.9	1219.7
162.5°	1242.9	1244.0	1244.0	1242.6	1241.3	1240.0	1238.7
165°	1268.8	1269.6	1269.4	1268.0	1266.7	1265.3	1263.9
167.5°	1288.4	1289.8	1289.8	1288.3	1286.9	1285.5	1284.0
170°	1299.9	1301.2	1301.2	1299.6	1298.0	1296.3	1294.7
172.5°	1308.1	1309.5	1309.5	1308.1	1306.6	1305.2	1303.8
175°	1317.4	1318.7	1318.6	1317.0	1315.4	1313.8	1312.2
177.5°	1321.3	1322.4	1322.3	1321.0	1319.7	1318.4	1317.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)