

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333411

Luminaire Tested: **S125DIW-S850D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333411  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125DIW-S850D770U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 850 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6079.9 lumens  
Efficiency: N/A  
Efficacy: 135.1 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.31  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 45  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	55	53	52	47
2	90	83	76	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	40	37	33
4	75	64	56	50	70	60	53	47	52	47	42	45	41	37	38	35	32	29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	25	22
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	8478	8478	8478
5°	8497	8416	8470
10°	8445	8357	8405
15°	8354	8256	8291
20°	8223	8115	8130
25°	8082	7948	7941
30°	7908	7768	7730
35°	7722	7574	7468
40°	7530	7363	7259
45°	7323	7172	7029
50°	7095	6939	6731
55°	6876	6677	6490
60°	6613	6412	6185
65°	6301	6094	5888
70°	6001	5727	5531
75°	5467	5288	5105
80°	4868	4790	4675
85°	4231	4313	4076



TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.8	2.0
10°-20°	349.6	5.8
20°-30°	516.2	8.5
30°-40°	602.4	9.9
40°-50°	605.0	10.0
50°-60°	531.1	8.7
60°-70°	395.7	6.5
70°-80°	226.3	3.7
80°-90°	67.9	1.1
90°-100°	63.9	1.1
100°-110°	188.7	3.1
110°-120°	319.6	5.3
120°-130°	420.6	6.9
130°-140°	471.2	7.8
140°-150°	461.9	7.6
150°-160°	387.9	6.4
160°-170°	257.9	4.2
170°-180°	90.2	1.5
0°-30°	989.7	16.3
0°-40°	1592.1	26.2
0°-60°	2728.2	44.9
0°-90°	3418.1	56.2
90°-120°	572.1	9.4
90°-150°	1925.8	31.7
90°-180°	2662.0	43.8
0°-180°	6079.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1313	1313	1313	1313	1313	
5°	1311	1308	1298	1307	1306	124
15°	1249	1246	1235	1240	1240	352
25°	1134	1128	1115	1117	1114	522
35°	979	975	961	955	947	612
45°	802	797	785	773	770	618
55°	611	607	593	584	576	545
65°	412	410	399	390	385	409
75°	219	217	212	209	205	234
85°	57	58	58	57	55	64
90°	1	7	12	16	18	6
95°	48	50	57	62	64	52
105°	169	173	177	182	184	181
115°	320	323	324	324	323	316
125°	467	471	472	471	470	418
135°	607	612	612	612	610	468
145°	736	739	741	741	739	460
155°	842	842	843	845	842	388
165°	915	914	915	917	913	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1316.1	1315.5	1315.0	1314.4	1313.8	1312.6	1310.8	1309.0	1307.1	1305.3	1307.1
5°	1310.7	1310.2	1309.7	1309.3	1308.8	1307.4	1305.1	1302.8	1300.5	1298.2	1300.3
7.5°	1298.6	1298.2	1297.7	1297.2	1296.8	1295.3	1292.7	1290.2	1287.7	1285.1	1287.1
10°	1287.8	1287.4	1286.9	1286.4	1286.0	1284.5	1281.9	1279.4	1276.9	1274.3	1276.2
12.5°	1274.5	1273.7	1272.9	1272.0	1271.2	1269.6	1267.3	1264.9	1262.5	1260.2	1261.7
15°	1249.4	1248.7	1248.0	1247.3	1246.6	1245.0	1242.5	1239.9	1237.4	1234.8	1236.0
17.5°	1220.5	1219.5	1218.5	1217.5	1216.5	1214.6	1212.0	1209.4	1206.7	1204.1	1205.5
20°	1196.4	1196.0	1195.5	1195.0	1194.6	1192.8	1189.8	1186.8	1183.8	1180.8	1182.5
22.5°	1172.3	1171.5	1170.7	1169.8	1169.0	1167.2	1164.4	1161.5	1158.7	1155.9	1157.0
25°	1134.1	1133.0	1131.8	1130.6	1129.5	1127.4	1124.4	1121.4	1118.4	1115.4	1115.9
27.5°	1089.4	1088.8	1088.1	1087.4	1086.7	1084.8	1081.7	1078.6	1075.5	1072.4	1072.5
30°	1060.4	1059.7	1059.0	1058.3	1057.6	1055.5	1052.1	1048.6	1045.1	1041.7	1041.2
32.5°	1028.8	1027.7	1026.7	1025.6	1024.6	1022.5	1019.4	1016.3	1013.2	1010.1	1009.3
35°	979.4	978.4	977.5	976.6	975.7	973.6	970.4	967.1	963.9	960.7	959.5
37.5°	928.1	926.9	925.7	924.6	923.4	921.3	918.3	915.2	912.2	909.2	907.4
40°	893.2	892.0	890.9	889.7	888.5	886.4	883.1	879.9	876.7	873.4	871.4
42.5°	855.8	854.8	853.8	852.9	851.9	849.8	846.6	843.3	840.1	836.9	835.0
45°	801.8	800.8	799.9	799.0	798.1	796.2	793.5	790.7	787.9	785.2	782.4
47.5°	743.6	743.7	743.7	743.7	743.8	742.2	738.8	735.5	732.2	728.9	726.0
50°	706.2	705.5	704.8	704.1	703.5	701.7	699.0	696.2	693.4	690.6	687.6
52.5°	668.0	667.5	667.0	666.5	666.0	664.2	661.3	658.3	655.4	652.4	649.8
55°	610.7	610.0	609.3	608.6	607.9	605.9	602.7	599.5	596.2	593.0	590.9
57.5°	550.2	549.9	549.5	549.1	548.8	547.2	544.5	541.8	539.0	536.3	533.6
60°	512.0	511.1	510.2	509.2	508.3	506.6	504.0	501.5	499.0	496.4	494.1
62.5°	472.1	471.4	470.7	469.9	469.2	467.7	465.6	463.4	461.2	459.0	456.6
65°	412.3	411.8	411.4	410.9	410.5	409.0	406.4	403.9	401.3	398.8	396.7
67.5°	354.4	353.4	352.4	351.4	350.5	349.0	347.2	345.3	343.4	341.5	339.7
70°	317.8	316.6	315.5	314.3	313.2	311.6	309.5	307.4	305.3	303.3	301.9
72.5°	277.9	277.1	276.3	275.6	274.8	273.7	272.4	271.0	269.7	268.4	266.8
75°	219.1	218.7	218.2	217.8	217.3	216.5	215.3	214.2	213.0	211.9	211.2
77.5°	164.9	164.7	164.6	164.4	164.2	163.8	163.1	162.5	161.8	161.2	160.8
80°	130.9	130.9	130.9	130.9	130.9	130.6	130.2	129.7	129.2	128.8	128.6
82.5°	100.9	100.6	100.2	99.8	99.5	99.2	99.1	99.1	99.0	98.9	98.5
85°	57.1	57.4	57.6	57.8	58.0	58.2	58.2	58.2	58.2	58.2	57.9
87.5°	22.6	22.8	23.1	23.4	23.6	23.8	23.8	23.9	23.9	24.0	24.1
90°	0.7	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7
92.5°	18.0	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6
95°	48.3	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3
97.5°	80.2	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1
100°	103.9	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1
102.5°	129.5	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0
105°	169.3	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4
107.5°	213.2	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8
110°	243.5	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9



TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.4	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4
115°	320.0	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2
117.5°	365.7	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5
120°	394.2	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6
122.5°	425.1	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2
125°	466.9	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8
127.5°	511.5	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7
130°	538.2	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2
132.5°	564.9	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6
135°	607.2	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4
137.5°	647.0	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2
140°	672.6	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8
142.5°	698.1	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2
145°	735.7	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9
147.5°	770.4	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2
150°	793.6	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8
152.5°	812.6	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2
155°	841.8	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2
157.5°	868.0	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7
160°	883.4	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6
162.5°	897.1	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4
165°	915.3	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2
167.5°	930.8	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8
170°	939.1	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1
172.5°	945.0	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0
175°	951.7	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7
177.5°	955.1	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7	1312.7
2.5°	1309.0	1310.8	1312.6	1313.5	1313.3	1313.1	1312.9	1312.7
5°	1302.4	1304.4	1306.5	1307.4	1307.2	1307.0	1306.7	1306.5
7.5°	1289.2	1291.2	1293.2	1294.1	1293.9	1293.7	1293.4	1293.2
10°	1278.0	1279.9	1281.7	1282.5	1282.3	1282.0	1281.8	1281.6
12.5°	1263.1	1264.6	1266.1	1266.8	1266.8	1266.7	1266.7	1266.6
15°	1237.2	1238.3	1239.5	1240.0	1240.0	1240.0	1240.0	1240.0
17.5°	1207.0	1208.4	1209.8	1210.0	1208.8	1207.7	1206.5	1205.4
20°	1184.1	1185.7	1187.3	1187.5	1186.4	1185.2	1184.1	1182.9
22.5°	1158.0	1159.1	1160.2	1160.3	1159.5	1158.7	1157.9	1157.2
25°	1116.3	1116.8	1117.3	1117.1	1116.5	1115.8	1115.1	1114.4
27.5°	1072.6	1072.7	1072.8	1072.5	1071.8	1071.1	1070.4	1069.7
30°	1040.8	1040.3	1039.8	1039.3	1038.6	1037.9	1037.2	1036.5
32.5°	1008.4	1007.6	1006.8	1005.7	1004.5	1003.2	1002.0	1000.8
35°	958.4	957.2	956.1	954.6	952.7	950.9	949.0	947.2
37.5°	905.7	904.0	902.3	900.9	899.9	898.8	897.8	896.7
40°	869.3	867.2	865.1	863.7	863.0	862.4	861.7	861.0
42.5°	833.1	831.2	829.3	827.8	826.8	825.7	824.6	823.6
45°	779.6	776.8	774.1	772.3	771.7	771.0	770.3	769.6
47.5°	723.2	720.4	717.6	715.4	713.8	712.2	710.5	708.9
50°	684.6	681.6	678.6	676.3	674.7	673.1	671.5	669.9
52.5°	647.2	644.5	641.9	639.7	637.9	636.1	634.3	632.5
55°	588.9	586.8	584.7	582.9	581.2	579.6	578.0	576.4
57.5°	531.0	528.3	525.6	523.8	522.9	522.1	521.2	520.3
60°	491.8	489.5	487.2	485.2	483.6	482.0	480.4	478.8
62.5°	454.1	451.6	449.1	447.2	446.0	444.7	443.5	442.2
65°	394.7	392.6	390.5	389.0	388.1	387.2	386.2	385.3
67.5°	338.0	336.2	334.5	333.3	332.8	332.2	331.6	331.1
70°	300.5	299.1	297.7	296.6	295.6	294.7	293.8	292.9
72.5°	265.2	263.7	262.1	260.8	259.9	259.0	258.1	257.1
75°	210.5	209.8	209.1	208.3	207.4	206.4	205.5	204.6
77.5°	160.4	159.9	159.5	159.0	158.3	157.7	157.1	156.4
80°	128.3	128.1	127.9	127.5	127.1	126.6	126.1	125.7
82.5°	98.0	97.6	97.2	97.0	96.9	96.8	96.7	96.6
85°	57.7	57.5	57.2	56.9	56.4	56.0	55.5	55.0
87.5°	24.3	24.5	24.6	24.6	24.3	24.0	23.8	23.5
90°	13.5	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	30.7	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	59.5	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	93.2	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	116.5	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	140.6	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	179.4	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.3	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.4	250.9	251.4	251.6	251.4	251.2	251.1	250.9





TEST NUMBER: P333411

CATALOG NUMBER: S125DIW-S850D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.6	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	324.1	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.6	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	428.1	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.5	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.6	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	543.1	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.4	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.4	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.2	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.4	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	774.6	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	815.6	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	843.9	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	868.4	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.2	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.2	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	915.9	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	929.8	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	938.1	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	944.0	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	950.7	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	953.7	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)