

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333658-927

Luminaire Tested: **S125RDIW-S375D1560U927-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333658-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S375D1560U927-4F0-1E-UDD-F  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 375 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1560 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6088.6 lumens  
Efficiency: N/A  
Efficacy: 114.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19				
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	75	67	60	54	66	59	53	49	45	41	38	31	29	27	19	18	17	12				
4	69	59	51	46	61	52	46	41	40	35	32	28	25	23	17	16	15	10				
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	14	13	9				
6	58	47	39	34	51	41	35	30	32	27	24	23	20	17	14	12	11	8				
7	54	42	34	29	47	37	31	26	29	24	21	20	17	15	13	11	10	7				
8	49	38	31	26	44	34	27	23	26	21	18	19	16	14	12	10	9	6				
9	46	34	27	23	40	31	25	20	24	19	16	17	14	12	11	9	8	6				
10	43	31	25	20	38	28	22	18	22	17	14	16	13	11	10	8	7	5				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3130	3130	3130
5°	3138	3102	3121
10°	3114	3074	3074
15°	3077	3011	2986
20°	3030	2924	2889
25°	2974	2838	2776
30°	2905	2738	2651
35°	2834	2636	2511
40°	2769	2528	2373
45°	2689	2408	2223
50°	2608	2277	2067
55°	2514	2152	1901
60°	2421	2001	1721
65°	2311	1825	1516
70°	2185	1603	1307
75°	2011	1352	1088
80°	1770	1060	915
85°	1489	867	815



TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.6	0.7
10°-20°	127.4	2.1
20°-30°	184.7	3.0
30°-40°	210.5	3.5
40°-50°	205.2	3.4
50°-60°	172.7	2.8
60°-70°	121.1	2.0
70°-80°	62.2	1.0
80°-90°	19.1	0.3
90°-100°	58.5	1.0
100°-110°	360.3	5.9
110°-120°	653.4	10.7
120°-130°	838.6	13.8
130°-140°	902.0	14.8
140°-150°	846.7	13.9
150°-160°	684.9	11.2
160°-170°	442.9	7.3
170°-180°	152.8	2.5
0°-30°	357.7	5.9
0°-40°	568.2	9.3
0°-60°	946.1	15.5
0°-90°	1148.5	18.9
90°-120°	1072.2	17.6
90°-150°	3659.5	60.1
90°-180°	4940.0	81.1
0°-180°	6088.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	485	485	485	485	485	
5°	484	482	478	482	481	46
15°	460	458	450	450	447	130
25°	417	411	398	394	390	192
35°	360	350	334	324	318	225
45°	294	283	264	249	243	227
55°	223	211	191	175	169	200
65°	151	138	119	105	99	150
75°	81	69	54	46	44	85
85°	20	14	12	11	11	23
90°	1	11	19	25	29	4
95°	68	62	19	25	25	87
105°	351	355	355	355	354	372
115°	658	664	665	661	654	652
125°	936	944	944	940	936	836
135°	1167	1174	1172	1170	1163	900
145°	1354	1356	1356	1357	1350	846
155°	1491	1484	1486	1489	1480	686
165°	1573	1566	1567	1573	1565	444
175°	1609	1602	1603	1611	1602	153
180°	1609	1609	1609	1609	1609	



TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	485.6	485.4	485.2	485.1	484.8	484.4	483.8	483.1	482.4	481.8	482.4
5°	484.0	483.7	483.4	483.0	482.7	482.1	481.2	480.3	479.4	478.5	479.3
7.5°	479.3	479.0	478.6	478.3	478.0	477.3	476.3	475.2	474.1	473.0	473.6
10°	474.8	474.6	474.4	474.1	473.9	473.2	472.1	470.9	469.8	468.7	468.9
12.5°	469.8	469.5	469.3	469.0	468.7	467.7	466.2	464.7	463.1	461.6	461.8
15°	460.2	459.7	459.2	458.8	458.3	457.2	455.4	453.8	452.0	450.4	450.3
17.5°	449.3	448.5	447.8	447.0	446.3	444.9	442.7	440.5	438.4	436.3	435.9
20°	440.8	440.0	439.2	438.4	437.5	435.9	433.2	430.6	428.0	425.4	425.0
22.5°	431.4	430.6	429.8	429.0	428.2	426.4	423.7	421.0	418.2	415.5	414.7
25°	417.4	416.1	414.9	413.7	412.5	410.4	407.3	404.3	401.3	398.3	397.3
27.5°	401.2	399.8	398.3	396.8	395.3	393.0	389.8	386.5	383.3	380.1	378.6
30°	389.5	388.0	386.4	384.9	383.3	380.9	377.5	374.1	370.7	367.2	365.4
32.5°	378.1	376.3	374.5	372.7	370.9	368.3	364.8	361.3	357.8	354.3	352.3
35°	359.5	357.6	355.6	353.6	351.7	348.9	345.2	341.6	337.9	334.3	331.9
37.5°	341.3	338.9	336.5	334.1	331.8	328.7	325.0	321.2	317.4	313.6	310.8
40°	328.4	326.0	323.5	321.1	318.6	315.4	311.6	307.7	303.7	299.8	296.8
42.5°	314.9	312.4	309.9	307.4	304.9	301.7	297.6	293.6	289.5	285.5	282.6
45°	294.4	292.0	289.6	287.2	284.9	281.5	277.0	272.6	268.1	263.6	260.3
47.5°	273.1	270.5	268.1	265.5	263.1	259.6	255.1	250.6	246.1	241.5	238.2
50°	259.6	256.9	254.2	251.5	248.8	245.2	240.5	235.9	231.2	226.6	223.2
52.5°	244.9	242.2	239.4	236.7	233.9	230.4	226.0	221.6	217.2	212.9	209.2
55°	223.3	220.7	218.1	215.6	212.9	209.4	204.8	200.2	195.7	191.1	187.4
57.5°	201.5	198.8	195.9	193.1	190.4	186.8	182.4	178.0	173.6	169.2	165.6
60°	187.4	184.6	181.7	178.9	176.0	172.5	168.0	163.7	159.2	154.9	151.3
62.5°	172.5	169.8	167.1	164.4	161.6	158.0	153.6	149.2	144.7	140.2	136.9
65°	151.2	148.5	145.7	142.9	140.1	136.6	132.3	128.0	123.7	119.4	116.1
67.5°	130.1	127.3	124.5	121.8	119.0	115.5	111.4	107.3	103.1	99.0	96.0
70°	115.7	113.0	110.2	107.4	104.6	101.2	97.1	93.1	89.0	84.9	82.4
72.5°	101.6	98.9	96.3	93.6	90.9	87.5	83.7	79.9	76.1	72.3	70.0
75°	80.6	78.1	75.7	73.2	70.8	67.9	64.4	61.0	57.6	54.2	52.4
77.5°	59.6	57.7	55.7	53.7	51.8	49.4	46.7	44.0	41.3	38.5	37.2
80°	47.6	45.6	43.7	41.7	39.8	37.7	35.4	33.1	30.8	28.5	27.8
82.5°	35.9	34.1	32.4	30.6	28.8	27.2	25.7	24.1	22.5	20.9	20.6
85°	20.1	18.7	17.2	15.8	14.3	13.3	12.9	12.5	12.1	11.7	11.6
87.5°	7.0	7.0	6.9	6.9	6.8	7.0	7.3	7.6	7.9	8.2	8.5
90°	1.2	3.3	5.5	7.5	9.7	11.6	13.5	15.4	17.2	19.1	20.4
92.5°	18.4	16.9	15.4	13.9	12.4	12.5	14.2	15.8	17.4	19.1	20.4
95°	68.0	67.2	66.4	65.6	64.8	59.3	49.3	39.2	29.2	19.1	20.4
97.5°	141.9	143.3	144.7	146.2	147.7	138.4	118.4	98.5	78.6	58.7	51.2
100°	199.2	199.9	200.7	201.5	202.3	203.3	204.3	205.4	206.4	207.5	168.0
102.5°	257.4	258.3	259.4	260.4	261.3	262.2	262.8	263.5	264.1	264.7	257.3
105°	350.6	351.6	352.8	353.8	354.8	355.4	355.4	355.4	355.4	355.4	355.4
107.5°	447.4	447.4	447.4	447.4	447.4	447.7	448.2	448.8	449.3	449.8	449.9
110°	510.4	510.4	510.4	510.4	510.4	510.6	511.2	511.7	512.2	512.8	512.0



TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	569.6	570.2	570.8	571.5	572.1	572.6	572.9	573.2	573.5	573.9	572.8
115°	658.3	659.6	660.9	662.3	663.5	664.3	664.6	664.9	665.2	665.4	664.3
117.5°	750.1	750.0	750.0	750.0	749.9	750.4	751.4	752.3	753.4	754.4	753.0
120°	807.3	807.1	806.8	806.5	806.3	806.5	807.3	808.1	808.9	809.7	809.2
122.5°	857.9	858.9	859.9	860.9	861.9	862.6	863.0	863.3	863.7	864.1	863.6
125°	936.1	937.9	939.8	941.7	943.6	944.4	944.4	944.4	944.4	944.4	943.4
127.5°	1010.7	1012.1	1013.4	1014.8	1016.1	1016.7	1016.5	1016.4	1016.2	1016.1	1015.4
130°	1056.5	1057.9	1059.2	1060.6	1061.8	1062.6	1063.0	1063.2	1063.4	1063.7	1063.0
132.5°	1102.3	1103.9	1105.4	1107.0	1108.5	1109.0	1108.4	1107.8	1107.2	1106.7	1106.5
135°	1167.4	1169.0	1170.7	1172.3	1173.9	1174.3	1173.9	1173.3	1172.7	1172.3	1171.7
137.5°	1227.3	1228.7	1230.1	1231.4	1232.9	1233.3	1232.8	1232.3	1231.8	1231.4	1231.5
140°	1266.5	1267.0	1267.5	1268.0	1268.6	1268.7	1268.4	1268.2	1267.9	1267.7	1268.2
142.5°	1301.7	1302.0	1302.3	1302.7	1303.0	1303.4	1303.8	1304.1	1304.5	1304.9	1305.0
145°	1353.5	1354.0	1354.6	1355.1	1355.7	1355.9	1355.9	1355.9	1355.9	1355.9	1356.1
147.5°	1398.8	1398.7	1398.6	1398.5	1398.4	1398.5	1398.8	1399.2	1399.5	1399.8	1400.1
150°	1427.4	1426.9	1426.4	1425.8	1425.3	1425.3	1425.8	1426.4	1426.9	1427.4	1428.0
152.5°	1455.1	1454.0	1452.8	1451.6	1450.4	1450.1	1450.6	1451.2	1451.8	1452.2	1452.8
155°	1490.6	1489.1	1487.5	1485.9	1484.3	1483.8	1484.3	1484.8	1485.3	1485.9	1486.7
157.5°	1518.1	1517.1	1516.2	1515.2	1514.3	1513.8	1513.9	1513.9	1513.9	1514.0	1514.9
160°	1537.2	1535.6	1534.0	1532.4	1530.8	1530.1	1530.4	1530.7	1530.9	1531.2	1532.2
162.5°	1552.4	1550.9	1549.3	1547.6	1546.0	1545.4	1545.6	1545.9	1546.2	1546.4	1547.9
165°	1573.0	1571.4	1569.7	1568.1	1566.5	1565.9	1566.1	1566.5	1566.7	1566.9	1568.5
167.5°	1588.2	1586.6	1584.9	1583.3	1581.6	1581.0	1581.2	1581.4	1581.8	1582.0	1583.9
170°	1596.8	1594.9	1593.1	1591.2	1589.4	1588.6	1588.8	1589.1	1589.4	1589.6	1591.7
172.5°	1602.5	1600.7	1598.8	1597.0	1595.1	1594.4	1594.9	1595.4	1595.9	1596.3	1598.2
175°	1608.7	1607.1	1605.5	1603.9	1602.3	1601.7	1602.0	1602.2	1602.5	1602.7	1604.9
177.5°	1611.5	1610.3	1609.0	1607.7	1606.5	1605.9	1606.1	1606.4	1606.5	1606.8	1608.3
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7



TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	484.7	484.7	484.7	484.7	484.7	484.7	484.7	484.7
2.5°	483.1	483.8	484.4	484.7	484.7	484.6	484.5	484.4
5°	480.1	480.9	481.7	482.1	482.0	481.7	481.6	481.4
7.5°	474.1	474.8	475.3	475.5	475.3	475.2	475.0	474.8
10°	469.1	469.4	469.6	469.6	469.4	469.1	468.9	468.7
12.5°	461.9	462.2	462.3	462.2	461.8	461.4	461.1	460.7
15°	450.1	450.0	450.0	449.6	448.9	448.1	447.4	446.6
17.5°	435.5	435.1	434.7	434.1	433.6	432.9	432.3	431.7
20°	424.6	424.2	423.8	423.3	422.5	421.8	421.0	420.3
22.5°	413.8	413.0	412.3	411.5	411.0	410.4	409.8	409.2
25°	396.2	395.1	394.1	393.2	392.2	391.3	390.5	389.5
27.5°	377.2	375.7	374.1	373.0	372.2	371.3	370.4	369.6
30°	363.5	361.6	359.7	358.5	357.7	357.0	356.2	355.5
32.5°	350.2	348.2	346.0	344.6	343.6	342.7	341.7	340.9
35°	329.5	327.2	324.8	323.1	321.9	320.8	319.6	318.5
37.5°	307.9	305.1	302.3	300.3	299.2	298.1	297.0	295.9
40°	293.7	290.6	287.5	285.4	284.5	283.5	282.5	281.5
42.5°	279.6	276.6	273.6	271.5	270.1	268.5	267.1	265.7
45°	257.1	253.8	250.6	248.3	247.2	245.9	244.7	243.4
47.5°	234.9	231.5	228.1	225.8	224.4	223.1	221.7	220.4
50°	219.8	216.3	212.9	210.6	209.5	208.2	207.0	205.7
52.5°	205.5	201.8	198.1	195.7	194.5	193.3	192.0	190.8
55°	183.8	180.1	176.5	174.0	172.7	171.3	170.1	168.8
57.5°	162.1	158.5	154.9	152.5	151.4	150.2	149.1	147.9
60°	147.7	144.1	140.5	138.2	136.9	135.7	134.5	133.2
62.5°	133.6	130.2	126.9	124.7	123.4	122.2	121.0	119.8
65°	112.8	109.6	106.3	104.1	102.9	101.6	100.4	99.2
67.5°	93.0	90.1	87.1	85.1	84.1	83.2	82.1	81.2
70°	79.9	77.4	74.9	73.1	72.1	71.1	70.2	69.2
72.5°	67.7	65.4	63.1	61.6	60.9	60.3	59.6	58.9
75°	50.6	48.8	47.1	45.9	45.3	44.7	44.1	43.6
77.5°	36.0	34.8	33.5	32.6	32.2	31.8	31.4	31.0
80°	27.1	26.4	25.7	25.2	25.0	24.9	24.7	24.6
82.5°	20.3	19.9	19.6	19.3	19.3	19.2	19.1	18.9
85°	11.6	11.5	11.4	11.3	11.2	11.2	11.1	11.0
87.5°	8.7	9.0	9.3	9.4	9.5	9.7	9.7	9.8
90°	21.7	23.1	24.4	25.4	26.2	27.0	27.8	28.6
92.5°	21.7	23.1	24.4	25.2	25.6	26.0	26.4	26.7
95°	21.7	23.1	24.4	25.0	25.0	25.0	25.0	25.0
97.5°	43.7	36.3	28.8	25.0	25.0	25.0	25.0	25.0
100°	128.5	89.0	49.6	29.3	28.2	27.2	26.1	25.0
102.5°	249.8	242.3	234.9	222.1	204.1	186.1	168.0	150.0
105°	355.4	355.4	355.4	355.2	355.0	354.7	354.4	354.2
107.5°	450.0	450.0	450.0	449.6	448.9	448.1	447.3	446.5
110°	511.2	510.4	509.6	509.4	509.6	509.8	510.2	510.4





TEST NUMBER: P333658-927

CATALOG NUMBER: S125RDIW-S375D1560U927-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	571.8	570.8	569.8	569.1	568.8	568.4	568.0	567.6
115°	663.3	662.3	661.2	659.9	658.3	656.6	655.1	653.5
117.5°	751.6	750.3	748.8	747.8	747.2	746.5	745.8	745.0
120°	808.7	808.1	807.6	806.7	805.3	804.0	802.7	801.4
122.5°	863.0	862.5	862.0	860.9	859.4	857.9	856.3	854.8
125°	942.4	941.3	940.2	939.3	938.5	937.7	936.9	936.1
127.5°	1014.9	1014.3	1013.7	1012.4	1010.4	1008.5	1006.5	1004.6
130°	1062.2	1061.4	1060.6	1059.5	1058.2	1056.9	1055.5	1054.2
132.5°	1106.4	1106.2	1106.0	1105.3	1104.0	1102.6	1101.3	1099.9
135°	1171.2	1170.7	1170.1	1169.0	1167.4	1165.9	1164.3	1162.7
137.5°	1231.6	1231.7	1231.8	1231.2	1229.8	1228.4	1227.0	1225.7
140°	1268.7	1269.2	1269.8	1269.2	1267.7	1266.1	1264.5	1262.9
142.5°	1305.0	1305.2	1305.3	1304.6	1302.9	1301.3	1299.7	1298.1
145°	1356.5	1356.7	1356.9	1356.3	1354.7	1353.1	1351.5	1350.0
147.5°	1400.4	1400.7	1401.1	1400.3	1398.4	1396.5	1394.6	1392.7
150°	1428.5	1429.0	1429.6	1428.8	1426.6	1424.5	1422.4	1420.3
152.5°	1453.3	1453.8	1454.4	1453.7	1451.8	1449.9	1448.0	1446.0
155°	1487.5	1488.3	1489.1	1488.4	1486.3	1484.2	1482.0	1479.9
157.5°	1515.7	1516.6	1517.4	1516.8	1514.7	1512.5	1510.4	1508.3
160°	1533.3	1534.4	1535.4	1534.9	1532.8	1530.7	1528.5	1526.5
162.5°	1549.4	1550.9	1552.4	1552.0	1549.7	1547.3	1545.0	1542.6
165°	1570.1	1571.8	1573.4	1573.0	1571.0	1568.8	1566.7	1564.6
167.5°	1585.8	1587.7	1589.6	1589.4	1587.0	1584.6	1582.2	1579.8
170°	1593.9	1596.0	1598.1	1598.0	1595.6	1593.2	1590.8	1588.4
172.5°	1600.1	1602.0	1603.9	1603.7	1601.3	1598.9	1596.6	1594.2
175°	1606.9	1609.1	1611.2	1611.1	1608.7	1606.3	1603.9	1601.6
177.5°	1609.8	1611.2	1612.7	1612.6	1610.9	1609.2	1607.5	1605.8
180°	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7	1608.7

(END OF REPORT)