

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333712

Luminaire Tested: **S125RDIW-S1090D1340U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333712
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D1340U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1340 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9627.0 lumens
Efficiency: N/A
Efficacy: 137.9 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 69.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44								
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	46	45	44	38								
2	88	81	75	71	81	75	70	65	62	59	56	51	49	46	41	39	37	32								
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28								
4	74	64	56	50	68	59	52	47	49	44	40	41	37	34	32	30	28	24								
5	68	57	49	43	62	52	46	40	44	39	35	37	33	30	29	27	24	21								
6	63	51	43	37	57	47	40	35	40	35	31	33	29	26	27	24	22	19								
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17								
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17	15								
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	16	13								
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14	12								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	1.6
10°-20°	462.1	4.8
20°-30°	732.6	7.6
30°-40°	883.5	9.2
40°-50°	789.0	8.2
50°-60°	605.0	6.3
60°-70°	393.2	4.1
70°-80°	191.2	2.0
80°-90°	49.3	0.5
90°-100°	63.5	0.7
100°-110°	391.2	4.1
110°-120°	709.5	7.4
120°-130°	910.5	9.5
130°-140°	979.3	10.2
140°-150°	919.2	9.5
150°-160°	743.6	7.7
160°-170°	480.9	5.0
170°-180°	165.9	1.7
0°-30°	1352.3	14.0
0°-40°	2235.8	23.2
0°-60°	3629.8	37.7
0°-90°	4263.4	44.3
90°-120°	1164.1	12.1
90°-150°	3973.2	41.3
90°-180°	5364.0	55.7
0°-180°	9627.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	31	1	31	1	31	15
95°	27	74	27	74	27	22
105°	384	381	384	381	384	348
115°	710	715	710	715	710	704
125°	1016	1016	1016	1016	1016	904
135°	1262	1268	1262	1268	1262	974
145°	1466	1470	1466	1470	1466	916
155°	1607	1618	1607	1618	1607	741
165°	1699	1708	1699	1708	1699	479
175°	1739	1747	1739	1747	1739	165
180°	1747	1747	1747	1747	1747	



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	18.1	17.4	16.7	16.5	16.9	17.7	16.9	16.1	15.8	15.5	15.6
90°	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6	22.2	20.7	18.7
92.5°	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6	22.2	20.7	18.9
95°	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6	22.2	20.7	31.6
97.5°	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5	55.6	63.7	85.3
100°	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5	182.4	225.3	224.1
102.5°	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2	279.3	287.4	286.7
105°	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5	488.4	488.4	487.8
110°	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0	555.9	556.7	556.2



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8	621.9	623.0	622.7
115°	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2	721.3	722.5	722.2
117.5°	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1	817.6	819.1	818.0
120°	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0	878.6	879.1	878.3
122.5°	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0	937.6	938.2	937.8
125°	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1	1024.3	1025.4	1025.4
127.5°	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9	1102.5	1103.1	1103.3
130°	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2	1154.1	1154.9	1154.6
132.5°	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2	1201.4	1201.5	1202.2
135°	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6	1272.2	1272.7	1273.3
137.5°	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2	1337.1	1337.0	1337.5
140°	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5	1376.9	1376.3	1376.6
142.5°	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9	1416.8	1416.7	1416.3
145°	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7	1472.4	1472.1	1472.1
147.5°	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5	1520.1	1519.8	1519.4
150°	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0	1550.4	1549.8	1549.2
152.5°	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9	1577.3	1576.7	1576.2
155°	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0	1614.1	1613.3	1612.7
157.5°	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7	1644.7	1643.8	1643.8
160°	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8	1663.6	1662.5	1662.2
162.5°	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2	1680.6	1679.0	1678.7
165°	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7	1703.0	1701.3	1701.0
167.5°	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8	1719.7	1717.6	1717.3
170°	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5	1728.2	1725.9	1725.6
172.5°	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3	1735.2	1733.1	1732.6
175°	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7	1742.4	1740.1	1739.9
177.5°	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8	1746.2	1744.5	1744.3
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	15.8	15.4	15.5	15.1	14.1	16.3	17.5	17.5	16.9	16.3	15.7
90°	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3	3.6	5.9	8.2
92.5°	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9	18.3	16.7	15.1
95°	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8	72.9	72.1	71.2
97.5°	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1	155.6	157.2	158.7
100°	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2	217.1	217.9	218.8
102.5°	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4	280.5	281.6	282.7
105°	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7	381.8	383.0	384.1
107.5°	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8	485.8	485.8	485.8
110°	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2	554.2	554.2	554.2



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4	619.1	619.8	620.4
115°	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7	716.1	717.6	719.0
117.5°	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4	814.3	814.3	814.2
120°	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5	876.3	876.0	875.7
122.5°	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4	932.5	933.6	934.7
125°	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4	1018.4	1020.4	1022.4
127.5°	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4	1098.9	1100.3	1101.7
130°	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1	1148.6	1150.0	1151.5
132.5°	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9	1198.5	1200.2	1201.9
135°	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6	1269.3	1271.0	1272.7
137.5°	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6	1334.0	1335.5	1337.0
140°	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0	1375.6	1376.2	1376.7
142.5°	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3	1413.7	1414.0	1414.4
145°	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5	1470.1	1470.7	1471.3
147.5°	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7	1518.6	1518.5	1518.4
150°	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1549.2	1548.7	1548.1
152.5°	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8	1578.6	1577.3	1576.1
155°	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4	1616.7	1615.0	1613.3
157.5°	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2	1647.2	1646.1	1645.1
160°	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9	1667.2	1665.5	1663.7
162.5°	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5	1683.8	1682.0	1680.3
165°	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8	1706.0	1704.3	1702.6
167.5°	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3	1722.6	1720.8	1719.0
170°	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7	1731.7	1729.6	1727.6
172.5°	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9	1737.9	1735.9	1733.8
175°	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6	1744.9	1743.2	1741.4
177.5°	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7	1748.3	1747.0	1745.6
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	15.6	16.0	15.9	17.4	16.2	17.1	17.4	17.1	17.4	17.7	17.4
90°	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6	25.0	26.5	27.6
92.5°	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6	25.0	26.5	27.4
95°	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6	25.0	26.5	27.2
97.5°	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5	39.4	31.2	27.2
100°	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5	96.7	53.8	31.8
102.5°	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2	263.1	255.0	241.1
105°	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.8	385.7
107.5°	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5	488.6	488.6	488.2
110°	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0	554.2	553.3	553.0



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8	619.8	618.7	617.9
115°	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2	719.0	717.9	716.4
117.5°	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1	814.6	813.1	811.9
120°	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0	877.4	876.8	875.8
122.5°	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0	936.4	935.9	934.7
125°	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1	1022.0	1020.8	1019.8
127.5°	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9	1101.2	1100.6	1099.2
130°	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2	1152.3	1151.5	1150.3
132.5°	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2	1201.0	1200.8	1200.0
135°	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6	1271.0	1270.4	1269.3
137.5°	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2	1337.3	1337.4	1336.7
140°	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5	1378.0	1378.6	1378.0
142.5°	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9	1417.1	1417.2	1416.4
145°	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7	1473.0	1473.3	1472.6
147.5°	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5	1520.8	1521.2	1520.3
150°	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0	1551.5	1552.1	1551.2
152.5°	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9	1578.5	1579.0	1578.3
155°	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0	1615.8	1616.7	1616.0
157.5°	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7	1646.6	1647.5	1646.8
160°	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8	1665.9	1667.1	1666.5
162.5°	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2	1683.9	1685.5	1685.0
165°	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7	1706.5	1708.2	1707.9
167.5°	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8	1723.8	1725.9	1725.6
170°	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5	1732.8	1735.1	1735.0
172.5°	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3	1739.4	1741.4	1741.2
175°	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7	1747.0	1749.3	1749.2
177.5°	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8	1749.4	1751.0	1750.9
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	18.1	17.7	17.9	18.1	17.9	17.7	18.1	17.4	17.7	17.4	17.1
90°	28.5	29.3	30.2	31.1	30.2	29.3	28.5	27.6	26.5	25.0	23.6
92.5°	27.8	28.2	28.6	29.0	28.6	28.2	27.8	27.4	26.5	25.0	23.6
95°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	26.5	25.0	23.6
97.5°	27.2	27.2	27.2	27.2	27.2	27.2	27.2	27.2	31.2	39.4	47.5
100°	30.6	29.5	28.3	27.2	28.3	29.5	30.6	31.8	53.8	96.7	139.5
102.5°	221.6	202.0	182.4	162.9	182.4	202.0	221.6	241.1	255.0	263.1	271.2
105°	385.4	385.1	384.8	384.5	384.8	385.1	385.4	385.7	385.8	385.8	385.8
107.5°	487.3	486.5	485.6	484.8	485.6	486.5	487.3	488.2	488.6	488.6	488.5
110°	553.3	553.6	553.9	554.2	553.9	553.6	553.3	553.0	553.3	554.2	555.0



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	617.5	617.1	616.7	616.3	616.7	617.1	617.5	617.9	618.7	619.8	620.8
115°	714.7	713.0	711.2	709.5	711.2	713.0	714.7	716.4	717.9	719.0	720.2
117.5°	811.2	810.5	809.7	809.0	809.7	810.5	811.2	811.9	813.1	814.6	816.1
120°	874.4	872.9	871.5	870.1	871.5	872.9	874.4	875.8	876.8	877.4	878.0
122.5°	933.1	931.4	929.7	928.1	929.7	931.4	933.1	934.7	935.9	936.4	937.0
125°	1019.0	1018.1	1017.2	1016.4	1017.2	1018.1	1019.0	1019.8	1020.8	1022.0	1023.1
127.5°	1097.1	1095.0	1092.8	1090.7	1092.8	1095.0	1097.1	1099.2	1100.6	1101.2	1101.9
130°	1148.9	1147.4	1146.0	1144.6	1146.0	1147.4	1148.9	1150.3	1151.5	1152.3	1153.2
132.5°	1198.6	1197.2	1195.7	1194.3	1195.7	1197.2	1198.6	1200.0	1200.8	1201.0	1201.2
135°	1267.6	1265.8	1264.1	1262.4	1264.1	1265.8	1267.6	1269.3	1270.4	1271.0	1271.6
137.5°	1335.2	1333.7	1332.2	1330.7	1332.2	1333.7	1335.2	1336.7	1337.4	1337.3	1337.2
140°	1376.3	1374.6	1372.9	1371.1	1372.9	1374.6	1376.3	1378.0	1378.6	1378.0	1377.5
142.5°	1414.6	1412.9	1411.2	1409.5	1411.2	1412.9	1414.6	1416.4	1417.2	1417.1	1416.9
145°	1470.8	1469.1	1467.4	1465.7	1467.4	1469.1	1470.8	1472.6	1473.3	1473.0	1472.7
147.5°	1518.2	1516.1	1514.1	1512.0	1514.1	1516.1	1518.2	1520.3	1521.2	1520.8	1520.5
150°	1548.9	1546.6	1544.3	1542.0	1544.3	1546.6	1548.9	1551.2	1552.1	1551.5	1551.0
152.5°	1576.2	1574.2	1572.1	1570.0	1572.1	1574.2	1576.2	1578.3	1579.0	1578.5	1577.9
155°	1613.7	1611.4	1609.1	1606.8	1609.1	1611.4	1613.7	1616.0	1616.7	1615.8	1615.0
157.5°	1644.5	1642.2	1639.9	1637.6	1639.9	1642.2	1644.5	1646.8	1647.5	1646.6	1645.7
160°	1664.2	1661.9	1659.6	1657.3	1659.6	1661.9	1664.2	1666.5	1667.1	1665.9	1664.8
162.5°	1682.5	1679.9	1677.4	1674.9	1677.4	1679.9	1682.5	1685.0	1685.5	1683.9	1682.2
165°	1705.6	1703.3	1701.0	1698.7	1701.0	1703.3	1705.6	1707.9	1708.2	1706.5	1704.7
167.5°	1723.0	1720.5	1717.9	1715.3	1717.9	1720.5	1723.0	1725.6	1725.9	1723.8	1721.8
170°	1732.4	1729.8	1727.2	1724.6	1727.2	1729.8	1732.4	1735.0	1735.1	1732.8	1730.5
172.5°	1738.6	1736.0	1733.4	1730.8	1733.4	1736.0	1738.6	1741.2	1741.4	1739.4	1737.3
175°	1746.6	1744.0	1741.4	1738.8	1741.4	1744.0	1746.6	1749.2	1749.3	1747.0	1744.7
177.5°	1749.0	1747.2	1745.3	1743.5	1745.3	1747.2	1749.0	1750.9	1751.0	1749.4	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	17.4	17.1	16.2	17.4	15.9	16.0	15.6	15.7	16.3	16.9	17.5
90°	22.2	20.7	18.7	16.7	14.7	12.7	10.5	8.2	5.9	3.6	1.3
92.5°	22.2	20.7	18.9	17.1	15.4	13.6	13.5	15.1	16.7	18.3	19.9
95°	22.2	20.7	31.6	42.6	53.5	64.4	70.3	71.2	72.1	72.9	73.8
97.5°	55.6	63.7	85.3	107.0	128.6	150.2	160.3	158.7	157.2	155.6	154.1
100°	182.4	225.3	224.1	223.0	221.8	220.7	219.7	218.8	217.9	217.1	216.2
102.5°	279.3	287.4	286.7	286.1	285.4	284.7	283.8	282.7	281.6	280.5	279.4
105°	385.8	385.8	385.8	385.8	385.8	385.8	385.3	384.1	383.0	381.8	380.7
107.5°	488.4	488.4	487.8	487.2	486.7	486.1	485.8	485.8	485.8	485.8	485.8
110°	555.9	556.7	556.2	555.6	555.0	554.4	554.2	554.2	554.2	554.2	554.2



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	621.9	623.0	622.7	622.3	622.0	621.7	621.1	620.4	619.8	619.1	618.4
115°	721.3	722.5	722.2	721.9	721.6	721.3	720.5	719.0	717.6	716.1	714.7
117.5°	817.6	819.1	818.0	816.9	815.8	814.7	814.2	814.2	814.3	814.3	814.4
120°	878.6	879.1	878.3	877.4	876.5	875.7	875.4	875.7	876.0	876.3	876.5
122.5°	937.6	938.2	937.8	937.4	937.0	936.6	935.8	934.7	933.6	932.5	931.4
125°	1024.3	1025.4	1025.4	1025.4	1025.4	1025.4	1024.4	1022.4	1020.4	1018.4	1016.4
127.5°	1102.5	1103.1	1103.3	1103.5	1103.6	1103.8	1103.2	1101.7	1100.3	1098.9	1097.4
130°	1154.1	1154.9	1154.6	1154.3	1154.1	1153.8	1152.9	1151.5	1150.0	1148.6	1147.1
132.5°	1201.4	1201.5	1202.2	1202.8	1203.4	1204.1	1203.5	1201.9	1200.2	1198.5	1196.9
135°	1272.2	1272.7	1273.3	1273.9	1274.5	1275.0	1274.5	1272.7	1271.0	1269.3	1267.6
137.5°	1337.1	1337.0	1337.5	1338.0	1338.5	1339.0	1338.5	1337.0	1335.5	1334.0	1332.6
140°	1376.9	1376.3	1376.6	1376.9	1377.2	1377.5	1377.3	1376.7	1376.2	1375.6	1375.0
142.5°	1416.8	1416.7	1416.3	1415.9	1415.5	1415.1	1414.7	1414.4	1414.0	1413.7	1413.3
145°	1472.4	1472.1	1472.1	1472.1	1472.1	1472.1	1471.8	1471.3	1470.7	1470.1	1469.5
147.5°	1520.1	1519.8	1519.4	1519.1	1518.7	1518.4	1518.3	1518.4	1518.5	1518.6	1518.7
150°	1550.4	1549.8	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8
152.5°	1577.3	1576.7	1576.2	1575.6	1575.0	1574.4	1574.8	1576.1	1577.3	1578.6	1579.8
155°	1614.1	1613.3	1612.7	1612.1	1611.5	1611.0	1611.5	1613.3	1615.0	1616.7	1618.4
157.5°	1644.7	1643.8	1643.8	1643.7	1643.6	1643.6	1644.1	1645.1	1646.1	1647.2	1648.2
160°	1663.6	1662.5	1662.2	1661.9	1661.6	1661.3	1662.0	1663.7	1665.5	1667.2	1668.9
162.5°	1680.6	1679.0	1678.7	1678.5	1678.2	1677.9	1678.6	1680.3	1682.0	1683.8	1685.5
165°	1703.0	1701.3	1701.0	1700.7	1700.4	1700.1	1700.9	1702.6	1704.3	1706.0	1707.8
167.5°	1719.7	1717.6	1717.3	1717.0	1716.7	1716.5	1717.2	1719.0	1720.8	1722.6	1724.3
170°	1728.2	1725.9	1725.6	1725.3	1725.0	1724.7	1725.6	1727.6	1729.6	1731.7	1733.7
172.5°	1735.2	1733.1	1732.6	1732.1	1731.6	1731.1	1731.8	1733.8	1735.9	1737.9	1739.9
175°	1742.4	1740.1	1739.9	1739.6	1739.3	1739.0	1739.7	1741.4	1743.2	1744.9	1746.6
177.5°	1746.2	1744.5	1744.3	1744.1	1743.9	1743.6	1744.2	1745.6	1747.0	1748.3	1749.7
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.5	16.3	14.1	15.1	15.5	15.4	15.8	15.6	15.5	15.8	16.1
90°	3.6	5.9	8.2	10.5	12.7	14.7	16.7	18.7	20.7	22.2	23.6
92.5°	18.3	16.7	15.1	13.5	13.6	15.4	17.1	18.9	20.7	22.2	23.6
95°	72.9	72.1	71.2	70.3	64.4	53.5	42.6	31.6	20.7	22.2	23.6
97.5°	155.6	157.2	158.7	160.3	150.2	128.6	107.0	85.3	63.7	55.6	47.5
100°	217.1	217.9	218.8	219.7	220.7	221.8	223.0	224.1	225.3	182.4	139.5
102.5°	280.5	281.6	282.7	283.8	284.7	285.4	286.1	286.7	287.4	279.3	271.2
105°	381.8	383.0	384.1	385.3	385.8	385.8	385.8	385.8	385.8	385.8	385.8
107.5°	485.8	485.8	485.8	485.8	486.1	486.7	487.2	487.8	488.4	488.4	488.5
110°	554.2	554.2	554.2	554.2	554.4	555.0	555.6	556.2	556.7	555.9	555.0



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	619.1	619.8	620.4	621.1	621.7	622.0	622.3	622.7	623.0	621.9	620.8
115°	716.1	717.6	719.0	720.5	721.3	721.6	721.9	722.2	722.5	721.3	720.2
117.5°	814.3	814.3	814.2	814.2	814.7	815.8	816.9	818.0	819.1	817.6	816.1
120°	876.3	876.0	875.7	875.4	875.7	876.5	877.4	878.3	879.1	878.6	878.0
122.5°	932.5	933.6	934.7	935.8	936.6	937.0	937.4	937.8	938.2	937.6	937.0
125°	1018.4	1020.4	1022.4	1024.4	1025.4	1025.4	1025.4	1025.4	1025.4	1024.3	1023.1
127.5°	1098.9	1100.3	1101.7	1103.2	1103.8	1103.6	1103.5	1103.3	1103.1	1102.5	1101.9
130°	1148.6	1150.0	1151.5	1152.9	1153.8	1154.1	1154.3	1154.6	1154.9	1154.1	1153.2
132.5°	1198.5	1200.2	1201.9	1203.5	1204.1	1203.4	1202.8	1202.2	1201.5	1201.4	1201.2
135°	1269.3	1271.0	1272.7	1274.5	1275.0	1274.5	1273.9	1273.3	1272.7	1272.2	1271.6
137.5°	1334.0	1335.5	1337.0	1338.5	1339.0	1338.5	1338.0	1337.5	1337.0	1337.1	1337.2
140°	1375.6	1376.2	1376.7	1377.3	1377.5	1377.2	1376.9	1376.6	1376.3	1376.9	1377.5
142.5°	1413.7	1414.0	1414.4	1414.7	1415.1	1415.5	1415.9	1416.3	1416.7	1416.8	1416.9
145°	1470.1	1470.7	1471.3	1471.8	1472.1	1472.1	1472.1	1472.1	1472.1	1472.4	1472.7
147.5°	1518.6	1518.5	1518.4	1518.3	1518.4	1518.7	1519.1	1519.4	1519.8	1520.1	1520.5
150°	1549.2	1548.7	1548.1	1547.5	1547.5	1548.1	1548.7	1549.2	1549.8	1550.4	1551.0
152.5°	1578.6	1577.3	1576.1	1574.8	1574.4	1575.0	1575.6	1576.2	1576.7	1577.3	1577.9
155°	1616.7	1615.0	1613.3	1611.5	1611.0	1611.5	1612.1	1612.7	1613.3	1614.1	1615.0
157.5°	1647.2	1646.1	1645.1	1644.1	1643.6	1643.6	1643.7	1643.8	1643.8	1644.7	1645.7
160°	1667.2	1665.5	1663.7	1662.0	1661.3	1661.6	1661.9	1662.2	1662.5	1663.6	1664.8
162.5°	1683.8	1682.0	1680.3	1678.6	1677.9	1678.2	1678.5	1678.7	1679.0	1680.6	1682.2
165°	1706.0	1704.3	1702.6	1700.9	1700.1	1700.4	1700.7	1701.0	1701.3	1703.0	1704.7
167.5°	1722.6	1720.8	1719.0	1717.2	1716.5	1716.7	1717.0	1717.3	1717.6	1719.7	1721.8
170°	1731.7	1729.6	1727.6	1725.6	1724.7	1725.0	1725.3	1725.6	1725.9	1728.2	1730.5
172.5°	1737.9	1735.9	1733.8	1731.8	1731.1	1731.6	1732.1	1732.6	1733.1	1735.2	1737.3
175°	1744.9	1743.2	1741.4	1739.7	1739.0	1739.3	1739.6	1739.9	1740.1	1742.4	1744.7
177.5°	1748.3	1747.0	1745.6	1744.2	1743.6	1743.9	1744.1	1744.3	1744.5	1746.2	1747.8
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	16.9	17.7	16.9	16.5	16.7	17.4	18.1
90°	25.0	26.5	27.6	28.5	29.3	30.2	31.1
92.5°	25.0	26.5	27.4	27.8	28.2	28.6	29.0
95°	25.0	26.5	27.2	27.2	27.2	27.2	27.2
97.5°	39.4	31.2	27.2	27.2	27.2	27.2	27.2
100°	96.7	53.8	31.8	30.6	29.5	28.3	27.2
102.5°	263.1	255.0	241.1	221.6	202.0	182.4	162.9
105°	385.8	385.8	385.7	385.4	385.1	384.8	384.5
107.5°	488.6	488.6	488.2	487.3	486.5	485.6	484.8
110°	554.2	553.3	553.0	553.3	553.6	553.9	554.2



TEST NUMBER: P333712

CATALOG NUMBER: S125RDIW-S1090D1340U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	619.8	618.7	617.9	617.5	617.1	616.7	616.3
115°	719.0	717.9	716.4	714.7	713.0	711.2	709.5
117.5°	814.6	813.1	811.9	811.2	810.5	809.7	809.0
120°	877.4	876.8	875.8	874.4	872.9	871.5	870.1
122.5°	936.4	935.9	934.7	933.1	931.4	929.7	928.1
125°	1022.0	1020.8	1019.8	1019.0	1018.1	1017.2	1016.4
127.5°	1101.2	1100.6	1099.2	1097.1	1095.0	1092.8	1090.7
130°	1152.3	1151.5	1150.3	1148.9	1147.4	1146.0	1144.6
132.5°	1201.0	1200.8	1200.0	1198.6	1197.2	1195.7	1194.3
135°	1271.0	1270.4	1269.3	1267.6	1265.8	1264.1	1262.4
137.5°	1337.3	1337.4	1336.7	1335.2	1333.7	1332.2	1330.7
140°	1378.0	1378.6	1378.0	1376.3	1374.6	1372.9	1371.1
142.5°	1417.1	1417.2	1416.4	1414.6	1412.9	1411.2	1409.5
145°	1473.0	1473.3	1472.6	1470.8	1469.1	1467.4	1465.7
147.5°	1520.8	1521.2	1520.3	1518.2	1516.1	1514.1	1512.0
150°	1551.5	1552.1	1551.2	1548.9	1546.6	1544.3	1542.0
152.5°	1578.5	1579.0	1578.3	1576.2	1574.2	1572.1	1570.0
155°	1615.8	1616.7	1616.0	1613.7	1611.4	1609.1	1606.8
157.5°	1646.6	1647.5	1646.8	1644.5	1642.2	1639.9	1637.6
160°	1665.9	1667.1	1666.5	1664.2	1661.9	1659.6	1657.3
162.5°	1683.9	1685.5	1685.0	1682.5	1679.9	1677.4	1674.9
165°	1706.5	1708.2	1707.9	1705.6	1703.3	1701.0	1698.7
167.5°	1723.8	1725.9	1725.6	1723.0	1720.5	1717.9	1715.3
170°	1732.8	1735.1	1735.0	1732.4	1729.8	1727.2	1724.6
172.5°	1739.4	1741.4	1741.2	1738.6	1736.0	1733.4	1730.8
175°	1747.0	1749.3	1749.2	1746.6	1744.0	1741.4	1738.8
177.5°	1749.4	1751.0	1750.9	1749.0	1747.2	1745.3	1743.5
180°	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6	1746.6

(END OF REPORT)