

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333704

Luminaire Tested: **S125RDIW-S1090D770U835-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333704
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-7,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S1090D770U835-4F0-1E-UDD-A
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1090 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 770 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7331.3 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): 1.4 / 1.22 / 1.47
Luminous Opening: Rectangular (W 4' x L: 0.42' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64	58								
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55	50								
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	51	49	47	43								
3	84	74	67	62	78	70	63	58	61	56	52	53	49	46	45	43	40	37								
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	38	35	32								
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	33	31	28								
6	65	53	45	39	61	50	43	38	44	38	34	39	34	31	34	30	27	24								
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24	22								
8	56	44	36	31	52	41	34	29	37	31	27	32	28	24	28	25	22	20								
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	22	20	18								
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18	16								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10619	10619	10619	10619
5°	12217	10633	9390	10633
10°	14014	10579	8286	10579
15°	15136	10470	7365	10470
20°	16690	10344	6801	10344
25°	19316	10177	6310	10177
30°	21020	10001	5990	10001
35°	17731	9797	5694	9797
40°	12382	9429	5440	9429
45°	9186	8933	5191	8933
50°	7324	8416	4977	8416
55°	6217	7775	4788	7775
60°	5371	7201	4481	7201
65°	4786	6580	3857	6580
70°	4205	6027	3518	6027
75°	3638	5220	3301	5220
80°	2760	4392	2760	4392
85°	2297	3453	2601	3453



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.2
10°-20°	462.1	6.3
20°-30°	732.6	10.0
30°-40°	883.5	12.1
40°-50°	789.0	10.8
50°-60°	605.0	8.3
60°-70°	393.2	5.4
70°-80°	191.2	2.6
80°-90°	47.7	0.7
90°-100°	36.3	0.5
100°-110°	223.9	3.1
110°-120°	406.0	5.5
120°-130°	521.1	7.1
130°-140°	560.5	7.6
140°-150°	526.1	7.2
150°-160°	425.5	5.8
160°-170°	275.2	3.8
170°-180°	94.9	1.3
0°-30°	1352.3	18.4
0°-40°	2235.8	30.5
0°-60°	3629.8	49.5
0°-90°	4261.8	58.1
90°-120°	666.2	9.1
90°-150°	2273.8	31.0
90°-180°	3069.0	41.9
0°-180°	7331.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1644	1644	1644	1644	1644	
5°	1884	1640	1448	1640	1884	188
15°	2264	1566	1102	1566	2264	649
25°	2711	1428	886	1428	2711	1245
35°	2249	1243	722	1243	2249	1358
45°	1006	978	568	978	1006	802
55°	552	690	425	690	552	501
65°	313	431	252	431	313	312
75°	146	209	132	209	146	155
85°	31	47	35	47	31	36
90°	18	1	18	1	18	9
95°	16	42	16	42	16	13
105°	220	218	220	218	220	199
115°	406	409	406	409	406	403
125°	582	582	582	582	582	517
135°	722	725	722	725	722	558
145°	839	841	839	841	839	524
155°	920	926	920	926	920	424
165°	972	977	972	977	972	274
175°	995	1000	995	1000	995	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1729.5	1728.4	1730.6	1724.6	1725.2	1716.0	1716.0	1709.0	1699.8	1692.8	1689.5
5°	1884.4	1885.8	1883.1	1873.0	1866.2	1856.1	1844.6	1824.4	1807.5	1791.3	1778.5
7.5°	2044.0	2044.9	2036.0	2032.9	2015.9	2003.5	1978.0	1950.4	1926.0	1895.0	1871.2
10°	2136.9	2136.2	2126.7	2119.3	2104.5	2085.6	2060.6	2028.2	1997.8	1964.1	1931.7
12.5°	2190.9	2189.1	2186.1	2177.1	2163.3	2146.6	2125.4	2093.5	2056.1	2019.2	1981.4
15°	2263.8	2259.0	2250.3	2238.8	2219.2	2199.6	2176.0	2147.7	2111.9	2070.0	2035.0
17.5°	2353.9	2354.1	2340.6	2324.6	2298.0	2263.5	2227.0	2181.3	2132.7	2086.7	2049.3
20°	2428.4	2426.4	2412.9	2381.9	2351.5	2308.3	2266.5	2210.4	2151.0	2091.0	2044.4
22.5°	2535.4	2530.1	2516.0	2475.3	2428.2	2372.6	2308.6	2240.1	2168.3	2100.1	2039.0
25°	2710.6	2706.5	2678.8	2631.6	2565.5	2479.7	2396.0	2302.2	2199.0	2109.2	2035.0
27.5°	2830.4	2826.0	2805.5	2766.2	2705.2	2615.0	2501.7	2376.3	2247.4	2123.9	2016.9
30°	2818.6	2828.7	2826.0	2807.8	2761.9	2680.9	2576.3	2435.2	2282.0	2136.9	2009.3
32.5°	2649.0	2658.1	2681.8	2717.6	2720.3	2687.9	2609.7	2479.5	2320.9	2155.8	2003.4
35°	2248.9	2261.1	2307.0	2379.2	2473.7	2552.6	2568.8	2498.6	2356.2	2178.7	1994.5
37.5°	1728.9	1795.3	1834.0	1910.0	2052.8	2198.0	2337.7	2389.2	2328.5	2169.3	1980.0
40°	1468.7	1484.9	1553.7	1639.4	1759.6	1910.8	2109.9	2253.6	2258.4	2147.7	1957.3
42.5°	1257.0	1277.5	1324.8	1393.2	1496.1	1647.3	1852.9	2042.5	2130.4	2088.3	1927.6
45°	1005.7	1021.2	1055.6	1108.3	1187.2	1312.1	1488.9	1708.3	1882.4	1950.6	1848.0
47.5°	826.1	834.5	864.5	904.6	963.0	1054.0	1190.9	1381.3	1590.2	1736.6	1722.2
50°	728.9	738.4	761.3	791.7	841.0	917.9	1027.3	1185.9	1401.2	1580.0	1615.8
52.5°	653.3	661.2	675.5	704.2	744.9	804.0	892.3	1035.8	1229.5	1419.7	1502.4
55°	552.1	557.5	569.0	585.2	617.6	660.1	736.4	835.6	992.2	1183.8	1305.3
57.5°	468.7	471.4	478.7	493.7	516.1	547.1	602.2	686.3	798.6	971.2	1105.3
60°	415.8	418.5	427.9	438.0	455.6	483.9	527.1	585.8	693.8	836.3	971.9
62.5°	373.6	375.3	379.3	389.4	404.8	426.7	460.7	508.6	594.5	719.6	847.7
65°	313.2	313.8	315.2	323.3	332.7	348.9	371.2	405.0	469.8	564.3	677.6
67.5°	255.1	256.1	260.8	263.6	273.5	282.0	295.1	320.9	366.5	430.2	518.4
70°	222.7	222.1	226.8	230.2	233.5	243.7	252.4	273.4	301.7	350.3	423.9
72.5°	192.5	190.7	192.8	194.0	198.4	205.3	214.1	226.9	248.8	282.3	338.6
75°	145.8	146.5	146.5	147.8	151.2	153.9	156.6	163.3	175.5	197.8	228.1
77.5°	102.3	101.2	104.1	104.5	106.5	109.5	111.8	114.5	119.5	128.6	144.3
80°	74.2	74.2	74.9	76.9	76.3	77.6	81.0	83.7	89.8	95.2	100.6
82.5°	57.0	56.4	57.1	57.5	57.4	58.7	59.9	60.5	62.8	65.5	69.2
85°	31.0	31.0	31.7	31.7	32.4	32.4	33.1	33.1	33.1	33.7	34.4
87.5°	15.4	14.8	14.2	14.1	14.5	15.4	14.7	14.0	13.9	13.7	14.0
90°	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5	12.7	11.9	10.7
92.5°	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5	12.7	11.9	10.8
95°	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5	12.7	11.9	18.1
97.5°	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2	31.8	36.5	48.8
100°	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9	104.4	128.9	128.3
102.5°	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2	159.9	164.5	164.1
105°	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6	279.5	279.5	279.2
110°	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6	318.1	318.6	318.3



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3	355.9	356.6	356.4
115°	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1	412.8	413.5	413.3
117.5°	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0	467.9	468.7	468.1
120°	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5	502.8	503.1	502.6
122.5°	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2	536.6	536.9	536.7
125°	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5	586.2	586.8	586.8
127.5°	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6	630.9	631.3	631.4
130°	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0	660.4	660.9	660.8
132.5°	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4	687.5	687.6	688.0
135°	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7	728.0	728.4	728.7
137.5°	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3	765.2	765.1	765.4
140°	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3	788.0	787.6	787.8
142.5°	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9	810.8	810.8	810.5
145°	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8	842.6	842.5	842.5
147.5°	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1	869.9	869.7	869.5
150°	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6	887.3	886.9	886.6
152.5°	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0	902.7	902.3	902.0
155°	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2	923.7	923.2	922.9
157.5°	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8	941.3	940.7	940.7
160°	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7	952.1	951.4	951.2
162.5°	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7	961.8	960.9	960.7
165°	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6	974.6	973.6	973.5
167.5°	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3	984.1	983.0	982.8
170°	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3	989.0	987.7	987.5
172.5°	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2	993.0	991.9	991.6
175°	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5	997.2	995.9	995.7
177.5°	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2	999.3	998.4	998.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1689.5	1685.7	1678.7	1672.2	1664.1	1657.1	1652.3	1646.3	1638.8	1629.6	1622.0
5°	1764.3	1749.4	1729.9	1713.0	1691.4	1674.5	1657.0	1640.1	1623.2	1601.6	1582.7
7.5°	1847.2	1816.5	1786.7	1749.2	1715.2	1684.8	1655.6	1626.1	1597.2	1566.5	1537.0
10°	1897.9	1860.8	1819.6	1772.4	1729.2	1688.0	1650.2	1613.1	1574.0	1539.5	1502.4
12.5°	1945.5	1897.5	1850.4	1790.8	1738.9	1688.6	1640.5	1594.2	1552.4	1507.7	1467.9
15°	1988.4	1941.1	1888.5	1815.6	1743.4	1682.6	1625.9	1565.9	1513.9	1463.9	1419.4
17.5°	2005.0	1955.4	1894.3	1824.2	1745.3	1668.9	1595.8	1530.0	1468.8	1410.6	1360.5
20°	1998.5	1950.6	1887.8	1821.0	1736.6	1657.0	1578.0	1505.1	1437.0	1375.5	1322.2
22.5°	1982.8	1933.3	1872.7	1802.1	1722.0	1637.5	1553.2	1475.4	1404.0	1340.4	1282.3
25°	1959.4	1891.9	1829.8	1760.9	1684.7	1601.0	1513.9	1428.2	1351.9	1287.1	1223.7
27.5°	1934.9	1850.7	1771.7	1703.3	1622.7	1548.0	1464.1	1376.2	1296.0	1230.0	1164.9
30°	1912.8	1818.3	1731.2	1653.6	1577.3	1506.5	1426.8	1341.1	1258.8	1190.6	1124.5
32.5°	1885.2	1784.8	1689.1	1599.6	1526.0	1455.7	1383.6	1301.7	1221.5	1151.2	1084.0
35°	1850.7	1722.5	1618.5	1523.3	1441.7	1373.5	1308.7	1242.6	1162.3	1089.4	1023.9
37.5°	1805.3	1659.8	1539.5	1435.9	1349.7	1281.3	1230.1	1169.7	1096.4	1026.6	965.8
40°	1777.8	1614.5	1482.8	1380.3	1289.8	1217.6	1169.7	1118.4	1051.6	986.1	925.3
42.5°	1741.1	1572.9	1425.6	1318.7	1227.7	1158.2	1109.7	1064.9	1008.9	947.2	882.1
45°	1669.1	1492.3	1337.7	1223.0	1131.2	1063.0	1017.8	978.0	935.5	878.8	822.1
47.5°	1575.4	1408.2	1246.5	1121.2	1031.3	968.0	924.1	892.7	862.3	814.1	759.0
50°	1500.4	1339.1	1181.1	1059.7	963.8	903.7	862.6	837.6	809.9	766.1	720.2
52.5°	1411.8	1267.8	1113.1	988.9	898.5	842.2	802.6	777.7	754.9	719.1	675.3
55°	1272.3	1146.1	1004.3	891.6	808.6	751.9	714.1	690.5	677.0	646.6	612.2
57.5°	1111.2	1020.8	895.8	787.1	713.7	657.7	630.0	609.9	594.6	573.2	548.9
60°	998.9	935.5	823.4	720.2	652.7	599.3	574.4	557.5	543.3	525.1	506.2
62.5°	885.0	838.8	741.4	652.7	590.6	545.9	522.5	507.3	491.0	478.7	460.3
65°	732.3	691.1	623.6	554.1	496.8	461.0	444.1	430.6	420.5	407.0	394.2
67.5°	569.7	552.9	506.3	458.4	417.2	385.4	370.8	361.4	349.2	341.1	332.3
70°	469.8	461.7	428.6	396.9	358.4	336.8	323.3	319.2	304.4	296.3	290.2
72.5°	381.2	377.4	358.4	336.4	309.3	290.4	277.9	273.4	263.9	257.4	253.5
75°	261.2	262.6	259.2	245.0	234.9	222.7	211.9	209.2	202.5	197.1	193.7
77.5°	165.2	172.1	172.4	171.7	167.7	160.2	155.8	153.8	147.1	145.1	144.3
80°	113.4	120.8	127.6	126.9	125.5	123.5	120.1	118.1	114.7	112.7	111.4
82.5°	75.6	82.5	88.1	91.8	91.5	89.5	87.2	86.3	85.6	84.1	83.8
85°	35.8	37.1	39.1	43.9	47.2	47.9	47.2	46.6	44.5	45.2	45.9
87.5°	14.3	14.1	14.4	14.2	13.4	15.8	17.2	17.4	16.6	15.8	15.0
90°	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7	2.1	3.4	4.7
92.5°	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4	10.5	9.6	8.6
95°	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2	41.7	41.2	40.8
97.5°	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2	89.1	90.0	90.8
100°	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7	124.2	124.7	125.2
102.5°	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9	160.5	161.2	161.8
105°	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8	218.5	219.2	219.8
107.5°	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0	278.0	278.0	278.0
110°	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9	354.3	354.7	355.1
115°	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0	409.8	410.7	411.5
117.5°	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1	466.0	466.0	466.0
120°	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6	501.5	501.3	501.1
122.5°	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0	533.7	534.3	534.9
125°	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7	582.8	584.0	585.1
127.5°	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0	628.9	629.7	630.5
130°	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5	657.3	658.1	659.0
132.5°	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9	685.9	686.9	687.8
135°	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4	726.4	727.4	728.4
137.5°	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6	763.5	764.3	765.2
140°	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9	787.2	787.6	787.9
142.5°	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8	809.0	809.2	809.4
145°	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0	841.3	841.7	842.0
147.5°	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2	869.1	869.0	869.0
150°	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	886.6	886.3	885.9
152.5°	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1	903.4	902.7	902.0
155°	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2	925.2	924.2	923.2
157.5°	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2	942.7	942.1	941.5
160°	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1	954.1	953.1	952.1
162.5°	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6	963.6	962.6	961.6
165°	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3	976.3	975.4	974.4
167.5°	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8	985.8	984.8	983.8
170°	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2	991.0	989.8	988.7
172.5°	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7	994.6	993.4	992.2
175°	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6	998.6	997.6	996.6
177.5°	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3	1000.5	999.8	999.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1616.6	1609.1	1603.7	1592.9	1585.3	1582.1	1576.1	1574.5	1580.4	1576.1	1575.6
5°	1568.6	1549.0	1533.5	1517.9	1501.1	1490.3	1474.1	1471.4	1467.3	1461.2	1459.9
7.5°	1510.9	1485.4	1465.4	1439.8	1417.5	1399.6	1379.3	1369.7	1364.5	1356.6	1346.1
10°	1472.0	1441.7	1414.7	1389.0	1361.4	1339.1	1318.8	1303.3	1293.2	1283.7	1279.7
12.5°	1433.7	1402.8	1368.2	1337.2	1306.3	1281.3	1258.9	1248.8	1237.6	1226.5	1217.1
15°	1374.2	1333.0	1295.2	1259.4	1233.1	1206.1	1184.5	1169.7	1152.8	1148.1	1129.9
17.5°	1311.0	1270.6	1226.4	1188.7	1158.2	1128.5	1104.7	1087.9	1075.2	1057.8	1049.4
20°	1271.6	1223.7	1180.5	1146.1	1112.3	1077.2	1052.9	1038.7	1026.6	1012.4	1005.7
22.5°	1229.5	1182.6	1138.4	1098.0	1063.7	1029.2	1011.9	997.2	983.4	970.3	961.4
25°	1167.6	1120.4	1073.8	1032.0	996.2	971.2	951.0	934.1	926.7	913.9	904.4
27.5°	1106.5	1056.3	1008.0	966.2	938.2	913.5	896.9	883.5	870.1	858.9	850.7
30°	1067.1	1015.8	963.1	930.1	900.4	876.7	858.5	845.7	835.6	825.5	819.4
32.5°	1027.7	974.8	928.0	892.3	864.2	843.8	825.0	812.8	802.1	790.9	783.7
35°	964.5	910.5	872.7	837.6	809.9	791.0	778.2	760.7	751.9	743.8	736.4
37.5°	905.8	855.6	814.7	783.9	759.8	741.1	724.5	715.0	704.2	696.9	690.7
40°	862.6	816.7	779.6	747.2	729.6	708.7	693.2	681.0	672.9	663.5	656.7
42.5°	823.7	781.0	745.0	715.8	694.0	676.3	661.3	649.2	638.9	632.2	626.5
45°	768.8	726.2	691.1	664.1	643.9	627.0	611.5	605.4	591.9	583.8	581.1
47.5°	711.9	673.9	640.0	615.1	594.4	578.4	563.8	551.4	544.0	536.0	531.7
50°	673.6	637.1	605.4	581.1	560.9	543.3	529.8	521.7	511.6	504.2	498.8
52.5°	635.3	601.5	569.8	546.6	529.0	511.5	496.4	488.3	478.7	473.9	470.2
55°	580.5	544.7	517.7	494.7	476.5	460.3	446.1	438.0	432.0	427.2	425.9
57.5°	518.4	490.0	464.9	444.2	425.3	410.1	397.7	390.0	384.6	383.9	379.9
60°	477.9	452.2	429.3	407.0	390.8	376.6	365.8	357.0	351.6	351.0	349.6
62.5°	437.4	412.8	391.5	371.9	357.3	343.7	333.4	323.6	320.3	317.0	314.0
65°	377.3	355.0	337.5	321.9	306.4	294.9	284.8	278.8	271.3	267.3	259.9
67.5°	318.3	301.0	284.2	271.1	258.9	248.0	239.6	230.6	225.6	222.3	216.9
70°	279.4	265.9	249.1	234.9	225.4	216.7	209.9	199.8	196.4	193.7	191.0
72.5°	242.7	230.8	216.7	205.2	195.7	187.5	179.7	174.9	171.6	168.9	167.3
75°	191.0	179.5	167.4	159.3	152.5	145.8	141.7	138.4	137.0	136.3	133.6
77.5°	140.3	134.2	124.5	118.0	113.5	110.8	107.2	105.4	105.3	102.3	101.4
80°	107.3	103.9	95.8	93.1	89.8	87.1	85.0	81.7	78.3	76.9	74.9
82.5°	79.8	76.4	73.2	68.8	66.0	64.4	62.4	61.1	61.6	59.7	58.7
85°	42.5	39.1	37.8	37.1	35.8	37.1	36.4	35.8	35.1	34.4	35.1
87.5°	14.7	14.9	14.6	15.9	14.6	15.3	15.5	15.1	15.3	15.4	15.0
90°	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5	14.3	15.1	15.8
92.5°	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5	14.3	15.1	15.7
95°	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5	14.3	15.1	15.6
97.5°	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2	22.5	17.9	15.6
100°	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9	55.3	30.8	18.2
102.5°	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2	150.6	145.9	138.0
105°	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.8	220.7
107.5°	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6	279.6	279.6	279.4
110°	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6	317.1	316.6	316.5



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3	354.7	354.0	353.6
115°	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1	411.5	410.8	410.0
117.5°	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0	466.2	465.3	464.7
120°	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5	502.1	501.8	501.2
122.5°	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2	535.9	535.6	534.9
125°	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5	584.9	584.2	583.6
127.5°	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6	630.2	629.9	629.1
130°	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0	659.5	659.0	658.3
132.5°	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4	687.3	687.2	686.8
135°	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7	727.4	727.1	726.4
137.5°	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3	765.3	765.4	765.0
140°	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3	788.6	789.0	788.6
142.5°	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9	811.0	811.0	810.6
145°	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8	843.0	843.1	842.7
147.5°	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1	870.3	870.5	870.0
150°	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6	887.9	888.3	887.8
152.5°	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0	903.3	903.7	903.2
155°	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2	924.7	925.2	924.8
157.5°	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8	942.3	942.8	942.4
160°	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7	953.4	954.0	953.7
162.5°	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7	963.6	964.6	964.3
165°	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6	976.6	977.6	977.4
167.5°	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3	986.5	987.7	987.6
170°	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3	991.7	993.0	992.9
172.5°	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2	995.4	996.6	996.4
175°	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5	999.8	1001.1	1001.0
177.5°	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2	1001.1	1002.1	1002.0
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1575.0	1569.1	1567.5	1569.6	1567.5	1569.1	1575.0	1575.6	1576.1	1580.4	1574.5
5°	1453.2	1446.4	1449.8	1448.4	1449.8	1446.4	1453.2	1459.9	1461.2	1467.3	1471.4
7.5°	1346.0	1337.6	1328.7	1331.5	1328.7	1337.6	1346.0	1346.1	1356.6	1364.5	1369.7
10°	1270.9	1264.2	1260.1	1263.5	1260.1	1264.2	1270.9	1279.7	1283.7	1293.2	1303.3
12.5°	1207.7	1203.7	1200.2	1198.7	1200.2	1203.7	1207.7	1217.1	1226.5	1237.6	1248.8
15°	1121.8	1113.7	1110.3	1101.5	1110.3	1113.7	1121.8	1129.9	1148.1	1152.8	1169.7
17.5°	1042.5	1039.8	1031.0	1027.3	1031.0	1039.8	1042.5	1049.4	1057.8	1075.2	1087.9
20°	995.5	992.8	984.1	989.5	984.1	992.8	995.5	1005.7	1012.4	1026.6	1038.7
22.5°	956.7	950.7	947.9	946.3	947.9	950.7	956.7	961.4	970.3	983.4	997.2
25°	901.7	892.9	889.6	885.5	889.6	892.9	901.7	904.4	913.9	926.7	934.1
27.5°	846.9	842.2	837.7	836.7	837.7	842.2	846.9	850.7	858.9	870.1	883.5
30°	811.3	806.6	803.2	803.2	803.2	806.6	811.3	819.4	825.5	835.6	845.7
32.5°	779.4	775.8	772.4	771.9	772.4	775.8	779.4	783.7	790.9	802.1	812.8
35°	733.0	727.6	726.2	722.2	726.2	727.6	733.0	736.4	743.8	751.9	760.7
37.5°	684.8	680.3	680.2	679.8	680.2	680.3	684.8	690.7	696.9	704.2	715.0
40°	654.0	650.6	650.0	645.2	650.0	650.6	654.0	656.7	663.5	672.9	681.0
42.5°	621.1	619.3	617.0	615.0	617.0	619.3	621.1	626.5	632.2	638.9	649.2
45°	576.4	571.7	571.7	568.3	571.7	571.7	576.4	581.1	583.8	591.9	605.4
47.5°	530.2	526.6	527.0	523.5	527.0	526.6	530.2	531.7	536.0	544.0	551.4
50°	499.5	497.4	496.8	495.4	496.8	497.4	499.5	498.8	504.2	511.6	521.7
52.5°	468.7	467.7	470.3	467.3	470.3	467.7	468.7	470.2	473.9	478.7	488.3
55°	427.2	425.2	429.3	425.2	429.3	425.2	427.2	425.9	427.2	432.0	438.0
57.5°	379.6	377.7	381.3	379.3	381.3	377.7	379.6	379.9	383.9	384.6	390.0
60°	348.3	344.2	346.2	346.9	346.2	344.2	348.3	349.6	351.0	351.6	357.0
62.5°	311.0	308.6	310.1	307.0	310.1	308.6	311.0	314.0	317.0	320.3	323.6
65°	258.5	256.5	253.8	252.4	253.8	256.5	258.5	259.9	267.3	271.3	278.8
67.5°	217.2	212.3	212.2	213.3	212.2	212.3	217.2	216.9	222.3	225.6	230.6
70°	187.0	187.0	186.3	186.3	186.3	187.0	187.0	191.0	193.7	196.4	199.8
72.5°	165.9	165.4	164.1	163.6	164.1	165.4	165.9	167.3	168.9	171.6	174.9
75°	133.6	134.3	133.0	132.3	133.0	134.3	133.6	133.6	136.3	137.0	138.4
77.5°	98.7	95.8	97.3	95.8	97.3	95.8	98.7	101.4	102.3	105.3	105.4
80°	74.9	74.2	76.3	74.2	76.3	74.2	74.9	74.9	76.9	78.3	81.7
82.5°	59.3	58.6	59.5	58.0	59.5	58.6	59.3	58.7	59.7	61.6	61.1
85°	35.8	35.1	34.4	35.1	34.4	35.1	35.8	35.1	34.4	35.1	35.8
87.5°	15.7	15.2	15.3	15.4	15.3	15.2	15.7	15.0	15.4	15.3	15.1
90°	16.3	16.8	17.3	17.8	17.3	16.8	16.3	15.8	15.1	14.3	13.5
92.5°	15.9	16.1	16.4	16.6	16.4	16.1	15.9	15.7	15.1	14.3	13.5
95°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.1	14.3	13.5
97.5°	15.6	15.6	15.6	15.6	15.6	15.6	15.6	15.6	17.9	22.5	27.2
100°	17.5	16.9	16.2	15.6	16.2	16.9	17.5	18.2	30.8	55.3	79.9
102.5°	126.8	115.6	104.4	93.2	104.4	115.6	126.8	138.0	145.9	150.6	155.2
105°	220.6	220.4	220.2	220.1	220.2	220.4	220.6	220.7	220.8	220.8	220.8
107.5°	278.9	278.4	277.9	277.4	277.9	278.4	278.9	279.4	279.6	279.6	279.6
110°	316.6	316.8	317.0	317.1	317.0	316.8	316.6	316.5	316.6	317.1	317.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	353.4	353.2	352.9	352.7	352.9	353.2	353.4	353.6	354.0	354.7	355.3
115°	409.0	408.0	407.0	406.0	407.0	408.0	409.0	410.0	410.8	411.5	412.1
117.5°	464.2	463.8	463.4	463.0	463.4	463.8	464.2	464.7	465.3	466.2	467.0
120°	500.4	499.6	498.8	497.9	498.8	499.6	500.4	501.2	501.8	502.1	502.5
122.5°	534.0	533.0	532.1	531.1	532.1	533.0	534.0	534.9	535.6	535.9	536.2
125°	583.1	582.6	582.2	581.7	582.2	582.6	583.1	583.6	584.2	584.9	585.5
127.5°	627.8	626.6	625.4	624.2	625.4	626.6	627.8	629.1	629.9	630.2	630.6
130°	657.5	656.7	655.8	655.0	655.8	656.7	657.5	658.3	659.0	659.5	660.0
132.5°	685.9	685.1	684.3	683.5	684.3	685.1	685.9	686.8	687.2	687.3	687.4
135°	725.4	724.4	723.4	722.4	723.4	724.4	725.4	726.4	727.1	727.4	727.7
137.5°	764.1	763.3	762.4	761.6	762.4	763.3	764.1	765.0	765.4	765.3	765.3
140°	787.6	786.7	785.7	784.7	785.7	786.7	787.6	788.6	789.0	788.6	788.3
142.5°	809.6	808.6	807.6	806.6	807.6	808.6	809.6	810.6	811.0	811.0	810.9
145°	841.7	840.7	839.8	838.8	839.8	840.7	841.7	842.7	843.1	843.0	842.8
147.5°	868.9	867.7	866.5	865.3	866.5	867.7	868.9	870.0	870.5	870.3	870.1
150°	886.4	885.1	883.8	882.5	883.8	885.1	886.4	887.8	888.3	887.9	887.6
152.5°	902.0	900.9	899.7	898.5	899.7	900.9	902.0	903.2	903.7	903.3	903.0
155°	923.5	922.2	920.9	919.5	920.9	922.2	923.5	924.8	925.2	924.7	924.2
157.5°	941.1	939.8	938.5	937.2	938.5	939.8	941.1	942.4	942.8	942.3	941.8
160°	952.4	951.1	949.8	948.4	949.8	951.1	952.4	953.7	954.0	953.4	952.7
162.5°	962.9	961.4	960.0	958.5	960.0	961.4	962.9	964.3	964.6	963.6	962.7
165°	976.1	974.8	973.5	972.1	973.5	974.8	976.1	977.4	977.6	976.6	975.6
167.5°	986.1	984.6	983.1	981.6	983.1	984.6	986.1	987.6	987.7	986.5	985.3
170°	991.4	989.9	988.4	987.0	988.4	989.9	991.4	992.9	993.0	991.7	990.3
172.5°	995.0	993.5	992.0	990.5	992.0	993.5	995.0	996.4	996.6	995.4	994.2
175°	999.6	998.1	996.6	995.1	996.6	998.1	999.6	1001.0	1001.1	999.8	998.5
177.5°	1000.9	999.9	998.8	997.8	998.8	999.9	1000.9	1002.0	1002.1	1001.1	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1576.1	1582.1	1585.3	1592.9	1603.7	1609.1	1616.6	1622.0	1629.6	1638.8	1646.3
5°	1474.1	1490.3	1501.1	1517.9	1533.5	1549.0	1568.6	1582.7	1601.6	1623.2	1640.1
7.5°	1379.3	1399.6	1417.5	1439.8	1465.4	1485.4	1510.9	1537.0	1566.5	1597.2	1626.1
10°	1318.8	1339.1	1361.4	1389.0	1414.7	1441.7	1472.0	1502.4	1539.5	1574.0	1613.1
12.5°	1258.9	1281.3	1306.3	1337.2	1368.2	1402.8	1433.7	1467.9	1507.7	1552.4	1594.2
15°	1184.5	1206.1	1233.1	1259.4	1295.2	1333.0	1374.2	1419.4	1463.9	1513.9	1565.9
17.5°	1104.7	1128.5	1158.2	1188.7	1226.4	1270.6	1311.0	1360.5	1410.6	1468.8	1530.0
20°	1052.9	1077.2	1112.3	1146.1	1180.5	1223.7	1271.6	1322.2	1375.5	1437.0	1505.1
22.5°	1011.9	1029.2	1063.7	1098.0	1138.4	1182.6	1229.5	1282.3	1340.4	1404.0	1475.4
25°	951.0	971.2	996.2	1032.0	1073.8	1120.4	1167.6	1223.7	1287.1	1351.9	1428.2
27.5°	896.9	913.5	938.2	966.2	1008.0	1056.3	1106.5	1164.9	1230.0	1296.0	1376.2
30°	858.5	876.7	900.4	930.1	963.1	1015.8	1067.1	1124.5	1190.6	1258.8	1341.1
32.5°	825.0	843.8	864.2	892.3	928.0	974.8	1027.7	1084.0	1151.2	1221.5	1301.7
35°	778.2	791.0	809.9	837.6	872.7	910.5	964.5	1023.9	1089.4	1162.3	1242.6
37.5°	724.5	741.1	759.8	783.9	814.7	855.6	905.8	965.8	1026.6	1096.4	1169.7
40°	693.2	708.7	729.6	747.2	779.6	816.7	862.6	925.3	986.1	1051.6	1118.4
42.5°	661.3	676.3	694.0	715.8	745.0	781.0	823.7	882.1	947.2	1008.9	1064.9
45°	611.5	627.0	643.9	664.1	691.1	726.2	768.8	822.1	878.8	935.5	978.0
47.5°	563.8	578.4	594.4	615.1	640.0	673.9	711.9	759.0	814.1	862.3	892.7
50°	529.8	543.3	560.9	581.1	605.4	637.1	673.6	720.2	766.1	809.9	837.6
52.5°	496.4	511.5	529.0	546.6	569.8	601.5	635.3	675.3	719.1	754.9	777.7
55°	446.1	460.3	476.5	494.7	517.7	544.7	580.5	612.2	646.6	677.0	690.5
57.5°	397.7	410.1	425.3	444.2	464.9	490.0	518.4	548.9	573.2	594.6	609.9
60°	365.8	376.6	390.8	407.0	429.3	452.2	477.9	506.2	525.1	543.3	557.5
62.5°	333.4	343.7	357.3	371.9	391.5	412.8	437.4	460.3	478.7	491.0	507.3
65°	284.8	294.9	306.4	321.9	337.5	355.0	377.3	394.2	407.0	420.5	430.6
67.5°	239.6	248.0	258.9	271.1	284.2	301.0	318.3	332.3	341.1	349.2	361.4
70°	209.9	216.7	225.4	234.9	249.1	265.9	279.4	290.2	296.3	304.4	319.2
72.5°	179.7	187.5	195.7	205.2	216.7	230.8	242.7	253.5	257.4	263.9	273.4
75°	141.7	145.8	152.5	159.3	167.4	179.5	191.0	193.7	197.1	202.5	209.2
77.5°	107.2	110.8	113.5	118.0	124.5	134.2	140.3	144.3	145.1	147.1	153.8
80°	85.0	87.1	89.8	93.1	95.8	103.9	107.3	111.4	112.7	114.7	118.1
82.5°	62.4	64.4	66.0	68.8	73.2	76.4	79.8	83.8	84.1	85.6	86.3
85°	36.4	37.1	35.8	37.1	37.8	39.1	42.5	45.9	45.2	44.5	46.6
87.5°	15.5	15.3	14.6	15.9	14.6	14.9	14.7	15.0	15.8	16.6	17.4
90°	12.7	11.9	10.7	9.6	8.4	7.2	6.0	4.7	3.4	2.1	0.7
92.5°	12.7	11.9	10.8	9.8	8.8	7.8	7.7	8.6	9.6	10.5	11.4
95°	12.7	11.9	18.1	24.4	30.6	36.9	40.3	40.8	41.2	41.7	42.2
97.5°	31.8	36.5	48.8	61.2	73.6	86.0	91.7	90.8	90.0	89.1	88.2
100°	104.4	128.9	128.3	127.6	127.0	126.3	125.7	125.2	124.7	124.2	123.7
102.5°	159.9	164.5	164.1	163.7	163.3	162.9	162.4	161.8	161.2	160.5	159.9
105°	220.8	220.8	220.8	220.8	220.8	220.8	220.5	219.8	219.2	218.5	217.8
107.5°	279.5	279.5	279.2	278.8	278.5	278.2	278.0	278.0	278.0	278.0	278.0
110°	318.1	318.6	318.3	318.0	317.6	317.3	317.1	317.1	317.1	317.1	317.1



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	355.9	356.6	356.4	356.2	356.0	355.8	355.5	355.1	354.7	354.3	353.9
115°	412.8	413.5	413.3	413.1	413.0	412.8	412.3	411.5	410.7	409.8	409.0
117.5°	467.9	468.7	468.1	467.5	466.9	466.2	465.9	466.0	466.0	466.0	466.1
120°	502.8	503.1	502.6	502.1	501.6	501.1	501.0	501.1	501.3	501.5	501.6
122.5°	536.6	536.9	536.7	536.4	536.2	536.0	535.6	534.9	534.3	533.7	533.0
125°	586.2	586.8	586.8	586.8	586.8	586.8	586.3	585.1	584.0	582.8	581.7
127.5°	630.9	631.3	631.4	631.5	631.6	631.7	631.3	630.5	629.7	628.9	628.0
130°	660.4	660.9	660.8	660.6	660.4	660.3	659.8	659.0	658.1	657.3	656.5
132.5°	687.5	687.6	688.0	688.3	688.7	689.1	688.8	687.8	686.9	685.9	684.9
135°	728.0	728.4	728.7	729.0	729.4	729.7	729.4	728.4	727.4	726.4	725.4
137.5°	765.2	765.1	765.4	765.7	766.0	766.3	766.0	765.2	764.3	763.5	762.6
140°	788.0	787.6	787.8	788.0	788.1	788.3	788.2	787.9	787.6	787.2	786.9
142.5°	810.8	810.8	810.5	810.3	810.1	809.8	809.6	809.4	809.2	809.0	808.8
145°	842.6	842.5	842.5	842.5	842.5	842.5	842.3	842.0	841.7	841.3	841.0
147.5°	869.9	869.7	869.5	869.3	869.2	869.0	868.9	869.0	869.0	869.1	869.2
150°	887.3	886.9	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9
152.5°	902.7	902.3	902.0	901.7	901.4	901.0	901.2	902.0	902.7	903.4	904.1
155°	923.7	923.2	922.9	922.6	922.3	921.9	922.3	923.2	924.2	925.2	926.2
157.5°	941.3	940.7	940.7	940.7	940.6	940.6	940.9	941.5	942.1	942.7	943.2
160°	952.1	951.4	951.2	951.1	950.9	950.7	951.2	952.1	953.1	954.1	955.1
162.5°	961.8	960.9	960.7	960.6	960.4	960.2	960.6	961.6	962.6	963.6	964.6
165°	974.6	973.6	973.5	973.3	973.1	973.0	973.4	974.4	975.4	976.3	977.3
167.5°	984.1	983.0	982.8	982.6	982.5	982.3	982.7	983.8	984.8	985.8	986.8
170°	989.0	987.7	987.5	987.4	987.2	987.0	987.5	988.7	989.8	991.0	992.2
172.5°	993.0	991.9	991.6	991.3	991.0	990.7	991.1	992.2	993.4	994.6	995.7
175°	997.2	995.9	995.7	995.5	995.4	995.2	995.6	996.6	997.6	998.6	999.6
177.5°	999.3	998.4	998.2	998.1	998.0	997.8	998.2	999.0	999.8	1000.5	1001.3
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1652.3	1657.1	1664.1	1672.2	1678.7	1685.7	1689.5	1689.5	1692.8	1699.8	1709.0
5°	1657.0	1674.5	1691.4	1713.0	1729.9	1749.4	1764.3	1778.5	1791.3	1807.5	1824.4
7.5°	1655.6	1684.8	1715.2	1749.2	1786.7	1816.5	1847.2	1871.2	1895.0	1926.0	1950.4
10°	1650.2	1688.0	1729.2	1772.4	1819.6	1860.8	1897.9	1931.7	1964.1	1997.8	2028.2
12.5°	1640.5	1688.6	1738.9	1790.8	1850.4	1897.5	1945.5	1981.4	2019.2	2056.1	2093.5
15°	1625.9	1682.6	1743.4	1815.6	1888.5	1941.1	1988.4	2035.0	2070.0	2111.9	2147.7
17.5°	1595.8	1668.9	1745.3	1824.2	1894.3	1955.4	2005.0	2049.3	2086.7	2132.7	2181.3
20°	1578.0	1657.0	1736.6	1821.0	1887.8	1950.6	1998.5	2044.4	2091.0	2151.0	2210.4
22.5°	1553.2	1637.5	1722.0	1802.1	1872.7	1933.3	1982.8	2039.0	2100.1	2168.3	2240.1
25°	1513.9	1601.0	1684.7	1760.9	1829.8	1891.9	1959.4	2035.0	2109.2	2199.0	2302.2
27.5°	1464.1	1548.0	1622.7	1703.3	1771.7	1850.7	1934.9	2016.9	2123.9	2247.4	2376.3
30°	1426.8	1506.5	1577.3	1653.6	1731.2	1818.3	1912.8	2009.3	2136.9	2282.0	2435.2
32.5°	1383.6	1455.7	1526.0	1599.6	1689.1	1784.8	1885.2	2003.4	2155.8	2320.9	2479.5
35°	1308.7	1373.5	1441.7	1523.3	1618.5	1722.5	1850.7	1994.5	2178.7	2356.2	2498.6
37.5°	1230.1	1281.3	1349.7	1435.9	1539.5	1659.8	1805.3	1980.0	2169.3	2328.5	2389.2
40°	1169.7	1217.6	1289.8	1380.3	1482.8	1614.5	1777.8	1957.3	2147.7	2258.4	2253.6
42.5°	1109.7	1158.2	1227.7	1318.7	1425.6	1572.9	1741.1	1927.6	2088.3	2130.4	2042.5
45°	1017.8	1063.0	1131.2	1223.0	1337.7	1492.3	1669.1	1848.0	1950.6	1882.4	1708.3
47.5°	924.1	968.0	1031.3	1121.2	1246.5	1408.2	1575.4	1722.2	1736.6	1590.2	1381.3
50°	862.6	903.7	963.8	1059.7	1181.1	1339.1	1500.4	1615.8	1580.0	1401.2	1185.9
52.5°	802.6	842.2	898.5	988.9	1113.1	1267.8	1411.8	1502.4	1419.7	1229.5	1035.8
55°	714.1	751.9	808.6	891.6	1004.3	1146.1	1272.3	1305.3	1183.8	992.2	835.6
57.5°	630.0	657.7	713.7	787.1	895.8	1020.8	1111.2	1105.3	971.2	798.6	686.3
60°	574.4	599.3	652.7	720.2	823.4	935.5	998.9	971.9	836.3	693.8	585.8
62.5°	522.5	545.9	590.6	652.7	741.4	838.8	885.0	847.7	719.6	594.5	508.6
65°	444.1	461.0	496.8	554.1	623.6	691.1	732.3	677.6	564.3	469.8	405.0
67.5°	370.8	385.4	417.2	458.4	506.3	552.9	569.7	518.4	430.2	366.5	320.9
70°	323.3	336.8	358.4	396.9	428.6	461.7	469.8	423.9	350.3	301.7	273.4
72.5°	277.9	290.4	309.3	336.4	358.4	377.4	381.2	338.6	282.3	248.8	226.9
75°	211.9	222.7	234.9	245.0	259.2	262.6	261.2	228.1	197.8	175.5	163.3
77.5°	155.8	160.2	167.7	171.7	172.4	172.1	165.2	144.3	128.6	119.5	114.5
80°	120.1	123.5	125.5	126.9	127.6	120.8	113.4	100.6	95.2	89.8	83.7
82.5°	87.2	89.5	91.5	91.8	88.1	82.5	75.6	69.2	65.5	62.8	60.5
85°	47.2	47.9	47.2	43.9	39.1	37.1	35.8	34.4	33.7	33.1	33.1
87.5°	17.2	15.8	13.4	14.2	14.4	14.1	14.3	14.0	13.7	13.9	14.0
90°	2.1	3.4	4.7	6.0	7.2	8.4	9.6	10.7	11.9	12.7	13.5
92.5°	10.5	9.6	8.6	7.7	7.8	8.8	9.8	10.8	11.9	12.7	13.5
95°	41.7	41.2	40.8	40.3	36.9	30.6	24.4	18.1	11.9	12.7	13.5
97.5°	89.1	90.0	90.8	91.7	86.0	73.6	61.2	48.8	36.5	31.8	27.2
100°	124.2	124.7	125.2	125.7	126.3	127.0	127.6	128.3	128.9	104.4	79.9
102.5°	160.5	161.2	161.8	162.4	162.9	163.3	163.7	164.1	164.5	159.9	155.2
105°	218.5	219.2	219.8	220.5	220.8	220.8	220.8	220.8	220.8	220.8	220.8
107.5°	278.0	278.0	278.0	278.0	278.2	278.5	278.8	279.2	279.5	279.5	279.6
110°	317.1	317.1	317.1	317.1	317.3	317.6	318.0	318.3	318.6	318.1	317.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	354.3	354.7	355.1	355.5	355.8	356.0	356.2	356.4	356.6	355.9	355.3
115°	409.8	410.7	411.5	412.3	412.8	413.0	413.1	413.3	413.5	412.8	412.1
117.5°	466.0	466.0	466.0	465.9	466.2	466.9	467.5	468.1	468.7	467.9	467.0
120°	501.5	501.3	501.1	501.0	501.1	501.6	502.1	502.6	503.1	502.8	502.5
122.5°	533.7	534.3	534.9	535.6	536.0	536.2	536.4	536.7	536.9	536.6	536.2
125°	582.8	584.0	585.1	586.3	586.8	586.8	586.8	586.8	586.8	586.2	585.5
127.5°	628.9	629.7	630.5	631.3	631.7	631.6	631.5	631.4	631.3	630.9	630.6
130°	657.3	658.1	659.0	659.8	660.3	660.4	660.6	660.8	660.9	660.4	660.0
132.5°	685.9	686.9	687.8	688.8	689.1	688.7	688.3	688.0	687.6	687.5	687.4
135°	726.4	727.4	728.4	729.4	729.7	729.4	729.0	728.7	728.4	728.0	727.7
137.5°	763.5	764.3	765.2	766.0	766.3	766.0	765.7	765.4	765.1	765.2	765.3
140°	787.2	787.6	787.9	788.2	788.3	788.1	788.0	787.8	787.6	788.0	788.3
142.5°	809.0	809.2	809.4	809.6	809.8	810.1	810.3	810.5	810.8	810.8	810.9
145°	841.3	841.7	842.0	842.3	842.5	842.5	842.5	842.5	842.5	842.6	842.8
147.5°	869.1	869.0	869.0	868.9	869.0	869.2	869.3	869.5	869.7	869.9	870.1
150°	886.6	886.3	885.9	885.6	885.6	885.9	886.3	886.6	886.9	887.3	887.6
152.5°	903.4	902.7	902.0	901.2	901.0	901.4	901.7	902.0	902.3	902.7	903.0
155°	925.2	924.2	923.2	922.3	921.9	922.3	922.6	922.9	923.2	923.7	924.2
157.5°	942.7	942.1	941.5	940.9	940.6	940.6	940.7	940.7	940.7	941.3	941.8
160°	954.1	953.1	952.1	951.2	950.7	950.9	951.1	951.2	951.4	952.1	952.7
162.5°	963.6	962.6	961.6	960.6	960.2	960.4	960.6	960.7	960.9	961.8	962.7
165°	976.3	975.4	974.4	973.4	973.0	973.1	973.3	973.5	973.6	974.6	975.6
167.5°	985.8	984.8	983.8	982.7	982.3	982.5	982.6	982.8	983.0	984.1	985.3
170°	991.0	989.8	988.7	987.5	987.0	987.2	987.4	987.5	987.7	989.0	990.3
172.5°	994.6	993.4	992.2	991.1	990.7	991.0	991.3	991.6	991.9	993.0	994.2
175°	998.6	997.6	996.6	995.6	995.2	995.4	995.5	995.7	995.9	997.2	998.5
177.5°	1000.5	999.8	999.0	998.2	997.8	998.0	998.1	998.2	998.4	999.3	1000.2
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6	999.6



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2	1644.2
2.5°	1716.0	1716.0	1725.2	1724.6	1730.6	1728.4	1729.5
5°	1844.6	1856.1	1866.2	1873.0	1883.1	1885.8	1884.4
7.5°	1978.0	2003.5	2015.9	2032.9	2036.0	2044.9	2044.0
10°	2060.6	2085.6	2104.5	2119.3	2126.7	2136.2	2136.9
12.5°	2125.4	2146.6	2163.3	2177.1	2186.1	2189.1	2190.9
15°	2176.0	2199.6	2219.2	2238.8	2250.3	2259.0	2263.8
17.5°	2227.0	2263.5	2298.0	2324.6	2340.6	2354.1	2353.9
20°	2266.5	2308.3	2351.5	2381.9	2412.9	2426.4	2428.4
22.5°	2308.6	2372.6	2428.2	2475.3	2516.0	2530.1	2535.4
25°	2396.0	2479.7	2565.5	2631.6	2678.8	2706.5	2710.6
27.5°	2501.7	2615.0	2705.2	2766.2	2805.5	2826.0	2830.4
30°	2576.3	2680.9	2761.9	2807.8	2826.0	2828.7	2818.6
32.5°	2609.7	2687.9	2720.3	2717.6	2681.8	2658.1	2649.0
35°	2568.8	2552.6	2473.7	2379.2	2307.0	2261.1	2248.9
37.5°	2337.7	2198.0	2052.8	1910.0	1834.0	1795.3	1728.9
40°	2109.9	1910.8	1759.6	1639.4	1553.7	1484.9	1468.7
42.5°	1852.9	1647.3	1496.1	1393.2	1324.8	1277.5	1257.0
45°	1488.9	1312.1	1187.2	1108.3	1055.6	1021.2	1005.7
47.5°	1190.9	1054.0	963.0	904.6	864.5	834.5	826.1
50°	1027.3	917.9	841.0	791.7	761.3	738.4	728.9
52.5°	892.3	804.0	744.9	704.2	675.5	661.2	653.3
55°	736.4	660.1	617.6	585.2	569.0	557.5	552.1
57.5°	602.2	547.1	516.1	493.7	478.7	471.4	468.7
60°	527.1	483.9	455.6	438.0	427.9	418.5	415.8
62.5°	460.7	426.7	404.8	389.4	379.3	375.3	373.6
65°	371.2	348.9	332.7	323.3	315.2	313.8	313.2
67.5°	295.1	282.0	273.5	263.6	260.8	256.1	255.1
70°	252.4	243.7	233.5	230.2	226.8	222.1	222.7
72.5°	214.1	205.3	198.4	194.0	192.8	190.7	192.5
75°	156.6	153.9	151.2	147.8	146.5	146.5	145.8
77.5°	111.8	109.5	106.5	104.5	104.1	101.2	102.3
80°	81.0	77.6	76.3	76.9	74.9	74.2	74.2
82.5°	59.9	58.7	57.4	57.5	57.1	56.4	57.0
85°	33.1	32.4	32.4	31.7	31.7	31.0	31.0
87.5°	14.7	15.4	14.5	14.1	14.2	14.8	15.4
90°	14.3	15.1	15.8	16.3	16.8	17.3	17.8
92.5°	14.3	15.1	15.7	15.9	16.1	16.4	16.6
95°	14.3	15.1	15.6	15.6	15.6	15.6	15.6
97.5°	22.5	17.9	15.6	15.6	15.6	15.6	15.6
100°	55.3	30.8	18.2	17.5	16.9	16.2	15.6
102.5°	150.6	145.9	138.0	126.8	115.6	104.4	93.2
105°	220.8	220.8	220.7	220.6	220.4	220.2	220.1
107.5°	279.6	279.6	279.4	278.9	278.4	277.9	277.4
110°	317.1	316.6	316.5	316.6	316.8	317.0	317.1



TEST NUMBER: P333704

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	354.7	354.0	353.6	353.4	353.2	352.9	352.7
115°	411.5	410.8	410.0	409.0	408.0	407.0	406.0
117.5°	466.2	465.3	464.7	464.2	463.8	463.4	463.0
120°	502.1	501.8	501.2	500.4	499.6	498.8	497.9
122.5°	535.9	535.6	534.9	534.0	533.0	532.1	531.1
125°	584.9	584.2	583.6	583.1	582.6	582.2	581.7
127.5°	630.2	629.9	629.1	627.8	626.6	625.4	624.2
130°	659.5	659.0	658.3	657.5	656.7	655.8	655.0
132.5°	687.3	687.2	686.8	685.9	685.1	684.3	683.5
135°	727.4	727.1	726.4	725.4	724.4	723.4	722.4
137.5°	765.3	765.4	765.0	764.1	763.3	762.4	761.6
140°	788.6	789.0	788.6	787.6	786.7	785.7	784.7
142.5°	811.0	811.0	810.6	809.6	808.6	807.6	806.6
145°	843.0	843.1	842.7	841.7	840.7	839.8	838.8
147.5°	870.3	870.5	870.0	868.9	867.7	866.5	865.3
150°	887.9	888.3	887.8	886.4	885.1	883.8	882.5
152.5°	903.3	903.7	903.2	902.0	900.9	899.7	898.5
155°	924.7	925.2	924.8	923.5	922.2	920.9	919.5
157.5°	942.3	942.8	942.4	941.1	939.8	938.5	937.2
160°	953.4	954.0	953.7	952.4	951.1	949.8	948.4
162.5°	963.6	964.6	964.3	962.9	961.4	960.0	958.5
165°	976.6	977.6	977.4	976.1	974.8	973.5	972.1
167.5°	986.5	987.7	987.6	986.1	984.6	983.1	981.6
170°	991.7	993.0	992.9	991.4	989.9	988.4	987.0
172.5°	995.4	996.6	996.4	995.0	993.5	992.0	990.5
175°	999.8	1001.1	1001.0	999.6	998.1	996.6	995.1
177.5°	1001.1	1002.1	1002.0	1000.9	999.9	998.8	997.8
180°	999.6	999.6	999.6	999.6	999.6	999.6	999.6

(END OF REPORT)