

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333707

Luminaire Tested: **S125RDIW-S1090D770U835-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P333707  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S125RDIW-S1090D770U835-4F0-1E-UDD-F1  
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1090 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 770 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6886.5 lumens  
Efficiency: N/A  
Efficacy: 128.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25  
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	61
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	59	58	57	52
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	52	50	48	44
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	41	38
4	77	66	58	52	72	62	55	50	55	49	45	48	44	40	42	39	36	33
5	71	59	51	45	66	56	48	43	49	43	39	43	39	35	38	34	31	28
6	65	53	45	39	61	50	43	37	45	39	34	39	35	31	34	31	28	25
7	60	48	40	34	57	45	38	33	41	35	30	36	31	27	32	28	25	22
8	56	44	36	31	53	41	34	29	37	31	27	33	28	25	29	25	22	20
9	52	40	33	27	49	38	31	26	34	28	24	30	26	22	27	23	20	18
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11544	11544	11544
5°	11570	11439	11509
10°	11482	11332	11332
15°	11346	11102	11012
20°	11171	10781	10652
25°	10967	10467	10236
30°	10712	10097	9775
35°	10452	9717	9260
40°	10209	9321	8752
45°	9913	8878	8199
50°	9616	8396	7623
55°	9272	7935	7007
60°	8928	7375	6347
65°	8520	6725	5590
70°	8055	5914	4817
75°	7411	4986	4007
80°	6527	3916	3362
85°	5498	3201	3001



TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	168.1	2.4
10°-20°	469.7	6.8
20°-30°	681.1	9.9
30°-40°	776.2	11.3
40°-50°	756.6	11.0
50°-60°	636.9	9.2
60°-70°	446.5	6.5
70°-80°	229.5	3.3
80°-90°	60.0	0.9
90°-100°	63.9	0.9
100°-110°	188.7	2.7
110°-120°	319.6	4.6
120°-130°	420.6	6.1
130°-140°	471.2	6.8
140°-150°	461.9	6.7
150°-160°	387.9	5.6
160°-170°	257.9	3.7
170°-180°	90.2	1.3
0°-30°	1318.9	19.2
0°-40°	2095.1	30.4
0°-60°	3488.6	50.7
0°-90°	4224.6	61.3
90°-120°	572.1	8.3
90°-150°	1925.8	28.0
90°-180°	2662.0	38.7
0°-180°	6886.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1787	1787	1787	1787	1787	
5°	1785	1779	1764	1777	1775	169
15°	1697	1688	1660	1659	1647	478
25°	1539	1517	1469	1451	1436	708
35°	1326	1292	1232	1194	1174	830
45°	1085	1044	972	920	898	837
55°	824	778	705	646	622	736
65°	558	510	440	388	366	552
75°	297	256	200	171	161	314
85°	74	51	43	42	40	83
90°	1	7	12	16	18	6
95°	48	50	57	62	64	52
105°	169	173	177	182	184	181
115°	320	323	324	324	323	316
125°	467	471	472	471	470	418
135°	607	612	612	612	610	468
145°	736	739	741	741	739	460
155°	842	842	843	845	842	388
165°	915	914	915	917	913	258
175°	952	949	949	953	948	90
180°	954	954	954	954	954	



TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1790.6	1789.9	1789.2	1788.4	1787.7	1786.2	1783.8	1781.4	1779.0	1776.6	1779.0
5°	1784.7	1783.5	1782.3	1781.1	1779.9	1777.6	1774.3	1771.0	1767.7	1764.4	1767.4
7.5°	1767.1	1766.0	1764.8	1763.7	1762.5	1760.0	1756.0	1752.1	1748.1	1744.2	1746.3
10°	1750.9	1750.0	1749.1	1748.2	1747.3	1744.8	1740.6	1736.4	1732.2	1728.0	1728.9
12.5°	1732.5	1731.4	1730.3	1729.1	1728.0	1724.6	1719.0	1713.3	1707.7	1702.0	1702.7
15°	1696.9	1695.1	1693.3	1691.5	1689.7	1685.7	1679.4	1673.1	1666.8	1660.5	1660.2
17.5°	1656.7	1653.9	1651.2	1648.4	1645.6	1640.3	1632.4	1624.5	1616.5	1608.6	1607.1
20°	1625.4	1622.4	1619.4	1616.4	1613.4	1607.1	1597.5	1587.9	1578.3	1568.7	1567.2
22.5°	1590.8	1587.8	1584.8	1581.8	1578.8	1572.3	1562.2	1552.1	1542.0	1531.9	1529.0
25°	1539.0	1534.5	1530.0	1525.5	1521.0	1513.2	1502.1	1491.0	1479.9	1468.8	1464.9
27.5°	1479.6	1474.1	1468.6	1463.2	1457.7	1449.1	1437.2	1425.3	1413.4	1401.5	1396.1
30°	1436.4	1430.7	1425.0	1419.3	1413.6	1404.4	1391.8	1379.2	1366.6	1354.0	1347.1
32.5°	1394.2	1387.6	1380.9	1374.3	1367.6	1357.9	1345.0	1332.2	1319.3	1306.5	1298.9
35°	1325.7	1318.5	1311.3	1304.1	1296.9	1286.5	1273.0	1259.5	1246.0	1232.5	1223.8
37.5°	1258.4	1249.7	1240.9	1232.2	1223.4	1212.1	1198.1	1184.2	1170.3	1156.4	1145.9
40°	1210.9	1201.9	1192.9	1183.9	1174.9	1163.2	1148.8	1134.4	1120.0	1105.6	1094.2
42.5°	1161.2	1152.0	1142.8	1133.5	1124.3	1112.2	1097.3	1082.5	1067.6	1052.7	1041.8
45°	1085.4	1076.7	1068.0	1059.3	1050.6	1038.0	1021.5	1005.0	988.5	972.0	960.0
47.5°	1006.8	997.6	988.4	979.3	970.1	957.2	940.6	923.9	907.3	890.7	878.3
50°	957.1	947.2	937.3	927.4	917.5	904.0	886.9	869.8	852.7	835.6	823.0
52.5°	903.1	893.0	882.8	872.7	862.6	849.4	833.3	817.1	801.0	784.9	771.3
55°	823.5	813.9	804.3	794.7	785.1	771.9	755.1	738.3	721.5	704.7	691.2
57.5°	743.0	732.8	722.5	712.2	702.0	688.8	672.6	656.4	640.2	624.0	610.8
60°	691.2	680.7	670.2	659.7	649.2	635.8	619.6	603.4	587.2	571.0	557.8
62.5°	636.1	626.1	616.1	606.0	596.0	582.8	566.4	549.9	533.5	517.0	504.8
65°	557.5	547.3	537.1	526.9	516.7	503.7	487.8	471.9	456.0	440.1	428.1
67.5°	479.5	469.3	459.1	448.9	438.7	426.0	410.7	395.5	380.3	365.0	354.1
70°	426.6	416.4	406.2	396.0	385.8	373.2	358.2	343.2	328.2	313.2	303.9
72.5°	374.8	364.8	354.8	344.9	334.9	322.9	308.9	294.8	280.8	266.8	258.2
75°	297.0	288.0	279.0	270.0	261.0	250.2	237.6	225.0	212.4	199.8	193.2
77.5°	219.8	212.6	205.4	198.2	191.0	182.3	172.3	162.2	152.1	142.0	137.4
80°	175.5	168.3	161.1	153.9	146.7	138.9	130.5	122.1	113.7	105.3	102.6
82.5°	132.3	125.8	119.3	112.9	106.4	100.3	94.5	88.7	83.0	77.2	76.0
85°	74.2	68.8	63.4	58.0	52.6	49.2	47.7	46.2	44.7	43.2	42.9
87.5°	25.0	23.6	22.2	20.7	19.3	18.6	18.6	18.6	18.6	18.6	18.7
90°	0.7	2.1	3.4	4.7	6.0	7.3	8.4	9.6	10.7	11.9	12.7
92.5°	18.0	18.9	19.8	20.7	21.7	22.8	24.3	25.7	27.1	28.5	29.6
95°	48.3	48.6	48.9	49.2	49.6	50.6	52.2	53.9	55.5	57.2	58.3
97.5°	80.2	80.3	80.4	80.6	80.7	81.9	84.2	86.5	88.7	91.0	92.1
100°	103.9	103.9	103.9	103.9	103.9	105.0	107.1	109.3	111.4	113.6	115.1
102.5°	129.5	130.1	130.8	131.4	132.1	133.0	134.1	135.2	136.2	137.3	139.0
105°	169.3	170.1	170.9	171.7	172.6	173.5	174.5	175.4	176.4	177.4	178.4
107.5°	213.2	214.0	214.9	215.7	216.5	217.3	218.1	218.8	219.6	220.3	220.8
110°	243.5	244.3	245.1	246.0	246.8	247.4	247.9	248.4	248.9	249.4	249.9



TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	274.4	274.8	275.2	275.7	276.1	276.6	277.2	277.9	278.5	279.1	279.4
115°	320.0	320.6	321.3	321.9	322.6	323.1	323.4	323.7	324.1	324.4	324.2
117.5°	365.7	366.0	366.3	366.6	366.9	367.2	367.5	367.8	368.1	368.4	368.5
120°	394.2	395.0	395.8	396.7	397.5	398.0	398.1	398.3	398.5	398.6	398.6
122.5°	425.1	425.4	425.7	426.0	426.3	426.6	427.0	427.5	427.9	428.3	428.2
125°	466.9	467.9	468.9	469.9	470.9	471.5	471.6	471.8	472.0	472.1	471.8
127.5°	511.5	512.0	512.6	513.2	513.7	514.1	514.3	514.5	514.7	514.9	514.7
130°	538.2	539.0	539.9	540.7	541.5	542.1	542.4	542.7	543.1	543.4	543.2
132.5°	564.9	566.3	567.6	569.0	570.3	571.0	570.9	570.8	570.8	570.7	570.6
135°	607.2	608.2	609.2	610.2	611.2	611.8	611.9	612.1	612.3	612.4	612.4
137.5°	647.0	648.0	648.9	649.9	650.9	651.5	651.9	652.2	652.6	653.0	653.2
140°	672.6	673.4	674.2	675.0	675.9	676.5	677.0	677.5	678.0	678.5	678.8
142.5°	698.1	698.8	699.5	700.2	700.9	701.5	702.2	702.8	703.4	704.0	704.2
145°	735.7	736.3	737.0	737.6	738.3	738.9	739.4	739.9	740.4	740.9	740.9
147.5°	770.4	770.8	771.1	771.5	771.9	772.2	772.6	773.0	773.4	773.8	774.2
150°	793.6	793.4	793.2	793.1	792.9	793.2	793.8	794.5	795.1	795.8	795.8
152.5°	812.6	812.8	813.0	813.3	813.5	813.7	814.0	814.3	814.5	814.8	815.2
155°	841.8	841.8	841.8	841.8	841.8	841.9	842.1	842.2	842.4	842.6	843.2
157.5°	868.0	867.6	867.2	866.9	866.5	866.4	866.6	866.7	866.9	867.1	867.7
160°	883.4	882.9	882.4	881.9	881.4	881.2	881.4	881.6	881.7	881.9	882.6
162.5°	897.1	896.7	896.3	896.0	895.6	895.4	895.5	895.5	895.5	895.6	896.4
165°	915.3	915.0	914.7	914.3	914.0	913.9	914.1	914.2	914.4	914.6	915.2
167.5°	930.8	930.1	929.4	928.8	928.1	927.8	927.8	927.8	927.8	927.8	928.8
170°	939.1	938.4	937.7	937.1	936.4	936.1	936.1	936.1	936.1	936.1	937.1
172.5°	945.0	944.3	943.7	943.0	942.4	942.0	942.0	942.0	942.0	942.0	943.0
175°	951.7	951.0	950.4	949.7	949.0	948.7	948.7	948.7	948.7	948.7	949.7
177.5°	955.1	954.6	954.0	953.5	953.0	952.7	952.5	952.4	952.3	952.1	952.9
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9



TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4	1787.4
2.5°	1781.4	1783.8	1786.2	1787.2	1787.0	1786.8	1786.5	1786.3
5°	1770.4	1773.4	1776.4	1777.6	1777.0	1776.4	1775.8	1775.2
7.5°	1748.4	1750.5	1752.6	1753.3	1752.6	1752.0	1751.3	1750.6
10°	1729.8	1730.7	1731.6	1731.6	1730.7	1729.8	1728.9	1728.0
12.5°	1703.4	1704.0	1704.7	1704.3	1702.9	1701.6	1700.2	1698.8
15°	1659.9	1659.6	1659.3	1657.8	1655.1	1652.4	1649.7	1647.0
17.5°	1605.6	1604.1	1602.6	1600.8	1598.5	1596.3	1594.1	1591.9
20°	1565.7	1564.2	1562.7	1560.6	1557.9	1555.2	1552.5	1549.8
22.5°	1526.1	1523.1	1520.2	1517.6	1515.4	1513.2	1510.9	1508.7
25°	1461.0	1457.1	1453.2	1449.6	1446.3	1443.0	1439.7	1436.4
27.5°	1390.6	1385.2	1379.7	1375.4	1372.2	1369.0	1365.8	1362.7
30°	1340.2	1333.3	1326.4	1321.6	1318.9	1316.2	1313.5	1310.8
32.5°	1291.3	1283.6	1276.0	1270.5	1267.1	1263.7	1260.2	1256.8
35°	1215.1	1206.4	1197.7	1191.3	1187.1	1182.9	1178.7	1174.5
37.5°	1135.5	1125.1	1114.6	1107.4	1103.3	1099.2	1095.1	1091.0
40°	1082.8	1071.4	1060.0	1052.5	1048.9	1045.3	1041.7	1038.1
42.5°	1030.9	1019.9	1009.0	1000.9	995.6	990.4	985.1	979.8
45°	948.0	936.0	924.0	915.7	911.2	906.7	902.2	897.7
47.5°	866.0	853.6	841.3	832.6	827.6	822.6	817.7	812.7
50°	810.4	797.8	785.2	776.7	772.2	767.7	763.2	758.7
52.5°	757.8	744.2	730.6	721.6	717.1	712.6	708.1	703.6
55°	677.7	664.2	650.7	641.5	636.7	631.9	627.1	622.3
57.5°	597.6	584.4	571.2	562.4	558.2	553.9	549.6	545.4
60°	544.6	531.4	518.2	509.4	504.9	500.4	495.9	491.4
62.5°	492.6	480.3	468.1	459.7	455.2	450.7	446.2	441.7
65°	416.1	404.1	392.1	383.8	379.3	374.8	370.3	365.8
67.5°	343.1	332.1	321.1	313.8	310.2	306.6	303.0	299.4
70°	294.6	285.3	276.0	269.5	265.9	262.3	258.7	255.1
72.5°	249.6	241.0	232.4	226.9	224.5	222.1	219.7	217.3
75°	186.6	180.0	173.4	169.0	166.9	164.8	162.7	160.6
77.5°	132.8	128.2	123.5	120.4	118.9	117.3	115.8	114.2
80°	99.9	97.2	94.5	92.8	92.2	91.6	91.0	90.4
82.5°	74.7	73.4	72.2	71.4	71.0	70.6	70.3	69.9
85°	42.6	42.3	42.0	41.7	41.4	41.1	40.8	40.5
87.5°	18.9	19.1	19.2	19.2	19.1	19.0	18.8	18.7
90°	13.5	14.4	15.2	15.8	16.3	16.8	17.3	17.8
92.5°	30.7	31.8	32.9	33.6	34.0	34.3	34.7	35.0
95°	59.5	60.6	61.8	62.5	62.9	63.2	63.5	63.8
97.5°	93.2	94.3	95.4	96.0	96.2	96.4	96.6	96.8
100°	116.5	118.0	119.5	120.4	120.8	121.1	121.4	121.7
102.5°	140.6	142.2	143.8	144.8	145.3	145.8	146.2	146.7
105°	179.4	180.4	181.4	182.1	182.6	183.1	183.6	184.1
107.5°	221.3	221.8	222.3	222.5	222.5	222.5	222.4	222.4
110°	250.4	250.9	251.4	251.6	251.4	251.2	251.1	250.9





TEST NUMBER: P333707

CATALOG NUMBER: S125RDIW-S1090D770U835-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	279.6	279.8	280.0	280.0	279.7	279.4	279.1	278.8
115°	324.1	323.9	323.7	323.6	323.4	323.3	323.1	322.9
117.5°	368.6	368.7	368.9	368.6	368.0	367.3	366.6	366.0
120°	398.6	398.6	398.6	398.3	397.7	397.0	396.3	395.7
122.5°	428.1	427.9	427.8	427.5	426.9	426.4	425.9	425.4
125°	471.5	471.1	470.8	470.6	470.4	470.2	470.1	469.9
127.5°	514.6	514.4	514.2	514.0	513.7	513.3	513.0	512.7
130°	543.1	542.9	542.7	542.5	542.2	541.8	541.5	541.2
132.5°	570.4	570.2	570.1	569.7	569.3	568.8	568.4	567.9
135°	612.4	612.4	612.4	612.1	611.4	610.8	610.1	609.5
137.5°	653.4	653.6	653.8	653.4	652.6	651.8	651.0	650.1
140°	679.2	679.5	679.8	679.6	678.8	677.9	677.1	676.3
142.5°	704.4	704.6	704.8	704.5	703.7	702.9	702.0	701.2
145°	740.9	740.9	740.9	740.6	740.1	739.6	739.1	738.6
147.5°	774.6	775.0	775.4	775.0	773.9	772.8	771.7	770.6
150°	795.8	795.8	795.8	795.6	795.3	795.0	794.6	794.3
152.5°	815.6	816.0	816.4	816.3	815.7	815.1	814.5	813.9
155°	843.9	844.5	845.2	845.1	844.3	843.5	842.6	841.8
157.5°	868.4	869.0	869.7	869.5	868.4	867.3	866.2	865.1
160°	883.2	883.9	884.5	884.5	883.6	882.8	882.0	881.2
162.5°	897.2	897.9	898.7	898.7	897.7	896.7	895.8	894.8
165°	915.9	916.6	917.2	917.0	916.1	915.1	914.1	913.1
167.5°	929.8	930.8	931.7	931.7	930.7	929.7	928.7	927.6
170°	938.1	939.1	940.1	940.0	938.8	937.7	936.5	935.4
172.5°	944.0	945.0	946.0	946.0	945.0	943.9	942.9	941.9
175°	950.7	951.7	952.7	952.6	951.4	950.3	949.1	948.0
177.5°	953.7	954.5	955.3	955.2	954.3	953.4	952.5	951.5
180°	953.9	953.9	953.9	953.9	953.9	953.9	953.9	953.9

(END OF REPORT)