

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P333675-927

Luminaire Tested: **S125RDIW-S610D1340U927-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P333675-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-11,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S125RDIW-S610D1340U927-4F0-1E-UDD-F1
Description: DEFINE 5 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 610 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1340 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5570.2 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.11 / 1.25
Luminous Opening: Rectangular (W 0.42' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34
1	94	90	86	83	85	81	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	30	24
3	78	69	62	57	71	63	57	52	51	46	43	39	36	34	29	27	25	21
4	72	61	54	48	65	56	49	44	45	40	37	35	32	29	26	24	22	18
5	66	55	47	41	59	50	43	38	40	35	31	31	28	25	23	21	19	16
6	61	49	41	36	55	45	38	33	36	31	27	28	25	22	21	19	17	14
7	56	44	36	31	50	40	33	29	33	28	24	26	22	20	19	17	15	12
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	15	14	11
9	48	36	29	24	44	33	27	23	27	22	19	22	18	16	16	14	12	10
10	45	33	26	22	41	30	24	20	25	20	17	20	17	14	15	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5147	5147	5147
5°	5159	5100	5131
10°	5119	5052	5052
15°	5059	4950	4910
20°	4981	4807	4748
25°	4890	4666	4563
30°	4776	4502	4359
35°	4660	4332	4128
40°	4552	4156	3903
45°	4420	3958	3656
50°	4287	3744	3399
55°	4135	3538	3125
60°	3981	3289	2830
65°	3799	2998	2492
70°	3592	2638	2149
75°	3306	2221	1787
80°	2912	1748	1499
85°	2453	1430	1341



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	1.3
10°-20°	209.4	3.8
20°-30°	303.7	5.5
30°-40°	346.1	6.2
40°-50°	337.4	6.1
50°-60°	284.0	5.1
60°-70°	199.1	3.6
70°-80°	102.3	1.8
80°-90°	28.7	0.5
90°-100°	88.4	1.6
100°-110°	261.2	4.7
110°-120°	442.4	7.9
120°-130°	582.2	10.5
130°-140°	652.3	11.7
140°-150°	639.3	11.5
150°-160°	537.0	9.6
160°-170°	357.0	6.4
170°-180°	124.9	2.2
0°-30°	588.0	10.6
0°-40°	934.1	16.8
0°-60°	1555.4	27.9
0°-90°	1885.5	33.9
90°-120°	792.0	14.2
90°-150°	2665.8	47.9
90°-180°	3685.0	66.2
0°-180°	5570.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	797	797	797	797	797	
5°	796	793	787	792	792	75
15°	757	752	740	739	734	213
25°	686	676	655	647	640	316
35°	591	576	550	533	524	370
45°	484	466	433	410	400	373
55°	367	347	314	288	278	328
65°	249	228	196	173	163	246
75°	132	114	89	76	72	140
85°	33	23	19	19	18	37
90°	1	9	16	21	25	5
95°	67	69	79	86	88	71
105°	234	239	246	252	255	250
115°	443	447	449	448	447	438
125°	646	652	654	652	650	579
135°	841	846	848	848	844	648
145°	1018	1022	1026	1025	1022	636
155°	1165	1165	1166	1170	1165	536
165°	1267	1265	1266	1270	1264	357
175°	1317	1314	1313	1319	1312	125
180°	1320	1320	1320	1320	1320	



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	798.4	798.0	797.7	797.4	797.1	796.4	795.3	794.2	793.1	792.1	793.1
5°	795.7	795.2	794.6	794.1	793.5	792.6	791.1	789.6	788.1	786.6	788.0
7.5°	787.9	787.3	786.9	786.3	785.8	784.7	782.9	781.2	779.4	777.6	778.6
10°	780.6	780.2	779.8	779.4	779.0	777.9	776.0	774.2	772.3	770.4	770.8
12.5°	772.5	772.0	771.4	771.0	770.4	768.9	766.4	763.9	761.4	758.8	759.1
15°	756.6	755.7	754.9	754.2	753.4	751.5	748.8	745.9	743.1	740.3	740.2
17.5°	738.6	737.4	736.2	735.0	733.7	731.3	727.8	724.3	720.7	717.2	716.5
20°	724.7	723.3	722.0	720.6	719.3	716.5	712.3	708.0	703.7	699.4	698.7
22.5°	709.2	707.9	706.6	705.3	703.9	701.0	696.5	692.1	687.5	683.0	681.8
25°	686.2	684.1	682.1	680.2	678.1	674.6	669.7	664.7	659.8	654.8	653.2
27.5°	659.7	657.3	654.8	652.4	649.9	646.1	640.8	635.5	630.2	624.9	622.4
30°	640.4	637.9	635.3	632.8	630.3	626.1	620.5	615.0	609.3	603.7	600.6
32.5°	621.6	618.7	615.7	612.8	609.7	605.4	599.7	594.0	588.2	582.5	579.1
35°	591.0	587.9	584.6	581.5	578.2	573.6	567.6	561.6	555.6	549.5	545.7
37.5°	561.1	557.1	553.3	549.4	545.5	540.4	534.2	528.0	521.8	515.6	511.0
40°	539.9	535.9	531.9	527.8	523.9	518.6	512.2	505.8	499.4	493.0	487.9
42.5°	517.8	513.7	509.5	505.4	501.3	495.9	489.3	482.6	476.0	469.4	464.5
45°	483.9	480.1	476.2	472.3	468.4	462.8	455.4	448.1	440.7	433.3	428.0
47.5°	448.9	444.8	440.7	436.7	432.5	426.7	419.4	411.9	404.6	397.1	391.7
50°	426.7	422.3	417.9	413.5	409.1	403.1	395.5	387.9	380.2	372.6	366.9
52.5°	402.7	398.2	393.6	389.1	384.6	378.7	371.5	364.3	357.1	349.9	343.9
55°	367.2	362.9	358.6	354.3	350.1	344.1	336.7	329.2	321.7	314.2	308.2
57.5°	331.3	326.7	322.1	317.6	313.0	307.0	299.8	292.6	285.4	278.2	272.3
60°	308.2	303.5	298.8	294.1	289.5	283.5	276.2	269.0	261.8	254.6	248.7
62.5°	283.6	279.2	274.6	270.2	265.8	259.8	252.5	245.2	237.9	230.5	225.1
65°	248.6	244.1	239.5	235.0	230.4	224.6	217.5	210.4	203.3	196.2	190.8
67.5°	213.8	209.2	204.7	200.2	195.6	190.0	183.2	176.3	169.5	162.7	157.9
70°	190.2	185.7	181.1	176.6	172.0	166.4	159.7	153.0	146.3	139.7	135.5
72.5°	167.1	162.6	158.2	153.8	149.3	143.9	137.7	131.4	125.2	118.9	115.1
75°	132.5	128.4	124.4	120.4	116.4	111.5	105.9	100.3	94.7	89.0	86.1
77.5°	98.0	94.7	91.6	88.3	85.2	81.3	76.8	72.3	67.8	63.3	61.2
80°	78.3	75.0	71.9	68.6	65.4	61.9	58.1	54.4	50.7	47.0	45.7
82.5°	59.0	56.1	53.2	50.3	47.5	44.7	42.1	39.5	37.0	34.5	33.9
85°	33.1	30.7	28.3	25.9	23.4	21.9	21.2	20.6	20.0	19.3	19.1
87.5°	11.2	10.9	10.5	10.1	9.7	9.7	9.9	10.1	10.3	10.5	10.8
90°	1.0	2.9	4.7	6.5	8.3	10.1	11.6	13.2	14.8	16.5	17.6
92.5°	24.9	26.1	27.4	28.7	29.9	31.6	33.6	35.6	37.5	39.5	41.0
95°	66.8	67.3	67.7	68.1	68.6	70.0	72.2	74.5	76.8	79.1	80.7
97.5°	111.0	111.1	111.4	111.5	111.7	113.4	116.5	119.7	122.9	126.0	127.5
100°	143.9	143.9	143.9	143.9	143.9	145.4	148.3	151.3	154.2	157.2	159.3
102.5°	179.2	180.1	181.0	182.0	182.8	184.1	185.6	187.1	188.6	190.1	192.3
105°	234.3	235.4	236.5	237.7	238.8	240.1	241.5	242.9	244.2	245.6	247.0
107.5°	295.1	296.3	297.4	298.6	299.7	300.8	301.8	302.9	304.0	305.0	305.7
110°	337.1	338.2	339.4	340.5	341.6	342.5	343.3	343.9	344.6	345.2	345.9



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	379.8	380.4	381.0	381.6	382.1	382.9	383.7	384.6	385.5	386.3	386.7
115°	442.9	443.8	444.7	445.6	446.6	447.3	447.7	448.1	448.6	449.1	448.9
117.5°	506.2	506.6	507.0	507.4	507.9	508.3	508.7	509.1	509.5	509.9	510.1
120°	545.7	546.8	548.0	549.1	550.2	550.9	551.1	551.4	551.6	551.8	551.8
122.5°	588.4	588.8	589.2	589.6	590.0	590.6	591.1	591.8	592.3	592.9	592.7
125°	646.3	647.7	649.1	650.5	651.8	652.6	652.8	653.1	653.3	653.6	653.1
127.5°	708.0	708.8	709.6	710.3	711.1	711.6	711.9	712.2	712.5	712.7	712.5
130°	745.0	746.2	747.3	748.5	749.6	750.4	750.8	751.3	751.7	752.2	751.9
132.5°	782.0	783.9	785.8	787.6	789.5	790.4	790.3	790.2	790.1	790.0	789.8
135°	840.6	841.9	843.3	844.7	846.1	846.8	847.1	847.3	847.6	847.8	847.8
137.5°	895.6	897.0	898.3	899.6	900.9	901.8	902.4	902.9	903.4	903.9	904.1
140°	931.0	932.2	933.3	934.5	935.6	936.4	937.2	937.9	938.5	939.2	939.7
142.5°	966.4	967.3	968.3	969.2	970.2	971.1	971.9	972.8	973.7	974.5	974.9
145°	1018.4	1019.2	1020.2	1021.0	1022.0	1022.8	1023.5	1024.1	1024.8	1025.6	1025.6
147.5°	1066.4	1066.9	1067.5	1067.9	1068.4	1069.0	1069.5	1070.1	1070.6	1071.2	1071.7
150°	1098.5	1098.3	1098.0	1097.8	1097.6	1097.9	1098.8	1099.8	1100.7	1101.6	1101.6
152.5°	1124.8	1125.1	1125.5	1125.8	1126.1	1126.4	1126.8	1127.1	1127.5	1127.9	1128.5
155°	1165.3	1165.3	1165.3	1165.3	1165.3	1165.4	1165.6	1165.9	1166.1	1166.3	1167.2
157.5°	1201.4	1200.9	1200.5	1199.9	1199.4	1199.3	1199.5	1199.8	1200.0	1200.2	1201.1
160°	1222.8	1222.2	1221.5	1220.8	1220.1	1219.9	1220.1	1220.4	1220.5	1220.8	1221.7
162.5°	1241.7	1241.3	1240.7	1240.2	1239.8	1239.5	1239.5	1239.6	1239.6	1239.7	1240.8
165°	1267.0	1266.5	1266.1	1265.7	1265.2	1265.1	1265.3	1265.5	1265.7	1266.0	1266.9
167.5°	1288.4	1287.5	1286.6	1285.6	1284.8	1284.3	1284.3	1284.3	1284.3	1284.3	1285.6
170°	1299.9	1299.0	1298.1	1297.2	1296.2	1295.8	1295.8	1295.8	1295.8	1295.8	1297.2
172.5°	1308.1	1307.2	1306.3	1305.4	1304.5	1304.0	1304.0	1304.0	1304.0	1304.0	1305.4
175°	1317.4	1316.4	1315.6	1314.6	1313.8	1313.3	1313.3	1313.3	1313.3	1313.3	1314.6
177.5°	1322.1	1321.4	1320.6	1319.9	1319.1	1318.7	1318.5	1318.3	1318.2	1318.0	1319.1
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	796.9	796.9	796.9	796.9	796.9	796.9	796.9	796.9
2.5°	794.2	795.3	796.4	796.9	796.8	796.6	796.5	796.5
5°	789.3	790.7	792.0	792.6	792.3	792.0	791.8	791.5
7.5°	779.5	780.5	781.4	781.7	781.4	781.1	780.9	780.5
10°	771.2	771.6	772.1	772.1	771.6	771.2	770.8	770.4
12.5°	759.5	759.8	760.0	759.9	759.2	758.7	758.0	757.4
15°	740.1	739.9	739.8	739.1	737.9	736.7	735.5	734.3
17.5°	715.9	715.2	714.5	713.7	712.7	711.7	710.7	709.7
20°	698.1	697.4	696.7	695.8	694.6	693.4	692.2	690.9
22.5°	680.4	679.1	677.8	676.6	675.7	674.6	673.7	672.6
25°	651.4	649.7	647.9	646.3	644.8	643.3	641.9	640.4
27.5°	620.0	617.6	615.1	613.2	611.8	610.4	609.0	607.5
30°	597.5	594.5	591.4	589.2	588.0	586.8	585.7	584.5
32.5°	575.7	572.4	568.9	566.5	564.9	563.4	561.9	560.4
35°	541.8	537.9	534.0	531.2	529.3	527.4	525.5	523.6
37.5°	506.3	501.6	496.9	493.7	491.9	490.1	488.3	486.5
40°	482.8	477.7	472.6	469.3	467.7	466.0	464.5	462.9
42.5°	459.6	454.7	449.9	446.2	443.9	441.6	439.2	436.9
45°	422.6	417.3	411.9	408.3	406.3	404.3	402.3	400.3
47.5°	386.1	380.6	375.1	371.2	369.0	366.8	364.6	362.3
50°	361.3	355.7	350.1	346.3	344.3	342.3	340.2	338.3
52.5°	337.9	331.8	325.7	321.7	319.7	317.7	315.7	313.7
55°	302.1	296.1	290.1	286.1	283.9	281.8	279.6	277.5
57.5°	266.4	260.5	254.7	250.7	248.8	246.9	245.1	243.2
60°	242.8	236.9	231.1	227.1	225.1	223.1	221.1	219.1
62.5°	219.6	214.1	208.7	204.9	203.0	201.0	198.9	196.9
65°	185.5	180.1	174.8	171.1	169.1	167.2	165.1	163.1
67.5°	153.0	148.1	143.1	139.9	138.3	136.7	135.1	133.5
70°	131.3	127.2	123.0	120.2	118.6	117.0	115.3	113.8
72.5°	111.3	107.4	103.6	101.2	100.1	99.0	98.0	96.9
75°	83.2	80.2	77.3	75.3	74.5	73.5	72.6	71.6
77.5°	59.2	57.1	55.1	53.7	53.0	52.3	51.7	50.9
80°	44.5	43.3	42.1	41.4	41.1	40.9	40.6	40.3
82.5°	33.3	32.7	32.2	31.8	31.7	31.5	31.4	31.2
85°	19.0	18.9	18.7	18.6	18.5	18.3	18.2	18.1
87.5°	10.9	11.2	11.4	11.6	11.6	11.6	11.6	11.6
90°	18.7	19.9	21.0	21.9	22.6	23.3	24.0	24.6
92.5°	42.5	44.0	45.5	46.5	47.0	47.5	48.0	48.5
95°	82.3	83.9	85.6	86.5	87.0	87.5	87.9	88.4
97.5°	129.0	130.5	132.0	132.9	133.2	133.5	133.7	134.0
100°	161.4	163.3	165.4	166.7	167.2	167.6	168.1	168.5
102.5°	194.6	196.8	199.1	200.5	201.1	201.8	202.4	203.0
105°	248.3	249.7	251.0	252.1	252.8	253.5	254.1	254.8
107.5°	306.3	307.0	307.8	308.1	308.0	307.9	307.9	307.8
110°	346.7	347.3	348.0	348.2	348.0	347.8	347.5	347.3



TEST NUMBER: P333675-927

CATALOG NUMBER: S125RDIW-S610D1340U927-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	387.0	387.3	387.6	387.6	387.2	386.8	386.3	386.0
115°	448.6	448.4	448.1	447.9	447.7	447.4	447.3	447.0
117.5°	510.2	510.4	510.6	510.2	509.4	508.4	507.6	506.6
120°	551.8	551.8	551.8	551.4	550.4	549.5	548.6	547.7
122.5°	592.6	592.4	592.2	591.8	591.0	590.3	589.5	588.8
125°	652.6	652.2	651.7	651.4	651.2	650.9	650.7	650.5
127.5°	712.3	712.0	711.9	711.5	711.1	710.6	710.1	709.6
130°	751.7	751.5	751.3	750.9	750.5	750.0	749.6	749.1
132.5°	789.6	789.3	789.1	788.7	788.1	787.3	786.7	786.1
135°	847.8	847.8	847.8	847.3	846.4	845.5	844.5	843.7
137.5°	904.4	904.7	905.0	904.5	903.4	902.2	901.1	900.0
140°	940.2	940.6	941.0	940.7	939.5	938.4	937.3	936.1
142.5°	975.1	975.4	975.7	975.3	974.1	973.0	971.8	970.7
145°	1025.6	1025.6	1025.6	1025.2	1024.5	1023.8	1023.1	1022.5
147.5°	1072.2	1072.8	1073.3	1072.9	1071.3	1069.8	1068.2	1066.7
150°	1101.6	1101.6	1101.6	1101.4	1100.9	1100.4	1099.9	1099.5
152.5°	1128.9	1129.5	1130.0	1130.0	1129.1	1128.3	1127.4	1126.6
155°	1168.2	1169.0	1170.0	1169.8	1168.7	1167.6	1166.4	1165.3
157.5°	1202.1	1202.9	1203.9	1203.6	1202.1	1200.6	1199.0	1197.5
160°	1222.6	1223.5	1224.4	1224.3	1223.2	1222.0	1220.9	1219.7
162.5°	1241.9	1242.9	1244.0	1244.0	1242.6	1241.3	1240.0	1238.7
165°	1267.8	1268.8	1269.6	1269.4	1268.0	1266.7	1265.3	1263.9
167.5°	1287.1	1288.4	1289.8	1289.8	1288.3	1286.9	1285.5	1284.0
170°	1298.5	1299.9	1301.2	1301.2	1299.6	1298.0	1296.3	1294.7
172.5°	1306.8	1308.1	1309.5	1309.5	1308.1	1306.6	1305.2	1303.8
175°	1316.0	1317.4	1318.7	1318.6	1317.0	1315.4	1313.8	1312.2
177.5°	1320.2	1321.3	1322.4	1322.3	1321.0	1319.7	1318.4	1317.2
180°	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5	1320.5

(END OF REPORT)